

Brilliance



Application illustration only, subject lamps not used in photo.



GE LED Decorative Lamps

GE's LED Decorative Lamps now use a design-inspired crown diffuser to cast light more similar to traditional incandescent candles and globes. This creates better light distribution and adds more brilliance to decorative fixtures where the lamp is visible, such as chandeliers, pendants, and sconces.

LOW-COST OPERATION

- Uses 87% Less energy than incandescent
- For example, using only 6.5 watts of energy, saves over \$88 in energy costs over the rated life of a lamp versus a standard 60 watt incandescent lamp based on \$0.11 per kWh and provides similar light output (550 vs 650 lumens)
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources

COLOR RENDERING

- Available with a CRI of 80 - 82
- Candles have "sparkle" similar to incandescent

COLOR TEMPERATURE

- Halogen-like color
- Available in 2400K, 2700K and 5000K

LONG LIFE

- 15,000 hour rated life (L70)
- Lasts 15X longer than incandescent/halogen (1,000 hrs)

DIMMABLE

- Dims from 100% to 10%

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

GE QUALITY AND RELIABILITY

- 3-year limited warranty

ecomaginationSM





To learn more about saving money and energy, go to: <http://products.currentbyge.com>.

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

current
powered by GE



GE LED Decorative Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty*	MOL (in)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
Candles																	
	MED	4	75554	LED4DCAMCF/824	120	6	4.2	250		2400	80	25W	15,000	Yes		Damp	Clear, Bent tip
			21250	LED4DCAM-C3/827	120	6	4.2	300		2700	80	40W	15,000	Yes	★	Damp	Clear, Bent tip
			69111	LED4DCAM-C3/850	120	6	4.2	300		5000	80	40W	15,000	Yes	★	Damp	Clear, Bent tip
	CAND	4	92389	LED4DCAM-W3/827	120	6	4.2	300		2700	80	40W	15,000	Yes	★	Damp	White, Bent tip
			21251	LED7DCAM-C3/827	120	6	4.8	500		2700	80	60W	15,000	Yes	★	Damp	Clear, Bent tip
75553			LED4DCACCF/824	120	6	4.3	250		2400	80	25W	15,000	Yes	★	Damp	Clear, Bent tip	
21231			LED4DCAC-C3/827	120	6	4.3	300		2700	80	40W	15,000	Yes	★	Damp	Clear, Bent tip	
	CAND	4	75553	LED4DCACCF/824	120	6	4.3	250		2400	80	25W	15,000	Yes	★	Damp	Clear, Bent tip
			21231	LED4DCAC-C3/827	120	6	4.3	300		2700	80	40W	15,000	Yes	★	Damp	Clear, Bent tip
			69109	LED4DCAC-C3/850	120	6	4.3	300		5000	80	40W	15,000	Yes	★	Damp	Clear, Bent tip
			92388	LED4DCAC-W3/827	120	6	4.3	300		2700	80	40W	15,000	Yes	★	Damp	White, Bent tip
			21233	LED7DCAC-C3/827	120	6	4.8	500		2700	80	60W	15,000	Yes	★	Damp	Clear, Bent tip
Globes																	
	MED	4.5	68172	LED4DG25M-C/TP	120	3	4.3	280		2700	82	25W	15,000	Yes		Damp	Clear
			21253	LED5DG25-W3/827	120	6	4.3	350		2700	80	40W	15,000	Yes	★	Damp	White
			21255	LED7DG25-W3/827	120	6	4.3	500		2700	80	60W	15,000	Yes	★	Damp	White
	CAND	4	39702	LED4DG16C-C3-OT	120	3	3.0	270		2700	80	25W	15,000	Yes	★	Damp	White
			39716	LED4DG16C-W3-OT	120	3	3.0	270		2700	80	25W	15,000	Yes	★	Damp	White

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in /TP* indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.

ecomaginationSM



Product is compliant with material restriction requirements of RoHS

ENERGY STAR® is a registered U.S. mark

current
powered by GE

<http://products.currentbyge.com>

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2017 GE.

