

WAC LIGHTING

2016 January New Products


Table of Contents

InvisiLED®		
Symmetrical Recessed Channel	New	2
Asymmetrical Recessed Channel	New	3
Indirect Recessed Channel	New	4
InvisiLED® Pro 3	New	5
InvisiLED® Pro 2	New	6
<hr/>		
LED Recessed		
Duo	New	8
Aether	New	10
Summit 2.0	New	11
Tesla		13
Precision Multiples		21
Mini Multiple Spots	New	24
<hr/>		
LED Track		
W Track Current Limiter		25
W Track Quick Connect™ Adapter		26
H Track Current Limiter	New	27
Paloma		28
Exterminator II		29
Exterminator		32
Summit		33
Precision		35
LED Track Luminaires		36
<hr/>		
LED Task		
InvisiLED® Lite	New	37
InvisiLED® Pro2	New	38
InvisiLED® Pro3	New	39
InvisiLED® Mounting Accessories	New	40
Touch and Occupancy Control Kit		41
LED90 Edge Lit Button Light	New	42
LINE		43
Light Bars		45
<hr/>		
LED Exterior		
Recessed Inground + Indicator	New	47
Step Lights	New	51
Endurance™	New	53
Tube Architectural	New	59
Tube		63
Scoop		67
Rubix		68
<hr/>		
LED Decorative		
Disc	New	71
Flo	New	72
Glo		73
Blo	New	74
Vector		75
Monterrey		77
<hr/>		
Dweled	New	79-132



Symmetrical Recessed Channel


- Installs within drywall depth
- Linear channel can be field cut
- Accommodates either one or two runs of InvisiLED® indoor tape
- Includes a translucent white acrylic diffuser
- Dense foam insert for spackling



8 ft linear channel

LED-T-RCH1-WT


Includes an end cap and diffuser



Power feed

LED-T-RBOX1-WT


*Includes a wiring box, two hanger bars, two five-pin InvisiLED® adapters, an end cap and diffuser
The end cap may be placed on either side or be removed
Hanger bars may be installed on any side of the wiring box*



Lateral corner

LED-T-CTC1-WT


Includes diffuser



Perpendicular corner

LED-T-WTC1-WT


*Transitions between walls or wall to ceiling
Includes diffuser*



Outside corner


LED-T-WTW1-WT

*Transitions around columns, bump outs, or soffits
Includes diffuser*



Asymmetrical Recessed Channel


- Installs within drywall depth
- Linear channel can be field cut
- Accommodates one run of InvisiLED® indoor tape
- Dense foam insert for spackling
- Recommended installation within 15 inches of surface to be illuminated



8 ft linear channel

Includes two end caps


LED-T-RCH2-WT



Power feed



Includes a wiring box, two hanger bars, a five-pin InvisiLED® adapter, and two end caps
The end cap may be placed on either side or be removed
Hanger bars may be installed on any side of the wiring box

LED-T-RBOX2-WT




Indirect Recessed Channel

- Linear channel can be field cut
- Accommodates up to two runs of InvisiLED® indoor tapes
- Dense foam insert for spackling



8ft linear channel
Includes an end cap


LED-T-RCH3-WT



Power feed

LED-T-RBOX3-WT


Includes a wiring box, two hanger bars, two five-pin InvisiLED® adapters, and one end cap
The end cap may be placed on either side or be removed
Hanger bars may be installed on any side of the wiring box



Pro3 InvisiLED® New Product

Power: 5W / ft
Lumens: Up to 475 lm / ft
CRI: 90
Rated Life: 70,000 hours

- Can be inside a recessed channel to use as cove, wallwash, and downlight
- Brightest InvisiLED® system available
- Laterally bendable design
- CEC Title 24 Compliant
- UL listed for damp location
- May be field cut every 6 inches at the end of a run
- Includes an end cap and a male to male connector with each tape section
- Specially rated for installation in the storage area of a clothes closet
- ELV dimming - see specification sheet for list of tested dimmers



Tape Selections

System	Color Temp	CRI	Length	Qty	Finish
LED-TE24	27 2700K	95	6IN 6 inches	1	WT White
	30 3000K	95	1 1 foot	1	
	35 3500K	90	5 5 feet	1	
	45 4500K	90	1-40 1 foot	40	

Example: **LED-TE2435-6IN-WT**

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	12 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	20 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	20 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	12 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	20 feet	Yes

Accessories

For mounting accessories, please see page 40



Lead Wire	LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies	
Extension Cable	LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section	
Low Voltage Wiring Box With Feed	LED-TC-B-2	L: 1½ in W: ¾ in H: 7/8 in	Neatly houses up to two wires with 2" female feed
Low Voltage Wiring Box	LED-T-B	L: 1½ in W: ¾ in H: 7/8 in	Neatly houses up to two wires
Wiring Box With Switch	TB-S	L: 6¼ in W: 15/8 in H: 1¼ in	Use when spanning a large gap in a system layout without leaving exposed wiring
Joiner Cable	LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in	Connects tape sections	
3-Way "Y" Connector	LED-TC-Y	Connects tape sections	
4-Way "X" Connector	LED-TC-X	Connects tape sections	
"L" Connector	LED-TC-L	Connects tape sections	
End cap	LED-TC-EC	1 cut end cap 1 male end cap	

Pro2 InvisiLED®

New 2200K Color Temperature

Power: 4W / ft
Lumens: Up to 330 lm / ft
CRI: 90
Rated Life: 80,000 hours

- Can be inside a recessed channel to use as accent, indicator or wayfinding light
- CEC Title 24 Compliant
- UL listed for damp location
- May be field cut every 6 inches at the end of a run
- Includes an end cap
- Specially rated for installation in the storage area of a clothes closet
- ELV dimming - see specification sheet for list of tested dimmers



Tape Selections

System	Color Temp	Length	Qty	Finish
LED-TX24	22 2200K	6IN 6 inches	1	WT White
	27 2700K		1	
	30 3000K		1	
	35 3500K		1	
	45 4500K		40	

Example: **LED-TX2435-6IN-WT**

"L" Connector

System	Color Temp	Finish
LED-TX24	22 2200K	5L-WT White
	27 2700K	
	30 3000K	
	35 3500K	
	45 4500K	

Example: **LED-TX2435-5L-WT**

Each "L" connector consumes 2 watt

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	15 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	25 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	25 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	15 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	25 feet	Yes

Accessories


For mounting accessories, please see page 40

Lead Wire		LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies
Extension Cable		LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section
Low Voltage Wiring Box With Feed		LED-TC-B-2	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires with 2" female feed
Low Voltage Wiring Box		LED-T-B	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires
Wiring Box With Switch		TB-S	L: 6 1/4 in W: 1 5/8 in H: 1 1/4 in Use when spanning a large gap in a system layout without leaving exposed wiring


Joiner Cable		LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in	Connects tape sections
3-Way "Y" Connector		LED-TC-Y	Connects tape sections
4-Way "X" Connector		LED-TC-X	Connects tape sections
"L" Connector		LED-TC-L	Connects tape sections
End cap		LED-TC-EC	1 cut end cap 1 male end cap

Set the right atmosphere



Depending on the activity, the lighting theme can change from bright to dim, crisp white to warmer tone, and from spot to ambient distribution all in one luminaire, just by adjusting your regular dimmer. Specify in multi-functional residential or commercial spaces, television rooms, or areas with heavy visual display usage.



Spot light distribution
High brightness
Crisp white light color



Ambient light distribution
Lower brightness
Warm white color




3" Duo™ New Product

Glare Reducing Dual-source LED Downlight



A spot light at the maximum light output for task becomes a wide distribution ambient light source as it dims down



Input: 120V
Power: 15W
Rated Life: 50,000 hours

- Reduces overhead glare in the aperture with a warm dimming mixing chamber
- Offered in two warm dimming CCT ranges from 2700K to 2200K and 3000K to 2200K
- CEC Title 24 compliant
- 52° cut-off angle
- ELV dimming - see specification sheet for list of tested dimmers
- Patent pending

Trims (Order Housing Separately)

	At the brightest output				At the lowest output				
	Color Temp	Lumen	Beam Spread	CRI	Color Temp	Lumen	Beam Spread	CRI	
	HR3D-RO92722S-WT	2700K	810	20°	90+	2200K	15	120°	90+
	HR3D-RO93022S-WT	3000K	890	20°	90+	2200K	15	120°	90+

Housings (Required)

	Model	Input	Notes
	HR3D-2015-NICA New Construction IC-Rated, Airtight	120V	Ceiling thickness: 1/2"–1"
	HR3D-2015-RA Remodel Non-IC, Airtight	120V	Ceiling thickness: 1/2"–1"




3.5"

Fits in tight plenums

with complex HVAC ducts, sprinkler pipes and conduit runs



Aether™
3.5" Shallow IC
LED Downlight



Aether™ Now available as IC standard









3.5" Shallow IC LED Downlight

Power: 22.5W
Delivered Lumens: Up to 1375
Comparable to: 75W MR16
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 50,000 hours





Designed to fit in tight plenum

- Narrow IC Housing
- Energy Star® rated
- Wet location listed
- 3.5" trim aperture and 3.5" housing height
- 35° cut-off angle
- Universal input voltage (120V-220V-277V)
- Ceiling thickness: ½" - 1½"
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

		HR-3LED-T120-WT <i>Round</i>
		HR-3LED-T720-WT <i>Square</i>
		HR-3LED-TL220-WT <i>Round Trimless</i>
		HR-3LED-TL820-WT <i>Square Trimless</i>

Housings

	Beam	Max CBCP	Max Lumen	Color Temp	CRI
 	HR-3LED-H20A <i>New Construction IC-rated, Airtight</i>				
	N 25°	4480	1375	927 2700K	90
 	F 40°	2555	1315	27 2700K	85
				930 3000K	90
				30 3000K	85
				35 3500K	85
			40 4000K	85	

Example: **HR-3LED-H20A-F-930**



Summit™ 2.0 3.5" LED IC-Rated New Product

Power:	14.5W	<ul style="list-style-type: none"> ACLED IC-rated downlight Integral housing and trim, no driver needed Single spot light source 30° Visual cutoff angle for glare control Ceiling thickness: ½" - ¾" ELV dimming - see specification sheet for list of tested dimmers 	<ul style="list-style-type: none"> Energy Star® rated Title 24 Compliant ETL&cETL wet location listed
Comparable to:	50W MR16		
ELV Dimming:	100%-10%		
Input:	120V		
Beam Angle:	45°		
Rated Life:	50,000 hours		

Trims and Housing

		Lumen	Color Temp	CRI
	<p>HR35-ICR30F-WT Round Trim New Construction IC-Rated, Airtight</p>	910	3000K	90
	<p>HR35-ICS30F-WT Square Trim New Construction IC-Rated, Airtight</p>	895	3000K	90



Summit™ 2.0 3.5" LED Non-IC New Product

Power:	14.5W	<ul style="list-style-type: none"> ACLED non-IC downlight Configurable for both new construction and remodel Integral housing and trim, no driver needed Single spot light source 30° Visual cutoff angle for glare control Ceiling thickness: ½" - ¾" ELV dimming - see specification sheet for list of tested dimmers 	<ul style="list-style-type: none"> Energy Star® rated Title 24 Compliant ETL&cETL wet location listed
Comparable to:	50W MR16		
ELV Dimming:	100%-10%		
Input:	120V		
Beam Angle:	45°		
Rated Life:	50,000 hours		

Trims and Housing

		Lumen	Color Temp	CRI	
		<p>HR35-R30F-WT <i>Round Trim</i> New Construction and Remodel Non-IC, Airtight</p>	910	3000K	90
		<p>HR35-S30F-WT <i>Square Trim</i> New Construction and Remodel Non-IC, Airtight</p>	895	3000K	90

Tesla Pro 2" LED

















Delivered Lumens: Up to 1090
Comparable to: 50W MR16
Power: 14.5W
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 50,000 hours

High Output LED

- Wet and damp location listed
- Energy Star® rated
- CEC Title 24 Compliant (see website for list of models)
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- Universal input voltage (120V-220V-277V)
- 2" aperture
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

Trims (Order Housing Separately)		Beam	Color Temp	CRI	Finish
		HR2LD-ET109P High Brightness Wet Location Listed Energy Star® 9° visual cutoff	N 30° F 55°		
		HR2LEDT109P Open Reflector Energy Star®	N 27° F 40°		
		HR2LEDT309P 0°- 30° Adjustable Energy Star®	N 27° F 40°		
		HR2LEDT409P 30°- 45° Adjustable Energy Star®	N 27° F 40°	827 2700K 85 927 2700K 90 830 3000K 85 930 3000K 90 835 3500K 85 840 4000K 85	BN Brushed Nickel CB Copper Bronze WT White
		HR2LEDT209P Shower Light Wet Location Listed Energy Star®	N 27°		
		HR2LEDT709P Open Reflector Energy Star®	N 30° F 45°		
		HR2LEDT509P 0°- 30° Adjustable Energy Star®	N 30° F 45°		

Example: **HR2LEDT109PF835BN**

Replacement Modules

Reflectors with different beam spreads and LED modules with different color temperatures may be ordered separately

Reflectors

Narrow Flood **SL-REF-BL10-1-N**
 Flood **SL-REF-BL10-1-F**

LED

2700K 85 CRI **BXRC-27E1000-B-03**
 2700K 90 CRI **BXRC-27G1000-B-03**
 3000K 85 CRI **BXRC-30E1000-B-03**
 3000K 90 CRI **BXRC-30G1000-B-03**
 3500K 85 CRI **BXRC-35E1000-B-03**
 4000K 85 CRI **BXRC-40E1000-B-03**

Chicago Plenum

Chicago Plenum housings add extra building safety features that confine airflow in and out of the housing with elastomer gasket

Tesla Pro 2" Housing

Housings (Required)	Model	Input	Notes
<p><i>Adjustable New Construction</i></p>	<p>HR-2LED-H09D-ICA <i>IC-Rated, Airtight</i></p>	120V-277V	<p>Allows adjustment in any direction when used with adjustable trims</p>
<p><i>Remodel</i></p>	<p>HR-2LED-R09D-A <i>Non-IC, Airtight</i></p>	120V-277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2"–1"</p> <p>Does not accommodate adjustments</p>
<p><i>Adjustable Remodel</i></p>	<p>HR-2LED-R14D <i>Non-IC</i></p>	120V-277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2"–5/8"</p>

















Tesla 2" LED



Delivered Lumens: Up to 730
Comparable to: 50W MR16
Power: 14.5W
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 90,000 hours

- Universal input voltage (120V-220V-277V)
- Wet and damp location listed
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- 2" aperture
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

		Beam	Color Temp	CRI	Finish
		HR-2LD-ET109 <i>Wet Location Listed</i> <i>Energy Star®</i> <i>9° visual cutoff</i>	S 16.5° N 30° F 53°		
		HR-2LED-T109 <i>Open Reflector</i>			
		HR-2LED-T309 <i>0°-30° Adjustable</i>	S 15° N 26° F 45°		
		HR-2LED-T409 <i>30°-45° Adjustable</i>	27 2700K 85 9W 3000K 90 W 3000K 85 35 3500K 85 C 4000K 85		BN Brushed Nickel CB Copper Bronze WT White
		HR-2LED-T209 <i>Shower Light</i> <i>Wet Location Listed</i>	N 26°		
		HR-2LED-T709 <i>Open Reflector</i>	S 15° N 26° F 45°		
		HR-2LED-T509 <i>0°-30° Adjustable</i>			

Example: **HR-2LD-ET109F-9W-BN**

Replacement Modules

Reflectors with different beam spreads and LED modules with different color temperatures may be ordered separately

Reflectors

Spot	SL-REF-LUX10-S
Narrow Flood	SL-REF-LUX10-N
Flood	SL-REF-LUX10-F




LED

2700K	85 CRI	LXS8-PW27
3000K	90 CRI	LXS9-PW30
3000K	85 CRI	LXS8-PW30
3500K	85 CRI	LXS8-PW35
4000K	85 CRI	LXS8-PW40

Chicago Plenum

Chicago Plenum housings add extra building safety features that confine airflow in and out of the housing with elastomer gasket

Tesla 2" Housing

Housings (Required)	Model	Input	Notes
<p><i>Adjustable New Construction</i></p> 	<p>HR-2LED-H09D-ICA <i>IC-Rated, Airtight</i></p>	<p>120V-277V</p>	<p><i>Allows adjustment in any direction when used with adjustable trims</i></p>
<p><i>Remodel</i></p> 	<p>HR-2LED-R09D-A <i>Non-IC, Airtight</i></p>	<p>120V-277V</p>	<p><i>Requires 3" of clearance from insulation on all sides</i></p> <p><i>Ceiling thickness: 1/2" - 1"</i></p> <p><i>Does not accommodate adjustments</i></p>
<p><i>Adjustable Remodel</i></p> 	<p>HR-2LED-R14D <i>Non-IC</i></p>	<p>120V-277V</p>	<p><i>Allows adjustment in any direction when used with adjustable trims</i></p> <p><i>Requires 3" of clearance from insulation on all sides</i></p> <p><i>Ceiling thickness: 1/2" - 5/8"</i></p>



Tesla Pro 3.5" LED

























Power: 22W
Delivered Lumens: Up to 1460
Comparable to: 75W MR16
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 50,000 hours

High Output LED






- Universal input voltage (120V-220V-277V)
- All Energy Star® rated
- Wet and Damp location listed
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- 3.5" aperture
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

Trims (Order Housing Separately)		Beam	Color Temp	CRI	Finish	Reflector/Trim
	 3 1/2" x 5 1/4"	HR3LD-ET118P High Brightness Wet Location Listed Energy Star® 9° visual cutoff	F 48°	827 2700K 85 927 2700K 90 830 3000K 85 930 3000K 90 835 3500K 85 840 4000K 85	BN Brushed Nickel CB Copper Bronze WT White	
	 3 1/2" x 5 1/4"	HR3LEDT118P Downlight Energy Star®	N 30° F 55°	827 2700K 85 927 2700K 90 830 3000K 85 930 3000K 90 835 3500K 85 840 4000K 85	HBN Haze/Brushed Nickel HCB Haze/Copper Bronze HWT Haze/White BBN Specular Black/Brushed Nickel BCB Specular Black/Copper Bronze BWT Specular Black/White BN Brushed Nickel CB Copper Bronze WT White	
	 3 1/2" x 5 1/4"	HR3LEDT318P 0°- 30° Adjustable Energy Star®	N 30° F 55°	827 2700K 85 927 2700K 90 830 3000K 85 930 3000K 90 835 3500K 85 840 4000K 85	BN Brushed Nickel CB Copper Bronze WT White	
	 3 1/2" x 5 1/4"	HR3LEDT418P 30°- 45° Adjustable Energy Star®	N 26° F 38°			
	 3 1/2" x 5 1/4"	HR3LEDT218P Shower Light Wet Location Listed Energy Star®	N 30°			
	 2 7/8" x 5 1/4"	HR3LEDT718P Open Reflector Energy Star®	N 30° F 52°	827 2700K 85 927 2700K 90 830 3000K 85 930 3000K 90 835 3500K 85 840 4000K 85	BN Brushed Nickel CB Copper Bronze WT White	
	 2 7/8" x 5 1/4"	HR3LEDT518P 0°- 30° Adjustable Energy Star®	N 30° F 52°			
	 2 7/8" x 5 1/4"	HR3LEDT918P 30°- 45° Adjustable Energy Star®	N 26° F 38°			
	 2 7/8" x 5 1/4"	HR3LEDT818P Shower Light Wet Location Listed Energy Star®	N 30°			

Example: **HR3LD-ET118PF930BN**

Tesla Pro 3.5" Housing

Housings (Required)	Model	Input	Notes
<p><i>Narrow New Construction</i></p>  <p>21" (total width), 5 5/8" (depth), 6" (height), 4 5/8" (width to center), 18 3/8" (width to center), Min 14 1/2" (height to center), Max 24 1/2" (height to center), 10 1/8" (height to center), 5" (width to center)</p>	<p>HR-3LED-H18D1-ICA IC-Rated, Airtight</p>	120V -277V	<p>Allows adjustment in one direction when used with HR3LEDT918P</p>
	<p>HR-3LED-H18D1-ICAC IC-Rated, Airtight Chicago Plenum</p>	120V -277V	<p>Does not accommodate HR3LEDT418P</p> <p>Ceiling thickness: 1/2" - 3/4"</p>
<p><i>Adjustable New Construction</i></p>  <p>19 3/8" (total width), 6" (depth), 6 3/8" (height), 4 5/8" (width to center), 16 3/4" (width to center), Min 14 1/2" (height to center), Max 24 1/2" (height to center), 14 1/8" (height to center), 6 3/8" (width to center)</p>	<p>HR-3LED-H18D-ICA IC-Rated, Airtight</p>	120V -277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Ceiling thickness: 1/2" - 3/4"</p>
	<p>HR-3LED-H18D-ICAC IC-Rated, Airtight Chicago Plenum</p>	120V -277V	
	<p>HR-3LED-H18D-EMICA IC-Rated, Airtight Emergency Backup Battery</p>	120V	
<p><i>New Construction</i></p>  <p>6 3/4" (depth), 4 3/8" (width to center), 5 1/2" (height to center), 8 1/4" (height to center), Min 14 1/2" (height to center), Max 24 1/2" (height to center)</p>	<p>HR-3LED-H18D-A Non-IC, Airtight</p>	120V -277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2" - 1"</p> <p>Does not accommodate adjustments</p>
<p><i>Remodel</i></p>  <p>6 5/8" (depth), 4 3/8" (width to center), 16 1/2" (width to center)</p>	<p>HR-3LED-R18D-A Non-IC, Airtight</p>	120V -277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2" - 1"</p> <p>Does not accommodate adjustments</p>
<p><i>Adjustable Remodel</i></p>  <p>3/4" (depth), 24" max (width to center), 5 1/2" (width to center), 1 1/2" (height to center)</p>	<p>HR-3LED-R22D Non-IC</p>	120V -277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2" - 5/8"</p>

Replacement Modules

Reflectors with different beam spreads and LED modules with different color temperatures may be ordered separately

Reflectors

Narrow Flood	SL-REF-BL10-1-N
Flood	SL-REF-BL10-1-F

LED

2700K	85 CRI	BXRC-27E1000-B-03
2700K	90 CRI	BXRC-27G1000-B-03
3000K	85 CRI	BXRC-30E1000-B-03
3000K	90 CRI	BXRC-30G1000-B-03
3500K	85 CRI	BXRC-35E1000-B-03
4000K	85 CRI	BXRC-40E1000-B-03

Chicago Plenum

Chicago Plenum housings add extra building safety features that confine airflow in and out of the housing with elastomer gasket





















Tesla 3.5" LED



Power: 21.5W
Delivered Lumens: Up to 1070
Comparable to: 75W MR16
ELV Dimming: 100%-15% (120V Only)
0-10V Dimming: 100%-10%
Rated Life: 50,000 hours






- Damp location listed (Shower Light is wet location listed)
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- Universal driver (120V-220V-277V)
- ELV dimming - see specification sheet for list of tested dimmers

Trims (Order Housing Separately)

	Beam	Color Temp	CRI	Finish	Reflector/Trim
  <p>HR-3LD-ET118 Round Downlight Energy Star® 9° visual cutoff</p>	F 40°	27 2700K 85 9W 3000K 90 W 3000K 85 35 3500K 85 C 4000K 85		BN CB WT	Brushed Nickel/Brushed Nickel Copper Bronze/Copper Bronze White/White
  <p>HR-3LED-T118 Round Downlight</p>	S 15° N 28° F 50°	27 2700K 85 9W 3000K 90 W 3000K 85 35 3500K 85 C 4000K 85		HZ/BN HZ/CB HZ/WT SB/BN SB/CB SB/WT BN CB WT	Haze/Brushed Nickel Haze/Copper Bronze Haze/White Specular Black/Brushed Nickel Specular Black/Copper Bronze Specular Black/White Brushed Nickel/Brushed Nickel Copper Bronze/Copper Bronze White/White
  <p>HR-3LED-T318 Round 0°- 30° Adjustable</p>					
  <p>HR-3LED-T618 Round Pin Hole, 0°- 30° Adjustable</p>	S 15°				
  <p>HR-3LED-T418 Round 30°- 45° Adjustable</p>	S 15° N 28° F 41°				
  <p>HR-3LED-T218 Round Shower Light Wet Location Listed</p>	N 28°				
  <p>HR-3LED-T718 Square Downlight</p>	S 15° N 28° F 50°	27 2700K 85 9W 3000K 90 W 3000K 85 35 3500K 85 C 4000K 85		BN CB WT	Brushed Nickel/Brushed Nickel Copper Bronze/Copper Bronze White/White
  <p>HR-3LED-T818 Square Shower Light Wet Location Listed</p>	N 28°				
  <p>HR-3LED-T518 Square 0°- 30° Adjustable</p>	S 15° N 28° F 50°				
  <p>HR-3LED-T918 Square 30°- 45° Adjustable</p>					

Example: **HR-3LED-T918F-W-CB**

Tesla 3.5" Housing

Housings (Required)	Model	Input	Notes
<p><i>Narrow New Construction</i></p>  <p>21" width, 6" height, 5 5/8" depth, 18 3/8" width, 10 7/8" height, 5" width, Min 14 1/2" Max 24 1/2" depth</p>	<p>HR-3LED-H18D1-ICA IC-Rated, Airtight</p>	120V -277V	<p>Allows adjustment in one direction when used with HR3LEDT918</p>
	<p>HR-3LED-H18D1-ICAC IC-Rated, Airtight Chicago Plenum</p>	120V -277V	<p>Does not accommodate HR3LEDT418</p> <p>Ceiling thickness: 1/2" - 3/4"</p>
<p><i>Adjustable New Construction</i></p>  <p>19 3/8" width, 6" height, 6 3/8" depth, 16 3/4" width, 14 1/8" height, 6 3/8" width, Min 14 1/2" Max 24 1/2" depth</p>	<p>HR-3LED-H18D-ICA IC-Rated, Airtight</p>	120V -277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Ceiling thickness: 1/2" - 3/4"</p>
	<p>HR-3LED-H18D-ICAC IC-Rated, Airtight Chicago Plenum</p>	120V -277V	
	<p>HR-3LED-H18D-EMICA IC-Rated, Airtight Emergency Backup Battery</p>	120V	
<p><i>New Construction</i></p>  <p>6 3/4" height, 4 3/8" width, 5 1/2" 8 1/4" depth, Min 14 1/2" Max 24 1/2" depth</p>	<p>HR-3LED-H18D-A Non-IC, Airtight</p>	120V -277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2" - 1"</p> <p>Does not accommodate adjustments</p>
<p><i>Remodel</i></p>  <p>6 5/8" height, 4 3/8" width, 16 1/2" width</p>	<p>HR-3LED-R18D-A Non-IC, Airtight</p>	120V -277V	<p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2" - 1"</p> <p>Does not accommodate adjustments</p>
<p><i>Adjustable Remodel</i></p>  <p>3/4" height, 24" max width, 5 1/2" width, 1 1/2" depth</p>	<p>HR-3LED-R22D Non-IC</p>	120V -277V	<p>Allows adjustment in any direction when used with adjustable trims</p> <p>Requires 3" of clearance from insulation on all sides</p> <p>Ceiling thickness: 1/2" - 5/8"</p>

Replacement Modules

Reflectors with different beam spreads and LED modules with different color temperatures may be ordered separately

Reflectors

Spot	SL-REF-LUX10-S
Narrow Flood	SL-REF-LUX10-N
Flood	SL-REF-LUX10-F

LED

2700K	85 CRI	LXS8-PW27
3000K	90 CRI	LXS9-PW30
3000K	85 CRI	LXS8-PW30
3500K	85 CRI	LXS8-PW35
4000K	85 CRI	LXS8-PW40

Chicago Plenum

Chicago Plenum housings add extra building safety features that confine airflow in and out of the housing with elastomer gasket

Precision Multiples 4" LED with ELV or 0-10V dimming options



Black trim shown





Comparable to: 75W MR16
 Rated Life: 50,000 hours

Retractable Spot Lights

- ELV and 0-10V dimming options
 - see specification sheet for list of tested dimmers
- Black, white, or Invisible Trim™ option
- Energy Star® rated
- CEC Title 24 Compliant
- Fully retractable from housing
- 355° horizontal rotation and 180° vertical aiming
- Accepts 1 replacement lens


1 Light

Trims

		MT-4LD116T Trim	WT White BK Black
		MT-4LD116TL-WT Invisible Trim™	

Example: **MT-4LD116T-WT**





Housings

Housings	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD116N 0-10V dimming Non-IC, 120V-277V input	16.5W	S 20° 1100 F 40° 1080	5370 2390	27 2700K 927 2700K 30 3000K 930 3000K 35 3500K 40 4000K	85	BK Black
	MT4LD116NE ELV dimming Non-IC, 120V input	16.5W	S 20° 1005 F 40° 990	4700 2115			
	MT4LD111NE ELV dimming IC-Rated, 120V input	11.5W	S 20° 890 F 40° 885	3925 1820			

Example: **MT4LD111NE-F930-BK**


2 Lights

Trims

		MT-4LD216T Trim	WT White BK Black
		MT-4LD216TL-WT Invisible Trim™	

Example: **MT-4LD216T-WT**

Housings

Housings	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD216N 0-10V dimming Non-IC, 120V-277V input	33W	S 20° 2200 F 40° 2160	5370x2 2390x2	27 2700K 927 2700K 30 3000K 930 3000K 35 3500K 40 4000K	85	BK Black
	MT4LD216NE ELV dimming Non-IC, 120V input	33W	S 20° 2010 F 40° 1980	4700x2 2115x2			
	MT4LD211NE ELV dimming IC-Rated, 120V input	23W	S 20° 1785 F 40° 1765	3928x2 1820x2			

Example: **MT-4LD216N-S927-BK**





Replacement Lens

Amber	LENS-16-AMB	
Blue	LENS-16-BLU	
Green	LENS-16-GRN	
Red	LENS-16-RED	
Yellow	LENS-16-YEL	

UV Filter	LENS-16-UVF	
Frosted	LENS-16-FR	
Spread	LENS-16-SPR	
Beam Elongator	LENS-16-BEL	


3 Lights

Trims

		MT-4LD316T Trim	WT White BK Black
		MT-4LD316TL-WT Invisible Trim™	

Example: **MT-4LD316T-WT**





Housings

	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD316N 0-10V dimming Non-IC, 120V-277V input 49.5W	S 20°	3300	5370x3	27 2700K 85 927 2700K 90	85	BK Black
		F 40°	3240	2390x3			
	MT4LD316NE ELV dimming Non-IC, 120V input 49.5W	S 20°	3015	4700x3	30 3000K 85 930 3000K 90	85	
	34.5W	S 20°	2680	3925x3	35 3500K 85 40 4000K 85	85	
MT4LD311NE ELV dimming IC-Rated, 120V input		F 40°	2650	1820x3			

Example: **MT4LD311NE-S30-BK**


4 Lights

Trims

		MT-4LD416T Trim	WT White BK Black
		MT-4LD416TL-WT Invisible Trim™	

Example: **MT-4LD416T-WT**





Housings

	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD416N 0-10V dimming Non-IC, 120V-277V input 66W	S 20°	4400	5370x4	27 2700K 85 927 2700K 90	85	BK Black
		F 40°	4320	2390x4			
	MT4LD416NE ELV dimming Non-IC, 120V input 66W	S 20°	4020	4700x4	30 3000K 85 930 3000K 90	85	
	46W	S 20°	3570	3925x4	35 3500K 85 40 4000K 85	85	
MT4LD411NE ELV dimming IC-Rated, 120V input		F 40°	3535	1820x4			

Example: **MT-4LD416N-S927-BK**


4 Lights (2x2)

Trims

		MT-4LD226T Trim	WT White BK Black
		MT-4LD226TL-WT Invisible Trim™	

Example: **MT-4LD226T-WT**

Housings

	Power	Beam	Lumens	CBCP	Color Temp	CRI	Interior
	MT-4LD226N 0-10V dimming Non-IC, 120V-277V input 66W	S 20°	4400	5370x4	27 2700K 85 927 2700K 90	85	BK Black
		F 40°	4320	2390x4			
	MT4LD226NE ELV dimming Non-IC, 120V input 66W	S 20°	4020	4700x4	30 3000K 85 930 3000K 90	85	
	46W	S 20°	3570	3925x4	35 3500K 85 40 4000K 85	85	
MT4LD221NE ELV dimming IC-Rated, 120V input		F 40°	3535	1820x4			

Example: **MT4LD226NE-S930-BK**



Mini LED Multiple Spots



New Color Temperature options

Comparable: 50W MR16
Dimming: 100 - 10%
Rated Life: 50,000 hours
Input Voltage: 120V

- Integral housing and trim**
- Energy Star®
 - Individually adjustable luminaires
 - Complete unit includes housing & trim
 - 30° visual cutoff for glare control
 - ELV dimming - see specification sheet for list of tested dimmers




1 Light



			Power	Beam	Max Lumens	Max CBCP	Color Temp	CRI	Finish
	MT-3LD111NA <i>New Construction</i> <i>Non-IC, Airtight</i>		11W	F 25°	805	2224	927 2700K 90 930 3000K 90 935 3500K 90 940 4000K 90	90	BK White trim with black interior
				W 45°	795	1042			
	MT-3LD111R <i>Remodel</i> <i>Non-IC</i>		11W	F 25°	805	2224			
				W 45°	795	1042			
								WT White trim with white interior	

Example: **MT-3LD111NA-F927-WT**

2 Lights



			Power	Beam	Max Lumens	Max CBCP	Color Temp	CRI	Finish
	MT-3LD211NA <i>New Construction</i> <i>Non-IC, Airtight</i>		22W	F 25°	805x2	2224x2	927 2700K 90 930 3000K 90 935 3500K 90 940 4000K 90	90	BK White trim with black interior
				W 45°	795x2	1042x2			
	MT-3LD211R <i>Remodel</i> <i>Non-IC</i>		22W	F 25°	805x2	2224x2			
				W 45°	795x2	1042x2			
								WT White trim with white interior	

Example: **MT-3LD211R-F927-WT**

3 Lights



			Power	Beam	Max Lumens	Max CBCP	Color Temp	CRI	Finish
	MT-3LD311NA <i>New Construction</i> <i>Non-IC, Airtight</i>		33W	F 25°	805x3	2224x3	927 2700K 90 930 3000K 90 935 3500K 90 940 4000K 90	90	BK White trim with black interior
				W 45°	795x3	1042x3			
	MT-3LD311R <i>Remodel</i> <i>Non-IC</i>		33W	F 25°	805x3	2224x3			
				W 45°	795x3	1042x3			
								WT White trim with white interior	

Example: **MT-3LD311R-F927-WT**

Driver hidden inside
W track

Twist to adjust beam angle



Use with a track cover for a seamless installation



8 foot W track cover: **W8-COV-WT**
Can be field-cut and painted




Paloma Adjustable Beam LED

Power: 24W
Delivered Lumens: Up to 1600
CBCP: Up to 7650
Comparable to: 20W HID
Rated Life: 50,000 hours

Museum-quality LED luminaire with adjustable beam angle

- Adjustable beam angle between 15° - 60°
- Die-cast aluminum construction
- 365° horizontal rotation and 180° vertical aiming
- Smooth and continuous ELV dimming for 120V
- ELV dimming - see specification sheet for list of tested dimmers





Track		Model	Color Temp	CRI	Max Lumens	Max CBCP	Finish
W Track	WTK WHK	120V 277V	LED523	27 2700K	85	1340	6840
				927 2700K	90	1260	6515
				30 3000K	85	1500	7595
				930 3000K	90	1350	6635
				35 3500K	85	1495	7280
			40 4000K	85	1600	7650	
							BK Black PT Platinum WT White

Example: **WTK-LED523-927-WT**

Adjustable Beam Angle

Adjustable between 15° - 60°



W Track Quick Connect™ Adapter



Transformer hidden inside W track



See website www.waclighting.com for all other pendant options

The Quick Connect™ collection includes a wide array of pendants and fixtures with different mounting options.



The threaded male adapter makes inter-system compatibility a snap. Simply insert the metal fitting into the system adapter and hand tighten the collar.

Order one per Quick Connect™ fixture or pendant used.

Use with a track cover for a seamless installation




8 foot W track cover: **W8-COV-WT**
Can be field-cut and painted


System Adapter	Specifications	Model	Finish
W Track 120V 	<ul style="list-style-type: none"> • Recessed transformer within W track • Allows all Quick Connect™ elements to be used with the W track 120V systems • 1W minimum load transformer • Smooth and continuous ELV dimming 	EN-WQ50AR	BK Black PT Platinum WT White 

Example: **EN-WQ50AR-WT**


W Track Current Limiter



Surface Mount




Recessed Flanged




Recessed Flangeless

120V W Track

	Model	Rating	Circuit Breaker	Max Wattage	Finish
Single Live end (Left)	WEDL Surface Mount	1/5A 1/2A 1A 2A 5A 7A 10A 12A	2 X 0.2Amp 2 X 0.5Amp 2 X 1 Amp 2 X 2.5Amp 2 X 5 Amp 2 X 7.5Amp 2 X 10Amp 2 X 12Amp	2 X 24W 2 X 60W 2 X 120W 2 X 300W 2 X 600W 2 X 900W 2 X 1200W 2 X 1440W	BK Black PT Platinum WT White 
	WEDL-RT Recessed Flanged				
	WEDL-RTL Recessed Flangeless				
Single Live end (Right)	WEDR Surface Mount				
	WEDR-RT Recessed Flanged				
	WEDR-RTL Recessed Flangeless				

Example: **WEDL-1/5A-BK**











277V W Track

	Model	Rating	Circuit Breaker	Max Wattage	Finish
Single Live end (Left)	WHEDL Surface Mount	1A 2A 5A 7A 10A 12A	2 X 1 Amp 2 X 2.5Amp 2 X 5 Amp 2 X 7.5Amp 2 X 10Amp 2 X 12Amp	2 X 277W 2 X 692W 2 X 1385W 2 X 2077W 2 X 2770W 2 X 3324W	BK Black PT Platinum WT White 
	WHEDL-RT Recessed Flanged				
	WHEDL-RTL Recessed Flangeless				
Single Live end (Right)	WHEDR Surface Mount				
	WHEDR-RT Recessed Flanged				
	WHEDR-RTL Recessed Flangeless				

Example: **WHEDL-1A-BK**

H Track Current Limiter

- Slim single live end nearly matches the width and height of the H track stem
- Small capacity current limiters allow further energy saving credits

	Model	Circuit Breaker	Max Wattage	Finish
 <p>New Product</p> <p><i>Slim Single Live End</i></p>  <p>THL-HLES</p>				
 <p><i>Single Live End</i></p>  <p>THL-HLE</p>	1/5A 1/2A 1A 2A 5A 7A 10A	200mA 500mA 1A 2.5A 5A 7.5A 10A	24W 60W 120W 300W 600W 900W 1200W	
 <p><i>Double Live End</i></p>  <p>THL-HI</p>	1-1/5A 2-1/5A	200mA 200mA per end	24W 24W per end	
 <p><i>Double Live End (Left)</i></p>  <p>THL-LEFT</p>	1-1/2A 2-1/2A 1-1A 2-1A 1-2A 2-2A 1-5A 2-5A 1-7A 2-7A	500mA 500mA per end 1A 1A per end 2.5A 2.5A per end 5A 5A per end 7.5A 7.5A per end	60W 60W per end 120W 120W per end 300W 300W per end 600W 600W per end 900W 900W per end	
 <p><i>Double Live End (Right)</i></p>  <p>THL-RIGHT</p>	1-10A 2-10A	10A 10A per end	1200W 1200W per end	

BK	Black	
BN	Brushed Nickel	
DB	Dark Bronze	
WT	White	

Example: **THL-LEFT-1-1/5A-WT**



52W Exterminator II

Comparable: 70W HID
 ELV Dimming: 100% - 1%
 Rated Life: 80,000 hours

- Energy Star® rated
- Accommodates one lens accessory and one glare control accessory
- Reflectors and LED modules can be purchased separately for alternative beam angles and color temperatures
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model	Max Lumens	Max CBCP	Color Temp	CRI	Finish
<p>WTK 120V WHK 277V</p>	1052 52W	N 25° 4237 F 55° 3910	15970 1640	827 2700K 85	85	BK Black PT Platinum WT White
				927 2700K 90		
				830 3000K 85		
				930 3000K 90		
				835 3500K 85		
				840 4000K 85		
<p>H H TRACK L L TRACK J J/J2 TRACK</p>	1052 52W	N 25° 4237 F 55° 3910	15970 4640	827 2700K 85	85	BN Brushed Nickel BK Black WT White
				927 2700K 90		
				830 3000K 85		
				930 3000K 90		
				835 3500K 85		
				840 4000K 85		

Example: **WTK-1052N-930-WT**

LENS ACCESSORIES

Amber	LENS-25-AMB
Blue	LENS-25-BLU
Green	LENS-25-GRN
Red	LENS-25-RED
Yellow	LENS-25-YEL
UV Filter	LENS-25-UVF
Frosted	LENS-25-FR
Spread	LENS-25-SPR
Beam Elongating	LENS-25-BEL

REFLECTORS

25°	SL-REF-LUX1208-N
55°	SL-REF-LUX1208-F

GLARE CONTROL ACCESSORIES

Cross Louver	LENS-25-CRL
Snoot	LENS-25-SNOOT

LED MODULES

2700K	CRI 85	LHC1-2780-1208-W
2700K	CRI 90	LHC1-2790-1208-W
3000K	CRI 85	LHC1-3080-1208-W
3000K	CRI 90	LHC1-3090-1208-W
3500K	CRI 85	LHC1-3580-1208-W
4000K	CRI 85	LHC1-4080-1208-W



35W Exterminator II

Comparable: 50W HID
 ELV Dimming: 100% - 5%
 Rated Life: 60,000 hours

- Energy Star® rated
- CEC Title 24 Compliant
- Accommodates one lens accessory and one glare control accessory
- Reflectors and LED modules can be purchased separately for alternative beam angles and color temperatures
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model	Max Lumens	Max CBCP	Color Temp	CRI	Finish		
<p>WTK 120V WHK 277V</p>	1035 35W	N 25° 2795	9748	827 2700K 85	BK Black			
				F 55° 2828			3886	927 2700K 90
								830 3000K 85
								930 3000K 90
								835 3500K 85
								840 4000K 85
<p>H H TRACK L L TRACK J J/J2 TRACK J TRACK</p>	1035 35W	N 25° 2795	9748	827 2700K 85	BN Brushed Nickel			
				F 55° 2828			3886	927 2700K 90
								830 3000K 85
								930 3000K 90
								835 3500K 85
								840 4000K 85

Example: **WHK-1035F-830-BK**

LENS ACCESSORIES

Amber	LENS-20-AMB
Blue	LENS-20-BLU
Green	LENS-20-GRN
Red	LENS-20-RED
Yellow	LENS-20-YEL
UV Filter	LENS-20-UVF
Frosted	LENS-20-FR
Spread	LENS-20-SPR
Beam Elongating	LENS-20-BEL

REFLECTORS

25°	SL-REF-BL18-N
55°	SL-REF-BL18-F

GLARE CONTROL ACCESSORIES

Cross Louver	LENS-20-CRL
Snoot	LENS-20-SNOOT

LED MODULES

2700K	CRI 85	BXRC-27E4000-F-23
2700K	CRI 90	BXRC-27G4000-F-23
3000K	CRI 85	BXRC-30E4000-F-23
3000K	CRI 90	BXRC-30G4000-F-23
3500K	CRI 85	BXRC-35E4000-F-23
4000K	CRI 85	BXRC-40E4000-F-23



14W Exterminator II

Comparable: 20W HID
ELV Dimming: 100% - 1%
Rated Life: 100,000 hours

- Energy Star® rated
- CEC Title 24 Compliant
- Accommodates one lens accessory and one glare control accessory
- Reflectors and LED modules can be purchased separately for alternative beam angles and color temperatures
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model		Max Lumens	Max CBCP	Color Temp	CRI	Finish
<p>WTK 120V</p>	1014 14W	N 20°	965	4585	827 2700K	85	BK Black PT Platinum WT White
		F 40°	980	2117	927 2700K	90	
					830 3000K	85	
					930 3000K	90	
					835 3500K	85	
					840 4000K	85	
<p>H H TRACK L L TRACK J J/J2 TRACK</p>	1014 14W	N 20°	965	4585	827 2700K	85	BN Brushed Nickel BK Black WT White
		F 40°	980	2117	927 2700K	90	
					830 3000K	85	
					930 3000K	90	
					835 3500K	85	
					840 4000K	85	

Example: **WTK-1014N-927-WT**

LENS ACCESSORIES

Amber	LENS-11-AMB
Blue	LENS-11-BLU
Green	LENS-11-GRN
Red	LENS-11-RED
Yellow	LENS-11-YEL
UV Filter	LENS-11-UVF
Frosted	LENS-11-FR
Spread	LENS-11-SPR
Beam Elongating	LENS-11-BEL

REFLECTORS

20°	SL-REF-CXA1310-N
40°	SL-REF-CXA1310-F

GLARE CONTROL ACCESSORIES

Cross Louver	LENS-11-CRL
Snoot	LENS-11-SNOOT

LED MODULES

2700K	CRI 85	CXA1310-00J227H-W
2700K	CRI 90	CXA1310-0YG227H-W
3000K	CRI 85	CXA1310-00J430H-W
3000K	CRI 90	CXA1310-0YG430H-W
3500K	CRI 85	CXA1310-00J435H-W
4000K	CRI 85	CXA1310-0HK240H-W



23W Exterminator

Comparable: 39W HID
ELV Dimming: 100% - 10%
Rated Life: 60,000 hours

- Recessed Driver
- Energy Star® Rated
- Accommodates one lens accessory
- Reflectors and LED modules can be purchased separately for alternative beam angles and color temperatures
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model	Max Lumens	Max CBCP	Color Temp	CRI	Finish
<p>WTK 120V WHK 277V</p>	LED20 23W	S 20° 1450 F 40° 1390	6772 2928	27 2700K 85	85	BK Black PT Platinum WT White
				927 2700K 90		
				30 3000K 85		
				930 3000K 90		
				35 3500K 85		
40 4000K 85						
<p>H H TRACK L L TRACK J J/J2 TRACK</p>	LED20 23W	S 20° 1450 F 40° 1390	6772 2928	27 2700K 85	85	BN Brushed Nickel BK Black WT White
				927 2700K 90		
				30 3000K 85		
				930 3000K 90		
				35 3500K 85		
40 4000K 85						

Example: **WTK-LED20F-30-PT**

LENS ACCESSORIES

Amber	LENS-16-AMB
Blue	LENS-16-BLU
Green	LENS-16-GRN
Red	LENS-16-RED
Yellow	LENS-16-YEL
UV Filter	LENS-16-UVF
Frosted	LENS-16-FR
Spread	LENS-16-SPR
Beam Elongating	LENS-16-BEL

REFLECTORS

20°	RF-S
40°	RF-F

LED MODULES

2700K	CRI 85	BXRC-27E1000
2700K	CRI 90	BXRC-27G1000
3000K	CRI 85	BXRC-30E1000
3000K	CRI 90	BXRC-30G1000
3500K	CRI 85	BXRC-35E1000
4000K	CRI 85	BXRC-40E1000



LED207





LED201

Summit LED

Power: 15W
Comparable: 50W MR16
CRI: 85
ELV Dimming: 100% - 10%
Input: 120V
Rated Life: 50,000 hours

Compact driverless LED track luminaire

- Energy Star® rated
- 120VAC - no driver needed
- Beamshift™ enables in-field change of beam angle (patent pending)
- Die-cast aluminum construction
- ELV dimming - see specification sheet for list of tested dimmers


Track	Model	Color Temp	Beam*	Lumens	CBCP	Finish
H H TRACK L L TRACK J J/J2 TRACK	 LED207-30	3000K	25° 40°	540 660	1275 1030	BK Black WT White
	 LED201-30	3000K	25° 40°	540 660	1275 1030	BK Black WT White

Example: **H-LED207-30-WT**


*All Summit LED track luminaires come with Flood (40°) beam setting by default, which may be reconfigured to Narrow(25°) in field.

BeamShift™

All Summit series track luminaires come with BeamShift™, allowing in-field change of beam angle simply by changing the location of the lens



Flood Configuration
Lens located at the back



Spot Configuration
Lens located in the front



LED202







LED208

Summit LED

Power: 15W
 Comparable: 50W MR16
 CRI: 85
 ELV Dimming: 100% - 10%
 Input: 120V
 Rated Life: 50,000 hours

Compact driverless LED track luminaire

- Energy Star® rated
- 120VAC - no driver needed
- Beamshift™ enables in-field change of beam angle (patent pending)
- Die-cast aluminum construction
- ELV dimming - see specification sheet for list of tested dimmers

Track		Model	Color Temp	Beam*	Lumens	CBCP	Finish
H L J	H TRACK L TRACK J/J2 TRACK	 LED202-30	3000K	25° 40°	540 660	1275 1030	BK Black WT White
		 LED208-30	3000K	25° 40°	540 660	1275 1030	AB Antique Bronze
HM1	FLEXRAIL 1™	 LED202-30	3000K	25° 40°	540 660	1275 1030	PT Platinum
		 LED208-30	3000K	25° 40°	540 660	1275 1030	DB Dark Bronze

Example: H-LED202-30-BK

* All Summit LED track luminaires come with Flood (40°) beam setting by default, which may be reconfigured to Narrow(25°) in field.



Precision LED

Power: 14.5W
Delivered Lumens: Up to 975
CBCP: Up to 4500
Comparable to: 65W MR16
ELV Dimming: 100%-10%
Rated Life: 70,000 hours

Compact single diode LED

- CEC Title24 Compliant
- Die-cast aluminum construction
- 365° horizontal rotation and 180° vertical aiming
- ELV dimming - see specification sheet for list of tested dimmers

Track	Model	Beam	Color Temp	CRI	Finish
H H TRACK L L TRACK J J/J2 TRACK	 LED160	S 20° F 40°	927 2700K	90	BK Black WT White
			27 2700K	85	
			930 3000K	90	
			30 3000K	85	
			35 3500K	85	
			40 4000K	85	

Example: **H-LED160S-927-BK**

Replacement Lenses

Amber	LENS-16-AMB	
Blue	LENS-16-BLU	
Green	LENS-16-GRN	
Red	LENS-16-RED	
Yellow	LENS-16-YEL	

UV Filter	LENS-16-UVF	
Frosted	LENS-16-FR	
Spread	LENS-16-SPR	
Beam Elongator	LENS-16-BEL	

LED Track Luminaires MR16 Replacement - Now with 1W-60W Transformer

Power: 8W
Lumens: 450
CBCP: 850
Color Temp: 3000K
CRI: 85
ELV Dimming: 100% - 10%
Input: 120V
Rated Life: 25,000 hours

- 1 W to 60 W load transformer
- Fixtures specifically designed to ensure proper lamp fit
- LED lamp included
- ELV dimming - see specification sheet for list of tested dimmers


System	Model	Finish
 HHT LHT JHT	164LED	BK WT <i>Black White</i>
 HHT LHT JHT	886LED	AB <i>Antique Bronze</i>
 HHT LHT JHT	874LED	AB <i>Antique Bronze</i>
 HHT LHT JHT	856LED	AB BK BN WT <i>Antique Bronze Black Brushed Nickel White</i>
 HHT LHT JHT	817LED	BK PT/BK PT/WT WT <i>Black Platinum/Black Platinum/White White</i>
 HHT LHT JHT	826LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	816LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	808LED	BK DB WT <i>Black Dark Bronze White</i>

System	Model	Finish
 HHT LHT JHT	160LED	BK WT <i>Black White</i>
 HHT LHT JHT	180LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	809LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	802LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	846LED	BK WT <i>Black White</i>
 HHT LHT JHT	204LED	BK BN WT <i>Black Brushed Nickel White</i>
 HHT LHT JHT	801LED	BK WT <i>Black White</i>
 HHT LHT JHT	007LED	BK BN WT <i>Black Brushed Nickel White</i>

Example: HHT-808LED-DB

Power: 2W / ft
Lumens: Up to 150 lm / ft
CRI: 85
Rated Life: 50,000 hours

- UL listed for damp location
- May be field cut every 2 inches at the end of a run
- Includes an end cap
- Specially rated for installation in the storage area of a clothes closet
- ELV dimming - see specification sheet for list of tested dimmers



Tape Selections

System	Color Temp	Length	Qty	Finish
LED-T24	27L 2700K 30L 3000K	2IN 2 inches	1	WT White
		2IN10 2 inches	10	
		1 1 foot	1	
		5 5 feet	1	
		1-40 1 foot	40	

Example: **LED-T2427L-5-WT**

"L" Connector

System	Color Temp	Finish
LED-T24	27L 2700K 30L 3000K	3L-WT White

Example: **LED-T2427L-3L-WT**

Each "L" connector consumes 0.7 watt

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	30 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	40 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	40 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	30 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	40 feet	Yes

Accessories

For mounting accessories, please see page 40



Lead Wire		LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies
Extension Cable		LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section
Low Voltage Wiring Box With Feed		LED-TC-B-2	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires with 2" female feed
Low Voltage Wiring Box		LED-T-B	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires
Wiring Box With Switch		TB-S	L: 6 1/4 in W: 1 5/8 in H: 1 1/4 in Use when spanning a large gap in a system layout without leaving exposed wiring
Joiner Cable		LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in	Connects tape sections
3-Way "Y" Connector		LED-TC-Y	Connects tape sections
4-Way "X" Connector		LED-TC-X	Connects tape sections
"L" Connector		LED-TC-L	Connects tape sections
End cap		LED-TC-EC	1 cut end cap 1 male end cap

Pro2 InvisiLED®

New 2200K Color Temperature

Power: 4W / ft
Lumens: Up to 330 lm / ft
CRI: 90
Rated Life: 80,000 hours

- CEC Title 24 Compliant
- UL listed for damp location
- May be field cut every 6 inches at the end of a run
- Includes an end cap
- Specially rated for installation in the storage area of a clothes closet
- ELV dimming - see specification sheet for list of tested dimmers



Tape Selections

System	Color Temp	Length	Qty	Finish
LED-TX24	22 2200K	6IN 6 inches	1	WT White
	27 2700K		1	
	30 3000K		1	
	35 3500K		1	
	45 4500K		40	

Example: **LED-TX2435-6IN-WT**

"L" Connector

System	Color Temp	Finish
LED-TX24	22 2200K	5L-WT White
	27 2700K	
	30 3000K	
	35 3500K	
	45 4500K	

Example: **LED-TX2435-5L-WT**
 Each "L" connector consumes 2 watt

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	15 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	25 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	25 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	15 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	25 feet	Yes

Accessories

For mounting accessories, please see page 40

Lead Wire		LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies
Extension Cable		LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section
Low Voltage Wiring Box With Feed		LED-TC-B-2	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires with 2" female feed
Low Voltage Wiring Box		LED-T-B	L: 1 1/2 in W: 3/4 in H: 7/8 in Neatly houses up to two wires
Wiring Box With Switch		TB-S	L: 6 1/4 in W: 1 5/8 in H: 1 1/4 in Use when spanning a large gap in a system layout without leaving exposed wiring


Joiner Cable		LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in	Connects tape sections
3-Way "Y" Connector		LED-TC-Y	Connects tape sections
4-Way "X" Connector		LED-TC-X	Connects tape sections
"L" Connector		LED-TC-L	Connects tape sections
End cap		LED-TC-EC	1 cut end cap 1 male end cap

Pro3 InvisiLED®

New Product

Power: 5W / ft
Lumens: Up to 475 lm / ft
CRI: 90
Rated Life: 70,000 hours

- Brightest InvisiLED® system available
- Laterally bendable design
- CEC Title 24 Compliant
- UL listed for damp location
- May be field cut every 6 inches at the end of a run
- Includes an end cap and a male to male connector with each tape section
- ELV dimming - see specification sheet for list of tested dimmers



Tape Selections

System	Color Temp	CRI	Length	Qty	Finish
LED-TE24	27 2700K	95	6IN 6 inches	1	WT White
	30 3000K	95	1 1 foot	1	
	35 3500K	90	5 5 feet	1	
	45 4500K	90	1-40 1 foot	40	

Example: **LED-TE2435-6IN-WT**

Compatible Class 2 Power Supply (Required)

Type	Model	Input	Output	Max Run	Dim
Remote	EN-2460-RB2-T	120VAC	24VAC / 60W	12 feet	Yes
	EN-24100-RB2-T	120VAC	24VAC / 96W	20 feet	Yes
Remote	EN-24100-277-RB2-T	100 - 277VAC	24VDC / 96W	20 feet	No
Plug-in	EN-2460-P-AR-T	120VAC	24VAC / 60W	12 feet	Yes
	EN-24100-P-AR-T	120VAC	24VAC / 96W	20 feet	Yes

Curve clip **LED-T-CL1** shown (see page 40 for detail)

Longitudinally bendable over marked signs

Field-cutable every 6" at the end of a run

Accessories

For mounting accessories, please see page 40

Lead Wire		LED-TC-P-2 2 ft LED-TC-P-12 12 ft	Alternative lengths for plug-in power supplies	Joiner Cable		LED-TC-IC2 2 in LED-TC-IC6 6 in LED-TC-IC12 12 in LED-TC-IC36 36 in LED-TC-IC72 72 in	Connects tape sections
Extension Cable		LED-TC-EXT-144 12 ft	Extends distance between a hard wired power supply or wiring box to a tape section	3-Way "Y" Connector		LED-TC-Y	Connects tape sections
Low Voltage Wiring Box With Feed		LED-TC-B-2	L: 1½ in W: ¾ in H: 7/8 in Neatly houses up to two wires with 2" female feed	4-Way "X" Connector		LED-TC-X	Connects tape sections
Low Voltage Wiring Box		LED-T-B	L: 1½ in W: ¾ in H: 7/8 in Neatly houses up to two wires	"L" Connector		LED-TC-L	Connects tape sections
Wiring Box With Switch		TB-S	L: 6¼ in W: 1½ in H: 1¼ in Use when spanning a large gap in a system layout without leaving exposed wiring	End cap		LED-TC-EC	1 cut end cap 1 male end cap


Mounting accessories

Compatible with InvisiLED® Pro, Pro2, Pro3, LITE, Classic, Daylight to Sunset, and Palette

Aluminum Channel

LED-T-CH

5 feet



Includes a diffuser, two end caps, and five screws



Deep Aluminum Channel

LED-T-CH1

5 feet




Includes a diffuser, two end caps, and five screws



45° Angled Aluminum Channel

LED-T-CH2

5 feet



Includes a diffuser, two end caps, and five screws



Fixed Angle Channel Clip

LED-T-CL3-PT

2 pcs




Used to mount any aluminum channel
Includes 2 pieces, 4 screws



Adjustable Channel Clip

LED-T-CL2-PT

2 pcs




Used to mount any aluminum channel
Adjusts 50° from center either way
Includes 2 pieces, 4 screws



Retrofit Channel

LED-T-RC

3 feet




Can be bent to create fixed curves



Clip

LED-T-CL

10 pcs



Holds the tape from the underside
Includes 10 pieces, 10 screws



New Product

Curve Clip


LED-T-CL1

10 pcs




Runs over the tape to secure the angled tape
Includes 10 pieces, 10 screws





12V or 24V Capacitive Touch Switch and Occupancy Control Kit For Low Voltage Systems



CT-6A-R2


Includes a Touch Panel, an Occupancy Sensor, and a Controller
AC/DC input at 12V(60W Max) or 24V(96W Max)
Connect on secondary side of driver/transformer

Three custom settings of lighting control


Touch and Sensor: Touch panel turns the luminaire on/off manually while the motion sensor turns it off when the space is vacant

Touch: Touch panel turns the luminaire on/off manually

Sensor: Motion sensor turns the luminaire on/off autonomously



Surface mounted



Recessed

LED90 Edge Lit Button Light New Dark Bronze Finish



Power: 24V, 5W
CRI: 90
ELV Dimming: 100% – 5%
Rated Life: 100,000 hours
Cutout: 3 3/4" for recessed applications

- Energy Star® rated
- CEC Title24 Compliant
- Can be surface mounted or recessed
- Super thin profile at 1/2"
- Edge-lit LEDs reduce glare and assure even light distribution
- Anti-microbial white paint
- ELV dimming - see specification sheet for list of tested dimmers

Model	Color Temp	Lumens	Finish
HR-LED90	27 2700K	200	BN <i>Brushed Nickel</i>
	30 3000K	200	BK <i>Black</i>
			DB <i>Dark Bronze</i>
			WT <i>White</i>

Example: **HR-LED90-30-WT**
 Includes 6 foot lead wire

Class 2 enclosed electronic transformers (Required)

Model	Input	Output	Min Load	Max Fixture Run	L	W	H	
 EN-2460-RB2	120V	24V, 60W	1W	7	6 1/2"	1 5/8"	1 1/4"	<i>Fits through small openings</i>
	120V	24V, 96W	1W	10	6 1/2"	1 5/8"	1 1/4"	
 EN-2460-P-AR	120V	24V, 60W	1W	7	2 3/4"	1 5/8"	1 3/4"	<i>Plug-in power supply with on/off switch and 6' detachable cord</i>

- Secondary wiring for Class 2 transformers does not require conduit sheathed cable or clamp wiring techniques
- Intrinsically safe, Class 2 transformers permit no greater than a 5 amp current to be drawn
- Non-metallic sheathed cable may be used for secondary wiring in walls and ceilings
- Power consumption may vary depending on the efficiency of the power supply being used



LINE™ 2.0 LED Undercabinet


Fixed Light Panel

- Energy Star® rated
- Diffused light source reduces glare, eliminates hard shadows
- Asymmetrical forward throw for optimal light distribution
- Anti-microbial paint (white only)
- Connections made at the center of each fixture
- ELV dimming - see specification sheet for list of tested dimmers

CRI: 90+
ELV Dimming: 100% – 10% (120V only)
Rated Life: 100,000 hours

	Length	Watt	Max Lumens	Max Fixture Run		Color Temp	Finish
				60 W	96 W		
	LN-LED06P	6.5W	265	6	11	27 2700K 30 3000K	AL Brushed Aluminum WT White
	LN-LED12P	10.5W	515	3	6		
	LN-LED18P	16W	875	2	4		
	LN-LED24P	20W	1160	2	3		
	LN-LED30P	23.5W	1345	1	2		

Example: **LN-LED18P-30-WT**



LINE™ LED Undercabinet

Detachable light panel for maintenance

- Energy Star® rated
- Diffused light source reduces glare, eliminates hard shadows
- Asymmetrical forward throw for optimal light distribution
- ELV dimming - see specification sheet for list of tested dimmers



CRI: 90+
ELV Dimming: 100% – 10% (120V only)
 100% / 50% high/low settings on board
Rated Life: 80,000 hours

	Length	Watt	Max Lumens	Max Fixture Run		Color Temp	Finish
				60 W	96 W		
	LN-LED06	7.0W	275	8	13	27 2700K 30 3000K	AL Brushed Aluminum
	LN-LED12	12.5W	600	4	7		
	LN-LED18	19.0W	955	3	5		
	LN-LED24	23.0W	1245	2	4		
	LN-LED30	26.0W	1345	2	3		


Example: **LN-LED18-27-AL**

"I" connector included with each luminaire





Class 2 Power Supply for LINE™ and LINE™ 2.0 (Required)

Type		Model	Output	Input	Dim	Dimensions
Remote		EN-2460-RB2-S EN-24100-RB2-S	60W (24V) 96W (24V)	120V	Yes	6½" × 1½" × 1¼"
Plug-In		EN-2460-P-AR-S EN-24100-P-AR-S	60W (24V) 96W (24V)	120V	Yes	2¾" × 1½" × 1¾" 4⅝" × 2" × 1⅝"






Control Accessory

Touch Panel and Motion Sensor		CT-6A-R2	Includes a Touch Panel, an Occupancy Sensor, and a Controller AC/DC input at 12V(60W Max) or 24V(96W Max) Connect on secondary side of driver/transformer
-------------------------------	---	-----------------	---

Power Supply Accessories

Wiring Box with On/Off Switch option		TB-S	6¼" × 1⅝" × 1¼"	Use when spanning a large gap in a system layout without leaving exposed wiring (i.e. lighting kitchen cabinets on either side of a sink or window).
Multiple Terminal Block		MTB-08	8 outputs 4⅞" × 1⅝" × ¾"	Easily wire multiple output connections for a neat installation without the use of open splices. One power supply input and 8 outputs. 5A capacity. Three mounting screws included.
12' Extension Cable		SL-EXT-144	Wire: 144" Connector: 1⅝"	Use to extend the distance between power supply or wiring box (TB-S) to a LINE™ section.
Wire Clip (10 Pack)		SL-WC-1	½" × ⅜"	Use to tack power cords or joiner cables neatly to a surface.

Connection Accessories


Joiner Cables		SL-IC-06 SL-IC-12 SL-IC-24 SL-IC-36	6" 12" 24" 36"	Connects two sections of LINE™.
Custom Cable Extenders		SL-IF	Ø3/8" × 3⅝"	Two female ends. Connects two joiner cables to create custom lengths.
4-way "X" Connector		SL-X	Wires: 4" each Connectors: 1⅝" each	"X" connector has four male connectors and can be used to easily customize your design layout.
3-way "Y" Connector		SL-Y	Wires: 4" each Connectors: 1⅝" each	"Y" connector has three male connectors and can be used to easily customize your design layout.
"I" Connector		SL-I	Ø¼" × ⅞"	For end-to-end connection of LINE™ sections.



New Brushed Aluminum Finish

Minimal space between luminaires


Shown: **BA-ACLED12-AL**



Uniform light

Using a 98% efficient reflector, light from the LED sources inside the housing diffuse inside the mixing chamber in order to create evenly distributed illumination. Energy Star® compliant.


- May be hard-wired with 120V power or used with a plug-in power cord
- Subsequent fixtures may be powered with an "I" Connector or Interconnect Cable carrying 120V
- May be individually switched and/or wired to a wall box switch/dimmer



Power Cord

Model	WT	Length
BA-PC6	White	6'
	Black	


Supplies power in any application.



"I" Connector

Model	Max Fixture Run
BA-I-WT	6

Interconnection for seamless end to end transitions. Each light bar includes one.




Interconnect Cable

Model	Length	Max Fixture Run	WT	BK
BA-IC12	12"	4	White	
BA-IC24	24"	4		Black
BA-IC36	36"	3		

Example: **BA-IC12-WT**

Links two light bars using a single power connection.



Light Bars LEDme® Pro

Color Temp: 2700K, 3000K
CRI: 90+
Dimming: 100% – 10% *smooth and continuous ELV dimming*
Rated Life: 90,000 hours

- Uniform Light
- Energy Star® Rated
- CEC Title24 Compliant
- 120VAC - no driver needed
- Diffused light source reduces glare
- 1 inch Profile
- Extruded aluminum construction for optimal thermal management
- Multiple knock outs for ease of wiring
- ELV dimming - see specification sheet for list of tested dimmers

	Model	Length	Watt	Lumens	Color Temp	Finish
	BA-ACLED8	8"	5.5W	255	927 2700K 930 3000K	BZ Bronze AL Brushed Aluminum WT White
	BA-ACLED12	12"	8.0W	365		
	BA-ACLED18	18"	10.0W	450		
	BA-ACLED24	24"	15.0W	705		
	BA-ACLED30	30"	17.0W	785		

Example: **BA-ACLED12-927-WT**




Light Bars LEDme®

Color Temp: 2700K, 3000K
CRI: 85
Dimming: 100% – 10% *smooth and continuous ELV dimming*
Rated Life: 70,000 hours

- Integral drivers
- 1 inch Profile
- Extruded aluminum construction for optimal thermal management
- Multiple knock outs for ease of wiring
- ELV dimming - see specification sheet for list of tested dimmers

	Model	Length	Watt	Lumens	Color Temp	Finish
	BA-LED2	8"	3.5W	150	27 2700K 3000K	BB Bronze SN Satin Nickel WT White
	BA-LED4	12"	6W	285		
	BA-LED6	18"	8.6W	465		
	BA-LED8	24"	10.9W	585		
	BA-LED10	30"	13.4W	695		

Example: **BA-LED4-27-BB** for 2700K
BA-LED4-BB for 3000K




Recessed Inground + Indicator

- IP68 rated, Suitable for continuous immersion under water
 - Factory sealed water tight fixtures
 - Solid stainless steel construction
- Options for use in wall or downlight applications
 - Available concrete pour kit
 - Constant output for 9V-15V input
- 10%-100% dimming - see specification sheet for list of tested dimmers

1" Aperture

Slim Round



1011-30SS
Stainless Steel

Round


Optional spring clip
accessory included



1021-30SS
Stainless Steel

Square

Optional Spring Clip
accessory included



1051-30SS
Stainless Steel

Input	9-15VAC
Power	1.9W 3VA
Brightness	80 lm
Color Temp	3000K Pure White
CRI	85
Beam Angle	50°
Rated Life	70,000 hours

6' lead wire included

1" Concrete Pour Kit




1000-CON-PVC

For installation in concrete. Use with a 4" outdoor rated junction box and a trade size 1" schedule 80 PVC pipe



2" Aperture

Slim Round



2011-30SS
Stainless Steel

2011-30BS
Bronzed Stainless Steel

Round

Optional Spring Clip
accessory included




2021-30SS
Stainless Steel

2021-30BS
Bronzed Stainless Steel

Square

Optional Spring Clip
accessory included



2051-30SS
Stainless Steel

2051-30BS
Bronzed Stainless Steel

Input	9-15VAC
Power	4.1W / 6.6VA
Brightness	170 lm
Color Temp	3000K Pure White
CRI	85
Beam Angle	25°
Rated Life	70,000 hours

6' lead wire included

2" Concrete Pour Kit




2000-CON-PVC


For installation in concrete. Use with a 4" outdoor rated junction box and a trade size 2" schedule 80 PVC pipe



12V Transformer



IP65 Rated
 12V to 15V taps
 Knock outs for power and photosensor connections
 3-prong outlet for timer
 Outdoor rated stainless steel transformer contains an outdoor rated 3-prong plug for power



Magnetic Transformer

9075-TRN-SS

75W Max

Dimensions: 13.97" L x 5.35"W x 5.63"H

9150-TRN-SS

150W Max

Dimensions: 18.90" L x 6.69"W x 6.30"H

9300-TRN-SS

300W Max

Dimensions: 18.90" L x 6.69"W x 6.30"H

9600-TRN-SS

600W Max (2 x 300W outputs)

Dimensions: 14.49" L x 10.08"W x 5.94"H

Accessories

Mechanical Timer

Connect within the transformer



9000-MTI-WT

Photosensor

Attached directly to the transformer



9000-PCH-GY

1000VA Max

Photosensor - Remote

If transformer is located in a shady spot, this photosensor has a 10 foot cord and a stainless steel bracket to secure in a sunny area



9000-PCR-GY

1000VA Max

IDEAL® Direct Burial Waterproof Wire Nuts



9020-WNT-BK

Silicone filled wire nut with gasket
 (Pack of 20pcs)

12V Direct Burial Outdoor Cable



9100-12G-BK

100 feet
 12 gauge

9250-12G-BK

250 feet
 12 gauge

9500-12G-BK


500 feet
 12 gauge




Rectangular Step and Wall Lights LEDme®



LED100
Stainless Steel Finish



LED200
Black Finish



- | | | |
|---------------------------------|---|--|
| Power: 3.9W | • Available die-cast brass and 316 marine grade stainless steel | • 120V or 277V direct wiring, no driver needed |
| Lumens: Up to 68 | • Fits into 2" X 4" J-Box with minimum inside dimensions of 3"x2"x2" | • No heat radiation |
| CRI: 85 | • IP66, wet location rated for indoor and outdoor installations* | • Smooth and continuous ELV dimming |
| Rated Life: 40,000 hours | • 5 year WAC warranty (lifetime warranty for brass and stainless steel) | |

*Finishes are not recommended for contact with chemicals or sustained contact with water.
Use Brass or Stainless Steel Step and Wall Lights for harsh environments.

System	Color	Finish
WL-LED100 <i>Horizontal Scoop, 120V</i> WL-LED100F <i>Horizontal Scoop, 277V</i>	C <i>White</i> 3000K (CCT)	BBR <i>Bronze on Brass</i>
	AM <i>Amber</i> 610nm (Peak)	SS <i>Stainless Steel</i>
	RD <i>Red</i> 640nm (Peak)	BK <i>Black on Aluminum</i>
	BL <i>Blue</i> 450nm (Peak)	WT <i>White on Aluminum</i>
		BN <i>Brushed Nickel on Aluminum</i>
WL-LED200 <i>Vertical Scoop, 120V</i> WL-LED200F <i>Vertical Scoop, 277V</i>		BZ <i>Bronze on Aluminum</i>
	C <i>White</i> 3000K (CCT)	SS <i>Stainless Steel</i>
	AM <i>Amber</i> 610nm (Peak)	BK <i>Black on Aluminum</i>
	RD <i>Red</i> 640nm (Peak)	WT <i>White on Aluminum</i>
	BL <i>Blue</i> 450nm (Peak)	BN <i>Brushed Nickel on Aluminum</i>
	BZ <i>Bronze on Aluminum</i>	

Example: **WL-LED100F-C-SS**


Colored light for animals

In coastal areas, bright step lights often attract marine life such as baby sea turtles, leading them away from the ocean by making them think it is the moon. Save the sea turtles by using amber or red step lights.




Spacing Recommendations for Optimal Light Distribution


Corridors / Hallways



Stairs - Wall Mount



Stairs - Step Mount



Mount in center of stair as close to the upper tread as possible. For best results use one light per step for steps narrower than 5 feet

Endurance™

WAC LIGHTING

LED technology offers superior alternatives to conventional Halogen and HID sources. With factory sealed die-cast aluminum housings. Endurance™ provides lasting performance for years.

Patent pending design for a water and dust proof, IP66 rated luminaire. Thermal engineering for up to 100,000 hours of rated life, eliminating the need for maintenance once installed. Thoughtful details include a built-in level and factory sealed light engine.



Energy Star® Rated



Factory-Sealed Fixture Housing
Protects LEDs From
Environmental Factors



Dark Sky Friendly



IP 66 Rated
Dust Tight, Waterproof



Motion and Photosensor Ready



LED Performs Efficiently
In Cold Weather With Added Lifespan



ETL & cETL Listed




Durable Die-Cast Aluminum
Aluminum



5 Year WAC Product Warranty

Sensors for Endurance™ Series



Motion Sensor
(120V)

MS-120-BZ	Bronze
MS-120-GY	Gray
MS-120-WT	White




Photosensor
(120V)


PC-120-BZ	Bronze
PC-120-GY	Gray
PC-120-WT	White

Endurance™ Flood

New Graphite Finish



Heavy Duty 1/2" Threaded Mounting Arm






360° Horizontal Rotation
90° Vertical Aiming

CRI: 85
Rated Life: 60,000 hours

- Waterproof breathable technology to maintain stable atmospheric pressure
- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® rated
- Die-Cast Aluminum Construction
- 120V Direct Wire - No Driver Needed
- 1/2" Threaded Heavy Duty Mounting Arm
- Photo/Motion Sensor Sold Separately - see page 53
- ELV dimming - see specification sheet for list of tested dimmers


Includes Two Canopy Accessories for use with Surface Mount or Recessed Junction Boxes



		Power	Comparable	Max Delivered Lumens	Color Temp	Finish
	WP-LED335	35W	100W HID	2070	30	aBZ Architectural Bronze
					50	aGH Architectural Graphite
						aWT Architectural White


Example: **WP-LED335-30-aBZ**





Endurance™ Single Spot New Product



CRI: 85
Rated Life: 43,000 hours


- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® rated
- Die-Cast Aluminum Construction
- 120V Direct Wire - No Driver Needed
- Photo/Motion Sensor Sold Separately - see page 53
- ELV dimming - see specification sheet for list of tested dimmers



		Power	Comparable	Color Temp	Delivered Lumens	Finish
	WP-LED415	15W	75W Halogen	30	3000K	965
				50	5000K	1030
	aBZ	Architectural Bronze				
	aGH	Architectural Graphite				
	aWT	Architectural White				


Example: **WP-LED415-30-aBZ**





Endurance™ Double Spot New Product



CRI: 85
Rated Life: 43,000 hours

- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® rated
- Die-Cast Aluminum Construction
- 120V Direct Wire - No Driver Needed
- Photo/Motion Sensor Sold Separately - see page 53
- ELV dimming - see specification sheet for list of tested dimmers



	Power	Comparable	Color Temp	Delivered Lumens	Finish
	WP-LED430 30W	150W Halogen	30 3000K	965 x2	aBZ Architectural Bronze  aGH Architectural Graphite  aWT Architectural White 
			50 5000K	1030 x 2	

Example: **WP-LED430-30-aWT**

Endurance™ Fin





Tempered Prismatic Glass
Reduces glare while optimizing light distribution

3 Outputs
2 Color Temperatures
1 Size

CRI: 85
Rated Life: 100,000 hours

- Waterproof breathable technology to maintain stable atmospheric pressure
- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® and DLC rated
- Die-Cast Aluminum Construction
- 20° Forward Throw Illumination
- Built-in Level For Easy Adjustment
- Photo/Motion Sensor Sold Separately
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers




	Power	Comparable	Max Delivered Lumens	Color Temp	Finish	
	WP-LED119	19W	39W HID	1460	30 3000K 50 5000K	aBZ Architectural Bronze aGH Architectural Graphite aWT Architectural White
	WP-LED127	27W	70W HID	2135		
	WP-LED135	35W	100W HID	2825		


Example: **WP-LED119-30-aWT**

Endurance™ Hawk

Also Includes a Box Sleeve when used with existing Surface Mount Junction Boxes



Shown with the Box Sleeve over an existing Surface Mount Junction Box



Tempered Prismatic Glass
Reduces glare while optimizing light distribution

Mounts In Any Orientation



For Direct and Indirect Illumination





CRI: 85
Rated Life: 100,000 hours

- Waterproof breathable technology to maintain stable atmospheric pressure
- IP66 and ETL & cETL Wet Location Listed
- Factory-Sealed LED Light Engine
- Energy Star® and DLC rated
- Die-Cast Aluminum Construction
- 20° Forward Throw Illumination
- Photo/Motion Sensor Sold Separately
- Built-in Level For Easy Adjustment
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers


Also Includes a Box Sleeve when used with existing Surface Mount Junction Boxes



		Power	Comparable	Max Delivered Lumens	Color Temp	Finish	
	WP-LED219	19W	39W HID	1435	30 3000K	aBZ Architectural Bronze	
	WP-LED227	27W	70W HID	2095	50 5000K	aGH Architectural Graphite	
						aWT Architectural White	

Example: **WP-LED219-30-aBZ**

Tube Architectural LED Single Light Wall Mount



DS-WS05

Power: 120V - 277V
CRI: Up to 90
0-10V Dimming: 100% - 20%
Rated Life: 80,000 hours


High performance facade LED wall mount light

- IP65 rated, ETL & cETL wet location listed
- Energy Star® rated
- Solid aluminum construction
- Universal driver (120V-220V-277V)

Distribution	Diameter	Watt	Max Delivered Lumens	Beam	Color Temp	CRI	Light Direction	Finish	
Single	DS-WS	05 5"	24W	1610	S 17° N 28° F 40°	27 2700K 85	S Straight up or down		BK Black WT White BZ Bronze GH Graphite
						927 2700K 90			
						30 3000K 85			
						930 3000K 90			
						35 3500K 85			
						40 4000K 85			
		06 6"	42W	2620	F	27 2700K 85	A Away from the wall		
						927 2700K 90			
						30 3000K 85			
						930 3000K 90			
						35 3500K 85			
						40 4000K 85			
08 8"	54W	4015	F	27 2700K 85	B Towards the wall				
				927 2700K 90					
				30 3000K 85					
				930 3000K 90					
				35 3500K 85					
				40 4000K 85					

Example: **DS-WS05-N930S-BK**

Tube Architectural LED Double Light Wall Mount



Power: 120V - 277V
CRI: Up to 90
0-10V Dimming: 100% - 20%
Rated Life: 80,000 hours

High performance facade LED wall mount light

- IP65 rated, ETL & cETL wet location listed
- Solid aluminum construction
- Universal driver (120V-220V-277V)




DS-WD05


Distribution	Diameter	Watt	Max Delivered Lumens	Beam	Color Temp	CRI	Light Direction	Finish																					
Double DS-WD	05	5"	24W x2	1610 x2	S 17°	27 2700K 85	S Straight up and down		BK Black WT White BZ Bronze GH Graphite																				
										06	6"	42W x2	2620 x2	N 28°	927 2700K 90	A Away from the wall													
																		08	8"	54W x2	4015 x2	F 40°	30 3000K 85	B Towards the wall					
																										27 2700K 85	C One side each		
																													927 2700K 90
	930 3000K 90																												
		35 3500K 85																											
			40 4000K 85																										

Example: **DS-WD08-F930B-BK**


Tube Architectural LED Ceiling Mount Downlight



DS-CD05



DS-CD06



DS-CD08

Power: 120V - 277V
CRI: Up to 90
0-10V Dimming: 100% - 20%
Rated Life: 80,000 hours

High performance exterior rated LED downlights

- IP65 rated, ETL & cETL wet location listed
- Energy Star® rated
- Solid aluminum construction
- Universal driver (120V-220V-277V)




DS-CD05


		Diameter	Watt	Beam	Max Delivered Lumens	Max CBCP	Color Temp	CRI	Finish
Ceiling Mount	DS-CD	05 5"	24W	S 20°	1610	7065			BK Black WT White BZ Bronze GH Graphite
				N 27°	1575	4485			
				F 36°	1450	3045			
	06 6"	42W	S 17°	2615	17275	27 2700K 85			
			N 30°	2565	7080	927 2700K 90			
			F 42°	2620	4880	30 3000K 85			
						35 3500K 85			
				40 4000K 85					
08 8"	54W	S 14°	4015	28660					
		N 28°	4005	9390					
		F 40°	4005	6490					

Example: **DS-CD08-S27-BZ**


Tube Architectural LED Pendant Downlight



DS-PD05



DS-PD06



DS-PD08



DS-PD05

Power: 120V - 277V
CRI: Up to 90
0-10V Dimming: 100% - 20%
Rated Life: 80,000 hours



High performance exterior rated LED downlights

- IP65 rated, ETL & cETL wet location listed
- Energy Star® rated
- Solid aluminum construction
- Universal driver (120V-220V-277V)
- Includes three selectable length stems and flat canopy

		Diameter	Watt	Beam	Max Delivered Lumens	Max CBCP	Color Temp	CRI	Finish
Pendant Mount	DS-PD 05	5"	24W	S 20°	1610	7065	27 2700K 85 927 2700K 90 30 3000K 85 930 3000K 90 35 3500K 85 40 4000K 85	85	BK Black WT White BZ Bronze GH Graphite
				N 27°	1575	4485			
				F 36°	1450	3045			
	DS-PD 06	6"	42W	S 17°	2615	17275			
				N 30°	2565	7080			
				F 42°	2620	4880			
	DS-PD 08	8"	54W	S 14°	4015	28660			
				N 28°	4005	9390			
				F 40°	4005	6490			

Example: **DS-PD08-S930-WT**

Mounting Accessories

		Finish
 <p>Swivel Canopy Suspension Kit</p>	<p>DS-PDSK</p> <p>Seismic swivel tilts up to 45° to accommodate sloped ceiling</p> <p>Includes swivel canopy and two 24" extension rods</p> <p>Extendable up to 96" using DS-PDX24</p> <p>Can be field cut</p>	BK Black WT White BZ Bronze GH Graphite
 <p>Extension Rod</p>	<p>DS-PDX24</p> <p>One 24" extension rod for DS-PDSK</p> <p>Can be field cut</p>	BK Black WT White BZ Bronze GH Graphite


Example: **DS-PDSK-WT**




Tube Wall Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours




- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- ADA Compliant
- Mounts up or down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



WS-W2609



WS-W2610

Distribution	Beam	Voltage	Watt	Lumens	Finish	
 Single Light	WS-W2609 Dark Sky Friendly Energy Star®	70°	120V - 277V	16W	825	
 Double Light	WS-W2610	70°	120V - 277V	30W	1525	
					AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White	


Example: **WS-W2609-WT**




Tube Wall Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours




- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- Mounts up or down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



WS-W2605



WS-W2604

Distribution	Beam	Voltage	Watt	Lumens	Finish
 Single Light WS-W2605 <i>Dark Sky Friendly</i> <i>Energy Star®</i>	33°	120V - 277V	16W	800	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White 
 Double Light WS-W2604	33°	120V - 277V	30W	1750	


Example: **WS-W2604-BZ**



Tube Ceiling Mount




Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- CEC Title 24 Compliant
- Ceiling Mount
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



FM-W2612

FM-W2605

	Distribution		Beam	Voltage	Watt	Lumens	Finish
	Down	FM-W2612	91°	120V - 277V	30W	1740	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White
	Down	FM-W2605	33°	120V - 277V	16W	800	


Example: **FM-W2612-GH**




Tube Pendant Mount


Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- CEC Title 24 Compliant
- Die-Cast Aluminum Construction
- Hang Straight Swivel
- Three 12" and one 6" down rods included
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



Distribution	Beam	Voltage	Watt	Lumens	Finish
 Down	33°	120V - 277V	16W	800	AL Brushed Aluminum
					BK Black
					BZ Bronze
					GH Graphite
					WT White


Example: **PD-W2605-BK**




Scoop Wall Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours


- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- Mounts Up or Down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- ADA Compliant
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



WS-W20506

Distribution	Beam	Voltage	Watt	Lumens	Finish
 Single Light	86°	120V - 277V	16W	805	AL Brushed Aluminum
					BK Black
					BZ Bronze
					GH Graphite
					WT White


Example: **WS-W20506-BZ**




Rubix Wall Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours



- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- ADA Compliant
- Mounts Up or Down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



WS-W2509



WS-W2510

Distribution	Beam	Voltage	Watt	Lumens	Finish
 Single Light	WS-W2509 Dark Sky Friendly Energy Star®	86°	120V - 277V	16W	805
 Double Light	WS-W2510	86°	120V - 277V	30W	1385
					AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White




Example: **WS-W2510-GH**





Rubix Wall Mount

Color Temp: 3000K
 CRI: 90
 Rated Life: 70,000 hours

- IP65 Rated, ETL & cETL Wet Location Listed
- Energy Star® rated
- CEC Title 24 Compliant
- Mounts up or down
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



WS-W2504, WS-W2505

Distribution		Beam	Voltage	Watt	Lumens	Finish
 Single Light	WS-W2504 Dark Sky Friendly Energy Star®	86°	120V - 277V	16W	750	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White
 Double Light	WS-W2505	86°	120V - 277V	30W	1400	


Example: **WS-W2504-GH**




Rubix Ceiling Mount

Color Temp: 3000K
CRI: 90
Rated Life: 70,000 hours




- IP65 Rated, ETL & cETL Wet Location Listed
- CEC Title 24 Compliant
- Ceiling Mount
- Die-Cast Aluminum Construction
- Universal Voltage Input (120V - 277V)
- 0 - 10V and ELV dimming - see specification sheet for list of tested dimmers



FM-W2505



FM-W2510

	Distribution		Beam	Voltage	Watt	Lumens	Finish	
	Down	FM-W2505	86°	120V - 277V	16W	750	AL Brushed Aluminum BK Black BZ Bronze GH Graphite WT White	
	Down	FM-W2510	95°	120V - 277V	30W	1875		

Example: **FM-W2510-WT**



New 4 inch model and 6 inch 4000K Color Temperature

Disc LED Ceiling and Wall

Dimming: 100% - 10%
Rated Life: 35,000 hours




- Energy Star® rated
- Wet Location Listed
- CEC Title 24 Compliant
- ADA compliant
- Wall or Ceiling Mount
- Translucent acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- ELV dimming - see specification sheet for list of tested dimmers



Install over a junction box



Retrofit over a 4", 5" or 6" recessed can

	Watt	ColorTemp	CRI	LED Lumens	Delivered Lumens		Finish
 FM-304	12W	930 3000K	90	670	570	<i>Fits over a 4" recessed can</i>	BN Brushed nickel BZ Bronze WT White 
 FM-306	15W	930 3000K 940 4000K	90	1110 1165	865 905	<i>Fits over a 5" to 6" recessed can</i>	








Example: **FM-306-930-WT**



Flo LED Ceiling and Wall New Product

CRI: 85
Dimming: 100% - 10%
Rated Life: 35,000 hours

- Energy Star® rated
- Wall or Ceiling Mount, closet rated
- Translucent acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- ELV dimming - see specification sheet for list of tested dimmers

				Watt	Color Temp	LED Lumens	Delivered Lumens	Finish
		WS-224	24"	20.5W	27 2700K	1670	1190	WT White 
					35 3500K	1870	1340	
		WS-236	36"	31W	27 2700K	2570	1785	
					35 3500K	2865	2005	
		WS-248	48"	40.5W	27 2700K	3280	2325	
					35 3500K	3555	2685	








Example: **WS-236-35-WT**



Glo LED Ceiling and Wall

CRI: 85
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Energy Star® rated
- ADA compliant for FM-211 and FM-214
- Wall or Ceiling Mount
- Translucent acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- ELV dimming - see specification sheet for list of tested dimmers

				Watt	Color Temp	LED Lumens	Delivered Lumens	Finish
		FM-211	11"	15W	27 2700K 35 3500K	1355 1465	990 1100	WT White 
		FM-214	14"	23W	27 2700K 35 3500K	1915 2175	1405 1510	
		FM-216	16"	34W	27 2700K 35 3500K	2815 3015	2175 2260	

Example: **FM-214-35-WT**









Blo LED Ceiling and Wall

New Product

CRI: 85
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Energy Star® rated
- ADA compliant
- Wall or Ceiling Mount
- Translucent acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- ELV dimming - see specification sheet for list of tested dimmers

			Watt	Color Temp	LED Lumens	Delivered Lumens	Finish
		FM-113	13" 23W	27 2700K	1695	1405	WT White 
				35 3500K	1770	1510	
		FM-115	15" 34W	27 2700K	2475	2175	WT White 
				35 3500K	2595	2260	



Example: **FM-115-35-WT**



Vector Fixed Rail

Color Temp: 3000K
CRI: 90
Rated Life: 60,000 hours

- Energy Star® rated
- Individually Adjustable Heads
- ETL & cETL Damp Location Listed
- Wall or Ceiling Mount
- Aluminum Construction
- Universal Voltage Input (120V - 277V)
- Driver located in J box with minimum inside dimension of 3½" x 3½" x 1½"
- 0-10V and ELV dimming - see specification sheet for list of tested dimmers



Brushed Nickel

Brushed Brass

Chrome

		Watt	LED Lumens	Delivered Lumens	Finish
	TK-49534	33W	1500	1465	BN <i>Brushed Nickel</i> BR <i>Brushed Brass</i> CH <i>Chrome</i>


Example: **TK-49534-CH**





Vector Monopoint

Color Temp: 3000K
CRI: 90
Rated Life: 60,000 hours

- Energy Star® rated
- Adjustable Head
- ETL & cETL Damp Location Listed
- Wall or Ceiling Mount
- Aluminum Construction
- Universal Voltage Input (120V - 277V)
- Driver located in J box with minimum inside dimension of 3½" x 3½" x 1½"
- 0-10V and ELV dimming - see specification sheet for list of tested dimmers



		Watt	LED Lumens	Delivered Lumens	Finish	
	MO-495	9W	441	438	BN <i>Brushed Nickel</i> BR <i>Brushed Brass</i> CH <i>Chrome</i>	


Example: **MO-495-BR**



Monterrey Fixed Rail

Color Temp: 3000K
CRI: 90
Rated Life: 60,000 hours

- Individually Adjustable Heads
- CEC Title 24 Compliant
- ETL & cETL Damp Location Listed
- Wall or Ceiling Mount
- Universal Voltage Input (120V - 277V)
- Driver located in J box with minimum inside dimension of 3½" x 3½" x 1½"
- 0-10V and ELV dimming - see specification sheet for list of tested dimmers





Antique Bronze

Antique Nickel

Burnished Brass

Polished Nickel

		Watt	LED Lumens	Delivered Lumens	Finish
	TK-48536	33W	1972	1905	AB <i>Antique Bronze</i> AN <i>Antique Nickel</i> BB <i>Burnished Brass</i> PN <i>Polished Nickel</i>

Example: **TK-48536-AB**

dweLED

by WAC Lighting

[dweL-E-D]

LED technology becomes accessible for decorative luminaires, with transitional styling and 2700K warm white light for even the most demanding applications.

dweLED decorative LED luminaires are designed to integrate within a variety of spaces ranging from multi-family residential to commercial and healthcare. Options include ADA compliance, ELV dimming, 277 volt power, wet location, and a variety of sizes and finishes.


The dweLED collection incorporates indoor and outdoor sconces, vanities, swing-arm reading lights, ceiling-mount lights, picture lights, and chandeliers, all engineered optimally for energy efficient LEDs.

Consult the factory to take advantage of our custom capabilities in large quantities.



Sublime	81	Moderne	106
Slice	83	Aviator	108
Dice	85, 95	Prohibition	109
Niveous	86, 127	Empire	110
Compass	88, 96, 137	Delano	111
Level	89, 121	Corbusier	113
Brink	90, 122	Float	114
Bliss	91, 115	Coco	116
Rondelle	92	Bric	117
Soho	93	Blok	118
Greta	97	Mythical	119
Elementum	98, 125	Laced	123
Kube	99	Mod	128
Ashton	101	Funnel	129
Dunhill	102, 112	Zulu	131
Roswell	103	Folsom	132
Palais	105	Arch	133
Havana	106	Steampunk	135
		Flip	140









Sublime LED Crystal Pendants

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10%
Rated Life: 55,000 hours

- Hand cut clear crystal
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- 10' of wire included
- 3-12" and 1-6" downrods included
- Hang straight swivel
- Driver located in canopy
- Universal driver (120V-220V-277V)





			Watt	LED Lumens	Delivered Lumens	Finish
	8"	PD-88608	11W	690	546	PN <i>Polished Nickel</i> 
	6"	PD-93611	11W	690	546	




Example: **PD-88608-PN / PD-93611-PN**



Slice LED Ceiling and Wall

CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Etched 3/4" thick pressed glass diffuser with interior ceramic glaze
- Mount as a ceiling fixture or wall sconce
- ADA compliant when mounted on wall
- FM-4115 is IP44
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- Also rated for installation in closets
- Transformer located in J box
- 277V available (special order) for FM-4114, FM-4109, FM-4111





		Color Temp	Watt	LED Lumens	Delivered Lumens	Finish
	FM-4114-27*	2700K	31W	1323	595	BN <i>Brushed Nickel</i>
	FM-4114-30*	3000K	31W	1356	670	
	FM-4109-27*	2700K	27W	1356	750	BN <i>Brushed Nickel</i> BZ <i>Bronze</i> CH <i>Chrome</i>
	FM-4109-30*	3000K	27W	1392	770	
	FM-4111-27*	2700K	31W	1593	915	
	FM-4111-30*	3000K	31W	1635	940	
	FM-4115-27	2700K	25W	2130	950	
	FM-4115-30	3000K	25W	2355	1050	

Example: **FM-4111-27-BZ**


*For 277V special order, add an "F" before the color temperature: **FM-4111F-27-BZ**
For alternate color temperature, special order adding -35: **FM-4109-35-BZ**



Dice LED Ceiling and Wall

CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours


- Etched $\frac{3}{4}$ " thick pressed glass diffuser with interior ceramic glaze
- Mount as a ceiling fixture or wall sconce
- ADA compliant when mounted on wall
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- Also rated for installation in closets
- Transformer located in J box
- 277V available (special order) for FM-4014, FM-4006, FM-4009




4014



4006















4009



4012



		Color Temp	Watt	LED Lumens	Delivered Lumens	Finish
	FM-4014-27*	2700K	31W	1323	610	BN <i>Brushed Nickel</i> 
	FM-4014-30*	3000K	31W	1356	640	
	FM-4006-27*	2700K	17.5W	779	355	BN <i>Brushed Nickel</i> 
	FM-4006-30*	3000K	17.5W	800	365	
	FM-4009-27*	2700K	27W	1341	885	BN <i>Brushed Nickel</i>  BZ <i>Bronze</i>  CH <i>Chrome</i> 
	FM-4009-30*	3000K	27W	1376	910	
	FM-4012-27	2700K	25W	1990	890	BN <i>Brushed Nickel</i>  BZ <i>Bronze</i>  CH <i>Chrome</i> 
	FM-4012-30	3000K	25W	2200	985	

Example: **FM-4009-30-CH**

*For 277V special order, add an "F" before the color temperature: **FM-4006F-27-BZ**
For alternate color temperature, special order adding -35: **FM-4009-35-BZ**





Niveous LED Ceiling and Wall

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- Mount as a ceiling fixture or wall sconce
- ETL & cETL Wet location, IP65 rated

- ELV dimming - see specification sheet for list of tested dimmers
- Also rated for installation in closets
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	6"	FM-W52306	9.5W	800	680	WT White 
	9"	FM-W52309	18W	1600	1428	

Example: **FM-W52306-WT**


For 277V, add an "F" before the finish: **FM-W52306F-WT**
 For alternate color temperature, special order adding -27 or -35: **FM-W52306-35-WT**





Compass LED Indoor/Outdoor Ceiling & Wall

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 45,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- Mount as a ceiling fixture or wall sconce
- ELV dimming - see specification sheet for list of tested dimmers
- ADA compliant, low profile design
- ETL & cETL wet location listed, IP65
- Also rated for installation in closets
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	12"	FM-W33612	19W	1647	1147	AL Brushed Aluminum BZ Bronze
	16"	FM-W33616	35W	3112	1668	

Example: **FM-W33616-AL**










Level LED Vanities & Sconces

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Acrylic lens
- CEC Title 24 compliant
- Vertical or horizontal mount
- Adjustable backplate
- ETL & cETL damp location listed
- WS-85618 is ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	19"	WS-85618	15.5W	1300	865	AL Brushed Aluminum 
	25"	WS-85624	20.5W	1735	1255	
	37"	WS-85636	30W	2561	1800	


Example: **WS-85618-AL**







Brink LED Vanities & Sconces


Color Temp: 3500K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Adjustable backplate
- Co-extruded clear and white acrylic provides substance, luminosity and optical efficacy
- Vertical or horizontal mount
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-77618	15.5W	1300	1095	AL Brushed Aluminum 
	24"	WS-77624	20.5W	1735	1460	
	36"	WS-77636	30W	2561	2130	

Example: **WS-77618-AL**







Bliss LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- White mitered glass
- CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-79622	25W	2390	1646	PN Polished Nickel 
	2 Lights	WS-79636	38.5W	3472	2540	

Example: **WS-79622-PN**




For 277V special order, add an "F" before the finish: **WS-79636F-PN**
 For alternate color temperature, special order adding -27 or -35: **WS-79636-35-PN**







Rondelle LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 60,000 hours

- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in J box
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-42505	8.5W	230	220	
	2 Lights	WS-42514	16W	518	490	PN Polished Nickel 
	3 Lights	WS-42524	24.5W	865	805	

Example: **WS-42524-PN**


For 277V special order, add an "F" before the finish: **WS-42524F-PN**







Soho LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Etched opal glass
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant
- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4 inch Jbox included
- Transformer located in J box
- 277V available (special order)





			Watt	LED Lumens	Delivered Lumens	Finish
	11"	WS-6111	16W	700	520	
	17"	WS-6117	25W	1170	860	BN <i>Brushed Nickel</i> CH <i>Chrome</i> GL <i>Gold Plated</i> 
	23"	WS-6123	33.5W	1597	1245	

Example: **WS-6117-GL**

For 277V special order, add an "F" before the finish: **WS-6117F-GL**
 For alternate color temperature, special order adding -30 or -35: **WS-6117-30-GL**





Dice LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Mouth blown etched opal glass
- WS-20624 & WS-20635 are CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet

- for list of tested dimmers
- Conversion plate for 4" J box included
- No transformer or driver required



			Watt	LED Lumens	Delivered Lumens	Finish
	2 Light	WS-20624	24W	1972	1247	
	3 Lights	WS-20635	36W	2898	1672	BN Brushed Nickel 
	4 Lights	WS-20646	48W	3850	2507	

Example: **WS-20624-BN**










Compass LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver required



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-21611	12W	900	495	
	2 Lights	WS-21622	24W	1840	1055	AL Brushed Aluminum 
	3 Lights	WS-21633	35.5W	2665	1675	

Example: **WS-21622-AL**






Greta LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 40,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed

- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver needed



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-82609	10W	679	505	
	2 Lights	WS-82620	20W	1450	970	SN Satin Nickel 
	3 Lights	WS-82631	30.5W	2049	1386	

Example: **WS-82609-SN**










Elementum LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 70,000 hours

- Mouth blown etched opal glass
- Luminaire may be rotated 180° when mounting
- Up & down light
- ETL & cETL damp location listed

- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



		Watt	LED Lumens	Delivered Lumens	Finish
	1 Light WS-76608	8W	468	422	
	2 Lights WS-76612	15W	949	804	SN <i>Satin Nickel</i> 
	3 Lights WS-76622	22W	1335	1110	



Example: **WS-76622-SN**



Kube LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 60,000 hours

- Each light also contains a powerful downlight
- ETL & cETL damp location listed
- ADA compliant for WS-44505
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in J box with minimum inside dimension of 3½" x 3½" x 1½"
- 277V available for WS-44505 and WS-44512 (special order)
- WS-44522 has Universal Driver (120V-220V-277V)







		Watt	LED Lumens	Delivered Lumens	Finish
	1 Light WS-44505*	18W	675	605	
	2 Lights WS-44512*	32W	1554	1355	CH Chrome
	3 Lights WS-44522 (120V-277V Input)	47.5W	2346	2210	

Example: **WS-44505-CH**

*For 277V special order, add an "F" before the finish: **WS-44505F-CH**



Ashton LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Etched opal glass
- Vertical or horizontal mount
- ETL & cETL Wet Location listed
- ADA compliant
- Transformer located in J box

- ELV dimming - see specification sheet for list of tested dimmers
- WS-39513 emits downlight as well as ambient light
- 277V available (special order)

			Watt	LED Lumens	Delivered Lumens	Finish
	13"	WS-39513	25.5W	1093	770	
	22"	WS-39522	30W	1373	990	
	28"	WS-39528	41W	1512	1320	
						AB Antique Bronze AN Antique Nickel BB Burnished Brass PN Polished Nickel 

Example: **WS-39513-BB**

For 277V special order, add an "F" before the finish: **WS-39513F-BB**






Dunhill LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours

- Etched opal glass
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant
- Conversion plate included



- ELV dimming - see specification sheet for list of tested dimmers
- Transformer located in J box
- 277V available (special order)




			Watt	LED Lumens	Delivered Lumens	Finish
	20"	WS-40520	27W	1125	770	
	26"	WS-40526	33.5W	1551	935	
	38"	WS-40538	50W	2437	1330	
						AB <i>Antique Bronze</i> AN <i>Antique Nickel</i> BB <i>Burnished Brass</i> PN <i>Polished Nickel</i>

Example: **WS-40520-PN**


For 277V special order, add an "F" before the finish: **WS-40520F-PN**
 For alternate color temperature, special order adding -30 or -35: **WS-40520-30-PN**



84611



84616







84624

Roswell LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 69,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- Luminaire may be rotated 180° when mounting
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-84611	8.5W	400	355	
	2 Lights	WS-84616	16W	930	815	NR Natural Iron 
	3 Lights	WS-84624	23W	1385	1180	

Example: **WS-84611-NR**






Palais LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 55,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish	
	18"	WS-49618	11W	708	424	SN Satin Nickel	

Example: **WS-49618-SN**

For alternate color temperature, special order adding -27 or -35: **WS-49618-35-SN**






Havana LED Sconce

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 85,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	17"	WS-47617	16W	967	522	SN Satin Nickel 

Example: **WS-47617-SN**

For alternate color temperature, special order adding -27 or -35: **WS-47617-27-SN**






Moderne LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 55,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- Driver located in outlet box
- ELV dimming - see specification sheet for list of tested dimmers
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	15"	WS-40615	20W	1482	887	SN Satin Nickel 

Example: **WS-40615-SN**

For alternate color temperature, special order adding -27 or -35: **WS-40615-27-SN**






Aviator LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-43613	16W	1134	761	SN <i>Satin Nickel</i> 

Example: **WS-43613-SN**

For alternate color temperature, special order adding -27 or -35: **WS-43613-27-SN**






Prohibition LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 55,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



	Height	Watt	LED Lumens	Delivered Lumens	Finish	
	20"	WS-45620	18W	1377	817	SN <i>Satin Nickel</i> 

Example: **WS-45620-SN**

For alternate color temperature, special order adding -27 or -35: **WS-45620-27-SN**






Empire LED Sconce

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 55,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- Driver located in outlet box
- ELV dimming - see specification sheet for list of tested dimmers
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-41618	15.5W	1207	870	SN <i>Satin Nickel</i> 

Example: **WS-41618-SN**

For alternate color temperature, special order adding -27 or -35: **WS-41618-27-SN**






Delano LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- White mitered glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



		Watt	LED Lumens	Delivered Lumens	Finish
	18" WS-87618	25W	1625	1165	SN <i>Satin Nickel</i> 

Example: **WS-87618-SN**


For alternate color temperature, special order adding -27 or -35: **WS-87618-27-SN**




Dunhill LED Vanities & Sconces

Color Temp: 2700K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours


- Etched opal glass
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ELV dimming - see specification sheet for list of tested dimmers
- ADA compliant
- Conversion plate included
- Transformer located in J box
- 277V available (special order)



40520



40526



40538

			Watt	LED Lumens	Delivered Lumens	Finish
	20"	WS-40520	27W	1125	770	
	26"	WS-40526	33.5W	1551	935	
	38"	WS-40538	50W	2437	1330	
						AB <i>Antique Bronze</i> AN <i>Antique Nickel</i> BB <i>Burnished Brass</i> PN <i>Polished Nickel</i>

Example: **WS-40520-PN**


For 277V special order, add an "F" before the finish: **WS-40520F-PN**
 For alternate color temperature, special order adding -30 or -35: **WS-40520-30-PN**





Corbusier LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Super white mitered ceramic glazed glass
- CEC Title 24 compliance
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish	
	15"	WS-42618	20W	1476	827	SN Satin Nickel	

Example: **WS-42618-SN**

For alternate color temperature, special order adding -27 or -35: **WS-42618-27-SN**







Float LED Sconce

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 85,000 hours

- No visible mounting hardware
- Super white mitered ceramic glazed glass
- CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location listed

- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-7312	15W	1125	615	BN <i>Brushed Nickel</i> CH <i>Chrome</i> 
	18"	WS-7318	20.5W	1555	890	

Example: **WS-7318-BN**

For alternate color temperature, special order adding -27 or -35: **WS-7312-27-BN**







Bliss LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- White mitered glass
- CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	1 Light	WS-79622	25W	2390	1646	PN Polished Nickel 
	2 Lights	WS-79636	38.5W	3472	2540	

Example: **WS-79622-PN**

For 277V special order, add an "F" before the finish: **WS-79636F-PN**
 For alternate color temperature, special order adding -27 or -35: **WS-79636-27-PN**






Coco LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- ELV dimming - see specification sheet for list of tested dimmers


- ETL & cETL damp location listed
- Driver located in outlet box
- Universal driver (120V-220V-277V)



	Height	Watt	LED Lumens	Delivered Lumens	Finish	
	9"	WS-46609	21W	1377	873	SN <i>Satin Nickel</i> 

Example: **WS-46609-SN**

For alternate color temperature, special order adding -27 or -35: **WS-46609-27-SN**



New Brushed Bronze Finish


Bric LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours

- Sconce may be rotated 180° when mounting
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- CEC Title 24 compliant

- Mounts on a 4" x 2" horizontal switch box
- Conversion plate for 4" J box included
- Replaceable LED module
- Approved wiring compartment is also within fixture
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	7"	WS-11807	9W	800	660	BN <i>Brushed Nickel</i>
						WT <i>White</i>
						BO <i>Brushed Bronze</i>

Example: **WS-11807-BO**

For 277V special order, add an "F" before the finish: **WS-11807F-BO**
 For alternate color temperature, special order adding -27 or -35: **WS-11807-27-BO**





Blok LED Sconce with Emergency Back Up Battery Option

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 70,000 hours

- Up & down light
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers

- Driver located inside the fixture
- Universal driver (120V-220V-277V)
- Emergency battery back up option (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-25612	29W	1479	1162	SN <i>Satin Nickel</i>
						WT <i>Textured White</i>

Example: **WS-25612-SN**

For emergency battery, add -EM after the finish: **WS-25612-SN-EM**
 For alternate color temperature, special order adding -27 or -35: **WS-25612-27-SN**






Mythical LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours




- Clear seeded glass
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers

- Up & down light
- CEC Title 24 compliant
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-12712	16W	772	559	PN Polished Nickel 

Example: **WS-12712-PN**







Mythical LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours

- Clear seeded glass
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- No driver or transformer needed
- 277V available (special order)

		Height		Watt	LED Lumens	Delivered Lumens	Finish
	Small	13"	WS-12713	5.5W	415	70	PN Polished Nickel 
	Medium	18"	WS-12718	10.5W	830	140	
	Large	24"	WS-12724	10.5W	830	160	

Example: **WS-12718-PN**

For 277V, add an "F" before the finish: **WS-12718F-PN**










Level LED Vanities & Sconces

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Acrylic lens
- CEC Title 24 compliant
- Vertical or horizontal mount
- Adjustable backplate
- ETL & cETL damp location listed
- WS-85618 is ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	19"	WS-85618	15.5W	1300	865	AL Brushed Aluminum 
	25"	WS-85624	20.5W	1735	1255	
	37"	WS-85636	30W	2561	1800	


Example: **WS-85618-AL**







Brink LED Vanities & Sconces

Color Temp: 3500K
CRI: 90
Dimming: 100% - 10%
Rated Life: 85,000 hours

- Adjustable backplate
- Co-extruded clear and white acrylic provides substance, luminosity and optical efficacy.
- Vertical or horizontal mount
- CEC Title 24 compliant
- ETL & cETL damp location listed
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Conversion plate for 4" J box included
- Driver located in outlet box
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish
	18"	WS-77618	15.5W	1300	1095	
	24"	WS-77624	20.5W	1735	1460	AL Brushed Aluminum 
	36"	WS-77636	30W	2561	2130	


Example: **WS-77618-AL**






Laced LED Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 65,000 hours

- Mouth blown etched opal glass
- CEC Title 24 compliant
- Vertical or horizontal mount
- ETL & cETL damp location
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)








			Watt	LED Lumens	Delivered Lumens	Finish
	21"	WS-32621	15.5W	1030	557	BN <i>Brushed Nickel</i> 

Example: **WS-32621-BN**

For alternate color temperature, special order adding -27 or -35: **WS-32621-27-BN**



Elementum LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 70,000 hours

- Mouth blown etched opal glass
- Luminaire may be rotated 180° when mounting
- ETL & cETL damp location listed
- Up & down light

- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located in outlet box
- Universal driver (120V-220V-277V)

		Watt	LED Lumens	Delivered Lumens	Finish
	1 Light WS-76608	8W	468	422	
	2 Lights WS-76612	15W	949	804	SN Satin Nickel 
	3 Lights WS-76622	22W	1335	1110	

Example: **WS-76622-SN**




Elementum LED Pendant

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 65,000 hours

- Mouth blown etched opal glass
- Twist lock glass attachment
- CEC Title 24 compliant
- ETL & cETL damp location listed
- Universal driver (120V-220V-277V)
- Driver located in outlet box

- ELV dimming - see specification sheet for list of tested dimmers
- Hang straight swivel
- 10' of wire included
- 1-6" and 3-12" downrods included



			Watt	LED Lumens	Delivered Lumens	Finish
	11"	PD-26611	15W	1187	858	SN <i>Satin Nickel</i>
	16"	PD-26616	20W	1769	1363	

Example: **PD-26616-SN**

For alternate color temperature, special order adding -27 or -35: **PD-26616-27-SN**




Niveous LED Ceiling and Wall

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 45,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- Mount as a ceiling fixture or wall sconce
- ETL & cETL Wet location, IP65 rated

- ELV dimming - see specification sheet for list of tested dimmers
- Also rated for installation in closets
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	6"	FM-W52306	9.5W	800	680	WT <i>White</i> 
	9"	FM-W52309	18W	1600	1428	

Example: **FM-W52306-WT**

For 277V, add an "F" before the finish: **FM-W52306F-WT**
 For alternate color temperature, special order adding -27 or -35: **FM-W52306-27-WT**






Mod LED Outdoor Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 70,000 hours

- Diecast aluminum construction
- Dark Sky friendly
- Luminaire may be rotated 180° when mounting
- ETL & cETL wet location listed, IP65

- ADA compliant
- ELV dimming - see specification sheet for list of tested dimmers
- Driver located inside the fixture
- Universal driver (120V-220V-277V)



			Watt	LED Lumens	Delivered Lumens	Finish	
	6"	WS-W65607	15W	1165	850	BZ Bronze GH Graphite	



Example: **WS-W65607-GH**






Funnel LED Vanities & Sconces

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 75,000 hours



- Up & down light
- Vertical or horizontal mount (WS-W37617)
- Energy Star® rated
- CEC Title 24 compliant
- ETL & cETL Wet location listed, IP65 rated
- ELV and 0-10V dimming - see specification sheet for list of tested dimmers
- Driver located inside the fixture
- Universal driver (120V-220V-277V)





			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-W37612	21W	1546	997	BZ Bronze 
	17"	WS-W37617	21W	1546	960	

Example: **WS-W37617-BZ**




Zulu LED Outdoor Sconce

Color Temp: 3000K
CRI: 90
Dimming: 90% - 10%
Rated Life: 45,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- ETL & cETL wet location listed, IP65
- ADA compliant, low profile design

- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver required
- 277V available (special order)

			Watt	LED Lumens	Delivered Lumens	Finish
	12"	WS-W67612	12W	875	336	BZ Bronze TT Texture Titanium
	16"	WS-W67616	18W	1471	579	

Example: **WS-W67612-BZ**



For 277V, add an "F" before the finish: **WS-W67612F-BZ**
 For alternate color temperature, special order adding -27 or -35: **WS-W6712-27-BZ**





Folsom LED Outdoor Sconce

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 50,000 hours


- UV rated acrylic, aluminum construction
- Vertical or horizontal mount
- CEC Title 24 compliant
- ETL & cETL Wet Location listed, IP65 rated
- ADA compliant, low profile design
- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver required
- 277V available (special order)



			Watt	LED Lumens	Delivered Lumens	Finish
	10"	WS-W23610	6.5W	630	120	BZ Bronze GH Graphite
	14"	WS-W23614	12W	965	120	

Example: **WS-W23610-GH**


For 277V special order, add an "F" before the finish: **WS-W23610F-GH**





Arch LED Outdoor

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours

- Mounts vertical or horizontal
- ADA compliant
- Die-cast aluminum construction
- ETL & cETL wet location listed, IP65 rated
- ELV dimming - see specification sheet for list of tested dimmers
- 277V available (special order)





			Watt	LED Lumens	Delivered Lumens	Finish
	13"	WS-W26513	5W	154	120	BZ <i>Bronze</i>
	18"	WS-W26518	9.5W	398	225	GH <i>Graphite</i>

Example: **WS-W26518-BZ**


For 277V special order, add an "F" before the finish: **WS-W26518F-BZ**





Steampunk LED Outdoor

Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 80,000 hours


- Clear hammered seeded mouth blown glass
- ETL & cETL wet location listed, IP65 rated
- Die-cast Aluminum Construction
- ELV dimming - see specification sheet for list of tested dimmers
- 277V available (special order)




			Watt	LED Lumens	Delivered Lumens	Finish
	9"	WS-W24509	10W	624	365	BZ Bronze GH Graphite
	13"	WS-W24513	10W	657	440	

Example: **WS-W24513-BZ**

For 277V special order, add an "F" before the finish: **WS-W24513F-BZ**





Pivot hinge on canopy allows installation on sloped ceiling



Steampunk LED Outdoor Pendant

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 80,000 hours

- Clear hammered seeded mouth blown glass
- ETL & cETL wet location listed, IP65 rated
- Die-cast Aluminum Construction
- ELV dimming - see specification sheet for list of tested dimmers
- 277V available (special order)

		Watt	LED Lumens	Delivered Lumens	Finish
	13" PD-W24513	10W	750	470	BZ Bronze GH Graphite 

Example: **PD-W24513-GH**

For 277V special order, add an "F" before the finish: **PD-W24513F-GH**






Compass LED Indoor/Outdoor Pendant

Color Temp: 3000K
CRI: 90
Dimming: 100% - 10%
Rated Life: 35,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- 1-6" and 3-12" downrods included
- 10' of wire included
- Hang straight swivel

- ETL & cETL Wet location listed, IP65 rated
- ELV dimming - see specification sheet for list of tested dimmers
- No transformer or driver required



			Watt	LED Lumens	Delivered Lumens	Finish
	20"	PD-W33620	35W	3200	1890	AL Brushed Aluminum BZ Bronze
						


Example: **PD-W33620-AL**



Compass LED Indoor/Outdoor Ceiling & Wall


Color Temp: 3000K
 CRI: 90
 Dimming: 100% - 10%
 Rated Life: 45,000 hours

- Aluminum construction
- Mouth blown etched opal glass
- CEC Title 24 compliant
- Mount as a ceiling fixture or wall sconce
- ELV dimming - see specification sheet for list of tested dimmers
- ADA compliant, low profile design
- ETL & cETL wet location listed, IP65
- Also rated for installation in closets
- No transformer or driver required



			Watt	LED Lumens	Delivered Lumens	Finish
	12"	FM-W33612	19W	1647	1147	AL Brushed Aluminum BZ Bronze
	16"	FM-W33616	35W	3112	1668	

Example: **FM-W33616-AL**



Flip LED Floor

Color Temp: 3000K

CRI: 85

Dimming: 100% - 10% (Integral dimmer)

Rated Life: 70,000 hours

- Fingertip touch dimmer
- Smooth arm swivel
- ETL & cETL damp location listed
- Driver located at the plug

	Watt	LED Lumens	Delivered Lumens	Finish
FL-1350	8W	490	430	BZ <i>Bronze</i> TT <i>Titanium</i>

Example: **FL-1350-BZ**



Flip LED Task


Color Temp: 3000K

CRI: 85

Dimming: 100% - 10% (Integral dimmer)

Rated Life: 70,000 hours

- Fingertip touch dimmer
- Smooth arm swivel
- ETL & cETL damp location listed
- Driver located at the plug



	Watt	LED Lumens	Delivered Lumens	Finish	
TL-1310	8W	490	430	BZ Bronze TT Titanium	

Example: **TL-1310-BZ**

WAC LIGHTING
Responsible Lighting®

Many LED luminaire designs within contain patent pending features.

WAC Lighting will not hesitate to enforce its intellectual property rights through injunctive relief and seek further relief through damages if it has reason to believe the patents are being infringed upon.

wacighting.com 1-800-526-2588

WAC Lighting retains the right to modify the design of our products at any time as part of the company's continuous improvement program.
Please refer to our website for the latest product specifications. Copyright 2015