


# Straight Blade Devices

Pass & Seymour



**PlugTail™. The fastest, most consistent and reliable wiring devices – ever!** Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. The connector simply snaps into the back of the device – no preparing, stripping or looping conductors, no exposed terminals to tighten or tape, and no mistakes mean no costly callbacks! Now device installation is a snap!



## Index

Device	Rating	Page Number
PlugTail™ Extra Heavy-Duty Receptacles	15 & 20A, 125V	B-2 – B-4
Extra Heavy-Duty Hospital Grade Receptacles	15 & 20A, 125V; 20A, 250V	B-5
Extra Heavy-Duty Hospital Grade MRI Receptacles	15 & 20A, 125V	B-6
Heavy-Duty Hospital Grade Receptacles	15 & 20A, 125V	B-7
Industrial Extra Heavy-Duty Specification Grade Receptacles	15 & 20A, 125 & 250V	B-8, B-9
Heavy-Duty Specification Grade Receptacles	15 & 20A, 125 & 250V	B-10
PlugTail™ Specification Grade Receptacles	15 & 20A, 125V	B-11
Hard Use Specification Grade Receptacles	15 & 20A, 125V; 15A, 250V	B-12
Construction Specification Grade Receptacles	15 & 20A, 125V	B-13, B-14
Commercial Specification Grade Receptacles	15 & 20A, 125V	B-15
Heavy-Duty Specification Grade Single Receptacles	15 & 20A, 125 & 250V	B-16
Commercial Specification Grade Single Receptacles	15 & 20A, 125 & 250V	B-17
Tamper-Resistant Duplex Receptacles	15 & 20A, 125V	B-18, B-19
Isolated Ground Receptacles	15 & 20A, 125V; 20A, 250V	B-20
PlugTail™ Decorator Receptacles	15 & 20A, 125V	B-21
Hospital & Specification Grade Decorator Receptacles	15 & 20A, 125 & 250V	B-22 – B-24
TradeMaster® Receptacles	15A, 125V	B-25
TradeMaster® Decorator Receptacles & Combination Receptacles	15A, 125V	B-26 – B-29
TradeMaster® Decorator Hallway Lights & Combination Devices	15A, 120/125VAC	B-30
TradeMaster®, Specification & Hospital Grade GFCI Receptacles	15 & 20A, 125VAC	B-31 – B-34
Decorator Combination GFCI Receptacles	15A, 125VAC	B-35, B-36
TVSS Straight Blade Receptacles	15 & 20A, 125VAC	B-37, B-38
Quad Receptacles & Specifications & Accessories	15 & 20A, 125V	B-39, B-40
Dust & Moisture Resistant & Clock Hanger Receptacles	15 & 20A, 125V	B-41
Power Outlet Receptacles & Plugs	20, 30, 50 & 60A	B-42 – B-44
Miscellaneous Configurations		B-45
Power & TVSS Strips & Device Specifications		B-46, B-47

Pass & Seymour



# Straight Blade Devices PlugTail™ Extra Heavy-Duty Specification Grade Receptacles

**Auto-ground clip**  
assures positive ground.


**Two drive screws anchor strap**  
to back body and face.

**Exclusive patented feature, circuit label on face** allows permanent circuit identification.

**Strap tabs wrap around and lock down on face** to prevent strap from separating from face and back body.

**.036 inch thick, brass, triple-wipe power contacts** for lasting retention.

**Tamper-resistant version** features dual mechanical shutter system to help prevent insertion of foreign objects.





**No exposed terminals** create a finger-safe application before, during, and after installation.

**Large crimped and welded brass contacts** snugly terminate on device blade terminals.

**Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.

**Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.




**Pre-stripped connector leads** fasten to conductors, easier than standard pigtailed.

PT5362A-W


# Straight Blade Devices PlugTail™ Extra Heavy-Duty Specification Grade Receptacles

15 & 20A, 125V


Pass & Seymour



PT5362A-W



PTTR63-W




PT6STR

PTR6STR

Catalog Number	Rating A. V.		Color	NEMA Config. No.	3rd Party Compliance	
					UL498	FSUL WC596
<b>Duplex Receptacles</b>						
PT5262A-I	15	125	Ivory	5-15R	•	•
PT5262A-W	15	125	White	5-15R	•	•
PT5262A	15	125	Brown	5-15R	•	•
PT5262A-GRY	15	125	Gray	5-15R	•	•
PT5262A-BK	15	125	Black	5-15R	•	•
PT5262A-BL	15	125	Blue	5-15R	•	•
PT5262A-RED	15	125	Red	5-15R	•	•
PT5262A-LA	15	125	Light Almond	5-15R	•	•
PT5362A-I	20	125	Ivory	5-20R	•	•
PT5362A-W	20	125	White	5-20R	•	•
PT5362A	20	125	Brown	5-20R	•	•
PT5362A-GRY	20	125	Gray	5-20R	•	•
PT5362A-BK	20	125	Black	5-20R	•	•
PT5362A-BL	20	125	Blue	5-20R	•	•
PT5362A-RED	20	125	Red	5-20R	•	•
PT5362A-LA	20	125	Light Almond	5-20R	•	•
<b>Tamper-Resistant Duplex Receptacles</b>						
PTTR62-I	15	125	Ivory	5-15R	•	•
PTTR62-W	15	125	White	5-15R	•	•
PTTR62	15	125	Brown	5-15R	•	•
PTTR62-GRY	15	125	Gray	5-15R	•	•
PTTR62-BK	15	125	Black	5-15R	•	•
PTTR62-BL	15	125	Blue	5-15R	•	•
PTTR62-RED	15	125	Red	5-15R	•	•
PTTR62-LA	15	125	Light Almond	5-15R	•	•
PTTR63-I	20	125	Ivory	5-20R	•	•
PTTR63-W	20	125	White	5-20R	•	•
PTTR63	20	125	Brown	5-20R	•	•
PTTR63-GRY	20	125	Gray	5-20R	•	•
PTTR63-BK	20	125	Black	5-20R	•	•
PTTR63-BL	20	125	Blue	5-20R	•	•
PTTR63-RED	20	125	Red	5-20R	•	•
PTTR63-LA	20	125	Light Almond	5-20R	•	•

Catalog Number	Wire Type	Wire Length
<b>PlugTail Connectors*</b>		
PT6STR	Stranded	6"
PT6SOL	Solid	6"
<b>PlugTail Connectors – Right Angle*</b>		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"

2 Pole, 3 Wire



NEMA 5-15R

NEMA 5-20R

\*All PlugTail Connectors are available in various Wire Lengths, please use Configurable Solutions to order.


Configurable Solutions for PlugTail Receptacles and Connectors, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Straight Blade Devices

PlugTail™ EHD Specification Grade Receptacles

Pass & Seymour




PT8300-W



PTTR63H-W



2 Pole, 3 Wire



NEMA 5-15R

NEMA 5-20R

# Straight Blade Devices PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles

15 & 20A, 125V

### Features

- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				UL498	FSUL WC596
<b>Duplex Receptacles</b>					
PT8200-I	15 125	Ivory	5-15R	•	•
PT8200-W	15 125	White	5-15R	•	•
PT8200	15 125	Brown	5-15R	•	•
PT8200-GRY	15 125	Gray	5-15R	•	•
PT8200-BK	15 125	Black	5-15R	•	•
PT8200-BL	15 125	Blue	5-15R	•	•
PT8200-RED	15 125	Red	5-15R	•	•
PT8200-LA	15 125	Light Almond	5-15R	•	•
PT8300-I	20 125	Ivory	5-20R	•	•
PT8300-W	20 125	White	5-20R	•	•
PT8300	20 125	Brown	5-20R	•	•
PT8300-GRY	20 125	Gray	5-20R	•	•
PT8300-BK	20 125	Black	5-20R	•	•
PT8300-BL	20 125	Blue	5-20R	•	•
PT8300-RED	20 125	Red	5-20R	•	•
PT8300-LA	20 125	Light Almond	5-20R	•	•
<b>Tamper-Resistant Duplex Receptacles</b>					
PTTR62H-I	15 125	Ivory	5-15R	•	•
PTTR62H-W	15 125	White	5-15R	•	•
PTTR62H	15 125	Brown	5-15R	•	•
PTTR62H-GRY	15 125	Gray	5-15R	•	•
PTTR62H-BK	15 125	Black	5-15R	•	•
PTTR62H-BL	15 125	Blue	5-15R	•	•
PTTR62H-RED	15 125	Red	5-15R	•	•
PTTR62H-LA	15 125	Light Almond	5-15R	•	•
PTTR63H-I	20 125	Ivory	5-20R	•	•
PTTR63H-W	20 125	White	5-20R	•	•
PTTR63H	20 125	Brown	5-20R	•	•
PTTR63H-GRY	20 125	Gray	5-20R	•	•
PTTR63H-BK	20 125	Black	5-20R	•	•
PTTR63H-BL	20 125	Blue	5-20R	•	•
PTTR63H-RED	20 125	Red	5-20R	•	•
PTTR63H-LA	20 125	Light Almond	5-20R	•	•

For PlugTail Connectors, see Page B-3.

Configurable Solutions for PlugTail Receptacles and Connectors, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.



# Straight Blade Devices Extra Heavy-Duty Hospital Grade Receptacles

15 & 20A, 125V; 20A, 250V

**Pass & Seymour**




Straight Blade Devices


Extra Heavy-Duty Hospital Grade Receptacles

Features	
<ul style="list-style-type: none"> <li>■ One-piece brass mounting strap with integral ground.</li> <li>■ Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.</li> <li>■ Two drive screws anchor strap to back body and face.</li> <li>■ Exclusive patented feature, circuit label on face allows permanent circuit identification.</li> <li>■ .040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention.</li> <li>■ Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.</li> <li>■ Impact-resistant nylon face and back body.</li> <li>■ Oversized #10 deep tri-drive head brass terminal and ground screws.</li> </ul>	<ul style="list-style-type: none"> <li>■ Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.</li> <li>■ External nickel-plated screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.</li> <li>■ Line terminals accept #14 – #10 AWG stranded or solid copper clad conductors.</li> <li>■ Auto-ground clip assures positive ground.</li> <li>■ Illuminated version features exclusive LED lamp with solder connection for long durable life (10-12 years).</li> </ul>

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	CS C22.2 No. 42
<b>Duplex Receptacles Back &amp; Side Wire</b>						
8200-I	15 125	Ivory	5-15R	•	•	•
8200-W	15 125	White	5-15R	•	•	•
8200	15 125	Brown	5-15R	•	•	•
8200-GRY	15 125	Gray	5-15R	•	•	•
8200-BK	15 125	Black	5-15R	•	•	•
8200-RED	15 125	Red	5-15R	•	•	•
8200-LA	15 125	Light Almond	5-15R	•	•	•
8300-I	20 125	Ivory	5-20R	•	•	•
8300-W	20 125	White	5-20R	•	•	•
8300	20 125	Brown	5-20R	•	•	•
8300-GRY	20 125	Gray	5-20R	•	•	•
8300-BK	20 125	Black	5-20R	•	•	•
8300-RED	20 125	Red	5-20R	•	•	•
8300-LA	20 125	Light Almond	5-20R	•	•	•
8800-I	20 250	Ivory	6-20R	•	•	•
8800-W	20 250	White	6-20R	•	•	•
8800	20 250	Brown	6-20R	•	•	•
8800-GRY	20 250	Gray	6-20R	•	•	•
8800-BK	20 250	Black	6-20R	•	•	•
8800-RED	20 250	Red	6-20R	•	•	•
<b>LED Illuminated Face Duplex Receptacles Back &amp; Side Wire</b>						
8200-ILI	15 125	Ivory	5-15R	•	•	•
8200-ILRED	15 125	Red	5-15R	•	•	•
8200-ILW	15 125	White	5-15R	•	•	•
8300-ILI	20 125	Ivory	5-20R	•	•	•
8300-ILRED	20 125	Red	5-20R	•	•	•
8300-ILLA	20 125	Light Almond	5-20R	•	•	•
8300-ILGRY	20 125	Gray	5-20R	•	•	•



**8300-I**



**8300-ILI**

2 Pole, 3 Wire



**NEMA  
5-15R**



**NEMA  
5-20R**



**NEMA  
6-20R**

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.




# Straight Blade Devices Extra Heavy-Duty Hospital Grade MRI Receptacles

15 & 20A, 125V

**Receptacles designed expressly for MRI applications** – We build these exclusive P&S receptacles with no ferrous metal, so they are perfect for high-magnetic-field environments such as magnetic-resonance imaging (MRI) suites. With the same basic design as our standard Extra Heavy-Duty Receptacles, they are extremely durable.

Features	
<ul style="list-style-type: none"> <li>Exclusive patented feature, circuit label on face allows permanent circuit identification.</li> <li>Extra heavy-duty brass, one-piece mounting strap with integral ground for superior structural integrity and long-term performance.</li> <li>.036 inch thick, brass, triple-wipe power contacts for lasting retention.</li> <li>Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.</li> </ul>	<ul style="list-style-type: none"> <li>Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.</li> <li>Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.</li> <li>External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.</li> <li>Auto-ground clip assures positive ground.</li> </ul>



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL498	FSUL WC596	CS C22.2 No. 42
<b>Hospital Grade Duplex Receptacles Back &amp; Side Wire</b>						
<b>8200-IMRI</b>	15 125	Ivory	5-15R	•	•	•
<b>8200-WMRI</b>	15 125	White	5-15R	•	•	•
<b>8200-MRI</b>	15 125	Brown	5-15R	•	•	•
<b>8200-GRYMRI</b>	15 125	Gray	5-15R	•	•	•
<b>8200-BKMRI</b>	15 125	Black	5-15R	•	•	•
<b>8200-REDMRI</b>	15 125	Red	5-15R	•	•	•
<b>8200-LAMRI</b>	15 125	Light Almond	5-15R	•	•	•
<b>8300-IMRI</b>	20 125	Ivory	5-20R	•	•	•
<b>8300-WMRI</b>	20 125	White	5-20R	•	•	•
<b>8300-MRI</b>	20 125	Brown	5-20R	•	•	•
<b>8300-GRYMRI</b>	20 125	Gray	5-20R	•	•	•
<b>8300-BKMRI</b>	20 125	Black	5-20R	•	•	•
<b>8300-REDMRI</b>	20 125	Red	5-20R	•	•	•
<b>8300-LAMRI</b>	20 125	Light Almond	5-20R	•	•	•

2 Pole, 3 Wire



NEMA  
5-15R



NEMA  
5-20R

# Straight Blade Devices Heavy-Duty Hospital Grade Receptacles

15 & 20A, 125V

Pass & Seymour




Straight Blade Devices

Heavy-Duty Hospital Grade Receptacles


Features	
<ul style="list-style-type: none"> <li>Heavy-duty, brass strap for added strength and ground conductivity.</li> <li>.032 inch thick, brass, triple-wipe power contacts for lasting retention.</li> <li>Strap tabs wrap around face to prevent strap from separating from face and back body.</li> <li>Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.</li> </ul>	<ul style="list-style-type: none"> <li>Two drive screws anchor strap to back body and face.</li> <li>Tri-drive brass terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for more wiring flexibility.</li> <li>Auto-ground clip assures positive ground.</li> <li>Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up.</li> </ul>

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	CS C22.2 No. 42
<b>Duplex Receptacles Back &amp; Side Wire</b>						
PS8200-HI	15 125	Ivory	5-15R	•	•	•
PS8200-HW	15 125	White	5-15R	•	•	•
PS8200-H	15 125	Brown	5-15R	•	•	•
PS8200-HGRY	15 125	Gray	5-15R	•	•	•
PS8200-HRED	15 125	Red	5-15R	•	•	•
PS8200-HLA	15 125	Light Almond	5-15R	•	•	•
PS8300-HI	20 125	Ivory	5-20R	•	•	•
PS8300-HW	20 125	White	5-20R	•	•	•
PS8300-H	20 125	Brown	5-20R	•	•	•
PS8300-HGRY	20 125	Gray	5-20R	•	•	•
PS8300-HRED	20 125	Red	5-20R	•	•	•
PS8300-HLA	20 125	Light Almond	5-20R	•	•	•
<b>Duplex Receptacles – Smooth Face Back &amp; Side Wire</b>						
PS8200-HSI	15 125	Ivory	5-15R	•	•	•
PS8200-HSW	15 125	White	5-15R	•	•	•
PS8200-HS	15 125	Brown	5-15R	•	•	•
PS8200-HSGRY	15 125	Gray	5-15R	•	•	•
PS8200-HSBK	15 125	Black	5-15R	•	•	•
PS8200-HSRED	15 125	Red	5-15R	•	•	•
PS8200-HSLA	15 125	Light Almond	5-15R	•	•	•
PS8300-HSI	20 125	Ivory	5-20R	•	•	•
PS8300-HSW	20 125	White	5-20R	•	•	•
PS8300-HS	20 125	Brown	5-20R	•	•	•
PS8300-HSGRY	20 125	Gray	5-20R	•	•	•
PS8300-HSBK	20 125	Black	5-20R	•	•	•
PS8300-HSRED	20 125	Red	5-20R	•	•	•
PS8300-HSLA	20 125	Light Almond	5-20R	•	•	•

**NEW**



PS8200-HI



PS8300-HSLA

2 Pole, 3 Wire



NEMA  
5-15R



NEMA  
5-20R

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

# Straight Blade Devices Industrial Extra Heavy-Duty Specification Grade Receptacles

**.036 inch thick, brass, triple-wipe power contacts** for lasting retention.

**Strap tabs wrap around and lock down on face** to prevent strap from separating from face and back body.

**Exclusive patented feature, circuit label on face** allows permanent circuit identification.

**Exclusive, patented feature, external screw-pressure-plate back wire clamp on ground terminal** for faster, easier installation.


**External screw-pressure-plate back wire clamps with #10 brass terminal screws** for visual assurance of a good connection.

**Two drive screws anchor strap** to back body and face where abrupt removal torque is strongest.

5362-AI

**Auto-ground clip** assures positive ground.

**Heavy-duty, one-piece brass strap** and integral ground for added strength and safety.





# Straight Blade Devices Industrial Extra Heavy-Duty Specification Grade Receptacles

15 & 20A, 125 & 250V


**Pass & Seymour**



Straight Blade Devices


Features	
<ul style="list-style-type: none"> <li>■ One-piece brass mounting strap with integral ground.</li> <li>■ Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.</li> <li>■ Two drive screws anchor strap to back body and face.</li> <li>■ Exclusive patented feature, circuit label on face allows permanent circuit identification.</li> <li>■ .036 inch thick, brass, triple-wipe power contacts for lasting retention.</li> <li>■ Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.</li> <li>■ Impact-resistant nylon face and back body.</li> <li>■ Oversized #10 deep tri-drive head brass terminal and ground screws.</li> </ul>	<ul style="list-style-type: none"> <li>■ Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.</li> <li>■ External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.</li> <li>■ Line terminals accept #14 – #10 AWG stranded or solid copper clad conductors.</li> <li>■ Auto-ground clip assures positive ground.</li> <li>■ Corrosion-resistant models have nickel-plated straps and contacts.</li> </ul>

Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance		
	A.	V.			UL	FSUL	CS
<b>Duplex Receptacles Back &amp; Side Wire</b>							
5262-AI	15	125	Ivory	5-15R	•	•	•
5262-AW	15	125	White	5-15R	•	•	•
5262-A	15	125	Brown	5-15R	•	•	•
5262-AGRY	15	125	Gray	5-15R	•	•	•
5262-ABK	15	125	Black	5-15R	•	•	•
5262-ARED	15	125	Red	5-15R	•	•	•
5262-ALA	15	125	Light Almond	5-15R	•	•	•
CR6200*	15	125	Yellow	5-15R	•	•	•
5362-AI	20	125	Ivory	5-20R	•	•	•
5362-AW	20	125	White	5-20R	•	•	•
5362-A	20	125	Brown	5-20R	•	•	•
5362-AGRY	20	125	Gray	5-20R	•	•	•
5362-ABK	20	125	Black	5-20R	•	•	•
5362-ARED	20	125	Red	5-20R	•	•	•
5362-ALA	20	125	Light Almond	5-20R	•	•	•
CR6300*	20	125	Yellow	5-20R	•	•	•
5662-AI	15	250	Ivory	6-15R	•	•	•
5662-AW	15	250	White	6-15R	•	•	•
5662-A	15	250	Brown	6-15R	•	•	•
5662-AGRY	15	250	Gray	6-15R	•	•	•
5662-ABK	15	250	Black	6-15R	•	•	•
5662-ARED	15	250	Red	6-15R	•	•	•
5862-AI	20	250	Ivory	6-20R	•	•	•
5862-AW	20	250	White	6-20R	•	•	•
5862-A	20	250	Brown	6-20R	•	•	•
5862-AGRY	20	250	Gray	6-20R	•	•	•
5862-ABK	20	250	Black	6-20R	•	•	•
5862-ARED	20	250	Red	6-20R	•	•	•
5862-ALA	20	250	Light Almond	6-20R	•	•	•



\*Corrosion-Resistant.

2 Pole, 3 Wire



For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Industrial EHD Spec. Grade Receptacles

# Straight Blade Devices Heavy-Duty Specification Grade Receptacles

15 & 20A, 125 & 250V

### Features

- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- High strength nylon face.
- Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors. Eight back wire holes.
- Auto-ground clip assures positive ground.



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL498	FSUL WC596	C22.2 No. 42
<b>Duplex Receptacles Back &amp; Side Wire</b>						
PS5262-I	15 125	Ivory	5-15R	•	•	•
PS5262-W	15 125	White	5-15R	•	•	•
PS5262	15 125	Brown	5-15R	•	•	•
PS5262-GRY	15 125	Gray	5-15R	•	•	•
PS5262-BK	15 125	Black	5-15R	•	•	•
PS5262-RED	15 125	Red	5-15R	•	•	•
PS5262-LA	15 125	Light Almond	5-15R	•	•	•
PS5262-BL	15 125	Blue	5-15R	•	•	•
PS5362-I	20 125	Ivory	5-20R	•	•	•
PS5362-W	20 125	White	5-20R	•	•	•
PS5362	20 125	Brown	5-20R	•	•	•
PS5362-GRY	20 125	Gray	5-20R	•	•	•
PS5362-BK	20 125	Black	5-20R	•	•	•
PS5362-RED	20 125	Red	5-20R	•	•	•
PS5362-LA	20 125	Light Almond	5-20R	•	•	•
PS5362-BL	20 125	Blue	5-20R	•	•	•
5662-I	15 250	Ivory	6-15R	•	•	•
5662-W	15 250	White	6-15R	•	•	•
5662	15 250	Brown	6-15R	•	•	•
5862-I	20 250	Ivory	6-20R	•	•	•
5862-W	20 250	White	6-20R	•	•	•
5862	20 250	Brown	6-20R	•	•	•
5862-GRY	20 250	Gray	6-20R	•	•	•
5862-BK	20 250	Black	6-20R	•	•	•
5862-RED	20 250	Red	6-20R	•	•	•

For Configurable Solutions, see Page U-1.

2 Pole, 3 Wire



**NEMA  
5-15R**



**NEMA  
5-20R**



**NEMA  
6-15R**



**NEMA  
6-20R**

# Straight Blade Devices PlugTail™ Specification Grade Receptacles

15 & 20A, 125V


Pass & Seymour




Straight Blade Devices

## Features

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance..
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Crimped and welded contacts.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.
- Isolated ground version features a plastic barrier that isolates grounding terminal from mounting strap and metal boxes.



PT5362-LA



PTIG5362-LA

2 Pole, 3 Wire



NEMA  
5-15R



NEMA  
5-20R

Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance	
	A.	V.			UL498	FSUL WC596
<b>Duplex Receptacles</b>						
PT5262-I	15	125	Ivory	5-15R	•	•
PT5262-W	15	125	White	5-15R	•	•
PT5262	15	125	Brown	5-15R	•	•
PT5262-GRY	15	125	Gray	5-15R	•	•
PT5262-BL	15	125	Blue	5-15R	•	•
PT5262-RED	15	125	Red	5-15R	•	•
PT5262-LA	15	125	Light Almond	5-15R	•	•
PT5362-I	20	125	Ivory	5-20R	•	•
PT5362-W	20	125	White	5-20R	•	•
PT5362	20	125	Brown	5-20R	•	•
PT5362-GRY	20	125	Gray	5-20R	•	•
PT5362-BL	20	125	Blue	5-20R	•	•
PT5362-RED	20	125	Red	5-20R	•	•
PT5362-LA	20	125	Light Almond	5-20R	•	•
<b>Isolated Ground Duplex Receptacles</b>						
PTIG5262-I	15	125	Ivory	5-15R	•	•
PTIG5262-W	15	125	White	5-15R	•	•
PTIG5262	15	125	Orange	5-15R	•	•
PTIG5262-GRY	15	125	Gray	5-15R	•	•
PTIG5262-RED	15	125	Red	5-15R	•	•
PTIG5262-LA	15	125	Light Almond	5-15R	•	•
PTIG5362-I	20	125	Ivory	5-20R	•	•
PTIG5362-W	20	125	White	5-20R	•	•
PTIG5362	20	125	Orange	5-20R	•	•
PTIG5362-GRY	20	125	Gray	5-20R	•	•
PTIG5362-RED	20	125	Red	5-20R	•	•
PTIG5362-LA	20	125	Light Almond	5-20R	•	•

NEW

NEW

For PlugTail Connectors, see Page B-3.

Configurable Solutions for PlugTail Receptacles and Connectors, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

PlugTail™ Specification Grade Receptacles

Pass & Seymour




# Straight Blade Devices Hard Use Specification Grade Receptacles

15 & 20A, 125V; 15A, 250V

### Features


- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 – 14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	CS C22.2 No. 42
<b>Duplex Receptacles Back &amp; Side Wire</b>						
5262-I	15 125	Ivory	5-15R	•	•	•
5262-W	15 125	White	5-15R	•	•	•
5262	15 125	Brown	5-15R	•	•	•
5262-GRY	15 125	Gray	5-15R	•	•	•
5262-BK	15 125	Black	5-15R	•	•	•
5262-LA	15 125	Light Almond	5-15R	•	•	•
5362-I	20 125	Ivory	5-20R	•	•	•
5362-W	20 125	White	5-20R	•	•	•
5362	20 125	Brown	5-20R	•	•	•
5362-GRY	20 125	Gray	5-20R	•	•	•
5362-BK	20 125	Black	5-20R	•	•	•
5362-LA	20 125	Light Almond	5-20R	•	•	•
5362-BL	20 125	Blue	5-20R	•	•	•
5652-I	15 250	Ivory	6-15R	•	•	•
5652	15 250	Brown	6-15R	•	•	•
5652-BK	15 250	Black	6-15R	•	•	•
5652-LA	15 250	Light Almond	6-15R	•	•	•
<b>Duplex Receptacles Side Wire Only</b>						
5642-I	15 250	Ivory	6-15R	•	•	•
5642	15 250	Brown	6-15R	•	•	•

For Configurable Solutions, see Page U-1.

2 Pole, 3 Wire



All devices listed on this page conform to NEMA WD-1 and WD-6.


# Straight Blade Devices Construction Specification Grade Receptacles

15 & 20A, 125V


Pass & Seymour



Features	
<ul style="list-style-type: none"> <li>Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.</li> <li>.032 inch thick, brass, triple-wipe power contacts for lasting retention.</li> <li>Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.</li> <li>Impact-resistant nylon face and thermoplastic back body.</li> </ul>	<ul style="list-style-type: none"> <li>8 hole internal screw-pressure-plate back wire terminals accept #10 – 14 AWG solid or stranded copper or copper-clad conductors.</li> <li>Terminal compartments isolated from each other for positive conductor containment.</li> <li>Tri-drive terminal and mounting screws.</li> <li>Auto-ground clip assures positive ground.</li> <li>Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up.</li> </ul>



CRB5362-I




CRB5362S-LA

Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance		
	A.	V.			UL	FSUL	CS
<b>Duplex Receptacles Back &amp; Side Wire</b>							
CRB5262-I	15	125	Ivory	5-15R	•	•	•
CRB5262-W	15	125	White	5-15R	•	•	•
CRB5262	15	125	Brown	5-15R	•	•	•
CRB5262-GRY	15	125	Gray	5-15R	•	•	•
CRB5262-BK	15	125	Black	5-15R	•	•	•
CRB5262-RED	15	125	Red	5-15R	•	•	•
CRB5262-LA	15	125	Light Almond	5-15R	•	•	•
CRB5362-I	20	125	Ivory	5-20R	•	•	•
CRB5362-W	20	125	White	5-20R	•	•	•
CRB5362	20	125	Brown	5-20R	•	•	•
CRB5362-GRY	20	125	Gray	5-20R	•	•	•
CRB5362-BK	20	125	Black	5-20R	•	•	•
CRB5362-RED	20	125	Red	5-20R	•	•	•
CRB5362-LA	20	125	Light Almond	5-20R	•	•	•
<b>Duplex Receptacles – Smooth Face Back &amp; Side Wire</b>							
CRB5262S-I	15	125	Ivory	5-15R	•	•	•
CRB5262S-W	15	125	White	5-15R	•	•	•
CRB5262S	15	125	Brown	5-15R	•	•	•
CRB5262S-GRY	15	125	Gray	5-15R	•	•	•
CRB5262S-BK	15	125	Black	5-15R	•	•	•
CRB5262S-RED	15	125	Red	5-15R	•	•	•
CRB5262S-LA	15	125	Light Almond	5-15R	•	•	•
CRB5362S-I	20	125	Ivory	5-20R	•	•	•
CRB5362S-W	20	125	White	5-20R	•	•	•
CRB5362S	20	125	Brown	5-20R	•	•	•
CRB5362S-GRY	20	125	Gray	5-20R	•	•	•
CRB5362S-BK	20	125	Black	5-20R	•	•	•
CRB5362S-RED	20	125	Red	5-20R	•	•	•
CRB5362S-LA	20	125	Light Almond	5-20R	•	•	•

NEW

For Configurable Solutions, see Page U-1.

2 Pole, 3 Wire



All devices listed on this page conform to NEMA WD-1 and WD-6.






# Straight Blade Devices Construction Specification Grade Receptacles

15 & 20A, 125V

### Features

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Impact-resistant nylon face and thermoplastic back body.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- Pre-wired with welded wire leads that create faster, more reliable connections. Split circuit capable types have four leads – 2 hot, 1 neutral, and 1 ground. (Non-split circuit types have a total of three leads – 1 hot, 1 neutral, and 1 ground.)
- Pre-stripped leads fasten to conductors, faster than standard pigtails.



CRL5362-LA

2 Pole, 3 Wire



NEMA 5-15R



NEMA 5-20R



Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance		
	A.	V.			UL498	FSUL WC596	C22.2 No. 42
<b>Duplex Receptacles with 6" Leads</b>							
CRL5262-IB	15	125	Ivory	5-15R	•	•	•
CRL5262-WB	15	125	White	5-15R	•	•	•
CRL5262-B	15	125	Brown	5-15R	•	•	•
CRL5262-GRYB	15	125	Gray	5-15R	•	•	•
CRL5262-BKB	15	125	Black	5-15R	•	•	•
CRL5262-REDB	15	125	Red	5-15R	•	•	•
CRL5262-LAB	15	125	Light Almond	5-15R	•	•	•
CRL5362-IB	20	125	Ivory	5-20R	•	•	•
CRL5362-WB	20	125	White	5-20R	•	•	•
CRL5362-B	20	125	Brown	5-20R	•	•	•
CRL5362-GRYB	20	125	Gray	5-20R	•	•	•
CRL5362-BKB	20	125	Black	5-20R	•	•	•
CRL5362-REDB	20	125	Red	5-20R	•	•	•
CRL5362-LAB	20	125	Light Almond	5-20R	•	•	•
<b>Duplex Receptacles with 6" Leads – Split Circuit Capable</b>							
CRL5262SC-IB	15	125	Ivory	5-15R	•	•	•
CRL5262SC-WB	15	125	White	5-15R	•	•	•
CRL5262SC-B	15	125	Brown	5-15R	•	•	•
CRL5262SC-GRYB	15	125	Gray	5-15R	•	•	•
CRL5262SC-BKB	15	125	Black	5-15R	•	•	•
CRL5262SC-REDB	15	125	Red	5-15R	•	•	•
CRL5262SC-LAB	15	125	Light Almond	5-15R	•	•	•
CRL5362SC-IB	20	125	Ivory	5-20R	•	•	•
CRL5362SC-WB	20	125	White	5-20R	•	•	•
CRL5362SC-B	20	125	Brown	5-20R	•	•	•
CRL5362SC-GRYB	20	125	Gray	5-20R	•	•	•
CRL5362SC-BKB	20	125	Black	5-20R	•	•	•
CRL5362SC-REDB	20	125	Red	5-20R	•	•	•
CRL5362SC-LAB	20	125	Light Almond	5-20R	•	•	•

Available in Bulk Packs of 100.

For Configurable Solutions, see Page U-1.

# Straight Blade Devices Commercial Specification Grade Receptacles


15 & 20A, 125V

Pass & Seymour



Features	
<ul style="list-style-type: none"> <li>Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.</li> <li>.032 inch thick, brass, triple-wipe power contacts for lasting retention.</li> <li>Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.</li> <li>Impact-resistant nylon face and thermoplastic back body.</li> </ul>	<ul style="list-style-type: none"> <li>CR Series: #14 – #10 AWG solid side wire only. BR Series: side and internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire.</li> <li>Terminal compartments isolated from each other for positive conductor containment.</li> <li>Tri-drive terminal and mounting screws.</li> <li>Auto-ground clip assures positive ground.</li> </ul>

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				UL UL498	CSA C22.2 No. 42
<b>Duplex Receptacles Side Wire</b>					
CR15-I	15 125	Ivory	5-15R	•	•
CR15-W	15 125	White	5-15R	•	•
CR15	15 125	Brown	5-15R	•	•
CR15-GRY	15 125	Gray	5-15R	•	•
CR15-LA	15 125	Light Almond	5-15R	•	•
CR20-I	20 125	Ivory	5-20R	•	•
CR20-W	20 125	White	5-20R	•	•
CR20	20 125	Brown	5-20R	•	•
CR20-GRY	20 125	Gray	5-20R	•	•
CR20-BK	20 125	Black	5-20R	•	•
CR20-LA	20 125	Light Almond	5-20R	•	•
<b>Duplex Receptacles Back &amp; Side Wire</b>					
BR15-I	15 125	Ivory	5-15R	•	•
BR15-W	15 125	White	5-15R	•	•
BR15	15 125	Brown	5-15R	•	•
BR15-GRY	15 125	Gray	5-15R	•	•
BR15-LA	15 125	Light Almond	5-15R	•	•
BR20-I	20 125	Ivory	5-20R	•	•
BR20-W	20 125	White	5-20R	•	•
BR20	20 125	Brown	5-20R	•	•
BR20-GRY	20 125	Gray	5-20R	•	•
BR20-LA	20 125	Light Almond	5-20R	•	•



CR15-I

2 Pole, 3 Wire



NEMA  
5-15R



NEMA  
5-20R

For Configurable Solutions, see Page U-1.


All devices listed on this page conform to NEMA WD-1 and WD-6.

# Straight Blade Devices Heavy-Duty Specification Grade Single Receptacles

15 & 20A, 125 & 250V

### Features

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.



5361-I

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL498	FSUL WC596	C22.2 No. 42
<b>Single Receptacles Back &amp; Side Wire</b>						
5261-I	15 125	Ivory	5-15R	•	•	•
5261-W	15 125	White	5-15R	•	•	•
5261	15 125	Brown	5-15R	•	•	•
5261-GRY	15 125	Gray	5-15R	•	•	•
5261-BK	15 125	Black	5-15R	•	•	•
5261-RED	15 125	Red	5-15R	•	•	•
5261-LA	15 125	Light Almond	5-15R	•	•	•
5361-I	20 125	Ivory	5-20R	•	•	•
5361-W	20 125	White	5-20R	•	•	•
5361	20 125	Brown	5-20R	•	•	•
5361-GRY	20 125	Gray	5-20R	•	•	•
5361-BK	20 125	Black	5-20R	•	•	•
5361-RED	20 125	Red	5-20R	•	•	•
5361-LA	20 125	Light Almond	5-20R	•	•	•
5671-I	15 250	Ivory	6-15R	•	•	•
5671	15 250	Brown	6-15R	•	•	•
5671-LA	15 250	Light Almond	6-15R	•	•	•
5871-I	20 250	Ivory	6-20R	•	•	•
5871-W	20 250	White	6-20R	•	•	•
5871	20 250	Brown	6-20R	•	•	•
5871-GRY	20 250	Gray	6-20R	•	•	•
5871-BK	20 250	Black	6-20R	•	•	•
5871-RED	20 250	Red	6-20R	•	•	•
5871-LA	20 250	Light Almond	6-20R	•	•	•

2 Pole, 3 Wire



NEMA  
5-15R



NEMA  
5-20R



NEMA  
6-15R



NEMA  
6-20R

# Straight Blade Devices Specification Grade Single Receptacles

15 & 20A, 125 & 250V


Pass & Seymour




Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				UL498	C22.2 No. 42
<b>Single Receptacles Side Wire</b>					
5251-I	15 125	Ivory	5-15R	•	•
5251-W	15 125	White	5-15R	•	•
5251	15 125	Brown	5-15R	•	•
5251-LA	15 125	Light Almond	5-15R	•	•
5351-I	20 125	Ivory	5-20R	•	•
5351-W	20 125	White	5-20R	•	•
5351	20 125	Brown	5-20R	•	•
5351-LA	20 125	Light Almond	5-20R	•	•
5651-I	15 250	Ivory	6-15R	•	•
5651-W	15 250	White	6-15R	•	•
5651	15 250	Brown	6-15R	•	•
5651-LA	15 250	Light Almond	6-15R	•	•
5851-I	20 250	Ivory	6-20R	•	•
5851-W	20 250	White	6-20R	•	•
5851	20 250	Brown	6-20R	•	•
5851-LA	20 250	Light Almond	6-20R	•	•
<b>Single Receptacles Side Wire Right Angle Slots</b>					
5371-I	20 125	Ivory	Non-NEMA	•	•
5371-W	20 125	White	Non-NEMA	•	•
5371	20 125	Brown	Non-NEMA	•	•

<b>Short Strap Single Receptacles Screw Spacing 1.750"</b>					
5258-I	15 125	Ivory	5-15R	•	•
5258-W	15 125	White	5-15R	•	•
5258	15 125	Brown	5-15R	•	•
5358-I	20 125	Ivory	5-20R	•	•
5358-W	20 125	White	5-20R	•	•
5358	20 125	Brown	5-20R	•	•
5358-BK	20 125	Black	5-20R	•	•
5658-I	15 250	Ivory	6-15R	•	•
5658	15 250	Brown	6-15R	•	•
5858-I	20 250	Ivory	6-20R	•	•
5858-W	20 250	White	6-20R	•	•
5858	20 250	Brown	6-20R	•	•


Supplied with mounting screws.



5251-I



5371-I



5258-I

2 Pole, 3 Wire



NEMA  
5-15R



NEMA  
5-20R



NEMA  
6-15R




NEMA  
6-20R

Pass & Seymour



# Straight Blade Devices Tamper-Resistant Specification Grade Receptacles

15 & 20A, 125V



TR62-I



### Features

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.


Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	CS C22.2 No. 42
<b>Specification Grade Receptacles Back &amp; Side Wire</b>						
TR62-I	15 125	Ivory	5-15R	•	•	•
TR62-W	15 125	White	5-15R	•	•	•
TR62	15 125	Brown	5-15R	•	•	•
TR62-GRY	15 125	Gray	5-15R	•	•	•
TR62-RED	15 125	Red	5-15R	•	•	•
TR62-LA	15 125	Light Almond	5-15R	•	•	•
TR63-I	20 125	Ivory	5-20R	•	•	•
TR63-W	20 125	White	5-20R	•	•	•
TR63	20 125	Brown	5-20R	•	•	•
TR63-GRY	20 125	Gray	5-20R	•	•	•
TR63-RED	20 125	Red	5-20R	•	•	•
TR63-LA	20 125	Light Almond	5-20R	•	•	•

For PlugTail™ Tamper-Resistant Receptacles, see Pages B-3, B-4, and C-3.


### The Mechanical Shutter System



Thermoplastic shutter in closed position covers access to contacts.



Insertion of object in any one side does not open shutter.



Two-bladed plug or grounding plug compresses spring and simultaneously opens both shutters.

**This tamper-resistant receptacle, like all others, can be defeated by actions such as inserting foreign objects in both sides of the slots simultaneously.**

**2002 National Electrical Code® Section 517-18(c) Pediatric Locations** 15 and 20-ampere, 125-volt receptacles intended to supply patient care areas of pediatric wards, rooms, or areas shall be listed tamper-resistant. For the purpose of this section, a tamper resistant receptacle is a receptacle that, by its construction, limits improper access to its energized contacts.



# Straight Blade Devices Tamper-Resistant Hospital Grade Receptacles

15 & 20A, 125V


**Pass & Seymour**



Straight Blade Devices

### Features

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.



**TR62-HI**

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL498	FSUL WC596	C22.2 No. 42
<b>Hospital Grade Receptacles Back &amp; Side Wire</b>						
TR62-HI	15 125	Ivory	5-15R	•	•	•
TR62-HW	15 125	White	5-15R	•	•	•
TR62-H	15 125	Brown	5-15R	•	•	•
TR62-HGRY	15 125	Gray	5-15R	•	•	•
TR62-HRED	15 125	Red	5-15R	•	•	•
TR63-HI	20 125	Ivory	5-20R	•	•	•
TR63-HW	20 125	White	5-20R	•	•	•
TR63-H	20 125	Brown	5-20R	•	•	•
TR63-HGRY	20 125	Gray	5-20R	•	•	•
TR63-HRED	20 125	Red	5-20R	•	•	•
TR63-HLA	20 125	Light Almond	5-20R	•	•	•

For PlugTail™ Tamper-Resistant Receptacles, see Pages B-3, B-4, and C-3.

2 Pole, 3 Wire



**NEMA  
5-15R**




**NEMA  
5-20R**

Tamper-Resistant Hospital Grade Recept.




# Straight Blade Devices Isolated Ground Receptacles


15 & 20A, 125V; 20A, 250V



**IG6200**





**IG26262-I**



**IG5261  
IG5361  
IG8301**

Catalog Number		Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance			
Specification Grade	Hospital Grade				UL498	FSUL WC596	cUL/CSA	
<b>Duplex Receptacles Back &amp; Side Wire</b>								
IG6200-I	IG8200-RED	15 125	Ivory	5-15R	•	•	•	
IG6200-GRY		15 125	Gray	5-15R	•	•	•	
IG6200-RED		15 125	Red	5-15R	•	•	•	
IG6200-LA		15 125	Light Almond	5-15R	•	•	•	
IG6200		IG8200	15 125	Orange	5-15R	•	•	•
IG6300-I	IG8300-RED	20 125	Ivory	5-20R	•	•	•	
IG6300-W		20 125	White	5-20R	•	•	•	
IG6300-GRY		20 125	Gray	5-20R	•	•	•	
IG6300-RED		20 125	Red	5-20R	•	•	•	
IG6300-LA		20 125	Light Almond	5-20R	•	•	•	
IG6300	IG8300	20 125	Orange	5-20R	•	•	•	
IG6800	IG8800	20 250	Orange	6-20R	•	•	•	
<b>Decorator Duplex Receptacles Back &amp; Side Wire</b>								
IG26262-I	IG26262-HGRED	15 125	Ivory	5-15R	•	•	•	
IG26262-W		15 125	White	5-15R	•	•	•	
IG26262-GRY		15 125	Gray	5-15R	•	•	•	
IG26262-RED		15 125	Red	5-15R	•	•	•	
IG26262-LA		15 125	Light Almond	5-15R	•	•	•	
IG26262	IG26262-HG	15 125	Orange	5-15R	•	•	•	
IG26362-I	IG26362-HGW	20 125	Ivory	5-20R	•	•	•	
IG26362-W		20 125	White	5-20R	•	•	•	
IG26362-GRY		20 125	Gray	5-20R	•	•	•	
IG26362-RED		IG26362-HGRED	20 125	Red	5-20R	•	•	•
IG26362-LA		20 125	Light Almond	5-20R	•	•	•	
IG26362	IG26362-HG	20 125	Orange	5-20R	•	•	•	
<b>Single Receptacles Back &amp; Side Wire</b>								
IG5261		15 125	Orange	5-15R	•	•	•	
IG5361	IG8301	20 125	Orange	5-20R	•	•	•	

2 Pole, 3 Wire



# Straight Blade Devices PlugTail™ Decorator Receptacles

15 & 20A, 125V


**Pass & Seymour**




Straight Blade Devices

PlugTail™ Decorator Receptacles


Features	
<ul style="list-style-type: none"> <li>.036 inch thick, brass, triple-wipe power contacts for lasting retention.</li> <li>Plated steel wrap strap design for maximum durability and corrosion resistance..</li> <li>No exposed terminals create a finger safe application before, during, and after installation.</li> <li>Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.</li> <li>Crimped and welded contacts.</li> </ul>	<ul style="list-style-type: none"> <li>Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.</li> <li>Large brass contacts snugly terminate on device blade terminals.</li> <li>Pre-stripped connector leads fasten to conductors, easier than standard pigtails.</li> <li>Auto-ground clip assures positive ground.</li> <li>Isolated ground version features nylon isolator plate for isolating ground from strap and box system.</li> </ul>



**PT26352-LA**



**PT26362HG-I**



**PTIG26362-LA**

**NEW**

**NEW**


**NEW**

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				UL 498	FSUL WC596
<b>Duplex Receptacles</b>					
PT26252-I	15 125	Ivory	5-15R	•	•
PT26252-W	15 125	White	5-15R	•	•
PT26252	15 125	Brown	5-15R	•	•
PT26252-GRY	15 125	Gray	5-15R	•	•
PT26252-BK	15 125	Black	5-15R	•	•
PT26252-RED	15 125	Red	5-15R	•	•
PT26252-LA	15 125	Light Almond	5-15R	•	•
PT26352-I	20 125	Ivory	5-20R	•	•
PT26352-W	20 125	White	5-20R	•	•
PT26352	20 125	Brown	5-20R	•	•
PT26352-GRY	20 125	Gray	5-20R	•	•
PT26352-BK	20 125	Black	5-20R	•	•
PT26352-RED	20 125	Red	5-20R	•	•
PT26352-LA	20 125	Light Almond	5-20R	•	•
<b>Hospital Grade Duplex Receptacles</b>					
PT26262HG-I	15 125	Ivory	5-15R	•	•
PT26262HG-W	15 125	White	5-15R	•	•
PT26262HG-GRY	15 125	Gray	5-15R	•	•
PT26262HG-RED	15 125	Red	5-15R	•	•
PT26362HG-I	20 125	Ivory	5-20R	•	•
PT26362HG-W	20 125	White	5-20R	•	•
PT26362HG-GRY	20 125	Gray	5-20R	•	•
PT26362HG-RED	20 125	Red	5-20R	•	•
<b>Isolated Ground Duplex Receptacles</b>					
PTIG26262-I	15 125	Ivory	5-15R	•	•
PTIG26262-W	15 125	White	5-15R	•	•
PTIG26262	15 125	Orange	5-15R	•	•
PTIG26262-GRY	15 125	Gray	5-15R	•	•
PTIG26262-RED	15 125	Red	5-15R	•	•
PTIG26262-LA	15 125	Light Almond	5-15R	•	•
PTIG26362-I	20 125	Ivory	5-20R	•	•
PTIG26362-W	20 125	White	5-20R	•	•
PTIG26362	20 125	Orange	5-20R	•	•
PTIG26362-GRY	20 125	Gray	5-20R	•	•
PTIG26362-RED	20 125	Red	5-20R	•	•
PTIG26362-LA	20 125	Light Almond	5-20R	•	•

For PlugTail Connectors, see Page B-3.

Configurable Solutions for PlugTail Receptacles and Connectors, see Page U-1.

2 Pole, 3 Wire



NEMA 5-15R

NEMA 5-20R

All devices listed on this page conform to NEMA WD-1 and WD-6.


Pass & Seymour




# Straight Blade Devices Hospital Grade & Specification Grade Decorator Receptacles

15 & 20A, 125V


- | Features   |  |
|--|--|
| <ul style="list-style-type: none"> <li>Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.</li> <li>One-piece, brass, triple-wipe power contacts for lasting retention.</li> <li>Heavy-duty compact design for easier installation and long lasting performance.</li> <li>Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.</li> </ul> | <ul style="list-style-type: none"> <li>Impact-resistant nylon face.</li> <li>Terminal compartments isolated from each other for positive conductor containment.</li> <li>Side and internal screw-pressure-plate back wire accepts #14 – #10 AWG solid or stranded wire.</li> <li>All devices fit standard #26 opening wall plate.</li> <li>Tri-drive terminal and mounting screws.</li> <li>Auto-ground clip assures positive ground.</li> </ul> |



26262-HGI




IG26262-HGI



26252-I

2 Pole, 3 Wire



NEMA 5-15R

NEMA 5-20R

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL498	FSUL WC596	cUL/CSA
<b>Heavy-Duty Hospital Grade Duplex Receptacles Back &amp; Side Wire</b>						
26262-HGI	15 125	Ivory	5-15R	•	•	•
26262-HGW	15 125	White	5-15R	•	•	•
26262-HGGRY	15 125	Gray	5-15R	•	•	•
26262-HGRED	15 125	Red	5-15R	•	•	•
26362-HGI	20 125	Ivory	5-20R	•	•	•
26362-HGW	20 125	White	5-20R	•	•	•
26362-HG	20 125	Brown	5-20R	•	•	•
26362-HGGRY	20 125	Gray	5-20R	•	•	•
26362-HGRED	20 125	Red	5-20R	•	•	•
26362-HGLA	20 125	Light Almond	5-20R	•	•	•
<b>Heavy-Duty Hospital Grade Isolated Ground Duplex Recept. Back &amp; Side Wire</b>						
IG26262-HG	15 125	Orange	5-15R	•		•
IG26262-HGRED	15 125	Red	5-15R	•		•
IG26362-HGW	20 125	White	5-20R	•		•
IG26362-HG	20 125	Orange	5-20R	•		•
IG26362-HGRED	20 125	Red	5-20R	•		•
<b>Heavy-Duty Hospital Grade Illuminated Duplex Recept. Back &amp; Side Wire</b>						
26222-HGI	15 125	Ivory	5-15R	•		•
26322-HGI	20 125	Ivory	5-20R	•		•
26322-HGW	20 125	White	5-20R	•		•
26322-HGRED	20 125	Red	5-20R	•		•

<b>Heavy-Duty Specification Grade Duplex Receptacles Back &amp; Side Wire</b>						
26252-I	15 125	Ivory	5-15R	•	•	•
26252-W	15 125	White	5-15R	•	•	•
26252	15 125	Brown	5-15R	•	•	•
26252-GRY	15 125	Gray	5-15R	•	•	•
26252-BK	15 125	Black	5-15R	•	•	•
26252-RED	15 125	Red	5-15R	•	•	•
26252-LA	15 125	Light Almond	5-15R	•	•	•
26352-I	20 125	Ivory	5-20R	•	•	•
26352-W	20 125	White	5-20R	•	•	•
26352	20 125	Brown	5-20R	•	•	•
26352-GRY	20 125	Gray	5-20R	•	•	•
26352-BK	20 125	Black	5-20R	•	•	•
26352-RED	20 125	Red	5-20R	•	•	•
26352-LA	20 125	Light Almond	5-20R	•	•	•

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

# Straight Blade Devices Specification Grade Decorator Receptacles


15 & 20A, 125 & 250V

**Pass & Seymour**




### Features

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 – #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	cUL/CSA
<b>Specification Grade Duplex Receptacles Back &amp; Side Wire</b>						
26652-I	15 250	Ivory	6-15R	•	•	•
26652-W	15 250	White	6-15R	•	•	•
26652	15 250	Brown	6-15R	•	•	•
26652-GRY	15 250	Gray	6-15R	•	•	•
26652-BK	15 250	Black	6-15R	•	•	•
26652-RED	15 250	Red	6-15R	•	•	•
26852-I	20 250	Ivory	6-20R	•	•	•
26852-W	20 250	White	6-20R	•	•	•
26852	20 250	Brown	6-20R	•	•	•
26852-GRY	20 250	Gray	6-20R	•	•	•
26852-BK	20 250	Black	6-20R	•	•	•
26852-RED	20 250	Red	6-20R	•	•	•
26852-LA	20 250	Light Almond	6-20R	•	•	•
<b>Specification Grade Duplex Receptacles Side Wire Only*</b>						
26242-I	15 125	Ivory	5-15R	•	•	•
26242-W	15 125	White	5-15R	•	•	•
26242	15 125	Brown	5-15R	•	•	•
26242-GRY	15 125	Gray	5-15R	•	•	•
26242-BK	15 125	Black	5-15R	•	•	•
26242-RED	15 125	Red	5-15R	•	•	•
26342-I	20 125	Ivory	5-20R	•	•	•
26342-W	20 125	White	5-20R	•	•	•
26342	20 125	Brown	5-20R	•	•	•
26342-GRY	20 125	Gray	5-20R	•	•	•
26342-BK	20 125	Black	5-20R	•	•	•
26342-RED	20 125	Red	5-20R	•	•	•

2 Pole, 3 Wire



For Configurable Solutions, see Page U-1.






# Straight Blade Devices Specification Grade Combination & Decorator Receptacles

15 & 20A, 125 & 250V; 20A, 120/125VAC

Features	
<ul style="list-style-type: none"> <li>Impact-resistant face and body.</li> <li>GE Lexan™ high impact-resistant lens.</li> <li>External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.</li> <li>Ground screw position under the end of the strap minimizes the risk of contact.</li> </ul>	<ul style="list-style-type: none"> <li>Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.</li> <li>Sensor automatically turns light ON in the dark.</li> <li>Increased light output for better illumination.</li> <li>Light sensor for enhanced sensitivity.</li> </ul>




PS8HWL-LA



Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance	
					UL <sup>US</sup> UL498	
<b>Specification Grade Decorator Hallway Light &amp; Single Receptacle</b>						
PS8HWL-I	20 120/125	0.2561	Ivory	5-20R		•
PS8HWL-W	20 120/125	0.2561	White	5-20R		•
PS8HWL-LA	20 120/125	0.2561	Light Almond	5-20R		•


\*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See Page U-42 for more information.

Features	
<ul style="list-style-type: none"> <li>Corrosion-resistant, plated wraparound steel strap locked into assembly to prohibit strap from bending away from body.</li> <li>One-piece, brass, triple-wipe power contacts for lasting retention.</li> <li>Heavy-duty compact design for easier installation and long lasting performance.</li> <li>Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.</li> </ul>	<ul style="list-style-type: none"> <li>Impact-resistant nylon face.</li> <li>Terminal compartments isolated from each other for positive conductor containment.</li> <li>Side and internal screw-pressure-plate back wire accepts #14 – #10 AWG solid or stranded wire.</li> <li>All devices fit standard #26 opening wall plate.</li> <li>Tri-drive terminal and mounting screws.</li> <li>Auto-ground clip assures positive ground.</li> </ul>



26261-I

2 Pole, 3 Wire



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL <sup>US</sup> UL498	FSUL WC596	cUL/CSA
<b>Heavy-Duty Specification Grade Single Receptacles Back &amp; Side Wire</b>						
26261-I	15 125	Ivory	5-15R	•	•	•
26261-W	15 125	White	5-15R	•	•	•
26261	15 125	Brown	5-15R	•	•	•
26261-GRY	15 125	Gray	5-15R	•	•	•
26261-BK	15 125	Black	5-15R	•	•	•
26361-I	20 125	Ivory	5-20R	•	•	•
26361-W	20 125	White	5-20R	•	•	•
26361	20 125	Brown	5-20R	•	•	•
26361-GRY	20 125	Gray	5-20R	•	•	•
26361-BK	20 125	Black	5-20R	•	•	•
26361-LA	20 125	Light Almond	5-20R	•	•	•
26661-I	15 250	Ivory	6-15R	•	•	•
26661-W	15 250	White	6-15R	•	•	•
26661-GRY	15 250	Gray	6-15R	•	•	•
26661-BK	15 250	Black	6-15R	•	•	•
26861-I	20 250	Ivory	6-20R	•	•	•
26861-W	20 250	White	6-20R	•	•	•
26861	20 250	Brown	6-20R	•	•	•
26861-GRY	20 250	Gray	6-20R	•	•	•
26861-BK	20 250	Black	6-20R	•	•	•
26861-RED	20 250	Red	6-20R	•	•	•

# Straight Blade Devices TradeMaster® Receptacles

15A, 125V

**Pass & Seymour**



Straight Blade Devices

Features	
<ul style="list-style-type: none"> <li>■ High-impact resistant thermoplastic construction.</li> <li>■ Extra-long strap.</li> <li>■ Quickloop wire looping aid.</li> <li>■ Long-term blade retention.</li> <li>■ Longer tri-drive screws for easier 12 AWG looping.</li> <li>■ Extra-large circuit break-off tabs.</li> </ul>	<ul style="list-style-type: none"> <li>■ Side-access push wire release.</li> <li>■ Ultrasonic welding of face to back body.</li> <li>■ Side wire accepts #12 – #14 AWG solid wire.</li> <li>■ Push wire accepts #14 AWG solid only.</li> <li>■ “S” model provides automatic ground clip.</li> </ul>

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				UL UL498	SR C22.2 No. 42
<b>Duplex Receptacles – Grounding</b>					
3232-I*	15 125	Ivory	5-15R	•	•
3232-W*	15 125	White	5-15R	•	•
3232*	15 125	Brown	5-15R	•	•
3232-BK	15 125	Black	5-15R	•	•
3232-LA*	15 125	Light Almond	5-15R	•	•
<b>Self-Grounding Receptacles</b>					
3232-SI	15 125	Ivory	5-15R	•	•
3232-SW	15 125	White	5-15R	•	•
3232-S	15 125	Brown	5-15R	•	•
3232-SLA	15 125	Light Almond	5-15R	•	•
<b>4 Terminal, Screws In</b>					
3232-I4	15 125	Ivory	5-15R	•	•
3232-W4	15 125	White	5-15R	•	•
3232-4	15 125	Brown	5-15R	•	•
<b>Duplex Receptacles – Without Ears</b>					
3232-IMH	15 125	Ivory	5-15R	•	•
3232-WMH	15 125	White	5-15R	•	•
3232-MH	15 125	Brown	5-15R	•	•


\*Available in bulk packs of 150. Add “U” to end of Catalog Number. Example: 3232-LAU.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				UL UL498	SR C22.2 No. 42
<b>8 Hole Push Wire Without Terminal Screws</b>					
880-I	15 125	Ivory	5-15R	•	•
880-W	15 125	White	5-15R	•	•
880	15 125	Brown	5-15R	•	•
<b>8 Hole Push Wire – Without Ears Without Terminal Screws</b>					
880-IMH	15 125	Ivory	5-15R	•	•
880-WMH	15 125	White	5-15R	•	•
880-MH	15 125	Brown	5-15R	•	•


2 Pole, 3 Wire




NEMA  
5-15R




**3232-I**



**3232-SI**



**3232-IMH**



**880-I**

For Decorator version of 880 Series, see Page B-29.

All devices listed on this page conform to NEMA WD-1 and WD-6.


TradeMaster® Receptacles

## Straight Blade Devices TradeMaster® Decorator Receptacles with Pressure Plates

TradeMaster® Decorator receptacles feature longer steel straps than competitive devices, yet still fit under a standard wall plate!

High-impact thermoplastic face and back body eliminates cracks, breaks and callbacks. Plus, they're ultrasonically welded for added durability.

Patented design provides better plug retention.




External screw-pressure-plate back wire on all four terminal screws and ground screw eliminates wrapping. Accepts #12 and #14 stranded and solid wire.

Break-off tabs that are big enough to grab hold of – even if the contact screws are backed-out. Scored deeper, too, for fast, clean breaks every time.

All four contact screws and the ground screw are backed-out. All screws are tri-drive.

TM885-W



TM885-W

2 Pole, 3 Wire



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance
				UL498
<b>Decorator Duplex Receptacles with Pressure Plates</b>				
TM885-I	15 125	Ivory	5-15R	•
TM885-W	15 125	White	5-15R	•
TM885	15 125	Brown	5-15R	•
TM885-GRY	15 125	Gray	5-15R	•
TM885-BK	15 125	Black	5-15R	•
TM885-LA	15 125	Light Almond	5-15R	•
<b>Decorator Duplex Receptacles with Pressure Plates Self-Grounding</b>				
TM885-SI	15 125	Ivory	5-15R	•
TM885-SW	15 125	White	5-15R	•
TM885-SLA	15 125	Light Almond	5-15R	•
<b>Decorator Duplex Receptacles with Pressure Plates Bulk Pack of 150</b>				
TM885-I150	15 125	Ivory	5-15R	•
TM885-W150	15 125	White	5-15R	•
TM885-LA150	15 125	Light Almond	5-15R	•

# Straight Blade Devices TradeMaster® Decorator Tamper-Resistant & Combination Receptacles

Pass & Seymour



Straight Blade Devices

Decorator Tamper-Resistant Receptacles

**Impact-resistant thermoplastic face and back body** are ultrasonically welded for added durability.

**Clearly visible "TR" markings on face of device.**

**High output LED light** for better illumination and longer life.

**External light sensor** for enhanced sensitivity.

**High impact-resistant lens** made of GE-Lexan™.

**All screws are tri-drive.**

**Side and external screw-pressure-plate back wire.** Accepts #12 and #14 AWG.

**UL Listed tamper-resistant shutter** for outstanding protection against improper insertion of foreign objects.


**UL Listed tamper-resistant shutter** for outstanding protection against improper insertion of foreign objects.

885TR-BK


**Clearly visible "TR" markings on face of device.**

TM8HWLTR-WCC

Pass & Seymour



885TR-LA



TM8HWLTR-LACC

2 Pole, 3 Wire



NEMA  
5-15R

# Straight Blade Devices TradeMaster® Decorator Tamper-Resistant & Combination Receptacles

15A, 125V

### Features

- High impact-resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Tri-drive screws.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid.
- Push wire accepts #14 AWG solid only.
- UL Listed as tamper-resistant to prevent improper insertion of foreign objects per UL498.
- Specially designed for increased protection of children in their homes.
- Superior protection than traditional outlet “caps” or “protection plates”.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				cULus	UL498
<b>Decorator Tamper-Resistant Receptacles</b>					
885TR-I	15 125	Ivory	5-15R	•	•
885TR-W	15 125	White	5-15R	•	•
885TR-BK	15 125	Black	5-15R	•	•
885TR-LA	15 125	Light Almond	5-15R	•	•

### Features

- Impact-resistant face and body.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- GE Lexan™ high impact-resistant lens.
- Tri-drive screws.
- Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.
- Sensor automatically turns light ON in the dark.
- Increased light output for better illumination.
- Light sensor for enhanced sensitivity.
- UL tested shutter mechanism for protection against improper object insertion per UL498.
- Specially designed for increased protection of children in their homes.
- Superior protection than traditional outlet “caps” or “protection plates”.

Catalog Number	Rating A. VAC	Light Output in 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance
					cULus UL498
<b>Decorator Hallway Light with High Output Light &amp; Tamper-Resistant Single Receptacle</b>					
TM8HWLTR-ICC	15 125	0.2561	Ivory	5-15R	•
TM8HWLTR-WCC	15 125	0.2561	White	5-15R	•
TM8HWLTR-BKCC	15 125	0.2561	Black	5-15R	•
TM8HWLTR-CC	15 125	0.2561	Brown	5-15R	•
TM8HWLTR-LACC	15 125	0.2561	Light Almond	5-15R	•

\* FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See Page U-42 for more information.

For complete line of Decorator Combination Devices and Hallway Lights, see Pages D-6 – D-10, D-17, D-19, D-25, and D-26.



# Straight Blade Devices


## TradeMaster® Decorator Receptacles

15A, 125V


Pass & Seymour



Features	
<ul style="list-style-type: none"> <li>■ High impact-resistant thermoplastic construction.</li> <li>■ Extra-long strap.</li> <li>■ Quickloop wire looping aid.</li> <li>■ Long-term blade retention.</li> <li>■ Tri-drive screws.</li> <li>■ Extra-large circuit break-off tabs.</li> </ul>	<ul style="list-style-type: none"> <li>■ Side-access push wire release.</li> <li>■ Ultrasonic welding of face to back body.</li> <li>■ Side wire accepts #12 – #14 AWG solid.</li> <li>■ Push wire accepts #14 AWG solid only.</li> <li>■ “S” model provides self-grounding clip.</li> </ul>



**885-I**



**880-DECOLA**

2 Pole, 3 Wire



NEMA  
5-15R

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				UL UL498	SF C22.2 42
<b>Decorator Duplex Receptacles</b>					
885-I	15 125	Ivory	5-15R	•	•
885-W	15 125	White	5-15R	•	•
885	15 125	Brown	5-15R	•	•
885-BK	15 125	Black	5-15R	•	•
885-LA	15 125	Light Almond	5-15R	•	•
<b>Self-Grounding Decorator Duplex Receptacles</b>					
885-SI	15 125	Ivory	5-15R	•	•
885-SW	15 125	White	5-15R	•	•
885-SLA	15 125	Light Almond	5-15R	•	•


*For Configurable Solutions, see Page U-1.*

Features	
<ul style="list-style-type: none"> <li>■ High-impact resistant thermoplastic construction.</li> <li>■ Extra-long strap.</li> <li>■ Quickloop wire looping aid.</li> <li>■ Long-term blade retention.</li> <li>■ Longer tri-drive screws for easier 12 AWG looping.</li> </ul>	<ul style="list-style-type: none"> <li>■ Extra-large circuit break-off tabs.</li> <li>■ Side-access push wire release.</li> <li>■ Ultrasonic welding of face to back body.</li> <li>■ Side wire accepts #12 – #14 AWG solid wire.</li> <li>■ Push wire accepts #14 AWG solid only.</li> </ul>


Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance	
				UL UL498	SF C22.2 42
<b>Decorator 8 Hole Push Wire Without Terminal Screws</b>					
880-DECOI	15 125	Ivory	5-15R	•	•
880-DECOW	15 125	White	5-15R	•	•
880-DECOBK	15 125	Black	5-15R	•	•
880-DECOLA	15 125	Light Almond	5-15R	•	•

All devices listed on this page conform to NEMA WD-1 and WD-6.


Pass & Seymour



TMHWL-CC



TMHWL-ECC



TM8HWL-WCC

2 Pole, 3 Wire



NEMA 5-15R

## Straight Blade Devices TradeMaster® Decorator Hallway Lights & Combination Devices

### Features

- Impact-resistant face and body.
- GE Lexan™ high impact-resistant lens.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Energy-efficient LED has average 20-year life expectancy; eliminates bulb replacement.
- Sensor automatically turns light ON in the dark.
- Increased light output for better illumination.
- Light sensor for enhanced sensitivity.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	3rd Party Compliance	
				cUL <sup>us</sup> UL1598	
<b>TradeMaster® Decorator Full Hallway Light</b>					
TMHWL-CC	— 120	0.1328	Clear	•	
<b>Enhanced Decorator Full Hallway Light with Light Sensor</b>					
TMHWL-ECC	— 120	1.079	Clear	•	
<b>Enhanced Decorator Full Hallway Light without Light Sensor</b>					
TMHWL-ENSCC	— 120	1.113	Clear	•	
<b>Full Hallway Decorator Light for use with P&amp;S Metal Louver Plates**</b>					
TMHWL-LOUVCC	— 120	0.0843	Clear	•	

\*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See Page U-xx for more information.

\*\*For Louver Plates, see Page S-19.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance	
					cUL <sup>us</sup> UL498	
<b>TradeMaster® Decorator Hallway Light &amp; Single Receptacle</b>						
TM8HWL-ICC	15 120/125	0.1442	Ivory	5-15R	•	
TM8HWL-WCC	15 120/125	0.1442	White	5-15R	•	
TM8HWL-BKCC	15 120/125	0.1442	Black	5-15R	•	
TM8HWL-CC	15 120/125	0.1442	Brown	5-15R	•	
TM8HWL-LACC	15 120/125	0.1442	Light Almond	5-15R	•	
<b>Enhanced Decorator Hallway Light &amp; Single Receptacle</b>						
TM8HWL-EICC	15 120/125	0.2561	Ivory	5-15R	•	
TM8HWL-EWCC	15 120/125	0.2561	White	5-15R	•	
TM8HWL-ELACC	15 120/125	0.2561	Light Almond	5-15R	•	

\*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See Page U-42 for more information.

For complete line of Decorator Combination Devices and Hallway Lights, see Pages D-6 – D-10, D-17, D-19, D-25 and D-26.

# Straight Blade Devices TradeMaster® & Specification Grade GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

**Pass & Seymour**




Straight Blade Devices


Features	
<ul style="list-style-type: none"> <li>■ Meets 2006 UL requirements.</li> <li>■ SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.</li> <li>■ Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.</li> <li>■ Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.</li> <li>■ FSUL Listed (Federal Specification WC596).</li> <li>■ Trip indicator light (red lamp).</li> <li>■ Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.</li> <li>■ Two back wire holes per terminal.</li> <li>■ Ground screw has a back wire clamp for easy installation.</li> </ul>	<ul style="list-style-type: none"> <li>■ 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.</li> <li>■ Mounting screws are shipped captive in the device and wall plate for easier installation.</li> <li>■ High-impact-resistant thermoplastic construction.</li> <li>■ Extra-long strap.</li> <li>■ Button colors match the device face.</li> <li>■ Dual-direction test and reset buttons.</li> <li>■ Class A rated GFCI.</li> <li>■ Supplied with matching TP26 nylon wall plate.</li> <li>■ Tri-drive screws.</li> <li>■ GFCIs with Auto-Ground assure a positive ground to metal box.</li> </ul>
Specifications	
<ul style="list-style-type: none"> <li>■ Supply Voltage: 125VAC, 60 Hz</li> <li>■ Supply Voltage Range: 102-132 VAC</li> <li>■ Trip Threshold: 5± 1mA</li> </ul>	<ul style="list-style-type: none"> <li>■ Trip Time: 0.025 sec., nominal per UL Standard</li> <li>■ 20 Amp feed-thru capacity</li> </ul>



**1595-W**



**2095-W**



**1595-SW**



Available in Bulk Packaging, i.e. 1595-W20 is 20 pack, 1595-W100 is 100 pack. Please contact Customer Support at 1-800-223-4189.

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>TradeMaster®/Spec Grade 15 Amp Duplex GFCI</b>							
1595-I	15	125	Ivory	5-15R	•	•	•
1595-W	15	125	White	5-15R	•	•	•
1595	15	125	Brown	5-15R	•	•	•
1595-GRY	15	125	Gray	5-15R	•	•	•
1595-BK	15	125	Black	5-15R	•	•	•
1595-RED	15	125	Red	5-15R	•	•	•
1595-LA	15	125	Light Almond	5-15R	•	•	•
<b>TradeMaster®/Spec Grade 15 Amp Duplex GFCI with Auto-Ground</b>							
1595-SI	15	125	Ivory	5-15R	•	•	•
1595-SW	15	125	White	5-15R	•	•	•
1595-SLA	15	125	Light Almond	5-15R	•	•	•
<b>Specification Grade 20 Amp Duplex GFCI</b>							
2095-I	20	125	Ivory	5-20R	•	•	•
2095-W	20	125	White	5-20R	•	•	•
2095	20	125	Brown	5-20R	•	•	•
2095-GRY	20	125	Gray	5-20R	•	•	•
2095-BK	20	125	Black	5-20R	•	•	•
2095-RED	20	125	Red	5-20R	•	•	•
2095-LA	20	125	Light Almond	5-20R	•	•	•
<b>Specification Grade 20 Amp Duplex GFCI with Auto-Ground</b>							
2095-SI	20	125	Ivory	5-20R	•	•	•
2095-SW	20	125	White	5-20R	•	•	•
2095-SLA	20	125	Light Almond	5-20R	•	•	•

Available Spring 2006.

For Configurable Solutions, see Page U-1.


All devices listed on this page conform to NEMA WD-1 and WD-6.

TradeMaster® & Spec. Grade GFCI Receptacles




## Straight Blade Devices Hospital Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1595-HGW



2095-HGW

### Features

- Meets 2006 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red lamp).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

### Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity



Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>Hospital Grade 15 Amp Duplex GFCI</b>						
1595-HGI	15 125	Ivory	5-15R	•	•	•
1595-HGW	15 125	White	5-15R	•	•	•
1595-HG	15 125	Brown	5-15R	•	•	•
1595-HGGRY	15 125	Gray	5-15R	•	•	•
1595-HGRED	15 125	Red	5-15R	•	•	•
1595-HGLA	15 125	Light Almond	5-15R	•	•	•
<b>Hospital Grade 20 Amp Duplex GFCI</b>						
2095-HGI	20 125	Ivory	5-20R	•	•	•
2095-HGW	20 125	White	5-20R	•	•	•
2095-HG	20 125	Brown	5-20R	•	•	•
2095-HGGRY	20 125	Gray	5-20R	•	•	•
2095-HGRED	20 125	Red	5-20R	•	•	•
2095-HGLA	20 125	Light Almond	5-20R	•	•	•



NEMA  
5-15R



NEMA  
5-20R

Available Spring 2006.

For Configurable Solutions, see Page U-1.

# Straight Blade Devices Illuminated GFCI Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Pass & Seymour




Straight Blade Devices


Features	
<ul style="list-style-type: none"> <li>Green indicator light is ON when power is available. Helps identify emergency power branch circuits.</li> <li>Meets 2006 UL requirements.</li> <li>SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.</li> <li>Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.</li> <li>Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.</li> <li>FSUL Listed (Federal Specification WC596).</li> <li>Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.</li> <li>Two back wire holes per terminal.</li> </ul>	<ul style="list-style-type: none"> <li>Ground screw has a back wire clamp for easy installation.</li> <li>1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.</li> <li>Mounting screws are shipped captive in the device and wall plate for easier installation.</li> <li>High-impact-resistant thermoplastic construction.</li> <li>Extra-long strap.</li> <li>Button colors match the device face.</li> <li>Dual-direction test and reset buttons.</li> <li>Class A rated GFCI.</li> <li>Supplied with matching TP26 nylon wall plate.</li> <li>Tri-drive screws.</li> </ul>
Specifications	
<ul style="list-style-type: none"> <li>Supply Voltage: 125VAC, 60 Hz</li> <li>Supply Voltage Range: 102-132 VAC</li> <li>Trip Threshold: 5± 1mA</li> </ul>	<ul style="list-style-type: none"> <li>Trip Time: 0.025 sec., nominal per UL Standard</li> <li>20 Amp feed-thru capacity</li> </ul>



1595-WL



2095-HGWL



Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>NEW TradeMaster®/Spec Grade Illuminated 15 Amp Duplex GFCI</b>							
1595-IL	15	125	Ivory	5-15R	•	•	•
1595-WL	15	125	White	5-15R	•	•	•
1595-L	15	125	Brown	5-15R	•	•	•
1595-LAL	15	125	Light Almond	5-15R	•	•	•
<b>NEW Specification Grade Illuminated 20 Amp Duplex GFCI</b>							
2095-IL	20	125	Ivory	5-20R	•	•	•
2095-WL	20	125	White	5-20R	•	•	•
2095-L	20	125	Brown	5-20R	•	•	•
2095-GRYL	20	125	Gray	5-20R	•	•	•
2095-LAL	20	125	Light Almond	5-20R	•	•	•
<b>NEW Hospital Grade Illuminated 15 Amp Duplex GFCI</b>							
1595-HGIL	15	125	Ivory	5-15R	•	•	•
1595-HGWL	15	125	White	5-15R	•	•	•
1595-HGL	15	125	Brown	5-15R	•	•	•
1595-HGGRYL	15	125	Gray	5-15R	•	•	•
1595-HGREDL	15	125	Red	5-15R	•	•	•
1595-HGLAL	15	125	Light Almond	5-15R	•	•	•
<b>NEW Hospital Grade Illuminated 20 Amp Duplex GFCI</b>							
2095-HGIL	20	125	Ivory	5-20R	•	•	•
2095-HGWL	20	125	White	5-20R	•	•	•
2095-HGL	20	125	Brown	5-20R	•	•	•
2095-HGGRYL	20	125	Gray	5-20R	•	•	•
2095-HGREDL	20	125	Red	5-20R	•	•	•
2095-HGLAL	20	125	Light Almond	5-20R	•	•	•

Available Spring 2006.


For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.



Illuminated GFCI Receptacles



1595-TRWCC4



2095-HGTRW



# Straight Blade Devices Tamper-Resistant GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

### Features

- Protects children: patented, UL-Listed shutter system helps prevent improper insertion of foreign objects.
- Meets 2006 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red lamp).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

### Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>NEW TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI</b>							
1595-TRICC4	15	125	Ivory	5-15R	•	•	•
1595-TRWCC4	15	125	White	5-15R	•	•	•
1595-TRBKCC4	15	125	Black	5-15R	•	•	•
1595-TRLACC4	15	125	Light Almond	5-15R	•	•	•
<b>NEW Specification Grade Tamper-Resistant 20 Amp Duplex GFCI</b>							
2095-TRI	20	125	Ivory	5-20R	•	•	•
2095-TRW	20	125	White	5-20R	•	•	•
2095-TR	20	125	Brown	5-20R	•	•	•
2095-TRGRY	20	125	Gray	5-20R	•	•	•
2095-TRBK	20	125	Black	5-20R	•	•	•
2095-TRRED	20	125	Red	5-20R	•	•	•
2095-TRLA	20	125	Light Almond	5-20R	•	•	•
<b>NEW Hospital Grade Tamper-Resistant 15 Amp Duplex GFCI</b>							
1595-HGTRI	15	125	Ivory	5-15R	•	•	•
1595-HGTRW	15	125	White	5-15R	•	•	•
1595-HGTR	15	125	Brown	5-15R	•	•	•
1595-HGTRGRY	15	125	Gray	5-15R	•	•	•
1595-HGTRRED	15	125	Red	5-15R	•	•	•
1595-HGTRLA	15	125	Light Almond	5-15R	•	•	•
<b>NEW Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI</b>							
2095-HGTRI	20	125	Ivory	5-20R	•	•	•
2095-HGTRW	20	125	White	5-20R	•	•	•
2095-HGTR	20	125	Brown	5-20R	•	•	•
2095-HGTRGRY	20	125	Gray	5-20R	•	•	•
2095-HGTRRED	20	125	Red	5-20R	•	•	•
2095-HGTRLA	20	125	Light Almond	5-20R	•	•	•

Available Spring 2006.

For Configurable Solutions, see Page U-1.


All devices listed on this page conform to NEMA WD-1 and WD-6.




# Straight Blade Devices Decorator Combination Switch/GFCI Receptacles

15A, 125VAC

Pass & Seymour



1595-SWTWCC4




1595-2SWTWCC4




Features	
<ul style="list-style-type: none"> <li>Meets 2006 UL requirements.</li> <li>SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.</li> <li>Up-down switching.</li> <li>15 Amp single pole switch rated for 1/2 HP motor loads – perfect for bath or kitchen vents and garbage disposals.</li> <li>Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.</li> <li>Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.</li> <li>FSUL Listed (Federal Specification WC596).</li> <li>Trip indicator light (red lamp).</li> <li>Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.</li> </ul>	<ul style="list-style-type: none"> <li>Two back wire holes per terminal.</li> <li>Ground screw has a back wire clamp for easy installation.</li> <li>1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.</li> <li>Mounting screws are shipped captive in the device and wall plate for easier installation.</li> <li>High-impact-resistant thermoplastic construction.</li> <li>Extra-long strap.</li> <li>Button colors match the device face.</li> <li>Dual-direction test and reset buttons.</li> <li>Class A rated GFCI.</li> <li>Supplied with matching TP26 nylon wall plate.</li> <li>Tri-drive screws.</li> </ul>
Specifications	
<ul style="list-style-type: none"> <li>Supply Voltage: 125VAC, 60 Hz</li> <li>Supply Voltage Range: 102-132 VAC</li> <li>Trip Threshold: 5± 1mA</li> </ul>	<ul style="list-style-type: none"> <li>Trip Time: 0.025 sec., nominal per UL Standard</li> <li>20 Amp feed-thru capacity</li> </ul>

Catalog Number	Switch Rating A. VAC	Receptacle Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	UL20 C22.2 No. 111
<b>NEW</b> <b>Combination Single Pole Switch/GFCI</b>							
1595-SWTICC4	15 120	15 125	Ivory	5-15R	•	•	•
1595-SWTWCC4	15 120	15 125	White	5-15R	•	•	•
1595-SWTBKCC4	15 120	15 125	Black	5-15R	•	•	•
1595-SWTLACC4	15 120	15 125	Light Almond	5-15R	•	•	•
<b>NEW</b> <b>Combination Two Single Pole Switches/GFCI</b>							
1595-2SWTICC4	15 120	15 125	Ivory	5-15R	•	•	•
1595-2SWTWCC4	15 120	15 125	White	5-15R	•	•	•
1595-2SWTBKCC4	15 120	15 125	Black	5-15R	•	•	•
1595-2SWTLACC4	15 120	15 125	Light Almond	5-15R	•	•	•



Available Spring 2006.



1595-NTLWCC4



2095-HGNTLW



**NEW**

**NEW**

# Straight Blade Devices Decorator Combination Nightlight/GFCI Receptacles

15 & 20A, 125VAC

### Features

- Meets 2006 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- Photocell turns nightlight ON in dark, OFF in daylight.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red lamp).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

### Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Time: 0.025 sec., nominal per UL Standard
- Trip Threshold: 5± 1mA
- 20 Amp feed-thru capacity

Catalog Number	Rating A.	VAC	Light Output in 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance		
						UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>Combination Nightlight/GFCI</b>								
1595-NTLICCC4	15	125	0.1618	Ivory	5-15R	•	•	•
1595-NTLWCC4	15	125	0.1618	White	5-15R	•	•	•
1595-NTLBKCC4	15	125	0.1618	Black	5-15R	•	•	•
1595-NTLLACC4	15	125	0.1618	Light Almond	5-15R	•	•	•
2095-NTLI	20	125	0.1233	Ivory	5-20R	•	•	•
2095-NTLW	20	125	0.1233	White	5-20R	•	•	•
2095-NTLGRY	20	125	0.1233	Gray	5-20R	•	•	•
2095-NTLRED	20	125	0.1233	Red	5-20R	•	•	•
2095-NTLLA	20	125	0.1233	Light Almond	5-20R	•	•	•
<b>Hospital Grade Combination Nightlight/GFCI</b>								
1595-HGNTLI	15	125	0.1618	Ivory	5-15R	•	•	•
1595-HGNTLW	15	125	0.1618	White	5-15R	•	•	•
1595-HGNTL	15	125	0.1618	Brown	5-15R	•	•	•
1595-HGNTLGRY	15	125	0.1618	Gray	5-15R	•	•	•
1595-HGNTLRED	15	125	0.1618	Red	5-15R	•	•	•
1595-HGNTLLA	15	125	0.1618	Light Almond	5-15R	•	•	•
2095-HGNTLI	20	125	0.1233	Ivory	5-20R	•	•	•
2095-HGNTLW	20	125	0.1233	White	5-20R	•	•	•
2095-HGNTL	20	125	0.1233	Brown	5-20R	•	•	•
2095-HGNTLGRY	20	125	0.1233	Gray	5-20R	•	•	•
2095-HGNTLRED	20	125	0.1233	Red	5-20R	•	•	•
2095-HGNTLLA	20	125	0.1233	Light Almond	5-20R	•	•	•

\*FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See Page U-42 for more information.

Available Spring 2006.

All devices listed on this page conform to NEMA WD-1 and WD-6.

# Straight Blade Devices

## TVSS Straight Blade Receptacles


15 & 20A, 125VAC

**Pass & Seymour**




Straight Blade Devices

Specifications	
<ul style="list-style-type: none"> <li>■ UL1449 (latest revision). (1.2 x 50μs 6000V, 8 x 20μs 3000A).</li> <li>■ 1 filtering capacitor for 7 to 1 average noise reduction.</li> <li>■ Nominal let-through (suppressed) voltage in all 3 modes, 500V.</li> <li>■ Response time less than 1 nanosecond for unmounted MOV.</li> <li>■ Overcurrent protection in all 3 modes.</li> <li>■ Electronic components potted for electrical, mechanical and thermal stability.</li> <li>■ Thermal protection in all 3 modes.</li> <li>■ Leakage current: 0.5mA at 25°C/120VAC.</li> </ul>	<ul style="list-style-type: none"> <li>■ 3 18mm dual pack MOVs to suppress transients in all modes – equally.</li> <li>■ Common mode noise attenuation: 500 KHz to 30 MHz; up to 35dB (50 ohm source impedance)</li> <li>■ Varistor voltage: 150V RMS.</li> <li>■ Back and side wire capability including ground terminal.</li> <li>■ Operating temperature: -40°C to 85°C (-40°F to 185°F)</li> <li>■ Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.</li> </ul>
Specification, Hospital and Isolated Ground Receptacles	
<ul style="list-style-type: none"> <li>■ Audible alarm able to be turned on/off.</li> <li>■ LED indicator light.</li> <li>■ 210 joules of energy absorption in each of the three modes.</li> </ul>	<ul style="list-style-type: none"> <li>■ 13,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.</li> <li>■ Isolated Ground version complies with NEC 410-56 (C) and 250-74 exception 4.</li> </ul>
Commercial Receptacles	
<ul style="list-style-type: none"> <li>■ LED indicator light.</li> <li>■ 130 joules of energy absorption in each of the three modes.</li> </ul>	<ul style="list-style-type: none"> <li>■ 9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.</li> </ul>




**8200-ISP**



**IG8300-ISP**

2 Pole, 3 Wire



All devices listed on this page conform to NEMA WD-1 and WD-6. Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE587), ANSI/IEEE C62.45.


Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance			
				UL1449	UL498	FSUL WC596	cUL/CSA
<b>Hospital Grade Duplex Receptacles Back &amp; Side Wire</b>							
8200-ISP	15 125	Ivory	5-15R	•	•	•	•
8200-WSP	15 125	White	5-15R	•	•	•	•
8200-SP	15 125	Brown	5-15R	•	•	•	•
8200-GRYSP	15 125	Gray	5-15R	•	•	•	•
8200-REDSP	15 125	Red	5-15R	•	•	•	•
8200-LASP	15 125	Light Almond	5-15R	•	•	•	•
8200-BLSP	15 125	Blue	5-15R	•	•	•	•
8300-ISP	20 125	Ivory	5-20R	•	•	•	•
8300-WSP	20 125	White	5-20R	•	•	•	•
8300-SP	20 125	Brown	5-20R	•	•	•	•
8300-GRYSP	20 125	Gray	5-20R	•	•	•	•
8300-REDSP	20 125	Red	5-20R	•	•	•	•
8300-LASP	20 125	Light Almond	5-20R	•	•	•	•
8300-BLSP	20 125	Blue	5-20R	•	•	•	•
<b>Isolated Ground Hospital Grade Duplex Receptacles Back &amp; Side Wire</b>							
IG8200-ISP	15 125	Ivory	5-15R	•	•	•	•
IG8200-WSP	15 125	White	5-15R	•	•	•	•
IG8200-GRYSP	15 125	Gray	5-15R	•	•	•	•
IG8200-LASP	15 125	Light Almond	5-15R	•	•	•	•
IG8200-BLSP	15 125	Blue	5-15R	•	•	•	•
IG8200-OSP	15 125	Orange	5-15R	•	•	•	•
IG8300-ISP	20 125	Ivory	5-20R	•	•	•	•
IG8300-WSP	20 125	White	5-20R	•	•	•	•
IG8300-GRYSP	20 125	Gray	5-20R	•	•	•	•
IG8300-LASP	20 125	Light Almond	5-20R	•	•	•	•
IG8300-BLSP	20 125	Blue	5-20R	•	•	•	•
IG8300-OSP	20 125	Orange	5-20R	•	•	•	•

TVSS Straight Blade Receptacles




# Straight Blade Devices TVSS Straight Blade Receptacles


15 & 20A, 125VAC



5262-ISP



IG5362-ISP



5252-ISP

2 Pole, 3 Wire



NEMA 5-15R



NEMA 5-20R

Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance			
	A.	VAC			UL1449	UL498	FSUL WC596	cUL/CSA
<b>Extra Heavy-Duty Spec. Grade Duplex Receptacles Back &amp; Side Wire*</b>								
5262-ISP	15	125	Ivory	5-15R	•	•	•	•
5262-WSP	15	125	White	5-15R	•	•	•	•
5262-SP	15	125	Brown	5-15R	•	•	•	•
5262-GRYSP	15	125	Gray	5-15R	•	•	•	•
5262-REDSP	15	125	Red	5-15R	•	•	•	•
5262-LASP	15	125	Light Almond	5-15R	•	•	•	•
5262-BLSP	15	125	Blue	5-15R	•	•	•	•
5362-ISP	20	125	Ivory	5-20R	•	•	•	•
5362-WSP	20	125	White	5-20R	•	•	•	•
5362-SP	20	125	Brown	5-20R	•	•	•	•
5362-GRYSP	20	125	Gray	5-20R	•	•	•	•
5362-REDSP	20	125	Red	5-20R	•	•	•	•
5362-LASP	20	125	Light Almond	5-20R	•	•	•	•
5362-BLSP	20	125	Blue	5-20R	•	•	•	•
<b>Isolated Ground Spec. Grade Duplex Receptacles Back &amp; Side Wire</b>								
IG5262-ISP	15	125	Ivory	5-15R	•	•	•	•
IG5262-WSP	15	125	White	5-15R	•	•	•	•
IG5262-GRYSP	15	125	Gray	5-15R	•	•	•	•
IG5262-BLSP	15	125	Blue	5-15R	•	•	•	•
IG5262-OSP	15	125	Orange	5-15R	•	•	•	•
IG5362-ISP	20	125	Ivory	5-20R	•	•	•	•
IG5362-WSP	20	125	White	5-20R	•	•	•	•
IG5362-GRYSP	20	125	Gray	5-20R	•	•	•	•
IG5362-LASP	20	125	Light Almond	5-20R	•	•	•	•
IG5362-BLSP	20	125	Blue	5-20R	•	•	•	•
IG5362-OSP	20	125	Orange	5-20R	•	•	•	•
<b>Specification Grade Duplex Receptacles Back &amp; Side Wire*</b>								
5252-ISP	15	125	Ivory	5-15R	•	•	•	•
5252-WSP	15	125	White	5-15R	•	•	•	•
5252-GRYSP	15	125	Gray	5-15R	•	•	•	•
5252-LASP	15	125	Light Almond	5-15R	•	•	•	•
5252-BLSP	15	125	Blue	5-15R	•	•	•	•
5352-ISP	20	125	Ivory	5-20R	•	•	•	•
5352-WSP	20	125	White	5-20R	•	•	•	•
5352-GRYSP	20	125	Gray	5-20R	•	•	•	•
5352-LASP	20	125	Light Almond	5-20R	•	•	•	•
5352-BLSP	20	125	Blue	5-20R	•	•	•	•

\*For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.  
Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE587), ANSI/IEEE C62.45.


Catalog Number	Description	Catalog Number	Description	Color
<b>Wall Plates for TVSS Duplex Receptacles</b>				
SS26	Stainless Steel Decorator	TP26-IG**	Thermoplastic Decorator	Orange
SS26-IG**	Stainless Steel Decorator	TP26-BL	Thermoplastic Decorator	Blue
SB26	Brass Decorator		**For Isolated Ground	

# Straight Blade Devices Quad Receptacles Specifications


Pass & Seymour



<b>Hard Use Spec Grade &amp; Hard Use TVSS Spec Grade Quads</b>	
<ul style="list-style-type: none"> <li>• Isolated ground complied with NEC® 410-56(c) and 250-74 exception 4</li> <li>• Conforms to NEMA WD-1, WD-6.</li> </ul>	
<b>Electrical</b>	
Frequency	60Hz
Voltage	125V
<b>Mechanical</b>	
Terminal Identification	Brass = Hot, Nickel = Neutral, Green = Ground
Terminal Accommodation	#14 –12 AWG copper and copper-clad
Product Identification	Ratings are permanent part of device
Weight	10.75 oz.
<b>Environmental</b>	
Flammability	UL94 V2
Operating Temperature	-40°C to 65°C (-40°F to 150°F) continuous without impact
<b>Materials</b>	
Face	Nylon
Body	Nylon
Line Terminals	.035" T-type Triple-Wipe Phosphor Bronze
Terminal Screws	Brass #8-32
Hex Head Grounding Screw	Steel (Green)
Mounting Screws	Zinc-plated steel
<b>Additional Specifications for Hard Use TVSS Spec Grade Quads</b>	
<ul style="list-style-type: none"> <li>• ANSI /IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45</li> <li>• Installation Categories "A" (ring wave) and "B" (unidirectional impulse)</li> </ul>	
<b>Electrical</b>	
MOV Rating	18mm
UL1449 Suppressed Voltage Rating	500V (L-N, L-G, N-G)
Noise Attenuation	-35db Noise Filtering at 5kHz-50MHz
Thermal Protection	Fused
Green LED Indicator	ON when protection is active, OFF when protection is inactive



**Quad Receptacle**




**Adapter Plate**

# Straight Blade Devices Quad Receptacles & Accessories

15 & 20A, 125V


**Application**  
Pass & Seymour/Legrand's quad receptacles are designed for dense, multiple-outlet applications such as personal computers and peripherals, office equipment, and home entertainment centers. The bidirectional outlet configuration allows use of up to four oversized plugs, in close proximity. The clean, contemporary design of the quad receptacle allows for surface mounting with minimal protrusion from the wall. No wall plate is required.

- Features**
- Rugged nylon face and body withstands impacts and hard use.
  - Built-in wire stripping gauge.
  - Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.
  - Heavy-duty, phosphor bronze contacts.
  - Shielding walls guard against live-circuit-to-ground shorts.
  - Split circuit break-off tabs.
  - UL and CSA listed.



Quad Receptacle

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL498	UL1449	CSA
<b>Hospital Grade Isolated TVSS Quads</b>						
IG420-HISP	20 125	Ivory	5-20R	•	•	
IG420-HWSP	20 125	White	5-20R	•	•	
IG420-HGRYSP	20 125	Gray	5-20R	•	•	
IG420-HBLSP	20 125	Blue	5-20R	•	•	
<b>Hospital Grade Quads</b>						
420-HI	20 125	Ivory	5-20R	•		•
420-HW	20 125	White	5-20R	•		•
420-H	20 125	Brown	5-20R	•		•
420-HGRY	20 125	Gray	5-20R	•		•
420-HRED	20 125	Red	5-20R	•		•
<b>Specification Grade TVSS Quads</b>						
420-ISP	20 125	Ivory	5-20R	•	•	
420-BLSP	20 125	Blue	5-20R	•	•	
<b>Specification Isolated Grade Quads</b>						
IG415	15 125	Orange	5-15R	•		•
IG420	20 125	Orange	5-20R	•		•
<b>Specification Grade Quads</b>						
415-I	15 125	Ivory	5-15R	•		•
415-W	15 125	White	5-15R	•		•
415-GRY	15 125	Gray	5-15R	•		•
420-I	20 125	Ivory	5-20R	•		•
420-W	20 125	White	5-20R	•		•
420-GRY	20 125	Gray	5-20R	•		•
<b>Quad Adapter Plates</b>						
4AP-I		Ivory		•		•
4AP-W		White		•		•
4AP		Brown		•		•
4AP-GRY		Gray		•		•
4AP-RED		Red		•		•
4AP-BL		Blue		•		•
4AP-ORG		Orange		•		•





# Straight Blade Devices Dust & Moisture Resistant & Clock Hanger Receptacles

15 & 20A, 125V


**Pass & Seymour**




Straight Blade Devices

### Features – Dust & Moisture Resistant

- Duplex receptacle has face backed by neoprene gasket which is slit to provide wiping action on plug blades and to provide positive closure when not in use.
- Cellular neoprene sealing mat fits under wall plate.



**6207**




**S3713-I**

Catalog Number	Rating A. V.	Description	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	CS C22.2 No. 42
<b>Dust &amp; Moisture Resistant</b>						
<b>6207</b>	15 125	Duplex, Dust and Moisture Resistant, Gray	5-15R	•	•	•
<b>CR6207</b>	15 125	Duplex, Corrosion, Dust and Moisture Resistant, Yellow	5-15R	•	•	•
<b>6307</b>	20 125	Duplex, Dust and Moisture Resistant, Gray	5-20R	•	•	•
<b>CR6307</b>	20 125	Duplex, Corrosion, Dust and Moisture Resistant, Yellow	5-20R	•	•	•

Catalog Number	Rating A. V.	Description	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	CS C22.2 No. 42
<b>Clock Hangers</b>						
<b>S3713-I</b>	15 125	Recessed Receptacle with Ivory Smooth Wall Plate	5-15R	•	•	•
<b>S3713-W</b>	15 125	Recessed Receptacle with White Smooth Wall Plate	5-15R	•	•	•
<b>S3713-BK</b>	15 125	Recessed Receptacle with Black Smooth Wall Plate	5-15R	•	•	•
<b>S3713-LA</b>	15 125	Recessed Receptacle with Light Almond Smooth Wall Plate	5-15R	•	•	•
<b>S3733-SS</b>	15 125	Recessed Receptacle with Stainless Steel Wall Plate	5-15R	•	•	•
<b>S3733</b>	15 125	Recessed Receptacle with Brass Wall Plate	5-15R	•	•	•

2 Pole, 3 Wire



**NEMA  
5-15R**

**NEMA  
5-20R**

All devices listed on this page conform to NEMA WD-1 and WD-6.

Dust & Moisture Resistant & Clock Hanger

# Straight Blade Devices Power Outlet Receptacles & Plugs

20, 30, 50, & 60A

Rating A. V.	Receptacle/Plug Configuration & NEMA No.						
		Flush Receptacle	Wall Plate	Surface Receptacle	Plug	Angle Plug	Connector
				Catalog Nos.			
<b>2 Pole, 3 Wire Grounding</b>							
30 125	5-30	<b>3802</b> AL/CU	1-Gang: <b>TP724**</b> 2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>		<b>D0531</b> .57"-1.26"		<b>D0533</b> .57"-1.26"
30 125	NEMA TT30	<b>3830</b> AL/CU*	1-Gang: <b>TP724**</b> 2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>				
30 250	6-30	<b>3801</b> AL/CU	1-Gang: <b>TP724**</b> 2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>		<b>D0631</b> .57"-1.26"	<b>3869</b>	<b>D0633</b> .57"-1.26"
50 125	5-50				<b>D0551</b> .57"-1.26"		<b>D0553</b> .57"-1.26"
50 250	6-50	<b>3804</b> AL/CU	1-Gang: <b>TP724**</b> 2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>	<b>3852</b> AL/CU	<b>D0651</b> .57"-1.26"	<b>3869</b>	<b>D0653</b> .57"-1.26"
<b>3 Pole, 3 Wire Non-Grounding</b>							
30 125/250 Dryer	10-30	<b>3860</b> AL/CU	1-Gang: <b>TP724**</b> 2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>	<b>388</b> AL/CU	<b>1031</b>	<b>3861</b>	
50 125/250 Range	10-50	<b>3890</b> AL/CU	1-Gang: <b>TP724**</b> 2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>	<b>385</b> AL/CU	<b>1051</b> .57"-1.26"	<b>3861</b>	<b>1053</b> .32"-.91"
<b>3 Pole, 4 Wire Grounding</b>							
20 125/250	14-20	<b>3820</b>	1-Gang: <b>SS7**</b>				
30 125/250 Dryer	14-30	<b>3864</b> AL/CU	2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>	<b>3884/3884-40†</b> AL/CU	<b>1431</b> .57"-1.26"	<b>5746-AN</b> <b>3867</b>	
30 3ø, 250	15-20				<b>1521</b> .57"-1.26"		
30 3ø, 250	15-30	<b>5740</b> AL/CU	2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>			<b>5741-AN</b>	
50 125/250 Range	14-50	<b>3894</b> AL/CU	2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>	<b>3854/3854-40†</b> AL/CU	<b>1451</b> .57"-1.26"	<b>5745-AN</b> <b>3867</b>	
50 3ø, 250	15-50	<b>5750</b> AL/CU	2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>			<b>5751-AN</b>	
60 3ø, 250	15-60	<b>5760</b> AL/CU	2-Gang: <b>SS702**</b> 2-Gang: <b>TP703†</b>			<b>5761-AN</b>	
<b>4 Pole, 4 Wire Non-Grounding</b>							
20 3øY, 120/208	18-20	<b>3822</b>	1-Gang: <b>SS7**</b>		<b>7251-DF</b> .35"-1.05"		
60 3øY, 120/208	18-60	<b>3870</b> AL/CU	2-Gang: <b>SS701†</b>		<b>D1861</b> .57"-1.26"	<b>8302-AN</b>	

\*For recreational vehicles. \*\*For 2 screw mounting. †For 4 screw mounting. ‡In bulk pack of 40 with plastic snap-in wire clamp.  
For further information consult Wall Plate Section R (for Stainless Steel versions of TP724 and TP703, refer to pages S-11 and S-12).

All devices listed on this page conform to NEMA WD-1 and WD-6.











# Straight Blade Devices Power Outlet Receptacles & Plugs

20, 30, 50, & 60A

Pass & Seymour



Straight Blade Devices



All devices listed on this page conform to NEMA WD-1 and WD-6.

Power Outlet Receptacles & Plugs



# Straight Blade Devices Power Outlet Receptacles & Plugs


20, 30, 50 & 60A



Flush Receptacle



Surface Receptacle



Angle Plug



Plug



Wall Plate

### Application




Power devices are for use in industrial, institutional, commercial, and certain residential applications to provide higher amperage power to equipment such as air conditioners, copiers, small welders, ranges, and dryers.

### Features

- Flush receptacle bodies are molded of arc-resistant plastic.
- All devices are of dead front design.
- Receptacles have double-wipe contacts of high performance copper-based alloy.
- Recommended stainless steel wall plates are listed with each flush receptacle.
- UL Listed for use with aluminum wiring.

Receptacle Amp. Rating	AWG Size	Material
<b>Conductor Size &amp; Material for Power Outlet Receptacles</b>		
20A	#14 – #10	Copper/Copper-clad
30A	#10 – #6	Copper/Copper-clad/Aluminum
50A	#10 – #6	Copper/Copper-clad/Aluminum
60A	#8 – #4	Copper/Copper-clad/Aluminum

Ampere Rating	With Non-Metallic Sheathed Cable	With Conduit
<b>Recommended Box Sizes for Flush Receptacles</b>		
30A	4" sq. x 2-1/8" deep	4-11/16" sq. x 2-1/8" deep
50A	4-11/16" sq. x 2-1/8" deep	2-g deep box (4" sq. x 2-1/2" deep)
60A	4-11/16" sq. x 2-1/8" deep with 1/2" raised ring	2-g deep box (4" sq. x 2-1/2" deep)

Description	Color	Nylon	Metal	Wall Plates Recommended for the Following Flush Receptacles
		TradeMaster®	Material	
<b>Accessories – Flush Receptacle Wall Plates</b>				
 • 2.156" hole for 2.125" dia. device • 2 mtg. holes	Ivory White Brown Gray Black Light Almond	TP724-I TP724-W TP724 TP724-GRY TP724-BK TP724-LA	Chrome S384-C  302S/S SS724	2 Pole, 3 Wire Grounded 3801 3804 3802 3830
 • 2-5/32" hole for 2-1/8" dia. device • 2 mtg. holes			302S/S SS702	3 Pole, 3 Wire Ungrounded 3860 3860
 • 2.1563" hole for 2.125" dia. device • 4 mtg. holes	Ivory White Brown Gray Black Light Almond	TP703-I TP703-W TP703 TP703-GRY TP703-BK TP703-LA	Chrome S3862-C 302S/S SS703	3 Pole, 4 Wire Ungrounded 3864 5740 3894 5750 5760

**New Installations require 4 wire range and dryer outlets.** Ref: 2002 NEC 250-134, 250-138  
**Existing Installations permitted to use 3 wire range and dryer outlets.** Ref: 2002 NEC 250-140

# Straight Blade Devices Miscellaneous Configurations

**Pass & Seymour**



## Straight Blade Devices, 3 Wire, Specification Grade

Catalog Number	Rating A. V.	Description	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	CS C22.2 No. 42
<b>2 Pole, 3 Wire Grounding</b>						
5762	15 277	Duplex Receptacle, Self-Grounding	7-15R	•		
D0711	15 277	Plug, Yellow	7-15P	•		•
7621	20 277	Single Receptacle	7-20R	•		
D0721	20 277	Plug, Yellow	7-20P			
<b>3 Pole, 3 Wire Non-Grounding</b>						
6810-I	20 125/250	Receptacle, Ivory	10-20R	•		
6810	20 125/250	Receptacle, Black	10-20R	•		
9977	20 125/250	Plug, Nylon	10-20P			
9750-DF	10 250	Plug, with Nylon Insert	NON-NEMA			
7088	20 125/250	Connector, Armored	10-20R			



NEMA 7-15R



NEMA 7-15P



NEMA 7-20R




NEMA 7-20P




NEMA 10-20R




NEMA 10-20P




5762



6810-I




7088



9750-DF



9977



7621

All devices listed on this page conform to NEMA WD-1 and WD-6.

# Straight Blade Devices Power & TVSS Strips

### Features

- UL1449 listed.
- Heavy duty cord from 3' to 15', depending on device.
- Circuit breaker switch.

Catalog Number	Rating A.	Rating V.	Type of Housing	# of Outlets	Cord Length	Color
<b>Power Strips without Surge Protection</b>						
PNS6	15	125	Strip	6	3'	Black
PNS7L	15	125	Strip	7	8'	Black
PNS10	15	125	Block	10	15'	Black

### Application

There are an average of over 250 power disturbances per year in each home or office in the United States. Over 8% data loss is a direct result from lightning and the value of equipment and data is sometimes much greater than that of equipment.

Surges and spikes can come through power lines as well as phone and coax lines. So choose a protector which includes phone and/or coax protection.


### Features

- 330V clamping voltage, UL's best rating.
- UL1449 listed.
- Heavy duty cord from 3' to 15', depending on device.
- Multiple function protection available for power, phone, fax, modem, coax or data.
- Extremely long life with dependable protection.
- Surge protection indicator on surge devices.
- Circuit breaker switch.
- Heavy-duty high-energy MOVs.
- Thermal fuses break the electrical circuit.
- Power shutdown feature disconnects power to outlets when source protection has expired to protect your connected equipment.


### Protection Specifications

- Line protection modes: L-N, L-G, N-G.
- Spike protection for sudden, dramatic surges, over 330V.
- Surge protection lasts for 1/120 of a second, for moderate short term overvoltage.
- EMI/RFI noise attenuation.


Catalog Number	Rating A.	Rating V.	Type of Housing	# of Outlets	Cord Length	Joule Rating Range	Max. Spike Current (Amps)	Type of Protection		Color
								Phone/Fax	Coax	
<b>Power Strips with Surge Protection</b>										
PS1	15	125	Tap	1		330J	18K			PC Gray
PS1P	15	125	Tap	1		555J	36K	X		PC Gray
PS6	15	125	Strip	6	3'	330J	18K			PC Gray
PS7	15	125	Strip	7	6'	555J	36K			PC Gray
PS7P	15	125	Strip	7	6'	555J	36K	X		PC Gray
PS7L	15	125	Strip	7	15'	555J	36K			PC Gray
PS8C	15	125	Block	8	8'	925J	60K		X	PC Gray
PS8P	15	125	Block	8	8'	925J	60K	X	X	PC Gray
PS10PC	15	125	Block	10	8'	1295J	84K	X	X	PC Gray



**TAP – PS1**



**STRIP – PNS7L**



**BLOCK – PS10PC**



# Straight Blade Devices Power & TVSS Device Specifications

**Pass & Seymour**



Power Devices – Ratings			
Catalog Number	PNS6	PNS7L	PNS10
Type of Housing	Strip	Strip	Strip
Total Outlets	6	7	10
Standard Grounded Outlets	6	6	6
Transformer Ready Outlets	0	1	4
Power Indicator			X
Circuit Breaker Switch	Unlighted	Lighted	Lighted
Cord Length (exposed) ft.	3'	8'	15'
Plug	Straight	Straight	Straight
Molded Add-On Safety Covers	0	0	5
Molded Housing Color	Black	Black	Black

Power & TVSS Devices – Ratings									
Catalog Number	PS1	PS1P	PS6	PS7	PS7P	PS7L	PS8C	PS8P	PS10PC
Type of Housing	Tap	Tap	Strip	Strip	Strip	Strip	Block	Block	Block
Number of Outlets	1	1	6	7	7	7	8	8	10
Standard Grounded Outlets	1	1	6	6	6	6	0	0	6
Transformer Ready Outlets	1	1	0	1	1	1	8	8	4
Joule Rating Range	330J	555J	330J	555J	555J	555J	925J	925J	1295J
MOV Configuration	3-14mm	3-20mm	3-14mm	3-20mm	3-20mm	3-20mm	5-20mm	5-20mm	7-20mm
Clamping Voltage	330V	330V	330V	330V	330V	330V	330V	330V	330V
Max. Spike Current (Amps)	18K	36K	18K	36K	36K	36K	60K	60K	84K
EMI Filter Capacitors	X	X		X	X	X	X	X	X
Noise Reduction Coil							X	X	X
Protection (L-N, L-G, N-G)	X	X	X	X	X	X	X	X	X
Surge Protection Indicator	X	X	X	X	X	X	X	X	X
Ground/Wiring Indicator				X	X	X	X	X	X
Power Shutdown Feature			X	X	X	X	X	X	X
Circuit Breaker Switch			Unlighted	Lighted	Lighted	Lighted	Lighted	Lighted	Lighted
Cord Length (exposed) ft.			3'	6'	6'	15'	8'	8'	8'
Plug			Straight	Straight	Straight	Straight	Rt. Angle	Rt. Angle	Rt. Angle
Phone/Fax Protection		X			X			X	X
Phone Line(s) Configuration					1 in/1 out			1 in/2 out	1 in/1 out
Phone Jack Spec		RJ-11			RJ-11			RJ-45	RJ-45
Nickel-Coaxial Jack Protection							X		X
6' Phone Cable (6P2C)		X			X			X	X
6' Coax Cable (Nickel Plated)							X		X
Molded Add-On Safety Covers	0	0	0	2	2	2	4	4	5
Molded Housing Color	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray	PC Gray
UL1449 2nd Edition	X	X	X	X	X	X	X	X	X




# Devices & Wall Plates Color Selection Chart


Pass & Seymour



## Devices & Plastic Wall Plate Colors



Ivory      Light Almond      White



Black      Blue      Brown      Gray      Orange      Red


See specific device and wall plate catalog charts for particular color availabilities.

## Metal Wall Plates




**Metal Finish**      Aluminum      Brass (Brushed)      Polished Brass      Stainless Steel      Brushed Bronze      Chrome

## Custom Metal Wall Plates Paint Finish Colors



**Paint Color**      Light Blue      Orange      Navy      Peach      Hunter Green      Gray      Yellow



**Paint Color**      Glossy Black      Brown      Burgundy      White      Primer      Red



**Paint Color**      Beige      Pink      Flat Black      Ivory      Light Almond      Medium Blue

To order custom metal wall plates, see Pages S-40 - S-43.