



- 1) Turn off power.
  - 2) Assemble conduit connector to knocked-out hole on fixture housing.
  - 3) Run wire through assembled conduit connector.
  - 4) Tighten screws on conduit connector to clamp conduit in position.
  - 5) Grounding instructions: (See illus. A or B)
    - A) On fixtures where mounting strap is provided with a hole and two raised dimples. Wrap ground wire from outlet box around green ground screw, and thread into hole.
    - B) On fixtures where a cupped washer is provided. Attach ground wire from outlet box under cupped washer and green ground screw, and thread into mounting strap.
- If fixture is provided with ground wire. Connect fixture ground wire to outlet box ground wire with wire connector. (Not provided)



- 6) Make wire connections (connectors not provided). Reference chart below for correct connections and wire accordingly.

Connect Black or Red Supply Wire to:	Connect White Supply Wire to:
Black	White
*Parallel cord (round & smooth)	*Parallel cord (square & ridged)
Clear, Brown, Gold or Black without tracer	Clear, Brown, Gold or Black with tracer
Insulated wire (other than green) with copper conductor	Insulated wire (other than green) with silver conductor

\*Note: When parallel wires (SPT I & SPT II) are used. The neutral wire is square shaped or ridged and the other wire will be round in shape or smooth (see illus.)



- 7) Secure fixture housing to outlet box.
- 8) Slide faceplate onto backpan.
- 9) Fit diffuser over fixture housing.
- 10) Secure diffuser to fixture housing with screws.