

# Section N Wallplates and Covers

## Index

Product	Page
Features and Benefits .....	N-2
Snap-On Wallplates .....	N-4
Toggle Switch Wallplates .....	N-5
Duplex and Single Receptacle Wallplates .....	N-6
Single Receptacle Wallplates .....	N-7
Blank Wallplates .....	N-8
347 Volt Wallplates .....	N-9
Decorator Wallplates .....	N-10
Combination Wallplates, 2-Gang .....	N-11
Combination Wallplates, 3-Gang .....	N-13
Combination Wallplates, 4- and 5-Gang .....	N-14
Telephone and Coaxial Outlet Plates .....	N-15
Jumbo, Metal Wallplates .....	N-16
Pre-Marked "EMERGENCY" and Barrel Key Switch Wallplates .....	N-17
Pre-Marked "ISOLATED GROUND" or "COMPUTER ONLY" Wallplates .....	N-18
Security Wallplates .....	N-19
Accessories and Selection Charts .....	N-20
Weatherproof Plates for Receptacles .....	N-21
Weatherproof Plates for Receptacles and Switches .....	N-22
Weatherproof Covers for Flanged Devices .....	N-23
Weatherproof Switch Plates, Covers and Locking Covers .....	N-24
Heavy Duty Weatherproof Covers .....	N-25
Weatherproof Covers .....	N-26
Extra Duty Metallic While-In-Use Covers .....	N-27
While-In-Use Weatherproof Covers .....	N-28
Screws and Accessories .....	N-29
Technical Information .....	N-30
Wallplate Dimensions .....	N-31
Custom Metal Wallplates .....	N-32

### Features and Benefits



### Nylon Wallplates



### Metal Wallplates



### Weatherproof Covers



# Wallplates Nylon Wallplates

Features and Benefits




## Nylon Wallplates

Our line of nylon wallplates features larger standard sized wallplates to provide extra coverage to hide rough box opening, improved aesthetics, greater strength, impact resistance, along with excellent cleanability in all different types of environments.


- Standard size is 1/8 inch larger to give you extra coverage to hide rough box openings. Also available in mid-size and pre-marked.
- Curved corners for improved aesthetics, for use in any application.
- Reinforcement ribs for extra strength.
- Captive screw feature holds mounting screw in place for quick and easy installation.
- High-impact, self-extinguishing nylon material, which is virtually unbreakable.
- Smooth, easy to clean finish is highly resistant to solvents and cleaning solutions, providing long life in the harshest environments.

Hubbell's standard sized wallplates are 1/8 inch larger to provide you that extra coverage to hide rough box openings. The depth is 1/4 inch so that it will comfortably fit over the device even on imperfect installations or on retrofit work.


## Nylon Wallplates



## Nylon Pre-Marked Wallplates




## Metal Wallplates



## Pre-Marked





**Protective plastic film helps to prevent scratches and damage.**

**Stainless Steel**

Provide solutions for a variety of industrial and commercial applications.

- Environments subjected to heavy abuse.
- The 302/304 type stainless steel wallplates are ideal for highly corrosive environments such as food processing, hospitals, static free requirements and more.

Non-magnetic: 18.0% Chromium  
8.0% Nickel

- Standard commercial use.
- The 430 type stainless steel wallplates are aesthetically identical to the 302/304 type stainless steel wallplates and are best suited for environments where corrosion resistance is less critical.

Magnetic: 17.0% Chromium  
Less than 0.5% Nickel

**Smooth Solid Brass**

- Provides a plush appearance with the durability of metal.
- Finish is lacquer coated to inhibit oxidation.

**Anodized Aluminum**

- Non-magnetic and corrosion resistance for a wide range of applications.
- Finish is lacquer coated to inhibit oxidation.

**Extra-Duty Metallic While-in-Use Covers**

These covers are designed for use whenever protection is required while an outlet is in use. Covers meet or exceed the extra-duty rating per UL 514D, and are NEMA 3R rated.

- Die-cast aluminum construction
- Powder coated “chip resistant” paint corrosion protection
- Unique plug management provision for securing device and cord



**2014 National Electrical Code (NEC®) Requirement**

**406.9 Receptacles in Damp or Wet Locations.**

406.9 Receptacles in Damp or Wet Locations.

(B) Wet Locations.

(1) 15 and 20 Ampere Receptacles in a Wet Location. 15 and 20 ampere, 125 and 250 volt receptacles installed in a wet location shall have an enclosure that is weatherproof whether or not the attachment plug cap is inserted. An outlet box hood installed for this purpose shall be listed, and shall be identified as “extra-duty.” All 15 and 20 ampere, 125 and 250 volt nonlocking-type receptacles shall be listed weather-resistant type.

Exception: 15 and 20 ampere, 125 through 250 volt receptacles installed in a wet location and subject to routine high-pressure spray washing shall be permitted to have an enclosure that is weatherproof when the attachment plug is removed.

(2) Other Receptacles. All other receptacles installed in a wet location shall comply with (B)(2)(a) or (B)(2)(b).


(a) A receptacle installed in a wet location, where the product intended to be plugged into it is not attended while in use, shall have an enclosure that is weatherproof with the attachment plug cap inserted or removed.

(b) A receptacle installed in a wet location where the product intended to be plugged into it will be attended while in use (e.g., portable tools) shall have an enclosure that is weatherproof when the attachment plug is removed.



### More Style In a Snap

Snap-on wallplates offer a clean, elegant look that can be installed in seconds. Screw the mounting plate onto the device and press the snap-on cover into place.












### Snap-On Wallplates

Description		Color	Decorator Catalog Number	Toggle Catalog Number
1-Gang, 1-Decorator	1-Gang, 1-Toggle Style	Ivory Light Almond White	<b>RCW1I</b> <b>RCW1LA</b> <b>RCW1W</b>	<b>RFW1I</b> - <b>RFW1W</b>
2-Gang, 2-Decorator	2-Gang, 2-Toggle Style	Ivory Light Almond White	<b>RCW2I</b> <b>RCW2LA</b> <b>RCW2W</b>	<b>RFW2I</b> - <b>RFW2W</b>
3-Gang, 3-Decorator	3-Gang, 3-Toggle Style	Ivory Light Almond White	<b>RCW3I</b> <b>RCW3LA</b> <b>RCW3W</b>	<b>RFW3I</b> - <b>RFW3W</b>
4-Gang, 4-Decorator		Ivory Light Almond White	<b>RCW4I</b> <b>RCW4LA</b> <b>RCW4W</b>	- - -
5-Gang, 5-Decorator		Ivory Light Almond White	<b>RCW5I</b> <b>RCW5LA</b> <b>RCW5W</b>	- - -
6-Gang, 6-Decorator		Ivory Light Almond White	<b>RCW6I</b> <b>RCW6LA</b> <b>RCW6W</b>	- - -

Dimensions in Inches (mm)

## Toggle Switch Wallplates






Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number	
 1-Gang, 1-Toggle	Almond	<b>NP1AL</b>	<b>NPJ1AL</b>	Aluminum	<b>SA1</b>	
	Black	<b>NP1BK</b>	<b>NPJ1BK</b>	Brass	<b>SB1</b>	
	Brown	<b>NP1</b>	<b>NPJ1</b>	Brass Plated	<b>SBP1</b>	
	Gray	<b>NP1GY</b>	<b>NPJ1GY</b>	Chrome	<b>SCH1</b>	
	Ivory	<b>NP1I</b>	<b>NPJ1I</b>	S/S 302/304	<b>SS1</b>	
	Light Almond	<b>NP1LA</b>	<b>NPJ1LA</b>	S/S 430	<b>SS1L</b>	
	Office White	<b>NP1OW</b>	<b>NPJ1OW</b>	Steel, Almond	<b>SP1AL*</b>	
	Red	<b>NP1R</b>	<b>NPJ1R</b>	Steel, Gray	<b>SP1G*</b>	
	White	<b>NP1W</b>	<b>NPJ1W</b>			
	 2-Gang, 2-Toggle	Almond	<b>NP2AL</b>	<b>NPJ2AL</b>	Aluminum	<b>SA2</b>
Black		<b>NP2BK</b>	<b>NPJ2BK</b>	Brass	<b>SB2</b>	
Brown		<b>NP2</b>	<b>NPJ2</b>	Brass Plated	<b>SBP2</b>	
Gray		<b>NP2GY</b>	<b>NPJ2GY</b>	Chrome	<b>SCH2</b>	
Ivory		<b>NP2I</b>	<b>NPJ2I</b>	S/S 302/304	<b>SS2</b>	
Light Almond		<b>NP2LA</b>	<b>NPJ2LA</b>	S/S 430	<b>SS2L</b>	
Office White		<b>NP2OW</b>	<b>NPJ2OW</b>	Steel, Almond	<b>SP2AL*</b>	
Red		<b>NP2R</b>	<b>NPJ2R</b>	Steel, Gray	<b>SP2G*</b>	
White		<b>NP2W</b>	<b>NPJ2W</b>			
 3-Gang, 3-Toggle		Almond	<b>NP3AL</b>	<b>NPJ3AL</b>	Aluminum	①
	Black	<b>NP3BK</b>	<b>NPJ3BK</b>	Brass	<b>SB3</b>	
	Brown	<b>NP3</b>	<b>NPJ3</b>	Brass Plated	<b>SBP3</b>	
	Gray	<b>NP3GY</b>	<b>NPJ3GY</b>	Chrome	<b>SCH3</b>	
	Ivory	<b>NP3I</b>	<b>NPJ3I</b>	S/S 302/304	<b>SS3</b>	
	Light Almond	<b>NP3LA</b>	<b>NPJ3LA</b>	S/S 430	<b>SS3L</b>	
	Office White	<b>NP3OW</b>	<b>NPJ3OW</b>	Steel, Almond	<b>SP3AL*</b>	
	Red	-	<b>NPJ3R</b>			
	White	<b>NP3W</b>	<b>NPJ3W</b>			
	 4-Gang, 4-Toggle	Black	<b>NP4BK</b>	<b>NPJ4BK</b>	Aluminum	①
Brown		<b>NP4</b>	<b>NPJ4</b>	Brass	<b>SB4</b>	
Gray		<b>NP4GY</b>	<b>NPJ4GY</b>	Brass Plated	<b>SBP4</b>	
Ivory		<b>NP4I</b>	<b>NPJ4I</b>	Chrome	①	
Light Almond		<b>NP4LA</b>	<b>NPJ4LA</b>	S/S 302/304	<b>SS4</b>	
Office White		<b>NP4OW</b>	<b>NPJ4OW</b>	S/S 430	<b>SS4L</b>	
White		<b>NP4W</b>	<b>NPJ4W</b>	Steel, Almond	<b>SP4AL*</b>	
 5-Gang, 5-Toggle		Black	<b>NP5BK</b>	-	Aluminum	①
		Brown	<b>NP5</b>	-	Brass	<b>SB5</b>
		Gray	<b>NP5GY</b>	-	Brass Plated	①
	Ivory	<b>NP5I</b>	-	Chrome	①	
	Light Almond	<b>NP5LA</b>	-	S/S 302/304	<b>SS5</b>	
	White	<b>NP5W</b>	-	S/S 430	-	
 6-Gang, 6-Toggle	Brown	<b>NP6</b>	-	Aluminum	①	
	Gray	<b>NP6GY</b>	-	Brass	<b>SB6</b>	
	Ivory	<b>NP6I</b>	-	Brass Plated	①	
	Light Almond	<b>NP6LA</b>	-	Chrome	①	
	White	<b>NP6W</b>	-	S/S 302/304	<b>SS6</b>	
				S/S 430	-	
 7-Gang, 7-Toggle	Almond	-	-	Aluminum	①	
	Brown	-	-	Brass	①	
	Gray	-	-	Brass Plated	①	
	Ivory	-	-	Chrome	①	
	White	-	-	S/S 302/304	<b>SS607</b>	
 8-Gang, 8-Toggle	Almond	-	-	Aluminum	①	
	Brown	-	-	Brass	①	
	Gray	-	-	Brass Plated	①	
	Ivory	-	-	Chrome	①	
	White	-	-	S/S 302/304	<b>SS608</b>	
 2-Gang, 1-Toggle	Almond	-	-	Aluminum	-	
	Brown	-	-	Brass	-	
	Gray	-	-	Brass Plated	-	
	Ivory	-	-	Chrome	-	
	White	-	-	S/S 302/304	<b>SS740</b>	
				S/S 430	-	

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.




① Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.

\*Powder coat paint finish.

## Duplex Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 1-Gang, 1-Duplex	Almond	<b>NP8AL</b>	<b>NPJ8AL</b>	Aluminum	<b>SA8</b>
	Black	<b>NP8BK</b>	<b>NPJ8BK</b>	Brass	<b>SB8</b>
	Blue	-	<b>NPJ8BL</b>	Brass Plated	<b>SBP8</b>
	Brown	<b>NP8</b>	<b>NPJ8</b>	Chrome	<b>SCH8</b>
	Gray	<b>NP8GY</b>	<b>NPJ8GY</b>	S/S 302/304	<b>SS8</b>
	Ivory	<b>NP8I</b>	<b>NPJ8I</b>	S/S 430	<b>SS8L</b>
	Light Almond	<b>NP8LA</b>	<b>NPJ8LA</b>	Steel, Almond	<b>SP8AL*</b>
	Office White	<b>NP8OW</b>	<b>NPJ8OW</b>	Steel, Gray	<b>SP8G*</b>
	Orange	<b>NP8OR</b>	-		
	Red	<b>NP8R</b>	<b>NPJ8R</b>		
	White	<b>NP8W</b>	<b>NPJ8W</b>		
 2-Gang, 2-Duplex	Black	<b>NP82BK</b>	<b>NPJ82BK</b>	Aluminum	<b>SA82</b>
	Brown	<b>NP82</b>	<b>NPJ82</b>	Brass	<b>SB82</b>
	Gray	<b>NP82GY</b>	<b>NPJ82GY</b>	Brass Plated	<b>SBP82</b>
	Ivory	<b>NP82I</b>	<b>NPJ82I</b>	Chrome	<b>SCH82</b>
	Light Almond	<b>NP82LA</b>	<b>NPJ82LA</b>	S/S 302/304	<b>SS82</b>
	Office White	<b>NP82OW</b>	<b>NPJ82OW</b>	S/S 430	<b>SS82L</b>
	Orange	<b>NP82OR</b>	-	Steel, Almond	<b>SP82AL*</b>
	Red	<b>NP82R</b>	<b>NPJ82R</b>	Steel, Gray	<b>SP82G*</b>
	White	<b>NP82W</b>	<b>NPJ82W</b>		
 3-Gang, 3-Duplex	Brown	<b>NP83</b>	-	Aluminum	①
	Ivory	<b>NP83I</b>	-	Brass	①
	White	<b>NP83W</b>	-	Brass Plated	①
				Chrome	①
			S/S 302/304	<b>SS83</b>	
			S/S 430	-	
			Steel, Almond	<b>SP83AL*</b>	
 4-Gang, 4-Duplex	Brown	<b>NP84</b>	-	Aluminum	①
	Ivory	<b>NP84I</b>	-	Brass	①
	White	<b>NP84W</b>	-	Brass Plated	①
				Chrome	①
			S/S 302/304	<b>SS84</b>	
			S/S 430	-	
 2-Gang, 1-Duplex	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	<b>SS748</b>
	-	-	-	S/S 430	-

## Single 15/20A Straight Blade or 15A Twist-Lock® Receptacle Wallplates






Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 1-Gang, 1-Single 1.40 in. (35.6) Dia. Hole	Black	<b>NP7BK</b>	<b>NPJ7BK</b>	Aluminum	<b>SA7</b>
	Brown	<b>NP7</b>	<b>NPJ7</b>	Brass	<b>SB7</b>
	Gray	<b>NP7GY</b>	<b>NPJ7GY</b>	Brass Plated	<b>SBP7</b>
	Ivory	<b>NP7I</b>	<b>NPJ7I</b>	Chrome	<b>SCH7</b>
	Light Almond	<b>NP7LA</b>	<b>NPJ7LA</b>	S/S 302/304	<b>SS7</b>
	Office White	<b>NP7OW</b>	<b>NPJ7OW</b>	S/S 430	<b>SS7L</b>
	Red	<b>NP7R</b>	<b>NPJ7R</b>	Steel, Almond	<b>SP7AL*</b>
	White	<b>NP7W</b>	<b>NPJ7W</b>	Steel, Gray	<b>SP7G*</b>
 2-Gang, 1-Single 1.40 in. (35.6) Dia. Hole	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	<b>SS747</b>
			S/S 430	-	
 2-Gang, 2-Single 1.40 in. (35.6) Dia. Hole	-	-	-	Aluminum	①
	-	-	-	Brass	①
	-	-	-	Brass Plated	①
	-	-	-	Chrome	①
	-	-	-	S/S 302/304	<b>SS72</b>
			S/S 430	-	

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.







① Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.

\*Powder coat paint finish.

**Single 20/30A Twist-Lock® Receptacle Wallplates**












Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 1-Gang, 1-Single 1.60 in. (40.6) Dia. Hole	Black	<b>NP720BK</b>	-	Aluminum	<b>SA720</b>
	Brown	<b>NP720</b>	-	Brass	<b>SB720</b>
	Gray	<b>NP720GY</b>	-	Brass Plated	①
	Ivory	<b>NP720I</b>	-	Chrome	①
	Office White	<b>NP720OW</b>	-	S/S 302/304	<b>SS720</b>
	Red	<b>NP720R</b>	-	S/S 430	-
	White	<b>NP720W</b>	-	-	-
 1-Gang, 1-Single 1.74 in. (44.2) Dia. Hole	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	<b>SS725</b>
 2-Gang, 1-Single 1.60 in. (40.6) Dia. Hole	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	<b>SS749</b>
 3-Gang, 2-Single 1.60 in. (40.6) Dia. Hole	-	-	-	Aluminum	①
	-	-	-	Brass	①
	-	-	-	Brass Plated	①
	-	-	-	Chrome	①
	-	-	-	S/S 302/304	<b>SS320</b>
 3-Gang, 2-Single 1.74 in. (44.2) Dia. Hole	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	<b>SS330</b>

**Single Receptacle Wallplates**

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 1-Gang, 1-Single 1.97 in. (50.0) Dia. Hole	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	<b>SS737</b>
	-	-	-	S/S 430	-
 1-Gang, 1-Single 2.16 in. (54.9) Dia. Hole	Black	<b>NP724BK</b>	<b>NPJ724BK</b>	Aluminum	<b>SA723</b>
	Brown	<b>NP724</b>	<b>NPJ724</b>	Brass	①
	Gray	<b>NP724GY</b>	<b>NPJ724GY</b>	Brass Plated	①
	Ivory	<b>NP724I</b>	<b>NPJ724I</b>	Chrome	<b>SCH723</b>
	White	<b>NP724W</b>	<b>NPJ724W</b>	S/S 302/304	<b>SS723</b>
				S/S 430	<b>SS723L</b>
 2-Gang, 1-Single 2.16 in. (54.9) Dia. Hole	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Chrome	<b>SCH702</b>
	-	-	-	S/S 302/304	<b>SS702</b>
	-	-	-	S/S 430	-
 2-Gang, 1-Single 2.16 in. (54.9) Dia. Hole	Black	<b>NP703BK</b>	<b>NPJ703BK</b>	Aluminum	-
	Brown	<b>NP703</b>	<b>NPJ703</b>	Brass	-
	Gray	<b>NP703GY</b>	<b>NPJ703GY</b>	Brass Plated	-
	Ivory	<b>NP703I</b>	<b>NPJ703I</b>	Chrome	-
	White	<b>NP703W</b>	<b>NPJ703W</b>	S/S 302/304	<b>SS703</b>
				S/S 430	<b>SS703L</b>
 2-Gang, 1-Single 2.48 in. (63.0) Dia. Hole	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	<b>SS701</b>
	-	-	-	S/S 430	-
 2-Gang, 1-Single 2.66 in. (67.6) Dia. Hole	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	<b>SS716</b>
	-	-	-	S/S 430	-

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.  
 ① Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.

**Blank Wallplates, Box Mount and Strap Mount**

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 1-Gang, 1-Blank, Box Mount	Almond	<b>NP13AL</b>	<b>NPJ13AL</b>	Aluminum	<b>SA13A</b>
	Black	<b>NP13BK</b>	<b>NPJ13BK</b>	Brass	<b>SB13</b>
	Brown	<b>NP13</b>	<b>NPJ13</b>	Brass Plated	<b>SBP13</b>
	Gray	<b>NP13GY</b>	<b>NPJ13GY</b>	Chrome	<b>SCH13</b>
	Ivory	<b>NP13I</b>	<b>NPJ13I</b>	S/S 302/304	<b>SS13</b>
	Light Almond	<b>NP13LA</b>	<b>NPJ13LA</b>	S/S 430	<b>SS13L</b>
	Office White	<b>NP13OW</b>	<b>NPJ13OW</b>	Steel, Almond	<b>SP14BAL*</b>
	White	<b>NP13W</b>	<b>NPJ13W</b>	Steel, Gray	<b>SP14BG*</b>
 2-Gang, 2-Blank, Box Mount	Almond	<b>NP23AL</b>	<b>NPJ23AL</b>	Aluminum	<b>SA23</b>
	Black	<b>NP23BK</b>	-	Brass	<b>SB23</b>
	Brown	<b>NP23</b>	<b>NPJ23</b>	Brass Plated	①
	Gray	<b>NP23GY</b>	-	Chrome	<b>SCH23</b>
	Ivory	<b>NP23I</b>	<b>NPJ23I</b>	S/S 302/304	<b>SS23</b>
	Light Almond	<b>NP23LA</b>	<b>NPJ23LA</b>	S/S 430	<b>SS23L</b>
	White	<b>NP23W</b>	<b>NPJ23W</b>	Steel, Almond	<b>SP24BAL*</b>
	Steel, Gray				<b>SP24BG*</b>
 3-Gang, 3-Blank, Box Mount	Brown	<b>NP33</b>	-	Aluminum	①
	Ivory	<b>NP33I</b>	-	Brass	①
	White	<b>NP33W</b>	-	Brass Plated	①
				Chrome	①
 3-Gang, 3-Blank, Box Mount				S/S 302/304	<b>SS33</b>
				S/S 430	-
				Steel, Almond	<b>SP34BAL*</b>
 4-Gang, 4-Blank, Box Mount	Brown	<b>NP43</b>	-	Aluminum	①
	Ivory	<b>NP43I</b>	-	Brass	①
	White	<b>NP43W</b>	-	Brass Plated	①
				Chrome	①
				S/S 302/304	<b>SS43</b>
				S/S 430	-
 1-Gang, 1-Blank, Strap Mount	Black	<b>NP14BK</b>	-	Aluminum	①
	Brown	<b>NP14</b>	-	Brass	<b>SB14</b>
	Gray	<b>NP14GY</b>	-	Brass Plated	①
	Ivory	<b>NP14I</b>	-	Chrome	①
	Office White	<b>NP14OW</b>	-	S/S 302/304	<b>SS14</b>
	Red	<b>NP14R</b>	-	S/S 430	<b>SS14L</b>
	White	<b>NP14W</b>	-	Steel, Almond	<b>SP14AL*</b>
	Steel, Gray				<b>SP14G*</b>
 2-Gang, 2-Blank, Strap Mount	Black	<b>NP24BK</b>	-	Aluminum	①
	Brown	<b>NP24</b>	-	Brass	①
	Gray	<b>NP24GY</b>	-	Brass Plated	①
	Ivory	<b>NP24I</b>	-	Chrome	①
	Office White	<b>NP24OW</b>	-	S/S 302/304	<b>SS24</b>
	Red	<b>NP24R</b>	-	S/S 430	<b>SS24L</b>
	White	<b>NP24W</b>	-	Steel, Almond	<b>SP24AL*</b>
	Steel, Gray				<b>SP24G*</b>
 3-Gang, 3-Blank, Strap Mount	Brown	<b>NP34</b>	-	Aluminum	①
	Ivory	<b>NP34I</b>	-	Brass	①
	White	<b>NP34W</b>	-	Brass Plated	①
				Chrome	①
 3-Gang, 3-Blank, Strap Mount				S/S 302/304	<b>SS34</b>
				S/S 430	-
				Steel, Almond	<b>SP34AL*</b>
 4-Gang, 4-Blank, Strap Mount	Brown	<b>NP44</b>	-	Aluminum	①
	Ivory	<b>NP44I</b>	-	Brass	①
	White	<b>NP44W</b>	-	Brass Plated	①
				Chrome	①
 4-Gang, 4-Blank, Strap Mount				S/S 302/304	<b>SS44</b>
				S/S 430	-







Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.




\*Powder coat paint finish.



**347 Volt Toggle Wallplates with 2.25" (57.2) Spacing Between Gangs, Stamped "347V"**




Description	Color	Nylon Catalog Number	Material	Metal Catalog Number
1-Gang, 1-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	<b>SS1C</b>
-	-	-	S/S 430	-
2-Gang, 2-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	<b>SS2C</b>
-	-	-	S/S 430	-
3-Gang, 3-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	<b>SS3C</b>
-	-	-	S/S 430	-
4-Gang, 4-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	<b>SS4C</b>
-	-	-	S/S 430	-
5-Gang, 5-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	<b>SS5C</b>
-	-	-	S/S 430	-
6-Gang, 6-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	<b>SS6C</b>
-	-	-	S/S 430	-

**347 Volt Decorator Wallplates**

Description	Color	Nylon Catalog Number	Material	Metal Catalog Number
1-Gang, 1-Decorator 	Black	<b>HPS1347BK</b>	Aluminum	-
	Gray	<b>HPS1347GY</b>	Brass	-
	Ivory	<b>HPS1347I</b>	Brass Plated	-
	White	<b>HPS1347W</b>	Chrome	-
	-	-	S/S 302/304	-
-	-	-	S/S 430	-
2-Gang, 2-Decorator 	Black	<b>HPS2347BK</b>	Aluminum	-
	Gray	<b>HPS2347GY</b>	Brass	-
	Ivory	<b>HPS2347I</b>	Brass Plated	-
	White	<b>HPS2347W</b>	Chrome	-
	-	-	S/S 302/304	-
-	-	-	S/S 430	-
3-Gang, 3-Decorator 	Ivory	<b>HPS3347I</b>	Aluminum	-
	White	<b>HPS3347W</b>	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	-
-	-	-	S/S 430	-









Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

**GFCI, Surge Receptacles and Style Line® Device Wallplates**

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number	
 <p>1-Gang, 1-Decorator</p>	Almond	<b>NP26AL</b>	<b>NPJ26AL</b>	Aluminum	①	
	Black	<b>NP26BK</b>	<b>NPJ26BK</b>	Brass	<b>SB26</b>	
	Blue	-	-	Brass Plated	<b>SBP26</b>	
	Brown	<b>NP26</b>	<b>NPJ26</b>	Chrome	<b>SCH26</b>	
	Gray	<b>NP26GY</b>	<b>NPJ26GY</b>	S/S 302/304	<b>SS26</b>	
	Ivory	<b>NP26I</b>	<b>NPJ26I</b>	S/S 430	<b>SS26L</b>	
	Light Almond	<b>NP26LA</b>	<b>NPJ26LA</b>	Steel, Almond	<b>PHPS1AL*</b>	
	Office White	<b>NP26OW</b>	<b>NPJ26OW</b>	Steel, Gray	<b>PHPS1G*</b>	
	Red	<b>NP26R</b>	<b>NPJ26R</b>			
	White	<b>NP26W</b>	<b>NPJ26W</b>			
	 <p>2-Gang, 2-Decorator</p>	Almond	<b>NP262AL</b>	<b>NPJ262AL</b>	Aluminum	①
Black		<b>NP262BK</b>	<b>NPJ262BK</b>	Brass	<b>SB262</b>	
Brown		<b>NP262</b>	<b>NPJ262</b>	Brass Plated	<b>SBP262</b>	
Gray		<b>NP262GY</b>	<b>NPJ262GY</b>	Chrome	<b>SCH262</b>	
Ivory		<b>NP262I</b>	<b>NPJ262I</b>	S/S 302/304	<b>SS262</b>	
Light Almond		<b>NP262LA</b>	<b>NPJ262LA</b>	S/S 430	<b>SS262L</b>	
Office White		<b>NP262OW</b>	<b>NPJ262OW</b>	Steel, Almond	<b>PHPS2AL*</b>	
Red		<b>NP262R</b>	<b>NPJ262R</b>	Steel, Gray	<b>PHPS2G*</b>	
White		<b>NP262W</b>	<b>NPJ262W</b>			
 <p>3-Gang, 3-Decorator</p>		Almond	<b>NP263AL</b>	<b>NPJ263AL</b>	Aluminum	①
		Black	<b>NP263BK</b>	<b>NPJ263BK</b>	Brass	①
	Brown	<b>NP263</b>	<b>NPJ263</b>	Brass Plated	<b>SBP263</b>	
	Gray	<b>NP263GY</b>	<b>NPJ263GY</b>	Chrome	①	
	Ivory	<b>NP263I</b>	<b>NPJ263I</b>	S/S 302/304	<b>SS263</b>	
	Light Almond	<b>NP263LA</b>	<b>NPJ263LA</b>	S/S 430	-	
	Office White	<b>NP263OW</b>	<b>NPJ263OW</b>	Steel, Almond	<b>PHPS3AL*</b>	
	Red	<b>NP263R</b>	<b>NPJ263R</b>			
	White	<b>NP263W</b>	<b>NPJ263W</b>			
	 <p>4-Gang, 4-Decorator</p>	Almond	<b>NP264AL</b>	<b>NPJ264AL</b>	Aluminum	①
		Black	<b>NP264BK</b>	<b>NPJ264BK</b>	Brass	①
Brown		<b>NP264</b>	<b>NPJ264</b>	Brass Plated	①	
Gray		<b>NP264GY</b>	<b>NPJ264GY</b>	Chrome	①	
Ivory		<b>NP264I</b>	<b>NPJ264I</b>	S/S 302/304	<b>SS264</b>	
Light Almond		<b>NP264LA</b>	<b>NPJ264LA</b>	S/S 430	-	
Office White		<b>NP264OW</b>	<b>NPJ264OW</b>	Steel, Almond	<b>PHPS4AL*</b>	
White		<b>NP264W</b>	<b>NPJ264W</b>			
 <p>5-Gang, 5-Decorator</p>		Black	<b>NP265BK</b>	-	Aluminum	①
		Brown	<b>NP265</b>	-	Brass	①
		Gray	<b>NP265GY</b>	-	Brass Plated	①
	Ivory	<b>NP265I</b>	-	Chrome	①	
	Light Almond	<b>NP265LA</b>	-	S/S 302/304	<b>SS265</b>	
	White	<b>NP265W</b>	-	S/S 430	-	
				Steel, Almond	<b>PHPS5AL*</b>	
 <p>6-Gang, 6-Decorator</p>	Black	<b>NP266BK</b>	-	Aluminum	①	
	Brown	<b>NP266</b>	-	Brass	①	
	Gray	<b>NP266GY</b>	-	Brass Plated	①	
	Ivory	<b>NP266I</b>	-	Chrome	①	
	Light Almond	<b>NP266LA</b>	-	S/S 302/304	<b>SS266</b>	
	White	<b>NP266W</b>	-	S/S 430	-	
			Steel, Almond	<b>PHPS6AL*</b>		

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.  
 ①Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.  
 \*Powder coat paint finish.

**Combination Wallplates, 2-Gang**

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 <p>2-Gang, 1-Toggle, 1-Duplex</p>	Almond	<b>NP18AL</b>	<b>NPJ18AL</b>	Aluminum	①
	Black	<b>NP18BK</b>	<b>NPJ18BK</b>	Brass	①
	Brown	<b>NP18</b>	<b>NPJ18</b>	Brass Plated	<b>SBP18</b>
	Gray	<b>NP18GY</b>	<b>NPJ18GY</b>	Chrome	<b>SCH18</b>
	Ivory	<b>NP18I</b>	<b>NPJ18I</b>	S/S 302/304	<b>SS18</b>
	Light Almond	<b>NP18LA</b>	<b>NPJ18LA</b>	S/S 430	<b>SS18L</b>
	Office White	<b>NP18OW</b>	<b>NPJ18OW</b>	Steel, Almond	<b>SP18AL*</b>
	Red	<b>NP18R</b>	<b>NPJ18R</b>	Steel, Gray	<b>SP18G*</b>
	White	<b>NP18W</b>	<b>NPJ18W</b>		
	 <p>2-Gang, 1-Duplex, 1-Decorator</p>	Almond	<b>NP826AL</b>	<b>NPJ826AL</b>	Aluminum
Black		<b>NP826BK</b>	<b>NPJ826BK</b>	Brass	<b>SB826</b>
Brown		<b>NP826</b>	<b>NPJ826</b>	Brass Plated	①
Gray		<b>NP826GY</b>	<b>NPJ826GY</b>	Chrome	①
Ivory		<b>NP826I</b>	<b>NPJ826I</b>	S/S 302/304	<b>SS826</b>
Light Almond		<b>NP826LA</b>	<b>NPJ826LA</b>	S/S 430	-
Office White		<b>NP826OW</b>	-		
White		<b>NP826W</b>	<b>NPJ826W</b>		
 <p>2-Gang, 1-Toggle, 1-Decorator</p>	Almond	<b>NP126AL</b>	<b>NPJ126AL</b>	Aluminum	①
	Black	<b>NP126BK</b>	<b>NPJ126BK</b>	Brass	<b>SB126</b>
	Brown	<b>NP126</b>	<b>NPJ126</b>	Brass Plated	<b>SBP126</b>
	Gray	<b>NP126GY</b>	<b>NPJ126GY</b>	Chrome	①
	Ivory	<b>NP126I</b>	<b>NPJ126I</b>	S/S 302/304	<b>SS126</b>
	Light Almond	<b>NP126LA</b>	<b>NPJ126LA</b>	S/S 430	<b>SS126L</b>
	White	<b>NP126W</b>	<b>NPJ126W</b>	Steel, Almond	<b>PJS126AL*</b>
				Steel, Gray	<b>PJS126G*</b>
 <p>2-Gang, 1-Duplex, 1-Telephone .406 in. (10.3) Hole Strap Mount</p>	Black	<b>NP128BK</b>	-	Aluminum	-
	Brown	<b>NP128</b>	-	Brass	-
	Gray	<b>NP128GY</b>	-	Brass Plated	-
	Ivory	<b>NP128I</b>	-	Chrome	-
	White	<b>NP128W</b>	-	S/S 302/304 S/S 430	- -
 <p>2-Gang, 1-Toggle, 1-Telephone .406 in. (10.3) Hole Strap Mount</p>	Black	<b>NP112BK</b>	-	Aluminum	-
	Brown	<b>NP112</b>	-	Brass	-
	Gray	<b>NP112GY</b>	-	Brass Plated	-
	Ivory	<b>NP112I</b>	-	Chrome	-
	Office White	<b>NP112OW</b>	-	S/S 302/304	-
	White	<b>NP112W</b>	-	S/S 430	-
 <p>2-Gang, 1-Decorator, 1-Telephone .406 in. (10.3) Hole Strap Mount</p>	Black	<b>NP1226BK</b>	-	Aluminum	-
	Brown	<b>NP1226</b>	-	Brass	-
	Gray	<b>NP1226GY</b>	-	Brass Plated	-
	Ivory	<b>NP1226I</b>	-	Chrome	-
	White	<b>NP1226W</b>	-	S/S 302/304 S/S 430	- -
 <p>2-Gang, 1-Single Receptacle 1.40 in. (35.6) Hole, 1-Duplex</p>	Almond	<b>NP78AL</b>	-	Aluminum	①
	Brown	<b>NP78</b>	-	Brass	①
	Gray	<b>NP78GY</b>	-	Brass Plated	①
	Ivory	<b>NP78I</b>	-	Chrome	①
	White	<b>NP78W</b>	-	S/S 302/304 S/S 430	<b>SS78</b> -
 <p>2-Gang, 1-Single Recept. 1.60 in. (40.6) Hole, 1-Duplex</p>	Almond	-	-	Aluminum	①
	Brown	-	-	Brass	①
	Ivory	-	-	Brass Plated	①
	White	-	-	Chrome	①
				S/S 302/304 S/S 430	<b>SS8720</b> -

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.  
 ①Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.  
 \*Powder coat paint finish.

**Combination Wallplates, 2-Gang**








Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 <p>2-Gang, 1-Toggle, 1-Single Receptacle 1.40 in. (35.6) Hole</p>	Black	<b>NP17BK</b>	-	Aluminum	⓪
	Brown	<b>NP17</b>	-	Brass	⓪
	Gray	<b>NP17GY</b>	-	Brass Plated	⓪
	Ivory	<b>NP17I</b>	-	Chrome	⓪
	White	<b>NP17W</b>	-	S/S 302/304	<b>SS17</b>
				S/S 430	-
 <p>2-Gang, 1-Toggle, 1-Blank, Box Mount</p>	Black	<b>NP113BK</b>	-	Aluminum	⓪
	Brown	<b>NP113</b>	<b>NPJ113</b>	Brass	⓪
	Gray	<b>NP113GY</b>	-	Brass Plated	⓪
	Ivory	<b>NP113I</b>	<b>NPJ113I</b>	Chrome	⓪
	Light Almond	<b>NP113LA</b>	-	S/S 302/304	<b>SS113</b>
White	<b>NP113W</b>	-	S/S 430	-	
 <p>2-Gang, 1-Toggle, 1-Blank, Strap Mount</p>	Black	-	-	Aluminum	⓪
	Brown	-	-	Brass	⓪
	Gray	-	-	Brass Plated	⓪
	Ivory	-	-	Chrome	⓪
	Light Almond	-	-	S/S 302/304	<b>SS114</b>
White	-	-	S/S 430	-	
 <p>2-Gang, 1-Blank, 1-Duplex, Box Mount</p>	Black	<b>NP138BK</b>	-	Aluminum	⓪
	Brown	<b>NP138</b>	<b>NPJ138</b>	Brass	⓪
	Gray	<b>NP138GY</b>	-	Brass Plated	⓪
	Ivory	<b>NP138I</b>	<b>NPJ138I</b>	Chrome	⓪
	Light Almond	<b>NP138LA</b>	-	S/S 302/304	<b>SS138</b>
White	<b>NP138W</b>	<b>NPJ138W</b>	S/S 430	-	
 <p>2-Gang, 1-Blank, 1-Duplex, Strap Mount</p>	Black	-	-	Aluminum	⓪
	Brown	-	-	Brass	⓪
	Gray	-	-	Brass Plated	⓪
	Ivory	-	-	Chrome	⓪
	Light Almond	-	-	S/S 302/304	<b>SS148</b>
White	-	-	S/S 430	-	
 <p>2-Gang, 1-Blank, 1-Decorator, Box Mount</p>	Black	<b>NP1326BK</b>	<b>NPJ1326BK</b>	Aluminum	⓪
	Brown	<b>NP1326</b>	<b>NPJ1326</b>	Brass	⓪
	Gray	<b>NP1326GY</b>	<b>NPJ1326GY</b>	Brass Plated	⓪
	Ivory	<b>NP1326I</b>	<b>NPJ1326I</b>	Chrome	⓪
	Light Almond	<b>NP1326LA</b>	<b>NPJ1326LA</b>	S/S 302/304	<b>SS1426*</b>
White	<b>NP1326W</b>	<b>NPJ1326W</b>	S/S 430	-	
 <p>2-Gang, 1-Telephone, .406 in. (10.3) Hole, 1-Blank, Strap Mount</p>	Black	<b>NP1214BK</b>	-	Aluminum	-
	Brown	<b>NP1214</b>	-	Brass	-
	Gray	<b>NP1214GY</b>	-	Brass Plated	-
	Ivory	<b>NP1214I</b>	-	Chrome	-
	White	<b>NP1214W</b>	-	S/S 302/304	-
				S/S 430	-
 <p>2-Gang, 1-Single Receptacle 1.40 in. (35.6) Hole 1-Blank, Strap Mount</p>	Black	<b>NP147BK</b>	-	Aluminum	⓪
	Brown	<b>NP147</b>	-	Brass	⓪
	Gray	<b>NP147GY</b>	-	Brass Plated	⓪
	Ivory	<b>NP147I</b>	-	Chrome	⓪
	White	<b>NP147W</b>	-	S/S 302/304	⓪
				S/S 430	-

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

⓪ Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.





\*Strap Mount.

**Combination Wallplates, 3-Gang**

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
3-Gang, 2-Toggle, 1-Duplex 	Brown	<b>NP28</b>	<b>NPJ28</b>	Aluminum	①
	Gray	<b>NP28GY</b>	-	Brass	①
	Ivory	<b>NP28I</b>	<b>NPJ28I</b>	Brass Plated	<b>SBP28</b>
	Light Almond	<b>NP28LA</b>	<b>NPJ28LA</b>	Chrome	①
	White	<b>NP28W</b>	<b>NPJ28W</b>	S/S 302/304	<b>SS28</b>
				S/S 430	-
				Steel, Almond	<b>SP28AL*</b>
				Steel, Gray	<b>SP28G*</b>
3-Gang, 1-Toggle, 2-Duplex 	Black	<b>NP182BK</b>	-	Aluminum	①
	Brown	<b>NP182</b>	-	Brass	①
	Gray	<b>NP182GY</b>	-	Brass Plated	①
	Ivory	<b>NP182I</b>	-	Chrome	①
	White	<b>NP182W</b>	-	S/S 302/304	<b>SS182</b>
				S/S 430	-
3-Gang, 2-Toggle, 1-Decorator 	Black	<b>NP226BK</b>	<b>NPJ226BK</b>	Aluminum	①
	Brown	<b>NP226</b>	<b>NPJ226</b>	Brass	①
	Gray	<b>NP226GY</b>	<b>NPJ226GY</b>	Brass Plated	①
	Ivory	<b>NP226I</b>	<b>NPJ226I</b>	Chrome	①
	Light Almond	<b>NP226LA</b>	<b>NPJ226LA</b>	S/S 302/304	<b>SS226</b>
	White	<b>NP226W</b>	<b>NPJ226W</b>	S/S 430	-
			Steel, Gray	<b>PJS226G*</b>	
3-Gang, 1-Toggle, 2-Decorator 	Black	<b>NP1262BK</b>	-	Aluminum	①
	Brown	<b>NP1262</b>	-	Brass	①
	Gray	<b>NP1262GY</b>	-	Brass Plated	①
	Ivory	<b>NP1262I</b>	-	Chrome	①
	Light Almond	<b>NP1262LA</b>	-	S/S 302/304	①
	White	<b>NP1262W</b>	-	S/S 430	-
3-Gang, 2-Duplex, 1-Blank 	Black	-	-	Aluminum	①
	Brown	-	-	Brass	①
	Gray	-	-	Brass Plated	①
	Ivory	-	-	Chrome	①
	Light Almond	-	-	S/S 302/304	<b>SS211</b>
	White	-	-	S/S 430	-
3-Gang, 1-Duplex, 1-Blank, 1-Duplex 	Black	-	-	Aluminum	①
	Brown	-	-	Brass	①
	Gray	-	-	Brass Plated	①
	Ivory	-	-	Chrome	①
	Light Almond	-	-	S/S 302/304	<b>SS8147</b>
	White	-	-	S/S 430	-
3-Gang, 2-Toggle, 1-Blank 	Black	-	-	Aluminum	①
	Brown	-	-	Brass	①
	Gray	-	-	Brass Plated	①
	Ivory	-	-	Chrome	①
	Light Almond	-	-	S/S 302/304	<b>SS213</b>
	White	-	-	S/S 430	-

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.  
 ①Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.  
 \*Powder coat paint finish.







**Combination Plates, 4- and 5-Gang**

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
4-Gang, 3-Toggle, 1-Duplex 	Brown	<b>NP38</b>	-	Aluminum	①
	Ivory	<b>NP38I</b>	-	Brass	①
	Light Almond	<b>NP38LA</b>	-	Brass Plated	①
	White	<b>NP38W</b>	-	Chrome	①
				S/S 302/304	<b>SS38</b>
			S/S 430	-	
4-Gang, 3-Toggle, 1-Decorator 	Black	<b>NP326BK</b>	-	Aluminum	①
	Brown	<b>NP326</b>	-	Brass	①
	Gray	<b>NP326GY</b>	-	Brass Plated	①
	Ivory	<b>NP326I</b>	-	Chrome	①
	Light Almond	<b>NP326LA</b>	-	S/S 302/304	<b>SS326</b>
	White	<b>NP326W</b>	-	S/S 430	-
4-Gang, 2-Toggle, 2-Decorator 	Black	<b>NP2262BK</b>	-	Aluminum	①
	Brown	<b>NP2262</b>	-	Brass	①
	Gray	<b>NP2262GY</b>	-	Brass Plated	①
	Ivory	<b>NP2262I</b>	-	Chrome	①
	Light Almond	<b>NP2262LA</b>	-	S/S 302/304	①
	White	<b>NP2262W</b>	-	S/S 430	-
5-Gang, 4-Toggle, 1-Duplex 	Brown	<b>NP48</b>	-	Aluminum	①
	Ivory	<b>NP48I</b>	-	Brass	①
	White	<b>NP48W</b>	-	Brass Plated	①
				Chrome	①
				S/S 302/304	①
			S/S 430	-	

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.













① Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.

**Telephone and Coaxial Outlet Plates**


Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 <p>1-Gang, 1-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Box Mount</p>	Almond	<b>NP11AL</b>	<b>NPJ11AL</b>	Aluminum	①
	Black	<b>NP11BK</b>	-	Brass	①
	Brown	<b>NP11</b>	<b>NPJ11</b>	Brass Plated	①
	Gray	<b>NP11GY</b>	-	Chrome	①
	Ivory	<b>NP11I</b>	<b>NPJ11I</b>	S/S 302/304	<b>SS11*</b>
	Light Almond	<b>NP11LA</b>	<b>NPJ11LA</b>	S/S 430	<b>SS11L*</b>
	Red	<b>NP11R</b>	-		
	White	<b>NP11W</b>	<b>NPJ11W</b>		
 <p>1-Gang, 1-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Strap Mount</p>	Almond	<b>NP12AL</b>	-	Aluminum	①
	Black	<b>NP12BK</b>	-	Brass	<b>SB12*</b>
	Brown	<b>NP12</b>	-	Brass Plated	<b>SBP12*</b>
	Gray	<b>NP12GY</b>	-	Chrome	<b>SCH12*</b>
	Ivory	<b>NP12I</b>	-	S/S 302/304	<b>SS12*</b>
	White	<b>NP12W</b>	-	S/S 430	<b>SS12L*</b>
 <p>1-Gang, 1-Tel .625 in. (15.9) Hole, Box Mount</p>	Almond	<b>NP737AL</b>	-	Aluminum	-
	Brown	<b>NP737</b>	-	Brass	-
	Ivory	<b>NP737I</b>	-	Brass Plated	-
	White	<b>NP737W</b>	-	Chrome	-
				S/S 302/304	-
 <p>1-Gang, 1-Tel .625 in. (15.9) Hole, Strap Mount</p>	Brown	<b>NP730</b>	-	Aluminum	-
	Ivory	<b>NP730I</b>	-	Brass	-
	White	<b>NP730W</b>	-	Brass Plated	-
				Chrome	-
				S/S 302/304	-
 <p>1-Gang, 1-Tel .380 in. (9.7) Hole, Box Mount or Strap Mount</p>	Almond	-	-	Aluminum	①
	Brown	-	-	Brass	①
	Ivory	-	-	Brass Plated	①
	White	-	-	Chrome	①
				S/S 302/304	<b>SS739</b>
				S/S 302/304, Strap Mount	<b>SS738</b>
 <p>2-Gang, 2-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Box Mount</p>	Black	<b>NP21BK</b>	-	Aluminum	①
	Brown	<b>NP21</b>	-	Brass	①
	Gray	<b>NP21GY</b>	-	Brass Plated	①
	Ivory	<b>NP21I</b>	-	Chrome	①
	White	<b>NP21W</b>	-	S/S 302/304, Strap Mount	<b>SS22*</b>
				S/S 430	-
 <p>2-Gang, 1-Tel .640 in. (16.3) Hole, Box Mount</p>	Almond	-	-	Aluminum	-
	Brown	-	-	Brass	-
	Ivory	-	-	Brass Plated	-
	White	-	-	Chrome	-
				S/S 302/304	<b>SS741*</b>
			S/S 430	-	

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.  
 ① Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.  
 \*.50" (12.7) I.D. nylon bushing provided.

**Jumbo, Smooth, Stainless Steel Type 302/304 Wallplates**

Configuration	Catalog Number	Configuration	Catalog Number
1-Gang, 1-Toggle 	<b>SSJ1</b>	1-Gang, 1-Single Receptacle for 2.09–2.13 in. (53.1–54.1) Dia. Face 	<b>SSJ723</b>
2-Gang, 2-Toggle 	<b>SSJ2</b>	1-Gang, 1-Blank, Box Mount 	<b>SSJ13</b>
1-Gang, 1-Duplex 	<b>SSJ8</b>	1-Gang, 1-Telephone Opening, .640 in. (16.3) Box Mount 	<b>SSJ11*</b>
2-Gang, 2-Duplex 	<b>SSJ82</b>	2-Gang, 1-Toggle, 1-Duplex 	<b>SSJ18</b>
1-Gang, 1-Decorator 	<b>SSJ26</b>	2-Gang, 1-Toggle, 1-Decorator 	<b>SSJ126</b>
2-Gang, 2-Decorator 	<b>SSJ262</b>		
1-Gang, 1-Single Receptacle for 1.36–1.39 in. (34.5–35.3) Dia. Face 	<b>SSJ7</b>		

Note: \*.50 in. (12.7) I.D. nylon bushing provided.  
 Specifications are subject to change without notice.






**Jumbo Wallplate**

Oversize dimensions (see page N-31 for more details).  
 1-Gang, 5.25 in. x 3.50 in. (133.4 x 88.9).  
 2-Gang, 5.25 in. x 5.31 in. (133.4 x 134.9).  
 3-Gang, 5.25 in. x 7.12 in. (133.4 x 180.8).

Dimensions in Inches (mm)



**Pre-Marked "EMERGENCY" Wallplates**

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, 1-Duplex, paint filled white lettering 	Red	-	<b>NPJ8RMEV</b>	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - <b>SS8MEV</b> -
1-Gang, 1-Toggle, paint filled white lettering 	Red	-	<b>NPJ1RME</b>	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - <b>SS1ME</b> -
2-Gang, 2 Duplex, paint filled red lettering 	-	-	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - <b>SS82MEV</b> -

Note: See page N-31 for mid-size plate dimensions.  
All lettering .25 in. (6.3) high.



**Stainless Steel Barrel Key Switch Wallplates**

Description	1-Gang, with on/off markings	1-Gang, with position markings	2-Gang, with on/off markings	2-Gang, with position markings
Stainless steel, 302/304, smooth.	<b>SS12RKL</b>	<b>SS12RKLM</b>	<b>SS22RKL</b>	<b>SS22RKLM</b>
				


Note: See page D-6 for barrel key switch selection.

**Single Count Screws and Accessories**

Description	Catalog Number
Stainless steel screw, standard slot, .38 in. (9.7) long.	<b>HBL7341SS</b>
Security spanner head screws, 6-32 thread, 100 count.	<b>HBL7342RKL</b>
Screwdriver with spanner head security bit.	<b>HBL7372RKL</b>







**HBL7342RKL**






**HBL7372RKL**


**Pre-Marked “ISOLATED GROUND” Wallplates**

Description	Color	Nylon Standard	Nylon No Marking	Material	Metal Catalog Number
1-Gang, 1-Duplex, paint filled black 	Orange	<b>NP8OIG</b>	<b>NP8OR</b>	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
1-Gang, 1-Decorator, paint filled black 	Orange	<b>NP26OIG</b>	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
1-Gang, 1-Single Recept. 1.40 in. (35.6) Hole for 1.36–1.39 in. (34.5–35.3) Dia. face, paint filled black 	Orange	<b>NP7OIG</b>	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
1-Gang, 1-Single Recept. 1.60 in. (40.6) Hole for 20 and 30A Twist-Lock® with 1.55–1.58 in. (39.4–40.1) Dia. face, paint filled black 	Orange	<b>NP72OIG</b>	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -

**Pre-Marked “COMPUTER ONLY” Wallplates**

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, 1-Duplex, paint filled black 	Orange Ivory	- -	<b>NPJ8CO</b> <b>NPJ8C</b>	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
2-Gang, 2-Duplex, paint filled black 	Orange	-	<b>NPJ82CO</b>	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
1-Gang, 1-Decorator, paint filled black 	Blue Ivory	- -	<b>NPJ26CBL</b> <b>NPJ26C</b>	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -

**Louver Plate, 1-Gang, Box Mount**

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, Vertical Mounted Louver 	- - - -	- - - -	- - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	⓪ <b>SB771</b> <b>SBP771</b> ⓪ <b>SS771</b> -

Note: \*See page N-31 for mid-size plate dimensions.

⓪ Available as a custom wallplate, see pages N-32 to N-36. Consult custom wallplates section for additional openings and combinations.

## 1-Gang, White

Description	Catalog Number
1-Toggle switch	<b>SWP1</b>
1-Duplex receptacle	<b>SWP8</b>
1-GFCI/Style Line® opening	<b>SWP26</b>
1-Telephone or TV opening .640 in. (16.3)	<b>SWP12</b>
1-Blank	<b>SWP13</b>



**SWP1**



**SWP8**

## 2-Gang, White

Description	Catalog Number
2-Toggle switches	<b>SWP2</b>
2-Duplex receptacles	<b>SWP82</b>
1-Toggle switch, 1-Duplex receptacle	<b>SWP18</b>
2-GFCI/Style Line® openings	<b>SWP262</b>
1-Toggle switch, 1-GFCI/Style Line® opening	<b>SWP126</b>
1-Duplex receptacle, 1-Telephone or TV	<b>SWP812</b>
1-Duplex receptacle, 1-Blank	<b>SWP813</b>
2-Blank	<b>SWP23</b>



**SWP82**




**SWP18**

## 3-Gang, White

Description	Catalog Number
2-Toggle switches, 1-Duplex receptacle	<b>SWP28</b>



**SWP28**



## Dimensions

	A	B	C	D	E	F	G	H
1-Gang	3.77"	5.52"	.55"	3.37"	5.13"	1.00"	4.63"	2.88"
in. (mm)	(95.8)	(140.2)	(14.0)	(85.6)	(130.3)	(25.4)	(117.6)	(73.2)
2-Gang	5.52"	5.52"	.55"	5.13"	5.13"	1.00"	4.63"	4.63"
in. (mm)	(140.2)	(140.2)	(14.0)	(130.3)	(130.3)	(25.4)	(117.6)	(117.6)
3-Gang	7.39"	5.52"	.55"	7.00"	5.13"	1.00"	4.63"	6.50"
in. (mm)	(187.71)	(140.21)	(14.0)	(177.8)	(130.3)	(25.4)	(117.6)	(165.1)

## Specifications

Tamper resistant wallplate 1-gang duplex receptacle shall be of the following construction:

Cover plate: One piece #14 cold rolled zinc plated steel. Plate shall have a five stage baked white polyester powder enamel finish. Gloss: 85%; reflectance: 93%; hardness minimum: 2H and pass 600 hour salt spray test.

Back plate: #10 cold rolled galvanized steel. Plate assembly shall use four (4) #8-32 X 1/2 inch stainless steel T-15 TORX® head screws with center pin reject. Plate must be UL listed to UL 514D and comply with the NEC®.

TORX® is a registered trademark of Textron Inc.  
NEC® is a registered trademark of the The National Electrical Code.

Dimensions in Inches (mm)



**HBL96067**  
Shown with receptacle  
(sold separately)



**HBL6187**  
Shown with receptacle  
and back box  
(sold separately)

### Brass Locking Cover Plate

Description	Catalog Number
Locking cover plate for single 15 and 20A straight blade receptacles and 15A Twist-Lock® receptacles. Straight cylinder type lock. All cylinder locks keyed alike.	<b>HBL96067</b>

### Weather Shield Plate

Description	Catalog Number
20° angle plate for duplex receptacles.	<b>HBL6187</b>

### Catalog Number of Receptacles in Groups A through E below

Group A		Group B			Group C	Group D	Group E
Boss diameter 1.36" to 1.39" (34.5 to 35.3)		Boss diameter 1.55" to 1.58" (39.4 to 40.1)			Boss diameter 1.68" to 1.72" (42.7 to 43.7)	Boss diameter 2.09" to 2.13" (53.1 to 54.1)	Boss diameter 2.28" to 2.44" (57.9 to 62.0)
<b>HBL23000HG</b>	<b>HBL5661</b>	<b>HBL23CM10</b>	<b>HBL2530</b>	<b>HBL2770</b>	<b>HBL45105</b>	<b>HBL7962</b>	<b>HBL7301A</b>
<b>HBL23030</b>	<b>HBL6810</b>	<b>HBL2310</b>	<b>HBL26CM10</b>	<b>HBL2810</b>	<b>HBL45205</b>	<b>HBL9350</b>	<b>HBL8330A</b>
<b>HBL4560</b>	<b>HBL7210B</b>	<b>HBL2320</b>	<b>HBL2610</b>	<b>HBL2820</b>	<b>HBL45305</b>	<b>HBL9308</b>	<b>HBL8350A</b>
<b>HBL4710</b>	<b>HBL7250</b>	<b>HBL2330</b>	<b>HBL2620</b>	<b>HBL2830</b>	<b>HBL45905</b>	<b>HBL9315</b>	<b>HBL8430A</b>
<b>HBL4760</b>	<b>HBL7310B</b>	<b>HBL2340</b>	<b>HBL2630</b>	<b>HBL3330</b>		<b>HBL9330</b>	<b>HBL8450A</b>
<b>HBL5251</b>	<b>HBL7310BG</b>	<b>HBL2410</b>	<b>HBL2640</b>	<b>HBL3330G</b>		<b>HBL9360•</b>	<b>HBL8460A</b>
<b>HBL52CM61</b>	<b>HBL7535</b>	<b>HBL2420</b>	<b>HBL2650</b>	<b>HBL3430</b>		<b>HBL9365•</b>	<b>HBL9430A</b>
<b>HBL5261</b>	<b>HBL7582</b>	<b>HBL2430</b>	<b>HBL2710</b>	<b>HBL3430G</b>		<b>HBL9367•</b>	<b>HBL9450A</b>
<b>HBL53CM61</b>	<b>HBL8210</b>	<b>HBL2440</b>	<b>HBL2720</b>	<b>HBL3520</b>			<b>HBL9460A</b>
<b>HBL5361</b>	<b>HBL8310</b>	<b>HBL2450</b>	<b>HBL2730</b>	<b>HBL7410B</b>			
<b>HBL5461</b>	<b>HBL8410</b>	<b>HBL2460</b>	<b>HBL2740</b>	<b>HBL7410BG</b>			
<b>HBL5552B</b>	<b>HBL8420</b>	<b>HBL2510</b>	<b>HBL2750</b>				
		<b>HBL2520</b>	<b>HBL2760</b>				

Note: •50A 2P 3W.

### Wallplates for Single Receptacles

Description	Group A		Group B		Group C		Group D		Group E
	Boss diameter 1.36" to 1.39" (34.5 to 35.3)		Boss diameter 1.55" to 1.58" (39.4 to 40.1)		Boss diameter 1.68" to 1.72" (42.7 to 43.7)		Boss diameter 2.09" to 2.13" (53.1 to 54.1)		Boss diameter 2.28" to 2.44" (57.9 to 62.0)
	1-Gang	2-Gang	1-Gang	2-Gang	1-Gang	2-Gang	1-Gang	2-Gang	2-Gang
Smooth nylon, brown.	<b>NP7*</b>	-	<b>NP720*</b>	-	-	-	<b>NP724*</b>	<b>NP703*</b>	-
Cast aluminum.	<b>HBL7320</b>	-	<b>HBL7320</b>	-	<b>HBL3394</b>	-	<b>HBL9419</b>	-	-
Stainless steel, 302/304, smooth.	<b>SS7**</b>	<b>SS72</b>	<b>SS720</b>	-	<b>SS725</b>	-	<b>SS723</b>	<b>SS703</b>	<b>SS701</b>

Note: See pages N-6 and N-7 for complete plate descriptions.

\*Catalog number indicated is Brown, add with the following to designate color: "AL" (Almond), "BK" (Black), "GY" (Gray), "I" (Ivory), and "W" (white).

\*\*Catalog number indicated is Stainless Steel, replace "SS" with the following prefix to designate material: "SA" for Anodized Aluminum, "SB" for Solid Brass.

### Weatherproof Lift Covers for WDL "Closed" and WDL "Open", Wet Locations, 1-Gang

Description	Group A	Group B	Group C	Group D	50A Twist-Lock® Receptacles	30A 4W Hubbelllock® Receptacles
	Boss diameter 1.36" to 1.39" (34.5 to 35.3)	Boss diameter 1.55" to 1.58" (39.4 to 40.1)	Boss diameter 1.68" to 1.72" (42.7 to 43.7)	Boss diameter 2.09" to 2.13" (53.1 to 54.1)		
Thermoplastic, with cover "open", gray.	<b>HBL7423WO</b>	<b>HBL7425WOA</b>	<b>HBL7424WO</b>	-	<b>HBL7774WO▲</b>	-
Thermoplastic, with cover "open", yellow.	<b>HBL74CM23WO</b>	<b>HBL74CM25WOA</b>	<b>HBL74CM24WO</b>	-	<b>HBL77CM74WO▲</b>	-
Cast aluminum, with cover "closed".	<b>HBL7420</b>	<b>HBL7420</b>	<b>HBL3393</b>	<b>HBL9420</b> <b>HBL9425•</b>	<b>HBL7770</b>	<b>HBL20405†</b> <b>HBL20446†</b>

Note: •50A 2P 3W.

▲The "CS" versions of 50A Twist-Lock® receptacles will only fit these thermoplastic plates.

†HBL20446 plate painted red for use with HBL20443 only. HBL20405 plate is for use with HBL20403 only. See page B-65 for devices.

**IP44**  
 SUITABILITY

**For Receptacles with Face Diameters of 2.28–2.44 in. (57.9–62.0)**

Description	Catalog Number
Thermoplastic, 2-gang, wet and damp locations with cover “closed”, gray.	<b>HBL7777A<sup>▲</sup></b>
Thermoplastic, 2-gang, wet and damp locations with cover “closed”, yellow.	<b>HBL77CM77A<sup>▲</sup></b>
Thermoplastic, 2-gang, wet and damp locations with cover “closed”, gray.	<b>HBL7777<sup>▽</sup></b>



**HBL7777A**

**For Receptacles with Face Diameters of 2.09–2.13 in. (53.1–54.1)**

Description	Catalog Number
Cast aluminum, wet locations only when cover “closed” and damp locations.	<b>HBL9420</b>
Cast aluminum, no lift cover. NOT weatherproof.	<b>HBL9419</b>



**HBL9420**

**For 50A Twist-Lock<sup>®</sup> Single Receptacles**

Description	Catalog Number
Thermoplastic, wet and damp locations with cover “open”, gray.	<b>HBL7774WO*</b>
Thermoplastic, wet and damp locations with cover “open”, yellow.	<b>HBL77CM74WO*</b>
Cast aluminum, wet locations only when cover “closed” and damp locations.	<b>HBL7770</b>
Galvanized Steel, fits 4" square or 2-gang box.	<b>HBL50SC**</b>
Stainless steel, single gang, wallplate. NOT weatherproof.	<b>SS750<sup>▲</sup></b>



**HBL7774WO**

**For 30A, 4 Wire Hubbellock<sup>®</sup> Receptacles**

Description	Catalog Number
Thermoplastic, wet and damp locations with cover “open”, gray.	<b>HBL7428WOG*</b>
Thermoplastic, wet and damp locations with cover “open”, yellow.	<b>HBL7428WOY*</b>
Thermoplastic, wet and damp locations with cover “open”, red.	<b>HBL7428WOR*</b>
Cast aluminum, wet locations only when cover “closed” and damp locations, lift cover plate.	<b>HBL20405</b>
Cast aluminum, wet locations only when cover “closed” and damp locations, red finish.	<b>HBL20446</b>
Cast aluminum, no lift cover. NOT weatherproof.	<b>HBL20406</b>



**HBL7770**

Note: <sup>▲</sup>Will fit FS/FD boxes having plate mounting holes on 3.25 in. x 3.75 in. (82.6 x 95.3) centers.  
<sup>▽</sup>Will only fit old style porcelain face devices.  
 \*The “CS” versions of 50A Twist-Lock<sup>®</sup> will only fit these plates.  
 \*\*IP20 Suitability.

**Weatherproof Covers for Single Receptacles for Use on FS/FD Boxes**

Note: All weatherproof plates are UL Listed for WET LOCATIONS WITH COVER CLOSED, for intermittent use in wet locations or use in damp locations. Those with suffix “WO” are listed for WET LOCATIONS with cover open in continuous use. All plates are gasketed and self-closing.




**HBL20405**

**Accessories**

Description	Catalog Number
Sub-plate for mounting and weatherproofing flanged devices with mounting centers of 1.76", 1.94" or 2.13" such as HBL7556, HBL4716, etc. when used with a HBL7420 or HBL7425WOA type weatherproof plate.	<b>7452<sup>•</sup></b>
Adapter plate for mounting HBL7423WO, HBL7424WO, HBL7425WOA or HBL7420 plates to standard boxes.	<b>HBL7349<sup>•</sup></b>

Note: <sup>•</sup>Not UL Listed.



**HBL7349**

Dimensions in Inches (mm)



HBL7423WO



HBL7425WOA



HBL7420



HBL7320



HBL7424WO



HBL3393

## For Receptacles with Face Diameters of 1.36–1.39 in. (34.5–35.3)

**IP44**  
SUITABILITY

Description	Catalog Number
Thermoplastic, wet and damp locations with cover "open", gray.	<b>HBL7423WO</b>
Thermoplastic, wet and damp locations with cover "open", yellow.	<b>HBL74CM23WO</b>
Cast aluminum, wet location only when cover "closed" and damp locations.	<b>HBL7420</b>
Cast aluminum, no lift cover, NOT weatherproof.	<b>HBL7320*</b>

## For Switches and Receptacles with Face Diameters of 1.55–1.58 in. (39.4–40.1)

Description	Catalog Number
Thermoplastic, wet and damp locations with cover "open", gray.	<b>HBL7425WOA</b>
Thermoplastic, wet and damp locations with cover "open", yellow.	<b>HBL74CM25WOA</b>
Thermoplastic, wet and damp locations with cover "open", white.	<b>HBL74CM25WOAW</b>
Cast aluminum, wet and damp locations with cover "closed."	<b>HBL7420*</b>
Cast aluminum, no lift cover, NOT weatherproof.	<b>HBL7320*</b>
Thermoplastic, wet and damp locations with cover "open", gray.	<b>HBL7428WOG**</b>
Thermoplastic, wet and damp locations with cover "open", yellow.	<b>HBL7428WOY**</b>
Thermoplastic, wet and damp locations with cover "open", red.	<b>HBL7428WOR**</b>

## For Receptacles with Face Diameters of 1.68–1.72 in. (42.7–43.7)

Description	Catalog Number
Thermoplastic, wet and damp locations with cover "open", gray.	<b>HBL7424WO</b>
Thermoplastic, wet and damp locations with cover "open", yellow.	<b>HBL74CM24WO</b>
Cast aluminum, wet location only when cover "closed" and damp locations.	<b>HBL3393</b>
Cast aluminum, no lift cover, NOT weatherproof.	<b>HBL3394*</b>

Note: \*Cast aluminum lift cover with fibershield for standard toggle and PresSwitch® Switches.

\*\*Features two #6-32 threaded inserts to back mount device to cover.

\*IP20 SUITABILITY.

All weatherproof lift cover plates on this page are UL Listed as "WDL Closed" for use in wet locations with cover closed and in damp locations.

## Weatherproof Covers for Single Receptacles on FS/FD Boxes


Note: All weatherproof plates are UL Listed for WET LOCATIONS WITH COVER CLOSED for intermittent use in wet locations or use in damp locations. Those with suffix "WO" are listed for WET LOCATIONS with cover open in continuous use. All plates are gasketed and self-closing.

### 2011 National Electrical Code (NEC®)

#### 406.9 Receptacles in Damp or Wet Locations.

(A) Damp Locations. A receptacle installed outdoors in a location protected from the weather or in other damp locations shall have an enclosure for the receptacle that is weatherproof when the receptacle is covered (attachment plug cap not inserted and receptacle covers closed). An installation suitable for wet locations shall also be considered suitable for damp locations. A receptacle shall be considered to be in a location protected from the weather where located under roofed open porches, canopies, marquees, and the like, and will not be subjected to a beating rain or water runoff. All 15 and 20A, 125 and 250V nonlocking receptacles shall be listed weather-resistant type. FPN: The types of receptacles covered by this requirement are identified as 5-15, 5-20, 6-15 and 6-20 in ANSI/NEMA WD 6-2002, National Electrical Manufacturers Association Standard for Dimensions of Attachment Plugs and Receptacles.

(B) Wet Locations. 15 and 20A, 125 and 250V receptacles installed in a wet location shall have an enclosure that is weatherproof whether or not the attachment plug cap is inserted. For other one or two family dwellings, an outlet box hood installed for this purpose shall be listed, and where installed on an enclosure supported from grade as described in 314.23(B) or as described in 314.23(F) shall be identified as "extra-duty". All 15 and 20A, 125 and 250V nonlocking type receptacles shall be listed weather resistant type.



Typical Plate, 1-Gang

NEC® is a registered trademark of the The National Electrical Code.

## Weatherproof Thermoplastic Cover For Flanged Inlets and Flanged Receptacles

**IP44**  
SUITABILITY

Description	Catalog Number
For use with 15 and 20A, 2 pole, 2 wire and 2 pole, 3 wire Insulgrip® flanged inlets and flanged receptacles below.	<b>WP1</b>

### Straight Blade, 2 pole, 3 wire Flanged Inlets


### Flanged Receptacles

	<b>HBL5278C</b>		<b>HBL5279C</b>
	<b>HBL5378C</b>		<b>HBL5379C</b>
	<b>HBL5478C</b>		<b>HBL5479C</b>
	<b>HBL5678C</b>		<b>HBL5679C</b>



### Twist-Lock®, 2 pole, 2 wire and 2 pole, 3 wire Flanged Inlets

### Flanged Receptacles

	<b>HBL8815C</b>		<b>HBL8809C</b>
	<b>HBL7524C</b>		<b>HBL7526C</b>
	<b>HBL4716C</b>		<b>HBL4715C</b>
	<b>HBL4586C</b>		<b>HBL4585C</b>
	<b>HBL4786C</b>		<b>HBL4785C</b>



## Weatherproof Thermoplastic Cover For Flanged Inlets and Flanged Receptacles

Description	Catalog Number
For 20 and 30A, 3, 4, and 5 wire Insulgrip flanged inlets and flanged receptacles below.	<b>WP2</b>

### Twist-Lock®, 2 pole, 3 wire; 3 pole, 4 wire; 4 pole, 4 wire; 4 pole, 5 wire Flanged Inlets

	<b>HBL2315</b>	<b>HBL2445</b>	<b>HBL2635</b>	<b>HBL2765</b>
	<b>HBL2325</b>	<b>HBL2455</b>	<b>HBL2645</b>	<b>HBL2775</b>
	<b>HBL2335</b>	<b>HBL2465</b>	<b>HBL2655</b>	<b>HBL2815</b>
	<b>HBL2345</b>	<b>HBL2515</b>	<b>HBL2715</b>	<b>HBL2825</b>
	<b>HBL2355</b>	<b>HBL2525</b>	<b>HBL2725</b>	<b>HBL2835</b>
	<b>HBL2415</b>	<b>HBL2535</b>	<b>HBL2735</b>	<b>HBL3325C</b>
	<b>HBL2425</b>	<b>HBL2615</b>	<b>HBL2745</b>	<b>HBL3334C</b>
	<b>HBL2435</b>	<b>HBL2625</b>	<b>HBL2755</b>	<b>HBL7408C</b>



### Flanged Receptacles


	<b>HBL2316</b>	<b>HBL2446</b>	<b>HBL2636</b>	<b>HBL2766</b>
	<b>HBL2326</b>	<b>HBL2456</b>	<b>HBL2646</b>	<b>HBL2776</b>
	<b>HBL2336</b>	<b>HBL2466</b>	<b>HBL2656</b>	<b>HBL2816</b>
	<b>HBL2346</b>	<b>HBL2516</b>	<b>HBL2716</b>	<b>HBL2826</b>
	<b>HBL2356</b>	<b>HBL2526</b>	<b>HBL2726</b>	<b>HBL2836</b>
	<b>HBL2416</b>	<b>HBL2536</b>	<b>HBL2736</b>	<b>HBL3326C</b>
	<b>HBL2426</b>	<b>HBL2616</b>	<b>HBL2746</b>	<b>HBL3335C</b>
	<b>HBL2436</b>	<b>HBL2626</b>	<b>HBL2756</b>	<b>HBL7409C</b>



## Weatherproof Thermoplastic Cover For Flanged Inlets 50 Amp CS Series

Description	Catalog Number
For 50A, 2 pole, 3 wire and 3 pole, 4 wire flanged inlets below.	<b>HBL7780</b>

### Twist-Lock®, 2 pole, 3 wire; 3 pole, 4 wire Flanged Inlets

	<b>CS6377</b>	<b>CS6375</b>	<b>HBL3777</b>
	<b>CS8275</b>	<b>CS8375</b>	<b>HBL3775</b>
	<b>CS8475</b>	<b>CS8175</b>	<b>HBL7958</b>





HBL1795

**Weatherproof Plates**

Description	Catalog Number
Clear bubble plate, silicone rubber for use with all general purpose AC toggle and PresSwitch® Switches. Fits both FS/FD and standard boxes.	<b>HBL1795</b>

**IP44**  
SUITABILITY



HBL1750

**Weatherproof Plates**

Description	Catalog Number
Gray neoprene PresSwitch® Plate. Fits FS/FD and standard boxes.	<b>HBL1750*</b>
Same as above except yellow.	<b>HBL17CM50*</b>

Note: \*Not UL Listed.



HBL1785

**Weatherproof Plates**

Description	Catalog Number
Gray neoprene PresSwitch® Plate with 125V red pilot light. Fits only FS/FD boxes.	<b>HBL1785*</b>
Same as above except yellow.	<b>HBL17CM85*</b>

Note: \*Not UL Listed.



HBL7420

**Weatherproof Covers**

Description	Catalog Number
Cast aluminum lift cover plate with fiber shield. For standard toggle and PresSwitch® Switches. Fits only FS/FD boxes.	<b>HBL7420</b>

**Brass Locking Covers Attachment for Switches**

Description	Catalog Number
Straight keying (all locks alike) appropriate for most applications. Straight cylinder type lock, each HBL96061 ordered operates on the same key—all locks are keyed alike.	<b>HBL96061*</b>
Same as above except in dull chrome finish to match stainless steel plates.	<b>HBL96061DCH*</b>
Straight keying (individual). Straight cylinder type lock, each HBL96062 ordered operates on a different key. All locks are keyed differently and individually. This type cannot be master keyed.	<b>HBL96062*</b>

Note: \*Not UL Listed.



HBL96061  
shown with wallplate and  
switch (sold separately)

**Locking Device**

Description	Catalog Number
Locking device for weatherproof covers.	<b>HBLWLC</b>



HBLWLC



**IP44**  
 SUITABILITY

### Duplex Covers For Vertical Mounting

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Thermoplastic, gray, for FS/FD box mounting.	4.56" x 2.89" x 1.08" (115.8 x 73.4 x 27.4)		<b>HBL5221</b>
Thermoplastic, yellow, for FS/FD box mounting.	4.56" x 2.89" x 1.08" (115.8 x 73.4 x 27.4)		<b>HBL52CM21</b>
Thermoplastic, white, for FS/FD box mounting.	4.56" x 2.89" x 1.08" (115.8 x 73.4 x 27.4)		<b>HBL52CM21W</b>
Thermoplastic, gray, for device mounting.	4.56" x 2.89" x 1.08" (115.8 x 73.4 x 27.4)		<b>HBL5222</b>
Thermoplastic, yellow, for device mounting.	4.56" x 2.89" x 1.08" (115.8 x 73.4 x 27.4)		<b>HBL52CM22</b>
Die cast aluminum, gray, commercial grade, vertical position, device mount.	4.56" x 2.81" x 0.75" (115.8 x 71.4 x 19.1)		<b>WP8V</b>



HBL5221



WP8V

### Duplex Covers For Horizontal Mounting

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Cast aluminum, for device mounting.	2.88" x 4.56" x 0.79" (73.2 x 115.8 x 20.1)		<b>HBL5205WO</b>
Cast aluminum, for FS/FD box mounting.	2.88" x 4.56" x 0.79" (73.2 x 115.8 x 20.1)		<b>HBL5206WO</b>
Die cast aluminum, gray, commercial grade, horizontal position, device mount.	2.90" x 4.60" x 0.75" (73.7 x 116.8 x 19.1)		<b>WP8H</b>



HBL5206WO



WP8H

### GFCI, Surge and Style Line® Covers

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Die cast aluminum, gray, commercial grade, vertical position, device mount.	4.56" x 2.81" x 0.75" (115.8 x 71.4 x 19.1)		<b>WP26V</b>
Die cast aluminum, gray, commercial grade, horizontal position, device mount.	2.30" x 4.75" x 0.73" (58.4 x 120.7 x 18.5)		<b>WP26H</b>



WP26V



WP26H

### Toggle Cover

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Thermoplastic, gray, for FS/FD box mounting.	4.56" x 2.89" x 1.08" (115.8 x 73.4 x 27.4)		<b>HBL5201</b>

Note: All weatherproof plates are UL Listed for WET LOCATIONS WITH COVER CLOSED, for intermittent use in wet locations or use in damp locations. Those with Suffix "WO" are listed for WET LOCATIONS with cover open in continuous use. All plates are gasketed and self-closing.



RW51550



RW51470



RW51040

### 1-Gang Weatherproof Covers for Vertical Mounting

Description	Dimensions		Catalog Number
	Height	Width x Depth	
Zinc die cast, gray, duplex cover for box mounting.	4.58"	2.82" x 0.57" (116.3 x 71.6 x 14.5)	<b>RW51470</b>
Zinc die cast, gray, 1.40 in. (35.6) cover for single receptacle or toggle switch for device mounting.	4.56"	2.81" x 0.88" (115.8 x 71.4 x 22.4)	<b>RW51550*</b>
Zinc die cast, gray, GFCI, Surge and Style Line® cover for device mounting.	4.58"	2.81" x 0.57" (116.3 x 71.4 x 14.5)	<b>RW51040</b>

### 1-Gang Weatherproof Covers for Horizontal Mounting

Description	Dimensions		Catalog Number
	Height	Width x Depth	
Zinc die cast, gray, duplex cover for device mounting.	2.82"	4.57" x 0.79" (71.6 x 116.1 x 20.1)	<b>RW51810</b>
Zinc die cast, gray, 1.40 in. (35.6) cover for single receptacle or toggle switch for device mounting.	2.81"	4.56" x 0.99" (71.4 x 115.8 x 25.1)	<b>RW51520*</b>
Zinc die cast, gray, GFCI, Surge and Style Line® cover for device mounting.	2.82"	4.56" x 0.52" (71.6 x 115.8 x 13.2)	<b>RW51020</b>

### 2-Gang Weatherproof Covers for Vertical Mounting

Description	Dimensions		Catalog Number
	Height	Width x Depth	
Zinc die cast, gray, duplex cover for device mounting.	4.54"	4.54" x 0.75" (115.3 x 115.3 x 19.1)	<b>RW51320</b>
Zinc die cast, gray, one duplex/one GFCI, Surge and Style Line® cover for box mounting.	4.54"	4.54" x 0.77" (115.3 x 115.3 x 19.6)	<b>RW51330</b>
Zinc die cast, gray, 1.40 in. (35.6) cover for single receptacle or toggle switch for device mounting.	4.54"	4.54" x 0.77" (115.3 x 115.3 x 19.6)	<b>RW51380</b>
Zinc die cast, gray, two GFCI, Surge and Style Line® cover for box mounting.	4.54"	4.56" x 0.73" (115.3 x 115.8 x 18.5)	<b>RW51450</b>

Note: All weatherproof plates are UL Listed for WET LOCATIONS WITH COVER CLOSED, for intermittent use in wet locations or use in damp locations. All plates are gasketed and self-closing.

\*cULus Listed.



RW51330



RW51320



RW51450



RW51380

## Features

Extra-Duty Metallic While-in-Use Covers are designed for use whenever protection is required while an outlet is in use. Covers meet or exceed the extra-duty rating per UL 514D, and are NEMA 3R rated.

- Superior commercial quality die-cast aluminum construction
- Meets or exceeds Extra-Duty rating in UL 514D
- Unique lid design allows larger plugs and provides more room for bend radius of electrical cords

- Provision on each side for holding cords – Reduces pull-outs
- Padlockable – Accepts standard size padlocks
- Includes gasket and hardware
- Powder coated for corrosion protection
- Device or box mounting
- NEMA 3R rated
- Can be installed to comply with 2011 NEC 406.9(B) (See page N-22).

### 1-Gang Extra-Duty Metallic While-In-Use Covers for Vertical Mounting

Description	Dimensions Height x Width x Depth	Catalog Number
While-in-Use cover, gray, 1-gang, duplex cover for vertical mounting.	6.5" x 3.1" x 3.3" (165.1 x 78.7 x 83.2)	<b>WP8E</b>
While-in-Use cover, gray, 1-gang, round hole 1.55" or 2.10" cover, for vertical mounting.	6.5" x 4.5" x 3.3" (165.1 x 114.3 x 83.2)	<b>WP700E</b>
While-in-Use cover, gray, 1-gang, GFCI cover for vertical mounting.	6.5" x 3.1" x 3.3" (165.1 x 78.7 x 83.2)	<b>WP26E</b>



### 1-Gang Extra-Duty Metallic While-In-Use Covers for Horizontal Mounting

Description	Dimensions Height x Width x Depth	Catalog Number
While-in-Use cover, gray, 1-gang, duplex cover for horizontal mounting.	4.7" x 5.1" x 3.3" (119.4 x 129.5 x 83.2)	<b>WP8EH</b>
While-in-Use cover, gray, 1-gang, GFCI cover for horizontal mounting.	4.7" x 5.1" x 3.3" (119.4 x 129.5 x 83.2)	<b>WP26EH</b>



### 2-Gang Extra-Duty Metallic While-In-Use Covers for Vertical Mounting

Description	Dimensions Height x Width x Depth	Catalog Number
While-in-Use cover, gray, 2-gang, double duplex cover for vertical mounting.	6.5" x 5.1" x 3.3" (165.1 x 129.5 x 83.2)	<b>WP82E</b>
While-in-Use cover, gray, 2-gang, GFCI and duplex cover for vertical mounting.	6.5" x 5.1" x 3.3" (165.1 x 129.5 x 83.2)	<b>WP268E</b>
While-in-Use cover, gray, 2-gang, double GFCI cover for vertical mounting.	6.5" x 5.1" x 3.3" (165.1 x 129.5 x 83.2)	<b>WP262E</b>



**IP66**  
 SUITABILITY



**RW57300**

**1-Gang Weatherproof Covers for Vertical Mounting**

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 3.5" x 2.8" (147.3 x 88.9 x 71.1)		<b>RW57300</b>



**RW57350**

Thermoplastic, gray, extra deep, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 3.5" x 4.8" (147.3 x 88.9 x 121.9)	<b>RW57350</b>
--	--	----------------



**1-Gang Weatherproof Covers for Horizontal Mounting**

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	4.0" x 5.2" x 2.8" (101.6 x 132.1 x 71.1)		<b>RW57400</b>



**RW57400**



**RW57750**

**2-Gang Weatherproof Covers for Vertical Mounting**

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 5.3" x 2.8" (147.3 x 134.6 x 71.1)		<b>RW57750</b>



**RW57900**

Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 5.3" x 4.8" (147.3 x 134.6 x 121.9)	<b>RW57900</b>
--	---	----------------



**RW57950**

Thermoplastic, gray, single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.8" x 5.3" x 4.8" (147.3 x 134.6 x 121.9)	<b>RW57950</b>
---	---	----------------




*Note: Required by the NEC® for while-in-use outdoor power distribution. Thermoplastic covers provide protection for use in wet locations with the cover closed, NEMA® 3R rated. Meets NEC 406.8 – receptacles in damp or wet locations. Holes for padlocks are .40 inch.*

*NEC® is a registered trademark of the The National Electrical Code.  
 NEMA® is a registered trademark of The National Electrical Manufacturers Association.*

## Screws, 6-32 Thread, 100 Count

Description	Color/Material	Catalog Number
Decorator Wallplate Screws, Oval Head Milled Slot, 3/8 in. Long – 6-32 Thread, 100 per Box (Order 1 to receive a box of 100)	Almond	<b>RA38ALPK100</b>
	Black	<b>RA38BKPK100</b>
	Brown	<b>RA38PK100</b>
	Gray	<b>RA38GYPK100</b>
	Ivory	<b>RA38IPK100</b>
	Light Almond	<b>RA38LAPK100</b>
	White	<b>RA38WPK100</b>
Standard Wallplate Screws, Oval Head Milled Slot, 1/2 in. Long – 6-32 Thread, 100 per Box (Order 1 to receive a box of 100)	Almond	<b>RA12ALPK100</b>
	Black	<b>RA12BKPK100</b>
	Brown	<b>RA12PK100</b>
	Gray	<b>RA12GYPK100</b>
	Ivory	<b>RA12IPK100</b>
	Light Almond	<b>RA12LAPK100</b>
	White	<b>RA12WPK100</b>
Standard Wallplate Screws, Oval Head Milled Slot, 5/8 in. Long – 6-32 Thread, 100 per Box (Order 1 to receive a box of 100)	Ivory	-
	White Stainless Steel	<b>RA58SSPK100</b>
Standard Wallplate Screws, Oval Head Milled Slot, 1.0 in. Long – 6-32 Thread, 100 per Box (Order 1 to receive a box of 100)	Ivory	<b>RA88IPK100</b>
	White	<b>RA88WPK100</b>
	Stainless Steel	<b>RA88SSPK100</b>



RA38IPK100



RA12IPK100



RA58SS



RA88IPK100

## Single Count Screws and Accessories

Description	Color	Catalog Number
Blank adapter, to fill a toggle opening.	Brown	<b>RA756</b>
	Ivory	<b>RA756I</b>
	White	<b>RA756W</b>
Blank adapter, to fill a decorator opening.	Ivory	<b>NS620I</b>
	Light Almond	<b>NS620LA</b>
	White	<b>NS620W</b>
Blank adapter, .406" (10.30) dia. hole, to fill a decorator opening.	Ivory	<b>NS621I</b>
	Light Almond	<b>NS621LA</b>
	White	<b>NS621W</b>
Mounting strap, with screws.	Steel	<b>RA40</b>
Brass plated screw, standard slot, .38 in. (9.7) long.	Brass	<b>HBL7341</b>



RA756I

RA40



NS620I

NS621I



HBL7341

### Specifications

#### Listings

Non-Metallic Plates	UL Standard 514D.
Metallic Plates	UL Standard 514D.
Certification	UL Files #E31999, E92074. CSA Standard C22.2 No. 42.1. CSA File 1733174.

#### Nylon Plate

Thickness	.06 in. (1.5).
Mounting Screw(s)	Steel (painted slotted screw head).
Feature	Captive mounting screw hole.
Operating Temperature	-40°C to 85°C.
Appearance	Smooth.

#### 302/304 Stainless Steel (18% Chromium, 8% Nickel) Plate

Thickness	.035 in. (0.9) nominal.
Mounting Screw(s)	302/304 stainless steel (18% chromium, 8% nickel). Slotted screw head.
Appearance	Horizontal brushed finish.

#### 430 Stainless Steel (17% Chromium, less than 0.5% Nickel) Plate

Thickness	.035 in. (0.9) nominal.
Mounting Screw(s)	302/304 stainless steel (17% chromium, less than 0.5% nickel). Slotted screw head.
Appearance	Horizontal brushed finish.

#### Brass (70% Copper, 30% Zinc) Plate

Thickness	.04 in. (1.0).
Mounting Screw(s)	Brass (70% Copper, 30% Zinc). Slotted screw head.
Appearance	Horizontal brushed finish.

#### Aluminum Plate

Thickness	.05 in. (1.3).
Mounting Screw(s)	302/304 stainless steel (17% chromium, less than 0.5% nickel). Slotted screw head.
Appearance	Horizontal brushed finish.

#### Brass Plated Steel Plate

Thickness	.03 in. (0.8) nominal.
Mounting Screw(s)	Brass slotted head.
Appearance	Polished, coated to inhibit oxidation.

#### Chrome Plated Steel Plate

Thickness	.03 in. (0.8) nominal.
Mounting Screw(s)	302/304 stainless steel (17% chromium, less than 0.5% nickel). Slotted screw head.
Appearance	Polished, coated to inhibit oxidation.


#### Steel Painted Plate

Thickness	.03 in. (0.8) nominal.
Mounting Screw(s)	Steel (painted slotted screw head).
Appearance	Powder coat paint.


# Wallplates Wallplate Dimensions

## Product Dimensions


Size	Standard Metal		Painted Metal	Size	Jumbo Metal	
	Height	Width	Width		Height	Width
1-Gang	4.50" (114.3)	2.87" (72.9)	2.75" (69.8)	1-Gang	5.25" (133.4)	3.50" (88.9)
2-Gang	4.50" (114.3)	4.60" (116.8)	4.56" (115.8)	2-Gang	5.25" (133.4)	5.31" (134.9)
3-Gang	4.50" (114.3)	6.41" (162.8)	6.38" (162.1)	3-Gang	5.25" (133.4)	7.12" (180.8)
4-Gang	4.50" (114.3)	8.22" (208.8)	8.18" (207.8)			
5-Gang	4.50" (114.3)	10.03" (254.8)	10.00" (254.0)			
6-Gang	4.50" (114.3)	11.81" (300.0)	11.81" (300.0)			
7-Gang	4.50" (114.3)	13.68" (347.5)				
8-Gang	4.50" (114.3)	15.44" (392.1)				



Size	Standard Nylon		Size	Mid-Size Nylon	
	Height	Width		Height	Width
1-Gang	4.63" (117.6)	2.88" (73.2)	1-Gang	4.88" (124.0)	3.13" (79.5)
2-Gang	4.63" (117.6)	4.69" (119.1)	2-Gang	4.88" (124.0)	4.94" (125.4)
3-Gang	4.63" (117.6)	6.50" (165.1)	3-Gang	4.88" (124.0)	6.75" (171.5)
4-Gang	4.63" (117.6)	8.31" (211.1)	4-Gang	4.88" (124.0)	8.56" (217.4)
5-Gang	4.63" (117.6)	10.12" (256.1)			
6-Gang	4.63" (117.6)	11.93" (303.0)			




Size	Snap-On Nylon	
	Height	Width
1-Gang	4.68" (118.9)	2.94" (74.7)
2-Gang	4.68" (118.9)	4.75" (120.7)
3-Gang	4.68" (118.9)	6.56" (166.6)
4-Gang	4.68" (118.9)	8.37" (212.6)
5-Gang	4.68" (118.9)	10.18" (258.6)
6-Gang	4.68" (118.9)	11.99" (304.5)



## Wallplate Openings and Mounting Dimensions

#6-32 Oval Head Screws Typical



Note: Specifications are subject to change without notice.

# Custom Metal Wallplates

How To Select A Custom Metal Wallplate

## Step 1:

Determine wallplate material and enter in box marked "Catalog Number"

Smooth Metal Material	Code
Anodized Aluminum	<b>AL</b>
Brass plated steel	<b>BP</b>
Solid brass	<b>BR</b>
Chrome plated steel	<b>CH</b>
Stainless steel 302/304	<b>SS</b>

Determine number of gangs required and enter in box marked "Catalog Number" next to material.

Number of Gangs	Code
1-gang	<b>1</b>
2-gang	<b>2</b>
3-gang	<b>3</b>
4-gang	<b>4</b>
5-gang	<b>5</b>
6-gang	<b>6</b>
7-gang	<b>7</b>
8-gang	<b>8</b>

Enter Catalog Number

◆ WC\* SS 4

## Step 2:

Enter quantity.

## Step 3:


Select the custom metal wallplate configuration.

Refer to the custom wallplate configuration chart to select a configuration for each gang in the wallplate. Each configuration has a specific 3-digit code located in the right hand side of the chart on pages N-33 to N-36. Enter this 3-digit configuration code in the corresponding box on the order form grid to match the position required on the finished custom wallplate.

Item No.	Catalog Number	Quantity	Code	Position 1	Position 2	Position 3	Position 4
<b>1</b>	<b>WCSS4</b>		<b>H*</b>	<b>001</b>	<b>149</b>	<b>008</b>	<b>026</b>
<b>2</b>							

Note: \*WC and H are preprinted on the distributor order form. Number to use for pricing.

The 3-digit numbers listed at the upper right of the Sample Order Form (001, 149, etc.) represent the custom metal wallplate selected on the right. See Configuration Chart and Hubbell Configuration Selector Guide on pages N-33 to N-36 for additional configuration choices.










































# Wallplates


## Custom Metal Wallplates

Configuration Chart

	<b>001</b> Switch.		<b>079</b> Barrel Key Switch with hash marks.		<b>456</b> .375" (9.5) Dia. Round Box Mounted.
	<b>007</b> Single Receptacle. 1.40" ID (35.6) Hole.		<b>080</b> Barrel Key Switch with On/Off and hash marks.		<b>458</b> .500" (12.7) Dia. Round Box Mounted.
	<b>008</b> Duplex Receptacle.		<b>091</b> Single Receptacle. 1.60" ID (40.5) Hole.		<b>435</b> 9-Pin Vertical Box Mounted.
	<b>011</b> 1-gang .635" ID (16.1) Hole Box Mounted with .50" ID (12.7) Nylon Bushing.		<b>098</b> Single Receptacle. 2.16" ID (54.7) Hole.		<b>438</b> 15-Pin Vertical Box Mounted.
	<b>012</b> 1-gang .635" ID (16.1) Hole Strap Mtd. incl. Strap with .50" ID (12.7) Nylon Bushing.		<b>135</b> Vertical Mounted Louver.		<b>295</b> 25-Pin Vertical Box Mounted.
	<b>013</b> Blank Box Mounted.		<b>149</b> Totally Blank (no mounting holes).		<b>314</b> IBM® Type Opening Box Mounted.
	<b>014</b> Blank Strap Mounted incl. Strap.	<b>Coax/Twinax and Modular Jack Openings</b>			<b>415</b> IBM® Type Opening with One .586" x .762" (14.9 x 19.3).
	<b>026</b> Rectangular Opening.		<b>422</b> .51" (12.8) Dia. "D" Box Mounted. .44" (11.1) Flat Dia.	<b>Voice/Data Opening</b>	
	<b>055</b> 1-gang .375" ID (9.5) Hole Strap Mounted incl. Strap.		<b>425</b> .51" (12.8) Dia. "D" Box Mounted. .47" (12) Flat Dia.		<b>470</b> .542" x .750" (13.8 x 19.0) Vertical Box Mounted.
	<b>056</b> 1-gang .375" ID (9.5) Hole Box Mounted.		<b>428</b> .58" (14.7) Dia. "D" Box Mounted. .55" (14) Flat Dia.		<b>473</b> .586" x .762" (14.9 x 19.4) Vertical Box Mounted.
	<b>057</b> 1-gang .50" ID (12.7) Hole Strap Mounted incl. Strap.		<b>430</b> .76" (19.2) Dia. "D" Box Mounted. .73" (18.6) Flat Dia.		<b>476</b> .586" x .815" (14.9 x 20.7) Vertical Box Mounted.
	<b>058</b> 1-gang .50" ID (12.7) Hole Box Mounted.		<b>431</b> .76" (19.2) Dia. "D" Box Mounted. .73" (18.6) Flat Dia.		<b>477</b> .586" x .815" (14.9 x 20.7) Vertical Box Mounted.
	<b>078</b> Barrel Key Switch.		<b>431</b> .76" (19.2) Dia. "D" Box Mounted. .73" (18.6) Flat Dia.		<b>480</b> .575" x .783" (14.6 x 19.9) Vertical Box Mounted.


Note: For detailed dimensions of the above configurations, see pages N-34 to N-36. Available in smooth metal, standard size only up to and including 8-gang type.

IBM® is a registered trademark of International Business Machines Corporation.




Configuration 001

Toggle Switch Plate.




Configuration 026

GFI/Rectangular Opening.




Configuration 007

Single 15 or 20A Straight Blade Receptacle.  
15A Twist-Lock® Receptacle.




Configuration 055

Single, .375" (9.5) Telephone (Strap Mount).




Configuration 008

Duplex Receptacle.




Configuration 056

Single, .375" (9.5) Telephone (Box Mount).




Configuration 011

Single, .635" (16.1) Telephone (Box Mount).




Configuration 057

Single, .50" (12.7) Telephone (Strap Mount).




Configuration 012

Single, .635" (16.1) Telephone (Strap Mount).




Configuration 058

Single, .50" (12.7) Telephone (Box Mount).




Configuration 013

Blank Plate (Box Mount).




Configuration 078

Barrel Key Switch.



Configuration 014

Blank Plate (Strap Mount).



Configuration 079


Barrel Key Switch with hash marks.

Note: Specifications are subject to change without notice.

# Wallplates


## Custom Metal Wallplates

Configuration Selector Guide




**Configuration 080**

Barrel Key Switch with On/Off and hash marks.




**Configuration 091**

Single 20 or 30A Twist-Lock® Receptacle.




**Configuration 098**

Single Receptacle, 30 or 50A Straight Blade, 3 Wire Power Outlet.




**Configuration 135**

Louvered Plate (Strap Mount).




**Configuration 149**

Totally Blank Plate.




**Configuration 295**

RS232 Port Single 25-Pin (Box Mount).




**Configuration 314**

IBM® Type (Box Mount).




**Configuration 411**

Dual .635" (16.1) Holes (Box Mount).




**Configuration 415**

IBM® Type and Modular Jack (Box Mount).




**Configuration 422**

Single .505" (12.8) D-Hole (Box Mount).




**Configuration 423**

Dual .505" (12.8) D-Holes (Box Mount).




**Configuration 425**

Single .505" (12.8) D-Hole (Box Mount).



**Configuration 426**

Dual .505" (12.8) D-Holes (Box Mount).



**Configuration 428**

Single .580" (14.7) D-Hole (Box Mount).


Note: Specifications are subject to change without notice.

IBM® is a registered trademark of International Business Machines Corporation.

# Wallplates


## Custom Metal Wallplates

### Configuration Selector Guide




Configuration  
**429**

Dual .580" (14.7) D-Holes  
(Box Mount).




Configuration  
**430**

Single .755" (19.2) D-Hole  
(Box Mount).




Configuration  
**431**

Dual .755" (19.2) D-Holes  
(Box Mount).




Configuration  
**435**

Single 9-Pin RS232  
(Box Mount).




Configuration  
**438**

Single 15-Pin RS232  
(Box Mount).




Configuration  
**456**

Dual .375" (9.5) Round  
(Box Mount).




Configuration  
**458**

Dual .50" (12.7) Round  
(Box Mount).




Configuration  
**470**

Single Modular Jack  
(Box Mount).




Configuration  
**471**

Dual Modular Jack  
(Box Mount).




Configuration  
**473**

Single Modular Jack  
(Box Mount).




Configuration  
**474**

Dual Modular Jack  
(Box Mount).




Configuration  
**476**

Dual Modular Jack  
(Box Mount).




Configuration  
**477**

Dual Modular Jack  
(Box Mount).



Configuration  
**479**

Single Modular Jack  
(Box Mount).



Configuration  
**480**

Dual Modular Jack  
(Box Mount).

Note: Specifications are subject to change without notice.