

The background is a vibrant, abstract composition of iridescent colors, including shades of blue, green, red, and purple, creating a shimmering, liquid-like effect. A single, soft pink flower is visible in the lower right quadrant, partially obscured by the colorful patterns.

minkaAire®

2018



Minka-Aire® invites you to view our ceiling fan collection designed for today's varying lifestyles.

Within this catalog, you will find designs of contemporary flair with elegant grace, transitional timeless styles and a collection from our licensed design series.

The architectural trend toward Great Rooms has led Minka-Aire® to redesign some of our most popular styles with enlarged bodies and longer blades to circulate more air and complement the spaciousness of these rooms.

Our Outdoor Series of fans allows your friends and family to enjoy outdoor dining or time in your spa while continuing to have pleasant surroundings.

We offer many design choices for the outdoors; rated for all-weather exposure.

Minka-Aire® ceiling fans offer a wide variety of designs for the American home.



THE PRODUCTS DEPICTED IN THIS CATALOG ARE PROTECTED BY UNITED STATES FEDERAL AND/OR STATE LAW, INCLUDING PATENT, TRADEMARK AND/OR COPYRIGHT LAWS.

© 2018 MINKA LIGHTING, INC.
CATALOG DESIGN AND ALL ELEMENTS OF CATALOG DESIGN ARE PROTECTED BY UNITED STATES FEDERAL AND/OR STATE LAW, INCLUDING PATENT, TRADEMARK AND/OR COPYRIGHT LAWS.

TABLE OF CONTENTS

Acero™	128-129	Gyro™ Wet	152-153, 210-211	Tear	100-101
Airus™	146-147	Java	62-63, 232-233	Timber	50-51
Aluma	92-93	Java LED	108-109, 230-231	Timeless	168-173
Aluma Wet	234-235	Kafé	182-185	Traditional Concept™ 44"	132-133, 228-229
Alva	158-159	Kafé-XL	178-181	Traditional Concept™ 52"	130-131, 226-227
Anywhere	204-205	Kewl	138-139	Traditional Gyro™	150
Artemis™	68-73	Kola	176-177	Traditional Mojo	268-269
Artemis™ IV	56-59	Kola-XL	174-175	Triple	12-15
Artemis™ XL5	74-77	Light Wave	86-87	Ultra-Max™	284-285
Aviation	42-45	Lineage™	189	Vintage Gyro™	148-149
Aviation LED	38-41	Lun-Aire	260-261	Volterra™	198
Bling	110-111	Mesa	310	Wave	30-31
Bolo	186-187	Metropolis	88-89	Wave II	122-125
Cage Free Gyro™	156	Mojave	64-67	Wing	116-117
Calais™	199	Mojo	270-271	Xtreme	21-24
Cirque™	140-141	Mojo II	272-273	Xtreme H ₂ O	16-20, 206-209
Classica	194-197	Napoli™	190	Zen	142-143
Classica - Gallery Edition	192-193	Napoli™ II	191		
Clean	34-37	New Era	144-145	ACCESSORY FAN BLADES	334-335
Como™	134-135	Ninety-Nine	25-29	FAN CONTROL SYSTEMS	
Concept™ I	136-137	Pancake	84-85	Compatibility Chart	324-327
Concept™ II 44"	114-115	Pancake XL LED	80-83	Fan Controls	320-323
Concept™ II 52"	112-113	Rainman™	240-241	FAN HANGING SYSTEMS	
Concept™ II Wet 52"	224-225	Raptor	60-61	Accessories	330
Concept™ I Wet 52"	222-223	Retro Style Fan	276	Downrods	328-330
Concept™ I Wet 58"	220-221	Roto	54-55	GLASS SHADES	318
Cone	32-33, 216-217	Roto XL	218-219	LIGHT KITS	
Contractor 42"	308-309	Rudolph	262-263	Custom LED Light Kits	319
Contractor 52"	306-307	Sabot	118-119	Custom Light Kits	317
Contractor LED	280-281	Santa Lucia™	188	Universal LED Light Kits	311
Contractor Plus	282-283	Shade	238-239	Universal Light Kits	311-316
Contractor Uni-Pack LED	278-279	Shangri-La®	254-255	BULB REFERENCE	336
Contractor Uni-Pack with 3-Light	298-299	Simple 44"	48-49	DIMENSIONS & SPECIFICATIONS	364-366
Contractor Uni-Pack with Light	300-305	Simple 52"	46-47, 212-213	FAN STYLES	351-363
Cristafano™	200-201	Slant	126-127	FINISH GUIDE	331-333
Delano®	164-165	Slipstream	102-103, 242-243	AIRFLOW CFM	337-340
Delano® II	166-167	Spacesaver	274-275	INDEX	344-350
Dream Star	8-11	Spectre	104-107		
Dyno	264-265	Stack	98-99		
Elemental Gyro™	154-155	Steal	266-267		
Escape	258-259	Strata	236-237		
Flyte®	120-121	Sundance™	250-251		
Force	90-91	Sundowner®	246-249		
Gauguin™	252-253	Sunseeker	244-245		
Gear	52-53	Supra® 32"	296-297		
Great Room Traditional	160-163	Supra® 44"	294-295		
Groton	214-215	Supra® 44" with Light	292-293		
Gyrette™	157	Supra® 52"	288-291		
Gyro™	151	Supra® 52" with Light	286-287		
		Swept	94-97		
		Symbio	78-79		



WANT AN OUTDOOR FAN?

Minka-Aire® only produces UL Wet Rated Outdoor Fans.

	Minka-Aire® UL Wet	UL Damp	Indoor
INDOOR USE			
Common Area, Bedrooms	✓	✓	✓
Garage	✓	✓	✓
Bathroom with Showers	✓	✓	
Homes near Ocean	✓		
OUTDOOR USE			
Fully Covered Patio/Porch	✓	✓	
Partially Covered Patio/Porch	✓		
Direct Exposure to Rain	✓		
Direct Exposure to Snow	✓		
Pergola	✓		
Near Sprinklers	✓		
Near the Ocean	✓		
Simple to Clean (<i>Hose it Down!</i>)	✓		
OTHER FACTORS			
Completely Sealed Motor Housing	✓		
Rust/Corrosion Resistant	✓		
Non-Corrosive Screws	✓		
UV Inhibitors	✓		

MINKA-AIRE® ICON LEGEND

LED

LED lighting is efficient, lasts up to 4 times longer than conventional lighting and using less energy.

DC MOTOR

Best in class with energy efficient operation. Uses up to 70% less energy than traditional AC motors while producing more power.



Strict guidelines set by the U.S. Environmental Protection Agency (EPA) are met.



Indicates that product can be directly exposed to the elements. Rain, Snow or Sun.



BOND Smart Together. Connect your remote controlled ceiling fans over Wi-Fi


BOND™

Connect your
remote-controlled



ceiling fans over Wi-Fi

USING YOUR PHONE, TABLET, OR SMART SPEAKER



You control the BOND, the BOND
controls your ceiling fans, and you'll
never need your old remotes again.

www.minkaaire.com | www.bondhome.io

BOND™

Now an exclusive **minkaAire**
technology partner!

SECONDS TO SET UP!




Connect to Wi-Fi



Download the app



Pair remote controls



**Define controls
& store remotes**
(you won't need them!)

Smart Together



ENERGY EFFICIENCY



- DC motors are up to 67% more efficient than typical (AC Motor) ceiling fan motors
- Minka-Aire® DC motor fans use a maximum of 48 watts of electricity
- DC motors can move greater degree of fan blade pitches without adding significant energy consumption
- DC motors provide a wider range of fan speeds. All of Minka-Aire's DC motors offer 6 different fan speeds creating a more personalized comfort setting.

Look for this logo for fans that carry Minka-Aire's most energy efficient motor

DC MOTOR



Minka-Aire's DC Motor Features



DC MOTOR
AIRFLOW:
EXCELLENT

AC MOTOR
AIRFLOW:
GOOD

Benefits

- Limited Lifetime Motor Warranty
- Flatter laminations in the motor helps reduce motor buzz
- Minka-Aire® DC motors use the latest innovative technology and high quality materials
- DC motors are held to higher quality standards
- Currently Minka-Aire® uses 4 different DC motors, providing the flexibility to create amazing fan styles and designs.

Benefits of LED Lighting

1. Long Life

Longer lifetime is the number one benefit of LED lights. The diodes within our LEDs have an outstanding lifetime expectation of up to 30,000 hours.

2. Energy Efficiency

This is today's most efficient way of illumination and lighting, saving 80%-90% when compared to traditional lighting and conventional light bulbs.

3. Ecologically Friendly

LED lights are free of toxic chemicals. Most conventional fluorescent lighting bulbs contain a multitude of materials like e.g. mercury that are dangerous for the environment.

4. Durable Quality

LEDs are extremely durable and built with sturdy components that are highly rugged and can withstand the roughest conditions.

5. Zero UV Emissions

LED illumination produces little infrared light and close to no UV emissions, which attracts less insects.





6. All Minka-Aire® LED fans are dimmable as compared to CFLs which are not.



ROOM SIZE AND CEILING HEIGHT RECOMMENDATIONS


Room Size

These measurements are for general air flow requirements only. Decorating plans or aesthetic considerations should influence your fan choices beyond these room size specifications. For very large rooms, multiple fans is an option.

				
Blade Sweep	26"-42"	44"	52"-54"	60"-99"
Approximate Room Size	6' x 8' 40-60 sq. ft.	8' x 10' 70-90 sq. ft.	10' x 12' 100-150 sq. ft.	12' x 15' (Great Room) Over 160 sq. ft.

Ceiling Height

Be sure there is at least 7 feet of clearance under your ceiling fan blades. The standard 6" downrod should work in most 8 foot ceiling installations. This will position the blades far enough from the ceiling to have enough "supply" air above the blades to provide good air movement. If greater floor to fan clearance is needed, some fans can use our low ceiling adapter (A180) without using any downrod. However, air movement is reduced using the low ceiling adapter. This chart shows recommended downrod lengths for various ceiling heights.





F788L-GS


DREAM STAR

with LED Light

Pursuing a courageous statement with eight curved vanes, the Dream Star provides an engineered, yet artistic design. Leaving no detail to chance, this powerhouse of air movement is complemented by a fade-away canopy, which eliminates any evidence of a hanging system. Dream Star is also equipped with a 18 watt integrated LED light.

DREAM STAR

with LED Light



F788L-GS • Graphite Steel Finish • Graphite Steel Finish Blades • Etched Lens

LED **DC MOTOR**

minkaAire.



F788L-WH

DREAM STAR

with LED Light

Pursuing a courageous statement with eight curved vanes, the Dream Star provides an engineered, yet artistic design. Leaving no detail to chance, this powerhouse of air movement is complemented by a fade-away canopy, which eliminates any evidence of a hanging system. Dream Star is also equipped with a 18 watt integrated LED light.

FEATURES

- Variable Blade Pitch • 8-Blades 60" Sweep • DC 168 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 18W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K
- CRI 80 • Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

Energy Use: 33 Watts

- Airflow 8,063 Cubic Feet Per Minute

Airflow Efficiency: 244 Cubic Feet Per Minute Per Watt

F788L-WH • White Finish • White Blades • Etched Lens

F788L-ORB • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Etched Lens

F788L-GS • Graphite Steel Finish • Graphite Steel Finish Blades • Etched Lens
(Shown on previous page)



RC400

For Details
See Page(s): 320



BOND
Compatible Fan

DREAM STAR

with LED Light



F788L-ORB

LED DC MOTOR

minkaAire.



F832L-VI

TRIPLE

with LED Light

Clearing the way for fresh Aire, TRIPLE delivers a refined modern industrial design. Its turbine-like three blades provide a utilitarian and raw contemporary edge that enhances the space of any room. The TRIPLE is equipped with an integrated 20 watt LED light and advanced DC motor technology.

TRIPLE

with LED Light



F832L-VI • Vintage Iron Finish • Urban Walnut Blades • Etched Lens

LED DC MOTOR

minkaAire®

TRIPLE

with LED Light



F832L-ORB/MM



F832L-BS



F832L-BN/SL

TRIPLE

with LED Light

Clearing the way for fresh Aire, TRIPLE delivers a refined modern industrial design. Its turbine-like three blades provide a utilitarian and raw contemporary edge that enhances the space of any room. The TRIPLE is equipped with an integrated 20 watt LED light and advanced DC motor technology.

FEATURES

- Variable Blade Pitch • 3-Blades 60" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 20W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K
- CRI 90 • Special Hand Held Remote Control System Included - RC400

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$8
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 29 Watts
- Airflow 4,089 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 141 Cubic Feet Per Minute Per Watt

- F832L-BN/SL** • Brushed Nickel Finish • Silver Blades • Etched Lens
- F832L-ORB/MM** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Lens
- F832L-BS** • Brushed Steel Finish • Urban Light Oak Blades • Etched Lens
- F832L-VI** • Vintage Iron Finish • Urban Walnut Blades • Etched Lens
(Shown on previous page)




RC400
For Details
See Page(s): 320



BOND
Compatible Fan

F896-84-ORB

*Shown with optional
K9886L-ORB LED light kit*



F896-84-BNW

F896-84-ORB
See Opposite Page

XTREME H₂O 84"

An outdoor version of one of our most popular large fan introductions, this industrial sized fan lends itself to any setting. Xtreme H₂O's clean, sleek, contemporary design, complete with a DC motor and a choice of sizes, makes it perfect for large areas indoor or outdoor.

FEATURES

- 4° Blade Pitch • 8-Blades 84" Sweep • DC 123 x 30mm Motor • 6" Downrod
- ABS Blades • Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9886L Available (Sold Separately Page(s): 319)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 32 Watts
- Airflow 8,252 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 262 Cubic Feet Per Minute Per Watt

- F896-84-ORB** • Oil Rubbed Bronze • Oil Rubbed Bronze Blades
- F896-84-BNW** • Brushed Nickel Wet Finish • Silver Blades
- F896-84-SI** • Smoked Iron Finish • Smoked Iron Finish Blades




RC400
For Details
See Page(s): 320



BOND
Compatible Fan

** Estimated



F896-84-SI
*Shown with optional
K9886L-SI LED light kit*





F896-65-BNW

XTREME H₂O 65"

An outdoor version of one of our most popular large fan introductions, this industrial sized fan lends itself to any setting. Xtreme H₂O's clean, sleek, contemporary design, complete with a DC motor and a choice of sizes, makes it perfect for large areas indoor or outdoor.

FEATURES

- 4° Blade Pitch • 8-Blades 65" Sweep • DC 123 x 30mm Motor • 6" Downrod
- ABS Blades • Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9886L Available (Sold Separately Page(s): 319)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 32 Watts
- Airflow 6,565 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 205 Cubic Feet Per Minute Per Watt

- F896-65-BNW** • Brushed Nickel Wet Finish • Silver Blades
- F896-65-ORB** • Oil Rubbed Bronze • Oil Rubbed Bronze Blade
- F896-65-WHF** • Flat White Finish • Flat White Blades




RC400

For Details
See Page(s): 320



BOND
Compatible Fan

XTREME H₂O




F896-65-ORB
Shown with optional
K9886L-ORB LED light kit



F896-65-WHF
Shown with optional
K9886L-WHF LED light kit





XTREME

This industrial size fan lends itself to almost any setting. Xtreme's clean, sleek, contemporary design with a DC motor and a choice of sizes makes it perfect for large areas.

FEATURES

- 4° Blade Pitch • 9-Blades 72" or 96" Sweep • DC 165 x 25mm Motor
- 6" Downrod • Aluminum Blades • Install with Blades at least 10' above the Floor
- Special Hand Held Remote Control System Included - RC400

72" ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 23 Watts
- Airflow 6,134 Cubic Feet Per Minute
- Airflow Efficiency: 270 Cubic Feet Per Minute Per Watt

96" ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 31 Watts
- Airflow 13,080 Cubic Feet Per Minute
- Airflow Efficiency: 429 Cubic Feet Per Minute Per Watt

- F887-72-BN 72"** • Brushed Nickel Finish • Silver Blades
- F887-96-BN 96"** • Brushed Nickel Finish • Silver Blades




RC400
For Details
See Page(s): 320



BOND
Compatible Fan

** Estimated



F887-72-BN 72"
F887-96-BN 96" *(Shown)*

F887-72-ORB 72"
F887-96-ORB 96"
See Next Page



XTREME

This industrial size fan lends itself to almost any setting. Xtreme's clean, sleek, contemporary design with a DC motor and a choice of sizes makes it perfect for large areas.

FEATURES

- 4° Blade Pitch • 9-Blades 72" or 96" Sweep • DC 165 x 25mm Motor
- 6" Downrod • Aluminum Blades • Install with Blades at least 10' above the Floor
- Special Hand Held Remote Control System Included - RC400

72" ENERGY GUIDE INFORMATION**

(All estimates based on typical use, excluding lights)

Energy Use: 23 Watts

- Airflow 6,134 Cubic Feet Per Minute

Airflow Efficiency: 270 Cubic Feet Per Minute Per Watt

96" ENERGY GUIDE INFORMATION**

(All estimates based on typical use, excluding lights)

Energy Use: 31 Watts

- Airflow 13,080 Cubic Feet Per Minute

Airflow Efficiency: 429 Cubic Feet Per Minute Per Watt

F887-72-ORB 72" • Brushed Nickel Finish • Silver Blades

F887-96-ORB 96" • Brushed Nickel Finish • Silver Blades



RC400

For Details


See Page(s): 320



BOND

Compatible Fan

XTREME



F887-72-ORB 72"
F887-96-ORB 96" *(Shown)*

F887-72-BN 72"
F887-96-BN 96"
See Previous Page



NINETY-NINE
with LED Light

F899L-DK

F899L-DK • Distressed Koa Finish • Distressed Koa Blades • Etched Opal Glass


DC MOTOR

LED

WWW.MINKAIRE.COM

NINETY-NINE

with LED Light



F899L-BN/SL



F899L-ORB

F899L-DK
See Previous Page



NINETY-NINE

with LED Light

Minka-Aire® introduces our Ninety-Nine fan, featuring a total of 99 inches in diameter! A refreshing transitional design featuring 9-blades, 26 watt LED and a DC motor. Ideal for residential and commercial use. Includes a six speed hand held remote control and is reversible for winter and summer.

FEATURES

- Variable Blade Pitch • 9-Blades 99" Sweep • DC 172 x 25mm Motor • 6" Downrod
- Integrated LED Light Uses 26W LED (Included) 3 Year Warranty • 1,899 Lumens • 2,700K
- CRI 81 • Special Hand Held Remote Control System Included - RC600

U.S. Patent(s): D806,856; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 33 Watts
- Airflow 11,871 Cubic Feet Per Minute
- Airflow Efficiency: 385 Cubic Feet Per Minute Per Watt

- F899L-ORB** • Oil Rubbed Bronze Finish • Toned Tobacco Blades • Etched Opal Glass
- F899L-BN/SL** • Brushed Nickel Finish • Silver Blades • Etched Opal Glass
- F899L-DK** • Distressed Koa Finish • Distressed Koa Blades • Etched Opal Glass




RC600
For Details
See Page(s): 320



BOND
Compatible Fan

** Estimated



F843-SL

WAVE

A truly unique design that draws inspiration from the ocean's graceful and tubular wave formations.

FEATURES

- Variable Blade Pitch • 3-Blades 52" Sweep • 6" Downrod
- Hand Held Remote Control System Included

U.S. Patent(s): D715,419; D715,421

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 43 Watts

- Airflow 3,229 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 76 Cubic Feet Per Minute Per Watt

F843-SL • Silver Finish

F843-DK • Distressed Koa Finish

F843-WH • White Finish




RCS213

For Details
See Page(s): 320



BOND
Compatible Fan

WAVE



F843-DK



F843-WH





F541L-SL
Indoor/Outdoor

CONE

with LED Light

The Cone lends an iconic presence to both indoor and outdoor settings for those who are looking for a blast from the past. This standard amongst designs offers a three, four and five blade option to suit everyone's preference as well as a clear and hooded light shade to create different lighting options.

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 20W Dimmable LED (Included) 3 Year Warranty
- 1,100 Lumens • 3,000K • CRI 90 • Optional Clear Lens in box • **Convertible into 3, 4 or 5 Blade**
- Special Hand Held Remote Control System Included - RC400
- Indoor/Outdoor Use - ETL Listed for Wet Locations

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$8
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 29 Watts
- Airflow 5,625 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 194 Cubic Feet Per Minute Per Watt

F541L-SL • Silver Finish • Silver Blades • Removable Silver Metal Ring • Etched Lens

F541L-ORB • Oil Rubbed Bronze Finish • Removable Oil Rubbed Bronze Metal Ring
• Medium Maple Blades • Etched Lens

F541L-WH • White Finish • White Blades • Removable White Metal Ring • Etched Lens



RC400

For Details
See Page(s): 320



BOND
Compatible Fan

CONE

with LED Light



F541L-ORB
Shown with 4-Blade Option
Indoor/Outdoor



F541L-WH
Shown with 3-Blade Option
Indoor/Outdoor



F541L-SL
Shown with Removable Metal Ring
Indoor/Outdoor

LED

DC MOTOR



minkaAire



F684L-MBK/BN

CLEAN

with LED Light

Designed with ultra-sophistication and minimalistic styling, Clean utilizes a unique eye catching blade arm that links the cylindrical fan body to its five blades. Body and the blades move in unison creating a distinctive look. Clean has an integrated 10 watt LED light and an energy efficient DC motor that provides significant air flow.



F684L-MBK/BN • Matte Black with Brushed Nickel Finish • Urban Walnut Blades • Etched Lens

LED DC MOTOR

minkaAire®



F684L-ORB/TB

CLEAN

with LED Light

Designed with ultra-sophistication and minimalistic styling, Clean utilizes a unique eye catching blade arm that links the cylindrical fan body to its five blades. Body and the blades move in unison creating a distinctive look. Clean has an integrated 10 watt LED light and an energy efficient DC motor that provides significant air flow.

FEATURES

- 12° Blade Pitch • 5-Blades 60" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 10W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 80
- Special Hand Held Remote Control System Included - RC400 • Cap for Non-Light Use (Included)

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

Energy Use: 57 Watts

- Airflow 10,948 Cubic Feet Per Minute

Airflow Efficiency: 193 Cubic Feet Per Minute Per Watt

F684L-GI/BN • Grey Iron/Brushed Nickel Finish • Grey Iron Finish Blades • Etched Lens

F684L-ORB/TB • Oil Rubbed Bronze/Toned Brass Finish • Urban Walnut Blades • Etched Lens

F684L-PN • Polished Nickel Finish • Silver Blades • Etched Lens

F684L-MBK/BN • Matte Black with Brushed Nickel Finish • Urban Walnut Blades • Etched Lens
(Shown on previous page)



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

CLEAN
with LED Light



F684L-GI/BN



F684L-PN
Shown with Cap for Non-Light Use

AVIATION LED

with LED Light



F853L-BN/DK • Brushed Nickel Finish • Distressed Koa Blades • Etched Lens



F853L-BN/DK

AVIATION LED

with LED Light

Inspired by the classic form of vintage aircraft propellers, our Aviation fans have an updated appeal, addressing a new audience with sleek, elegant lines and a combination of finish techniques compatible with today's trends. The new Aviation LED features an integrated 15 watt LED light.



AVIATION LED

with LED Light

F853L-BN/AMP

Inspired by the classic form of vintage aircraft propellers, our Aviation fans have an updated appeal, addressing a new audience with sleek, elegant lines and a combination of finish techniques compatible with today's trends. The new Aviation LED features an integrated 15 watt LED light.

FEATURES

- Variable Blade Pitch • 3-Blades 60" Sweep • DC 120 x 25mm Motor • 6" Downrod
 - 15W LED • 955 Lumens • 80 CRI • Special Hand Held Remote Control System Included - RC500
- U.S. Patent(s): D721,429; D721,800; D726,298; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$5
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 20 Watts
- Airflow 3,703 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 190 Cubic Feet Per Minute Per Watt

- F853L-BN/AMP** • Brushed Nickel Finish • Ash Maple Blades • White Lens
F853L-BN/MM • Brushed Nickel Finish • Medium Maple Blades • White Lens
F853L-BN/SL • Brushed Nickel Finish • Silver Blades • White Lens
F853L-BN/WH • Brushed Nickel Finish • White Blades • White Lens
F853L-BN/DK • Brushed Nickel Finish • Distressed Koa Blades • White Lens
(Shown on previous page)



RC500
For Details
See Page(s): 320



BOND
Compatible Fan

AVIATION LED

with LED Light



F853L-BN/MM



F853L-BN/WH



F853L-BN/SL



F853-BN/DK



F853-RW

F853-BN/DK
See Opposite Page

AVIATION

Inspired by the classic form of vintage aircraft propellers, our Aviation fan has an updated appeal that addresses a new audience with sleek, elegant lines and a combination of finish techniques that work for all of today's trends.

FEATURES

- Variable Blade Pitch • 3-Blades 60" Sweep • DC 120 x 25mm Motor • 6" Downrod
- Special Hand Held Remote Control System Included - RC500

U.S. Patent(s): D721,429; D721,800; D726,298

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$5
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 20 Watts
- Airflow 3,703 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 190 Cubic Feet Per Minute Per Watt

- F853-BN/DK** • Brushed Nickel Finish • Distressed Koa Blades
- F853-RW** • Rosewood Finish • Rosewood Blades



RC500
For Details
See Page(s): 320



BOND
Compatible Fan




F853-BN/MM

AVIATION

F853-BN/MM • Brushed Nickel Finish • Medium Maple Blades
F853-WH • White Finish • White Blades
F853-BN/SL • Brushed Nickel Finish • Silver Blades


AVIATION



F853-WH



F853-BN/SL



F787-SL
Shown with optional
K9787L-SL LED Light Kit
Indoor/Outdoor



F787-ORB
Indoor/Outdoor



F787-WHF
*Shown with optional
K9787L-WHF LED Light Kit
Indoor/Outdoor*



F787-BNW
Indoor/Outdoor

F787-SL
*See Opposite Page
Indoor/Outdoor*

SIMPLE 52"

So simple! We gave this wonderful design a name that best denotes it's spirit! Incredibly delicate and nearly invisible. This design best displays the advancement in technology with indoor/outdoor use, DC motor, optional LED light kit and a hand held remote.

FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9787L Available (Sold Separately. Page(s): 319)
- Indoor/Outdoor Use ETL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 20 Watts
- Airflow 3,633 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 184 Cubic Feet Per Minute Per Watt

- F787-SL** • Silver Finish • Silver Blades
- F787-BNW** • Brushed Nickel Wet Finish • Silver Blades
- F787-ORB** • Oil rubbed Bronze Finish • Medium Maple Blades
- F787-WHF** • Flat White Finish • Flat White Blades



RC400
For Details
See Page(s): 320



BOND
Compatible Fan





F786-ORB
Indoor/Outdoor

SIMPLE 44"

So simple! We gave this wonderful design a name that best denotes it's spirit! Incredibly delicate and nearly invisible. This design best displays the advancement in technology with indoor or outdoor use, DC motor, optional LED light kit and a hand held remote.

FEATURES

- 26° Blade Pitch • 3-Blades 44" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9787L Available (Sold Separately. Page(s): 319)
- Indoor/Outdoor Use ETL Listed for Wet Locations

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$8
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 29 Watts
- Airflow 3,572 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 122 Cubic Feet Per Minute Per Watt

- F786-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades
- F786-BNW** • Brushed Nickel Wet Finish • Silver Blades
- F786-SL** • Silver Finish • Silver Blades
- F786-WHF** • Flat White Finish • Flat White Blades



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

SIMPLE 44"



F786-BNW
Indoor/Outdoor



F786-WHF
*Shown with optional
K9787L-WHF LED Light Kit*
Indoor/Outdoor



F786-SL
Indoor/Outdoor



TIMBER

with LED Light



F847L-HBZ/AW



F847L-HBZ/MP



TIMBER

with LED Light

With the continued rise in a natural look within today's home, Timber's real Tung wood blades accomplish a warmth every home desires. With its 84" blades, its energy efficient DC motor and an integrated 26 watt LED light, you can't miss.

FEATURES

- 14° Blade Pitch • 3-Blades 84" Sweep • DC 172x25mm Motor • 6" Downrod
- Solid Wood Blades • Integrated LED Light Uses 26W LED (Included) 3 Year Warranty
- 1,899 Lumens • 2,700K • CRI 81
- Special Hand Held Remote Control System Included - RC600

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 25 Watts
- Airflow 8,100 Cubic Feet Per Minute
- Airflow Efficiency: 324 Cubic Feet Per Minute Per Watt

- F847L-HBZ/AW** • Heirloom Bronze • Aged Boardwalk Blades • Etched Lens
- F847L-HBZ/MP** • Heirloom Bronze • Maple Blades • Etched Lens



RC600
For Details
See Page(s): 320



BOND
Compatible Fan

** Estimated

GEAR

with LED Light



F736L-BS/SDBK



F736L-BS/WHF



F736L-PN/BS



F736L-PN/ORB

GEAR

with LED Light

Holding court as the centerpiece of your living space, Gear demands attention with its bold columns and art deco inspired lines. A three-bladed fan, it is built with advanced energy efficient technology with a DC motor and 18 watt LED light.

FEATURES

- 14° Blade Pitch • 3-Blades 54" Sweep • DC 125 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 18W LED (Included) 3 Year Warranty • 1,400 Lumens • 3,000K • CRI 80
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 20 Watts
- Airflow 4,953 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 249 Cubic Feet Per Minute Per Watt

F736L-PN/ORB • Polished Nickel/Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Etched Glass

F736L-BS/SDBK • Brushed Steel/Sand Black Finish • Matte Black Blades • Etched Glass

F736L-PN/BS • Polished Nickel/Brushed Steel Finish • Silver Blades • Etched Glass

F736L-BS/WHF • Brushed Steel/Flat White Finish • Flat White Blades • Etched Glass



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

** Estimated

F524-WHF





F524-ABD



F524-DK



F524-ORB

F524-WHF
See Opposite Page

ROTO

Roto features a sleek and contemporary design with a classic industrial look. Well edited and an impeccably executed design features a slight "fold" construction along the length of the blades to increase the flow of air. A perfect marriage of form and function.

FEATURES

- 22° Blade Pitch • 3-Blades 52" Sweep • 6" Downrod • Aluminum Construction
- 2 Wire Wall Control System Included - WC105-WH • Convertible to Electronic Control System

U.S. Patent(s): D750,221; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 31 Watts
- Airflow 3,090 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 101 Cubic Feet Per Minute Per Watt

- F524-WHF** • Flat White Finish • Flat White Blades
- F524-ABD** • Brushed Aluminum Finish • Silver Blades
- F524-DK** • Distressed Koa Finish • Distressed Koa Blades
- F524-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades



WC105-WH
For Details
See Page(s): 323



F903L-SBR/MBK

ARTEMIS™ IV

with LED Light

Our next generation of Artemis™ continues the tradition of curves and curls lending the feel of kinetic sculpture to any contemporary setting. An integrated 20 watt LED light provides energy efficient illumination. This 4-blade gem is offered in new finish selections, providing a uniqueness all its own.

ARTEMIS™ IV

with LED Light



F903L-SBR/MBK • Soft Brass Finish • Matte Black Blades • Etched Lens

LED **DC MOTOR**

minkaAire.



F903L-BN/SL

ARTEMIS™ IV

with LED Light

Our next generation of Artemis™ continues the tradition of curves and curls lending the feel of kinetic sculpture to any contemporary setting. An integrated 20 watt LED light provides energy efficient illumination. This 4-blade gem is offered in new finish selections, providing a uniqueness all its own.

FEATURES

- Variable Blade Pitch • 4-Blades 64" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 20W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 90
- Special Hand Held Remote Control System Included - RC400 • Cap for Non-Light Use (Included)

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 52 Watts
- Airflow 8,520 Cubic Feet Per Minute
- Airflow Efficiency: 166 Cubic Feet Per Minute Per Watt

F903L-BN/SL • Brushed Nickel Finish • Silver Blades • Etched Lens
F903L-ORB • Oil Rubbed Bronze Finish • Toned Tobacco Blades • Etched Lens
F903L-GM/MBK • Gun Metal Finish • Matte Black Blades • Etched Lens
F903L-SBR/MBK • Soft Brass Finish • Matte Black Blades • Etched Lens
(Shown on previous page)



RC400

For Details
See Page(s): 320




BOND
Compatible Fan

ARTEMIS™ IV

with LED Light



F903L-ORB



F903L-GM/MBK
Shown with Cap for Non-Light Use



F617L-ORB/AB



F617L-BN

F617L-GM

See Opposite Page

RAPTOR

with LED Light

This contemporary design is coupled with the energy saving advancements of DC motor technology and an integrated 17 watt LED light source. An option of three transitional finishes.

FEATURES

- 12° Blade Pitch • 5-Blades 60" Sweep • 6" Downrod • DC 172 x 12mm Motor
- Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 80
- Special Hand Held Remote Control System Included - RC600

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$5

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 19 Watts

- Airflow 4,183 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 228 Cubic Feet Per Minute Per Watt

F617L-GM • Gun Metal Finish • Gun Metal Finish fBlades • Etched Opal Glass

F617L-ORB/AB • Oil Rubbed Bronze/Antique Brass Finish • Toned Tobacco Blades • Tinted Opal Glass

F617L-BN • Brushed Nickel Finish • Silver Blades • Etched Opal Glass



RC600

For Details See Page(s): 320



BOND Compatible Fan



F617L-GM



F753-KA

JAVA

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments.

FEATURES

- 14° Blade Pitch • 3-Blades 54" Sweep • 6" Downrod
- Hand Held Remote Control System Included • Indoor/Outdoor Use - UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 32 Watts
- Airflow 4,113 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 128 Cubic Feet Per Minute Per Watt

- F753-KA** • Kocoo Finish • Kocoo Blades
- F753-PN** • Polished Nickel Finish • Silver Blades
- F753-WHF** • Flat White Finish • Flat White Blades
- F753-BNW** • Brushed Nickel Wet Finish • Silver Blades



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan



F753-PN
(Finish for Indoor Use Only)




F753-WHF



F753-BNW





MOJAVE

with LED Light

The Mojave's focus, inspired by rolling dunes of the California desert, provides a clean, cool appearance for the hottest environments. The variable pitch blades, powered by the latest DC technology, will leave you feeling anything but desolate.



F829L-CH/CH

F829L-CH/CH • Chrome Finish • Chrome Blades • White Lens



F829L-WHF

MOJAVE

with LED Light

The Mojave's focus, inspired by rolling dunes of the California desert, provides a clean, cool appearance for the hottest environments. The variable pitch blades, powered by the latest DC technology, will leave you feeling anything but desolate.

FEATURES

- Variable Blade Pitch • 3-Blades 56" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 20W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 90
- Special Hand Held Remote Control System Included - RC400

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 31 Watts
- Airflow 5,127 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 164 Cubic Feet Per Minute Per Watt

- F829L-CH/SL** • Chrome Finish • Silver Blades • White Lens
- F829L-WHF** • Flat White Finish • Flat White Blades • White Lens
- F829L-SL** • Silver Finish • Silver Blades • White Lens
- F829L-CH/CH** • Chrome Finish • Chrome Blades • White Lens *(Shown on previous page)*



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

MOJAVE

with LED Light



F829L-CH/SL



F829L-SL

LED DC MOTOR

minkaAire.

F803L-RD





F803L-DK

F803L-RD
See Opposite Page

ARTEMIS™

with LED Light

The distinct profile of the Artemis™ is captured by the Flying Vanes™ that incorporate the fan housing. A true design statement!

Winner of the 2005 Chicago Athenaeum:
Museum of Architecture and Design's Good Design Award.

FEATURES

- Contoured Aerodynamic Vanes • Variable Blade Pitch • 3-Vanes 58" Sweep • 6" Downrod
 - Integrated LED Light Uses 17W Dimmable LED (Included) 3 Year Warranty
 - 800 Lumens • 3,000K • CRI 81
 - Full Function Wall Control System Included • Cap for Non-Light Use (Included)
- U.S. Patent(s): D535,011; D535,015; D535,387; D535,388; D536,083; 7,481,626

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$17
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 61 Watts
- Airflow 3,983 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 65 Cubic Feet Per Minute Per Watt

- F803L-RD** • High Gloss Pure Red Finish • Etched Opal Glass
- F803L-DK** • Distressed Koa Finish • Tinted Opal Glass

LED

WWW.MINKAIRE.COM



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan




F803L-LN

ARTEMIS™

with LED Light

- F803L-LN** • Liquid Nickel Finish • Etched Opal Glass
- F803L-MG** • Mahogany Finish • Etched Opal Glass
- F803L-CPBR** • Copper Bronze Finish • Tinted Opal Glass
- F803L-SL** • Silver Finish • Etched Opal Glass

ARTEMIS™



F803L-MG



F803L-SL



F803L-CPBR

LED



F803L-MP

ARTEMIS™

with LED Light

- F803L-MP** • Maple Finish • Etched Opal Glass
- F803L-TL** • Translucent Finish • Etched Opal Glass
- F803L-BK** • High Gloss Black Finish • Etched Opal Glass
- F803L-WH** • High Gloss White Finish • Etched Opal Glass

ARTEMIS™



F803L-TL




F803L-WH



F803L-BK

LED



F905L-LN

ARTEMIS™ XL5 LED

The big brother of our original Artemis™, the distinct profile of the Artemis™ XL5 is captured by the five Flying Vanes™ that encase the fan housing - creating a true design statement!



F905L-LN • Liquid Nickel Finish • Etched Opal Glass

DC MOTOR

LED

WWW.MINKA.AIRE.COM



F905L-DK

ARTEMIS™ XL5

with LED Light

The big brother of our original Artemis™, the distinct profile of the Artemis™ XL5 is captured by the five Flying Vanes™ that encase the fan housing - creating a true design statement!

FEATURES

- Variable Blade Pitch • 5-Blades 62" Sweep • DC 172 x 25mm Motor • 6" Downrod
- Integrated Light Uses 17W Dimmable LED (Included) 3 Year Warranty
- 1,100 Lumens • 2,700K • CRI 80 • Special Hand Held Remote Control System Included - RC600
- Cap for Non-Light Use (Included)

U.S. Patent(s): D721,430

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$7
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 26 Watts
- Airflow 4,820 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 183 Cubic Feet Per Minute Per Watt

F905L-DK • Distressed Koa Finish • Tinted Opal Glass

F905L-SL • Silver Finish • Etched Opal Glass

F905L-WH • White Finish • Etched Opal Glass

F905L-LN • Liquid Nickel Finish • Etched Opal Glass (Shown on previous page)




RC600

For Details
See Page(s): 320



BOND
Compatible Fan

ARTEMIS™ XL5




F905L-SL



F905L-WH
Shown with Cap for Non-Light Use

SYMBIO

with LED Light



F828-BN



F828-ORB



F828-WHF



F828-BN/WH



F828-BN/DW

SYMBIO

with **LED** Light

This clean contemporary powerhouse delivers the air flow of larger fans using DC motor technology to keep energy consumption to a minimum while the integrated DC LED light provides energy efficient illumination.

FEATURES

- 15° Blade Pitch • 5-Blades 56" Sweep • DC 125 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 16W DC LED (Included) 3 Year Warranty • 710 Lumens • 3,000K
- CRI 80 • Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): D788,283; D788,286; D802,114; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 21 Watts
- Airflow 4,043 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 194 Cubic Feet Per Minute Per Watt

- F828-BN/DW** • Brushed Nickel Finish • Dark Walnut Blades • Etched Glass
- F828-BN** • Brushed Nickel Finish • Silver Blades • Etched Glass
- F828-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Glass
- F828-WHF** • Flat White Finish • Flat White Blades • Etched Glass
- F828-BN/WH** • Brushed Nickel Finish • White Blades • Etched Glass



RC400

For Details
See Page(s): 320



BOND
Compatible Fan



F739L-BN

PANCAKE XL LED

with LED Light

A 62" version of our successful Pancake fan includes an integrated 20 watt LED light. Our Pancake XL LED ceiling fan magically houses all the necessary components of a high performance ceiling fan into the same slim body. Minimal, elegant and smooth, the profile is narrow, allowing for an unobtrusive, non-competing addition to any room. **Go big!**



F739L-BN • Brushed Nickel Finish • Silver Blades • White Lens

DC MOTOR **LED**

minkaAire.

PANCAKE XL LED

with LED Light



F739L-WHF



F739L-DK



F739L-SL

PANCAKE XL LED

with LED Light

A 62" version of our successful Pancake fan includes an integrated 20 watt LED light. Our Pancake XL LED ceiling fan magically houses all the necessary components of a high performance ceiling fan into the same slim body. Minimal, elegant and smooth, the profile is narrow, allowing for an unobtrusive, non-competing addition to any room. **Go big!**

FEATURES

- 12° Blade Pitch • 4-Blades 62" Sweep • DC 188 x 14mm Motor
- 6" Internally Threaded Downrod • Max Ceiling Slope Angle 18° • 20W LED
- 1300 Lumens • 80 CRI • Special Hand Held Remote Control System Included - RC500

U.S. Patent(s): D750,215; D750,219; 9,810,227; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$4

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 13 Watts

- Airflow 4,949 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 395 Cubic Feet Per Minute Per Watt

F739L-SL • Silver Finish • Silver Blades • White Lens

F739L-WHF • Flat White Finish • Flat White Blades • White Lens

F739L-DK • Distressed Koa Finish • Distressed Koa Blades • White Lens

F739L-BN • Brushed Nickel Finish • Silver Blades • White Lens



RC500

For Details

See Page(s): 320



BOND

Compatible Fan

** Estimated
See Page 84 for Pancake Family

PANCAKE



F738-SL



F738-WHF



F738-DK



F738-ORB

PANCAKE

Our Pancake ceiling fan magically houses all the needed components of a high performance ceiling fan in a slim 3-inch deep body. Minimal, elegant and smooth, the profile is narrow, allowing for an unobtrusive, non-competing addition to any room.

FEATURES

- 12° Blade Pitch • 4-Blades 52" Sweep • 6" Internally Threaded Downrod
 - Max Ceiling Slope Angle 18° • Full Function Hand Held Remote Control System Included
- U.S. Patent(s): D750,215; D750,219; 9,810,227; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 40 Watts
- Airflow 2,464 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 62 Cubic Feet Per Minute Per Watt

- F738-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades
- F738-SL** • Silver Finish • Silver Blades
- F738-WHF** • Flat White Finish • Flat White Blades
- F738-DK** • Distressed Koa Finish • Distressed Koa Blades



RC212
For Details
See Page(s): 320



BOND
Compatible Fan



F844-SL



F844-WH



F844-DK

F844-SL
See Opposite Page

LIGHT WAVE

with LED Light

Light Wave is the next generation of our highly successful, ground-breaking Wave fan. Its energy-efficient LED light source integrates light without compromising design.

FEATURES

- Variable Blade Pitch • 3-Blades 52" Sweep • 6" Downrod
- Integrated Light Uses 17W Dimmable LED (Included) 3 Year Warranty
- 1,100 Lumens • 3,000K • CRI 80 • Hand Held Remote Control System Included
- Replacement LED Assembly (Part #6F844LK01)

U.S. Patent(s): D750,213; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 40 Watts
- Airflow 3,068 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 77 Cubic Feet Per Minute Per Watt

- F844-SL** • Silver Finish • Silver Blades • Etched Lens
- F844-WH** • White Finish • White Blades • Etched Lens
- F844-DK** • Distressed Koa Finish • Distressed Koa Blades • Etched Lens



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan

LED



F834L-BS/PN

F834L-ORB/PN

See Opposite Page

METROPOLIS

with LED Light

The Metropolis shows off lustrous lines and gorgeous details for a striking fan display that brings out the best in modern spaces. It features polished metal blade irons that spin 3-blades between low, medium and high speed settings. The Metropolis includes a hand held remote and pushes over 5,000 cubic feet of air per minute at its maximum speed. 15 watt LED light kit included for additional light.

FEATURES

- 14° Blade Pitch • 3-Blades 56" Sweep • 153 x 22mm Motor • 6" Downrod
- Integrated LED Light Uses 15W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 90
- Full Function Hand Held Remote Control System Included

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$14
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 50 Watts
- Airflow 4,175 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 84 Cubic Feet Per Minute Per Watt

- F834L-BS/PN** • Brushed Steel/Polished Nickel • Silver Blades • Etched White Glass
F834L-ORB/PN • Oil Rubbed Bronze/Polished Nickel • Oil Rubbed Bronze Blades • Etched White Glass



RC212
For Details
See Page(s): 320



BOND
Compatible Fan



F834L-ORB/PN

METROPOLIS
with LED Light



FORCE

with LED Light

F838L-DK

A sleek, well proportioned, contemporary design featuring an integrated 20 watt LED with a 60-inch sweep. The Force by Minka-Aire® will make a design statement in any décor.

FEATURES

- Variable Blade Pitch • 3-Blades 60" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 20W LED (Included) 3 Year Warranty • 750 Lumens • 3,000K • CRI 90
- Special Hand Held Remote Control System Included - RC400
- Custom LED Light Kit K9838L Available (Sold Separately. Page(s): 319)

U.S. Patent(s): D807,492; D807,493; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$8
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 30 Watts
- Airflow 2,364 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 79 Cubic Feet Per Minute Per Watt

F838L-DK • Distressed Koa Finish • Distressed Koa Blades • Etched Lens

F838L-WH • White Finish • White Blades • Etched Lens

F838L-SL • Silver Finish • Silver Blades • Etched Lens



RC400

For Details
See Page(s): 320



BOND
Compatible Fan

FORCE

with LED Light



F838L-WH



F838L-SL
*Shown with Optional
K9838L-SL LED Light Kit*



F521-ABD

ALUMA

The Aluma is minimal in form with a youthful soft contemporary twist that makes it a fan with universal appeal.

FEATURES

- 12° Blade Pitch • 4-Blades 52" Sweep • 6" Downrod • All Aluminum Construction
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- 4-Speed Full Range Dimmer Included - WC106-WH • Convertible to Electronic Control System
- Cap for Non-Light Use (Included)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 37 Watts
- Airflow 2,910 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 78 Cubic Feet Per Minute Per Watt

- F521-ABD** • Brushed Aluminum Finish • Silver Blades • Etched Opal Glass
- F521-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass
- F521-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass



WC106-WH
For Details
See Page(s): 323

ALUMA



F521-ORB



F521-WHF
Shown with Cap for Non Light Use



F543L-DK

SWEPT

with LED Light

This contemporary design provides four variable pitch blades and a tiered motor housing for styling sophistication. SWEPT by Minka-Aire® has all the latest advancements in technology with a DC motor and 20 watt LED light. A hand held remote control is included.



F543L-DK • Distressed Koa Finish • Distressed Koa Blades • Etched Lens

LED **DC MOTOR**



F543L-SL

SWEPT

with LED Light

This contemporary design provides four variable pitch blades and a tiered motor housing for styling sophistication. SWEPT by Minka-Aire® has all the latest advancements in technology with a DC motor and 20 watt LED light. A hand held remote control is included.

FEATURES

- 14° Blade Pitch • 4-Blades 56" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 20W Dimmable LED (Included) 3 Year Warranty
- 1,100 Lumens • 3,000K • CRI 90 • Special Hand Held Remote Control System Included - RC400

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 42 Watts
- Airflow 8,177 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 195 Cubic Feet Per Minute Per Watt

- F543L-SL** • Silver Finish • Silver Blades • Etched Lens
- F543L-DK** • Distressed Koa Finish • Distressed Koa Blades • Etched Lens
(Shown on previous page)
- F543L-WHF** • Flat White Finish • Flat White Finish • Etched Lens
- F543L-KA** • Kocoo Finish • Kocoo Blades • Etched Lens



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

SWEPT

with LED Light



F543L-WHF



F543L-KA

LED DC MOTOR

minkaAire.

STACK

with LED Light



F849L-SL



F849L-BN/SL



F849L-WH

STACK

with LED Light

Inspired by a Danish architect of the 1920s, this three-tiered light shade system fan best exemplifies the mid-century modern trends of today's interior design. The STACK is equipped with three 56" blades and DC motor technology with a 21 watt DC LED downlight and a 10 watt LED uplight.

FEATURES

- 14° Blade Pitch • 3-Blades 56" Sweep • DC 125 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 21W Dimmable LED Downlight and 10W Dimmable LED Uplight (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 80
- Special Hand Held Remote Control System Included - RC400

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 20 Watts
- Airflow 3,899 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 190 Cubic Feet Per Minute Per Watt

- F849L-WH** • White Finish • White Blades • Etched Opal Glass
- F849L-SL** • Silver Finish • Silver Blades • Etched Opal Glass
- F849L-BN/SL** • Brushed Nickel Finish • Silver Blades • Etched Opal Glass



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

** Estimated

TEAR

with LED Light




F831L-SL



F831L-ORB



F831L-WHF



F831L-TD

TEAR

with LED Light

The Tear ceiling fan is designed to rejuvenate. Part of a collection of stylish and urbane fans being introduced in 2018, it blends contemporary form with reliable performance.

FEATURES

- Variable Blade Pitch • 3-Blades 60" Sweep • DC 120 x 20mm Motor • 6" Downrod
- Integrated LED Light Uses 15W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K
- CRI 80 • Special Hand Held Remote Control System Included - RC500

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 34 Watts
- Airflow 7,869 Cubic Feet Per Minute
- Airflow Efficiency: 237 Cubic Feet Per Minute Per Watt

- F831L-TD** • Tie Dye • Tie Dye Blades • Etched Lens
- F831L-SL** • Silver Finish • Silver Blades • Etched Lens
- F831L-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Etched Lens
- F831L-WHF** • Flat White Finish • Flat White Blades • Etched Lens



RC500
For Details
See Page(s): 320



BOND
Compatible Fan

** Estimated



F888-BNW

SLIPSTREAM

Sleek industrial styling destines this 8-bladed wonder to make a cool statement in any indoor or outdoor setting.

FEATURES

- 14° Blade Pitch • 8-Concave Blades 65" Sweep • DC 165 x 25mm Motor
- Galvanized Steel 6" Downrod • Stainless Steel Hardware and All Weather Blades
- Integrated Light Uses 1-18W GU24 Non-Dimmable Squat CFL (Included)
- Special Hand Held Remote Control System Included - RC400 • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D715,917

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 22 Watts
- Airflow 6,216 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 285 Cubic Feet Per Minute Per Watt

- F888-BNW** • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass
- F888-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass
- F888-DK** • Distressed Koa Finish • Distressed Koa Blades • Tinted Opal Glass
- F888-ORB** • Oil Rubbed Bronze • Oil Rubbed Bronze Blades • Tinted Opal Glass



RC400

For Details
See Page(s): 320




BOND
Compatible Fan


SLIPSTREAM



F888-WHF



F888-DK



F888-ORB

Shown with Cap for Non-Light Use





F726-BN/SL

SPECTRE

with LED Light

Versatile, industrial styling and creative details are the key to Spectre. The distinctive blade irons hug the fan body, providing a unique look compatible with contemporary environments.

FEATURES

- 14° Blade Pitch • 4-Blades 60" Sweep • DC 188 x 10mm Motor • 6" Downrod
- Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 80
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): D778,422; D779,052; D779,093; D792,577; D806,226; D808,513; Add'l U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 21 Watts
- Airflow 4,204 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 198 Cubic Feet Per Minute Per Watt

F726-BN/SL • Brushed Nickel Finish • Silver Blades • Clear Lens
F726-WHF/BN • Flat White/Brushed Nickel Finish • Flat White Blades • Clear Lens
F726-BN/ORG • Brushed Nickel/Orange Finish • Orange Blades • Clear Lens



RC400

For Details
See Page(s): 320



BOND
Compatible Fan

SPECTRE

with LED Light



F726-WHF/BN



F726-BN/ORG

LED DC MOTOR

minkaAire.



F726-ORB/AB

SPECTRE

with LED Light

F726-ORB/AB • Oil Rubbed Bronze/Antique Brass Finish • Toned Tobacco Blades • Clear Lens
F726-ORB/BN • Oil Rubbed Bronze/Brushed Nickel Finish • Oil Rubbed Bronze Blades • Clear Lens
F726-WHF/BN • Flat White/Brushed Nickel Finish • Flat White Blades • Clear Lens

SPECTRE

with LED Light



F726-ORB/BN



F726-WHF/BN

LED DC MOTOR

minkaAire.



F753L-BNW



F753L-KA



F753L-PN
(Finish for Indoor Use Only)



F753L-WHF

F753L-BNW
See Opposite Page

JAVA LED

with LED Light

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all indoor or outdoor environments. The Java LED features an integrated 17 watt LED light.

FEATURES

- 14° Blade Pitch • 3-Blades 54" Sweep • 6" Downrod
- Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 630 Lumens • 3,000K
- CRI 80 • Hand Held Remote Control System Included
- Indoor/Outdoor Use - UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 34 Watts
- Airflow 4,394 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 131 Cubic Feet Per Minute Per Watt

- F753L-BNW** • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass
- F753L-KA** • Kocoa Finish • Kocoa Blades • Etched Opal Glass
- F753L-PN** • Polished Nickel Finish • Silver Blades • Etched Opal Glass
- F753L-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan





F902L-CH

BLING

with LED Light

The Bling fan combines a sleek contemporary Chrome body and hardware with a relaxed lamp shade bedazzled with crystal. The integrated light is equipped with three - 4 watt LED. The ample wood blades, attached with gem-like faceted blade arms, provide significant air movement for any environment

FEATURES

- 14° Blade Pitch • 5-Blades 56" Sweep • DC 125 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 3-4W LED (Included) 3 Year Warranty • 1,100 Lumens • 2,700K • CRI 80
- Special Hand Held Remote Control System Included - RC400

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 33 Watts
- Airflow 6,000 Cubic Feet Per Minute
- Airflow Efficiency: 84 Cubic Feet Per Minute Per Watt

F902L-CH • Chrome Finish • Silver Blades • Crystal Glass



RC400
For Details
See Page(s): 320



BOND
Compatible Fan



F902L-CH



F519L-BN

CONCEPT™ II 52"

with LED Light

As the name implies, "a taste of things to come", simple in style, yet ingenious by design, the Concept™ II requires 75% less time and labor to assemble than conventional ceiling fans.

FEATURES

- 14° Blade Pitch • 3-Concave Blades 52" Sweep
 - Flush Mount - Ideal for Low Ceilings Total Hanging Depth 11½" with or without Light
 - Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K • CRI 80
 - Full Function Hand Held Remote Control System Included • Cap for Non-Light Use (Included)
- U.S. Patent(s): 7,008,192

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 41 Watts
- Airflow 3,759 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt

- F519L-BN** • Brushed Nickel Finish • Silver Blades • White Opal Glass
- F519L-WH** • White Finish • White Blades • White Opal Glass
- F519L-ORB** • Oil Rubbed Bronze Finish • Taupe Blades • White Opal Glass
- F519L-MG** • Mahogany Finish • Mahogany Blades • White Opal Glass
- F519L-PN** • Polished Nickel Finish • Silver Blades • White Opal Glass



RCS212
For Details
See Page(s): 320



BOND
Compatible Fan

CONCEPT™ II 52"

with LED Light



F519L-ORB



F519L-WH



F519L-MG



F519L-PN

LED



F518L-ORB

CONCEPT™ II 44"

with LED Light

As the name implies, "a taste of things to come", simple in style, yet ingenious by design, the Concept™ II requires 75% less time and labor to assemble than conventional ceiling fans.

FEATURES

- 14° Blade Pitch • 3-Concave Blades 44" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 11½" with or without Light
- Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K • CRI 80
- Full Function Hand Held Remote Control System Included • Cap for Non-Light Use (Included)

U.S. Patent(s): 7,008,192

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$8

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 29 Watts

- Airflow 2,629 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt

F518L-ORB • Oil Rubbed Bronze Finish • Taupe Blades • White Opal Glass

F518L-WH • White Finish • White Blades • White Opal Glass

F518L-PN • Polished Nickel Finish • Silver Blades • White Opal Glass

F518L-BN • Brushed Nickel Finish • Silver Blades • White Opal Glass



RCS212

For Details
See Page(s): 320



BOND
Compatible Fan

CONCEPT™ II 44"

with LED Light



F518L-PN
Shown with Cap for Non-Light Use



F518L-WH



F518L-BN

LED



F823-DK

WING

A unique 52" single wing fan that transcends all conventional designs.

Winner of the 2010 Chicago Athenaeum: Museum of Architecture and Design's Good Design Award.

FEATURES

- Variable Blade Pitch • 1-Wing 52" Sweep • DC 125 x 30mm Motor • 6" Downrod
 - Special Hand Held Remote Control System Included - RC400
- U.S. Patent(s): D678,977; 9,004,863; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$5
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 19 Watts
- Airflow 3,855 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 205 Cubic Feet Per Minute Per Watt

- F823-DK** • Distressed Koa Finish
- F823-SL** • Silver Finish
- F823-WH** • High Gloss White Finish



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

WING



F823-SL



F823-WH

DC MOTOR



minkaAire.



F745-ORB

*Shown with Medium Maple Blades
Reversible to Dark Walnut Blades*

SABOT

with LED Light

Sabot's sleek, contemporary design has created a vision for today's interiors. Its low profile provides maximum air management in rooms with minimal ceiling heights.

The Sabot's integrated, energy efficient LED light will bring any room to life.

FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • DC 172 x 12mm Motor • 6" Downrod
- Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 80
- Special Hand Held Remote Control System - RC600

U.S. Patent(s): D795,412; D804,646 Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 22 Watts
- Airflow 2,797 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 126 Cubic Feet Per Minute Per Watt

F745-ORB • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades • White Lens

F745-BN • Brushed Nickel Finish • Silver Blades • White Lens

F745-DK • Distressed Koa Finish • Reversible Medium Maple/Dark Walnut Blades • White Lens



RC600
For Details
See Page(s): 320



BOND
Compatible Fan

SABOT

with LED Light



F745-BN



F745-DK

*Shown with Dark Walnut Blades
Reversible to Medium Maple Blades*

FLYTE®



F531-L-BN



F531-L-WH



F531-L-BN/MG
Shown with Cap for Non-Light Use

FLYTE®

The essence of simplicity and elegance, the Flyte® fan's combination of integrated halogen light and distinctive hanging system gives this contemporary design a compelling and sophisticated presence.

Winner of the 2001 Chicago Athenaeum:
Museum of Architecture and Design's Good Design Award

FEATURES

- 14° Blade Pitch • 3-Blades 56" Sweep • Includes 9" Downlink™ Hanging System with ½" I.D. Downrod
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Suitable for Installation on Vaulted Ceilings up to 21°
- Wall Control System Included • Cap for Non-Light Use (Included)
- Capable of using 3½" Downrod for Low Ceiling Application (Part #DR235-44 and #DR235-BN)

Accessory Blades Available. See Page(s): 334

Additional Downlink™ Options Available See Page(s): 330

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 44 Watts

- Airflow 4,389 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 100 Cubic Feet Per Minute Per Watt

F531-L-BN/MG • Brushed Nickel Finish • Mahogany Blades • White Opal Glass
• Mahogany Downlink™

F531-L-BN • Brushed Nickel Finish • Birdseye Maple Blades • White Opal Glass

F531-L-WH • White Finish • High Gloss White Blades • White Opal Glass



WC212

For Details

See Page(s): 321



BOND
Compatible Fan



F846-WHF

WAVE II

Wave II is a 2-blade addition to the distinctive designs of the Wave and the Light Wave series. The uncompromising design, though minimalistic, provides maximum air flow while becoming a conversation piece to enjoy for years to come.



F846-WHF • Flat White Finish

DC MOTOR

WWW.MINKA.AIRE.COM



F846-DK

WAVE II

Wave II is a 2-blade addition to the distinctive designs of the Wave and the Light Wave series. The uncompromising design, though minimalistic, provides maximum air flow while becoming a conversation piece to enjoy for years to come.

FEATURES

- Variable Blade Pitch • 2-Blades 60" Sweep • DC 168 x 15mm Motor • 6" Downrod
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 30 Watts
- Airflow 4,231 Cubic Feet Per Minute
- Airflow Efficiency: 144 Cubic Feet Per Minute Per Watt

- F846-DK** • Distressed Koa Finish
- F846-SL** • Silver Finish
- F846-WHF** • Flat White Finish *(Shown on previous page)*



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

WAVE II



F846-WHF



F846-SL



F410L-BS

SLANT

with LED Light

Designed with the futuristic styling of the late 1950s & early 1960s, Slant by Minka-Aire® harkens back to the mid-century modern era of architecture and technology. An integrated 18 watt LED light. Supported with three 36" slanted blades, this fan is best suited for smaller rooms, kitchens and bathrooms.

FEATURES

- 20° Blade Pitch • 3-Blades 36" Sweep • 120 x 20mm Motor • 6" Downrod
- Integrated LED Light Uses 18W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 80
- Wall Control System Included - WC110L

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 53 Watts
- Airflow 2,800 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 61 Cubic Feet Per Minute Per Watt

- F410L-BS** • Brushed Steel Finish • Silver Blades • Etched Opal Glass
- F410L-WH** • White Finish • White Blades • Etched Opal Glass
- F410L-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Etched Opal Glass



WC110L
For Details
See Page(s): 323

SLANT

with LED Light



F410L-WH



F410L-ORB

LED



F601-BS/MG

ACERO™

An evolution of form and function merging today's technology with contemporary styling, this fan comes with an integrated light.

Winner of the 1999 Chicago Athenaeum:
Museum of Architecture and Design's Good Design Award

FEATURES

- 14° Blade Pitch • 3-Concave Blades 52" Sweep • 6" Downrod • Unique Wire Form Design
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Full Function Wall Control System Included • Cap for Non-Light Use (Included)

U.S. Patent(s): 6,354,801; 6,517,316

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 45 Watts

- Airflow 4,092 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 91 Cubic Feet Per Minute Per Watt

F601-BS/MG • Brushed Steel/Mahogany Finish • Mahogany Blades • Opal Frosted Glass

F601-PN • Polished Nickel Finish • Silver Blades • Opal Frosted Glass

F601-ORB • Oil Rubbed Bronze Finish • Aaron Mahogany Blades • Opal Frosted Glass

F601-BS/BN • Brushed Steel/Brushed Nickel Finish • Silver Blades • Opal Frosted Glass



WCS212

For Details
See Page(s): 321



BOND
Compatible Fan



F601-PN



F601-ORB



F601-BS/BN
Shown with Cap for Non-Light Use

F594L-ORB



TRADITIONAL
CONCEPT™ 52"

130

with LED Light

minkaAire®



F594L-PW



F594L-WH

F594L-ORB
See Opposite Page

TRADITIONAL CONCEPT™ 52" with LED Light

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 10¾" Drop from Ceiling
- Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K
- CRI 80 • Full Function Wall Control System Included • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 40 Watts
- Airflow 3,638 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 91 Cubic Feet Per Minute Per Watt

- F594L-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass
- F594L-PW** • Pewter Finish • Dark Maple Blades • Opal Glass
- F594L-WH** • White Finish • White Blades • Opal Glass



RCS212
For Details
See Page(s): 320



BOND
Compatible Fan





F593L-PW

TRADITIONAL CONCEPT™ 44"

with LED Light

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

FEATURES

- 14° Blade Pitch • 3-Blades 44" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 10¾" Drop from Ceiling
- Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K • CRI 80
- Full Function Wall Control System Included • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 35 Watts
- Airflow 2,682 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 77 Cubic Feet Per Minute Per Watt

- F593L-PW** • Pewter Finish • Dark Maple Blades • Opal Glass
- F593L-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass
- F593L-WH** • White Finish • White Blades • Opal Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

TRADITIONAL CONCEPT™ 44"

with LED Light



F593L-ORB



F593L-WH
Shown with Cap for Non-Light Use



COMO™



F603-WH



F603-ORB



F603-BN

COMO™

Como™ is a harmonious, versatile design with clean, contemporary lines highlighted with subtle chrome, bronze and brushed nickel accents.

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod
- Integrated Halogen Light Uses 2-75W Mini-Can Halogen Bulbs (Included)
- Full Function Wall Control System Included

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$16
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 56 Watts
- Airflow 3,595 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 65 Cubic Feet Per Minute Per Watt

- F603-BN** • Brushed Nickel Finish • Silver Blades • Satin White Opal Glass
- F603-ORB** • Oil Rubbed Bronze Finish • Tobacco Blades • Satin White Opal Glass
- F603-WH** • White Finish • White Blades • Satin White Opal Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



F516L-ORB 44"
F517L-ORB 52"

CONCEPT™ I

with LED Light

FEATURES

- 14° Blade Pitch • 3-Concave Blades 44" or 52" Sweep • 6" Downrod
- Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K • CRI 80
- Full Function Hand Held Remote Control System Included • Cap for Non-Light Use (Included)

U.S. Patent(s): 7,008,192

Accessory Blades Available. See Page(s): 334

F516L ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$8

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 29 Watts

- Airflow 2,646 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt

F517L ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 40 Watts

- Airflow 3,764 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 93 Cubic Feet Per Minute Per Watt

- F516L-ORB 44"** • Oil Rubbed Bronze Finish • Taupe Blades • White Opal Glass
- F516L-PN 44"** • Polished Nickel Finish • Silver Blades • White Opal Glass
- F516L-WH 44"** • White Finish • White Blades • White Opal Glass
- F516L-BN 44"** • Brushed Nickel Finish • Silver Blades • White Opal Glass
- F517L-ORB 52"** • Oil Rubbed Bronze Finish • Taupe Blades • White Opal Glass
- F517L-PN 52"** • Polished Nickel Finish • Silver Blades • White Opal Glass
- F517L-WH 52"** • White Finish • White Blades • Etched White Glass
- F517L-BN 52"** • Brushed Nickel Finish • Silver Blades • White Opal Glass



RCS212
 For Details
 See Page(s): 320



BOND
 Compatible Fan

CONCEPT™ I

with LED Light



F516L-PN 44"
F517L-PN 52"




F516L-WH 44"
F517L-WH 52"



F516L-BN 44"
F517L-BN 52"
Shown with Cap for Non-Light Use

LED



F833-RD

KEWL

A traditional design, now morphed to a contemporary style, creating a synergistic blend that's perfect for numerous settings.

FEATURES

- 22° Blade Pitch • 3-Blades 52" Sweep • 6" Downrod
 - 2-Wire Installation Wall Control Included - WC105-WH • Convertible to Electronic Control System
- U.S. Patent(s): D715,418; D726,299

- Custom Finish Orders Accepted • 200 Piece Minimum Order Per Finish • 90 Day Lead Time

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 31 Watts
- Airflow 3,349 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 107 Cubic Feet Per Minute Per Watt



- F833-RD** • Red Finish
- F833-SL** • Silver Finish
- F833-BK** • Black Finish
- F833-WH** • White Finish



WC105-WH

For Details
See Page(s): 323


KEWL



F833-SL



F833-BK



F833-WH





F596-BN

CIRQUE™

Winner of the 2003 Chicago Athenaeum:
Museum of Architecture and Design's Good Design Award

FEATURES

- 14° Blade Pitch • 3-Blades 54" Sweep and 3-Blades 25" Sweep • 6" Downrod
- Integrated Halogen Light Uses 1-50W MR16 120V 2-Pin Halogen Bulb (Included)
- Full Function Wall Control System Included • Cap for Non-Light Use (Included)

U.S. Patent(s): D510,621; D513,316; D514,689; D524,433; D549,816

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 35 Watts
- Airflow 3,219 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 91 Cubic Feet Per Minute Per Watt

F596-BN • Brushed Nickel Finish • Silver Blades • Etched Glass
F596-PN/TL • Polished Nickel Finish • Translucent Blades • Etched Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



F596-PN/TL



F596-BN
Shown with Optional FB196-RYB Blades



F596-BN
Shown with Optional FB196-MG Blades

ZEN



F514-WH



F514-BN
Shown with Cap for Non-Light Use



F514-ORB

ZEN

A clean modern profile is accentuated in three finish options.

FEATURES

- 14° Blade Pitch • 4-Blades 52" Sweep • 6" Downrod
- Integrated Light Kit Uses 2-13W Non-Dimmable GU24 CFL Bulbs (Included)
- Full Function Hand Held Remote Control System Included • Cap for Non-Light Use (Included)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 45 Watts
- Airflow 4,102 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt

- F514-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass
- F514-WH** • White Finish • White Blades • White Frosted Glass
- F514-BN** • Brushed Nickel Finish • Silver Blades • White Frosted Glass



RCS212
For Details
See Page(s): 320



BOND
Compatible Fan



F513-BN

NEW ERA

Traditional in styling, yet defined by simple, soft lines.

FEATURES

- 14° Blade Pitch • 4-Blades 52" Sweep • 6" Downrod
- Full Function Hand Held Remote Control System Included
- Universal Light Kits Available (Part #K9380-1 and #K9380-2 Page(s): 311)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 45 Watts
- Airflow 3,373 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 75 Cubic Feet Per Minute Per Watt

- F513-BN** • Brushed Nickel Finish • Dark Walnut Blades
- F513-WH** • White Finish • White Blades
- F513-KA** • Kocoa Finish • Reversible Toned Medium Maple/Dark Maple Blades
- F513-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades



RCS212
For Details
See Page(s): 320



BOND
Compatible Fan

NEW ERA



F513-KA
*Shown with Toned Medium Maple Blades
Reversible to Dark Maple Blades*



F513-WH



F513-ORB





F598-ORB

AIRUS™

Airus™ is poetry in motion. Its graceful silhouette comfortably fits in any transitional setting. Featured uplight can be controlled independently of the halogen light below.

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod
- Integrated Halogen Uplight Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Full Function Wall Control System Independent Up/Downlight Included

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 48 Watts
- Airflow 3,158 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 66 Cubic Feet Per Minute Per Watt

F598-ORB • Oil Rubbed Bronze Finish • Medium Maple Blades • Excavation Glass
F598-WH • White Finish • High Gloss White Blades • Acid Etched Glass
F598-BN • Brushed Nickel Finish • Silver Blades • Acid Etched Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



F598-WH



F598-BN



F802-PN

VINTAGE GYRO™

An addition to our popular Gyro™ family, the Vintage Gyro™ performs with the same efficiency and unsurpassed level of comfort as our other Gyro™ models, but with an early 20th Century style.

FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch • 6" Downrod
- 720 - 1,350 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Cap for Non-Light Use (Included)

U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 35 Watts
- Airflow 1,439 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 41 Cubic Feet Per Minute Per Watt

- F802-PN** • Polished Nickel Finish • Rosewood Blades • Etched Opal Glass
- F802-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass
- F802-BN/CH** • Brushed Nickel/Chrome Finish • Rosewood Blades • Etched Opal Glass
- F802-KA** • Kocoa Finish • Kocoa Blades • Tinted Opal Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

VINTAGE GYRO™



F802-ORB



F802-BN/CH



F802-KA





Gyro Fans
Rotate 360°

F502-BCW

TRADITIONAL GYRO™

A magnificent rendition of the original Gyro™ design, the traditional finish transcends the turns of time.

FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch • 4½" and 12" Downrod
- 720 - 1,350 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Cap for Non-Light Use (Included)

U.S. Patent(s): D523,548; D523,549; D523,550; D523,983; D524,438; D526,059; D526,400; D526,712; D530,810; D532,097; D567,350; 6,832,902; 7,183,680; 7,229,255 © 2004 Minka Lighting, Inc.

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 35 Watts
- Airflow 2,003 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 57 Cubic Feet Per Minute Per Watt

F502-BCW • Belcaro Walnut™ Finish • Belcaro Walnut™ Blades • Belcaro Walnut™ Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



F602-BN/CH



F602-RRB

GYRO™

A truly unique design offering an unsurpassed level of comfort. The Gyro™ fan's ability to precisely control the direction and intensity of the cooling breeze efficiently circulates air in any environment.

FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch • 6" Downrod
- 720 - 1,350 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation • Cap for Non-Light Use (Included)

U.S. Patent(s): D489,443; D490,146; 6,832,902; 7,183,680; 7,229,255

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 35 Watts
- Airflow 2,037 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 58 Cubic Feet Per Minute Per Watt

F602-BN/CH • Brushed Nickel/Chrome Finish with Chrome Accents and Cages
• Rosewood Blades • Etched Opal Glass

F602-RRB • Restoration Bronze™ Finish • Restoration Bronze™ Blades
• Etched Opal School House Globe Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

GYRO™ WET



F402-ORB

Gyro Fans
Rotate 360°





F402-BNW
Shown with Cap for Non-Light Use

GYRO™ WET

Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360° and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.

FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch
- Complete Assembly Rotates 360° at 3 R.P.M. • 720 - 1,350 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down • Galvanized Steel 6" Downrod
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 35 Watts

- Airflow 1,297 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 38 Cubic Feet Per Minute Per Watt

F402-ORB • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades
• Etched Opal School House Globe Glass

F402-BNW • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass



WCS212

For Details
See Page(s): 321



BOND
Compatible Fan



F306L-ORB/MM



F306L-BS/SL

F306L-ORB/MM
See Opposite page

ELEMENTAL GYRO™ with LED Light

Elemental Gyro™ is the newest addition to our Gyro™ series. A clean, industrial spirit combined with a LED light source and etched opal glass. The Gyro™ series continues to offer air movement throughout the entire room, or can be stopped to position air in only one area. Adjustable fan cages further enhance air movement.

FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 23° Blade Pitch • 6" Downrod
- 800 - 1,470 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Integrated LED Light Uses 16W LED (Included) 3 Year Warranty • 1,352 Lumens • 2,700K
- CRI 80 • Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation

U.S. Patent(s): D808,510; 6,832,902; 7,183,680; 7,229,255; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 37 Watts
- Airflow 1,981 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 54 Cubic Feet Per Minute Per Watt

F306L-ORB/MM • Oil Rubbed Bronze Finish • Medium Maple Blades
• Etched Opal Glass

F306L-BN/SL • Brushed Steel Finish • Silver Blades • Etched Opal Glass

LED

WWW.MINKAaire.COM



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



F304L-BN/SL



F304L-ORB/MM

CAGE FREE GYRO™

with LED Light

A wonderful addition to our Gyro™ series. Simple, clean design featuring twin turbo fans, 16 watt LED and cage free blades allow for a classic transitional spirit.

FEATURES

- High Performance Twin Turbofans Total Sweep 37" • 23° Blade Pitch • 4½" Downrod
- 800 - 1,470 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Integrated LED Light Uses 16W LED (Included) 3 Year Warranty • 1,352 Lumens • 2,700K • CRI 80
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation

U.S. Patent(s): D808,509; 6,832,902; 7,183,680; 7,229,255; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$21
 - Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 76 Watts
 - Airflow 2,122 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 28 Cubic Feet Per Minute Per Watt

- F304L-BN/SL** • Brushed Nickel Finish • Silver Blades • Etched Opal Glass
- F304L-ORB/MM** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Opal Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



Gyro Fans
Rotate 360°

F302-RRB



F302-BN

GYRETTE™

The Gyrette™ captures the design elements of the original Gyro™ in a smaller format. We have utilized flexible arms to maximize air circulation.

FEATURES

- High Performance Twin Turbofans Total Sweep 36" • Adjustable Turbofan Heads
- 14° Blade Pitch • Complete Assembly Rotates 360° at 3 R.P.M.
- 3-Speeds: 800, 1,090, 1,470 R.P.M. • 30° Flexible Arms • 6" Downrod
- Full Function Hand Held Remote Control System Included

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 21 Watts
- Airflow 281 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 14 Cubic Feet Per Minute Per Watt

- F302-RRB** • Restoration Bronze™ Finish • Restoration Bronze™ Blades
- F302-BN** • Brushed Nickel Finish • Brushed Nickel Blades



RCS212
For Details
See Page(s): 320



BOND
Compatible Fan



F852L-HBZ

ALVA

with LED Light

Inspired by a great American inventor, Alva merges technology and history in a transitional design of timeless aesthetic value. With five Dark Walnut Solid Wood Blades and three medium base LED ferro bulbs, it will bring comfort and a refreshing look to your home or office.

FEATURES

- 14° Blade Pitch • 5-Blades 56" Sweep • DC 120 x 15mm Motor • 6" Downrod
- Integrated Light Uses 3-6W LED Medium Base Ferro Bulb (Included)
- Hand Held Remote Included - RC500

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 22 Watts
- Airflow 5,272 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 243 Cubic Feet Per Minute Per Watt

F852L-HBZ • Heirloom Bronze Finish • Aged Boardwalk Blades

F852L-BN • Brushed Nickel Finish • Seashore Grey Blades

F852L-TI • Tarnished Iron Finish • Dark Walnut Blades



RC500

For Details
See Page(s): 320



BOND
Compatible Fan



F852L-BN



F852L-TI



F539-BNK

F539-BNK • Burnished Nickel Finish • Seashore Grey Blades



GREAT ROOM TRADITIONAL

Great Room interiors require new ways to manage air. We have accomplished this with expanded blade spans, larger motors and enhanced housings in styles designed to complement those rooms.



F539-HBZ

GREAT ROOM TRADITIONAL

Great Room interiors require new ways to manage air. We have accomplished this with expanded blade spans, larger motors and enhanced housings in styles designed to complement those rooms.

FEATURES

- 14° Blade Pitch • 5-Blades 72" Sweep • 6" Downrod • Full Function Wall Control System Included
- Universal Light Kit Adaptable (Sold Separately. See K9376-1 and K9376-2 on Page(s): 311)
- Quick Connect Switch Cup

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$18
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 65 Watts
- Airflow 6,846 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 106 Cubic Feet Per Minute Per Watt

- F539-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades
- F539-BN** • Brushed Nickel Finish • Dark Walnut Blades
- F539-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades
- F539-ORB** • Oil Rubbed Bronze Finish • Dark Walnut Blades
- F539-BNK** • Burnished Nickel Finish • Seashore Grey Blades *(Shown on previous page)*



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

GREAT ROOM TRADITIONAL



F539-BN



F539-BCW



F539-ORB



F701-PW



F701-DRF



F701-KA
*Shown with Toned Medium Maple Blades
Reversible to Dark Walnut Blades*



F701-DRB



F701-PN

DELANO®

FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod
- Integrated Uplight Use 6-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Wall Control System Independent Up/Downlight Included

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 46 Watts
- Airflow 3,691 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 81 Cubic Feet Per Minute Per Watt

- F701-PN** • Polished Nickel Finish • Silver Blades • White Frosted Glass
- F701-PW** • Pewter Finish • Natural Walnut Blades • Etched Marble Glass
- F701-DRF** • Driftwood Finish • Driftwood Blades • Bone White Glass
- F701-DRB** • Dark Restoration Bronze™ Finish • Dark Walnut Blades • Rustic Scavo Glass
- F701-KA** • Kocoa Finish • Reversible Toned Medium Maple/Dark Walnut Blades • Rustic Scavo Glass



WCS213
For Details
See Page(s): 321



BOND
Compatible Fan



F711-DRB

DELANO® II

Inspired by a long-time favorite, the Delano® II offers the same clean, neo-transitional look but with less than an 11-inch drop from the ceiling.

FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Less than 11" Drop from Ceiling
- Integrated Halogen Light Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Full Function Wall Control System Included

U.S. Patent(s): D595,403; D597,655

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$14
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 48 Watts
- Airflow 2,217 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 46 Cubic Feet Per Minute Per Watt

F711-DRB • Dark Restoration Bronze™ Finish • Dark Walnut Blades • Rustic Scavo Glass
F711-PN • Polished Nickel Finish • Silver Blades • White Frosted Glass
F711-PW • Pewter Finish • Natural Walnut Blades • Etched Marble Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

DELANO® II



F711-PN



F711-PW

minkaAire®



F614-HBZ

F614-HBZ • Heirloom Bronze Finish • Aged Boardwalk Blades



TIMELESS

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.

F614-BNK





F614-ORB



F614-DBB

F614-BNK
See Opposite Page

TIMELESS

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Available (Sold Separately. Page(s): 317)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 42 Watts
- Airflow 3,261 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 77 Cubic Feet Per Minute Per Watt

F614-BNK • Burnished Nickel Finish • Seashore Grey Blades

F614-MCG • Mottled Copper with Gold Highlights Finish • Dark Walnut Blades

F614-DBB • Dark Brushed Bronze Finish • Dark Maple Blades

F614-HBZ • Heirloom Bronze Finish • Aged Boardwalk Blades (Shown on previous page)





F614-PW

TIMELESS

F614-PW • Pewter Finish • Dark Walnut Blades
F614-ORB • Oil Rubbed Bronze Finish • Medium Maple Blades
F614-FB • French Beige Finish • Medium Maple Blades
F614-PI • Patina Iron Finish • Dark Maple Blades

TIMELESS



F614-FB



F614-PI



F689-KA

*Shown with Toned Medium Maple Blades
Reversible to Dark Maple Blades*

KOLA-XL

The Kola-XL 60-inch fan features the same design elements as the Kola 52-inch. It has been upgraded to provide the performance necessary for larger rooms and has the convenience of a remote control system.

FEATURES

- 12° Blade Pitch • 60" 5-Blades • 6" Downrod
- Full Function Hand Held Remote Control System Included
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$14
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 51 Watts
- Airflow 4,206 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 83 Cubic Feet Per Minute Per Watt

- F689-KA** • Kocoa Finish • Reversible Toned Medium Maple/Dark Maple Blades
- F689-WH** • White Finish • White Blades
- F689-DBB** • Dark Brushed Bronze Finish • Reversible Dark Maple/Dark Walnut Blades
- F689-PW** • Pewter Finish • Reversible Dark Maple/Dark Walnut Blades



RCS212
For Details
See Page(s): 320



BOND
Compatible Fan

KOLA-XL



F689-DBB
*Shown with Dark Walnut Blades
Reversible to Dark Maple Blades*



F689-WH



F689-PW
*Shown with Dark Maple Blades
Reversible to Dark Walnut Blades*





F688-PW

*Shown with Dark Maple Blades
Reversible to Dark Walnut Blades*

KOLA

Smooth lines with a sleek blade iron design and a robust body make the Kola a perfect complement to any home décor.

FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 43 Watts
- Airflow 3,142 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 74 Cubic Feet Per Minute Per Watt

F688-PW • Pewter Finish • Reversible Dark Maple/Dark Walnut Blades

F688-WH • White Finish • White Blades

F688-DBB • Dark Brushed Bronze Finish • Reversible Dark Maple/Dark Walnut Blades

F688-KA • Kocoa Finish • Reversible Toned Medium Maple/Dark Maple Blades

KOLA



F688-DBB

*Shown with Dark Walnut Blades
Reversible to Dark Maple Blades*



F688-WH



F688-KA

*Shown with Toned Medium Maple Blades
Reversible to Dark Maple Blades*





F696-HBZ

F696-HBZ • Heirloom Bronze Finish • Aged Boardwalk Blades



KAFÉ-XL

Simple elegance defined in rich finishes, the Kafé-XL brings an exciting look with enhanced features to our value collection.



F696-BNK

KAFÉ-XL

Simple elegance defined in rich finishes, the Kafé-XL brings an exciting look with enhanced features to our value collection.

FEATURES

- 12° Blade Pitch • 5-Blades 60" Sweep • 6" Downrod
- Full Function Hand Held Remote Control System Included
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$14
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 50 Watts
- Airflow 4,033 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 81 Cubic Feet Per Minute Per Watt

- F696-BNK** • Burnished Nickel Finish • Seashore Grey Blades
- F696-WH** • White Finish • White Blades
- F696-VP** • Vineyard Patina Finish • Reversible Dark Maple/Dark Walnut Blades
- F696-KA** • Cocoa Finish • Reversible Toned Medium Maple/Dark Maple Blades
- F696-CC** • Cognac Finish • Reversible Natural Walnut/Dark Walnut Blades
- F696-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades (*Shown on previous page*)



RCS212
For Details
See Page(s): 320



BOND
Compatible Fan

KAFÉ-XL



F696-VP
*Shown with Dark Walnut Blades
Reversible to Dark Maple Blades*



F696-WH



F696-CC
*Shown with Natural Walnut Blades
Reversible to Dark Walnut Blades*



F696-KA
*Shown with Toned Medium Maple Blades
Reversible to Dark Maple Blades*





F695-BNK

F695-BNK • Burnished Nickel Finish • Seashore Grey Blades



KAFÉ

Simple yet elegant in several finishes, the Kafé brings a refreshing look to our transitional collection.



F695-HBZ

KAFÉ

Simple yet elegant in several finishes, the Kafé brings a refreshing look to our transitional collection.

FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 44 Watts
- Airflow 3,696 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 84 Cubic Feet Per Minute Per Watt

- F695-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades
- F695-CC** • Cognac Finish • Reversible Natural Walnut/Dark Walnut Blades
- F695-WH** • White Finish • White Blades
- F695-VP** • Vineyard Patina Finish • Reversible Dark Maple/Dark Walnut Blades
- F695-KA** • Kocoa Finish • Reversible Toned Medium Maple/Dark Maple Blades
- F695-BNK** • Burnished Nickel Finish • Seashore Grey Blades (*Shown on previous page*)



F695-CC
*Shown with Natural Walnut Blades
Reversible to Dark Walnut Blades*



F695-WH



F695-VP
*Shown with Dark Maple Blades
Reversible to Dark Walnut Blades*



F695-KA
*Shown with Toned Medium Maple Blades
Reversible to Dark Maple Blades*





F620-BN

BOLO™

Four of our best selling finishes accent this fan, creating a decorative alternative to an everyday need. Includes glass bowl light kit and remote control system.

FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod
- Bowl Light Kit Uses 3-60W Candelabra Bulbs (Included)
- Hand Held Remote Control System Included • Cap for Non-Light Use (Included)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 48 Watts
- Airflow 3,389 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 71 Cubic Feet Per Minute Per Watt

- F620-BN** • Brushed Nickel Finish • Dark Walnut Blades • Etched Swirl Glass
- F620-DBB** • Dark Brushed Bronze Finish • Dark Maple Blades • Avorio Mezzo™ Glass
- F620-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades • Excavation Glass
- F620-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Excavation Glass



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan



F620-DBB



F620-BCW



F620-ORB



F820-CT



F820-IBR



CM8222-IBR 22"

SANTA LUCIA™

FEATURES

- 14° Blade Pitch • 5-Blades 60" Sweep • 6" Downrod
- Integrated Uplight Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Full Function Wall Control System with Independent Up/Downlight Control Included

U.S. Patent(s): D556,882; D559,436; D568,984; D570,986; D574,948; D599,000; D599,466; 5,554,006

© 2006 Minka Lighting, Inc.

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$16
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 56 Watts
- Airflow 4,284 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 77 Cubic Feet Per Minute Per Watt

F820-CT • Cattera Bronze™ Finish • Dark Walnut Blades • with Cognac Fluted Etched Glass

F820-IBR • Illuminati Bronze™ Finish • Dark Walnut Blades • with Silver Patina Glass

CM8222-IBR 22" • Illuminati Bronze™ Finish • 22" Diameter

• Matching Ceiling Medallion for F820-IBR • © 2005 Minka Lighting, Inc.



WCS212

For Details
See Page(s): 321



BOND
Compatible Fan



F812-IO

LINEAGE™

Simple, clean, architectural lines have been utilized to define the Lineage™.

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod
- Integrated Uplight Uses 6-15W Candelabra Bulbs (Included)
- Integrated Downlight Uses 2-60W Candelabra Bulbs (Included)
- Full Function Wall Control System Independent Up/Downlight Included
- Complements Lighting Available Through Minka-Lavery®

U.S. Patent(s): D528,652; D531,298; D532,098; D533,292; D535,012; D563,540

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$16
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 59 Watts
- Airflow 3,951 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 67 Cubic Feet Per Minute Per Watt

F812-IO • Iron Oxide Finish • Dark Walnut Blades • Venetian Scavo Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



F705-STW



CM7022-STW 22"
Fits Napoli™ and Napoli™ II

NAPOLI™

FEATURES

- 14° Blade Pitch • 5-Blades 56" Sweep • 12" Downrod • Full Function Wall Control System
- Integrated Halogen Light Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690; D516,702; D521,627; D522,122

F705 ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$15
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 54 Watts
- Airflow 4,006 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 75 Cubic Feet Per Minute Per Watt

F705-STW • Sterling Walnut™ Finish • Sterling Walnut™ Shaded Blades • Aged Champagne Glass
CM7022-STW 22" • Sterling Walnut™ Finish • Matching Ceiling Medallion • © 2005 Minka Lighting, Inc.



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



F715-STW 68"



CM7038-STW 38"
Fits Napoli™ and Napoli™ II

NAPOLI™ II

FEATURES

- 14° Blade Pitch • 5-Blades 56" or 68" Sweep • 12" Downrod • Full Function Wall Control System
- Integrated Halogen Light Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690; D516,702; D521,627; D522,122

F715 ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$19
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 69 Watts
- Airflow 4,065 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 59 Cubic Feet Per Minute Per Watt

F715-STW • Sterling Walnut™ Finish • Sterling Walnut™ Shaded Blades • Aged Champagne Glass
CM7038-STW 38" • Sterling Walnut™ Finish • Matching Ceiling Medallion • © 2005 Minka Lighting, Inc.



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



F759-PBL

CLASSICA GALLERY EDITION

Old world hand-painted finishes accentuate the hand-carved details to create a traditional European style fan.

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod
- Integrated 3-Light Kit Uses 3-60W Candelabra Bulbs (Included)
- Hand Held Remote Control System Included

© 2009 Minka Lighting, Inc.

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 46 Watts
- Airflow 3,479 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 76 Cubic Feet Per Minute Per Watt

F759-PBL Gallery Edition • Provencal Blanc Finish • Provencal Blanc Blades • Etched Glass



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan



F759-PBL Gallery Edition




F659-DRF

F659-DRF • Driftwood Finish • Driftwood Blades



CLASSICA

Old world hand-painted finishes accentuate the hand-carved details to create a traditional European style fan.



F659-PBL

CLASSICA

Old world hand-painted finishes accentuate the hand-carved details to create a traditional European style fan.

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)
- Custom Light Kit K9659 Available (Sold Separately. Page(s): 317)

© 2009 Minka Lighting, Inc.

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 41 Watts
- Airflow 3,394 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 83 Cubic Feet Per Minute Per Watt

F659-PBL • Provencal Blanc Finish • Provencal Blanc Blades

F659-BCW • Belcaro Walnut™ Finish • Dark Walnut Blades

F659-FB • French Beige Finish • Medium Maple Blades

F659-PI • Patina Iron Finish • Dark Walnut Blades

F659-DRF • Driftwood Finish • Driftwood Blades (Shown on previous page)

CLASSICA



F659-BCW



F659-FB



F659-PI



F659-MCG





F702-BCW



F702-VB

VOLTERRA™

Volterra™ is a neo-classical inspiration, incorporating an uplight with an integrated halogen downlight.

FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod
- Integrated Uplight Uses 6-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Wall Control System Independent Up/Downlight Included

© 2002 Minka Lighting, Inc.

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 47 Watts
- Airflow 3,652 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 78 Cubic Feet Per Minute Per Watt

- F702-BCW** • Belcaro Walnut™ Finish • Natural Walnut Blades • Aged Champagne Glass
F702-VB • Volterra Bronze™ Finish • Natural Walnut Blades • French Scavo Glass



WCS213
 For Details
 See Page(s): 321



BOND
 Compatible Fan



F544-BCW

CALAIS™

Elegance, style and performance for low ceiling applications, this fan has less than an 11-inch drop from ceiling to cap.

FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Less than 11" Drop from Ceiling
- Integrated Light Uses 2-60W Candelabra Bulbs (Included)
- Hand Held Remote Control System Included

U.S. Patent(s): D526,714; D527,094; D530,415; D532,896; D536,777

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$14
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 51 Watts
- Airflow 2,854 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 56 Cubic Feet Per Minute Per Watt

F544-BCW • Belcaro Walnut™ Finish • Dark Walnut Blades • Aged Champagne Glass



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan

CRISTAFANO™



F900-BCW

Shown with Optional GC900 SET
MADE WITH SPECTRA® CRYSTAL
GC900 Set only fits with 16" Downrod





F900-BCW

CRISTAFANO™

FEATURES

- 14° Blade Pitch • 5-Blades 68" Sweep • 16" Downrod
- Precision Machine Cut and Polished Lead-Free SPECTRA® CRYSTAL
- Integrated Uplight Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Full Function Wall Control System with Independent Up/Downlight Control Feature Included

© 2005 Minka Lighting, Inc.

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$18
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 63 Watts
- Airflow 5,438 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 86 Cubic Feet Per Minute Per Watt

F900-BCW • Belcaro Walnut™ Finish • Dark Walnut Blades • Etched Cut Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

F681-SDBK/WS



A vertical photograph on the left side of the page showing a view from a covered outdoor patio. The foreground shows a gravel path and a white lattice chair. The middle ground features a garden bed with green plants and red flowers. In the background, there is a large body of water under a clear blue sky.

INDOOR/OUTDOOR CEILING FAN COLLECTION

Minka-Aire® recognizes a need in today's al fresco lifestyle by offering an Outdoor Series of ceiling fans. All are UL or ETL Listed for wet location usage, making these fans perfect for patios, porches, and other exposed areas. Motor housings and blades are fully protected against water and all weather conditions. Particular models have a combined waterproof light kit to provide additional lighting outdoors. These fans feature various designer finishes to complement your patio furniture.

Now you are able to enjoy a wonderful breeze on your patio, in your gazebo, or over your outdoor spa! Of course, you may use all of these models indoors as well.





F307-BN
Oscillating Fan



F307-MBK
Oscillating Fan

F307-BN
See Opposite Page

ANYWHERE

The first wall mount fan in the industry to be wet-rated brings a contemporary look and feel to any indoor or outdoor environment. ANYWHERE can be mounted to a standard electrical box or plugged in to an outlet. ANYWHERE is designed to conform to any décor and to any climate. Oscillating cool comfort where a ceiling fan may not be an option.

FEATURES

- 3-Blade Turbofan 15" Diameter • 3 Speeds: 491, 650 and 985 R.P.M. • Oscillates 45° Side to Side
- Manual Tilt • 118" Heavy Duty Cord Length • 3 Speed Pull Chain
- Convertible to hardware or wall plug • Steel Construction • One Year Limited Warranty
- Indoor/Outdoor Use - UL Listed for Wet Locations

U.S. Patent(s): Pending

- F307-BN** • Brushed Nickel Finish • Silver Blades
- F307-MBK** • Matte Black Finish • Matte Black Blades





F896-84-BNW

XTREME H₂O 84"

An outdoor version of one of our most popular large fan introductions, this industrial sized fan lends itself to any setting. Xtreme H₂O's clean, sleek, contemporary design, complete with a DC motor and a choice of sizes, makes it perfect for large areas indoor or outdoor.

FEATURES

- 4° Blade Pitch • 8-Blades 84" Sweep • DC 123 x 30mm Motor • 6" Downrod
- ABS Blades • Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9886L Available (Sold Separately Page(s): 319)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 32 Watts
- Airflow 8,252 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 262 Cubic Feet Per Minute Per Watt

F896-84-ORB • Oil Rubbed Bronze • Oil Rubbed Bronze Blades

F896-84-BNW • Brushed Nickel Wet Finish • Silver Blades

F896-84-SI • Smoked Iron Finish • Smoked Iron Finish Blades




RC400

For Details
See Page(s): 320



BOND
Compatible Fan

XTREME H₂O



F896-84-SI
*Shown with optional
K9886L-SI LED light kit*



F896-84-ORB





F896-65-BNW

XTREME H₂O 65"

An outdoor version of one of our most popular large fan introductions, this industrial sized fan lends itself to any setting. Xtreme H₂O's clean, sleek, contemporary design, complete with a DC motor and a choice of sizes, makes it perfect for large areas indoor or outdoor.

FEATURES

- 4° Blade Pitch • 8-Blades 65" Sweep • DC 123 x 30mm Motor • 6" Downrod
- ABS Blades • Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9886L Available (Sold Separately Page(s): 319)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 32 Watts
- Airflow 6,565 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 205 Cubic Feet Per Minute Per Watt

F896-65-BNW • Brushed Nickel Wet Finish • Silver Blades
F896-65-ORB • Oil Rubbed Bronze • Oil Rubbed Bronze Blade
F896-65-WHF • Flat White Finish • Flat White Blades



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

XTREME H₂O



F896-65-ORB
Shown with optional
K9886L-ORB LED light kit



F896-65-WHF
Shown with optional
K9886L-WHF LED light kit





Gyro Fans
Rotate 360°

F402-BNW

F402-ORB
See Opposite Page

GYRO™ WET

Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360° and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.

FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch
- Complete Assembly Rotates 360° at 3 R.P.M. • 720 - 1,350 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down • Galvanized Steel 6" Downrod
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 35 Watts
- Airflow 1,297 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 38 Cubic Feet Per Minute Per Watt

F402-ORB • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades
• Etched Opal School House Globe Glass

F402-BNW • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan





F402-ORB



F787-ORB
Indoor/Outdoor

SIMPLE 52"

So simple! We gave this wonderful design a name that best denotes it's spirit! Incredibly delicate and nearly invisible. This design best displays the advancement in technology with indoor/outdoor use, DC motor, optional LED light kit and a hand held remote.

FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9787L Available (Sold Separately. Page(s): 319)
- Indoor/Outdoor Use ETL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 20 Watts
- Airflow 3,633 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 184 Cubic Feet Per Minute Per Watt

- F787-SL** • Silver Finish • Silver Blades
- F787-BNW** • Brushed Nickel Wet Finish • Silver Blades
- F787-ORB** • Oil rubbed Bronze Finish • Medium Maple Blades
- F787-WHF** • Flat White Finish • Flat White Blades



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

SIMPLE 52"



F787-SL
Indoor/Outdoor



F787-WHF
*Shown with optional
K9787L-WHF LED Light Kit*
Indoor/Outdoor



F787-BNW
Indoor/Outdoor



GROTON



F681-SDBK/WS



F681-BNW



F681-WA/PW



F681-PN
(Finish For Indoor Use Only)





F681-ORB

GROTON

Inspired by the clear Fresnel lens used in lighthouses along the coast of Connecticut, we are introducing our Groton collection. Classic design combined with nautical spirit in various finishes. All of which will suit both indoor and outdoor locations, as this fan has a UL wet rating.

FEATURES

- 12° Blade Pitch • 5-Blades 56" Sweep • 10" Downrod
- Integrated Halogen Light Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Full Function Hand Held Remote Control System Included
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D808,512; D812,215; D812,217; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 36 Watts
- Airflow 3,952 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 108 Cubic Feet Per Minute Per Watt

- F681-ORB** • Oil Rubbed Bronze Finish • Dark Pine Blades • Clear Fresnel Lens
- F681-SDBK/WS** • Sand Black/Weathered Steel Finish • Charcoal Driftwood Blades • Clear Fresnel Lens

- F681-BNW** • Brushed Nickel Wet Finish • Silver Blades • Clear Fresnel Lens
- F681-WA/PW** • Weathered Aluminum/Pewter Finish • Dark Pine Blades • Clear Fresnel Lens

- F681-PN** • Polished Nickel Finish • Silver Blades • Clear Fresnel Lens



RCS212
For Details
See Page(s): 320



BOND
Compatible Fan



F541L-SL
Indoor/Outdoor

CONE

with LED Light

The Cone lends an iconic presence to both indoor and outdoor settings for those who are looking for a blast from the past. This standard amongst designs offers a three, four and five blade option to suit everyone's preference as well as a clear and hooded light shade to create different lighting options.

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Integrated LED Light Uses 20W Dimmable LED (Included) 3 Year Warranty
- 1,100 Lumens • 3,000K • CRI 90 • Optional Clear Lens in box • **Convertible into 3, 4 or 5 Blade**
- Special Hand Held Remote Control System Included - RC400
- Indoor/Outdoor Use - ETL Listed for Wet Locations

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$8
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 29 Watts
- Airflow 5,625 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 194 Cubic Feet Per Minute Per Watt

F541L-SL • Silver Finish • Silver Blades • Removable Silver Metal Ring • Etched Lens

F541L-ORB • Oil Rubbed Bronze Finish • Removable Oil Rubbed Bronze Metal Ring
• Medium Maple Blades • Etched Lens

F541L-WH • White Finish • White Blades • Removable White Metal Ring • Etched Lens



RC400
For Details
See Page(s): 320



BOND
Compatible Fan

CONE

with LED Light



F541L-ORB
Shown with 4-Blade Option
Indoor/Outdoor



F541L-WH
Shown with 3-Blade Option
Indoor/Outdoor



F541L-SL
Shown with Removable Metal Ring
Indoor/Outdoor

LED

DC MOTOR



minkaAire



F624-ORB

ROTO XL

Roto XL features a sleek and contemporary design with a classic industrial look. Well edited; an impeccably executed design features a slight "fold" construction along the length of the blades to increase the flow of air. A perfect marriage of form and function. Roto XL features a full 62-inch spread combined with a wet location specification use for indoor or outdoors.

FEATURES

- 20° Blade Pitch • 3-Blades 62" Sweep • 6" Downrod • Aluminum Construction
- 2 Wire Wall Control Included - WC115 • Convertible to Electronic Control System Include
- Indoor/Outdoor Use - ETL Listed for Wet Locations

U.S. Patent(s): D750,221; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 45 Watts
- Airflow 4,286 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 96 Cubic Feet Per Minute Per Watt

- F624-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades
- F624-ABD** • Brushed Aluminum Finish • Silver Blades
- F624-WHF** • Flat White Finish • Flat White Blades



WC115
For Details
See Page(s): 323

ROTO XL



F624-ABD



F624-WHF





F477L-ORB

CONCEPT™ I WET 58"

with LED Light

UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series. Concept™ I Wet is constructed of marine grade stainless steel to ensure long lasting appearance and function in the toughest environments.

FEATURES

- 14° Blade Pitch • 3-Blades 58" Sweep • Stainless Steel 6" Downrod
- Marine Grade Stainless Steel Construction
- Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K • CRI 80
- Full Function Wall Control System Included • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): 7,008,192

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 44 Watts
- Airflow 4,103 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 93 Cubic Feet Per Minute Per Watt

- F477L-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Pietra Glass
- F477L-BNW** • Brushed Nickel Wet Finish • Silver Blades • White Opal Glass
- F477L-WH** • White Finish • White Blades • White Opal Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

CONCEPT™ | WET 58"

with LED Light

MARINE GRADE



F477L-BNW



F477L-WH
Shown with Cap for Non-Light Use





F476L-BNW

CONCEPT™ I WET 52" with LED Light

The Concept™ I ceiling fan collection is the most successful series in the history of Minka-Aire®. It is only natural that we would produce a new version that is UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series.

FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep • Galvanized Steel 6" Downrod • Construction Grade Polymer
- Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K • CRI 80
- Full Function Wall Control System Included • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): 7,008,192

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 37 Watts
- Airflow 4,108 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 112 Cubic Feet Per Minute Per Watt

- F476L-BNW** • Brushed Nickel Wet Finish • Silver Blades • White Opal Glass
- F476L-ORB** • Oil Rubbed Bronze Finish • Taupe Blades • Pietra Glass
- F476L-WH** • White Finish • White Blades • White Opal Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

CONCEPT™ | WET 52"

with LED Light



F476L-ORB



F476L-WH
Shown with Cap for Non-Light Use





F474L-ORB



F474L-WH

Shown with Cap for Non-Light Use

F474L-BNW

See Opposite Page

CONCEPT™ II WET 52"

with LED Light

As the name implies, the Concept™ II Wet ceiling fan is "a taste of things to come."
Simple in style, yet ingenious by design and UL Listed for wet locations.

FEATURES

- 14° Blade Pitch • 3-Concave Blades 52" Sweep • Construction Grade Polymer
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 12" Drop from Ceiling
- Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K • CRI 80
- Full Function Wall Control System Included • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations (Will Not Pendulum In Windy Conditions)

U.S. Patent(s): 7,008,192

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10

Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 37 Watts

- Airflow 3,990 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 107 Cubic Feet Per Minute Per Watt

F474L-BNW • Brushed Nickel Wet Finish • Silver Blades • White Opal Glass

F474L-ORB • Oil Rubbed Bronze Finish • Taupe Blades • Pietra Glass

F474L-WH • White Finish • White Blades • White Opal Glass



WCS212

For Details
See Page(s): 321



BOND
Compatible Fan



BOND
Compatible Fan



F474L-BNW

minkaAire®

CONCEPT™ II WET 52"
with LED Light

225



F594L-ORB

TRADITIONAL CONCEPT™ 52"

with LED Light

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 10¾" Drop from Ceiling
- Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K • CRI 80
- Full Function Wall Control System Included • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 40 Watts
- Airflow 3,638 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 91 Cubic Feet Per Minute Per Watt

- F594L-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass
- F594L-PW** • Pewter Finish • Dark Maple Blades • Opal Glass
- F594L-WH** • White Finish • White Blades • Opal Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

TRADITIONAL CONCEPT™ 52"

with LED Light



F594L-WH



F594L-PW





F593L-PW

TRADITIONAL CONCEPT™ 44"

with LED Light

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more transitional indoor and outdoor settings.

FEATURES

- 14° Blade Pitch • 3-Blades 44" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 10¾" Drop from Ceiling
- Integrated LED Light Uses 14W LED (Included) 3 Year Warranty • 540 Lumens • 3,000K • CRI 80
- Full Function Wall Control System Included • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 35 Watts
- Airflow 2,682 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 77 Cubic Feet Per Minute Per Watt

- F593L-PW** • Pewter Finish • Dark Maple Blades • Opal Glass
- F593L-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass
- F593L-WH** • White Finish • White Blades • Opal Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

TRADITIONAL CONCEPT™ 44"

with LED Light



F593L-WH
Shown with Cap for Non-Light Use



F593L-ORB



JAVA LED

with LED Light



F753L-WHF



F753L-BNW



F753L-KA

JAVA LED

with LED Light

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all indoor or outdoor environments. The Java LED features an integrated 17 watt LED light.

FEATURES

- 14° Blade Pitch • 3-Blades 54" Sweep • 6" Downrod
- Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 630 Lumens • 3,000K
- CRI 80 • Hand Held Remote Control System Included
- Indoor/Outdoor Use - UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 34 Watts
- Airflow 4,394 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 131 Cubic Feet Per Minute Per Watt

- F753L-BNW** • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass
- F753L-KA** • Kocoo Finish • Kocoo Blades • Etched Opal Glass
- F753L-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan



F753-KA

JAVA

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments.

FEATURES

- 14° Blade Pitch • 3-Blades 54" Sweep • 6" Downrod
- Hand Held Remote Control System Included • Indoor/Outdoor Use - UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 32 Watts
- Airflow 4,113 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 128 Cubic Feet Per Minute Per Watt

- F753-KA** • Kocoa Finish • Kocoa Blades
- F753-WHF** • Flat White Finish • Flat White Blades
- F753-BNW** • Brushed Nickel Wet Finish • Silver Blades



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan



F753-WHF



F753-BNW





F523-ABD

Shown with Cap for Non-Light Use

ALUMA WET

Aluma Wet is our answer to the fan that goes anywhere and has everything. For use indoors and outdoors, Aluma Wet is UL listed for use in wet locations. Produced from weather resistant materials, the Aluma Wet provides air circulation for every location including patio, porch and pergola.

FEATURES

- 12° Blade Pitch • 4-Blades 52" Sweep • 6" Downrod • All Aluminum Construction
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Hand Held Remote Control System Included • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 34 Watts
- Airflow 2,925 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 85 Cubic Feet Per Minute Per Watt

- F523-ABD** • Brushed Aluminum Finish • Silver Blades • Etched Opal Glass
- F523-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass
- F523-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass




RCS213
For Details
See Page(s): 320



BOND
Compatible Fan

ALUMA WET



F523-WHF



F523-ORB





F734-ORB

STRATA

The Strata with its Smoked Iron or Galvanized finishes adds a rustic yet contemporary style to your home.

FEATURES

- 12° Blade Pitch • 4-Blades 52" Sweep
- Galvanized Steel 6" Downrod (Uses 3/4" I.D. DR5 Series Downrod)
- Integrated Light Uses 1-75W Mini-Can Halogen Bulb (Included)
- Hand Held Remote Control System Included • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 34 Watts
- Airflow 3,365 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 98 Cubic Feet Per Minute Per Watt

- F734-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass
- F734-GL** • Galvanized Finish • Silver Blades • Etched Opal Glass
- F734-SI** • Smoked Iron Finish • Smoked Iron Finish Blades • Etched Opal Glass



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan

STRATA



F734-GL
Shown with Cap for Non-Light Use



F734-SI





F683L-BNW

SHADE

with LED Light

Illumination even in the harshest of environments. SHADE provides unmatched performance and comfort in the toughest conditions. Incorporating a DC motor for high efficiency with an integrated 15 watt LED light and a UL wet rating, SHADE meets both your indoor and outdoor location requirements.

FEATURES

- 14° Blade Pitch • 4-Blades 56" Sweep • 6" Downrod • DC 168 x 12mm Motor
- Integrated LED Light Uses 15W LED (Included) 3 Year Warranty • 1,285 Lumens • 2,700K • CRI 90
- Hand Held Remote Control System - RC400 • Indoor/Outdoor Use - UL Listed for Wet Locations

U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 42 Watts
- Airflow 8,181 Cubic Feet Per Minute
- Airflow Efficiency: 195 Cubic Feet Per Minute Per Watt

- F683L-BNW** • Brushed Nickel Wet Finish • Silver Blades • Clear Fresnel Glass
- F683L-GI** • Grey Iron Finish • Matte Black Blades • Clear Fresnel Glass
- F683L-HBZ** • Heirloom Bronze Finish • Charcoal Blades • Clear Fresnel Glass



RC400
For Details
See Page(s): 320




BOND
Compatible Fan

SHADE

with LED Light



F683L-GI



F683L-HBZ

Optional Shade



Optional
Green Shade
FS683L-GRN



Optional
Red Shade
FS683L-RD



Optional
White Shade
FS683L-WH



Optional
Tarnished Copper Shade
FS683L-TRN

LED

DC MOTOR



minkaAire

RAINMAN™



F582-BNW



F582-ORB



F582-GL





F582-SI

RAINMAN™

Reminiscent of lighting often found along shoreline walkways, the Rainman™, as the name suggests, is an excellent choice for exterior as well as interior use.

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades
- Integrated Halogen Caged Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Wall Control System Included • Indoor/Outdoor Use UL Listed for Wet Locations

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 39 Watts
- Airflow 3,495 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 89 Cubic Feet Per Minute Per Watt

- F582-SI** • Smoked Iron Finish • Smoked Iron Finish Blades • Acid Etched Glass
- F582-ORB** • Oil Rubbed Bronze Finish • Taupe Blades • Vintage Amber Glass
- F582-BNW** • Brushed Nickel Wet Finish • Silver Blades • Acid Etched Glass
- F582-GL** • Galvanized Finish • Silver Blades • Acid Etched Glass



WCS213
For Details
See Page(s): 321



BOND
Compatible Fan



F888-BNW

SLIPSTREAM

Sleek industrial styling destines this 8-bladed wonder to make a cool statement in any indoor or outdoor setting.

FEATURES

- 14° Blade Pitch • 8-Concave Blades 65" Sweep • DC 165 x 25mm Motor
- Galvanized Steel 6" Downrod • Stainless Steel Hardware and All Weather Blades
- Integrated Light Uses 1-18W GU24 Non-Dimmable Squat CFL (Included)
- Special Hand Held Remote Control System Included - RC400 • Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D715,917

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 22 Watts
- Airflow 6,216 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 285 Cubic Feet Per Minute Per Watt

- F888-BNW** • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass
- F888-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass
- F888-DK** • Distressed Koa Finish • Distressed Koa Blades • Tinted Opal Glass
- F888-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass



RC400

For Details
See Page(s): 320



BOND
Compatible Fan


SLIPSTREAM



F888-DK



F888-WHF



F888-ORB
Shown with Cap for Non-Light Use





F532-SI

SUNSEEKER

The Sunseeker features a 60-inch sweep, stylish transitional design and superb value. These elements make it an ideal choice for enjoying hot summer days outdoors.

FEATURES

- 14° Blade Pitch • 5-Blades 60" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • 3-Speed Pull Chain
- Indoor/Outdoor Use UL Listed for Wet Locations
- UL Wet Location Light Kits Available (Sold Separately. Page(s): 311)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 39 Watts
- Airflow 3,872 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 98 Cubic Feet Per Minute Per Watt

- F532-SI** • Smoked Iron Finish • Smoked Iron Finish Blades
- F532-BNW** • Brushed Nickel Wet Finish • Silver Blades
- F532-DRF** • Driftwood Finish • Driftwood Blades
- F532-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades
- F532-BWH** • Bone White Finish • Bone White Blades

SUNSEEKER



F532-BNW



F532-DRF



F532-BWH



F532-ORB





F589-ORB

SUNDOWNER®

Highly recommended for the most challenging environments, the Sundowner® combines superior performance with weatherproof components designed to withstand all outdoor conditions.

FEATURES

- 16° Blade Pitch • 5-Blades 54" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • 3-Speed Pull Chain
- Poly Molded and ABS Components • Indoor/Outdoor Use UL Listed for Wet Locations
- UL Wet Location Light Kits Available (Sold Separately. Page(s): 311)

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 46 Watts
- Airflow 4,217 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt

- F589-ORB** • Oil Rubbed Bronze Finish • Dark Maple Blades
- F589-DRF** • Driftwood Finish • Driftwood Blades
- F589-MW** • Mossoro Walnut™ Finish • Mossoro Walnut™ Blades
- F589-BWH** • Bone White Finish • Bone White Blades



F589-DRF



F589-BWH



F589-MW





F589-HT

SUNDOWNER®

- F589-HT** • Heritage™ Finish • Black Blades
- F589-VRT** • Vintage Rust™ Finish • Dark Maple Blades
- F589-BI/AI** • Black Iron with Aged Iron Accents Finish • Black Iron Finish Blades
- F589-WH** • White Finish • White Blades



F589-VRT



F589-WH



F589-BI/AI





F571-WH 52"

SUNDANCE™

Perfect for the porch, patio, gazebo or courtyard, the Sundance™ was designed to withstand all of the elements.

FEATURES

- 12° Blade Pitch • 5-Blades 52" or 42" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • 3-Speed Pull Chain
- Indoor/Outdoor Use UL Listed for Wet Locations
- UL Wet Location Light Kits Available (Sold Separately. Page(s): 311)

F571 ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 40 Watts
- Airflow 3,946 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 99 Cubic Feet Per Minute Per Watt

F572 ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 33 Watts
- Airflow 2,388 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 73 Cubic Feet Per Minute Per Watt

- F571-DRF 52"** • Driftwood Finish • Gray Blades
- F571-WH 52"** • White Finish • White Blades
- F571-ORB 52"** • Oil Rubbed Bronze Finish • Dark Oak Finish Blades
- F572-WH 42"** • White Finish • White Blades
- F572-ORB 42"** • Oil Rubbed Bronze Finish • Dark Oak Finish Blades

SUNDANCE™



F571-ORB 52"




F572-WH 42"



F572-ORB 42"

F571
Fans Only





F581-BG

GAUGUIN™

Tropical style influences the Gauguin™ by incorporating a remarkable combination of performance and unique design elements.

FEATURES

- 14° Blade Pitch • 4-Blades 52" Sweep
- Galvanized Steel 6" Downrod (Uses 3/4" I.D. DR5 Series Downrod)
- Stainless Steel Hardware and All Weather Blades
- Integrated Halogen Light Uses 1-50W MR16 120V 2-Pin Halogen Bulb (Included)
- Full Function Wall Control System Included • Cap for Non-Light Use (Included)
- Custom Ceiling Adapter Kit A581 Available (Sold Separately. Page(s): 330)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D513,319; D514,691; D514,692; D516,703; D517,201; D519,199

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 38 Watts
- Airflow 3,945 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 103 Cubic Feet Per Minute Per Watt

F581-BG • Bahama Beige™ Finish • Bahama Beige™ Blades • Etched Glass
F581-WHF • Flat White Finish • Flat White Blades • Etched Glass
F581-ORB • Oil Rubbed Bronze Finish • Bahama Beige™ Blades • Etched Glass



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan



F581-WHF



F581-ORB

F581-BG
*Shown with Optional A581-BG Ceiling Adapter
For Flush Mount Applications*





F580-VR/BB

SHANGRI-LA®

Our wicker design, coupled with a Vintage Rust™ finish, replicates a highly popular tropical motif.



F580-VR/BB
Shown with Cap for Non-Light Use

FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • 3-Speed Pull Chain
- Snap Lock/Set Screw Blade Assembly System
- Integrated Halogen Caged Etched Glass Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included) • Indoor/Outdoor Use UL Listed for Wet Location

U.S. Patent(s): D501,251; D501,922; D501,923; D502,770; D508,287; D514,215; D522,643; 7,008,192

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 46 Watts
- Airflow 3,599 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 79 Cubic Feet Per Minute Per Watt

F580-VR/BB • Vintage Rust™ Finish • Bamboo All Weather Blades • Caged Etched Glass



F727-BN/MM





VALUE COLLECTION

With the Minka-Aire® Value Collection, one need not sacrifice style and performance for affordability.

Choose from several finishes and light kit options to find the right Minka-Aire® ceiling fan with timeless style and design for the budget-conscious customer.



F690L-BN/SL

ESPACE

with LED Light

Shining as one of our brightest stars in our value collection, this transitional five blade design lends itself to larger living spaces. ESPACE provides a simplicity and refinement that inspires superior performance. It is equipped with an 18 watt AC LED light and includes a hand held remote.

FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod
- Integrated LED Light Uses 18W Dimmable LED (Included) 3 Year Warranty
- 1,100 Lumens • 3,000K • CRI 80
- Hand Held Remote Control System Included - RCS213

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 45 Watts
- Airflow 3,514 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 78 Cubic Feet Per Minute Per Watt

F690L-BN/SL • Brushed Nickel Finish • Silver Blades • Etched Opal Glass
F690L-ORB/MM • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Opal Glass
F690L-WH • White Finish • White Blades • Etched Opal Glass



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan

ESPACE

with LED Light



F690L-ORB/MM



F690L-WH

LED



F534L-ORB

LUN-AIRE

with LED Light

A versatile, all-in-one "everything" fan, Lun-Aire, with its five blades and three speeds, will be the hardest worker in the room. A simplistic, yet sophisticated design, combined with a cost efficient motor and inspired engineering for superior performance, Lun-Aire is destined to become the smartest, most dynamic orb for any room

FEATURES

- 12° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod • 3 Speed Pull Chain
 - Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 800 Lumens • 3,000K • CRI 80
- U.S. Patent(s): Pending

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
 - Airflow 3,781 Cubic Feet Per Minute
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 41 Watts
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt

F534L-ORB • Oil Rubbed Bronze Finish • Dark Pine Blades • Etched Opal Glass
F534L-WH • White Finish • White Blades • Etched Opal Glass
F534L-BN • Brushed Nickel Finish • Silver Blades • Etched Opal Glass

LUN-AIRE

with LED Light



F534L-WH



F534L-BN

LED



F727-BN/MM





F727-BN/SL
Shown with optional
K9727L-BN LED Light Kit



F727-ORB



F727-DK

RUDOLPH

Inspired by a contemporary architect of the 50's, this clean three blade design best exemplifies today's trend in home furnishings. Included is a wall control, cast blade holders and a 172 x 16mm motor for great air movement.

F727-BN/MM
See Opposite Page

FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep • 6" Downrod
- Wall Control System Included - WC116 • Convertible to Electronic Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)
- Custom LED Light Kit K9727L Available (Sold Separately. Page(s): 319)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$14
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 49 Watts
- Airflow 3,494 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 72 Cubic Feet Per Minute Per Watt

- F727-BN/MM** • Brushed Nickel Finish • Medium Maple Blades
- F727-BN/SL** • Brushed Nickel Finish • Silver Blades
- F727-ORB** • Oil Rubbed Bronze Finish • Tobacco Blades
- F727-DK** • Distressed Koa Finish • Distressed Koa Blades



WC116
For Details
See Page(s): 323



F1000-BN

*Shown with Dark Walnut Blades
Reversible to Medium Maple Blades*

DYNO

with LED Light

An addition to our Value Collection, featuring performance and design features at an affordable price. For the first time in our Value offerings, we introduce a fan with an integrated LED light source. Generous in size, style, adaptability and function, Dyno becomes one of our core fan offerings.

FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod
 - Integrated Light Uses 17W Dimmable LED (Included) 3 Year Warranty
 - 1,100 Lumens • 2,700K • CRI 80 • Hand Held Remote Control System Included
 - Replacement LED Assembly (Part #6F1000LK01)
- U.S. Patent(s): D762,836; D762,839; D780,905; Additional U.S. Patent(s) Pending

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 40 Watts
- Airflow 2,942 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 74 Cubic Feet Per Minute Per Watt

F1000-BN • Brushed Nickel Finish • Reversible Medium Maple/Dark Walnut Blades
• Etched Lens

F1000-ORB • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades
• Etched Lens

F1000-WH • White Finish • White Blades • Etched Lens



RCS213
For Details
See Page(s): 320



BOND
Compatible Fan

DYNO

with LED Light



F1000-ORB
*Shown with Dark Walnut Blades
Reversible to Medium Maple Blades*



F1000-WH

LED



F729-GM

STEAL

Inspired by the revolution that moved us from hand production methods to machines, and drove new manufacturing processes and iron production, Steal marks a major turning point in industrial style and design.

FEATURES

- 5° Blade Pitch • 3-Blades 54" Sweep • 188 x 15mm Motor • 6" Downrod
- Install with Blades at least 10' above the Floor
- 2-Wire Installation Wall Control Included - WC105-WH
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

ENERGY GUIDE INFORMATION** (All estimates based on typical use, excluding lights)

- Energy Use: 63 Watts
- Airflow 7,183 Cubic Feet Per Minute
- Airflow Efficiency: 114 Cubic Feet Per Minute Per Watt

F729-GM • Gun Metal Finish • Gun Metal Blades
F729-WHF • Flat White Finish • Flat White Blades
F729-BN • Brushed Nickel Finish • Brushed Nickel Blades



WC105-WH
For Details
See Page(s): 323

STEAL



F729-WHF



F729-BN

TRADITIONAL MOJO



F622-ORB

*Shown with Medium Maple Blades
Reversible to Dark Walnut Blades*



F622-BWH



F622-ORB/TS

*Shown with Medium Maple Blades
Reversible to Dark Walnut Blades*



F622-PW
 Shown with Dark Walnut Blades
 Reversible to Medium Maple Blades

TRADITIONAL MOJO

The Traditional Mojo is the next generation of our highly successful Mojo series. Traditional accents integrate perfectly for your home.

FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Low Profile Bowl Light Kit Uses 3-60W Candelabra Bulbs (Included) • Cap for Non-Light Use (Included)
- Solid Cap and Finial Adaptation for Remote Control Use (Included)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 43 Watts
- Airflow 3,357 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 79 Cubic Feet Per Minute Per Watt

F622-PW • Pewter Finish • Reversible Medium Maple/Dark Walnut Blades • Etched White Glass

F622-BWH • Bone White Finish • Bone White Blades • Bone White Glass

F622-ORB • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades • Etched White Glass

F622-ORB/TS • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades • Tea Stain Glass



F522-ORB/TS
 Shown with Medium Maple Blades
 Reversible to Dark Walnut Blades

Mojo

FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • Warp Resistant Plywood Blades • 3-Speed Pull Chain
- Low Profile Light Kit Uses 3-60W Candelabra Bulbs (Included) • Cap for Non-Light Use (Included)
- Solid Cap and Finial Adaptation Kit for Remote Control Use (Included)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 42 Watts
- Airflow 3,178 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 76 Cubic Feet Per Minute Per Watt

- F522-ORB/TS** • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades • Tea Stain Glass
F522-WH • White Finish • White Blades • Frosted White Glass
F522-BWH • Bone White Finish • Bone White Blades • Frosted White Glass
F522-ORB • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades • Frosted White Glass
F522-BN • Brushed Nickel Finish • Reversible Medium Maple/Dark Walnut Blades • Frosted White Glass



F522-BN
*Shown with Medium Maple Blades
Reversible to Dark Walnut Blades*



F522-WH



F522-BWH



F522-ORB
*Shown with Medium Maple Blades
Reversible to Dark Walnut Blades*

Mojo II



F533-BN
*Shown with Dark Walnut Blades
Reversible to Medium Maple Blades*



F533-WH



F533-BWH



F533-DK
*Shown with Dark Walnut Blades
Reversible to Medium Maple Blades*



F533-ORB
 Shown with Dark Walnut Blades
 Reversible to Medium Maple Blades

Mojo II

The Mojo II is another addition to our Value Collection featuring a wealth of performance and an integrated light source. A great value for low ceiling applications.

FEATURES

- 14° Blade Pitch • 4-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 13" with Light • 3-Speed Pull Chain
- Integrated Downlight Uses 3-60W Candelabra Bulbs (Included)
- Solid Cap and Finial Adaptation for Remote Control Use (Included)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 41 Watts
- Airflow 2,768 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 68 Cubic Feet Per Minute Per Watt

- F533-ORB** • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades • Tea Stain Glass
- F533-BN** • Brushed Nickel Finish • Reversible Medium Maple/Dark Walnut Blades • Frosted White Glass
- F533-DK** • Distressed Koa Finish • Reversible Medium Maple/Dark Walnut Blades • Tea Stain Glass
- F533-WH** • White Finish • White Blades • Frosted White Glass
- F533-BWH** • Bone White Finish • Bone White Blades • Bone White Glass



F510L-BS



F510L-WH

F510L-ORB
See Opposite Page

SPACESAVER

with LED Light

Contemporary styling and superb air circulation for those smaller spaces in your home; perfect for kitchens and food preparation areas, bathrooms, walk-in closets and hallways.

FEATURES

- 14° Blade Pitch • 3-Blades 26" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 10¾" Drop from Ceiling
- Integrated Light Uses 15W Dimmable LED (Included) 3 Year Warranty • 600 Lumens • 3,000K • CRI 90
- 4-Speed Fan Full Range Dimmer 3-Wire Installation Wall Control Included - WC110L
- Converts to Electronic Control

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$6
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 20 Watts
- Airflow 1,223 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 61 Cubic Feet Per Minute Per Watt

F510L-ORB • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass

F510L-BS • Brushed Steel Finish • Silver Blades • Etched Opal Glass

F510L-WH • White Finish • White Blades • Etched Opal Glass



WC110L
For Details
See Page(s): 323



F510L-ORB





F300-ORB
Oscillating Fan



F300-BN
Oscillating Fan

RETRO STYLE FAN

A special series of fans that go where you go. These portable fans offer the same style, quality and value you expect from Minka-Aire® in a compact and portable design. An accent that is reminiscent of times past, our Retro Style Fan is your quiet companion; a stylistic, subtle, tabletop solution for your comfort needs in any room.

FEATURES

- 4-Blade Turbofan 10" Sweep • 3 Speeds: 1,250, 1,400 and 1,500 R.P.M.
- Oscillates 70° Side to Side • Manual Tilt • Portable (Net Weight 7lbs.)
- 72" Heavy Duty Cord Length • Steel Construction • One Year Limited Warranty

F300-ORB • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades
F300-BN • Brushed Nickel Finish • Brushed Nickel Blades



F656L-BN/DW

ECONOMY COLLECTION

Our Economy section offers quality ceiling fans that will not break your budget. This collection of ceiling fans are comprised of quality materials and designed to uphold the Minka-Aire® commitment to excellence.

CONTRACTOR UNI-PACK LED

with LED Light



F656L-ORB

*Shown with Dark Walnut Blades
Reversible to Medium Maple Blades*



F656L-WH



F656L-PN



F656L-BN/DW
 Shown with Dark Walnut Blades
 Reversible to Medium Maple Blades

CONTRACTOR UNI-PACK LED

with LED Light

A full feature LED Contractor 52-inch fan. Featuring the incredible 26 watt LED, 1,647 Lumens, 3,000 Kelvin light source and a 172 x 14mm heavy duty motor.

FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Low Profile LED Light Uses 26W LED (Included) 3 Year Warranty • 1,647 Lumens • 3,000K • CRI 82
- Solid Cap and Finial Adaptation Kit for Remote Control Use (Included)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 43 Watts
- Airflow 3,392 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 81 Cubic Feet Per Minute Per Watt

F656L-BN/DW • Brushed Nickel Finish • Reversible Medium Maple/Dark Walnut Blades • Frosted White Glass
F656L-ORB • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades • Frosted White Glass
F656L-PN • Polished Nickel Finish • Silver Blades • Frosted White Glass
F656L-WH • White Finish • White Blades • Frosted White Glass

CONTRACTOR LED

with LED Light



F556L-BN



F556L-BWH



F556L-WH



F556L-BN/DW
*Shown with Medium Maple Blades
Reversible to Dark Walnut Blades*



F556L-ORB

*Shown with Medium Maple Blades
Reversible to Dark Walnut Blades*

CONTRACTOR LED

with LED Light

Smart simplicity at its best. This Contractor LED provides greater performance and offers energy efficiency through the use of the latest LED technology.

FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod
- Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 80
- Hand Held Remote Control Included • Replacements LED Assembly (Part #6F844LK01)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 41 Watts
- Airflow 3,646 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 89 Cubic Feet Per Minute Per Watt

F556L-ORB • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades • Etched Lens

F556L-BN • Brushed Nickel Finish • Silver Blades • Etched Lens

F556L-BWH • Bone White Finish • Bone White Blades • Etched Lens

F556L-WH • White Finish • White Blades • Etched Lens

F556L-BN/DW • Brushed Nickel Finish • Reversible Medium Maple/Dark Walnut Blades • Etched Lens



RCS213

For Details
See Page(s): 320



BOND
Compatible Fan

CONTRACTOR PLUS



F556-BN



F556-BWH



F556-BN/DW
*Shown with Medium Maple Blades
Reversible to Dark Walnut Blades*



F556-ORB
 Shown with Dark Walnut Blades
 Reversible to Medium Maple Blades

CONTRACTOR PLUS

Our Contractor Plus fan continues our tradition of offering design and reliability in several finishes.

FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$12
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 41 Watts
- Airflow 3,646 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 89 Cubic Feet Per Minute Per Watt

F556-ORB • Oil Rubbed Bronze Finish • Reversible Medium Maple/Dark Walnut Blades

F556-BN • Brushed Nickel Finish • Silver Blades

F556-BWH • Bone White Finish • Bone White Blades

F556-BN/DW • Brushed Nickel Finish • Reversible Medium Maple/Dark Walnut Blades

ULTRA-MAX™



F588-SP-ORB



F588-SP-WH



F588-SP-BN





F588-SP-BCW

ULTRA-MAX™

FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod
- Full Function Wall Control System and Hand Held Remote Control Included
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

ENERGY GUIDE INFORMATION

(All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$14
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 50 Watts
- Airflow 3,916 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 78 Cubic Feet Per Minute Per Watt

- F588-SP-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades
- F588-SP-WH** • White Finish • White Blades
- F588-SP-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades
- F588-SP-BN** • Brushed Nickel Finish • Dark Walnut Blades



RCS212
For Details
See Page(s): 320



WCS212
For Details
See Page(s): 321



BOND
Compatible Fan

SUPRA[®] 52"

with Light Kit



F569-BS



F569-WH



F569-ORB



F569-BS/DW

SUPRA[®] 52"

with Light Kit

A truly exceptional value! All the benefits of the Supra[®] 52" packaged with additional bells and whistles including a matching light kit and RCS223 Remote Control System.

FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6-Ply Warp Resistant Blades • 6" Downrod
- Halogen Light Kit Uses 1-100W Mini-Can Halogen Bulb (Included)
- Hand Held Remote Control System Included

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$14
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 49 Watts
- Airflow 3,792 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 77 Cubic Feet Per Minute Per Watt

- F569-BS/DW** • Brushed Steel Finish • Dark Walnut Blades • Opal Glass
- F569-BS** • Brushed Steel Finish • Silver Blades • Opal Glass
- F569-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Opal Glass
- F569-WH** • White Finish • White Blades • Opal Glass



RCS223
For Details
See Page(s): 320



BOND
Compatible Fan



F568-KA

*Shown with Toned Medium Maple Blades
Reversible to Medium Maple Blades*

SUPRA[®] 52"

The Supra[®] 52" offers decorative versatility in multiple finishes. It has clean, modern styling and uncompromising quality with superior performance.

FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6-Ply Warp Resistant Blades • 6" Downrod
- 3-Speed Pull Chain • Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 45 Watts
- Airflow 3,246 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 73 Cubic Feet Per Minute Per Watt

F568-KA • Kocoa Finish • Reversible Toned Medium Maple/Medium Maple Blades

F568-SWH • Shell White Finish • Shell White Blades

F568-BS/DW • Brushed Steel Finish • Dark Walnut Blades

F568-BWH • Bone White Finish • Bone White Blades

SUPRA[®] 52"



F568-SWH



F568-BS/DW



F568-BWH



SUPRA® 52"



F568-BCW



F568-WH



F568-BS



F568-ORB

SUPRA® 52"

- F568-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades
- F568-WH** • White Finish • White Blades
- F568-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades
- F568-BS** • Brushed Steel Finish • Silver Blades

SUPRA[®] 44"

with Light Kit



F563-SP



F563-SP-WH



F563-SP-BS/DW



F563-SP-ORB

SUPRA[®] 44"

with Light Kit

The Supra[®] 44", model F563-SP is a great economical option, packaged with a light kit to meet every need.

FEATURES

- 14° Blade Pitch • 5-Blades 44" Sweep • 6-Ply Warp Resistant Blades • 6" Downrod
- 3-Speed Pull Chain • Halogen Light Kit Uses 1-100W Mini-Can Halogen Bulb (Included)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 48 Watts
- Airflow 3,504 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 73 Cubic Feet Per Minute Per Watt

- F563-SP-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Opal Glass
- F563-SP** • Brushed Steel Finish • Silver Blades • Opal Glass
- F563-SP-BS/DW** • Brushed Steel Finish • Dark Walnut Blades • Opal Glass
- F563-SP-WH** • White Finish • White Blades • Opal Glass



F563-BS/DW

SUPRA[®] 44"

Designed with superior performance and all of the features found in full-size fans made available for mid-size rooms.

FEATURES

- 14° Blade Pitch • 5-Blades 44" Sweep • 6-Ply Warp Resistant Blades • 6" Downrod
- 3-Speed Pull Chain • Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$13
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 48 Watts
- Airflow 3,360 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 71 Cubic Feet Per Minute Per Watt

- F563-BS/DW** • Brushed Steel Finish • Dark Walnut Blades
- F563-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades
- F563-WH** • White Finish • White Blades
- F563-BS** • Brushed Steel Finish • Silver Blades

SUPRA[®] 44"



F563-ORB



F563-WH



F563-BS



F562-BS

SUPRA® 32"

Fashion, form and function for the smallest areas are highlighted in the Supra® 32". The perfect choice for bathrooms, hallways, entries and walk-in closets.

FEATURES

- 22° Blade Pitch • 6-Blades 32" Sweep • 6-Ply Warp Resistant Blades • 6" Downrod
- 3-Speed Pull Chain • Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 39 Watts
- Airflow 2,034 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 53 Cubic Feet Per Minute Per Watt

- F562-BS** • Brushed Steel Finish • Silver Blades
- F562-WH** • White Finish • White Blades
- F562-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades

SUPRA[®] 32"



F562-WH



F562-ORB



F647-BS

CONTRACTOR UNI-PACK

with 3-Light Kit

Offering affordable performance and reliability with designer finishes, the Contractor fan now comes with an integrated light kit.

FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 4" Downrod • 3-Speed Pull Chain
- Integrated Light Kit Uses 3-60W Candelabra Bulbs (Included)

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 39 Watts
- Airflow 2,659 Cubic Feet Per Minute

The higher the airflow, the more air the fan will move • Airflow Efficiency: 69 Cubic Feet Per Minute Per Watt

- F647-BS** • Brushed Steel Finish • Dark Walnut Blades • Etched Glass
- F647-ORB/TS** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tea Stain Glass
- F647-WH** • White Finish • White Blades • Etched Glass
- F647-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Glass

CONTRACTOR UNI-PACK

with 3-Light Kit



F647-ORB/TS



F647-WH



F647-ORB



F648-BS

CONTRACTOR UNI-PACK

with Bowl Light Kit

Our most economical and efficient fan and light combination for the budget-conscious customer, helping to save money and protect the environment through energy efficient products.

FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 4" Downrod • 3-Speed Pull Chain
- Bowl Light Kit (Included) Uses 2-13W Non-Dimmable GU24 Spiral CFL Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket • Cap for Non-Light Use (Included)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$11
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 39 Watts
- Airflow 2,864 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 73 Cubic Feet Per Minute Per Watt

F648-BS • Brushed Steel Finish • Dark Walnut Blades • Etched Swirl Glass

F648-WH • White Finish • White Blades • Etched Swirl Glass

F648-ORB • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Swirl Glass

CONTRACTOR UNI-PACK

with Bowl Light Kit



F648-WH



F648-ORB

CONTRACTOR UNI-PACK

with Bowl Light Kit



F548-WH



F548-ORB



F548-ORB/EX

CONTRACTOR UNI-PACK

with Bowl Light Kit

The most economical and efficient fan and light combination for the secondary rooms in the house.

FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Bowl Light Kit (Included) Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket • Cap for Non-Light Use (Included)

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 37 Watts
- Airflow 2,564 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 69 Cubic Feet Per Minute Per Watt

- F548-ORB/EX** • Oil Rubbed Bronze Finish • Medium Maple Blades • Excavation Glass
- F548-WH** • White Finish • White Blades • Etched Swirl Glass
- F548-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Swirl Glass

CONTRACTOR UNI-PACK

with Bowl Light Kit



F548-BWH



F548-BS



F548-BS/DW

CONTRACTOR UNI-PACK

with Bowl Light Kit

The most economical and efficient fan and light combination for the secondary rooms in the house.

FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Bowl Light Kit (Included) Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket • Cap for Non-Light Use (Included)

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 37 Watts
- Airflow 2,564 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 69 Cubic Feet Per Minute Per Watt

F548-BS/DW • Brushed Steel Finish • Dark Walnut Blades • Etched Swirl Glass
F548-BS • Brushed Steel Finish • Silver Blades • Etched Swirl Glass
F548-BWH • Bone White Finish • Bone white Blades • Etched Swirl Glass



F547-ORB

CONTRACTOR 52"

Our Contractor series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demands.

FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 4" Downrod (Uses 3/4" I.D. DR5 Series Downrod)
- 3-Speed Pull Chain • Quick Connect Detachable Switch Cup
- Pre-Installed One-Piece Motor/Blade Iron Gasket
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

Accessory Blades Available. See Page(s): 334

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 37 Watts
- Airflow 2,658 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 71 Cubic Feet Per Minute Per Watt

F547-ORB • Oil Rubbed Bronze Finish • Medium Maple Blades

F547-BS/DW • Brushed Steel Finish • Dark Walnut Blades

F547-BWH • Bone White Finish • Bone White Blades

F547-BS • Brushed Steel Finish • Silver Blades

F547-WH • White Finish • White Blades

CONTRACTOR 52"



F547-BS/DW



F547-BWH



F547-BS



F547-WH

CONTRACTOR 42"



F546-ORB



F546-WH



F546-BS



F546-BS/DW

CONTRACTOR 42"

Our Contractor 42" series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demand.

FEATURES

- 12° Blade Pitch • 5-Blades 42" Sweep • 4" Downrod • 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup • Pre-Installed One-Piece Motor/Blade Iron Gasket
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$9
Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 31 Watts
- Airflow 2,067 Cubic Feet Per Minute
The higher the airflow, the more air the fan will move • Airflow Efficiency: 67 Cubic Feet Per Minute Per Watt

- F546-BS/DW** • Brushed Steel Finish • Dark Walnut Blades
- F546-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades
- F546-BS** • Brushed Steel Finish • Silver Blades
- F546-WH** • White Finish • White Blades



F565-WH 52"



F565-BN 52"



F566-WH 42"

MESA

Our close-to-ceiling economy model in two sizes will move air in the tightest places.

FEATURES

- 12° Blade Pitch • 5-Blades 52" or 42" Sweep • Flush Mount 8¾" Overall Ceiling Drop
- 3-Speed Pull Chain • One-Piece Stamped Body • Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 311)

F565 ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$10
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 36 Watts
- Airflow 1,751 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 48 Cubic Feet Per Minute Per Watt

F566 ENERGY GUIDE INFORMATION (All estimates based on typical use, excluding lights)

- Estimated Yearly Energy Cost \$8
- Based on 12 cents per kWh and 6.4 hours use per day • Your costs depends on rates and use • Energy Use: 30 Watts
- Airflow 1,469 Cubic Feet Per Minute
- The higher the airflow, the more air the fan will move • Airflow Efficiency: 49 Cubic Feet Per Minute Per Watt

- F565-WH 52"** • White Finish • White Blades
- F565-BN 52"** • Brushed Nickel Finish • Silver Blades
- F566-WH 42"** • White Finish • White Blades

UNIVERSAL LED LIGHT KITS



K9110L **LED**

Etched White Glass
26W LED 1647 Lumens
12 1/4"Dia. x 3 3/4"H
Includes Brushed Nickel, Oil
Rubbed Bronze & White Caps
Dimmable Pull Chain



K9120L **LED**

Etched White Glass
26W LED 1647 Lumens
12 1/4"Dia. x 3 3/4"H
Includes Brushed Nickel, Oil
Rubbed Bronze & White Caps
Dimmable Pull Chain



K9115L **LED**

Etched White Glass
26W LED 1647 Lumens
12 1/4"Dia. x 2 1/2"H
Includes Brushed Nickel, Oil
Rubbed Bronze & White Caps
Dimmable Pull Chain

UNIVERSAL LIGHT KITS



K9500

Two Light
Belcaro Walnut™
60W Candelabra Base (Included)
11 1/4"Dia. x 6 1/2"H



K9515-1

Three Light
Frosted White
40W Candelabra Base (Included)
12 1/4"Dia. x 2 1/2"H
Includes Brushed Nickel & White Caps



K9515-2

Three Light
Tea Stain
40W Candelabra Base (Included)
12 1/4"Dia. x 2 1/2"H
Includes Dark Brushed Bronze & Oil
Rubbed Bronze Caps



K9525-1

Three Light
Frosted White
40W Candelabra Base (Included)
12 1/4"Dia. x 2 1/2"H
Includes Brushed Nickel & White Caps



K9525-2

Three Light
Tea Stain
40W Candelabra Base (Included)
12 1/4"Dia. x 2 1/2"H
Includes Dark Brushed Bronze & Oil
Rubbed Bronze Caps



* **K9548**

Three Light
Etched Swirl
60W Candelabra Base (Included)
12"Dia. x 5"H



K9380-1

Two Light
French Scavo
13W GU24 Spiral CFL Base
(Included)
11 1/2"Dia. x 5 1/2"H



K9380-2

Two Light
Excavation
13W GU24 Spiral CFL Base
(Included)
11 1/2"Dia. x 5 1/2"H

* Additional Cap Finishes Available
Please Note: All Light Kits include Chain with Decorative Fob.
(Not shown)

UNIVERSAL LIGHT KITS



*** K9369-L**

Three Light
Etched Swirl
60W Candelabra Base (Included)
13 1/4"Dia. x 6 1/4"H



K9372-1

Three Light
Caspian™
60W Candelabra Base (Included)
13 1/4"Dia. x 6 3/4"H



K9372-2

Three Light
Excavation
60W Candelabra Base (Included)
13 1/4"Dia. x 6 3/4"H



K9372-3

Three Light
Parchment
60W Candelabra Base (Included)
13 1/4"Dia. x 6 3/4"H



K9372-4

Three Light
Venetian Scavo
60W Candelabra Base (Included)
13 1/4"Dia. x 6 3/4"H



K9372-5

Three Light
Alabaster Dust™
60W Candelabra Base (Included)
13 1/4"Dia. x 6 3/4"H



*** K9363-L**

Three Light
Etched Marble
60W Candelabra Base (Included)
13 1/4"Dia. x 6 3/4"H



*** K9376-1**

Three Light
Caspian™
60W Candelabra Base (Included)
16"Dia. x 7 1/2"H



*** K9376-2**

Three Light
Excavation
60W Candelabra Base (Included)
16"Dia. x 7 1/2"H

Please Note: All Light Kits Include Chain with Decorative Fab. (Not Shown)



*** Additional Cap Finishes Available**

- | | | | |
|-----------|---------------------|---------------|-------------------------------------|
| AC100 | Swirled Glass | AC100-MCG | Mottled Copper with Gold Highlights |
| AC100-BCW | Belcara Walnut™ | AC100-ORB | Oil Rubbed Bronze |
| AC100-BS | Brushed Steel | AC100-PBL | Provencal Blanc |
| AC100-BWH | Bone White | AC100-PI | Patina Iron |
| AC100-CT | Cattera Bronze™ | AC100-PW | Pewter |
| AC100-DBB | Dark Brushed Bronze | AC100-STW/GOW | Sterling Walnut™/Golden Walnut |
| AC100-EX | Excavation | AC100-SWH | Shell White |
| AC100-FB | French Beige | AC100-VRT | Vintage Rust™ |
| AC100-KA | Kocca | | |



K9373-L-BS



K9373-L-ORB



K9373-L-WH

K9373

One Light Opal Glass
50W Mini-Can Xenon (Included)
9 1/2" Dia. x 5 1/4" H
For 30"/32" Sweep Fans



K9374-L-BS



K9374-L-WH

K9374

One Light Opal Glass
50W Mini-Can Xenon (Included)
10 1/2" Dia. x 5 1/4" H
For 40"/44" Sweep Fans



K9375-L-BS



K9375-L-BWH

K9375

One Light Opal Glass
50W Mini-Can Xenon (Included)
11 1/2" Dia. x 5 3/4" H
For 50"/56" Sweep Fans



K9375-L-ORB



K9375-L-WH

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)



K9401-L-BWH



K9401-L-DRF



K9401-L-HT



K9401-L-MW

Wet Location

K9401

Two Light Opal Glass
13W GU24 Spiral
CFL Bulbs (Included)
10 1/2" Dia. x 5 1/2" H



K9401-L-ORB



K9401-L-VRT



K9401-L-WH



K9402-L-ORB



K9402-L-44

K9402

One Light Opal Glass
60W Candelabra Base
(Included)
7 3/4" Dia. x 8 1/2" H

Finish Codes

BS	Brushed Steel	MW	Mossoro Walnut™
BWH	Bone White	ORB	Oil Rubbed Bronze
DRF	Driftwood	VRT	Vintage Rust™
HT	Heritage™	WH/44	White

UNIVERSAL LIGHT KITS

K37

Four Light
40W Candelabra Base (Included)
2 1/4" Side Shade
13"Dia. x 6 1/2"H



K37-L-BCW

K1

Four Light
40W Candelabra Base (Included)
2 1/4" Side Fitter
11 3/4"Dia. x 3"H



K1-L-BS



K1-L-ORB



K1-L-44

K1099

One Light
Opal Glass
60W Candelabra Base (Included)
8 1/2"Dia. x 6 3/4"H



K1099-1-L-44



K9365-L-44 (Low Profile)

Three Light
Etched Marble
60W Candelabra Base (Included)
12 1/2"Dia. x 4 1/2"H



GC900 SET

Optional Crystal Set
Available Only for the F900 Fan



Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)

Finish Codes

BCW	Belcaro Walnut™	ORB	Oil Rubbed Bronze
BS	Brushed Steel	SWH	Shell White



K33-L-BS



K33-L-FB



K33-L-MCG



K33-L-ORB



K33-L-44

K33
 Three Light
 60W Candelabra Base
 (Included)
 2 1/4" Side Shade
 6 1/4" Dia. x 3 1/2"H



K35-FB



K35-KA



K35-ORB

K35
 Three Light
 13W Spiral Medium Base
 (Included)
 2 1/4" Side Shade
 7 1/4" Dia. x 3 1/2"H



K35-MCG



K35-PW



K35-SWH



K35-VP



K35-44

Finish Codes

BN	Brushed Nickel	KA	Kocoa	PW	Pewter
BS	Brushed Steel	MCG	Mottled Copper w/Gold	SWH	Shell White
CC	Cognac	ORB	Oil Rubbed Bronze	VP	Vineyard Patina
DBB	Dark Brushed Bronze	PBL	Provencal Blanc	WH/44	White
FB	French Beige	PI	Patina Iron		

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)

UNIVERSAL LIGHT KITS



K34

Four Light
13W Spiral Medium Base
(Included)
2 1/4" Side Shade
11 3/4"Dia. x 2 3/4"H



K34-BN



K34-BCW



K34-BS



K34-CC



K34-DBB



K34-KA



K34-ORB



K34-PI



K34-PW



K34-SWH



K34-44

Finish Codes

BN	Brushed Nickel	DBB	Dark Brushed Bronze	PI	Patina Iron
BCW	Dark Brushed Bronze	KA	Kocoa	PW	Pewter
BS	Brushed Steel	MCG	Mottled Copper w/Gold	SWH	Shell White
CC	Cognac	ORB	Oil Rubbed Bronze	WH/44	White

CUSTOM LIGHT KITS



K9614-DBB



K9614-FB



K9614-MCG

K9614

Three Light
60W Candelabra Base
(Included)
2 ¼" Side Shade
8 ½"Dia. x 3 ¼"H

Compatible with the
F614 Timeless Fans Only



K9614-PW



K9659-BCW



K9659-DRF



K9659-FB

K9659

Three Light
60W Candelabra Base
(Included)
2 ¼" Side Shade
7 ½"Dia. x 3 ½"H

Compatible with the
F659 Classica Fans Only



K9659-MCG



K9659-PBL



K9659-PI

Finish Codes

BCW	Belcaro Walnut™	FB	French Beige	PI	Patina Iron
DBB	Dark Brushed Bronze	MCG	Mottled Copper w/Gold	PW	Pewter
DRF	Driftwood	PBL	Provencal Blanc		

*Please Note: All Light Kits Include Chain
with Decorative Fob. (Not Shown)*

2 1/4" GLASS SHADES



2018A
Opal
4 3/4"Dia. x 4 1/2"H



*** 2548**
Etched Opal
5 3/4"Dia. x 4 1/2"H



*** 2549**
Etched Marble
5 3/4"Dia. x 4 1/2"H



*** 2560**
Frosted/Clear
5"Dia. x 4 3/4"H



2565
Etched Seeded
4 3/4"Dia. x 4 3/4"H



*** 2593-1**
Aged Champagne
5"Dia. x 5 1/4"H



*** 2593-2**
Excavation
5"Dia. x 5 1/4"H



*** 2593-4**
Venetian Scavo
5"Dia. x 5 1/4"H



*** 2593-5**
French Cream
5"Dia. x 5 1/4"H



2632
Etched Salon Scavo™
5"Dia. x 4 3/4"H



2636
Tuscan Scavo
5"Dia. x 4 3/4"H



2645
Linen
5"Dia. x 5 1/4"H



2646
Tuscan Scavo
5"Dia. x 5 1/4"H



2652
Etched Marble
5"Dia. x 4 3/4"H



4099
4" Opal Glass Shade
8 1/2"Dia. x 5 1/2"H

CUSTOM LED LIGHT KITS



K9838L-DK



K9838L-SL



K9838L-WH

K9838L

LED Light
20W LED (Incl.)
6½" Dia. x 1¾" H
1,300 Lumens
3,000 Kelvin
CRI 90

Compatible with the
F838L Force Fans Only



K9886L-BNW



K9886L-ORB



K9886L-WHF



K9886L-SI

K9886L

LED Light
20W Dimmable LED (Incl.)
6½" Dia. x 1¾" H
1,430 Lumens
3,000 Kelvin
CRI 90
Etched Lens

Compatible with the
F886 and F896 Xtreme H₂O
Fans Only



K9787L-BNW



K9787L-ORB



K9787L-SL



K9787L-WHF

K9787L

LED Light
20W Dimmable LED (Incl.)
5" Dia. x 1½" H
1,300 Lumens
3,000 Kelvin
CRI 90
Etched Lens

Compatible with the
F786 Simple 44" and
F787 Simple 52" Fans Only



K9727L-BN



K9727L-DK



K9727L-ORB

K9727L

LED Light
17W LED (Incl.)
12" Dia. x 5" H
800 Lumens
2,700 Kelvin
CRI 80
Etched Glass

Compatible with the
F727 Rudolph Fans Only

Finish Codes

BN	Brushed Nickel	ORB	Oil Rubbed Bronze	WHF	Flat White
BNW	Brushed Nickel Wet	SI	Smoked Iron		
DK	Distressed Koa	WH/44	White		



**RCS212 Full
Function Hand Held
AireControl®
Remote System
256 Bit**

- Three Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer with Independent Up/Downlight Control
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS212 Wall Mount AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



**RCS213 Hand Held
AireControl®
Remote System
256 Bit**

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS223 Wall AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



**RCS223 Hand Held
AireControl®
Remote System
256 Bit**

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster and Canopy Mounted Receiver
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS213 Wall AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



**RC400
AireControl®
Remote System**

- For Fans that Applies, See Page 324
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008



**RC500
AireControl®
Remote System**

- For Fans that Applies, See Page 324
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008



**RC600
AireControl®
Remote System**

- For Fans that Applies, See Page 324
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008



WCS212
Full Function
AireControl®
256 Bit

- Three Speed Fan Control Forward and Reverse
- On/Off Plus Full Range Light Dimmer with Independent Up/Downlight Control
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS212 Wall Mount AireControl®
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WCS213
AireControl®
256 Bit

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS223 Wall AireControl®
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WCS223
AireControl®
256 Bit

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS213 Wall AireControl®
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



BD-1000
BOND
Wi-Fi Control System

- See Icon for Compatible Remotes



Full Function Hand Held
Remote Control

An ultra-thin design exclusive to Minka-Aire®, the remote enables the user with one finger to control all functions of Minka-Aire® ceiling fans.

AireControl® by Minka-Aire® controls all functions: reverse, uplight (where applicable), fan light, speed control, as well as off-on (RCS212 and WCS212)

RCS213, RCS223, WCS213 and WCS223 controls do not include the reverse function.

Included is a holster if you want to wall mount the control for your convenience.



WC400
AireControl[®]

- For Fans that Applies, See Page 324
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514



WC500
AireControl[®]

- For Fans that Applies, See Page 324
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514



WC600
AireControl[®]

- For Fans that Applies, See Page 324
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514



**WC105-WH
Speed Control**

- Four Speed Fan Control
- 2-Wire Installation



**WC115
Speed Control**

- For F624 Fans Only
- Four Speed Fan Control
- 2-Wire Installation



**WC106-WH
Speed Control**

- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation



**WC110
Speed Control**

- For F510 Fans Only
- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation



**WC110L
Speed Control**

- For F410L and F510L Fans Only
- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation



**WC116
Speed Control**

- For F727 Fans Only
- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation

Fan Control Systems Compatibility Chart

FAN MODEL	FAN NAME	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F302	Gyrette™	157	Incl.					•		
F304L	Cage Free Gyro™	156	•					Incl.		
F306L	Elemental Gyro™	155	•					Incl.		
F307	Anywhere	204								
F402	Gyro™ Wet	152,210	•					Incl.		
F410L	Slant	126	Wall Control Included WC110L							
F474L	Concept™ II Wet 52"	224	•					Incl.		
F476L	Concept™ I Wet 52"	222	•					Incl.		
F477L	Concept™ I Wet 58"	220	•					Incl.		
F502	Traditional Gyro™	150	•					Incl.		
F510L	Spacesaver	274	Wall Control Included WC110L							
F513	New Era	144	Incl.					•		
F514	Zen	142	Incl.					•		
F516L	Concept™ I 44"	136	Incl.					•		
F517L	Concept™ I 52"	136	Incl.					•		
F518L	Concept™ II 44"	114	Incl.					•		
F519L	Concept™ II 52"	112	Incl.					•		
F521	Aluma	74			•		Incl.			•
F522	Mojo	270			•		•			•
F523	Aluma Wet	234		Incl.					•	
F524	Roto	54			•	Incl.				•
F531	Flyte®	120		•			•		Incl.	
F532	Sunseeker	244				•	•			
F533	Mojo II	272			•		•			•
F534L	Lun-Aire	260	Compatible with WCS213 & RCS213 must use Receiver L001041000S							
F539	Great Room Traditional	160	•					Incl.		
F541L	Cone	32,216	Special Remote Included RC400, Compatible with WC400							
F543L	Swept	94	Special Remote Included RC400, Compatible with WC400							
F544	Calais™	199		Incl.			•		•	
F546	Contractor 42"	308			•	•	•			•
F547	Contractor 52"	306			•	•	•			•

• = Compatibility

Please Note: 256 Bit remote systems are not compatible with 32 Bit remote systems.
 - 256 Bit systems have a Green LED and Green receiver boxes.
 - 32 Bit systems have a Red LED and Black receiver boxes.

Fan Control Systems Compatibility Chart

FAN MODEL	FAN NAME	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F548	Contractor Uni-Pack	302			•		•			•
F556	Contractor Plus	282			•		•			•
F556L	Contractor LED	280		Incl.						
F562	Supra® 32"	296			•	•	•			•
F563	Supra® 44"	294			•	•	•			•
F563-SP	Supra® 44"	292			•		•			•
F565	Mesa™ 52"	310				•	•			
F566	Mesa™ 42"	310				•	•			
F568	Supra® 52"	288			•	•	•			•
F569	Supra® 52"	286		•	Incl.		•		•	
F571	Sundance™ 52"	250				•	•			
F572	Sundance™ 42"	250				•	•			
F580	Shangri-La®	254					•			
F581	Gauguin™	252	•					Incl.		
F582	Rainman™	240		•			•		Incl.	
F588-SP	Ultra-Max™	284	Incl.					Incl.		
F589	Sundowner®	246				•	•			
F593L	Traditional Concept™ 44"	132,228	•					Incl.		
F594L	Traditional Concept™ 52"	130,226	•					Incl.		
F596	Cirque™	140	•					Incl.		
F598	Airus™	146	•					Incl.		
F601	Acero™	128	•					Incl.		
F602	Gyro™	151	•					Incl.		
F603	Como™	134	•					Incl.		
F614	Timeless	168			•	•	•			•
F617L	Raptor	60	Special Remote Included RC600, Compatible with WC600							
F620	Bolo™	186		Incl.			•		•	
F622	Traditional Mojo	268			•		•			•
F624	Roto XL	218	Wall Control Included WC115							
F647	Contractor Uni-Pack	298			•		•			•
F648	Contractor Uni-Pack	300			•					•

• = Compatibility

Please Note: 256 Bit remote systems are not compatible with 32 Bit remote systems.

- 256 Bit systems have a Green LED and Green receiver boxes.

- 32 Bit systems have a Red LED and Black receiver boxes.

Fan Control Systems Compatibility Chart

FAN MODEL	FAN NAME	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F656L	Contractor Uni-Pack LED	278	Compatible with WCS213 & RCS213 must use Receiver L001021500S							
F659	Classica	194			•	•	•			•
F681	Groton	214	Incl.					•		
F683L	Shade	238	Special Remote Included RC400, Compatible with WC400							
F684L	Clean	34	Special Remote Included RC400, Compatible with WC400							
F688	Kola	176			•	•	•			•
F689	Kola-XL	174	Incl.					•		
F690L	Espace	258		Incl.						
F695	Kafé	182			•	•	•			•
F696	Kafé-XL	178	Incl.					•		
F701	Delano®	164		•			•		Incl.	
F702	Volterra™	198		•			•		Incl.	
F705	Napoli™	190	•					Incl.		
F711	Delano® II	166	•					Incl.		
F715	Napoli™ II	191	•					Incl.		
F726	Spectre	104	Special Remote Included RC400, Compatible with WC400							
F727	Rudolph	262	Wall Control Included WC116, Compatible with RCS213 & WCS223							
F729	Steal	266			•	Incl.				•
F734	Strata	236		Incl.						
F736L	Gear	52	Special Remote Included RC400, Compatible with WC400							
F738	Pancake	84	Incl.					•		
F739L	Pancake XL LED	80	Special Remote Included RC500, Compatible with WC500							
F745	Sabot	118	Special Remote Included RC600, Compatible with WC600							
F753	Java	62,232		Incl.						
F753L	Java LED	108,230		Incl.						
F759	Classica Gallery Edition	192		Incl.					•	
F786	Simple 44"	48	Special Remote Included RC400, Compatible with WC400							
F787	Simple 52"	46,212	Special Remote Included RC400, Compatible with WC400							
F788L	Dream Star	8	Special Remote Included RC400, Compatible with WC400							
F802	Vintage Gyro™	148	•					Incl.		

• = Compatibility

Please Note: 256 Bit remote systems are not compatible with 32 Bit remote systems.
 - 256 Bit systems have a Green LED and Green receiver boxes.
 - 32 Bit systems have a Red LED and Black receiver boxes.

Fan Control Systems Compatibility Chart

FAN MODEL	FAN NAME	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F803L	Artemis™	68	•					Incl.		
F812	Lineage™	189	•					Incl.		
F820	Santa Lucia™	188	•					Incl.		
F823	Wing	116	Special Remote Included RC400, Compatible with WC400							
F828	Symbio	78	Special Remote Included RC400, Compatible with WC400							
F829L	Mojave	64	Special Remote Included RC400, Compatible with WC400							
F831L	Tear	100	Special Remote Included RC500, Compatible with WC500							
F832L	Triple	12	Special Remote Included RC400, Compatible with WC400							
F833	Kewl	138			•	Incl.				•
F834L	Metropolis	88	Incl.					•		
F838L	Force	90	Special Remote Included RC400, Compatible with WC400							
F843	Wave	30		Incl.					•	
F844	Light Wave	86		Incl.					•	
F846L	Wave II	122	Special Remote Included RC400, Compatible with WC400							
F847L	Timber	50	Special Remote Included RC600, Compatible with WC600							
F849L	Stack	98	Special Remote Included RC400, Compatible with WC400							
F852L	Alva	240	Special Remote Included RC500, Compatible with WC500							
F853	Aviation	42	Special Remote Included RC500, Compatible with WC500							
F853L	Aviation LED	38	Special Remote Included RC500, Compatible with WC500							
F887	Xtreme	21	Special Remote Included RC400, Compatible with WC400							
F888	Slipstream	102,242	Special Remote Included RC400, Compatible with WC400							
F896-65	Xtreme H ₂ O	20	Special Remote Included RC400, Compatible with WC400							
F896-84	Xtreme H ₂ O	16,206	Special Remote Included RC400, Compatible with WC400							
F899L	Ninety-Nine	25	Special Remote Included RC600, Compatible with WC600							
F900	Cristafano™	200	•					Incl.		
F902L	Bling	110	Special Remote Included RC400, Compatible with WC400							
F903L	Artemis™ IV	56	Special Remote Included RC400, Compatible with WC400							
F905L	Artemis™ XL5	74	Special Remote Included RC600, Compatible with WC600							
F1000	Dyno	264		Incl.					•	


• = Compatibility

Please Note: 256 Bit remote systems are not compatible with 32 Bit remote systems.

- 256 Bit systems have a Green LED and Green receiver boxes.

- 32 Bit systems have a Red LED and Black receiver boxes.

HANGING SYSTEMS




FINISH	ABDD	BCW	BG	BI	BK	BN	BNK	BN/MG	BNW	BS	BWH	CC	CH	CPBR	CT	DBB	DRB	DRFF	FB	GI	GL	GM	GS	HBZ	HT	IBR	IO	KA	LN	
DR5 SERIES DOWNROD ARE 3/4" I.D.																														
DR500-COUPLER	•**	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR503	•	•	•	•	•	•	•	-	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	-	•	•	•	•	•	•
DR504	•	•	-	-	-	•	-	BN	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	
DR506	-	-	-	-	-	•	-	-	•	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
DR512	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR518	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR524	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR536	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR548	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR560	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR572	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DOWNLINK™ KIT (FOR USE WITH F531 ONLY)																														
DL06-6"	-	-	-	-	-	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL15-15"	-	-	-	-	-	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL27-27"	-	-	-	-	-	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL39-39"	-	-	-	-	-	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL51-51"	-	-	-	-	-	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL63-63"	-	-	-	-	-	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL75-75"	-	-	-	-	-	•	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
MINKA-AIRE® 45° SLOPE CEILING ADAPTER KITS (SCA)																														
* A245 3/4" I.D.	•**	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
A180	-	•	-	•	•	•	-	-	•	•	•	•	-	•	•	•	•	•	•	-	•	-	-	-	•	•	-	•	•	
*** A581	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

Minka-Aire® offers a full selection of downrods in 59 finishes and 8 lengths to complement any Minka-Aire® ceiling fan.

* A245 3/4" I.D. is also available in PR (Primer) finish.

** For F524-ABD, only.

*** For F581, only.



FINISH	MBK	MCG	MG	MP	MW	ODK	ORB	PBL	PI	PN	PW	RD	RRB	RW	SBR	SDBK	SI	SL	STW/GOW	SWH	TI	TSP	VB	VI	VP	VRT	WA	WH/44	WHF	
DR5 SERIES DOWNROD ARE 3/4" I.D.																														
DR500-COUPLER	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR503	-	•	•	•	•	•	•	•	•	•	•	•	•	•	-	-	•	•	•	•	•	•	-	•	•	•	-	•	•	
DR504	-	-	-	-	-	-	•	-	-	•	-	-	•	-	-	-	-	-	-	-	-	•	-	-	-	-	-	•	-	
DR506	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	•	
DR512	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR518	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR524	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR536	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR548	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR560	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR572	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DOWNLINK™ KIT (FOR USE WITH F531 ONLY)																														
DL06-6"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL15-15"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL27-27"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL39-39"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL51-51"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL63-63"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL75-75"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
MINKA-AIRE® 45° SLOPE CEILING ADAPTER KITS (SCA)																														
* A245 3/4" I.D.	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
A180	•	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	•	-	•	•	-	•	-	•	•	•	-	•	•	
*** A581	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	

All component parts and hardware supplied with your Minka-Aire® ceiling fan have been designed and engineered to assure proper and safe installation of your new ceiling fan. Substituting parts or hardware, such as, but not limited to the hanger ball and the hanger bracket, not supplied with your ceiling fan by Minka-Aire®, will void the Minka-Aire® Warranty.

HANGING SYSTEMS



Low Ceiling Adapter A180

For use on:
F513, F514, F522, F534L, F546, F547, F548,
F562, F563, F568, F569, F588, F589, F596,
F601, F603, F614, F620, F622, F647, F648,
F656L, F659, F688, F689, F690L, F695, F696,
F759, F828, F905L

Low Ceiling Adapter A581

For use on:
F581



A581-BG

A581-ORB

A581-WHF

Downlink™ Kit (for use on F531 only)



DL39

Downlink™ Kit
Maximum length is 72"

(Size and Finish: See Page(s): 328)

Note: It is not possible to join Downbridge™ or Downlink™ kits together for hanging fans in excess of maximum kit lengths.



Downrod Coupler DR500 (3/4" I.D.)

For those occasions when you need to hang your ceiling fan on a longer than 72" downrod, simply use one of our downrod couplers (DR500) available in finishes to match all our fans and downrods. The coupler enables you to couple our 3/4" downrods together and hang fans on total downrod lengths of up to 144".



Slope Ceiling Adapter Kit (SCA)


A245-BN (3/4" I.D.)

U.S. Patent(s): 7,510,160

Minka-Aire® 45° Slope Ceiling Adapter Kit (SCA)

Minka-Aire® SCA Kit was designed to meet the needs of the home building industry as demand increases for higher, more steeply angled ceilings. Minka-Aire® A245 SCA is used with 3/4" I.D. DR5 Series Downrod.

Sloped Ceiling Application with standard hanging systems for slopes up to a maximum of 21°



The above kit as shown includes the mounting bracket, the angled ball assembly and locking pin. For fans that weigh in excess of 35lbs, simply use the hanging bracket that comes with the fan in the box (75lbs rating standard) and the kit's angled ball assembly and locking pin. (Fan model numbers F528, F529 and F531 do not apply because of their unique Downbridge™ hanging systems)

Sloped Ceiling Installation
Minka-Aire® ceiling fans equipped with universal hanging systems may be hung from standard or vaulted ceilings up to 21° pitch.

When ordering SCA specify finish to match your needs.

(Size and Finish: See Page(s): 328)

F738 and F739L Fans Only



Internal Threaded Downrod (3/4" I.D.)

	ASL	BN	DK	ORB	WHF
DR1512	•	•	•	•	•
DR1518	•	•	•	•	•
DR1524	•	•	•	•	•
DR1536	•	•	•	•	•
DR1548	•	-	•	•	•
DR1560	•	-	•	•	•
DR1572	•	-	•	•	•

FINISHES



AB
Antique Brass



ABD/ABDD
Brushed Aluminum



BCW
Belcaro Walnut™



BG
Bahama Beige™



BI/AI
Black Iron/Aged Iron
Accents



BK
Black



BN
Brushed Nickel
(Plated)



BNK
Burnished Nickel



BNW
Brushed Nickel Wet
(Plated)



BS
Brushed Steel



BWH
Bone White



CC
Cognac



CH
Chrome
(Plated)



CPBR
Copper Bronze



CT
Cattera Bronze™



DBB
Dark Brushed Bronze



DK/ODK
Distressed Koa



DRB
Dark Restoration Bronze™



DRFF
Driftwood



FB
French Beige

Hand-painted finishes and components made from natural material may reflect variations in color and texture. These are not imperfections and enhance the unique appearance of each and every Minka-Aire® fixture. Specifications are subject to change at any time.

FINISHES



GBZ
Golden Bronze



GI
Grey Iron



GM
Gun Metal



GL
Galvanized



GS
Graphite Steel



HBZ
Heirloom Bronze



HT
Heritage™



IBR
Illuminati Bronze™



IO
Iron Oxide



KA
Kocoa



LN
Liquid Nickel
(Plated)



MBK
Matte Black



MCG
Mottled Copper
with Gold Highlights



MG
Mahogany



MP
Maple



MW
Mossoro Walnut™



ORB
Oil Rubbed Bronze



ORG
Orange



PBL
Provencal Blanc



PI
Patina Iron

FINISHES



PN
Polished Nickel
(Plated)



PW
Pewter



RD
Red



RRB
Restoration Bronze™



RW
Rosewood



SBR
Soft Brass



SDBK
Sand Black



SI
Smoked Iron



SL
Silver



STW
Sterling Walnut™



SWH
Shell White



TB
Toned Brass
(Plated)



TI
Tarnished Iron



TSP
Tuscan Patina™



VB
Volterra Bronze™



VI
Vintage Iron



VP
Vineyard Patina



VRT
Vintage Rust™



WH
White



WHF
Flat White


ACCESSORY FAN BLADES




CW
Cherry Wood




DC
Dark Cherry



DM
Dark Maple



DW
Dark Walnut




LC
Light Cherry



LM
Light Maple



ML
Reversible
Medium Oak



MM
Medium Maple

Fan Blade Compatibility Chart


Model	Fan Name	CW	DC	DM	DW	LC	LM	ML	MM	MO
F516L	Concept™ I	N/A	N/A	FB216-DM	FB216-DW	N/A	N/A	N/A	N/A	N/A
F517L	Concept™ I	N/A	N/A	FB217-DM	FB217-DW	N/A	N/A	N/A	N/A	N/A
F518L	Concept™ II	N/A	N/A	FB216-DM	FB216-DW	N/A	N/A	N/A	N/A	N/A
F519L	Concept™ II	N/A	N/A	FB217-DM	FB217-DW	N/A	N/A	N/A	N/A	N/A
F547	Contractor	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A
F548	Contractor Uni-Pack	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A
F562	Supra® 32"	N/A	FB422-DC	FB422-DM	FB422-DW	FB422-LC	FB422-LM	N/A	FB422-MM	N/A
F563	Supra® 44"	N/A	FB423-DC	FB423-DM	FB423-DW	FB423-LC	FB423-LM	N/A	FB423-MM	N/A
F568	Supra® 52"	N/A	FB424-DC	FB424-DM	FB424-DW	FB424-LC	FB424-LM	N/A	FB424-MM	N/A
F588	Ultra-Max™ 54"	FB107T-CW	N/A	N/A	FB107T-DW	FB107T-LC	N/A	N/A	FB107T-MM	N/A
F589	Sundowner®	N/A	N/A	FB107P-DM	FB107P-DW	N/A	N/A	N/A	FB107P-MM	N/A
F596	Cirque™	Optional Blades Sets are the FB196-RYB (Multi-colored, Red, Yellow, Blue) and the FB196-MG (Mahogany Finish)								
F647	Contractor Uni-Pack	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A




MO
Medium Oak




NM
Natural Maple



NW
Natural Walnut



RW
High Gloss
Rosewood



SL
Silver



SWH
Shell White



WO
Washed Oak



WP
Weathered Pine

Fan Blade Compatibility Chart

Model	Fan Name	NM	NP	NW	ORB	RW	SL	SWH	WO	WP
F516L	Concept™ I	N/A	N/A	N/A	FB216-ORB	N/A	N/A	N/A	N/A	N/A
F517L	Concept™ I	N/A	N/A	N/A	FB217-ORB	N/A	N/A	N/A	N/A	N/A
F518L	Concept™ II	N/A	N/A	N/A	FB216-ORB	N/A	N/A	N/A	N/A	N/A
F519L	Concept™ II	N/A	N/A	N/A	FB217-ORB	N/A	N/A	N/A	N/A	N/A
F547	Contractor	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP
F548	Contractor Uni-Pack	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP
F562	Supra® 32"	N/A	N/A	FB422-NW	N/A	N/A	FB422-SL	N/A	FB422-WO	FB422-WP
F563	Supra® 44"	N/A	N/A	FB423-NW	N/A	N/A	FB423-SL	N/A	FB423-WO	FB423-WP
F568	Supra® 52"	N/A	N/A	FB424-NW	N/A	N/A	FB424-SL	FB424-SWH	FB424-WO	FB424-WP
F588	Ultra-Max™ 54"	N/A	FB107T-NP	FB107T-NW	N/A	FB107T-RW	N/A	N/A	FB107T-WO	FB107T-WP
F589	Sundowner®	N/A	N/A	N/A	N/A	N/A	N/A	FB107P-SWH	N/A	N/A
F596	Cirque™		Optional Blades Sets are the FB196-RYB (Multi-colored, Red, Yellow, Blue) and the FB196-MG (Mahogany Finish)							
F647	Contractor Uni-Pack	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP

BULB REFERENCE



Watts: 10W / 20W
XENON JCX 12V
G4 BI-PIN BASE

Frosted JX4-20 (20W) Clear JX4C-10 (10W)
JX4C-20 (20W)



Watts: 35W / 50W
XENON JCX 12V
GY6.35 BI-PIN BASE

Frosted JX6-35 (35W)
JX6-50 (50W)



Watts: 25W / 35W / 40W / 60W / 75W
XENON 120V
G9 BASE

Frosted JX9-025 (25W)
JX9-035 (35W)
JX9-040 (45W)
JX9-060 (60W)
JX9-075 (75W) Clear JX9C-025 (25W)
JX9C-040 (40W)



Watts: 20W / 50W
XENON 120V
DC (BAYONET)

JXB15-20 (20W)
JXB15-50 (50W)



Watts: 75W
XENON 120V
E12 (CANDELABRA) BASE

Frosted JDXF-12-075 (75W)



Watts: 50W / 75W / 100W
MINI-CAN XENON 120V
E11 (CANDELABRA) BASE

Frosted JDX-050 (50W)
JDX-75 (75W)



Watts: 50W / 75W / 100W
MINI-CAN HALOGEN 120V
E11 (CANDELABRA) BASE

Frosted JDC-50 (50W)
JDC-75 (75W)
JDC-100 (100W) Clear JD-50 (50W)
JD-75 (75W)
JD-100 (100W)



Watts: 50W
JDD XENON 120V
E12 (CANDELABRA) BASE

Frosted JDX2F-050 (50W)
Clear JDX2-050 (50W)



Watts: 100W / 150W
78MM 120V DOUBLE ENDED
HALOGEN (J-TYPE)
R7S BASE

JB-100 (100W)
JB-150 (150W)



Watts: 8W DC / 10W AC / 11W AC / 14W AC
LED MODULE

L-L8-MD590 (8W)
L-AC10-MODULE (10W)
L-AC10-MD770 (11W)
L-AC14-MD950 (14W)



Watts: 50W
PAR16 HALOGEN
E26 (MEDIUM) BASE

PAR16-50 (50W)



Watts: 35W / 50W
HALOGEN MR16 120V
GU10 BASE

JGU-035 (35W)
JGU-50 (50W)



Watts: 20W / 35W / 50W
HALOGEN MR16
GX5.3 BI-PIN BASE

Frosted JMR16-20 (20W 120V)
JMR16-35 (35W 120V)
JMR16-50/120V (50W 120V) Clear JMR16-C-20 (20W 12V)
JMR16-C-35 (35W 12V)
JMR16-C-50 (50W 12V)



Watts: 13W / 26W
SPIRAL CFL
E26 (MEDIUM) BASE

FLB-13S (13W)



Watts: 13W / 26W
SPIRAL CFL
GU24 BASE

FLB-13M (13W)
FLB-26M (26W)



Watts: 18W / 26W
SQUAT SPIRAL CFL
GU24 BASE

FLS-18M (18W)
FLS-26M (26W)



Watts: 40W
FERRO
E26 (MEDIUM) BASE

E26-FW1910-40W (40W)



Watts: 40W / 60W / 100W
T10 120V
E26 (MEDIUM) BASE

Frosted JT10-060F (60W) Clear JT10-040C (40W)
JT10-060C (60W)
JT10-100C (100W)



Watts: 60W
T8 120V
E12 (CANDELABRA) BASE

Clear E12-FW1910-60W (60W)



Watts: 27W
FULL 24 CFL
GX10q-4 BASE

JT4-27 (27W)



Watts: 13W
4-PIN (PL-C)
G24q-1 BASE

FLT-13Q (13W)



Watts: 27W
CFL
GX10q-4 BASE

JT2-27 (27W)



Watts: 32W
FC12T9 T9 CIRCULINE
G10Q

FLC-22 (22W)
FLC-32 (32W)
FLC-40 (40W)



Watts: 8W / 13W
FLUORESCENT
T5 G13 BI-PIN BASE

Ballast: BLST08-T5
JT5-8
JT5-13



Watts: 7W
C7 CFL
E12 (CANDELABRA) BASE

FLB-07C (7W)



Watts: 75W
MR16
E17 BASE

JDR-75 (75W)



Watts: 40W / 60W
B10.5
E12 (CANDELABRA) BASE



Watts: 15W
C7
E12 (CANDELABRA) BASE

ECCC-15 (15W)



Watts: 60W
BR30
E26 (MEDIUM) BASE



Watts: 40W / 60W
A15
E26 (MEDIUM) BASE



Watts: 40W / 60W / 75W / 100W
A19
E26 (MEDIUM) BASE



Watts: 150W
A21 (3-WAY)
E26 (MEDIUM) BASE



Watts: 25W / 40W / 60W
G16 1/2
E12 (CANDELABRA) BASE



Watts: 60W / 100W
G25
E26 (MEDIUM) BASE



Watts: 60W / 100W
G30
E26 (MEDIUM) BASE



Watts: 40W / 60W / 100W
G40
E26 (MEDIUM) BASE

MODEL NUMBER	FAN NAME	PAGE	HIGH SPEED	LOW SPEED
F302	Gyrette™	157	1,502	985
F304L	Cage Free Gyro™	156	2,686	1,479
F306L	Elemental Gyro™	155	4,082	1,893
F307	Anywhere	204	1,122	605
F402	Gyro™ Wet	152,210	1,580	1,059
F410L	Slant	126	2,080	615
F474L	Concept™ II Wet 52"	224	5,363	2,821
F476L	Concept™ I Wet 52"	222	5,389	3,262
F477L	Concept™ I Wet 58"	220	5,491	2,573
F502	Traditional Gyro™	150	2,505	1,625
F510L	Spacesaver	274	1,992	459
F513	New Era	144	4,845	1,815
F514	Zen	142	6,158	1,879
F516L	Concept™ I 44"	136	3,558	1,619
F517L	Concept™ I 52"	136	5,236	2,087
F518L	Concept™ II 44"	114	3,783	1,479
F519L	Concept™ II 52"	112	5,491	1,915
F521	Aluma	74	4,318	1,353
F522	Mojo	270	4,224	2,028
F523	Aluma Wet	234	3,914	1,823
F524	Roto	54	4,623	1,553
F531	Flyte®	120	6,342	2,232
F532	Sunseeker	244	5,747	1,851
F533	Mojo II	272	4,223	1,255
F534L	Lun-Aire	260	5,198	2,175
F539	Great Room Traditional	160	9,071	3,679
F541L	Cone	32,216	8,385	2,563
F543L	Swept	94	8,177	2,508
F544	Calais™	199	6,050	2,150
F546	Contractor 42"	308	3,290	1,558
F547	Contractor 52"	306	3,807	1,488
F548	Contractor Uni-Pack	302	4,635	1,358

AIRFLOW CFM

MODEL NUMBER	FAN NAME	PAGE	HIGH SPEED	LOW SPEED
F556	Contractor Plus	282	5,450	1,746
F556L	Contractor LED	280	5,450	1,746
F562	Supra® 32"	296	3,155	914
F563	Supra® 44"	294	5,207	1,520
F563-SP	Supra® 44" -SP	292	5,322	1,619
F565	Mesa™ 52"	310	2,999	403
F566	Mesa™ 42"	310	2,388	487
F568	Supra® 52"	288	4,944	1,378
F569	Supra® 52" -SP	286	5,563	1,410
F571	Sundance™ 52"	250	5,907	1,750
F572	Sundance™ 42"	250	3,410	1,365
F580	Shangri-La®	254	5,517	1,548
F581	Gauguin™	252	5,297	2,503
F582	Rainman™	240	4,933	1,957
F588-SP	Ultra-Max™ -SP	284	6,187	1,430
F589	Sundowner®	246	6,401	1,747
F593L	Traditional Concept™ 44"	132,228	3,959	1,500
F594L	Traditional Concept™ 52"	130,226	5,203	2,116
F596	Cirque™	140	4,437	1,956
F598	Airus™	146	4,647	1,516
F601	Acero™	128	6,097	1,942
F602	Gyro™	151	2,477	1,670
F603	Como™	134	5,333	1,841
F614	Timeless	168	4,491	1,921
F617L	Raptor	60	6,710	1,894
F620	Bolo™	186	4,588	2,022
F622	Traditional Mojo	268	4,654	1,967
F624	Roto XL	218	5,927	2,526
F647	Contractor Uni-Pack	298	3,787	1,479
F648	Contractor Uni-Pack	300	4,039	1,581
F656L	Contractor Uni-Pack LED	278	5,142	1,523
F659	Classica	194	5,118	1,861

MODEL NUMBER	FAN NAME	PAGE	HIGH SPEED	LOW SPEED
F681	Groton	214	5,722	1,912
F683L	Shade	238	8,181	2,398
F684L	Clean	34	10,948	3,753
F688	Kola	176	4,740	1,403
F689	Kola-XL	174	6,727	1,647
F690L	Espace	258	5,124	1,732
F695	Kafé	182	5,741	1,518
F696	Kafé-XL	178	6,418	1,483
F701	Delano®	164	5,530	1,482
F702	Volterra™	198	5,243	1,868
F705	Napoli™	190	5,609	2,370
F711	Delano® II	166	3,772	936
F715	Napoli™ II	191	6,180	1,640
F726	Spectre	104	6,498	1,639
F727	Rudolph	262	5,168	1,712
F729	Steal	266	7,230	1,909
F734	Strata	236	4,648	1,925
F736L	Gear	52	7,450	2,146
F738	Pancake	84	3,941	780
F739L	Pancake XL LED	80	6,723	3,122
F745	Sabot	118	4,348	960
F753	Java	62,232	5,357	2,782
F753L	Java LED	108,230	5,846	2,898
F759	Classica Gallery Edition	192	4,970	1,884
F786	Simple 44"	48	5,323	1,615
F787	Simple 52"	46,212	5,745	1,326
F788L	Dream Star	8	8,063	1,823
F802	Vintage Gyro™	148	1,770	1,240
F803L	Artemis™	68	5,284	2,587
F812	Lineage™	189	6,238	1,589
F820	Santa Lucia™	188	5,837	2,696
F823	Wing	116	5,667	1,805

AIRFLOW CFM

MODEL NUMBER	FAN NAME	PAGE	HIGH SPEED	LOW SPEED
F828	Symbio	78	6,276	1,717
F829L	Mojave	64	7,594	2,547
F831L	Tear	100	7,869	3,120
F832L	Triple	12	6,012	2,125
F833	Kewl	138	5,010	1,507
F834L	Metropolis	88	5,589	2,601
F838L	Force	90	4,438	281
F843	Wave	30	4,818	1,657
F844	Light Wave	86	4,531	1,491
F846	Wave II	122	4,231	1,158
F847L	Timber	50	8,960	2,109
F849L	Stack	98	5,968	1,574
F852L	Alva	240	7,045	3,304
F853	Aviation	42	5,159	2,159
F853L	Aviation LED	38	5,159	2,159
F887-72	Xtreme 72"	21	8,905	3,036
F887-96	Xtreme 96"	21	13,080	9,152
F888	Slipstream	102,242	8,263	3,916
F896-65	Xtreme H ₂ O 65"	20	9,092	3,800
F896-84	Xtreme H ₂ O 84"	16,206	11,157	5,075
F899L	Ninety-Nine	25	13,350	7,803
F900	Cristafano™	200	7,885	3,038
F902L	Bling	110	6,019	1,523
F903L	Artemis™ IV	56	8,520	2,913
F905L	Artemis™ XL5	74	6,245	3,461
F1000	Dyno	264	4,223	1,561

Lined area for notes, consisting of 30 horizontal lines.

INDEX

ACCESSORIES

AC100	312
AC100-BCW	312
AC100-BS	312
AC100-BWH	312
AC100-CT	312
AC100-DBB	312
AC100-EX	312
AC100-FB	312
AC100-KA	312
AC100-MCG	312
AC100-ORB	312
AC100-PBL	312
AC100-PI	312
AC100-PW	312
AC100-STW/GOW	312
AC100-SWH	312
AC100-VRT	312
CM7022-STW	190
CM7038-STW	191
CM8222-IBR	188
GC900 SET	200, 314

ACCESSORY BLADES

FB103S-DM	334
FB103S-DW	334
FB103S-LC	334
FB103S-LM	334
FB103S-ML	334
FB103S-MM	334
FB103S-NM	335
FB103S-NW	335
FB103S-RW	335
FB103S-SL	335
FB103S-SWH	335

FB103S-WO	335
FB103S-WP	335
FB107P-DM	334
FB107P-DW	334
FB107P-MM	334
FB107P-SWH	335
FB107T-CW	334
FB107T-DW	334
FB107T-LC	334
FB107T-MM	334
FB107T-NP	335
FB107T-NW	335
FB107T-RW	335
FB107T-WO	335
FB107T-WP	335
FB196-MG	141, 334, 335
FB196-RYB	141, 334, 335
FB216-DM	334
FB216-DW	334
FB216-ORB	335
FB217-DM	334
FB217-DW	334
FB217-ORB	335
FB422-DC	334
FB422-DM	334
FB422-DW	334
FB422-LC	334
FB422-LM	334
FB422-MM	334
FB422-NW	335
FB422-SL	335
FB422-WO	335
FB422-WP	335
FB423-DC	334
FB423-DM	334

FB423-DW	334
FB423-LC	334
FB423-LM	334
FB423-MM	334
FB423-NW	335
FB423-SL	335
FB423-WO	335
FB423-WP	335
FB424-DC	334
FB424-DM	334
FB424-DW	334
FB424-LC	334
FB424-LM	334
FB424-MM	334
FB424-NW	335
FB424-SL	335
FB424-SWH	335
FB424-WO	335
FB424-WP	335

CONTROL SYSTEMS

BD-1000	321
RC400	320
RC500	320
RC600	320
RCS212	320
RCS213	320
RCS223	320
WC105-WH	323
WC106-WH	323
WC110	323
WC110L	323
WC115	323
WC116	323
WC400	322

WC500	322	F513-BN	144	F524-ABD	55
WC600	322	F513-KA	145	F524-DK	55
WCS212	321	F513-ORB	145	F524-ORB	55
WCS213	321	F513-WH	145	F524-WHF	54
WCS223	321	F514-BN	142	F531-L-BN	120
		F514-ORB	143	F531-L-BN/MG	121
FANS		F514-WH	142	F531-L-WH	120
F300-BN	276	F516L-BN	137	F532-BNW	245
F300-ORB	276	F516L-ORB	136	F532-BWH	245
F302-BN	157	F516L-PN	137	F532-DRF	245
F302-RRB	157	F516L-WH	137	F532-ORB	245
F304L-BN/SL	156	F517L-BN	137	F532-SI	244
F304L-ORB/MM	156	F517L-ORB	136	F533-BN	272
F306L-BS/SL	155	F517L-PN	137	F533-BWH	272
F306L-ORB/MM	154	F517L-WH	137	F533-DK	272
F307-BN	204	F518L-BN	115	F533-ORB	273
F307-MBK	205	F518L-ORB	114	F533-WH	272
F402-BNW	153, 210	F518L-PN	115	F534L-BN	261
F402-ORB	152, 211	F518L-WH	115	F534L-ORB	260
F410L-BS	126	F519L-BN	112	F534L-WH	261
F410L-ORB	127	F519L-MG	113	F539-BCW	163
F410L-WH	127	F519L-ORB	113	F539-BN	163
F474L-BNW	225	F519L-PN	113	F539-BNK	160
F474L-ORB	224	F519L-WH	113	F539-HBZ	162
F474L-WH	224	F521-ABD	92	F539-ORB	163
F476L-BNW	222	F521-ORB	93	F541L-ORB	33, 217
F476L-ORB	223	F521-WHF	93	F541L-SL	32, 33, 216, 217
F476L-WH	223	F522-BN	271	F541L-WH	33, 217
F477L-BNW	221	F522-BWH	271	F543L-DK	94
F477L-ORB	220	F522-ORB	271	F543L-KA	97
F477L-WH	221	F522-ORB/TS	270	F543L-SL	96
F502-BCW	150	F522-WH	271	F543L-WHF	97
F510L-BS	274	F523-ABD	234	F544-BCW	199
F510L-ORB	275	F523-ORB	235	F546-BS	308
F510L-WH	274	F523-WHF	235	F546-BS/DW	309

INDEX

F546-ORB	308	F566-WH	310	F589-VRT	249
F546-WH	308	F568-BCW	290	F589-WH	249
F547-BS	307	F568-BS	290	F593L-ORB	133, 229
F547-BS/DW	307	F568-BS/DW	289	F593L-PW	132, 228
F547-BWH	307	F568-BWH	289	F593L-WH	133, 229
F547-ORB	306	F568-KA	288	F594L-ORB	130, 226
F547-WH	307	F568-ORB	291	F594L-PW	131, 227
F548-BS	304	F568-SWH	289	F594L-WH	131, 227
F548-BS/DW	305	F568-WH	290	F596-BN	140, 141
F548-BWH	304	F569-BS	286	F596-PN/TL	141
F548-ORB	302	F569-BS/DW	287	F598-BN	147
F548-ORB/EX	303	F569-ORB	286	F598-ORB	146
F548-WH	302	F569-WH	286	F598-WH	147
F556-BN	282	F571-ORB	251	F601-BS/BN	129
F556-BN/DW	282	F571-WH	250	F601-BS/MG	128
F556-BWH	282	F572-ORB	251	F601-ORB	129
F556L-BN	280	F572-WH	251	F601-PN	129
F556L-BN/DW	280	F580-VR/BB	255	F602-BN/CH	151
F556L-BWH	280	F581-BG	252	F602-RRB	151
F556L-ORB	281	F581-ORB	253	F603-BN	135
F556L-WH	280	F581-WHF	253	F603-ORB	134
F556-ORB	283	F582-BNW	240	F603-WH	134
F562-BS	296	F582-GL	240	F614-BNK	170
F562-ORB	297	F582-ORB	240	F614-DBB	171
F562-WH	297	F582-SI	241	F614-FB	173
F563-BS	295	F588-SP-BCW	285	F614-HBZ	168
F563-BS/DW	294	F588-SP-BN	284	F614-ORB	171
F563-ORB	295	F588-SP-ORB	284	F614-PI	173
F563-SP	292	F588-SP-WH	284	F614-PW	172
F563-SP-BS/DW	292	F589-BI/AI	249	F617L-BN	60
F563-SP-ORB	293	F589-BWH	247	F617L-GM	61
F563-SP-WH	292	F589-DRF	247	F617L-ORB/AB	60
F563-WH	295	F589-HT	248	F620-BCW	187
F565-BN	310	F589-MW	247	F620-BN	186
F565-WH	310	F589-ORB	246	F620-DBB	187

F620-ORB	187	F684L-ORB/TB	36	F711-PW	167
F622-BWH	268	F684L-PN	37	F715-STW	191
F622-ORB	268	F688-DBB	177	F726-BN/ORG	105
F622-ORB/TS	268	F688-KA	177	F726-BN/SL	104
F622-PW	269	F688-PW	176	F726-ORB/AB	106
F624-ABD	219	F688-WH	177	F726-ORB/BN	107
F624-ORB	218	F689-DBB	175	F726-WHF/BN	105, 107
F624-WHF	219	F689-KA	174	F727-BN/MM	256, 262
F647-BS	298	F689-PW	175	F727-BN/SL	263
F647-ORB	299	F689-WH	175	F727-DK	263
F647-ORB/TS	299	F690L-BN/SL	258	F727-ORB	263
F647-WH	299	F690L-ORB/MM	259	F729-BN	267
F648-BS	300	F690L-WH	259	F729-GM	266
F648-ORB	301	F695-BNK	182	F729-WHF	267
F648-WH	301	F695-CC	185	F734-GL	237
F656L-BN/DW	277, 279	F695-HBZ	184	F734-ORB	236
F656L-ORB	278	F695-KA	185	F734-SI	237
F656L-PN	278	F695-VP	185	F736L-BS/SDBK	52
F656L-WH	278	F695-WH	185	F736L-BS/WHF	52
F659-BCW	197	F696-BNK	180	F736L-PN/BS	52
F659-DRF	194	F696-CC	181	F736L-PN/ORB	53
F659-FB	197	F696-HBZ	178	F738-DK	84
F659-MCG	197	F696-KA	181	F738-ORB	85
F659-PBL	196	F696-VP	181	F738-SL	84
F659-PI	197	F696-WH	181	F738-WHF	84
F681-BNW	214	F701-DRB	164	F739L-BN	80
F681-ORB	215	F701-DRF	164	F739L-DK	82
F681-PN	214	F701-KA	164	F739L-SL	83
F681-SDBK/WS	202, 214	F701-PN	165	F739L-WHF	82
F681-WA/PW	214	F701-PW	164	F745-BN	119
F683L-BNW	238	F702-BCW	198	F745-DK	119
F683L-GI	239	F702-VB	198	F745-ORB	118
F683L-HBZ	239	F705-STW	190	F753-BNW	63, 233
F684L-GI/BN	37	F711-DRB	166	F753-KA	62, 232
F684L-MBK/BN	34	F711-PN	167	F753L-BNW	108, 230

INDEX

F753L-KA	109, 231	F823-SL	117	F846-SL	125
F753L-PN	109	F823-WH	117	F846-WHF	122, 125
F753L-WHF	109, 230	F828-BN	78	F847L-HBZ/AW	50
F753-PN	63	F828-BN/DW	79	F847L-HBZ/MP	51
F753-WHF	63, 233	F828-BN/WH	78	F849L-BN/SL	98
F759-PBL	192, 193	F828-ORB	78	F849L-SL	98
F786-BNW	49	F828-WHF	78	F849L-WH	99
F786-ORB	48	F829L-CH/CH	65	F852L-BN	159
F786-SL	49	F829L-CH/SL	67	F852L-HBZ	158
F786-WHF	49	F829L-SL	67	F852L-TI	159
F787-BNW	47, 213	F829L-WHF	66	F853-BN/DK	42
F787-ORB	47, 212	F831L-ORB	100	F853-BN/MM	44
F787-SL	46, 213	F831L-SL	100	F853-BN/SL	45
F787-WHF	47, 213	F831L-TD	101	F853L-BN/AMP	40
F788L-GS	8	F831L-WHF	100	F853L-BN/DK	39
F788L-ORB	11	F832L-BN/SL	15	F853L-BN/MM	41
F788L-WH	10	F832L-BS	14	F853L-BN/SL	41
F802-BN/CH	149	F832L-ORB/MM	14	F853L-BN/WH	41
F802-KA	149	F832L-VI	12	F853-RW	43
F802-ORB	149	F833-BK	139	F853-WH	45
F802-PN	148	F833-RD	138	F887-72-BN	22
F803L-BK	73	F833-SL	139	F887-72-ORB	24
F803L-CPBR	71	F833-WH	139	F887-96-BN	22
F803L-DK	69	F834L-BS/PN	88	F887-96-ORB	24
F803L-LN	70	F834L-ORB/PN	89	F888-BNW	102, 242
F803L-MG	71	F838L-DK	90	F888-DK	103, 243
F803L-MP	72	F838L-SL	91	F888-ORB	103, 243
F803L-RD	68	F838L-WH	91	F888-WHF	103, 243
F803L-SL	71	F843-DK	31	F896-65-BNW	19, 208
F803L-TL	73	F843-SL	30	F896-65-ORB	20, 209
F803L-WH	73	F843-WH	31	F896-65-WHF	20, 209
F812-IO	189	F844-DK	87	F896-84-BNW	17, 206
F820-CT	188	F844-SL	86	F896-84-ORB	16, 207
F820-IBR	188	F844-WH	87	F896-84-SI	18, 207
F823-DK	116	F846-DK	124	F899L-BN/SL	27

F899L-DK	26
F899L-ORB	28
F900-BCW	200, 201
F902L-CH	110, 111
F903L-BN/SL	58
F903L-GM/MBK	59
F903L-ORB	59
F903L-SBR/MBK	56
F905L-DK	76
F905L-LN	74
F905L-SL	77
F905L-WH	77
F1000-BN	264
F1000-ORB	265
F1000-WH	265

FAN SHADE

FS683L-GRN	239
FS683L-RD	239
FS683L-TRN	239
FS683L-WH	239

GLASS SHADES

2018A	318
2548	318
2549	318
2560	318
2565	318
2593-1	318
2593-2	318
2593-4	318
2593-5	318
2632	318
2636	318
2645	318

2646	318
2652	318
4099	318

HANGING SYSTEMS

A180	328, 329, 330
A245	328, 329
A245-BN	330
A581	328, 329
A581-BG	253, 330
A581-ORB	330
A581-WHF	330
DL06	328, 329
DL15	328, 329
DL27	328, 329
DL39	328, 329, 330
DL51	328, 329
DL63	328, 329
DL75	328, 329
DR500	328, 329, 330
DR503	328, 329
DR504	328, 329
DR506	328, 329
DR512	328, 329
DR518	328, 329
DR524	328, 329
DR536	328, 329
DR548	328, 329
DR560	328, 329
DR572	328, 329
DR1512	330
DR1518	330
DR1524	330
DR1536	330
DR1548	330

DR1560	330
DR1572	330

LIGHT KITS - CUSTOM

K9614-DBB	317
K9614-FB	317
K9614-MCG	317
K9614-PW	317
K9659-BCW	317
K9659-DRF	317
K9659-FB	317
K9659-MCG	317
K9659-PBL	317
K9659-PI	317

LIGHT KITS - CUSTOM LED

K9727L-BN	319
K9727L-DK	319
K9727L-ORB	319
K9787L-BNW	319
K9787L-ORB	319
K9787L-SL	319
K9787L-WHF	319
K9838L-DK	319
K9838L-SL	319
K9838L-WH	319
K9886L-BNW	319
K9886L-ORB	319
K9886L-SI	319
K9886L-WHF	319

LIGHT KITS - UNIVERSAL

K1-L-44	314
K1-L-BS	314
K1-L-ORB	314

INDEX

K33-L-44	315	K9373-L-ORB	313
K33-L-BS	315	K9373-L-WH	313
K33-L-FB	315	K9374-L-BS	313
K33-L-MCG	315	K9374-L-WH	313
K33-L-ORB	315	K9375-L-BS	313
K34-44	316	K9375-L-BWH	313
K34-BCW	316	K9375-L-ORB	313
K34-BN	316	K9375-L-WH	313
K34-BS	316	K9376-1	312
K34-CC	316	K9376-2	312
K34-DBB	316	K9380-1	311
K34-KA	316	K9380-2	311
K34-ORB	316	K9401-L-BWH	313
K34-PI	316	K9401-L-DRF	313
K34-PW	316	K9401-L-HT	313
K34-SWH	316	K9401-L-MW	313
K35-44	315	K9401-L-ORB	313
K35-FB	315	K9401-L-VRT	313
K35-KA	315	K9401-L-WH	313
K35-MCG	315	K9402-L-44	313
K35-ORB	315	K9402-L-ORB	313
K35-PW	315	K9500	311
K35-SWH	315	K9515-1	311
K35-VP	315	K9515-2	311
K37-L-BCW	314	K9525-1	311
K1099-1-L-44	314	K9525-2	311
K9363-L	312	K9548	311
K9365-L-44	314		
K9369-L	312	LIGHT KITS - UNIVERSAL LED	
K9372-1	312	K9110L	311
K9372-2	312	K9115L	311
K9372-3	312	K9120L	311
K9372-4	312		
K9372-5	312		
K9373-L-BS	313		



Acero™
F601
Page(s) 128 - 129



Airus™
F598
Page(s) 146 - 147



Aluma
F521
Page(s) 92 - 93



Aluma Wet
F523
Page(s) 234 - 235



Alva
F852L
Page(s) 158 - 159



Anywhere
F307
Page(s) 204-205



Artemis™
F803L
Page(s) 68 - 73



Artemis™ IV
F903L
Page(s) 56 - 59



Artemis™ XL5
F905L
Page(s) 74 - 77



Aviation
F853
Page(s) 42 - 45



Aviation LED
F853L
Page(s) 38 - 41



Bling
F902L
Page(s) 110 - 111



Bolo™
F620
Page(s) 186 - 187



Cage Free Gyro™
F304L
Page(s) 156



Calais™
F544
Page(s) 199



Cirque™
F596
Page(s) 140 - 141



Classica
F659
Page(s) 194 - 197



Classica - Gallery Edition
F759
Page(s) 192 - 193



Clean
F684L
Page(s) 34 - 37



Como™
F603
Page(s) 134 - 135



Concept™ I 44"
F516L
Page(s) 136 - 137



Concept™ I 52"
F517L
Page(s) 136 - 137



Concept™ I Wet 52"
F476L
Page(s) 222 - 223



Concept™ I Wet 58"
F477L
Page(s) 220 - 221



Concept™ II 44"
F518L
Page(s) 114 - 115



Concept™ II 52"
F519L
Page(s) 112 - 113



Concept™ II Wet 52"
F474L
Page(s) 224 - 225



Cone
F541L
Page(s) 32 - 33, 216 - 217



Contractor 42"
F546
Page(s) 308 - 309



Contractor 52"
F547
Page(s) 306 - 307



Contractor LED
F556L
Page(s) 280 - 281



Contractor Plus
F556
Page(s) 282 - 283



Contractor Uni-Pack
F548
Page(s) 302 - 305



Contractor Uni-Pack
F647
Page(s) 298 - 299



Contractor Uni-Pack
F648
Page(s) 300 - 301



Contractor Uni-Pack LED
F656L
Page(s) 278 - 279



Cristafano™
F900
Page(s) 200 - 201



Delano®
F701
Page(s) 164 - 165



Delano® II
F711
Page(s) 166 - 167



Dream Star
F788L
Page(s) 8 - 11




Dyno
F1000
Page(s) 264 - 265



Elemental Gyro™
F306L
Page(s) 154 - 155



Espace
F690L
Page(s) 258 - 259



Flyte®
F531
Page(s) 120 - 121



Force
F838L
Page(s) 90 - 91



Gauguin™
F581
Page(s) 252 - 253



Gear
F736L
Page(s) 52 - 53



Great Room Traditional
F539
Page(s) 160 - 163



Groton
F681
Page(s) 214 - 215



Gyrette™
F302
Page(s) 157



Gyro™
F602
Page(s) 151



Gyro™ Wet
F402
Page(s) 152 - 153, 210 - 211



Java
F753
Page(s) 62 - 63, 232 - 233



Java LED
F753L
Page(s) 108 - 109, 230 - 231



Kafé
F695
Page(s) 182 - 185



Kafé-XL
F696
Page(s) 178 - 181



Kewl
F833
Page(s) 138 - 139



Kola
F688
Page(s) 176 - 177



Kola-XL
F689
Page(s) 174 - 175



Light Wave
F844
Page(s) 86 - 87



Lineage™
F812
Page(s) 189




Lun-Aire
F534L
Page(s) 260 - 261



Mesa™
F565/F566
Page(s) 310



Metropolis
F834L
Page(s) 88 - 89



Mojave
F829L
Page(s) 64 - 67



Mojo
F522
Page(s) 270 - 271



Mojo II
F533
Page(s) 272 - 273



Napoli™
F705
Page(s) 190



Napoli™ II
F715
Page(s) 191



New Era
F513
Page(s) 144 - 145



Ninety-Nine
F899L
Page(s) 25 - 29



Pancake
F738
Page(s) 84 - 85



Pancake XL LED
F739L
Page(s) 80 - 83




Rainman™
F582
Page(s) 240 - 241



Raptor
F617L
Page(s) 60 - 61



Retro Style Fan
F300
Page(s) 276



Roto
F524
Page(s) 54 - 55



Roto XL
F624
Page(s) 218 - 219



Rudolph
F727
Page(s) 262 - 263



Sabot
F745
Page(s) 118 - 119




Santa Lucia™
F820
Page(s) 188



Shade
F683L
Page(s) 238 - 239



Shangri-La®
F580
Page(s) 254 - 255



Simple 44"
F786
Page(s) 48 - 49



Simple 52"
F787
Page(s) 46 - 47, 212 - 213



Slant
F410L
Page(s) 126 - 127



Slipstream
F888
Page(s) 102 - 103, 242 - 243



Spacesaver
F510L
Page(s) 274 - 275



Spectre
F726
Page(s) 104 - 107



Stack
F849L
Page(s) 98 - 99



Steal
F729
Page(s) 266 - 267



Strata
F734
Page(s) 236 - 237



Sundance™
F571/F572
Page(s) 250 - 251



Sundowner®
F589
Page(s) 246 - 249



Sunseeker
F532
Page(s) 244 - 245



Supra® 32"
F562
Page(s) 296 - 297



Supra® 44"
F563
Page(s) 294 - 295



Supra® 44" -SP
F563-SP
Page(s) 292 - 293



Supra® 52"
F568
Page(s) 288 - 291




Supra® 52"
F569
Page(s) 286 - 287



Swept
F543L
Page(s) 94 - 97



Symbio
F828
Page(s) 78 - 79



Tear
F831L
Page(s) 100 - 101



Timber
F847L
Page(s) 50 - 51



Timeless
F614
Page(s) 168 - 173



Traditional Concept™ 44"
F593L
Page(s) 132 - 133, 228 - 229



Traditional Concept™ 52"
F594L
Page(s) 130 - 131, 226 - 227



Traditional Gyro™
F502
Page(s) 150



Traditional Mojo
F622
Page(s) 268 - 269



Triple
F832L
Page(s) 12 - 15



Xtreme
F887
Page(s) 21 - 24



Ultra-Max™
F588-SP
Page(s) 284 - 285



Vintage Gyro™
F802
Page(s) 148 - 149



Volterra™
F702
Page(s) 198



Xtreme H₂O
F896
Page(s) 16 - 20, 206 - 209



Zen
F514
Page(s) 142 - 143



Wave
F843
Page(s) 30 - 31



Wave II
F846
Page(s) 122 - 125



Wing
F823
Page(s) 116 - 117

FAN SPECIFICATIONS

		Page Number	Blade Sweep	No of Blades	Blade Pitch	Motor Size	RPM (Hi/Low)	Warranty	Light Kit	Downrods 3/4" ID	Downrod 1/2" ID	Lead Wire	Dimension A	Dimension B	Hanging Weight (LBS)
F300	Retro Style	276	10"	3	14°	70 x 70	1253/1525	One Year	N/A	N/A	N/A	72"	N/A	N/A	6
F302	Gyrette™	157	36"	8	14°	82 x 25	1470/800	Limited Lifetime	N/A	4 1/2"	N/A	54"	16 1/4"	22 1/2"	19
F304L	Cage Free Gyro™	156	37"	6	23°	70 x 16	1470/800	Limited Lifetime	Integrated	6"	N/A	80"	22 1/4"	17 3/4"	19
F306L	Elemental Gyro™	154	42"	6	23°	70 x 16	1470/800	Limited Lifetime	Integrated	6"	N/A	80"	23"	18"	19
F307	Anywhere	204	15"	3	23°	82 x 25	985/491	Limited Lifetime	N/A	6"	N/A	118"	N/A	N/A	20
F402	Gyro™ Wet	152, 210	42"	6	20°	82 x 25	1350/720	Limited Lifetime	Integrated	6"	N/A	80"	19 1/2"	17 3/4"	30
F410L	Slant	126	36"	3	20°	120 x 20	300/150	Limited Lifetime	Integrated	6"	N/A	80"	15"	10 1/2"	15
F474L	Concept™ II Wet 52"	224	52"	3	14°	188 x 20	170/92	Limited Lifetime	Integrated	N/A	N/A	8"	12"	8 1/2"	26
F476L	Concept™ I Wet 52"	222	52"	3	14°	188 x 20	168/93	Limited Lifetime	Integrated	6"	N/A	80"	20 1/2"	17"	25
F477L	Concept™ I Wet 58"	220	58"	3	14°	188 x 22	158/68	Limited Lifetime	Integrated	6"	N/A	80"	18 1/4"	14 1/4"	27
F502	Traditional Gyro™	150	42"	6	20°	80 x 25	1350/720	Limited Lifetime	Integrated	4 1/2" & 12"	N/A	80"	17"	16 1/2"	40
F510L	Spacesaver	274	26"	3	14°	153 x 12	392/170	Limited Lifetime	Integrated	N/A	N/A	8"	11"	7 1/4"	12
F513	New Era	144	52"	4	14°	172 x 16	199/67	Limited Lifetime	Adaptable	6"	N/A	80"	15 1/2"	12 3/4"	18
F514	Zen	142	52"	4	14°	172 x 16	209/67	Limited Lifetime	Integrated	6"	N/A	80"	18 1/2"	12 3/4"	20
F516L	Concept™ I 44"	136	44"	3	14°	153 x 15	189/91	Limited Lifetime	Integrated	6"	N/A	80"	17 1/2"	14 1/4"	22
F517L	Concept™ I 52"	136	52"	3	14°	172 x 20	183/70	Limited Lifetime	Integrated	6"	N/A	80"	17 1/2"	14 1/4"	25
F518L	Concept™ II 44"	114	44"	3	14°	153 x 15	181/79	Limited Lifetime	Integrated	N/A	N/A	8"	11 1/2"	8 1/4"	24
F519L	Concept™ II 52"	112	52"	3	14°	172 x 20	172/66	Limited Lifetime	Integrated	N/A	N/A	8"	11 1/2"	8 1/4"	27
F521	Aluma	92	52"	4	12°	153 x 15	187/100	Limited Lifetime	Integrated	6"	N/A	80"	15 3/4"	12 1/4"	17
F522	Mojo	270	52"	5	12°	153 x 15	162/60	Limited Lifetime	Included	6"	N/A	80"	17"	11 1/2"	18
F523	Aluma Wet	234	52"	4	12°	153 x 20	166/73	Limited Lifetime	Integrated	6"	N/A	80"	16 1/2"	13 1/4"	19
F524	Roto	54	52"	3	22°	153 x 15	210/112	Limited Lifetime	N/A	6"	N/A	80"	11 3/4"	9 1/2"	11
F531	Flyte®	120	56"	3	14°	188 x 25	178/82	Limited Lifetime	Integrated	N/A	9" DL	80"	17 3/4"	16 1/4"	27
F532	Sunseeker	244	60"	5	14°	188 x 25	135/50	Limited Lifetime	Integrated	6"	N/A	80"	16 1/2"	14 3/4"	28
F533	Mojo II	272	52"	4	14°	153 x 15	168/84	Limited Lifetime	Integrated	N/A	N/A	12"	12 1/2"	8"	18
F534L	Lun-Aire	260	54"	5	12°	172 x 17	150/70	Limited Lifetime	Integrated	6"	N/A	80"	15 1/4"	10 1/2"	25
F539	Great Room Traditional	160	72"	5	14°	212 x 25	126/45	Limited Lifetime	Adaptable	6"	N/A	80"	15 1/4"	13"	35
F541L	Cone	32, 216	54"	5	14°	DC123 x 30	169/102	Limited Lifetime	Integrated	6"	N/A	74"	13 3/4"	11 1/2"	14
F543L	Swept	94	56"	4	26°	DC123 x 30	191/51	Limited Lifetime	Integrated	6"	N/A	80"	14 1/2"	12"	14
F544	Calais™	199	52"	5	14°	172 x 17	165/62	Limited Lifetime	Integrated	N/A	N/A	8"	12"	7 1/2"	27
F546	Contractor 42"	308	42"	5	12°	153 x 10	214/113	Limited Lifetime	Adaptable	4"	N/A	80"	12 1/4"	9 3/4"	14
F547	Contractor 52"	306	52"	5	12°	153 x 13	162/67	Limited Lifetime	Adaptable	4"	N/A	80"	12 3/4"	10 1/4"	13
F548	Contractor Uni-Pack	302	52"	5	12°	153 x 13	162/56	Limited Lifetime	Included	4"	N/A	80"	17 1/4"	9 3/4"	17
F556	Contractor Plus	282	52"	5	12°	153 x 15	183/69	Limited Lifetime	Adaptable	6"	N/A	80"	14 3/4"	13"	15
F556L	Contractor LED	280	52"	5	12°	153 x 15	183/69	Limited Lifetime	Adaptable	6"	N/A	80"	16"	14 1/4"	15
F562	Supra® 32"	296	32"	6	22°	153 x 16	267/93	Limited Lifetime	Adaptable	6"	N/A	80"	14 3/4"	13"	15
F563	Supra® 44"	294	44"	5	14°	188 x 15	243/77	Limited Lifetime	Adaptable	6"	N/A	80"	14 1/2"	13 1/4"	19
F563	Supra® 44" -SP	292	44"	5	14°	188 x 15	243/77	Limited Lifetime	Included	6"	N/A	80"	27 1/2"	13 1/4"	22

Minka-Aire® ceiling fans are warranted to be free from defects in material and workmanship only if purchased from an authorized Minka-Aire® distributor:

Fan motor - Limited Lifetime Warranty to original purchaser with proof of purchase as long as fan remains in its original installation location and is installed using only the original hardware provided (including hanger bracket).

All other parts and controls - warranted to original purchaser with proof of purchase for one (1) year from date of purchase.

		Page Number	Blade Sweep	No of Blades	Blade Pitch	Motor Size	RPM (Hi/Low)	Warranty	Light Kit	Downrods 3/4" ID	Downrod 1/2" ID	Lead Wire	Dimension A	Dimension B	Hanging Weight (LBS)
F565	Mesa™ 52"	310	52"	5	12°	153 x 14	176/65	Limited Lifetime	Adaptable	N/A	N/A	8"	8¾"	6½"	13
F566	Mesa™ 42"	310	42"	5	12°	153 x 10	211/92	Limited Lifetime	Adaptable	N/A	N/A	8"	7¾"	5¾"	11
F568	Supra® 52"	288	52"	5	14°	188 x 15	179/58	Limited Lifetime	Adaptable	6"	N/A	80"	15¼"	13¼"	20
F569	Supra® 52" -SP	286	52"	5	14°	188 x 15	168/53	Limited Lifetime	Included	6"	N/A	80"	19½"	13¼"	24
F571	Sundance™ 52"	250	52"	5	12°	153 x 15	182/63	Limited Lifetime	Adaptable	6"	N/A	80"	14½"	13½"	16
F572	Sundance™ 42"	250	42"	5	12°	153 x 10	233/103	Limited Lifetime	Adaptable	6"	N/A	80"	14¾"	12½"	13
F580	Shangri-La®	254	52"	5	14°	188 x 20	172/58	Limited Lifetime	Included	6"	N/A	80"	24"	14"	35
F581	Gauguin™	252	52"	4	14°	188 x 20	148/76	Limited Lifetime	Integrated	6"	N/A	80"	16¼"	15¾"	25
F582	Rainman™	240	54"	5	14°	172 x 20	145/70	Limited Lifetime	Integrated	6"	N/A	80"	23¾"	13¼"	28
F588	Ultra-Max™ -SP	284	54"	5	14°	188 x 25	201/65	Limited Lifetime	Adaptable	6"	N/A	80"	14¾"	12¾"	24
F589	Sundowner®	246	54"	5	16°	188 x 20	185/51	Limited Lifetime	Adaptable	6"	N/A	80"	15"	13"	28
F593L	Traditional Concept™ 44"	132, 228	44"	3	14°	153 x 17	221/105	Limited Lifetime	Integrated	N/A	N/A	8"	11"	7½"	19
F594L	Traditional Concept™ 52"	130, 226	52"	3	14°	172 x 20	178/60	Limited Lifetime	Integrated	N/A	N/A	8"	11"	7½"	23
F596	Cirque™	140	54"	6	14°	188 x 25	143/64	Limited Lifetime	Integrated	4" & 6"	N/A	80"	14¾"	9¾"	26
F598	Airus™	146	54"	5	14°	188 x 18	150/45	Limited Lifetime	Integrated	6"	N/A	80"	16"	10¾"	26
F601	Acero™	128	52"	3	14°	188 x 15	181/62	Limited Lifetime	Integrated	6"	N/A	80"	15¾"	12¼"	24
F602	Gyro™	151	42"	6	20°	82 x 25	1350/720	Limited Lifetime	Integrated	6"	N/A	80"	16¼"	18¼"	31
F603	Como™	134	54"	5	14°	188 x 20	182/61	Limited Lifetime	Integrated	6"	N/A	80"	15¾"	11"	27
F614	Timeless	168	54"	5	14°	188 x 15	163/58	Limited Lifetime	K9614	6"	N/A	80"	16½"	14¼"	21
F617L	Raptor	60	60"	5	14°	DC172 x 12	150/60	Limited Lifetime	Integrated	6"	N/A	80"	13¾"	11"	29
F620	Bolo™	186	52"	5	14°	172 x 17	168/72	Limited Lifetime	Included	6"	N/A	80"	22¾"	15"	25
F622	Traditional Mojo	268	52"	5	12°	153 x 15	188/79	Limited Lifetime	Included	6"	N/A	80"	17½"	12¼"	17
F624	Roto XL	218	62"	3	20°	172 x 16	188/96	Limited Lifetime	N/A	6"	N/A	80"	12¾"	11¼"	14
F647	Contractor Uni-Pack	298	52"	5	12°	153 x 13	160/57	Limited Lifetime	Included	4"	N/A	80"	18"	9¾"	16
F648	Contractor Uni-Pack	300	52"	5	12°	153 x 15	188/68	Limited Lifetime	Included	4"	N/A	80"	17¼"	9¾"	17
F656L	Contractor Uni-Pack LED	278	52"	5	12°	172 x 14	197/58	Limited Lifetime	Integrated	6"	N/A	80"	17"	12½"	19
F659	Classica	194	54"	5	14°	172 x 16	188/64	Limited Lifetime	K9659	6"	N/A	80"	16¾"	13"	23
F681	Groton	214	56"	5	12°	188 x 25	135/50	Limited Lifetime	Integrated	10"	N/A	80"	20¼"	15½"	38
F683L	Shade	238	56"	4	14°	DC168 x 12	160/50	Limited Lifetime	Integrated	6"	N/A	80"	17½"	9½"	25
F684L	Clean	34	60"	5	12°	DC123 x 30	160/50	Limited Lifetime	Integrated	6"	N/A	80"	16"	15"	20
F688	Kola	176	52"	5	12°	172 x 14	190/61	Limited Lifetime	Adaptable	6"	N/A	80"	15½"	13¼"	18
F689	Kola-XL	174	60"	5	12°	188 x 20	160/44	Limited Lifetime	Adaptable	6"	N/A	80"	15½"	13¼"	23
F690L	Espace	258	52"	5	14°	172 x 17	161/59	Limited Lifetime	Integrated	6"	N/A	80"	14½"	10½"	21
F695	Kafé	182	52"	5	12°	172 x 14	190/61	Limited Lifetime	Adaptable	6"	N/A	80"	15"	12¾"	18
F696	Kafé-XL	178	60"	5	12°	188 x 20	160/44	Limited Lifetime	Adaptable	6"	N/A	80"	15"	12¾"	23
F701	Delano®	164	52"	5	14°	172 x 20	160/65	Limited Lifetime	Integrated	6"	N/A	80"	18"	10"	28
F702	Volterra™	198	52"	5	14°	172 x 20	159/71	Limited Lifetime	Integrated	6"	N/A	80"	18¼"	10"	28
F705	Napoli™	190	56"	5	14°	188 x 25	153/59	Limited Lifetime	Integrated	12"	N/A	80"	16½"	8¾"	40
F711	Delano® II	166	52"	5	14°	172 x 20	150/68	Limited Lifetime	Integrated	N/A	N/A	8"	11"	6¼"	25
F715	Napoli™ II	191	68"	5	14°	212 x 25	109/44	Limited Lifetime	Integrated	12"	N/A	80"	17"	9¼"	46
F726	Spectre	104	60"	4	14°	DC188 x 10	163/48	Limited Lifetime	Integrated	6"	N/A	80"	15¼"	11¾"	18

		Page Number	Blade Sweep	No of Blades	Blade Pitch	Motor Size	RPM (Hi/Low)	Warranty	Light Kit	Downrods 3/4" ID	Downrod 1/2" ID	Lead Wire	Dimension A	Dimension B	Hanging Weight (LBS)
F727	Rudolph	262	52"	3	14°	172 x 16	139/57	Limited Lifetime	K9727L	6"	N/A	80"	15½"	13½"	20
F729	Steal	266	54"	3	5°	188 x 15	170/65	Limited Lifetime	Adaptable	6"	N/A	80"	13½"	11¼"	30
F734	Strata	236	52"	4	12°	172 x 17	163/81	Limited Lifetime	Integrated	6"	N/A	80"	18"	14½"	21
F736L	Gear	52	54"	3	14°	DC125 x 30	155/51	Limited Lifetime	Integrated	6"	N/A	80"	16¼"	14"	15
F738	Pancake	84	52"	4	12°	153 x 18	180/70	Limited Lifetime	N/A	6"	N/A	12"	9¾"	7¾"	14
F739L	Pancake XL LED	80	62"	4	12°	DC188 x 14	160/70	Limited Lifetime	Integrated	6"	N/A	80"	10¾"	9"	25
F745	Sabot	118	52"	5	12°	DC172 x 12	173/50	Limited Lifetime	Integrated	6"	N/A	80"	12"	11"	13
F753	Java	62, 232	54"	3	14°	153 x 18	150/71	Limited Lifetime	N/A	6"	N/A	80"	14¾"	13¼"	16
F753L	Java LED	108, 230	54"	3	14°	153 x 18	150/71	Limited Lifetime	Integrated	6"	N/A	80"	15¾"	14¾"	17
F759	Classica Gallery Edition	192	54"	5	14°	172 x 16	188/64	Limited Lifetime	Adaptable	6"	N/A	80"	16¼"	13¼"	27
F786	Simple 44"	48	44"	3	26°	DC123 x 30	196/51	Limited Lifetime	K9787L	6"	N/A	74"	12¾"	11¼"	10
F787	Simple 52"	46, 212	52"	3	14°	DC123 x 30	191/148	Limited Lifetime	K9787L	6"	N/A	80"	12½"	10¾"	11
F788L	Dream Star	8	60"	8	Variable	DC168 x 30	105/50	Limited Lifetime	Integrated	6"	N/A	80"	16½"	8½"	15
F802	Vintage Gyro™	148	42"	6	20°	82 x 25	1350/720	Limited Lifetime	Integrated	6"	N/A	80"	16¾"	18"	34
F803L	Artemis™	68	58"	3	Variable	188 x 25	133/69	Limited Lifetime	Integrated	6"	N/A	80"	15½"	12"	26
F812	Lineage™	189	54"	5	14°	188 x 25	193/49	Limited Lifetime	Integrated	6"	N/A	80"	20¾"	13¾"	40
F820	Santa Lucia™	188	60"	5	14°	188 x 25	148/72	Limited Lifetime	Integrated	6"	N/A	80"	21"	14¾"	45
F823	Wing	116	52"	1	Variable	DC125 x 30	155/111	Limited Lifetime	N/A	6"	N/A	80"	13"	12¼"	14
F828	Symbio	78	56"	5	15°	DC125 x 30	161/48	Limited Lifetime	Integrated	6"	N/A	80"	17¾"	15¾"	16
F829L	Mojave	64	56"	3	21°	DC123 x 30	180/50	Limited Lifetime	Integrated	6"	N/A	80"	16½"	15½"	14
F831L	Tear	100	60"	3	16°	DC120 x 20	167/71	Limited Lifetime	Integrated	6"	N/A	80"	16½"	14¾"	14
F832L	Triple	12	60"	3	Variable	DC123 x 30	144/50	Limited Lifetime	Integrated	6"	N/A	74"	15¼"	10¾"	14
F833	Kewl	138	52"	3	22°	153 x 15	201/104	Limited Lifetime	N/A	6"	N/A	80"	14"	10"	12
F834L	Metropolis	88	56"	3	14°	153 x 22	172/82	Limited Lifetime	Integrated	6"	N/A	80"	16"	11½"	18
F838L	Force	90	60"	3	Variable	DC123 x 30	140/60	Limited Lifetime	Integrated	6"	N/A	80"	15"	12½"	30
F843	Wave	30	52"	3	48°	172 x 14	153/61	Limited Lifetime	N/A	4½" & 6"	N/A	80"	12½"	8½"	12
F844	Light Wave	86	52"	3	48°	172 x 14	139/57	Limited Lifetime	Integrated	4½" & 6"	N/A	80"	13¾"	8½"	14
F846	Wave II	122	60"	2	Variable	DC168 x 8	207/50	Limited Lifetime	N/A	6"	N/A	80"	13"	10"	12
F847L	Timber	50	84"	3	14°	DC172 x 25	90/50	Limited Lifetime	Integrated	6"	N/A	80"	13"	11½"	22
F849L	Stack	98	56"	3	14°	DC125 x 30	179/52	Limited Lifetime	Integrated	6"	N/A	80"	16¼"	10½"	20
F852L	Alva	158	56"	5	14°	DC120 x 20	170/80	Limited Lifetime	Integrated	6"	N/A	80"	20½"	11"	20
F853	Aviation	42	60"	3	Variable	DC120 x 25	115/89	Limited Lifetime	N/A	6"	N/A	80"	14"	12¼"	16
F853L	Aviation LED	38	60"	3	Variable	DC120 x 25	115/44	Limited Lifetime	Integrated	6"	N/A	80"	13	10½"	20
F887	Xtreme 72"	21	72"	9	4°	DC165 x 12	120/51	Limited Lifetime	N/A	6"	N/A	80"	13½"	12"	22
F887	Xtreme 96"	21	96"	9	4°	DC165 x 12	72/51	Limited Lifetime	N/A	6"	N/A	80"	13½"	12"	25
F888	Slipstream	102, 242	65"	8	14°	DC165 x 25	98/78	Limited Lifetime	Integrated	6"	N/A	80"	17¼"	13"	25
F896	Xtreme H20 65"	19	65"	8	4°	DC123 x 30	130/50	Limited Lifetime	K9886L	6"	N/A	80"	12	11¼"	45
F896	Xtreme H20 84"	16	84"	8	4°	DC123 x 30	90/50	Limited Lifetime	K9886L	6"	N/A	80"	12	11¼"	45
F899L	Ninety-Nine	25	99"	9	Variable	DC172 x 25	59/33	Limited Lifetime	Integrated	6"	N/A	80"	15½"	12"	45
F900	Cristafano™	200	68"	5	14°	212 x 25	112/49	Limited Lifetime	Integrated	16"	N/A	80"	19¾"	13"	42
F902L	Bling	110	56"	5	14°	DC125 x 30	170/80	Limited Lifetime	Integrated	6"	N/A	80"	17¾"	9"	20
F903L	Artemis™ IV	56	64"	4	Variable	DC123 x 30	154/51	Limited Lifetime	Integrated	6"	N/A	80"	16"	7¾"	20
F905	Artemis™ XL5	74	62"	5	28°	DC172 x 25	91/74	Limited Lifetime	Integrated	6"	N/A	80"	16¼"	12¾"	21
F1000	Dyno	264	52"	5	12°	153 x 17	175/63	Limited Lifetime	Integrated	6"	N/A	80"	14½"	11½"	15


FINISH CODES




Minka-Aire® Finishes

- AB Antique Brass
- ABD/ABDD Brushed Aluminum
- BCW Belcaro Walnut™
- BG Bahama Beige™
- BI/AI Black Iron with Aged Iron Accents
- BK Black
- BN Brushed Nickel
- BNK Burnished Nickel
- BNW Brushed Nickel Wet
- BS Brushed Steel
- BWH Bone White
- CC Cognac
- CH Chrome
- CPBR Copper Bronze
- CT Cattera Bronze™
- DBB Dark Brushed Bronze
- DK Distressed Koa
- DRB Dark Restoration Bronze™
- DRFF Driftwood
- FB French Beige
- GBZ Golden Bronze
- GI Grey Iron
- GL Galvanized
- GM Gun Metal
- GS Graphite Steel
- HBZ Heirloom Bronze
- HT Heritage™
- IBR Illuminati Bronze™
- HBZ Heirloom Bronze
- IBR Illuminati Bronze™
- IO Iron Oxide
- KA Kocoa
- LN Liquid Nickel
- MBK Matte Black
- MCG Mottled Copper with Gold Highlights
- MG Mahogany Finish
- MP Maple Finish
- MW Mossoro Walnut™
- ODK Distress Koa (Outdoor)
- ORB Oil Rubbed Bronze
- ORG Orange
- PBL Provencal Blanc
- PI Patina Iron
- PN Polished Nickel
- PW Pewter
- RD Red
- RRB Restoration Bronze™
- RW Rosewood
- SBR Soft Brass
- SDBK Sand Black
- SI Smoked Iron
- SL Silver
- STW Sterling Walnut™
- SWH Shell White
- TB Toned Brass
- TI Tarnished Iron
- TL Translucent
- TSP Tuscan Patina™
- VB Volterra Bronze™
- VI Vintage Iron
- VP Vineyard Patina
- VRT Vintage Rust™
- WH/O44 White
- WHF Flat White

Dimensions A and B were measured with the shortest downrod enclosed with the fan.



Minka-Aire® ceiling fans are suitable for year-round use and can contribute to your comfort in the summer and winter. With our reverse switch, in the winter you will be able to move the heat from your ceiling and circulate the air in your living area. In the summer you will save energy by recirculating air from the outside into your room and also if your air conditioning is used, save on energy costs.



We Support



Member



Graphic Design: Minka Group® Graphics
Product Originals: Minka Group®

Product specifications subject to change at any time.

Minka-Aire® A Minka Group® Company
Catalog MKACAT2018-02
Printed in U.S.A.
© 1993-2018 Minka Lighting, Inc.



World Headquarters

1151 West Bradford Court, Corona, California 92882

Showroom

Dallas Market Center

2100 Stemmons, Suite 3725, Dallas, TX 75207

951.278.3267 (FANS) 800.307.3267 Fax: 951.278.2828

sales@minkagroup.net | www.minkaaire.com | www.minkagroup.net

\$20.00