




Arlington

WHERE
INNOVATION
GROWS.

2014 CATALOG



NEW PRODUCTS. BETTER IDEAS

As the leading manufacturer of traditional and unique metallic and non-metallic electrical fittings, Arlington focuses on developing products that solve the industry's jobsite challenges, meet code requirements, and enhance safety while delivering solutions that save time and money!

We pride ourselves on growing with the industry and producing better products so you have what you need for a successful job and business!


Check out our new and unique products marked 'New' throughout the catalog – and visit our website, for the very latest in product development.

Roof Topper™

page S-1

Three styles now have a SLED that SLIDES on the roof surface

- Protects roof deck from damage caused by expansion and contraction movement
- Larger footprint distributes the weight onto a larger surface area




Wire Grabber™ and Kits

Page S-2

Reliable hanging support. Holds fixtures and more up to 75 lbs

- For static drop loads



NON-METALLIC Enclosure Boxes

Page M-6

Heavy-duty Exterior Protection for Devices, Back-ups and more!


- Three sizes: 12x12 now with back plate!
- Lockable



NEW!
EXPANDED
LINE

FLOOR BOX KITS • Boxes • Covers • Accessories

Section P



ON EXISTING FLOORS

FOR FLOORS UP TO 2" THICK

FOR NEW CONCRETE POURS



NEW
COST
EFFECTIVE

Arlington's UL Listed FLOOR BOX KITS offer installers the low cost, convenient way to put a receptacle in the floor – with a box that installs flush with the floor.

Interchangeable Steel Floor Box Kits, Boxes, Covers and Accessories

A series of floor box kits, covers and accessories that offers interchangeability with a variety of OTHER manufacturers' floor boxes.

NEW

Fan/Fixture Box

Page R-8

The Low Cost Box... with Adjustable Steel Bracket and Plastic Box

- Bracket ends adjust for flush installation on ceilings up to 1-1/4" thick



FBR423 UL RATINGS
70 lb fan
Up to 150 lb fixture

Made in USA

Grounding Bridges

IN ZINC AND BRONZE

Section G

ALL Meet 2014 NEC Ground Requirements

NEW

GB5NC Zinc bar ONLY SAVE MONEY!



Wide Flanged Boxes

Page L-8

Save Time. Prevent Water & Air Intrusion

- Here's help for obtaining Energy Star rating
- Device & fixture boxes eliminate the need for gaskets and caulking!



Made in USA

Plastic & Steel Recessed TV BOXES

Recessed combination power and low voltage TV boxes deliver the secure, easy way to mount flat screen TVs flush against a wall

- Plugs and connectors stay inside these Listed boxes without extending past the wall.
- For retrofit or new work.

Page N-1



TVBU505

Page N-6

NEW



TVBU810

Power & Low Voltage TV BOX™

- Easy installation
- Optional cover available

8x10 TV BOX™

- Install horizontally or vertically
- Multiple connections for sound system, cable TV, satellite and more...
- Neater cables – secure installation



Arlington

Made in USA



TABLE OF CONTENTS

| | | |
|---|-------------------------------------|-----------|
| ■ | PRODUCT INDEX WITH UPC NUMBERS..... | PAGES 1-6 |
| ■ | SPECIFICATIONS & STANDARDS | PAGE 7 |
| ■ | PATENT NUMBERS..... | PAGE 8 |
| ■ | LIQUID-TIGHT FITTINGS..... | SECTION A |
| ■ | EMT FITTINGS..... | SECTION B |
| ■ | NM CABLE FITTINGS & SUPPORTS..... | SECTION C |
| ■ | CORD GRIP FITTINGS..... | SECTION D |
| ■ | FLEX-AC-MC FITTINGS..... | SECTION E |
| ■ | MAST PARTS | SECTION F |
| ■ | GROUNDING..... | SECTION G |
| ■ | CONDUIT BODIES | SECTION H |
| ■ | RIGID-IMC FITTINGS..... | SECTION I |
| ■ | GARD-N-POST | SECTION J |
| ■ | INBOX | SECTION K |
| ■ | SIDING MOUNTING BLOCKS..... | SECTION L |
| ■ | SECURITY | SECTION M |
| ■ | HOME THEATER / AV..... | SECTION N |
| ■ | LOW VOLTAGE CABLE MGMT | SECTION O |
| ■ | FLOOR BOXES..... | SECTION P |
| ■ | SPECIALTY BOXES..... | SECTION Q |
| ■ | FAN/FIXTURE BOXES | SECTION R |
| ■ | MISCELLANEOUS..... | SECTION S |



Arlington

INDEX

| Part No. | UPC No. | Page | Part No. | UPC No. | Page | Part No. | UPC No. | Page | Part No. | UPC No. | Page |
|----------|---------|-----------|-----------|---------|-----------|-----------|---------|------|------------|---------|------|
| 1274 | 01274 | I-11 | 349 | 00349 | B-9, I-12 | 454100 | 01454 | G-3 | 720DB | 00721 | G-5 |
| 1275 | 01275 | I-11 | 350 | 00350 | I-12 | 455 | 00455 | G-3 | 720GB5 | 09754 | G-7 |
| 1276 | 01276 | I-11 | 351 | 00351 | I-12 | 455100 | 01455 | G-3 | 720GBB5 | 09755 | G-7 |
| 128 | 00128 | F-2 | 352 | 00352 | I-12 | 456 | 00456 | G-3 | 720S | 72010 | G-4 |
| 1283 | 01283 | I-11 | 353 | 00353 | I-12 | 456250 | 01456 | G-3 | 720Z | 72080 | G-5 |
| 1284 | 01284 | I-11 | 354 | 00354 | I-12 | 457 | 00457 | G-3 | 721B | 00722 | G-5 |
| 1285 | 01285 | I-11 | 355 | 00355 | I-12 | 457250 | 01457 | G-3 | 722B | 07222 | G-5 |
| 1286 | 01286 | I-11 | 356 | 00356 | B-9, I-12 | 458 | 00458 | G-3 | 723 | 00723 | F-8 |
| 1287 | 01287 | I-11 | 357 | 00357 | B-9, I-12 | 458250 | 01458 | G-3 | 723B | 07232 | G-5 |
| 129 | 00129 | F-2 | 358 | 00358 | B-9, I-12 | 459 | 00459 | G-3 | 724 | 00724 | F-8 |
| 1296 | 01296 | I-11 | 359 | 00359 | B-9, I-12 | 4591 | 04591 | G-3 | 725 | 00725 | F-8 |
| 1297 | 01297 | I-11 | 360 | 00360 | B-9 | 4591250 | 45912 | G-3 | 726 | 00726 | F-8 |
| 1298 | 01298 | I-11 | 361 | 00361 | B-9 | 4592 | 04592 | G-3 | 730B | 73020 | G-4 |
| 1307 | 01307 | I-11 | 362 | 00362 | B-9 | 4592250 | 45922 | G-3 | 7510AST | 55090 | E-2 |
| 1308 | 01308 | I-11 | 363 | 00363 | B-9 | 459250 | 01459 | G-3 | 75LPCGBAG | 55082 | D-1 |
| 1309 | 01309 | I-11 | 364 | 00364 | B-9 | 501 | 00501 | I-3 | 780 | 00780 | G-3 |
| 140 | 00140 | F-3 | 365 | 00365 | B-9 | 505010AST | 50720 | E-3 | 781 | 00781 | G-3 |
| 141 | 00141 | F-3 | 370 | 00370 | B-9 | 5010AST | 00517 | E-2 | 782 | 00782 | G-3 |
| 142 | 00142 | F-3 | 371 | 00371 | B-9 | 501L | 50130 | I-2 | 800 | 00800 | B-3 |
| 143 | 00143 | F-3 | 372 | 00372 | B-9 | 502 | 00502 | I-3 | 800A | 80010 | B-3 |
| 144 | 00144 | F-3 | 373 | 00373 | B-9 | 502L | 50230 | I-2 | 800ARH | 80019 | B-3 |
| 145 | 00145 | F-3 | 374 | 00374 | B-9 | 503 | 00503 | I-3 | 800RH | 80098 | B-3 |
| 146 | 00146 | F-3 | 375 | 00375 | B-9 | 503L | 50330 | I-2 | 801 | 00801 | B-3 |
| 147 | 00147 | F-3 | 38A | 00038 | E-1 | 504 | 00504 | I-3 | 801A | 80110 | B-3 |
| 148 | 00148 | F-3 | 38AST | 00070 | E-1 | 505 | 00505 | I-3 | 801ARH | 80119 | B-3 |
| 149 | 00149 | F-3 | 380AST | 00382 | E-1 | 506 | 00506 | I-3 | 801RH | 80198 | B-3 |
| 16 | 16400 | H-3 | 380ST | 00381 | E-1 | 507 | 00507 | I-3 | 802 | 00802 | B-3 |
| 17 | 16401 | H-3 | 3810AST | 00385 | E-2 | 508 | 00508 | I-3 | 802A | 80210 | B-3 |
| 18 | 16402 | H-3 | 383810AST | 10937 | E-3 | 509 | 00509 | I-3 | 802ARH | 80219 | B-3 |
| 19 | 16403 | H-3 | 3838AST | 36230 | E-3 | 50LPCGBAG | 55080 | D-1 | 802RH | 80298 | B-3 |
| 200 | 00200 | I-4 | 3838ST | 10935 | E-3 | 510 | 00510 | I-3 | 803 | 00803 | B-3 |
| 2000 | 02000 | I-10 | 40AST | 00041 | E-1 | 511 | 00511 | I-3 | 803A | 80310 | B-3 |
| 201 | 00201 | I-4 | 400AST | 00347 | E-1 | 512 | 00512 | I-3 | 803ARH | 80301 | B-3 |
| 2010 | 02010 | I-10 | 4001 | 04001 | S-10 | 522 | 00522 | I-11 | 803RH | 80300 | B-3 |
| 202 | 00202 | I-4 | 4002 | 04002 | S-10 | 523 | 00523 | I-11 | 804 | 00804 | B-3 |
| 2020 | 02020 | I-10 | 4003 | 04003 | S-10 | 524 | 00524 | I-11 | 804A | 80410 | B-3 |
| 2025 | 02025 | I-10 | 4004 | 04004 | S-10 | 525 | 00525 | I-11 | 804ARH | 80401 | B-3 |
| 203 | 00203 | I-4 | 4005 | 04005 | S-10 | 526 | 00526 | I-11 | 804RH | 80400 | B-3 |
| 204 | 00204 | I-4 | 4006 | 04006 | S-10 | 527 | 00527 | I-11 | 805 | 00805 | B-3 |
| 2040 | 02040 | I-10 | 401 | 00401 | I-5 | 528 | 00528 | I-11 | 805A | 80510 | B-3 |
| 205 | 00205 | I-4 | 4010AST | 40355 | E-2 | 529 | 00529 | I-11 | 805ARH | 80501 | B-3 |
| 2050 | 02050 | I-10 | 402 | 00402 | I-5 | 530 | 00530 | I-11 | 805RH | 80500 | B-3 |
| 206 | 00206 | I-4 | 403 | 00403 | I-5 | 531 | 00531 | I-11 | 806 | 00806 | B-3 |
| 2060 | 02060 | I-10 | 404 | 00404 | I-5 | 532 | 00532 | I-11 | 806A | 80610 | B-3 |
| 207 | 00207 | I-4 | 404010AST | 40533 | E-3 | 533 | 00533 | I-11 | 806ARH | 06014 | B-3 |
| 2070 | 02070 | I-10 | 4040AST | 40351 | E-3 | 534 | 00534 | I-11 | 806RH | 80806 | B-3 |
| 208 | 00208 | I-4 | 405 | 00405 | I-5 | 535 | 00535 | I-11 | 807 | 00807 | B-3 |
| 2080 | 02080 | I-10 | 406 | 00406 | I-5 | 536 | 00536 | I-11 | 807A | 80710 | B-3 |
| 209 | 00209 | I-4 | 407 | 00407 | I-5 | 6A10 | 64000 | I-4 | 807ARH | 06018 | B-3 |
| 2090 | 02090 | I-10 | 408 | 00408 | I-5 | 6A11 | 64002 | I-4 | 807RH | 80807 | B-3 |
| 210 | 00210 | I-4 | 409 | 00409 | I-5 | 6A2 | 61200 | I-4 | 8075 | 08075 | B-3 |
| 211 | 00211 | I-4 | 410 | 00410 | I-5 | 6A3 | 61300 | I-4 | 8075A | 80711 | B-3 |
| 2200 | 22000 | I-10 | 411 | 00411 | I-5 | 6A4 | 61400 | I-4 | 8075ARH | 08200 | B-3 |
| 2210 | 22100 | I-10 | 412 | 00412 | I-5 | 6A5 | 61500 | I-4 | 8075RH | 06016 | B-3 |
| 2220 | 22200 | I-10 | 4200 | 04200 | E-6 | 6A6 | 61600 | I-4 | 808 | 00808 | B-3 |
| 2225 | 22250 | I-10 | 4201 | 04201 | E-6 | 6A7 | 61700 | I-4 | 808A | 80810 | B-3 |
| 2230 | 22300 | I-10 | 4201A | 04208 | E-6 | 6A8 | 61800 | I-4 | 808ARH | 06020 | B-3 |
| 2240 | 22400 | I-10 | 4202 | 04202 | E-6 | 6A9 | 61900 | I-4 | 808RH | 06022 | B-3 |
| 2250 | 22500 | I-10 | 4202A | 14202 | E-6 | 60HC | 00686 | K-16 | 8081 | 80812 | L-1 |
| 2350 | 02350 | F-7 | 4203 | 04203 | E-6 | 60HW | 00684 | K-16 | 8081DBL | 80813 | L-3 |
| 2400 | 06920 | B-2, I-1 | 4203A | 04206 | E-6 | 60VC | 00682 | K-16 | 8081DBLGC | 08971 | L-3 |
| 2410 | 06921 | B-2, I-1 | 4204 | 04204 | E-6 | 60VW | 00680 | K-16 | 8081F | 80814 | L-1 |
| 2411 | 06922 | B-2, I-1 | 4204A | 04209 | E-6 | 61HC | 00687 | K-16 | 8081FB | 10941 | L-1 |
| 2850 | 28550 | F-7 | 440 | 00440 | I-5 | 61HW | 00685 | K-16 | 8081FBGC | 08980 | L-1 |
| 301 | 00301 | C-6 | 4400 | 04400 | S-9 | 61VC | 00683 | K-16 | 8081FC | 10939 | L-1 |
| 303 | 00303 | C-6 | 4401 | 04401 | S-9 | 61VW | 00681 | K-16 | 8081FDBL | 80815 | L-3 |
| 310 | 00310 | E-20 | 4402 | 04402 | S-9 | 610 | 00610 | F-5 | 8081FDBLC | 10943 | L-3 |
| 3100 | 03100 | I-13 | 4403 | 04403 | S-9 | 611 | 00611 | F-6 | 8081FDBLGC | 08972 | L-3 |
| 3101 | 03101 | I-13 | 4404 | 04404 | S-9 | 612 | 00612 | F-5 | 8081FGC | 08900 | L-1 |
| 3102 | 03102 | I-13 | 4405 | 04405 | S-9 | 613 | 00613 | F-5 | 8081GC | 08981 | L-1 |
| 3103 | 03103 | I-13 | 4406 | 04409 | S-9 | 615 | 00615 | F-6 | 8082F | 32240 | L-1 |
| 3104 | 03104 | I-13 | 441 | 00441 | I-5 | 616 | 00616 | F-5 | 8082FGC | 08982 | L-1 |
| 3105 | 03105 | I-13 | 442 | 00442 | I-5 | 617 | 00617 | F-5 | 8091F | 17856 | L-2 |
| 3106 | 03106 | I-13 | 443 | 00443 | I-5 | 620 | 00620 | F-6 | 8091FB | 10945 | L-2 |
| 3107 | 03107 | I-13 | 444 | 00444 | I-5 | 624 | 00624 | F-7 | 8091FBGC | 08983 | L-2 |
| 3108 | 03108 | I-13 | 445 | 00445 | I-5 | 625 | 00625 | F-7 | 8091FC | 10946 | L-2 |
| 3109 | 03109 | I-13 | 446 | 00446 | I-5 | 626 | 00626 | F-7 | 8091FDBL | 24168 | L-3 |
| 311 | 84174 | E-20 | 447 | 00447 | I-5 | 634 | 00634 | F-7 | 8091FDBLC | 10947 | L-3 |
| 313S | 00133 | C-6 | 448 | 00448 | I-5 | 635 | 00635 | F-7 | 8091FDBLGC | 09017 | L-3 |
| 314S | 00014 | C-6 | 449 | 00449 | I-5 | 636 | 00636 | F-7 | 8091FGC | 08901 | L-2 |
| 3232 | 32320 | C-6 | 4491 | 04491 | I-5 | 637 | 00637 | F-7 | 810 | 00810 | B-4 |
| 3282 | 03282 | C-6 | 4492 | 04492 | I-5 | 639 | 00639 | F-7 | 810RH | 81098 | B-4 |
| 3284 | 32840 | C-6 | 450 | 00450 | G-3 | 645 | 00645 | F-6 | 8100LP | 10749 | L-5 |
| 340 | 00340 | I-12 | 4501 | 04501 | E-14 | 660 | 00660 | F-2 | 8100MLP | 10752 | L-5 |
| 341 | 00341 | I-12 | 4502 | 04502 | E-14 | 662 | 00662 | F-2 | 811 | 00811 | B-4 |
| 342 | 00342 | I-12 | 4501ST | 06002 | E-14 | 663 | 00663 | F-4 | 811RH | 81198 | B-4 |
| 343 | 00343 | I-12 | 4502ST | 06004 | E-14 | 664 | 00664 | F-4 | 812 | 00812 | B-4 |
| 344 | 00344 | I-12 | 451 | 00451 | G-3 | 717DB | 12514 | G-6 | 812RH | 81298 | B-4 |
| 345 | 00345 | I-12 | 452 | 00452 | G-3 | 718DB | 72000 | G-6 | 813 | 00813 | B-4 |
| 346 | 00346 | B-9, I-12 | 453 | 00453 | G-3 | 719DB | 72001 | G-6 | 813RH | 81300 | B-4 |
| 347 | 00347 | B-9, I-12 | 453100 | 01453 | G-3 | 720B | 72020 | G-5 | 8131 | 08131 | L-4 |
| 348 | 00348 | B-9, I-12 | 454 | 00454 | G-3 | 720BBS | 72022 | G-5 | 8131GC | 08984 | L-4 |

| Part No. | UPC No. | Page | Part No. | UPC No. | Page | Part No. | UPC No. | Page | Part No. | UPC No. | Page |
|---------------|---------|------|-----------|---------|----------------|------------------------|---------|----------|-------------------------|---------|------|
| DBVR131WGC... | 08927 | K-5 | DWT0805 | 15020 | S-2 | FA101GC | 76881 | Q-2 | FLBAF101BL | 04342 | P-3 |
| DBVR141C | 14371 | K-5 | DWT0810 | 15021 | S-2 | FA102 | 04242 | Q-2 | FLBAF101BR | 04343 | P-3 |
| DBVR141CGC | 08992 | K-5 | DWY2H0810 | 11312 | S-2 | FA102D | 04245 | Q-2 | FLBAF101LA | 04341 | P-3 |
| DBVR141W | 14376 | K-5 | DWY2T0810 | 11306 | S-2 | FA102GC | 76883 | Q-2 | FLBAF101MB | 13805 | P-4 |
| DBVR141WGC | 08993 | K-5 | DWY2T0812 | 11314 | S-2 | FA103 | 04243 | Q-2 | FLBAF101NL | 13806 | P-4 |
| DBVR151C | 14372 | K-5 | DWYH0805 | 11307 | S-2 | FA103GC | 76884 | Q-2 | FLBAF101W | 04340 | P-3 |
| DBVR151CGC | 08994 | K-5 | DWYH0810 | 11308 | S-2 | FA104 | 04244 | Q-2 | FLBAR101BL | 04350 | P-3 |
| DBVR151W | 14377 | K-5 | DWYH0815 | 11309 | S-2 | FA104GC | 76885 | Q-2 | FLBAR101BR | 04351 | P-3 |
| DBVR151WGC | 08995 | K-5 | DWYH0820 | 11310 | S-2 | FAN/FIXTURE BOX RATING | | R-18 | FLBAR101LA | 04349 | P-3 |
| DBVR171C | 14373 | K-5 | DWYH0830 | 11311 | S-2 | FB405 | 72185 | R-10 | FLBAR101MB | 52261 | P-4 |
| DBVR171CGC | 08928 | K-5 | DWYT0805 | 11301 | S-2 | FB4050 | 28101 | R-10 | FLBAR101NL | 52262 | P-4 |
| DBVR171W | 14378 | K-5 | DWYT0810 | 11302 | S-2 | FB407 | 72177 | R-10 | FLBAR101W | 04348 | P-3 |
| DBVR171WGC | 08929 | K-5 | DWYT0812 | 11313 | S-2 | FB4070 | 28102 | R-10 | FLBC101BL | 04354 | P-1 |
| DBVR2C | 03964 | K-8 | DWYT0815 | 11303 | S-2 | FB412 | 72189 | R-10 | FLBC101BLTK | 13824 | P-11 |
| DBVR2CGC | 08996 | K-8 | DWYT0820 | 11304 | S-2 | FB415 | 72167 | R-13 | FLBC101BR | 04355 | P-1 |
| DBVR2W | 03965 | K-8 | DWYT0830 | 11305 | S-2 | FB4150 | 72182 | R-13 | FLBC101BRTK | 13823 | P-11 |
| DBVR2WGC | 08997 | K-8 | | | | FB417S | 72171 | R-11 | FLBC101LA | 04353 | P-1 |
| DBVS1C | 14317 | K-2 | E | | | FB417SLP | 72199 | R-11 | FLBC101LATK | 13822 | P-11 |
| DBVS1CGC | 08932 | K-2 | E STRAP | 43625 | C-6 | FB423 | 72190 | R-10 | FLBC101MB | 52267 | P-2 |
| DBVS1W | 14318 | K-2 | EB0708 | 12672 | M-6 | FB426 | 72179 | R-13 | FLBC101MBTK | 13825 | P-11 |
| DBVS1WGC | 08933 | K-2 | EB1111 | 12670 | M-6 | FB442 | 72194 | R-14 | FLBC101NL | 52266 | P-2 |
| DBVS2C | 03960 | K-8 | EB1212 | 12671 | M-6 | FB442F | 76220 | R-1 | FLBC101NLTK | 13826 | P-11 |
| DBVS2CGC | 08998 | K-8 | EB1212BP | 23155 | M-6 | FB442FD | 76221 | R-1 | FLBC101RK | 13820 | P-11 |
| DBVS2W | 03961 | K-8 | EBL1 | 11400 | M-6 | FB443 | 72197 | R-14 | FLBC101W | 04352 | P-1 |
| DBVS2WGC | 08999 | K-8 | EH200 | 58201 | F-3 | FB443F | 76222 | R-1 | FLBC101WTK | 13821 | P-11 |
| DBVW | 77642 | K-17 | EH201 | 43630 | F-3 | FB443FD | 76223 | R-1 | FLBC4500 | 22010 | P-10 |
| DHB1BR | 54875 | K-9 | EMT100 | 12220 | B-1, O-12 | FB444 | 72187 | R-12 | FLBC4500AR | 22004 | P-10 |
| DHB1BRC | 54881 | K-9 | EMT100C | 12207 | B-2 | FB450 | 75240 | R-15 | FLBC4500LR | 22011 | P-10 |
| DHB1BRCGC | 08935 | K-9 | EMT125 | 12225 | B-1, O-12 | FB900 | 75250 | R-15 | FLBC4500Y | 22012 | P-10 |
| DHB1BRGC | 08934 | K-9 | EMT125C | 12209 | B-2 | FBR415F | 72204 | Q-3, R-1 | FLBCF101BL | 06953 | P-1 |
| DHB1C | 54880 | K-9 | EMT150 | 12230 | B-1, O-12 | FBR423 | 52310 | R-8 | FLBCF101BLTK | 13830 | P-11 |
| DHB1CGC | 08936 | K-9 | EMT150C | 12211 | B-2 | FBR425F | 72205 | R-1 | FLBCF101BR | 06952 | P-1 |
| DHB1W | 54882 | K-9 | EMT200 | 12235 | B-1, O-12 | FBR425F | 72205 | R-1 | FLBCF101BRTK | 13829 | P-11 |
| DHB1WGC | 12902 | K-9 | EMT200C | 12213 | B-2 | FBR425F | 72205 | R-1 | FLBCF101LA | 06951 | P-1 |
| DLN1 | 43510 | I-7 | EMT200S | 15301 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBCF101LATK | 13828 | P-11 |
| DLN10 | 43511 | I-7 | EMT250 | 12240 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBCF101MB | 52454 | P-2 |
| DLN2 | 43520 | I-7 | EMT250 | 12240 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBCF101MBTK | 13831 | P-11 |
| DLN3 | 43530 | I-7 | EMT250C | 12215 | B-2, I-2 | FBR425F | 72205 | R-1 | FLBCF101NL | 52455 | P-2 |
| DLN4 | 43540 | I-7 | EMT250S | 12270 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBCF101NLTK | 13832 | P-11 |
| DLN5 | 43550 | I-7 | EMT300 | 12245 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBCF101W | 06950 | P-1 |
| DLN6 | 43560 | I-7 | EMT300 | 12245 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBCF101WTK | 13827 | P-11 |
| DLN7 | 43570 | I-7 | EMT300C | 12217 | B-2, I-2 | FBR425F | 72205 | R-1 | FLBR101BL | 04358 | P-5 |
| DLN8 | 43580 | I-7 | EMT300S | 12271 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBR101BR | 04359 | P-5 |
| DLN9 | 43590 | I-7 | EMT350 | 12250 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBR101LA | 04357 | P-5 |
| DR1 | 01551 | S-5 | EMT350C | 12219 | B-2, I-2 | FBR425F | 72205 | R-1 | FLBR101MB | 52263 | P-6 |
| DR2 | 01552 | S-5 | EMT350S | 12272 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBR101NL | 52264 | P-6 |
| DR3 | 01553 | S-5 | EMT400 | 12255 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBR101W | 04356 | P-5 |
| DR4 | 01554 | S-5 | EMT400C | 12221 | B-2, I-2 | FBR425F | 72205 | R-1 | FLBRF101BL | 16250 | P-5 |
| DSBHM1C | 09643 | K-12 | EMT400S | 22001 | B-1, I-1, O-12 | FBR425F | 72205 | R-1 | FLBRF101BR | 16251 | P-5 |
| DSBHM1W | 09648 | K-12 | EMT50 | 12200 | B-1, O-12 | FBR425F | 72205 | R-1 | FLBRF101LA | 16252 | P-5 |
| DSBHR1C | 09656 | K-10 | EMT50C | 12203 | B-2 | FBR425F | 72205 | R-1 | FLBRF101MB | 16254 | P-6 |
| DSBHR1W | 09657 | K-10 | EMT50S | 12204 | B-2 | FBR425F | 72205 | R-1 | FLBRF101NL | 16255 | P-6 |
| DSBHS1C | 09652 | K-11 | EMT75 | 12205 | B-1, O-12 | FBR425F | 72205 | R-1 | FLBRF101W | 16253 | P-5 |
| DSBHS1W | 09653 | K-11 | EMT75C | 12204 | B-2 | FBR425F | 72205 | R-1 | FLBT6615LR | 22029 | P-10 |
| DSBVM1C | 09642 | K-12 | F | | | FBR425F | 72205 | R-1 | FLBT6615MB | 22030 | P-10 |
| DSBVM1W | 09646 | K-12 | F101 | 43626 | Q-1 | FBR425F | 72205 | R-1 | FLC430 | 09742 | M-3 |
| DSBVR1C | 09654 | K-10 | F101F | 12520 | Q-15 | FBR425F | 72205 | R-1 | FLC430GC | 08949 | M-3 |
| DSBVR1W | 09655 | K-10 | F101FGC | 06905 | Q-3 | FBR425F | 72205 | R-1 | FLC430S | 09743 | M-3 |
| DSBVS1C | 09650 | K-11 | F101GC | 37950 | Q-1 | FBR425F | 72205 | R-1 | FLEX*AC*MC CABLE RANGES | | E-22 |
| DSBVS1W | 09651 | K-11 | F101H | 43634 | Q-1 | FBR425F | 72205 | R-1 | FLG3 | 01590 | S-2 |
| DSC1 | 43600 | S-10 | F101HGC | 37951 | Q-1 | FBR425F | 72205 | R-1 | FN101F | 15130 | Q-5 |
| DSC5 | 43605 | S-10 | F102 | 43640 | Q-1 | FBR425F | 72205 | R-1 | FN101FD | 15131 | Q-15 |
| DSHB1BR | 43613 | K-13 | F102D | 43544 | Q-1 | FBR425F | 72205 | R-1 | FN101FDGC | 15139 | Q-3 |
| DSHB1BRC | 43612 | K-13 | F102F | 06900 | Q-15 | FBR425F | 72205 | R-1 | FN101FGC | 15138 | Q-3 |
| DSHB1C | 43610 | K-13 | F102FGC | 06906 | Q-3 | FBR425F | 72205 | R-1 | FN102F | 15132 | Q-15 |
| DSHB1W | 43611 | K-13 | F102GC | 37952 | Q-1 | FBR425F | 72205 | R-1 | FN102FD | 15133 | Q-15 |
| DV1 | 43607 | L-6 | F103 | 43641 | Q-1 | FBR425F | 72205 | R-1 | FN102FDGC | 15141 | Q-3 |
| DVB1BR | 43595 | K-9 | F103F | 06901 | Q-15 | FBR425F | 72205 | R-1 | FN102FGC | 15140 | Q-3 |
| DVB1BRC | 43608 | K-9 | F103FGC | 06907 | Q-3 | FBR425F | 72205 | R-1 | FN103F | 15134 | Q-15 |
| DVB1BRCGC | 09001 | K-9 | F103GC | 37953 | Q-1 | FBR425F | 72205 | R-1 | FN103FD | 15135 | Q-15 |
| DVB1BRGC | 09002 | K-9 | F104 | 43642 | Q-1 | FBR425F | 72205 | R-1 | FN103FDGC | 15143 | Q-3 |
| DVB1C | 43609 | K-9 | F104F | 06902 | Q-15 | FBR425F | 72205 | R-1 | FN103FGC | 15142 | Q-3 |
| DVB1CGC | 09003 | K-9 | F104GC | 37954 | Q-1 | FBR425F | 72205 | R-1 | FN104F | 15136 | Q-15 |
| DVB1W | 43620 | K-9 | F426F | 06903 | R-2 | FBR425F | 72205 | R-1 | FN104FD | 15137 | Q-15 |
| DVB1WGC | 09004 | K-9 | F426FGC | 06909 | R-2 | FBR425F | 72205 | R-1 | FN104FDGC | 15145 | Q-3 |
| DVFR1W | 14330 | Q-3 | F8091H | 22002 | L-9 | FBR425F | 72205 | R-1 | FN104FGC | 15144 | Q-3 |
| DVFR1WGC | 08939 | Q-3 | F8091HGC | 22003 | L-9 | FBR425F | 72205 | R-1 | FN430F | 15100 | R-2 |
| DVFR2W | 14331 | Q-3 | F8091HC | 22045 | L-9 | FBR425F | 72205 | R-1 | FN430FGC | 15101 | R-2 |
| DVFR2WGC | 08941 | Q-3 | F8091HCGC | 22046 | L-9 | FBR425F | 72205 | R-1 | FN440F | 15120 | R-2 |
| DVFR3W | 14340 | Q-3 | F8091V | 22006 | L-9 | FBR425F | 72205 | R-1 | FN440FGC | 15121 | R-2 |
| DVFR3WGC | 09006 | Q-3 | F8091VC | 22008 | L-9 | FBR425F | 72205 | R-1 | FR101F | 12680 | L-8 |
| DVFR4W | 14342 | Q-3 | F8091VCGC | 22009 | L-9 | FBR425F | 72205 | R-1 | FR405F | 12681 | L-8 |
| DVFR4WGC | 09008 | Q-3 | F8091VGC | 22007 | L-9 | FBR425F | 72205 | R-1 | FR420F | 09615 | L-8 |
| DVFR3C | 10570 | Q-3 | FA101 | 04241 | Q-2 | FBR425F | 72205 | R-1 | FS420SCL | 12526 | R-5 |
| DVFR4C | 14337 | Q-3 | | | | FBR425F | 72205 | R-1 | FS427SCL | 12537 | R-5 |
| DWB0805 | 06805 | S-2 | | | | FBR425F | 72205 | R-1 | FS50 | 61050 | K-17 |
| DWB0812 | 06883 | S-2 | | | | FBR425F | 72205 | R-1 | FS75 | 61075 | K-17 |
| DWB0815 | 06815 | S-2 | | | | FBR425F | 72205 | R-1 | FS8091F | 17304 | L-7 |
| DWB0820 | 06820 | S-2 | | | | FBR425F | 72205 | R-1 | FS8091FGC | 08950 | L-7 |
| DWB0830 | 06830 | S-2 | | | | FBR425F | 72205 | R-1 | FS8141 | 17340 | L-9 |
| DWH0805 | 15022 | S-2 | | | | FBR425F | 72205 | R-1 | FS8141GC | 08951 | L-9 |
| DWH0810 | 15023 | S-2 | | | | FBR425F | 72205 | R-1 | | | |

| Part No. | UPC No. | Page | Part No. | UPC No. | Page | Part No. | UPC No. | Page | Part No. | UPC No. | Page |
|-----------|---------|-----------|------------|---------|----------|-----------|---------|------|--------------------|---------|-----------|
| FS8151 | 17341 | L-9 | GPBK35BGC | 08962 | J-3 | L49 | 34900 | E-11 | LVS2 | 00280 | O-3 |
| FS8151GC | 08952 | L-9 | GPBK35BR | 77041 | J-3 | LPG50 | 80086 | D-1 | LVS3 | 00282 | O-3 |
| FS8161 | 17342 | L-9 | GPBK35BRGC | 08963 | J-3 | LPCG50BL | 06070 | D-1 | LVS4 | 00283 | O-3 |
| FS8161GC | 09009 | L-9 | GPD19B | 77020 | J-2 | LPCG50W | 32875 | D-1 | LVU1W | 00285 | O-5 |
| FS8171 | 17343 | L-9 | GPD19BGC | 09014 | J-2 | LPCG50Z | 36110 | D-1 | LVU2W | 20011 | O-5 |
| FS8171GC | 08953 | L-9 | GPD19BR | 77021 | J-2 | LPCG503 | 50350 | D-1 | LVU3W | 20012 | O-5 |
| FSC3221R | 43633 | Q-11 | GPD19BRGC | 08964 | J-2 | LPCG503BL | 50351 | D-1 | LVU4W | 20013 | O-5 |
| FSC3227R | 12525 | Q-11 | GPD19G | 77022 | J-2 | LPCG503W | 50340 | D-1 | | | |
| FSR404BL | 00596 | Q-13 | GPD19GGC | 08965 | J-2 | LPCG503Z | 50352 | D-1 | M | | |
| FSR404RD | 00598 | Q-13 | GPD19W | 77023 | J-2 | LPCG507 | 50354 | D-1 | MB8 | 42330 | R-17 |
| FSR404S | 00597 | Q-13 | GPD19WGC | 09015 | J-2 | LPCG507BL | 50353 | D-1 | MBC25 | 34810 | S-11 |
| FSR404SRD | 00599 | Q-13 | GPD9B | 76161 | J-5 | LPCG507W | 50341 | D-1 | MBC25A | 42321 | S-11 |
| FSR404SD | 00600 | Q-13 | GPD9BGC | 08966 | J-5 | LPCG507Z | 50356 | D-1 | MBC26 | 42326 | S-11 |
| | | | GPD9BR | 76162 | J-5 | LPCG5073 | 50760 | D-1 | MBC27 | 42327 | S-11 |
| G | | | GPD9BRGC | 04685 | J-5 | LPCG753BL | 07450 | D-1 | MBC28 | 42328 | S-11 |
| GB5 | 76095 | G-1 | GPD9G | 76164 | J-5 | LPCG753W | 50342 | D-1 | MCI-A CABLE RANGES | | E-25 |
| GB5NC | 76094 | G-1 | GPD9GGC | 04686 | J-5 | LPCG753Z | 36105 | D-1 | MK200 | 42200 | F-8 |
| GB5P | 09720 | G-2 | GPD9W | 76163 | J-5 | LPCG754 | 50762 | D-1 | MK200ASF | 42210 | F-8 |
| GBB5 | 76096 | G-1 | GPD9WGC | 08967 | J-5 | LPCG754BL | 07455 | D-1 | MK200PS | 32044 | F-8 |
| GBB5P | 09721 | G-2 | GPI75B | 77042 | J-8 | LPCG754W | 50343 | D-1 | MK200WH | 42205 | F-8 |
| GBB50 | 09725 | G-1 | GPI75BR | 76159 | J-8 | LPCG754Z | 50764 | D-1 | MK250A | 32027 | F-8 |
| GBB50P | 09726 | G-2 | GPL19B | 77000 | J-6 | LPCG757 | 36100 | D-1 | MK250ASF | 42250 | F-8 |
| GBB5250 | 09756 | G-1 | GPL19BR | 77001 | J-6 | LPCG757BL | 07460 | D-1 | MK250ASFX | 42255 | F-8 |
| GF100 | 76100 | E-17 | GPL19G | 77002 | J-6 | LPCG757W | 50344 | D-1 | MM10 | 42278 | L-10 |
| GF100A | 76101 | E-18 | GPL19W | 77003 | J-6 | LPCG757Z | 50766 | D-1 | MM18 | 42280 | L-10 |
| GF125 | 76125 | E-17 | GPLN15B | 76205 | J-7 | LT10 | 32102 | A-2 | MM23 | 42282 | L-10 |
| GF125A | 76251 | E-18 | GPLN15GR | 76181 | J-7 | LT10A | 35087 | A-2 | | | |
| GF150 | 76150 | E-17 | GPLN19B | 69108 | J-7 | LT100 | 32100 | A-7 | N | | |
| GF150A | 76151 | E-18 | GPLN19BR | 76192 | J-7 | LT100A | 32101 | A-7 | NM CABLE RANGES | | C-13-C-14 |
| GF200 | 76200 | E-17 | GPP60B | 77046 | J-8 | LT125 | 32125 | A-7 | NM1000 | 54615 | I-9 |
| GF200A | 76201 | E-18 | GPP60BR | 77047 | J-8 | LT125A | 32121 | A-7 | NM1900 | 54514 | I-9 |
| GF38 | 76380 | E-17 | GPP60LB | 04605 | J-8 | LT150 | 32150 | A-7 | NM2000 | 54515 | I-9 |
| GF38A | 76381 | E-18 | GPP60LBR | 04606 | J-8 | LT150A | 32151 | A-7 | NM2005 | 54525 | I-9 |
| GF38AST | 80164 | E-18 | GPX18B | 76157 | J-6 | LT200 | 32200 | A-7 | NM2010 | 54516 | I-9 |
| GF38ST | 80162 | E-18 | GPX18BR | 76158 | J-6 | LT200A | 32201 | A-7 | NM2015 | 54526 | I-9 |
| GF50 | 76500 | E-17 | GPX18G | 76160 | J-6 | LT250 | 32250 | A-7 | NM2020 | 54517 | I-9 |
| GF50A | 76501 | E-18 | GPX18W | 76159 | J-6 | LT300 | 32300 | A-7 | NM2025 | 54518 | I-9 |
| GF50AST | 80168 | E-18 | | | | LT350 | 32350 | A-7 | NM2030 | 54528 | I-9 |
| GF50ST | 80166 | E-18 | H | | | LT38 | 32380 | A-7 | NM2040 | 54519 | I-9 |
| GF75 | 76750 | E-17 | H STRAP | 82990 | C-6 | LT38A | 32381 | A-7 | NM2045 | 54544 | I-9 |
| GF75A | 76751 | E-18 | HB1 | 15300 | L-6 | LT400 | 32400 | A-7 | NM2050 | 54520 | I-9 |
| GF75ST | 80170 | E-18 | HL100 | 50171 | B-8, I-6 | LT5 | 32502 | A-2 | NM2060 | 54521 | I-9 |
| GF850 | 85000 | E-21 | HL125 | 50173 | B-8, I-6 | LT5A | 35085 | A-2 | NM2070 | 54522 | I-9 |
| GF850ST | 84850 | E-21 | HL5000 | 83105 | B-8, I-6 | LT50 | 32500 | A-7 | NM2080 | 54523 | I-9 |
| GF860 | 76860 | B-7, E-19 | HL7500 | 83175 | B-8, I-6 | LT50A | 32501 | A-7 | NM2090 | 54592 | I-9 |
| GF861 | 76861 | B-7, E-19 | | | | LT7 | 32503 | A-2 | NM2150 | 54547 | I-9 |
| GF862 | 76862 | B-7, E-19 | J | | | LT7A | 38086 | A-2 | NM2520 | 54565 | S-5 |
| GF863 | 80173 | B-7, E-19 | JC12 | 13120 | S-11 | LT75 | 32750 | A-7 | NM3010 | 54010 | E-21 |
| GF864 | 80175 | B-7 | | | | LT75A | 32751 | A-7 | NM501 | 54501 | I-3 |
| GFC100 | 76340 | E-17 | K | | | LT9010 | 32104 | A-2 | NM501EL | 54584 | I-3 |
| GFC125 | 76360 | E-17 | K STRAP | 83770 | C-6 | LT9010A | 35090 | A-2 | NM502 | 54502 | I-3 |
| GFC150 | 76370 | E-17 | KC4 | 83665 | G-7 | LT90100 | 32910 | A-8 | NM503 | 54503 | I-3 |
| GFC200 | 76372 | E-17 | KC6 | 83667 | G-7 | LT90100A | 32911 | A-8 | NM504 | 54504 | I-3 |
| GFC50 | 76350 | E-17 | KD4550 | 83668 | O-6 | LT90125 | 32913 | A-8 | NM505 | 54505 | I-3 |
| GFC75 | 76375 | E-17 | | | | LT90125A | 32912 | A-8 | NM506 | 54506 | I-3 |
| GFSC38 | 20737 | E-15 | L | | | LT90150 | 32915 | A-8 | NM74 | 54510 | C-7 |
| GFSC38B | 20739 | E-15 | L15A | 80040 | E-12 | LT90150A | 32955 | A-8 | NM75 | 54513 | C-7 |
| GL100 | 77100 | G-4 | L15AST | 80044 | E-4 | LT90200 | 32920 | A-8 | NM840 | 54840 | C-7 |
| GL125 | 77125 | G-4 | L16 | 80060 | E-12 | LT90200A | 32921 | A-8 | NM841 | 54841 | C-7 |
| GL150 | 77150 | G-4 | L160 | 02416 | E-12 | LT90250 | 32925 | A-8 | NM842 | 54842 | C-7 |
| GL200 | 77200 | G-4 | L160ST | 80065 | E-4 | LT90300 | 32930 | A-8 | NM843 | 54843 | C-7 |
| GL250 | 77250 | G-4 | L165T | 80064 | E-4 | LT90350 | 32935 | A-8 | NM844 | 50175 | C-7 |
| GL300 | 77300 | G-4 | L17 | 34278 | E-12 | LT9038 | 32938 | A-8 | NM900 | 54000 | S-9 |
| GL350 | 77350 | G-4 | L17ST | 33905 | E-4 | LT9038A | 32931 | A-8 | NM901 | 54001 | S-9 |
| GL400 | 77400 | G-4 | L18 | 34282 | E-12 | LT90400 | 32940 | A-8 | NM902 | 54002 | S-9 |
| GL50 | 77050 | G-4 | L18ST | 33915 | E-4 | LT905 | 32504 | A-2 | NM903 | 54003 | S-9 |
| GL75 | 77075 | G-4 | L19 | 34287 | E-12 | LT905A | 24233 | A-2 | NM904 | 54004 | S-9 |
| GP19B | 77086 | J-1 | L19ST | 08650 | E-4 | LT9050 | 32950 | A-8 | NM905 | 54005 | S-9 |
| GP19BGC | 08954 | J-1 | L20 | 32000 | B-1 | LT9050A | 32951 | A-8 | NM904 | 05488 | C-8 |
| GP19BR | 77087 | J-1 | L42 | 34200 | E-9 | LT907 | 32505 | A-2 | NM940 | 72156 | C-8 |
| GP19BRGC | 08955 | J-1 | L420 | 34021 | E-9 | LT907A | 35089 | A-2 | NM95 | 10956 | C-8 |
| GP19G | 77088 | J-1 | L421 | 34210 | E-9 | LT9075 | 32970 | A-8 | NM96 | 72158 | C-8 |
| GP19GGC | 08956 | J-1 | L4210 | 34211 | E-9 | LT9075A | 32971 | A-8 | NMCG100750 | 55000 | D-2 |
| GP19W | 77089 | J-1 | L4210A | 42100 | E-9 | LTSC50 | 35405 | A-3 | NMCG100750BL | 06072 | D-2 |
| GP19WGC | 09010 | J-1 | L421A | 34212 | E-9 | LTSC75 | 35408 | A-3 | NMCG100875 | 55002 | D-2 |
| GP26B | 77090 | J-1 | L422 | 34220 | E-9 | LV1 | 58175 | O-1 | NMCG100875BL | 06074 | D-2 |
| GP26BGC | 08957 | J-1 | L422A | 34213 | E-9 | LV1LP | 58177 | O-2 | NMFS50 | 54050 | K-17 |
| GP26BR | 77092 | J-1 | L423 | 34230 | E-9 | LV2 | 10952 | O-1 | NMFS75 | 54075 | K-17 |
| GP26BRGC | 08958 | J-1 | L423A | 34214 | E-9 | LV2LP | 23102 | O-2 | NMLT10 | 54102 | A-1 |
| GP26G | 77094 | J-1 | L424 | 34240 | E-9 | LV3 | 09600 | O-1 | NMLT100 | 54100 | A-5 |
| GP26GGC | 09011 | J-1 | L424A | 34215 | E-9 | LV4 | 09601 | O-1 | NMLT100BL | 06112 | A-5 |
| GP26W | 77096 | J-1 | L425 | 34250 | E-9 | LVD2 | 10957 | Q-10 | NMLT125 | 04223 | A-5 |
| GP26WGC | 09012 | J-1 | L425A | 34216 | E-9 | LVD2R | 01000 | Q-10 | NMLT125BL | 06114 | A-5 |
| GP37B | 76153 | J-4 | L426 | 34260 | E-9 | LVH1 | 10979 | O-4 | NMLT150 | 04222 | A-5 |
| GP37BGC | 08959 | J-4 | L426A | 34217 | E-9 | LVH1K | 10984 | O-4 | NMLT150BL | 06116 | A-5 |
| GP37BR | 76154 | J-4 | L427 | 34270 | E-9 | LVMB1 | 14364 | O-4 | NMLT200 | 04221 | A-5 |
| GP37BRGC | 08960 | J-4 | L427A | 42700 | E-9 | LVMB2 | 14365 | O-4 | NMLT200BL | 06118 | A-5 |
| GP37G | 76156 | J-4 | L428 | 34280 | E-9 | LVN1 | 00261 | O-3 | NMLT38 | 54380 | A-5 |
| GP37GGC | 09013 | J-4 | L428A | 42800 | E-9 | LVN2 | 00275 | O-3 | NMLT38BL | 06120 | A-5 |
| GP37W | 76155 | J-4 | L429 | 34290 | E-9 | LVN3 | 00277 | O-3 | NMLT45100 | 54110 | A-6 |
| GP37WGC | 08961 | J-4 | L429A | 42900 | E-9 | LVN4 | 00278 | O-3 | NMLT45100BL | 06122 | A-6 |
| GPBK35B | 77040 | J-3 | L48 | 34800 | E-11 | LVS1 | 00262 | O-3 | NMLT45125 | 54125 | A-6 |

SNAP-TITE® & SNAP²IT® Products Note

Arlington's metallic SNAP-TITE® & SNAP²IT® products have been tested and listed by UL in accordance with UL's ground fault requirements.

N.E.C. 2014. 250.97. Bonding for Over 250 Volts. For circuits of over 250 volts to ground, the electrical continuity of metal raceways and cables with metal sheaths that contain any conductor other than service conductors shall be ensured by one or more of the methods specified for services in 250.92(B), except for (B)(1).

Exception: Where oversized, concentric, or eccentric knockouts are not encountered, or where a box or enclosure with concentric or eccentric knockouts is listed to provide a permanent, reliable bond, the following methods shall be permitted:

- (1) Threadless couplings and connectors for cables with metal sheaths
- (2) Two locknuts, on rigid metal conduit or intermediate metal conduit, one inside and one outside of boxes and cabinets
- (3) Fittings with shoulders that seat firmly against the box or cabinet, such as electrical metallic tubing connectors, flexible metal conduit connectors, and cable connectors, with one locknut on the inside of boxes and cabinets
- (4) Listed fittings

STANDARDS

| PRODUCT GROUP | UL STANDARD NUMBER | UL FILE NUMBER | UL CONTROL NUMBER | CSA FILE NUMBER | FED SPEC NUMBER | NEMA STANDARD |
|---------------------------------|--------------------|----------------|-------------------|-----------------|-----------------|---------------|
| Liquid-Tight Fittings | UL 514B | E60812 | 351F | LR49636 | A-A-50552 | FB-1 |
| EMT Fittings | UL 514B | E20643 | 365D | LR49636 | A-A-50553 | FB-1 |
| Non-Metallic Cable Connectors | UL 514B | E28474 | 388D | LR49636 | A-A-50552 | FB-1 |
| Flexible Cord Connectors | UL 514B | E105706 | 1B64 | LR49636 | A-A-50552 | FB-1 |
| Armored Cable Connectors | UL 514B | E18304 | 372D | LR49636 | A-A-50552 | FB-1 |
| Service Entrance Cable Fittings | UL 514B | E66990 | 282F | LR49636 | A-A-50563 | FB-1 |
| Grounding and Bonding Equipment | UL 467 | E75814 | 910F | LR49636 | A-A-50552 | FB-1 |
| Conduit Bodies | UL 514A UL 514B | E28474 | 5B36 | LR49636 | A-A-50563 | FB-1 |
| Conduit Fittings-Rigid | UL 514B | E60812 | 351F | LR49636 | A-A-50553 | FB-1 |
| MC Cable Connectors | UL 514B | E123751 | 388E | LR49636 | A-A-50552 | FB-1 |
| Grounding Lugs | UL 514B | E86540 | 910F | LR49636 | A-A-50552 | FB-1 |
| Flush Device Box Covers | UL 514A | E48106 | 910F | LR49636 | A-A-50563 | FB-1 |
| Non-Metallic Outlet Boxes | UL 514C | E170558 | 6D39 | LR49636 | A-A-50563 | FB-1 |

PATENT NUMBERS

Arlington products are covered by one or more of the following U.S. and foreign patents. Additional patents pending.

| | | | | | | |
|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| 8,324,516 | 7,735,794 | 7,307,213 | D522,347 | 6,742,748 | 6,369,322 | 6,100,470 |
| 8,314,350 | 7,591,656 | 7,307,212 | 7,045,713 | 6,740,813 | 6,355,887 | 6,093,890 |
| 8,302,265 | 7,586,039 | 7,304,251 | 7,038,131 | 6,734,356 | 6,355,884 | D427,889 |
| 8,297,579 | 7,582,827 | 7,304,240 | 7,036,960 | 6,709,280 | 6,355,883 | 6,080,933 |
| D663,274 | 7,563,979 | 7,304,236 | 7,025,311 | 6,682,355 | 6,355,882 | 6,051,786 |
| 8,212,144 | 7,537,467 | 7,304,235 | 7,021,591 | 6,677,523 | 6,352,439 | 6,044,868 |
| D659,644 | 7,531,745 | 7,294,781 | 7,009,110 | 6,670,553 | 6,346,674 | 6,043,432 |
| 8,158,882 | 7,528,322 | 7,262,370 | 7,005,578 | 6,655,644 | 6,335,488 | 6,028,268 |
| 8,148,635 | 7,525,043 | 7,259,337 | 6,978,973 | 6,646,201 | 6,313,406 | 6,005,190 |
| 8,148,634 | 7,518,061 | 7,259,328 | 6,967,284 | 6,642,451 | 6,310,290 | 5,988,570 |
| 8,124,891 | 7,495,184 | 7,238,894 | 6,965,078 | 6,632,998 | 6,307,154 | 5,959,246 |
| 8,124,873 | 7,488,891 | 7,234,670 | 6,957,968 | 6,629,676 | 6,281,434 | 5,939,680 |
| 8,091,721 | 7,485,806 | 7,227,085 | 6,956,171 | 6,624,355 | 6,268,563 | 5,939,671 |
| 8,087,631 | 7,485,805 | 7,226,309 | 6,956,170 | 6,616,194 | 6,263,619 | 5,916,094 |
| 8,076,578 | 7,476,807 | 7,216,838 | 6,951,983 | 6,607,086 | D443,499 | D407,963 |
| 8,076,575 | 7,470,859 | 7,214,875 | 6,935,890 | 6,604,400 | 6,239,368 | 5,823,482 |
| 8,076,573 | 7,462,775 | 7,176,377 | 6,932,390 | 6,600,117 | 6,222,128 | 5,804,764 |
| 8,067,703 | 7,446,266 | 7,166,801 | 6,924,431 | 6,596,939 | 6,213,316 | 5,775,739 |
| 8,063,302 | 7,442,079 | 7,161,095 | 6,921,861 | 6,585,221 | 6,204,447 | 5,773,760 |
| 8,044,300 | 7,435,900 | 7,154,054 | 6,915,992 | 6,581,884 | 6,194,661 | 5,765,786 |
| 7,954,538 | 7,429,025 | 7,151,219 | 6,863,251 | 6,538,201 | 6,194,657 | 5,736,674 |
| 7,942,679 | 7,407,138 | 7,135,640 | 6,857,606 | 6,521,831 | D438,175 | 5,693,910 |
| 7,897,870 | 7,402,748 | 7,117,591 | 6,849,803 | 6,517,032 | 6,191,362 | 5,628,087 |
| 7,882,886 | 7,390,980 | 7,115,820 | 6,806,426 | 6,513,766 | 6,180,879 | 5,596,177 |
| 7,854,627 | 7,388,162 | 7,109,419 | 6,794,573 | 6,511,028 | 6,180,878 | 5,543,582 |
| 7,847,190 | 7,381,088 | 7,098,399 | 6,780,100 | 6,509,524 | 6,177,633 | 5,539,152 |
| D627,317 | 7,374,212 | 7,087,837 | 6,780,029 | 6,460,813 | 6,173,935 | 5,442,141 |
| D627,305 | 7,355,118 | 7,080,859 | 6,779,764 | 6,452,813 | 6,152,413 | 5,410,104 |
| 7,834,267 | 7,350,659 | 7,077,280 | 6,777,615 | 6,452,098 | 6,143,982 | |
| 7,820,911 | 7,347,401 | D524,635 | 6,774,304 | 6,422,781 | 6,133,529 | |
| 7,816,604 | 7,329,144 | 7,075,004 | 6,770,811 | 6,386,489 | 6,114,631 | |
| D620,786 | 7,319,192 | 7,064,271 | 6,768,071 | 6,382,571 | 6,114,630 | |
| D620,346 | 7,312,395 | 7,060,900 | 6,767,032 | 6,380,489 | 6,112,927 | |
| 7,759,576 | 7,307,214 | 7,060,898 | 6,752,362 | 6,378,813 | 6,102,442 | |

SAVES TIME • EASY INSTALLATION

PUSH-ON CONNECTORS

FOR NON-METALLIC LIQUID-TIGHT CONDUIT, TYPE B



PUSH ON
installation



17 seconds
per connector
VS

Conventional
installation



57 seconds
per connector

Made in USA



View Video



- Push-on connectors in straight and 90° are the fastest, easiest way to install non-metallic liquid-tight conduit, type B
- One-piece connectors reduce labor steps; eliminate lost pieces
- Ship fully assembled ñ no disassembly needed
- Removable, reusable

SAVE 40 seconds or *33¢ per push-on connector!

*at \$30.00/hour labor rate



Arlington




SNAP²IT[®] Non-Metallic Connectors

For use with non-metallic liquid-tight conduit, type B only. Push on installation. Produced from UV rated plastic for long outdoor life.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NMLT5 | 54576 | 1/2 | 1/2 | 25 | 100 | 2.376 | .619 | 1.420 |
| NMLT7 | 54577 | 3/4 | 3/4 | 10 | 50 | 2.425 | .670 | 1.664 |
| NMLT10 | 54102 | 1 | 1 | 5 | 25 | 2.530 | .708 | 1.856 |



FEATURES AND BENEFITS

- Competitively priced
- Fast and easy installation
- Provides a super-secure, liquid-tight seal
- Removable and reusable!



PUSHES
onto conduit...
NO TOOLS!

Installation Instructions

To install, simply **PUSH ON** to conduit. That's it!



Scan For Video





90° SNAP²IT[®] Non-Metallic Connectors

For use with non-metallic liquid-tight conduit, type B only. Push on installation. Produced from UV rated plastic for long outdoor life.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NMLT905 | 54578 | 1/2 | 1/2 | 10 | 50 | 2.331 | .605 | 3.389 |
| NMLT907 | 54579 | 3/4 | 3/4 | 10 | 50 | 2.682 | .670 | 3.645 |
| NMLT9010 | 54104 | 1 | 1 | 5 | 25 | 2.874 | .708 | 4.107 |



Fast and easy installation
(see above)

SNAP²IT[®] Zinc Connectors

For use with metallic and non-metallic liquid-tight conduit, type B. Push on installation.



LT5



LT5A

Fast and easy installation
(see page A-1)

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| LT5 | 32502 | 1/2 | 1/2 | 25 | 100 | 2.376 | .619 | 1.420 |
| LT7 | 32503 | 3/4 | 3/4 | 10 | 50 | 2.425 | .670 | 1.664 |
| LT10 | 32102 | 1 | 1 | 5 | 25 | 2.495 | .708 | 1.890 |

PATENTED.



E60812 LR49636


With Insulated Throat

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| LT5A | 35085 | 1/2 | 1/2 | 25 | 100 | 2.376 | .619 | 1.420 |
| LT7A | 35086 | 3/4 | 3/4 | 10 | 50 | 2.425 | .670 | 1.664 |
| LT10A | 35087 | 1 | 1 | 5 | 25 | 2.495 | .708 | 1.890 |

PATENTED. ADDITIONAL PATENTS PENDING.



E60812 LR49636



Scan For Video



90° SNAP²IT[®] Zinc Connectors

For use with metallic and non-metallic liquid-tight conduit, type B. Push on installation.



LT905



LT905A

Fast and easy installation
(see page A-1)

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| LT905 | 32504 | 1/2 | 1/2 | 10 | 50 | 2.331 | .605 | 3.389 |
| LT907 | 32505 | 3/4 | 3/4 | 10 | 50 | 2.682 | .670 | 3.645 |
| LT9010 | 32104 | 1 | 1 | 5 | 25 | 2.874 | .708 | 4.107 |

PATENTED.



E60812 LR49636


With Insulated Throat

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| LT905A | 24233 | 1/2 | 1/2 | 10 | 50 | 2.331 | .605 | 3.389 |
| LT907A | 35089 | 3/4 | 3/4 | 10 | 50 | 2.682 | .670 | 3.645 |
| LT9010A | 35090 | 1 | 1 | 5 | 25 | 2.874 | .708 | 4.107 |

PATENTED. ADDITIONAL PATENTS PENDING.



E60812 LR49636



Scan For Video



SNAP²IT[®] Zero to 90[™] Non-Metallic Connectors

For use with non-metallic liquid-tight conduit, type B only. Push on installation. Produced from UV rated plastic for long outdoor life.





zero to 90[™]

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|
| NMLT590 | 03900 | 1/2 | 1/2 | 10 | 50 | 3.165 | 2.435 | 3.594 | 2.007 |
| NMLT790 | 03902 | 3/4 | 3/4 | 10 | 50 | 3.875 | 2.900 | 4.200 | 2.623 |

Add suffix "BL" to Catalog # when ordering in black, for example NMLT590BL.

Factory order only. Minimum quantities required.

PATENTED.



PUSHES
onto conduit...
NO TOOLS!



Adjusts for ALL ANGLES... from 0° to 90°!

To adjust the angle simply loosen the center nut, twist to the correct angle, and retighten.

One-Piece Screw-In Liquid Tight Connectors

For use with metallic and non-metallic liquid-tight conduit, type B only.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|
| LTSC50 | 35405 | 1/2 | 1/2 | 25 | 100 | .525 | 1.535 |
| LTSC75 | 35408 | 3/4 | 3/4 | 25 | 100 | .525 | 1.535 |

PATENTED.



FEATURES AND BENEFITS

- Costs 20% less than multi-piece fittings
- Fast and easy screw-on installation
- One-piece, low profile construction
- Built-in gasket maintains liquid-tight seal
- No tools required





Zero to 90™ Connectors

For use with non-metallic liquid-tight conduit, type B only. Produced from UV rated plastic for long outdoor life.




zero to 90™

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|
| NMLT5090 | 06240 | 1/2 | 1/2 | 10 | 50 | 2.765 | 1.945 | 2.324 | 2.387 |
| NMLT7590 | 06260 | 3/4 | 3/4 | 10 | 50 | 3.540 | 2.590 | 3.250 | 2.820 |



COSTS THE SAME as our "REGULAR" 90° FITTING!

Installation Instructions



Arlington's no-spin ferrule allows the Zero to 90 connector to be secured to the conduit while fully assembled. To install, simply loosen the tightening nut and screw onto conduit. A positive liquid-tight seal is formed by the pressure sensitive internal gland as the nut is tightened. The sealing ring assures a liquid-tight seal between the fitting and box.

Adjusts for ALL ANGLES... from 0° to 90°!

To adjust the angle simply loosen the center nut, twist to the correct angle, and retighten.



Screw-On Straight Non-Metallic Connectors


For use with non-metallic liquid-tight conduit, type B only. Produced from UV rated plastic for long outdoor life.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NMSC38 | 21005 | 3/8 | 1/2 | 25 | 100 | 1.350 | .535 | 1.250 |
| NMSC50 | 21000 | 1/2 | 1/2 | 25 | 100 | 1.410 | .535 | 1.228 |
| NMSC75 | 21010 | 3/4 | 3/4 | 25 | 100 | 1.546 | .546 | 1.594 |
| NMSC100 | 14950 | 1 | 1 | 5 | 25 | 1.810 | .650 | 1.750 |

Add suffix "BL" to Catalog # when ordering in black, for example NMSC50BL.

PATENTED.



Conduit threads onto ferrule and up inside the outer body. The inside taper squeezes down on the outside of conduit for a superior liquid-tight seal. The cut portion of the conduit does not show, giving a more attractive finished appearance. Also for use with flexible non-metallic tubing. These connectors screw on easily by hand and are removable with pliers.

Screw-On 90° Non-Metallic Connectors

For use with non-metallic liquid-tight conduit, type B only. Produced from UV rated plastic for long outdoor life.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NMSC9038 | 21003 | 3/8 | 1/2 | 25 | 100 | 2.110 | .534 | 2.289 |
| NMSC9050 | 21007 | 1/2 | 1/2 | 25 | 100 | 2.110 | .542 | 2.525 |
| NMSC9075 | 21009 | 3/4 | 3/4 | 25 | 100 | 2.489 | .545 | 2.872 |
| NMSC90100 | 14951 | 1 | 1 | 5 | 25 | 2.758 | .650 | 3.722 |

Add suffix "BL" to Catalog # when ordering in black, for example NMSC9050BL.

PATENTED.



Note: Screw connector onto the conduit until it stops. If the fitting is not in alignment with the knockout, you may unscrew the fitting up to one full turn for adjustment.



Conduit threads onto ferrule and up inside the outer body. The inside taper squeezes down on the outside of conduit for a superior liquid-tight seal. The cut portion of the conduit does not show, giving a more attractive finished appearance. Also for use with flexible non-metallic tubing. These connectors screw on easily by hand and are removable with pliers.

Straight Non-Metallic Connectors

For use with non-metallic liquid-tight conduit, type B only. Produced from UV rated plastic for long outdoor life.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NMLT38 | 54380 | 3/8 | 1/2 | 25 | 100 | 1.425 | .535 | 1.421 |
| NMLT50 | 54500 | 1/2 | 1/2 | 25 | 100 | 1.425 | .535 | 1.421 |
| NMLT75 | 54750 | 3/4 | 3/4 | 10 | 50 | 1.475 | .550 | 1.583 |
| NMLT100 | 54100 | 1 | 1 | 5 | 25 | 1.950 | .670 | 1.925 |
| NMLT125 | 04223 | 1-1/4 | 1-1/4 | 5 | 25 | 2.217 | .645 | 2.418 |
| NMLT150 | 04222 | 1-1/2 | 1-1/2 | 2 | 10 | 2.155 | .660 | 2.700 |
| NMLT200 | 04221 | 2 | 2 | 2 | 10 | 2.400 | .670 | 3.360 |

Add suffix "BL" to Catalog # when ordering in black, for example NMLT50BL.



Installation Instructions

Arlington's reusable Liquid-Tight Fittings may be secured to conduit while fully assembled because of our no-spin ferrule. Simply loosen nut, and screw onto conduit. A positive liquid-tight seal is provided by our pressure sensitive internal gland when the nut is tightened. A liquid-tight seal is also assured between the fitting and box by a sealing ring.




90° Non-Metallic Connectors

For use with non-metallic liquid-tight conduit, type B only. 90° connector provides a smooth, gradual radius bend. Wiring is easily pulled or pushed through fitting and there are no sharp edges to strip wire. Produced from UV rated plastic for long outdoor life.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NMLT9038 | 54903 | 3/8 | 1/2 | 10 | 50 | 2.325 | .562 | 2.440 |
| NMLT9050 | 54905 | 1/2 | 1/2 | 10 | 50 | 2.325 | .562 | 2.440 |
| NMLT9075 | 54907 | 3/4 | 3/4 | 10 | 50 | 2.550 | .545 | 2.840 |
| NMLT90100 | 54901 | 1 | 1 | 5 | 25 | 3.150 | .630 | 3.922 |
| NMLT90125 | 54912 | 1-1/4 | 1-1/4 | 5 | 25 | 4.440 | .645 | 4.650 |
| NMLT90150 | 54915 | 1-1/2 | 1-1/2 | 2 | 10 | 4.510 | .660 | 4.810 |
| NMLT90200 | 54920 | 2 | 2 | 2 | 10 | 5.062 | .670 | 5.320 |

Add suffix "BL" to Catalog # when ordering in black, for example NMLT9050BL.




45° Non-Metallic Connectors

For use with non-metallic liquid-tight conduit, type B only. 45° connector provides a smooth, gradual radius bend. Wiring is easily pulled or pushed through fitting and there are no sharp edges to strip wire. Produced from UV rated plastic for long outdoor life.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NMLT4538 | 54538 | 3/8 | 1/2 | 10 | 50 | 1.550 | .562 | 1.862 |
| NMLT4550 | 54550 | 1/2 | 1/2 | 10 | 50 | 1.596 | .562 | 1.975 |
| NMLT4575 | 54575 | 3/4 | 3/4 | 10 | 50 | 1.820 | .545 | 2.237 |
| NMLT45100 | 54110 | 1 | 1 | 5 | 25 | 2.200 | .630 | 2.990 |
| NMLT45125 | 54125 | 1-1/4 | 1-1/4 | 5 | 25 | 2.710 | .645 | 3.420 |
| NMLT45150 | 54150 | 1-1/2 | 1-1/2 | 2 | 10 | 2.960 | .660 | 3.675 |
| NMLT45200 | 54200 | 2 | 2 | 2 | 10 | 3.500 | .670 | 4.060 |

Add suffix "BL" to Catalog # when ordering in black, for example NMLT4550BL.



Straight Zinc Die-Cast Connectors

For use with metallic and non-metallic liquid-tight conduit, type B only.

Liquid Tight



LT50



LT250




LT50A

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| LT38 | 32380 | 3/8 | 1/2 | 25 | 100 | 1.440 | .510 | 1.260 |
| LT50 | 32500 | 1/2 | 1/2 | 25 | 100 | 1.440 | .520 | 1.385 |
| LT75 | 32750 | 3/4 | 3/4 | 10 | 50 | 1.562 | .500 | 1.720 |
| LT100 | 32100 | 1 | 1 | 5 | 25 | 1.825 | .593 | 1.900 |
| LT125 | 32125 | 1-1/4 | 1-1/4 | 5 | 25 | 2.068 | .625 | 2.176 |
| LT150 | 32150 | 1-1/2 | 1-1/2 | 2 | 10 | 2.008 | .625 | 2.507 |
| LT200 | 32200 | 2 | 2 | 2 | 10 | 2.103 | .593 | 3.178 |
| LT250* | 32250 | 2-1/2 | 2-1/2 | 1 | 1 | 3.269 | .980 | 4.218 |
| LT300* | 32300 | 3 | 3 | 1 | 1 | 4.060 | 1.070 | 4.919 |
| LT350* | 32350 | 3-1/2 | 3-1/2 | 1 | 1 | 4.115 | 1.065 | 5.520 |
| LT400* | 32400 | 4 | 4 | 1 | 1 | 4.323 | 1.139 | 5.948 |

*Provided with insulated throat.



E60812 LR49636




With Insulated Throat

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| LT38A | 32381 | 3/8 | 1/2 | 25 | 100 | 1.533 | .493 | 1.260 |
| LT50A | 32501 | 1/2 | 1/2 | 25 | 100 | 1.593 | .613 | 1.385 |
| LT75A | 32751 | 3/4 | 3/4 | 10 | 50 | 1.656 | .593 | 1.720 |
| LT100A | 32101 | 1 | 1 | 5 | 25 | 1.935 | .686 | 1.900 |
| LT125A | 32121 | 1-1/4 | 1-1/4 | 5 | 25 | 2.168 | .639 | 2.176 |
| LT150A | 32151 | 1-1/2 | 1-1/2 | 2 | 10 | 2.101 | .680 | 2.507 |
| LT200A | 32201 | 2 | 2 | 2 | 10 | 2.196 | .686 | 3.178 |
| LT250 | 32250 | 2-1/2 | 2-1/2 | 1 | 1 | 3.269 | .980 | 4.218 |
| LT300 | 32300 | 3 | 3 | 1 | 1 | 4.060 | 1.070 | 4.919 |
| LT350 | 32350 | 3-1/2 | 3-1/2 | 1 | 1 | 4.115 | 1.065 | 5.520 |
| LT400 | 32400 | 4 | 4 | 1 | 1 | 4.323 | 1.139 | 5.948 |



E60812 LR49636



90° Zinc Die-Cast Connectors

For use with metallic and non-metallic liquid-tight conduit, type B only.



LT9050



LT90150



LT9050A




LT90150A

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| LT9038 | 32938 | 3/8 | 1/2 | 10 | 50 | 2.062 | .520 | 2.340 |
| LT9050 | 32950 | 1/2 | 1/2 | 10 | 50 | 2.128 | .525 | 2.312 |
| LT9075 | 32970 | 3/4 | 3/4 | 10 | 50 | 2.515 | .510 | 2.664 |
| LT90100 | 32910 | 1 | 1 | 5 | 25 | 2.758 | .675 | 3.640 |
| LT90125 | 32913 | 1-1/4 | 1-1/4 | 2 | 10 | 3.362 | .700 | 3.912 |
| LT90150 | 32915 | 1-1/2 | 1-1/2 | 2 | 10 | 3.500 | .604 | 4.368 |
| LT90200 | 32920 | 2 | 2 | 2 | 10 | 4.106 | .680 | 4.865 |
| LT90250* | 32925 | 2-1/2 | 2-1/2 | 1 | 1 | 5.500 | .870 | 6.225 |
| LT90300* | 32930 | 3 | 3 | 1 | 1 | 6.000 | .950 | 6.720 |
| LT90350* | 32935 | 3-1/2 | 3-1/2 | 1 | 1 | 6.625 | .950 | 7.450 |
| LT90400* | 32940 | 4 | 4 | 1 | 1 | 7.000 | .950 | 8.000 |

*Provided with insulated throat.



E60812 LR49636




With Insulated Throat

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| LT9038A | 32931 | 3/8 | 1/2 | 10 | 50 | 2.137 | .520 | 2.340 |
| LT9050A | 32951 | 1/2 | 1/2 | 10 | 50 | 2.203 | .525 | 2.312 |
| LT9075A | 32971 | 3/4 | 3/4 | 10 | 50 | 2.590 | .510 | 2.664 |
| LT90100A | 32911 | 1 | 1 | 5 | 25 | 2.906 | .675 | 3.640 |
| LT90125A | 32912 | 1-1/4 | 1-1/4 | 2 | 10 | 3.473 | .700 | 3.912 |
| LT90150A | 32955 | 1-1/2 | 1-1/2 | 2 | 10 | 3.575 | .604 | 4.368 |
| LT90200A | 32921 | 2 | 2 | 2 | 10 | 4.206 | .680 | 4.865 |
| LT90250 | 32925 | 2-1/2 | 2-1/2 | 1 | 1 | 5.000 | .945 | 6.225 |
| LT90300 | 32930 | 3 | 3 | 1 | 1 | 6.000 | 1.025 | 6.720 |
| LT90350 | 32935 | 3-1/2 | 3-1/2 | 1 | 1 | 6.625 | 1.025 | 7.450 |
| LT90400 | 32940 | 4 | 4 | 1 | 1 | 7.000 | 1.025 | 8.000 |



E60812 LR49636



Insulating Bushings

Press fit. Holds firmly in place while pulling cables.



Example:
Telephone cable protected by EMT insulating bushing.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|---------------------------|--------------------------|------------|----------|---------|-------|-------|
| EMT50 | 12200 | 1/2 | 100 | 1000 | .531 | .840 |
| EMT75 | 12205 | 3/4 | 100 | 1000 | .531 | 1.056 |
| EMT100 | 12220 | 1 | 100 | 100 | .625 | 1.280 |
| EMT125 | 12225 | 1-1/4 | 100 | 100 | .625 | 1.660 |
| EMT150 | 12230 | 1-1/2 | 100 | 100 | .625 | 1.915 |
| EMT200 | 12235 | 2 | 50 | 50 | .625 | 2.377 |
| EMT250* | 12240 | 2-1/2 | 25 | 25 | 1.225 | 3.062 |
| EMT300* | 12245 | 3 | 25 | 25 | 1.225 | 3.690 |
| EMT350* | 12250 | 3-1/2 | 25 | 25 | 1.231 | 4.187 |
| EMT400* | 12255 | 4 | 25 | 25 | 1.233 | 4.815 |
| Split Insulating Bushings | | | | | | |
| EMT200S | 15301 | 2 | 50 | 50 | 0.875 | 2.327 |
| EMT250S* | 12270 | 2-1/2 | 25 | 25 | 1.240 | 3.065 |
| EMT300S* | 12271 | 3 | 25 | 25 | 1.240 | 3.695 |
| EMT350S* | 12272 | 3-1/2 | 25 | 25 | 1.240 | 4.311 |
| EMT400S* | 22001 | 4 | 25 | 25 | 1.240 | 4.812 |

NEW!

Refer to page I-1 for Rigid Insulating Bushings size 1/2" through 4".

*Can also be used for rigid, IMC, and PVC rigid conduit.





EMT200S - EMT400S

Arlington's EMT Insulating Bushings protect cables from abrasion by EMT. Examples: Power, Cable TV, computer datalines, telephone/modem, audio/video cables, alarm systems, security systems. EMT is often used to protect cables where damage could occur in a house or building.



The new EMT400S insulating bushing is split for easy installation when cables are already in place. They press fit onto conduit and secure with a cable tie. When used for cable protection only, these insulating bushings are a perfect substitution for costly fittings.

Scan For More Information




Meets 2014 NEC code requirements for 300.15(c) protection. Listed for use in environmental air handling spaces per 2014 NEC code requirements 300.22(c).

EMT 2-Piece Connector

Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|
| L20 | 32000 | 1/2 | 1/2 | 50 | 250 | .770 | 1.107 |



Conduit Caps

Conduit cap and insulating bushing.



EMT50C




EMT75C

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| EMT50C | 12203 | 1/2 | 100 | 1000 | .531 | .840 |
| EMT75C | 12204 | 3/4 | 100 | 1000 | .531 | 1.056 |
| EMT100C | 12207 | 1 | 100 | 100 | .625 | 1.280 |
| EMT125C | 12209 | 1-1/4 | 100 | 100 | .625 | 1.660 |
| EMT150C | 12211 | 1-1/2 | 100 | 100 | .625 | 1.915 |
| EMT200C | 12213 | 2 | 50 | 50 | .625 | 2.377 |
| EMT250C* | 12215 | 2-1/2 | 25 | 25 | 1.225 | 3.062 |
| EMT300C* | 12217 | 3 | 25 | 25 | 1.225 | 3.690 |
| EMT350C* | 12219 | 3-1/2 | 25 | 25 | 1.231 | 4.187 |
| EMT400C* | 12221 | 4 | 25 | 25 | 1.233 | 4.815 |

Refer to page I-1 for Rigid Insulating Bushings size 1/2" through 4".

*Can also be used for rigid, IMC, and PVC rigid conduit.



Use this capped version to seal off conduit during concrete pours. Then remove cap/seal with razor knife or use screwdriver to punch hole in cap. (EMT300C)



String can be used to aid removal.

Zinc Combination Couplings

EMT to Rigid


EMT set-screw to screw-in rigid metal conduit. Zinc die-cast.



2400

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------------------------------|----------|---------|-------|-------|-------|
| 2400 | 06920 | 1/2" EMT to 1/2" female threaded | 50 | 50 | 1.000 | 1.267 | .946 |
| 2410 | 06921 | 3/4" EMT to 1/2" female threaded | 50 | 50 | 1.000 | 1.412 | 1.200 |
| 2411 | 06922 | 3/4" EMT to 3/4" female threaded | 50 | 50 | 1.210 | 1.475 | 1.200 |


Use with any listed fitting.



Installation Shots



1/2" EMT to 2400 to SG3838 with flexible metal conduit



3/4" EMT to 2410 to 846 with NM cable



3/4" EMT to 2411 to L422 with flexible metal conduit

EMT Set-Screw Connectors

Concrete tight. Zinc die-cast.



800



803

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| 800‡ | 00800 | 1/2 | 1/2 | 50 | 500 | 1.143 | .375 | 1.076 |
| 801‡ | 00801 | 3/4 | 3/4 | 25 | 250 | 1.390 | .350 | 1.300 |
| 802‡ | 00802 | 1 | 1 | 20 | 200 | 1.550 | .460 | 1.550 |
| 803 | 00803 | 1-1/4 | 1-1/4 | 10 | 60 | 1.930 | .636 | 1.935 |
| 804* | 00804 | 1-1/2 | 1-1/2 | 10 | 60 | 2.200 | .707 | 2.175 |
| 805* | 00805 | 2 | 2 | 5 | 30 | 2.535 | .750 | 2.650 |
| 806*† | 00806 | 2-1/2 | 2-1/2 | 12 | 12 | 2.930 | .830 | 3.300 |
| 807*† | 00807 | 3 | 3 | 12 | 12 | 3.330 | .930 | 3.910 |
| 8075*† | 08075 | 3-1/2 | 3-1/2 | 6 | 6 | 3.500 | 1.000 | 4.465 |
| 808*† | 00808 | 4 | 4 | 6 | 6 | 3.665 | 1.000 | 4.984 |


‡Add suffix "RH" for Robertson Head Screws.

*Concrete tight when taped.

†Listed for use with steel and aluminum EMT, IMC, and rigid conduit.



E20643 LR49636



EMT Set-Screw Connectors with Insulated Throat

Concrete tight. Zinc die-cast.



800A



803A

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| 800A | 80010 | 1/2 | 1/2 | 50 | 500 | 1.240 | .470 | 1.076 |
| 801A | 80110 | 3/4 | 3/4 | 25 | 250 | 1.483 | .449 | 1.300 |
| 802A | 80210 | 1 | 1 | 20 | 200 | 1.643 | .550 | 1.550 |
| 803A | 80310 | 1-1/4 | 1-1/4 | 10 | 60 | 2.023 | .729 | 1.935 |
| 804A* | 80410 | 1-1/2 | 1-1/2 | 10 | 60 | 2.293 | .800 | 2.195 |
| 805A* | 80510 | 2 | 2 | 5 | 30 | 2.630 | .840 | 2.650 |
| 806A*† | 80610 | 2-1/2 | 2-1/2 | 12 | 12 | 3.030 | .920 | 3.280 |
| 807A*† | 80710 | 3 | 3 | 12 | 12 | 3.468 | 1.030 | 3.910 |
| 8075A*† | 80711 | 3-1/2 | 3-1/2 | 6 | 6 | 3.600 | 1.088 | 4.465 |
| 808A*† | 80810 | 4 | 4 | 6 | 6 | 3.758 | 1.100 | 4.984 |


Add suffix "RH" for Robertson Head Screws.

*Concrete tight when taped.

†Listed for use with steel and aluminum EMT, IMC, and rigid conduit.



E20643 LR49636



EMT Set-Screw Couplings


Concrete tight. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 810* | 00810 | 1/2 | 50 | 500 | .950 | 1.560 |
| 811* | 00811 | 3/4 | 25 | 250 | 1.145 | 1.869 |
| 812* | 00812 | 1 | 15 | 150 | 1.435 | 2.000 |
| 813 | 00813 | 1-1/4 | 20 | 120 | 1.828 | 2.500 |
| 814 | 00814 | 1-1/2 | 10 | 60 | 2.075 | 2.890 |
| 815 | 00815 | 2 | 5 | 30 | 2.535 | 2.567 |
| 816† | 00816 | 2-1/2 | 12 | 12 | 3.280 | 4.000 |
| 817† | 00817 | 3 | 12 | 12 | 3.910 | 4.500 |
| 8175† | 08175 | 3-1/2 | 6 | 6 | 4.460 | 4.814 |
| 818† | 00818 | 4 | 6 | 6 | 4.984 | 5.269 |

*Add suffix "RH" for Robertson Head Screws.

†Listed for use with steel and aluminum EMT, IMC, and rigid conduit.




EMT Compression Couplings

UL listed concrete tight. CSA listed concrete tight/rain tight. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 830 | 00830 | 1/2 | 50 | 500 | 1.550 | 1.080 |
| 831 | 00831 | 3/4 | 25 | 250 | 1.615 | 1.313 |
| 832 | 00832 | 1 | 15 | 150 | 1.692 | 1.616 |
| 833 | 00833 | 1-1/4 | 10 | 100 | 2.160 | 2.080 |
| 834 | 00834 | 1-1/2 | 10 | 60 | 2.290 | 2.380 |
| 835 | 00835 | 2 | 10 | 60 | 2.600 | 2.910 |
| 836* | 00836 | 2-1/2 | 12 | 12 | 3.070 | 3.470 |
| 837* | 00837 | 3 | 12 | 12 | 3.300 | 4.133 |
| 838* | 00838 | 3-1/2 | 6 | 6 | 3.330 | 4.775 |
| 839* | 00839 | 4 | 6 | 6 | 3.445 | 5.300 |

*Listed for use with steel and aluminum EMT, IMC, and rigid conduit.



EMT Compression Connectors

UL listed concrete tight. CSA listed concrete tight/rain tight. Zinc die-cast.



820




826

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| 820 | 00820 | 1/2 | 1/2 | 50 | 500 | 1.235 | .349 | 1.080 |
| 821 | 00821 | 3/4 | 3/4 | 25 | 250 | 1.350 | .453 | 1.313 |
| 822 | 00822 | 1 | 1 | 15 | 60 | 1.525 | .538 | 1.616 |
| 823 | 00823 | 1-1/4 | 1-1/4 | 5 | 25 | 1.878 | .600 | 2.080 |
| 824 | 00824 | 1-1/2 | 1-1/2 | 10 | 100 | 2.020 | .607 | 2.380 |
| 825 | 00825 | 2 | 2 | 10 | 60 | 1.995 | .645 | 2.910 |
| 826* | 00826 | 2-1/2 | 2-1/2 | 12 | 12 | 2.775 | .860 | 3.470 |
| 827* | 00827 | 3 | 3 | 12 | 12 | 2.847 | .998 | 4.133 |
| 828* | 00828 | 3-1/2 | 3-1/2 | 6 | 6 | 2.800 | .998 | 4.775 |
| 829* | 00829 | 4 | 4 | 6 | 6 | 3.000 | 1.007 | 5.300 |

*Listed for use with steel and aluminum EMT, IMC, and rigid conduit.



E20643 LR49636



EMT Compression Connectors with Insulated Throat

UL listed concrete tight. CSA listed concrete tight/rain tight. Zinc die-cast.



820A




826A

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| 820A | 82010 | 1/2 | 1/2 | 50 | 500 | 1.346 | .442 | 1.080 |
| 821A | 82110 | 3/4 | 3/4 | 25 | 250 | 1.443 | .546 | 1.313 |
| 822A | 82210 | 1 | 1 | 15 | 60 | 1.620 | .631 | 1.616 |
| 823A | 82310 | 1-1/4 | 1-1/4 | 5 | 25 | 1.971 | .693 | 2.080 |
| 824A | 82410 | 1-1/2 | 1-1/2 | 10 | 100 | 2.120 | .700 | 2.380 |
| 825A | 82510 | 2 | 2 | 10 | 60 | 2.088 | .738 | 2.910 |
| 826A* | 82610 | 2-1/2 | 2-1/2 | 12 | 12 | 2.870 | .953 | 3.470 |
| 827A* | 82710 | 3 | 3 | 12 | 12 | 2.940 | 1.091 | 4.133 |
| 828A* | 82810 | 3-1/2 | 3-1/2 | 6 | 6 | 2.900 | 1.091 | 4.775 |
| 829A* | 82910 | 4 | 4 | 6 | 6 | 3.150 | 1.100 | 5.300 |

*Listed for use with steel and aluminum EMT, IMC, and rigid conduit.



E20643 LR49636




Combination Couplings

EMT to Flex. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | EMT SIZE | FLEX SIZE | UNIT PKG | STD PKG | DIM A | DIM B | CABLE RANGE |
|----------------|--------------------------|----------|-----------|----------|---------|-------|-------|---------------|
| 860* | 00860 | 1/2 | 3/8 | 50 | 500 | 1.300 | 1.156 | .530 - .620 |
| 861 | 00861 | 1/2 | 1/2 | 25 | 250 | 1.645 | 1.363 | .850 - .910 |
| 862 | 00862 | 3/4 | 3/4 | 25 | 100 | 1.975 | 1.553 | 1.100 - 1.100 |

*CSA only.



Combination Set-Screw Couplings

EMT set-screw to Flex. Zinc die-cast.




8600



8610

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | EMT SIZE | FLEX SIZE | UNIT PKG | STD PKG | DIM A | DIM B | CABLE RANGE |
|----------------|--------------------------|----------|-----------|----------|---------|-------|-------|---------------|
| 8600* | 08600 | 1/2 | 3/8 | 50 | 500 | 1.162 | 1.090 | .530 - .620 |
| 8610 | 08610 | 1/2 | 1/2 | 50 | 500 | 1.736 | 1.170 | .850 - .910 |
| 8620 | 08620 | 3/4 | 3/4 | 25 | 100 | 1.934 | 1.360 | 1.100 - 1.100 |
| 8630 | 08630 | 1 | 1 | 10 | 40 | 2.290 | 1.625 | 1.255 - 1.375 |

*CSA only.




EMT Rain Tight Compression Couplings

UL listed rain tight and concrete tight. Steel. Blue compression nuts help identify these products as rain tight.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 830RT | 82030 | 1/2 | 50 | 50 | 1.890 | 1.125 |
| 831RT | 82031 | 3/4 | 50 | 50 | 2.052 | 1.375 |
| 832RT | 82032 | 1 | 25 | 25 | 2.219 | 1.688 |
| 833RT | 82033 | 1-1/4 | 10 | 10 | 2.558 | 2.063 |
| 834RT | 82034 | 1-1/2 | 10 | 10 | 2.587 | 2.250 |
| 835RT | 82035 | 2 | 10 | 10 | 2.746 | 2.750 |
| 836RT | 83035 | 2-1/2 | 12 | 12 | 4.207 | 3.625 |
| 837RT | 83006 | 3 | 12 | 12 | 4.500 | 4.250 |
| 838RT | 83007 | 3-1/2 | 6 | 6 | 5.025 | 4.688 |
| 839RT | 83008 | 4 | 6 | 6 | 5.460 | 5.188 |




EMT Rain Tight Compression Connectors

UL listed rain tight and concrete tight. Steel. Blue compression nuts help identify these products as rain tight.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| 820RT | 82020 | 1/2 | 1/2 | 50 | 50 | 1.608 | .437 | 1.125 |
| 821RT | 82021 | 3/4 | 3/4 | 50 | 50 | 1.657 | .437 | 1.375 |
| 822RT | 82022 | 1 | 1 | 25 | 25 | 1.823 | .500 | 1.688 |
| 823RT | 82023 | 1-1/4 | 1-1/4 | 10 | 10 | 2.103 | .625 | 2.063 |
| 824RT | 82024 | 1-1/2 | 1-1/2 | 10 | 10 | 2.191 | .625 | 2.250 |
| 825RT | 82025 | 2 | 2 | 10 | 10 | 2.298 | .688 | 2.750 |
| 826RT | 83005 | 2-1/2 | 2-1/2 | 12 | 12 | 3.548 | .750 | 3.625 |
| 827RT | 83006 | 3 | 3 | 12 | 12 | 3.628 | .875 | 4.250 |
| 828RT | 83007 | 3-1/2 | 3-1/2 | 6 | 6 | 3.834 | .937 | 4.688 |
| 829RT | 83008 | 4 | 4 | 6 | 6 | 4.135 | .937 | 5.188 |




EMT Rain Tight Compression Connectors with Insulated Throat

UL listed rain tight and concrete tight. Steel. Blue compression nuts help identify these products as rain tight.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| 820ART | 82045 | 1/2 | 1/2 | 50 | 50 | 1.670 | .500 | 1.125 |
| 821ART | 82046 | 3/4 | 3/4 | 50 | 50 | 1.719 | .500 | 1.375 |
| 822ART | 82047 | 1 | 1 | 25 | 25 | 1.885 | .563 | 1.688 |
| 823ART | 82048 | 1-1/4 | 1-1/4 | 10 | 10 | 2.166 | .688 | 2.063 |
| 824ART | 82049 | 1-1/2 | 1-1/2 | 10 | 10 | 2.253 | .688 | 2.250 |
| 825ART | 82050 | 2 | 2 | 10 | 10 | 2.360 | .750 | 2.750 |
| 826ART | 83000 | 2-1/2 | 2-1/2 | 12 | 12 | 3.610 | .813 | 3.625 |
| 827ART | 83001 | 3 | 3 | 12 | 12 | 3.690 | .938 | 4.250 |
| 828ART | 83002 | 3-1/2 | 3-1/2 | 6 | 6 | 3.896 | 1.000 | 4.688 |
| 829ART | 83003 | 4 | 4 | 6 | 6 | 4.197 | 1.000 | 5.188 |




Combination Compression Couplings

EMT compression to screw-in flexible metal conduit. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | EMT SIZE | FLEX SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|----------|-----------|----------|---------|-------|-------|-------|-------|
| GF860 | 76860 | 1/2 | 3/8 | 25 | 100 | 1.504 | .445 | .725 | 1.060 |
| GF861 | 76861 | 1/2 | 1/2 | 25 | 250 | 1.345 | .715 | .725 | 1.060 |
| GF862 | 76862 | 3/4 | 3/4 | 25 | 250 | 1.745 | .946 | .950 | 1.305 |
| GF863 | 80173 | 1 | 1 | 25 | 100 | 1.895 | 1.125 | 1.170 | 1.625 |
| GF864 | 80175 | 1-1/4 | 1-1/4 | 10 | 40 | 2.500 | 1.420 | 1.340 | 2.100 |




Combination Threaded Rigid and Set-Screw EMT

90° pulling elbows with cover and gasket. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| HL5000 | 83105 | 1/2 | 10 | 100 | 2.150 | 2.150 |
| HL7500 | 83175 | 3/4 | 5 | 50 | 2.300 | 2.300 |
| HL100 | 50171 | 1 | 5 | 25 | 3.040 | 3.040 |
| HL125 | 50173 | 1-1/4 | 2 | 10 | 3.900 | 3.900 |

See hub illustration below.




Combination Threaded Rigid and Set-Screw EMT To Box

90° pulling elbows with cover and gasket. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 9100 | 91005 | 1/2 | 5 | 50 | 2.030 | 1.945 |
| 9110 | 91100 | 3/4 | 5 | 50 | 2.260 | 2.140 |
| 9120 | 50165 | 1 | 5 | 25 | 2.610 | 2.610 |
| 9130 | 50167 | 1-1/4 | 2 | 10 | 3.037 | 3.037 |

See hub illustration below.



Hub Illustration

For Combination Threaded and Set-Screw Pull Elbows

Arlington's combination hubs are threaded for rigid and include set-screws for EMT. The set-screws may be used for rigid, but are not necessary. They are listed rain tight with rigid and concrete tight when taped for EMT. These products can also be used for EMT to rigid.




Heavy-Duty 1-Hole EMT Straps

Plated steel, Click-on.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | EMT SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|----------|----------|---------|-------|-------|-------|-------|
| 370 | 00370 | 1/2 | 100 | 1000 | 1.700 | .700 | .562 | .250 |
| 371 | 00371 | 3/4 | 100 | 1000 | 1.935 | .975 | .625 | .250 |
| 372 | 00372 | 1 | 50 | 500 | 2.210 | 2.210 | .750 | .312 |
| 373 | 00373 | 1-1/4 | 25 | 250 | 2.800 | 2.800 | .875 | .375 |
| 374 | 00374 | 1-1/2 | 25 | 100 | 3.140 | 3.140 | 1.000 | .375 |
| 375 | 00375 | 2 | 25 | 100 | 3.890 | 3.890 | 1.125 | .437 |
| 346 | 00346 | 2-1/2 | 25 | 25 | 4.927 | 4.927 | 1.250 | .562 |
| 347 | 00347 | 3 | 25 | 25 | 5.560 | 5.560 | 1.250 | .562 |
| 348 | 00348 | 3-1/2 | 10 | 10 | 6.337 | 6.337 | 1.250 | .562 |
| 349 | 00349 | 4 | 10 | 10 | 6.811 | 6.811 | 1.250 | .562 |




2-Hole EMT Straps

Plated steel, Click-on.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | EMT SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|----------|----------|---------|-------|-------|-------|-------|
| 360 | 00360 | 1/2 | 100 | 1000 | 2.200 | .790 | .562 | .187 |
| 361 | 00361 | 3/4 | 50 | 500 | 2.700 | .980 | .625 | .187 |
| 362 | 00362 | 1 | 50 | 250 | 2.975 | 1.185 | .688 | .187 |
| 363 | 00363 | 1-1/4 | 50 | 250 | 3.650 | 1.535 | .750 | .253 |
| 364 | 00364 | 1-1/2 | 25 | 250 | 4.250 | 1.670 | .875 | .253 |
| 365 | 00365 | 2 | 25 | 250 | 4.775 | 2.300 | 1.000 | .375 |
| 356 | 00356 | 2-1/2 | 25 | 100 | 5.850 | 2.855 | 1.000 | .375 |
| 357 | 00357 | 3 | 25 | 25 | 6.460 | 3.425 | 1.000 | .375 |
| 358 | 00358 | 3-1/2 | 10 | 10 | 7.300 | 3.925 | 1.000 | .375 |
| 359 | 00359 | 4 | 10 | 10 | 7.895 | 4.390 | 1.000 | .375 |



NON-METALLIC • MADE IN USA

MOUNTING BRACKETS

FOR CLASS 2 LOW VOLTAGE WIRING



The best way to install Class 2 wiring!

- Brackets seat wall plates flush with the mounting surface
- Install faster and cost less than metal!
- UL/CSA Listed

View Video for LV1



Easy, secure Installation

LV1, LV2, LV3, LV4 for EXISTING CONSTRUCTION:

- Centered mounting wing screws pull bracket secure against wall. Adjustable to fit 1/4" to 1" wall thicknesses.

FOR NEW CONSTRUCTION:

- Nail or screw-on LVN series brackets to a wood stud ñ cost less than extension rings ñ install faster than mud rings.

Use the *screw-on* LVS or LVMB series for *steel studs*.



LVMS2

LVMB1

RELIABLE HANGING SUPPORT UP TO 75 LBS

WIRE GRABBER™

FOR FIXTURES AND MORE • NOW IN KITS



FLG3 connector

EASY THUMB SCREW ADJUSTMENT

Better than traditional wire-hanging methods, **Wire Grabber® saves time and costs less than competitive products.**

- Holds static load up to 75 lbs, in wet or dry areas
- No internal spring
- Easy length adjustment - No special tool
- Fully assembled connector
- cULus Listed

View Video



KITS...

STRAIGHT with LOOPED END;

Ys with TOGGLES or HOOKS

with 5 to 30 ft of .080" braided wire



Arlington

CABLEWAY™ Cable Runway Support System

Cable support system for either power or low voltage cable. For new construction or retrofit. Non-metallic.

NM Cable




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-------------------------|---------|-------|-------|-------|--------|
| T205 | 38060 | Wire Tray-5 ft. Lengths | 10 | 4.150 | 2.000 | 3.380 | 60.000 |
| T23A | 38065 | Angle | 10 | 4.160 | 2.000 | 3.380 | 9.280 |
| T23C | 38061 | Coupling | 10 | 4.630 | 2.380 | 3.570 | 2.000 |
| T23E | 38062 | End Cap | 10 | 4.570 | 2.190 | 3.570 | .760 |
| T23F | 38066 | Flat Surface Bracket | 25 | 5.750 | 2.850 | 3.600 | 2.190 |
| T23H | 38063 | Support Bracket | 25 | 5.500 | 3.880 | 3.620 | 1.500 |
| T23T | 38067 | Tee | 10 | 4.160 | 2.000 | 3.380 | 9.280 |
| T23W | 38068 | Wall Mount Bracket | 10 | 2.410 | 5.240 | 5.970 | 5.240 |

PATENTED.



E161207

T23T



FEATURES AND BENEFITS

- Secure, UL Listed as a cable support system
- For power or low voltage cable
- Support brackets attach directly to framing members, without structural damage
- Time saving system – no holes to drill through joists
- Brackets hold cables in place – open the bracket for easier cable insertion
- Slide-on trough protects and covers cable
- Install additional trough sections as needed and join them together with couplings
- Push-on end caps complete the job

Scan for Video



Wire Fill Chart | Maximum Fill: 40 Units

| NM Cable w/ Copper Conductors | Fill Units Per Cable | (or) Total Cables of One Size |
|-------------------------------|----------------------|-------------------------------|
| 14/2 | 1 ea. | 40 |
| 14/3 | 1.25 ea. | 32 |
| 14/4 | 1.5 ea. | 26 |
| 12/2 | 1.5 ea. | 26 |
| 12/3 | 1.75 ea. | 22 |
| 12/4 | 2 ea. | 20 |
| 10/2 | 2 ea. | 20 |
| 10/3 | 2.25 ea. | 17 |
| 8/2 | 2.25 ea. | 17 |
| 8/3 | 2.50 ea. | 16 |
| 6/2 | 2.75 ea. | 14 |
| 6/3 | 3 ea. | 13 |



Rated for a maximum load of 6 lbs/linear foot of runway.

Example:

| | | |
|-----------|-------|------------------|
| (19) 14/2 | @1 | = 19 Units |
| (8) 12/2 | @1.5 | = 12 Units |
| (4) 10/3 | @2.25 | = 9 Units |
| | | total = 40 Units |

SNAP-TITE®

Connectors

With spring steel clip. For NM • SE • MCI • MCIA • Flex • AC cable. For steel and aluminum jacketed cables. Zinc die-cast.



840ST



8400ST

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 840ST | 80070 | 3/8 | 1/2 | 100 | 1000 | .485 | .879 | .858 | .225 - .612 |
| 8400ST | 80074 | 3/8 | 1/2 | 100 | 1000 | .485 | .879 | .858 | .225 - .612 |

Refer to pages C-13 and C-14 for complete cable ranges.

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.


For connectors that cost less and install faster see page C-8.

PATENTED.




E28474 LR49636


See Page E-1 for ring removal instructions



840ST



8400ST



NM Cable Connector

For NM cable. Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 841 | 00841 | 3/8 | 1/2 | 100 | 1000 | .422 | .825 | 1.105 | .225 - .612 |

Refer to pages C-13 and C-14 for complete cable ranges.

For connectors that cost less and install faster see page C-8.



E28474 LR49636



SNAP-TITE®

Connector

With spring steel clip. For NM cable. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 841ST | 80068 | 3/8 | 1/2 | 100 | 1000 | .510 | .912 | .920 | .225 - .612 |

Refer to pages C-13 and C-14 for complete cable ranges.


SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

PATENTED.



E28474 LR49636

See Page E-1 for ring removal instructions



SNAP-TITE®

Connector

With spring steel clip. For NM • SE cable. Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 842ST | 80084 | 3/4 | 3/4 | 50 | 500 | .510 | 1.070 | 1.200 | .300 - .780 |

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

PATENTED.



See Page E-1 for ring removal instructions



Cable Connectors

For NM • SE • MCI • MCI-A • AC cable. For steel and aluminum jacketed cables. Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 840* | 00840 | 3/8 | 1/2 | 100 | 1000 | .422 | .825 | 1.105 | .225 - .612 |
| 8400* | 08400 | 3/8 | 1/2 | 100 | 1000 | .422 | .825 | 1.105 | .225 - .612 |
| 8401* | 08401 | 3/8 | 1/2 | 100 | 1000 | .422 | .825 | 1.105 | .225 - .612 |
| 8402 | 08402 | 3/4 | 3/4 | 50 | 500 | .533 | 1.093 | 1.395 | .375 - .780 |

Refer to pages C-13 and C-14 for complete cable ranges.

*Listed for MCI only. UL# E123751.

†For connectors that cost less and install faster see page C-8.




Combination Coupling

EMT to NM. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | CABLE RANGE |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------------|
| 8600 | 08600 | 1/2 | 50 | 500 | 1.162 | 1.090 | .250 - .612 |




Cable Connectors

For NM • SEU cable. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | MAX OPENING |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 842 | 00842 | 3/4 | 3/4 | 50 | 500 | .481 | 1.000 | 1.375 | .730 |
| 843 | 00843 | 1 | 1 | 25 | 250 | .780 | 1.284 | 1.670 | .850 |
| 844 | 00844 | 1-1/4 | 1-1/4 | 10 | 100 | .710 | 1.312 | 2.030 | .900 |
| 848* | 00848 | 1-1/2 | 1-1/2 | 10 | 50 | .817 | 1.453 | 2.300 | .960 |
| 849* | 00849 | 2 | 2 | 10 | 50 | .823 | 1.590 | 2.900 | .960 |

*UL# E66990 - Service entrance ONLY.




Cable Connectors

For NM • SE cable. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | MAX OPENING |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 842 | 00842 | 3/4 | 3/4 | 50 | 500 | .481 | 1.000 | 1.375 | .730 |
| 843S | 84310 | 1 | 1 | 25 | 250 | .780 | 1.284 | 1.670 | .970 |
| 844S | 84410 | 1-1/4 | 1-1/4 | 10 | 100 | .710 | 1.312 | 2.030 | 1.160 |
| 848S | 84810 | 1-1/2 | 1-1/2 | 10 | 50 | .817 | 1.453 | 2.300 | 1.420 |
| 849S | 84910 | 2 | 2 | 10 | 50 | .823 | 1.590 | 2.900 | 1.750 |



NM Cable Connectors


Plated steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | MAX OPENING |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------------|
| BT50* | 24050 | 14/2 - 8-3 | 100 | 1000 | 1.500 | .720 | .250 - .600 |
| BT75* | 24075 | 8/2 - 6/2 | 50 | 500 | 1.764 | .811 | .124 - .934 |
| BT125 | 24125 | 2/0 - 3/0 | 25 | 250 | 2.245 | .842 | .275 - .900 |
| BT150 | 24150 | 4/0 | 20 | 200 | 2.705 | .835 | .275 - .900 |

*UL only.

Refer to pages C-13 and C-14 for complete cable ranges.




Gland-Type Service Entrance Cable Connectors

Twin screw type. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|--------------|
| WC1001 | 53101 | 1 | 1 | 1 | 50 | 1.400 | .615 | 1.500 | 2.230 | .630 x 1.000 |



UF Connectors


Compression type for underground feeder cable. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| UF50 | 36500 | 1/2 | 1/2 | 25 | 100 | 1.792 | .630 | 1.042 | 14/2 - 12/2 |
| UF75 | 51302 | 3/4 | 3/4 | 10 | 50 | 1.792 | .630 | 1.042 | 14/3 - 10/2 |

Low profile design to fit the new smaller UF cables as well as standard sizes.

PATENTED.



Non-Metallic UF Connectors


Compression type for underground feeder cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| NMUF50 | 55040 | 1/2 | 1/2 | 25 | 100 | 1.792 | .630 | 1.042 | 14/2 - 12/2 |
| NMUF75 | 54367 | 3/4 | 3/4 | 10 | 50 | 1.792 | .630 | 1.042 | 14/3 - 10/2 |

Low profile design to fit the new smaller UF cables as well as standard sizes.

PATENTED.




1-Hole Aluminum Straps

For service entrance cable.
Aluminum.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|------------------|----------|---------|-------|-------|-------|-------|
| 3232 | 32320 | 3 # 8 to 3 #4 | 100 | 1000 | 2.078 | .775 | .600 | .265 |
| 3282 | 03282 | 3 #1/0 to 3 #2/0 | 100 | 1000 | 2.488 | .940 | .720 | .265 |
| 3284 | 32840 | 3 #3/0 to 3 #4/0 | 100 | 1000 | 2.710 | 1.218 | 1.00 | .325 |




1-Hole Steel Straps

For service entrance cable. Plated steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|---------------|----------|---------|-------|-------|-------|-------|
| 301 | 00301 | 8/3 - 3/3 | 100 | 1000 | 1.637 | .442 | .565 | .265 |
| 303 | 00303 | 2/3 | 100 | 1000 | 1.830 | .530 | .575 | .265 |
| 313S | 00133 | 1, 1/0 or 2/0 | 100 | 1000 | 2.472 | .770 | 1.000 | .325 |
| 314S | 00014 | 3/0, 4/0 | 100 | 1000 | 2.790 | .920 | 1.000 | .330 |




2-Hole Cable Straps

For SEU cable. Plated steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-----------|----------|---------|-------|-------|-------|
| C-STRAP | 37500 | 8/3-3/3 | 50 | 200 | 2.410 | .750 | .470 |
| E-STRAP | 43625 | 2/3 | 50 | 200 | 1.080 | .750 | .575 |
| H-STRAP | 82990 | 1/0-2/0 | 50 | 200 | 3.183 | .755 | .750 |
| K-STRAP | 83770 | 3/0, 4/0 | 50 | 200 | 3.500 | .755 | .890 |



Non-Metallic Push-In Connectors

For NM and flexible cord.



NM840




NM841

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NM840 | 54840 | 3/8 | 1/2 | 100 | 1000 | 1.031 | .375 | .965 |
| NM841 | 54841 | 1/2 | 1/2 | 50 | 500 | 1.340 | .475 | 1.125 |
| NM842 | 54842 | 3/4 | 3/4 | 25 | 250 | 1.510 | .475 | 1.200 |
| NM843 | 54843 | 1 | 1 | 25 | 250 | 1.637 | .475 | 1.500 |
| NM844 | 50175 | 1-1/4 | 1-1/4 | 10 | 100 | 2.085 | .475 | 2.012 |

Refer to pages C-13 and C-14 for complete cable ranges.



E28474 LR49636



Installation Instructions

1. Disconnect electrical power. Push the connector into knockout.
2. Install required cables or cords.
3. Place wedge in connector slot and lock tight with a pair of pliers. Tightened wedge provides strong, positive grip.



Non-Metallic Cable Connectors

For non-metallic sheathed cable. One piece construction. Listed for 1 or 2 cables. Holds cables securely and handles a wide range of cable sizes.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NM74 | 54510 | 3/8 | 1/2 | 100 | 1000 | 1.289 | 1.029 | .875 |
| NM75 | 54513 | 3/4 | 3/4 | 25 | 250 | 1.289 | 1.271 | 1.117 |

Refer to pages C-13 and C-14 for complete cable ranges.

PATENTED.



E28474 LR49636



Black Button™ Non-Metallic Push-In Connectors

For NM cable.



NM94



NM95



NM96

The Black Button is not only the lowest cost NM connector on the market, but offers the fastest method of installing single or multiple cables.

For multiple cable installations:

- Two cables may be inserted together or individually.
- A second cable may be added without removing the first.

Plus, the NM94 meets UL and CSA requirements for single or multiple cables.


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| NM94 | 05488 | 3/8 | 1/2 | 250 | 1000 | 1.010 | .450 | .096 |
| NM940 | 72156 | 3/8 | 1/2 | 100 | 1000 | 1.010 | .450 | .096 |
| NM95 | 10956 | 3/4 | 3/4 | 50 | 500 | 1.293 | .597 | .096 |
| NM96 | 72158 | 1 | 1 | 25 | 250 | 1.648 | .683 | .156 |

Refer to pages C-13 and C-14 for complete cable ranges.

PATENTED.



E28474 LR49636



Installation Instructions

1. Disconnect electrical power.
Insert connector into knockout.
2. Push non-metallic sheathed cable into the connector to desired length.



Removal

If necessary, the NM94 series may be removed with a screwdriver.

1. Slip screwdriver under NM connector and twist.
2. NM94 pops out of the knockout.



Reduce your Labor Costs!

- Listed for both 1 or 2 cables.
- Installs easily... snaps into KO using light finger pressure.
- Cables insert without a struggle for a smooth installation.
- Holds wires securely - meets and exceeds UL pullout tests.
- Simple to remove with a twist of a screwdriver.
- Arlington's Black Button™ is the lowest cost NM cable connector available today.

Non-Metallic Bushings for Metal Studs




SB13




SB13BL

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | STUD SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-----------|----------|---------|-------|-------|-------|-------|
| SB13 | 40115 | 2 X 4 | 500 | 500 | 5.670 | 2.500 | .505 | 1.300 |
| SB130 | 40130 | 2 X 4 | 100 | 100 | 5.670 | 2.500 | .505 | 1.300 |
| SB13BL | 40151 | 2 X 4 | 25 | 250 | 5.670 | 2.500 | .505 | 1.300 |

These bushings fit existing irregular shaped holes in metal studs, alleviating the need to punch holes in metal studs, weakening the structural member. Use these bushings to comply with paragraph 300.4(b)(1) of the 2014 NEC code which states that: "In both exposed and concealed locations where nonmetallic-sheathed cables pass through either factory or field punched, cut, or drilled slots or holes in metal members, the cable shall be protected by bushings or grommets covering all metal edges and securely fastened in the opening prior to installation of the cable."





FITS
a standard
1" KNOCKOUT




Installation Instructions

To install these bushings in an irregular shaped hole, pass one end of the joined connector through the hole in the stud. Snap the bushing and the washer ends together. There's no need to separate the two halves.

If a punched hole is required, the SB13 can be installed in a standard 1" trade size, round punched hole (1-3/8" diameter). Snap the bushing end into the hole.



Common hole configurations in metal studs.




Non-Metallic Bushings for Metal Studs



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| SB1 | 18001 | 1/2 | 1000 | 1000 | .940 | .470 | .700 |
| SB10 | 18010 | 1/2 | 100 | 100 | .940 | .470 | .700 |
| SB3 | 18050 | 1 | 1000 | 1000 | 1.750 | .400 | 1.150 |
| SB30 | 18053 | 1 | 100 | 100 | 1.750 | .400 | 1.150 |

Note: See page R-9 for larger sizes.




CS6 Cable Standoff



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------|---------|-------|-------|-------|
| CS6 | 71006 | 500 | 500 | 1.750 | 2.000 | .563 |
| CS60 | 71060 | 100 | 100 | 1.750 | 2.000 | .563 |

Note: For position only. For support clips for AC/MC cable see NM310 on page E-21.

PATENTED.



Holds...

- Six 14/2 NM cables **or**
- Five 12/2 NM cables **or**
- Four 10/2 NM cables **or**
- One 14/2 to 10/2 MC/AC cable

Installation Instructions

Simply position the CS6 in the desired location and insert a sheet metal screw into a steel or wood stud or use a nail in a wood stud. Cable or cables can then be placed between serrated forks. Install mating washer over serrated forks to secure cable/cables.

Metal Stud



Wood Stud



Alternate fastening option: Use staple

Cable Standoffs

Positions non-metallic sheathed cable, phone/data cable, and coaxial cable. Installs with a screw or nail. Nail included with CS4.



CS4





CS7

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------|---------|-------|-------|-------|
| CS4 | 50174 | 100 | 100 | 4.100 | .750 | 1.200 |
| CS7* | 71007 | 100 | 100 | 3.490 | .880 | .740 |


*UL and CSA only

Note: For position only.



FEATURES AND BENEFITS

- Positions cables at a safe distance from nailing surface
- CS4 provides a neat, organized cable installation and prevents tangles
- CS7 positions cable 2" from a furring strip or 2x4 stud
- CS7 features positive lock to keep cables in place
- Positions both flat and round NM cables
- Complies with 2014 NEC Article 300.4d



CS4 Holds...

- One 14/3 to one 10/3
- Three 14/2 W/G to three 10/3

CS7 Holds...

- Up to five runs of 12/2 non-metallic sheathed cable.
- Up to eight runs of Cat 5 cable.
- Up to four runs of Cat 6 cable.
- Up to five runs of coaxial cable.

CS2 & CS20SC Cable Supports

Supports up to four 14/2 - 10/2 flat (any combination) and two 14/3 - 10/3 (any combination) NM cables.





CS2, CS20



#8 self-tapping sheet metal screw
CS20SC

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------|---------|-------|-------|-------|
| CS2 | 71002 | 500 | 500 | 2.650 | 2.530 | .500 |
| CS20 | 71020 | 100 | 100 | 2.650 | 2.530 | .500 |
| CS20SC | 71025 | 100 | 100 | 2.704 | 2.563 | .500 |
| CS20BAG | 71022 | 25 | 100 | 2.650 | 2.530 | .500 |



Installation Instructions

To install the CS2:

Position the CS2 in the desired location on a wood stud and drive in nail. Insert cable or cables.

To install the CS20SC:

Position the CS20SC in the desired location on a wood or metal stud and tighten self-tapping screw. Insert cable or cables.

CS2 on Wood Stud



CS20SC on Metal Stud




The Spacer™ Cable Spacer

Non-metallic cable spacer that holds power or low voltage cables secure and centered on a 2x4.



CS14

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-----------------------|----------|---------|-------|-------|-------|
| CS14 | 33827 | Nail on Cable Spacer | 25 | 250 | .633 | 3.296 | 1.920 |
| CS140 | 33829 | Nail on Cable Spacer | 500 | 500 | .633 | 3.296 | 1.920 |
| CS140SC | 01574 | Screw on Cable Spacer | 500 | 500 | .633 | 3.296 | 1.920 |
| CS14SC | 01573 | Screw on Cable Spacer | 25 | 250 | .633 | 3.296 | 1.920 |



Gland-Type Service Entrance Cable Connectors

Zinc die-cast.



WTC100



WTC200





| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| WTC100 | 58732 | 1" Includes three letter-coded glands | 50 | 50 | 1.583 | 1.450 | 1.610 |
| WTC125 | 58733 | 1-1/4" Includes two letter-coded glands | 50 | 50 | 1.995 | 1.858 | 2.084 |
| WTC150 | 58734 | 1-1/2" Includes two letter-coded glands | 10 | 10 | 2.025 | 2.100 | 2.400 |
| WTC200 | 58735 | 2" Includes two letter-coded glands | 10 | 10 | 2.150 | 2.560 | 2.917 |
| WTC210 | 58736 | 2" Includes three letter-coded glands | 10 | 10 | 2.150 | 2.560 | 2.917 |

PATENTED.



FEATURES AND BENEFITS

- Each connector provides two to three glands that are listed to handle particular cable sizes.
- Quick, easy installation of gland into connector
- Saves time and money
- Reduces inventory - **Five connectors now handle what twelve used to at the same cost!**



REDUCES INVENTORY!
Saves Money

Glands are labeled A, B, or C, indicating what cable range they are good for.

| CATALOG NUMBER | Glands | Grommet Opening MIN ID | Grommet Opening MAX ID | Insulated Conductor Size AWG | Uninsulated Conductor Size AWG |
|----------------|--------|------------------------|------------------------|------------------------------|--------------------------------|
| WTC100 | A | .408 | .655 | #8 | #8 |
| | B | .445 | .720 | #6 | #6 |
| | C | .490 | .795 | #4 | #4 |
| WTC125 | A | .600 | .970 | #2 | #2 |
| | B | .660 | 1.130 | #1 | #1 |
| WTC150 | A | .710 | 1.110 | 1/0 - 19 | 1/0 |
| | B | .780 | 1.230 | 2/0 - 19 | 2/0 |
| WTC200 | A | .710 | 1.110 | 1/0 - 19 | 1/0 |
| | B | .780 | 1.230 | 2/0 - 19 | 2/0 |
| WTC210 | A | .830 | 1.400 | 3/0 - 19 | 3/0 |
| | B | .906 | 1.435 | 4/0 - 19 | 4/0 |
| | C | 1.110 | 1.580 | 4/0 - 19 | 4/0 |

| FITTINGS | CABLE RANGE | | TYPE | |
|--|--|---|--|----------------------|
| 1/2" KO | | | | |
| BT50 | | 1-14/2 to 1-8/3 2-12/3 4-14/2 | NM NM NM | |
| 841, 841ST | 1-14/2 & 1-14/3 1-14/2 & 1-12/3 1-12/2 & 1-14/3 1-12/2 & 1-12/3 2-14/2 & 1-14/3 2-14/2 & 1-12/3 | 1-14/2 to 10/2 1-14/3 to 10/3 2-14/2 to 10/2 1-14/2 & 1-12/2 1-14/2 & 1-10/2 1-12/2 & 1-10/2 3-14/2 | NM NM NM NM NM NM NM | |
| NM74 | 1-14/2 to 1-10/2 1-14/3 to 1-10/3 | 2-14/2 to 2-10/2 2-14/3 | NM NM | |
| NM94 | 1-14/2 to 1-10/2 1-14/3 to 1-10/3 | 2-14/2 to 2-10/2 2-14/3 to 2-12/3 | 1-14/2 and 1-12/2 1-14/2 and 1-10/2 1-12/2 and 1-10/2 1-14/3 and 1-12/3 | NM NM NM NM |
| NM840 | | 1-14/2 to 1-10/2 | NM | |
| NM841 | 1-14/2 to 6/2 1-14/3 to 10/3 1-14/2 & 1-12/2 1-14/2 & 1-10/2 1-12/2 & 1-10/2 1-14/2 & 1-14/3 1-14/2 & 1-12/3 1-12/2 & 1-14/3 1-12/2 & 1-12/3 1-8/2 & 1-14/2 1-8/2 & 1-12/2 | 2-14/2 to 10/2 2-14/2 & 1-14/3 2-14/2 & 1-12/3 2-14/2 & 1-12/2 2-14/2 & 1-10/2 2-14/3 3-14/2 1-14/2 & 2-12/2 1-14/2 & 2-10/2 1-6/2 | NM NM NM NM NM NM NM NM NM NM | |
| 840, 840ST 8400, 8400ST 8401 | | 1-14/2 to 10/2 1-14/3 to 10/3 2-14/2 to 10/2 1-14/2 & 1-12/2 1-14/2 & 1-10/2 1-12/2 & 1-10/2 | NM NM NM NM NM NM | |
| 3/4" KO | | | | |
| BT75 842, 842ST NM842* | | 1-8/2 to 1-6/2 2-14/3 to 2-10/3 1-8/3 to 1-6/3 1-14/3 & 1-12/3 NM 1-12/3 & 1-10/3 1-8/2 to 1-4/2 | NM NM NM NM NM NM SE | |
| *Also listed for the combinations of NM842 on next page. 1-14/3 & 1-10/3 | | | | |

Continued next page

| FITTINGS | CABLE RANGE | | | | | TYPE |
|--|--|----------------|---|------------------|--|--|
| 8402 | 2-10/2 3-14/2 to 3-10/2 | | 1-8/2 to 1-6/2 2-14/3 to 2-10/3 1-8/3 to 1-6/3 1-14/3 & 1-12/3 1-14/3 & 1-10/3 1-12/3 & 1-10/3 1-8/2 to 1-4/2 1-.530 to .570 x .840 to .930 1-.375 to .685 | | | NM NM NM NM NM NM SE SE Flex Cord Flex Cord |
| NM75 | 1-6/2 1-6/3 | 1-8/2 1-8/3 | 1-10/2 1-10/3 | 2-14/2 2-12/2 | 2-10/2 2-10/3 | NM NM |
| NM95 | 1-14/2 to 1-6/2 1-14/3 to 1-6/3 | | 2-14/2 to 2-10/2 2-14/3 to 2-10/3 | | 1-14/2 and 1-12/2 1-14/2 and 1-10/2 1-12/2 and 1-10/2 1-14/3 and 1-12/3 | NM NM NM NM |
| NM842 | 3 to 4 14/2 to 10/2 plus any combination thereof. 2-14/3 & 1-14/2 to 2-14/3 & 1-10/2 3-14/3 to 3-12/3 2-14/3 & 1-12/3 2-12/3 & 1-14/3 to 2-12/3 & 1-10/2 2-14/2 & 1-14/3 to 2-14/2 & 1-10/3 2-12/2 & 1-14/3 to 2-12/2 & 1-10/3 | | 2-10/2 & 1-14/3 to 2-10/2 & 1-12/3 1-14/2 & 1-12/2 & 1-14/3 1-14/2 & 1-10/2 & 1-14/3 1-14/2 & 1-12/2 & 1-12/3 1-14/2 & 1-10/2 & 1-12/3 1-12/3 & 1-14/2 1-12/3 & 1-8/2 | | | NM NM NM NM NM NM NM |
| 1" KO | | | | | | |
| 843, 843S | 2-10/3 to 2-8/3 1-6/2 & 1-8/2 2-6/2 to 1-8/3 2-8/3 & 1-6/2 3-8/2 to 3-6/2 | | 1-6/2 to 1-4/2 1-8/3 to 1-4/3 2-10/3 to 2-8/2 1-8/3 to 1-6/3 1-12/3 & 1-8/2 | | 1-10/3 & 1-8/2 1-10/3 & 1-8/2 2-8/2 1-4/3 1-12/3 & 1-10/3 | NM, SE NM, SE NM, SE NM, SE NM, SE |
| NM843 | 2-10/3 and 2-8/2 | | 1-8/3 to 1-4/3 1-8/3 and 2-6/2 2-8/3 and 1-6/2 | | 3 to 6 14/3 | NM NM NM |
| Any combination of above with minimum Outer Diameter of .580 and a maximum Outer Diameter of .960. | | | | | | |
| NM96 | 1-4/3 to 8/3 | | 1-6/2 to 4/2 | | | NM |
| 1-1/4" KO | | | | | | |
| NM844 | 1-4/3 to 1-6/3 2-6/3 to 2-10/3 4-10/2 10-12/2 9-14/2 1-.750 1-.580 x .950 | | | | | NM NM NM NM Flex Cord Flex Cord |

Low-Profile Strain Relief Cord Connectors

Non-metallic. Liquid-tight • Oil-tight. Furnished with sealing ring and locknut.



WHITE SEALING RING MATCHES PRODUCT



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CORD RANGE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|------------|----------|---------|-------|-------|-------|
| LPCG503* | 50350 | 1/2 | .100-.300 | 25 | 100 | 1.792 | .630 | 1.042 |
| LPCG50W | 32875 | 1/2 | .200-.472 | 25 | 100 | 1.792 | .630 | 1.042 |
| LPCG50* | 80086 | 1/2 | .200-.472 | 25 | 100 | 1.792 | .630 | 1.042 |
| LPCG507 | 50354 | 1/2 | .385-.750 | 25 | 100 | 2.178 | .517 | 1.305 |
| LPCG753* | 50760 | 3/4 | .100-.300 | 10 | 50 | 1.963 | .570 | 1.042 |
| LPCG754 | 50762 | 3/4 | .240-.472 | 10 | 50 | 1.963 | .570 | 1.305 |
| LPCG757 | 36100 | 3/4 | .385-.750 | 10 | 50 | 2.250 | .600 | 1.305 |
| 50LPCGBAG▲ | 55080 | 1/2 | .100-.472 | - | 500 | 1.792 | .630 | 1.042 |
| 75LPCGBAG▲ | 55082 | 3/4 | .100-.472 | - | 100 | 1.963 | .570 | 1.305 |



* UL not applicable for under .240 wire diameter -- wire strength will not meet UL's 35lb test requirement for the fitting.

▲ Includes UF grommet 14/2 to 12/2 and cord grommet .100 to .300. Bags not available in black.

When ordering in black, add suffix "BL" to catalog number. When ordering in white, add suffix "W" to catalog number.

PATENTED.



Arlington's Low Profile Cord Connector has a unique grommet with gripping fingers. These connectors have the largest cord range in the industry, so there are fewer items to stock. A liquid-tight seal and superior pullout resistance is accomplished by just tightening the nut. A sealing ring is furnished to assure a liquid-tight seal when installing in non-threaded openings.

Low-Profile Strain Relief Cord Connectors

Zinc die-cast. Liquid-tight • Oil-tight. Furnished with sealing ring and locknut.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CORD RANGE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|------------|----------|---------|-------|-------|-------|
| LPCG503Z* | 50352 | 1/2 | .100-.300 | 25 | 100 | 1.792 | .630 | 1.042 |
| LPCG50Z* | 36110 | 1/2 | .200-.472 | 25 | 100 | 1.792 | .630 | 1.042 |
| LPCG507Z | 50356 | 1/2 | .385-.750 | 25 | 100 | 2.178 | .517 | 1.305 |
| LPCG753Z* | 36105 | 3/4 | .100-.300 | 10 | 50 | 1.963 | .570 | 1.042 |
| LPCG754Z | 50764 | 3/4 | .240-.472 | 10 | 50 | 1.963 | .570 | 1.305 |
| LPCG757Z | 50766 | 3/4 | .385-.750 | 10 | 50 | 2.250 | .600 | 1.305 |



* UL not applicable for under .240 wire diameter -- wire strength will not meet UL's 35lb pullout test requirement for the fitting.

PATENTED.




Strain Relief Cord Connectors

Liquid-tight • Oil-tight. Furnished with sealing ring. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CORD RANGE | STD PKG | DIM A | DIM B | DIM C | GROMMET COLOR |
|----------------|--------------------------|------------|------------|---------|-------|-------|-------|---------------|
| CG100750 | 30750 | 1 | .625-.750 | 5 | 2.125 | .650 | 1.370 | ORANGE |
| CG100875 | 30875 | 1 | .750-.875 | 5 | 2.150 | .750 | 1.370 | BLACK |
| CG1001000 | 31000 | 1 | .875-1.000 | 5 | 2.150 | .772 | 1.370 | PURPLE |



Colorgrip® Strain Relief Cord Connector


Non-metallic. Liquid-tight • Oil-tight. Furnished with sealing ring and locknut.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CORD RANGE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | GROMMET COLOR |
|----------------|--------------------------|------------|------------|----------|---------|-------|-------|-------|---------------|
| NMCG100750 | 55000 | 1 | .625-.750 | 5 | 30 | 1.800 | .688 | 1.931 | ORANGE |
| NMCG100875 | 55002 | 1 | .750-.875 | 5 | 30 | 1.839 | .671 | 1.931 | BLACK |



When ordering in black - add suffix "BL" to catalog number.



Cable Chart for Arlington Cord Grip Fittings

Check outside wire diameter or manufacturer's specifications for dimensions.

| CABLE RANGE | COMMUNICATION & CONTROL WIRE | SJ & SJO | S & SO | SJTO | STO |
|--------------|--------------------------------------|--------------------------------------|----------------------|--------------------------------------|------------------------------|
| .100 to .200 | 22-2 to 14-1 14-1 12-1 | | | | |
| .200 to .300 | 22-2 20-2 to 20-4 18-2 18-3 | 18-2 18-3 16-2 16-4 | 18-2 18-3 | 18-2 18-3 16-2 16-4 | 18-2 18-3 16-2 16-2 |
| .300 to .385 | | 16-3 | | 16-3 14-2 | |
| .385 to .472 | | 16-4 14-2 to 14-4 12-2 12-3 | 16-2 to 16-4 14-2 | 16-4 14-3 14-4 12-3 12-4 | 18-4 16-3 14-2 |

| CABLE RANGE | SJ & SJO | S & SO | SJTO | STO |
|---------------|----------------------|---|--------------|--|
| .472 to .625 | 12-4 10-2 to 10-4 | 14-3 14-4 12-2 to 12-4 10-3 8-2 | 10-2 to 10-4 | 14-3 14-4 12-2 to 12-4 10-2 10-3 |
| .625 to .750 | 10-4 | 12-4 10-2 to 10-4 8-2 8-3 | 10-4 | 12-4 10-2 to 10-4 |
| .750 to .875 | | 8-4 8-5 6-2 6-3 | | |
| .875 to 1.000 | | 6-4 4-2 4-3 | | 6-4 4-3 |

Non-Metallic Cord Grips

Connects multiple cables to combiner or junction boxes.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CORD RANGE | NUMBER/CABLES | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|-------------------|---------------|----------|---------|-------|-------|
| NMPV100 | 76870 | 1" | .225 to .255 Dia. | 1 to 9 | 25 | 25 | 2.004 | 1.926 |
| NMPV125 | 76871 | 1-1/4" | .225 to .255 Dia. | 1 to 13 | 25 | 25 | 2.628 | 2.426 |



NMPV100



NMPV125



FEATURES AND BENEFITS

- Ideal for jobs requiring the connection of multiple cables into solar, raceways, fittings, and combiner or junction boxes.
- For cables from .225 to .255 – Ideal for #10 PV cables
- NMPV100 - Capacity 1" holds one to nine cables
- NMPV125 - Capacity 1-1/4" holds one to thirteen cables
- UV rated for reliable outdoor use



Using NMPV100 or NMPV125 for SOLAR?

SC100



PAGE S-3

Check out our SC100 on page S-3, or our RoofTopper™ products such as the RTS4 on page S-1.

RTS4



PAGE S-1

THE INDUSTRY STANDARD FROM ARLINGTON

SNAP²IT[®] CONNECTORS

NO TOOLS • SECURE HOLD • EASIEST CABLE INSERTION



Made in USA 



404010AST
(383810AST)

- **Easiest cable installation**
- **Widest total cable ranges** for our ENTIRE line: 14/2 to 3/3
- **Widest variety of cables** AC, MC, HCF, MC continuous corrugated aluminum cable, MCI-A cables (steel and aluminum), AC90 and ACG90
- **Fast, super-secure installation** No chance of pullout!
- **Removable, reusable** from cable or box...easy!

**WIDEST CABLE RANGES.
FASTEST INSTALLATION!**



Arlington



SNAP²IT[®]


Connectors

Zinc die-cast. For AC • MCI-A • HCF steel and aluminum cable • Flexible metal conduit steel and aluminum (regular and reduced wall) • MCI cable • Continuous corrugated aluminum • AC90.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|-------------|
| 38AST* | 00070 | 3/8 | 1/2 | 50 | 500 | 1.410 | .850 | .405 | 1.000 | .405 - .612 |
| 38A* | 00038 | 3/8 | 1/2 | 50 | 500 | 1.410 | .850 | .405 | 1.000 | .405 - .612 |
| 380ST | 00381 | 3/8 | 1/2 | 50 | 500 | 1.280 | .850 | .400 | 1.000 | .405 - .612 |
| 380AST* | 00382 | 3/8 | 1/2 | 50 | 500 | 1.280 | .850 | .400 | 1.000 | .405 - .612 |

*Provided with insulated throat.

PATENTED.



38AST



40AST

With Insulated Throat and Red Tinted Inside Clip

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|-------------|
| 40AST | 00041 | 3/8 | 1/2 | 50 | 500 | 1.410 | .850 | .405 | 1.000 | .485 - .612 |
| 400AST | 40347 | 3/8 | 1/2 | 50 | 500 | 1.280 | .850 | .400 | 1.000 | .485 - .612 |

Refer to chart on page E-22 for a list of cable types.

Concrete tight when taped.

Flexible metal conduit, CSA listed with anti-short bushing (UL not applicable).

SNAP-TITE[®] and SNAP²IT[®] products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

See page E-25 for MCI-A cable ranges.

PATENTED.



For **EASIER** MC/AC INSTALLATIONS see **3810AST** to **7510AST** on Page E-2

NO TOOLS!

- Safe and fast installations
- **Saves about 17 seconds** per fitting!
- Competitively priced

SNAP²IT Connectors are EASY to Install...



Snap onto cable and give a clockwise twist.



Just snap into box!

And EASY to Remove...



Using a screwdriver, lift the ring and twist off.

COMPARE...



38AST



40AST

RED TINTING means 'OPEN TANG' Design!

It gives you more room inside the fitting for easy insertion of wires. The redesigned front end makes it easier than ever to snap the fitting into box!

SNAP²IT[®] Connectors with Insulated Throat

Zinc die-cast. For AC • MCI-A • HCF steel and aluminum cable • Flexible metal conduit steel and aluminum (regular and reduced wall) • MCI cable • Continuous corrugated aluminum • ACG90 • AC90.



3810AST



4010AST



5010AST



7510AST

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|--------------|
| 3810AST | 00385 | 3/8 | 1/2 | 50 | 500 | 1.473 | 1.179 | .840 | .316 | .370 - .490 |
| 4010AST | 40355 | 3/8 | 1/2 | 50 | 500 | 1.473 | 1.244 | .840 | .404 | .405 - .612 |
| 5010AST | 00517 | 1/2 | 1/2 | 25 | 250 | 2.210 | 1.514 | .840 | .614 | .590 - .920 |
| 7510AST | 55090 | 3/4 | 3/4 | 25 | 25 | 2.496 | 1.709 | 1.058 | .828 | .895 - 1.110 |

†Provided with red tinted inside clip so you can tell the difference between a 3810AST to 4010AST.

Refer to chart on page E-22 for a list of cable types. Refer to chart on page E-25 for MCI-A cable ranges. Concrete tight when taped.

SNAP-TITE[®] and SNAP²IT[®] products have been tested and listed by UL in accordance with UL's ground fault requirements.

For additional information see page 6.

PATENTED.




UL US
372D

SF
LR49636

FEATURES AND BENEFITS


- Installs as fast and costs the same as our other SNAP²IT fittings, but cable insertion is even easier!
- Simply snap the cable into the fitting and snap it into the box... no tools needed! The screw only holds the clip in place.
- Widest cable ranges – accommodates cable from 14/2 to 10/4.
- Super-secure – the angled, two-prong clip locks down on MC cable so there's no chance of pullout.
- Cable is removable. Simply loosen the screw on top.



Easy cable insertion – Tight, secure hold!



Back View
Note angled,
two-prong clip



Top View
Clip holds
cable firmly in
place

See Page E-1 for
removal instructions

SNAP²IT[®] Duplex Connectors with Insulated Throat

Zinc die-cast. For AC • MCI-A • HCF steel and aluminum cable • Flexible metal conduit steel and aluminum (regular and reduced wall) • MCI cable • Continuous corrugated aluminum • ACG90 • AC90.



383810AST



404010AST

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|-----------------|
| 383810AST | 10937 | 3/8 | 1/2 | 25 | 100 | 2.398 | 2.035 | .840 | .624 | (2) .370 - .490 |
| 404010AST† | 40533 | 3/8 | 1/2 | 25 | 100 | 2.398 | 2.165 | .840 | .624 | (2) .405 - .612 |
| 505010AST | 50720 | 1/2 | 3/4 | 25 | 25 | 3.054 | 2.717 | 1.058 | .810 | (2) .590 - .920 |


†Provided with red tinted inside clips so you can tell the difference between a 383810AST to 404010AST.

Refer to chart on page E-22 for a list of cable types. Refer to chart on page E-25 for MCI-A cable ranges. Concrete tight when taped.

SNAP-TITE[®] and SNAP²IT[®] products have been tested and listed by UL in accordance with UL's ground fault requirements.

For additional information see page 7.

PATENTED.



For the **WIDEST TOTAL CABLE RANGES**



Secure hold – Easy cable insertion!

Simply snap the cable into the fitting and snap it into the box...no tools needed!

The screw only holds the clip in place.

See Page E-1 for ring removal instructions

SNAP²IT[®] Duplex Connectors

Zinc die-cast. For AC • MCI-A • HCF steel and aluminum cable • Flexible metal conduit steel and aluminum (regular and reduced wall) • MCI cable • Continuous corrugated aluminum • AC90.



3838AST



4040AST

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|-----------------|
| 3838ST* | 10935 | 3/8 | 1/2 | 25 | 100 | 1.912 | 1.738 | .970 | .620 | (2) .405 - .612 |
| 3838AST* | 36230 | 3/8 | 1/2 | 25 | 100 | 1.772 | 1.605 | .840 | .620 | (2) .405 - .612 |
| 4040AST†* | 40351 | 3/8 | 1/2 | 25 | 100 | 1.772 | 1.605 | .840 | .620 | (2) .485 - .612 |

*Provided with insulated throat.

†Provided with insulated throat and red tinted inside clips.


See comparison on page E-1.

SNAP-TITE[®] and SNAP²IT[®] products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

See page E-25 for MCI-A cable ranges.

Concrete tight when taped.

PATENTED.



For **EASIER MC/AC INSTALLATIONS** see 383810AST & 404010AST (above)

No Tools Required...Fully Assembled!

Snap cables into connector and snap assembly into box or fixture.



See Page E-1 for ring removal instructions

“Take All” SNAP-TITE® Connectors

With spring steel clip. Single screw saddle type. For NM • Flex • AC • ACG90 • AC90 • Teck90 • MCI steel and aluminum jacketed cables. Zinc die-cast.



L15AST



L16ST

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|---------------|-------------------|
| L15AST* | 80040 | 3/8 | 1/2 | 50 | 500 | .984 | .420 | 1.032 | .460 - .585 | .340 x .430 |
| L16ST†‡ | 80060 | 3/8 | 1/2 | 50 | 500 | .923 | .375 | 1.208 | .405 - .650 | .400 x .580 |
| L160ST‡ | 02416 | 3/8 | 1/2 | 50 | 500 | .954 | .412 | 1.092 | .370 - .690 | .312 |
| L17ST | 34278 | 1/2 | 1/2 | 50 | 250 | 1.500 | .462 | 1.416 | .630 - .890 | .620 |
| L18ST | 34282 | 3/4 | 3/4 | 25 | 125 | 1.400 | .390 | 1.750 | .820 - 1.040 | .818 |
| L19ST | 34287 | 1 | 1 | 25 | 125 | 1.640 | .443 | 2.048 | 1.100 - 1.400 | 1.030 |

*Provided with insulated throat.

†Listed for flexible cord.

‡Also for MCI-A cable. Refer to page E-25 for cable ranges.

Refer to chart on page E-22 for a list of cable types.

Concrete tight when taped. SNAP-TITE® products have been tested and listed by UL in accordance with UL’s ground fault requirements. For additional information see page 7.

PATENTED.



See Page E-1 for ring removal instructions




L15AST




L160ST



L17ST - L19ST



L15AST - L16ST



L17ST - L19ST

Set-Screw Connectors

For steel only • Flex • AC • MCI cable. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 845 | 00845 | 3/8 | 1/2 | 100 | 1000 | .812 | .905 | .380 | .445 - .630 |
| 845R | 08459 | 3/8 | 1/2 | 100 | 1000 | .812 | .905 | .380 | .445 - .630 |

Refer to chart on page E-23 for a list of cable types.

Concrete tight when taped.


Not suitable for aluminum jacketed cables or aluminum flexible metal conduit.



845



845R



Set-Screw SNAP-TITE® Connectors

With spring steel clip.
For steel only • Flex • AC • MCI cable. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 845ST | 80092 | 3/8 | 1/2 | 100 | 1000 | .942 | .510 | .905 | .445 - .630 |

Refer to chart on page E-25 for a list of cable types.

Concrete tight when taped.

Not suitable for aluminum jacketed cables or aluminum flexible metal conduit.


SNAP-TITE® products have been tested and listed by UL in accordance with UL’s ground fault requirements.

For additional information see page 7.

PATENTED.



See Page E-1 for ring removal instructions



Steel Cable Hangers

For Flex • MCI • AC • HCF cable.
One-piece, galvanized steel cable hangers mount many ways on a variety of surfaces.



FEATURES AND BENEFITS

- Saves money...use SMC steel hangers in place of cable tray
- Each cable is held in place independently, so there's no bundling of cables or derating of conduit
- Accepts a wide range of cables... .375 - .625
- Mounts on concrete block walls or ceilings and screw mounts on metal or wood studs
- SMC4F also mounts on drop wire
- Attach with beam clamp, threaded rod, or with screws
- Meets NEC 2014 paragraphs 300.4(E), 320.30, 320.30(A), 330.30, 330.30(C), and 348.30(A,B).
- Listed to position, support, and secure 14/2 to 10/4 cables – as required by NEC 2014 330.30.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE CAPACITY |
|----------------|--------------------------|----------|---------|-------|-------|-------|-------|----------------|
| SMC4 | 42305 | 25 | 25 | 5.120 | 1.670 | 2.380 | 1.750 | 4 |
| SMC8 | 42307 | 25 | 25 | 7.500 | 1.670 | 2.380 | 1.750 | 8 |
| SMC4F | 42315 | 25 | 25 | 7.500 | .750 | 1.640 | 1.060 | 4 |


PATENT PENDING.



Available in three styles to secure 14/2-10/4 cables:



- SMC8 holds up to 8 cables
- SMC4 holds up to 4 cables
- SMC4F mounts flat – holds up to 4 cables on one side

Mounts in Many Ways!
SMC8 supports and FIRMLY SECURES up to eight cables to comply with NEC 2014.



Code Compliant

Arlington's steel MC cable hangers meet the NEW REQUIREMENTS of NEC 300.4(e) Installing MC or AC metal jacketed cables under corrugated metal roof decking. The outer surface of cable must be 1-1/2" from the underside of the decking. Our SMC hangers exceed this.



Installation Instructions



1 Insert screwdriver through slot.



2 Bend tab over cable, locking it securely in place.

Scan For Video




Twin Screw All-Purpose Connector

For Flex • AC • MCI • NM cable.
Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------------|-------------------|
| 4200 | 04200 | 3/8 | 1/4 | 25 | 25 | 1.040 | .920 | .225 - .612 | .380 |

Refer to chart on page E-23 for a list of cable types.
Concrete tight when taped.



The 4200...

- Allows you to securely hold cables in low profile height fixtures with 1/4" knockouts.
- Fits both standard round 1/4" KO (17/32" diameter) and 5/8" diameter KO with flats.
- Is furnished with 1/4-18 n.p.s. fixture nut for easy tightening.
- Is recommended for use with non-metallic sheathed cable, AC, flexible metal conduit, MC cable both steel and aluminum jacketed.
- Is primarily for use with low silhouette under-cabinet fluorescent fixtures.
- Normally only one fitting is supplied with lighting fixtures. Additional connectors are needed when multiple fixtures are wired in-line.



Twin Screw All-Purpose Connectors


For Flex • AC • MCI • NM cable.
Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| 4201 | 04201 | 1/2 | 1/2 | 25 | 250 | 1.535 | 1.139 | .610 | .630-810 | .615 |
| 4202 | 04202 | 3/4 | 3/4 | 20 | 200 | 1.528 | 1.276 | .814 | .830-1.090 | .820 |
| 4203 | 04203 | 1 | 1 | 10 | 50 | 1.726 | 1.605 | .985 | 1.00-1.365 | .985 |
| 4204 | 04204 | 1-1/4 | 1-1/4 | 5 | 25 | 1.783 | 1.885 | 1.375 | 1.385-1.640 | 1.365 |

Refer to chart on page E-23 for a list of cable types.
Concrete tight when taped.

Add suffix "A" to catalog number for insulated throat.



Cable Connectors

AC • MCI • NM • SE.

Zinc die-cast.



840



8400



8401

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| 840‡ | 00840 | 1/2 | 100 | 1000 | .350 | .825 | 1.085 | .225-.612 | .400 x .580 |
| 8400‡ | 08400 | 1/2 | 100 | 1000 | .350 | .825 | 1.085 | .225-.612 | .400 |
| 8401 | 08401 | 1/2 | 100 | 1000 | .500 | .825 | 1.085 | .225-.612 | .375 |
| 8402 | 08402 | 3/4 | 50 | 500 | .533 | 1.093 | 1.386 | .525-.780 | .620 |
| 8403* | 08403 | 1 | 25 | 250 | .428 | 1.072 | 1.500 | .780-.980 | .840 |
| 8404* | 08404 | 1-1/4 | 10 | 100 | .490 | 1.144 | 1.872 | 1.050-1.345 | 1.030 |
| 8405* | 08405 | 1-1/2 | 10 | 50 | .625 | 1.357 | 2.120 | 1.410-1.633 | 1.390 |
| 8407* | 08407 | 2 | 10 | 50 | .652 | 1.434 | 2.594 | 1.640-2.040 | 1.750 |
| 8408* | 72166 | 2-1/2 | - | 10 | .968 | 1.965 | 3.235 | 1.950-2.480 | 1.924 |
| 8409* | 72168 | 3 | - | 5 | 1.125 | 2.180 | 3.890 | 2.420-3.070 | 2.390 |
| 8410* | 72170 | 3-1/2 | - | 5 | 1.125 | 2.284 | 4.392 | 2.860-3.600 | 2.830 |

*Listed for MC only. UL# E123751.

‡Also for MCI-A cable. Refer to page E-25 for cable ranges.



Refer to chart on page E-23 for a list of cable types.

Refer to E-9 for new MC cable connectors with our largest cable ranges.

Concrete tight when taped.



E123751 LR49636



SNAP-TITE®

Connectors

With spring steel clip. Zinc die-cast.

For NM • SE • MCI • MCI-A • Flex • AC

steel and aluminum jacketed cables.



840ST



8400ST

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| 840ST | 80070 | 3/8 | 1/2 | 100 | 1000 | .510 | .985 | .912 | .225-.612 | .400 X .580 |
| 8400ST | 80074 | 3/8 | 1/2 | 100 | 1000 | .510 | .985 | .912 | .225-.612 | .375 |

Refer to chart on page E-23 for a list of cable types.

Refer to chart on page E-25 for MCI-A cable ranges.

Concrete tight when taped.



SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

PATENTED.



E18304 LR49636

See Page E-1 for ring removal instructions



Cable Connectors

Zinc die-cast. For MCI-A • MC/HCF steel and aluminum cable • AC/HCF steel and aluminum cable • Flexible metal conduit steel and aluminum (regular and reduced wall) • MCI cable • Continuous corrugated aluminum • AC90 • TECK90.



FEATURES AND BENEFITS


- Low cost – saves time and money!
- Fast and Easy to install. There's no need to remove the strap...just loosen the screws and insert the bushing that works best with the cables you're installing.
- Our zinc die-cast fittings cost much less than steel or malleable iron fittings
- Reduces inventory – comes with additional end stop bushings!
- Built-in end stop in fitting

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| 8412 | 08412 | 1 | 1 | 20 | 20 | 1.756 | .541 | 2.144 |
| 8413 | 08413 | 1-1/4 | 1-1/4 | 20 | 20 | 2.156 | .683 | 2.568 |
| 8414 | 08414 | 1-1/2 | 1-1/2 | 10 | 10 | 2.466 | .790 | 3.086 |
| 8415 | 00583 | 2 | 2 | 10 | 10 | 2.899 | .792 | 3.696 |
| 8416 | 08416 | 2-1/2 | 2-1/2 | 5 | 5 | 3.218 | .906 | 4.250 |
| 8417 | 08417 | 3 | 3 | 5 | 5 | 3.281 | .972 | 5.000 |

Refer to chart on page E-22 for a list of cable types.

Concrete tight when taped.


PATENT PENDING.



| Catalog Number | Cable Outer Diameter | | Wire Bundle Outer Diameter | | Throat Diameter Fitting/Bushings (A,B,C) | | | | Conductor Size # of Conductors* (AWG/KCMIL) |
|----------------|----------------------|-------|----------------------------|-------|--|-------|-------|-------|---|
| | Min. | Max. | Min. | Max. | Fitting | A | B | C | |
| 8412 | .780 | 1.120 | .660 | 1.000 | 1.018 | .625 | .750 | .870 | 6/3, 6/4, 4-3, 4-4, 2-3, 2-4, 1-3 |
| 8413 | 1.000 | 1.460 | .870 | 1.370 | 1.361 | .782 | 1.032 | 1.132 | 2-3, 2-4, 1-3, 1-4, 1/0-3, 1/0-4, 2/0-3, 2/0-4, 3/0-3 |
| 8414 | 1.360 | 1.770 | 1.250 | 1.590 | 1.587 | 1.175 | 1.277 | 1.382 | 2/0-4, 3/0-3, 3/0-4, 4/0-3, 4/0-4, 250-3, 250-4 |
| 8415 | 1.700 | 2.200 | 1.550 | 2.050 | 2.060 | 1.562 | 1.750 | 1.875 | 250-4, 300-4, 350-3, 350-4, 500-3 |
| 8416 | 2.100 | 2.700 | 1.950 | 2.400 | 2.462 | 1.979 | 2.194 | - | 500-3, 500-4, 600-3, 600-4, 750-3 |
| 8417 | 2.500 | 3.300 | 2.350 | 3.000 | 3.081 | 2.404 | 2.662 | - | 600-4, 750-3, 750-4 |

* Examples of 3- and 4-conductor cables. Cable dimensions vary dramatically between manufacturers. It is recommended that cable O.D. (outer diameter) be measured to ensure proper cable-to-fitting installation.

Each fitting has an end stop, but comes with additional end stop bushings to accommodate several cable sizes!




Installation Instructions



If you are using an end stop bushing, determine which one to use by sizing it to the cable bundle (not the metal jacket). **Incorrect size shown above.** The metal jacket should never go through the end stop.



Insert the appropriate end stop bushing, making sure that the half-moon shape is positioned at the top of the connector.



No need to remove strap – simply loosen the screws and insert end stop bushing, if necessary. Slip connector onto MC cable. Retighten screws on strap.

Squeeze Connectors

For Flex • AC • MCI cable.
Zinc die-cast.



L42



L421



L427

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| L42 | 34200 | 3/8 | 1/2 | 50 | 500 | .937 | .460 | 1.155 | .530-.620 | .400 |
| L420* | 34021 | 3/8 | 1/2 | 50 | 500 | 1.032 | .460 | 1.155 | .530-.620 | .400 x .580 |
| L421 | 34210 | 1/2 | 1/2 | 25 | 250 | 1.439 | .420 | 1.420 | .850-.910 | .620 |
| L422 | 34220 | 3/4 | 3/4 | 25 | 250 | 1.555 | .440 | 1.570 | 1.100-1.135 | .820 |
| L423 | 34230 | 1 | 1 | 10 | 100 | 1.770 | .560 | 1.860 | 1.255-1.375 | .940 |
| L424 | 34240 | 1-1/4 | 1-1/4 | 5 | 50 | 1.910 | .630 | 2.240 | 1.550-1.610 | 1.240 |
| L425 | 34250 | 1-1/2 | 1-1/2 | 5 | 50 | 2.125 | .610 | 2.640 | 1.810-1.895 | 1.460 |
| L426 | 34260 | 2 | 2 | 5 | 30 | 2.550 | .690 | 3.155 | 2.260-2.485 | 1.935 |
| L427 | 34270 | 2-1/2 | 2-1/2 | 5 | 5 | 2.890 | .890 | 3.810 | 2.770-2.950 | 2.440 |
| L428 | 34280 | 3 | 3 | 1 | 6 | 3.870 | .985 | 4.320 | 3.170-3.560 | 2.980 |
| L429 | 34290 | 3-1/2 | 3-1/2 | 1 | 6 | 4.265 | 1.000 | 4.860 | 3.630-4.155 | 3.478 |
| L4210 | 34211 | 4 | 4 | 1 | 6 | 4.560 | 1.000 | 5.415 | 4.030-4.635 | 3.977 |

*L420 not listed for flexible metal conduit.

Refer to chart on page E-24 for a list of cable types.

Concrete tight when taped.

Refer to E-8 for new MC cable connectors with our largest cable ranges.




E60812 LR49636




L420



L42



Sizes 3/8" - 2" are manufactured as shown above.



Sizes 2-1/2" - 4" are manufactured as shown above.

Squeeze Connectors with Insulated Throat

For Flex • AC • MCI cable.
Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| L421A | 34212 | 1/2 | 1/2 | 25 | 250 | 1.500 | .451 | 1.420 | .850-.910 | .620 |
| L422A | 34213 | 3/4 | 3/4 | 25 | 250 | 1.586 | .471 | 1.570 | 1.100-1.135 | .820 |
| L423A | 34214 | 1 | 1 | 10 | 100 | 1.800 | .591 | 1.860 | 1.255-1.375 | .940 |
| L424A | 34215 | 1-1/4 | 1-1/4 | 5 | 50 | 1.972 | .692 | 2.240 | 1.550-1.610 | 1.240 |
| L425A | 34216 | 1-1/2 | 1-1/2 | 5 | 50 | 2.187 | .672 | 2.640 | 1.810-1.895 | 1.460 |
| L426A | 34217 | 2 | 2 | 5 | 30 | 2.612 | .752 | 3.155 | 2.260-2.485 | 1.935 |
| L427A | 42700 | 2-1/2 | 2-1/2 | 5 | 5 | 2.983 | .983 | 3.810 | 2.770-2.950 | 2.440 |
| L428A | 42800 | 3 | 3 | 1 | 6 | 3.963 | 1.078 | 4.320 | 3.170-3.560 | 2.980 |
| L429A | 42900 | 3-1/2 | 3-1/2 | 1 | 6 | 4.358 | 1.093 | 4.860 | 3.630-4.155 | 3.478 |
| L4210A | 42100 | 4 | 4 | 1 | 6 | 4.653 | 1.093 | 5.415 | 4.030-4.635 | 3.977 |

Refer to chart on page E-24 for a list of cable types.


Concrete tight when taped.



E60812 LR49636



Sizes 3/8" - 2" are manufactured as shown above.



Sizes 2-1/2" - 4" are manufactured as shown above.


Duplex Connector

Zinc die-cast. Single screw for Flex • AC • MCI • MCI-A • NM cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|-------------|
| 846 | 00846 | 3/8 | 1/2 | 25 | 250 | 1.542 | .437 | .888 | 1.672 | .150-612 |

Refer to chart on page E-22 for a list of cable types.
Refer to chart on page E-25 for MCI-A cable ranges.
Concrete tight when taped.



Duplex SNAP-TITE® Connectors

Zinc die-cast. Single screw for Flex • AC • MCI • MCI-A • NM cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|-------------|
| 846ST‡ | 80050 | 3/8 | 1/2 | 25 | 250 | 1.635 | .510 | .888 | 1.654 | .150-612 |
| 846AST* | 80052 | 3/8 | 1/2 | 25 | 250 | 1.728 | .603 | .888 | 1.654 | .150-612 |

*Provided with insulated throat.

‡Also for MCI-A cable.


Refer to page E-22 for cable ranges.

Refer to chart on page E-25 for a list of cable types.
SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.
Concrete tight when taped.

PATENTED.



See Page E-1 for ring removal instructions




Duplex Connector

Twin screw with steel strap.
Zinc die-cast. For Flex • NM • AC • MCI steel and aluminum jacketed cables.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|-------------|
| 846SS | 80054 | 3/8 | 1/2 | 25 | 250 | 1.562 | .437 | .888 | 2.200 | .210-612 |

Refer to chart on page E-22 for a list of cable types.
Concrete tight when taped.



90° Duplex Connector

Zinc die-cast. Twin screw for Flex • NM • AC • MCI steel and aluminum jacketed cables • MCI-A cable.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|-------------|
| 84690 | 00090 | 3/8 | 1/2 | 10 | 100 | 1.087 | 1.707 | 1.965 | .379 | .512-.612 |

Refer to chart on page E-22 for a list of cable types.

Refer to chart on page E-25 for MCI-A cable ranges.

Concrete tight when taped.



90° Duplex SNAP-TITE® Connector

Zinc die-cast. Twin screw for NM • Flex • AC • MCI steel and aluminum jacketed cables • MCI-A cable.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|-------------|
| 84690ST | 58230 | 3/8 | 1/2 | 10 | 100 | 1.087 | 1.707 | 1.965 | .458 | .512-.612 |

Refer to chart on page E-22 for a list of cable types.


Refer to chart on page E-25 for MCI-A cable ranges.

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

Concrete tight when taped.



See Page E-1 for ring removal instructions



Set-Screw Connectors


For Flex • AC • MCI cable.
Zinc die-cast. Not for use with aluminum jacketed cables.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| L48 | 34800 | 1/2 | 1/2 | 25 | 250 | 1.470 | .450 | 1.260 | .625-.915 | .620 |
| L49 | 34900 | 3/4 | 3/4 | 20 | 200 | 1.540 | .450 | 1.500 | .820-.910 | .815 |

Refer to chart on page E-23 for a list of cable types.

Concrete tight when taped.



Duplex SADDLEGRIP® SNAP-TITE® Connectors

Zinc die-cast. For aluminum and steel Flex • AC • AC90 • MCI • MCI-A cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|---------------|
| SG3838ST | 80152 | 3/8 | 1/2 | 25 | 100 | .455 | 1.610 | .780 | (2) .445-.612 |
| SG3838AST* | 36210 | 3/8 | 1/2 | 25 | 100 | .605 | 1.560 | .780 | (2) .445-.612 |

*Provided with insulated throat.

With independent securing of the cables, you can use two different size cables.

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

Refer to chart on page E-23 for a list of cable types.


Refer to chart on page E-25 for MCI-A cable ranges.

Concrete tight when taped.

PATENTED.



See Page E-1 for ring removal instructions



Duplex SADDLEGRIP® Connectors

Zinc die-cast. For aluminum and steel Flex • AC • AC90 • MCI • MCI-A cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|---------------|
| SG3838 | 17383 | 3/8 | 1/2 | 25 | 100 | .452 | 1.526 | .780 | (2) .445-.612 |
| SG3838A* | 36205 | 3/8 | 1/2 | 25 | 100 | .512 | 1.586 | .780 | (2) .445-.612 |


*Provided with insulated throat.

Refer to chart on page E-23 for a list of cable types.

Refer to chart on page E-25 for MCI-A cable ranges.

Concrete tight when taped.

With independent securing of the cables, you can use two different size cables.



"Take All" Connectors

Single screw saddle type.

For NM • Flex • AC • AC90 • MCI steel and aluminum jacketed cables • ACG90 • Teck90. Zinc die-cast.



L15A

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|---------------|-------------------|
| L15A* | 80040 | 3/8 | 1/2 | 50 | 500 | .984 | .420 | 1.032 | .460 - .585 | .340 x .430 |
| L16†‡ | 80060 | 3/8 | 1/2 | 50 | 500 | .923 | .375 | 1.208 | .405 - .650 | .400 x .580 |
| L160‡ | 02416 | 3/8 | 1/2 | 50 | 500 | .954 | .412 | 1.092 | .370 - .690 | .312 |
| L17 | 34278 | 1/2 | 1/2 | 50 | 250 | 1.500 | .462 | 1.416 | .630 - .890 | .620 |
| L18 | 34282 | 3/4 | 3/4 | 25 | 125 | 1.400 | .390 | 1.750 | .820 - 1.040 | .818 |
| L19 | 34287 | 1 | 1 | 25 | 125 | 1.640 | .443 | 2.048 | 1.100 - 1.400 | 1.030 |

*Provided with insulated throat.

†Listed for flexible cord.


‡Also for MCI-A cable. Refer to page E-25 for cable ranges.

Refer to chart on page E-22 for a list of cable types.

Concrete tight when taped.



PATENTED. ADDITIONAL PATENTS PENDING.



L16

SADDLEGRIP® SNAP-TITE®

Connectors

For aluminum and steel
Flex • AC • AC90 • MCI • MCI-A
cable. Zinc die-cast.



SG38AST



SG380AST

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| SG38AST*‡ | 80144 | 3/8 | 1/2 | 50 | 500 | 1.203 | .555 | 1.077 | .405-.612 | .400 |
| SG380AST*‡ | 80148 | 3/8 | 1/2 | 50 | 500 | 1.145 | .555 | 1.077 | .405-.612 | .400 x .580 |
| SG50ST‡ | 80150 | 1/2 | 1/2 | 50 | 500 | 1.458 | .510 | 1.235 | .710-.910 | .620 |
| SG50AST*‡ | 17501 | 1/2 | 1/2 | 50 | 500 | 1.145 | .555 | 1.277 | .710-.910 | .620 |
| SG75ST | 18080 | 3/4 | 3/4 | 20 | 200 | 1.495 | .510 | 1.570 | .840-1.110 | .820 |
| SG75AST* | 17755 | 3/4 | 3/4 | 20 | 200 | 1.540 | .55 | 1.570 | .840-1.110 | .820 |

*Provided with insulated throat.

‡Also for MCI-A cable. Refer to page E-25 for cable ranges.

Refer to chart on page E-23 for a list of cable types.

For cables smaller than .405" see L16 on page E-12 and L16ST on page E-4.


SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 6.

Concrete tight when taped.

PATENTED.



See Page E-1 for ring removal instructions



SADDLEGRIP® Connectors

For aluminum and steel
Flex • AC • AC90 • MCI • MCI-A cable.
Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| SG38‡ | 18065 | 3/8 | 1/2 | 50 | 500 | 1.000 | .400 | 1.077 | .405-.612 | .400 |
| SG38A*‡ | 80138 | 3/8 | 1/2 | 50 | 500 | 1.090 | .490 | 1.077 | .405-.612 | .400 |
| SG380‡ | 18060 | 3/8 | 1/2 | 50 | 500 | 1.000 | .400 | 1.077 | .405-.612 | .400 x .580 |
| SG380A*‡ | 80140 | 3/8 | 1/2 | 50 | 500 | 1.090 | .490 | 1.077 | .405-.612 | .400 x .580 |
| SG40‡ | 01740 | 7/16 | 1/2 | 50 | 500 | 1.480 | .480 | 1.125 | .530-.790 | .620 |
| SG50‡ | 07500 | 1/2 | 1/2 | 50 | 500 | 1.480 | .480 | 1.277 | .710-.910 | .620 |
| SG50A*‡ | 37501 | 1/2 | 1/2 | 50 | 500 | 1.511 | .511 | 1.277 | .710-.910 | .620 |
| SG75 | 18075 | 3/4 | 3/4 | 20 | 200 | 1.435 | .450 | 1.470 | .840-1.110 | .820 |
| SG75A* | 17751 | 3/4 | 3/4 | 20 | 200 | 1.466 | .481 | 1.470 | .840-1.110 | .820 |


*Provided with insulated throat.

‡Also for MCI-A cable. Refer to page E-25 for cable ranges.

Refer to chart on page E-23 for a list of cable types.

Concrete tight when taped.

For cables smaller than .405" see L16 on page E-12 and L16ST on page E-4.



45° Connectors

Zinc die-cast. For aluminum and steel Flex • AC • MCI cable.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| 4501 | 04501 | 3/8 | 1/2 | 50 | 500 | .382 | 1.132 | 1.588 | .445-.612 | .620 |
| 4502 | 04502 | 1/2 | 1/2 | 25 | 250 | .382 | 1.150 | 1.775 | .620-.895 | .635 |

Refer to chart on page E-23 for a list of cable types.

Concrete tight when taped.



E60812 LR49636



45° SNAP-TITE® Connectors

Zinc die-cast. With spring steel clip. For aluminum and steel Flex • AC • MCI cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE | END STOP DIAMETER |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|-------------------|
| 4501ST | 06002 | 3/8 | 1/2 | 50 | 500 | .382 | 1.132 | 1.588 | .445-.612 | .620 |
| 4502ST | 06004 | 1/2 | 1/2 | 25 | 250 | .382 | 1.150 | 1.775 | .620-.895 | .635 |

Refer to chart on page E-23 for a list of cable types.

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.


Concrete tight when taped.

PATENTED.



E60812 LR49636

See Page E-1 for ring removal instructions



90° SNAP-TITE® Connectors

Zinc die-cast. With spring steel clip. For aluminum and steel Flex • AC • AC90 • MCI cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 850ST | 80154 | 3/8 | 1/2 | 50 | 500 | 1.540 | .430 | 1.800 | .440-.750 |
| 850AST* | 80156 | 3/8 | 1/2 | 50 | 500 | 1.600 | .490 | 1.775 | .440-.750 |
| 851ST‡ | 80158 | 1/2 | 1/2 | 25 | 250 | 1.600 | .430 | 2.140 | .642-1.075 |
| 851AST*‡ | 80160 | 1/2 | 1/2 | 25 | 250 | 1.651 | .490 | 2.145 | .648-1.081 |

*Provided with insulated throat.

‡Also for MCI-A cable. Refer to page E-25 for cable ranges.

Refer to chart on page E-24 for a list of cable types.

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.


Concrete tight when taped.

PATENTED.



372D LR49636

See Page E-1 for ring removal instructions



90° Connectors

Zinc die-cast. For aluminum and steel Flex • AC • AC90 • MCI • MCI-A cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 85‡ | 00893 | 3/8 | 1/2 | 50 | 500 | 1.370 | .340 | 1.800 | .370-.510 |
| 85A* | 12510 | 3/8 | 1/2 | 50 | 500 | 1.432 | .400 | 1.800 | .370-.510 |


*Provided with insulated throat.

‡Also for MCI-A cable. Refer to page E-25 for cable ranges.

Refer to chart on page E-24 for a list of cable types.

Concrete tight when taped.

PATENTED.



90° SNAP-TITE® Connectors

Zinc die-cast. With spring steel clip. For aluminum and steel Flex • AC • AC90 • MCI • MCI-A cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------------|
| 85ST‡ | 00894 | 3/8 | 1/2 | 50 | 500 | 1.540 | .430 | 1.800 | .370-.510 |
| 85AST* | 12511 | 3/8 | 1/2 | 50 | 500 | 1.600 | .490 | 1.800 | .370-.510 |

*Provided with insulated throat.

‡Also for MCI-A cable. Refer to page E-25 for cable ranges.

Refer to chart on page E-24 for a list of cable types.


SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

Concrete tight when taped.

PATENTED.



See Page E-1 for ring removal instructions




Screw-On Snap-In Connectors

Spring steel clip with non-metallic body. Screws onto 3/8" Flex.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|
| GFSC38 | 20737 | 3/8 | 1/2 | 50 | 500 | 1.005 | .785 |
| GFSC38B | 20739 | 3/8 | 1/2 | - | 1000 | 1.005 | .785 |

For flexible metal conduit only.



Snaps into KO with 50% less force!

90° Connectors

Zinc die-cast. For aluminum and steel Flex • AC • AC90 • MCI • MCI-A cable.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|--------|-------------|
| 850† | 00850 | 3/8 | 1/2 | 50 | 500 | 1.370 | .340 | 1.800 | 440-750 |
| 851† | 00851 | 1/2 | 1/2 | 25 | 250 | 1.780 | .410 | 2.140 | 635-1.085 |
| 852 | 00852 | 3/4 | 3/4 | 15 | 150 | 2.065 | .500 | 2.346 | 830-1.085 |
| 853 | 00853 | 1 | 1 | 10 | 50 | 2.560 | .500 | 2.896 | 1.330-1.570 |
| 854 | 00854 | 1-1/4 | 1-1/4 | 5 | 25 | 2.812 | .500 | 3.080 | 1.625-1.940 |
| 855 | 00855 | 1-1/2 | 1-1/2 | 1 | 10 | 4.875 | .750 | 6.050 | 1.400-2.400 |
| 856 | 00856 | 2 | 2 | 1 | 10 | 4.875 | .750 | 6.050 | 1.400-2.400 |
| 857† | 00857 | 2-1/2 | 2-1/2 | 1 | 1 | 6.125 | .875 | 7.187 | 2.600-3.100 |
| 858† | 00858 | 3 | 3 | 1 | 1 | 6.700 | 1.031 | 7.875 | 3.100-3.640 |
| 859† | 00859 | 3-1/2 | 3-1/2 | 1 | 1 | 7.500 | 1.031 | 9.400 | 3.380-4.220 |
| 8510† | 08510 | 4 | 4 | 1 | 1 | 8.700 | 1.031 | 10.200 | 3.730-4.550 |

†Malleable.

‡Also for MCI-A cable. Refer to page E-25 for cable ranges.

Refer to chart on page E-24 for a list of cable types.

Concrete tight when taped.



90° Connectors with Insulated Throat

Zinc die-cast. For aluminum and steel Flex • AC • AC90 • MC • MCI-A cable.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|--------|-------------|
| 850A† | 85010 | 3/8 | 1/2 | 50 | 500 | 1.432 | .400 | 1.800 | 440-750 |
| 851A† | 85110 | 1/2 | 1/2 | 25 | 250 | 1.510 | .400 | 2.260 | 635-1.085 |
| 852A | 85210 | 3/4 | 3/4 | 15 | 150 | 2.096 | .531 | 2.380 | 830-1.085 |
| 853A | 85310 | 1 | 1 | 10 | 50 | 2.622 | .687 | 2.080 | 1.330-1.570 |
| 854A | 85410 | 1-1/4 | 1-1/4 | 5 | 25 | 3.222 | .687 | 3.080 | 1.625-1.940 |
| 855A | 85510 | 1-1/2 | 1-1/2 | 1 | 10 | 4.968 | .843 | 6.050 | 1.400-2.400 |
| 856A | 85610 | 2 | 2 | 1 | 10 | 4.968 | .843 | 6.050 | 1.400-2.400 |
| 857A† | 08571 | 2-1/2 | 2-1/2 | 1 | 1 | 6.218 | .968 | 7.187 | 2.600-3.100 |
| 858A† | 08581 | 3 | 3 | 1 | 1 | 6.793 | 1.125 | 7.875 | 3.100-3.640 |
| 859A† | 08591 | 3-1/2 | 3-1/2 | 1 | 1 | 8.810 | 1.125 | 9.400 | 3.380-4.220 |
| 8510A† | 85101 | 4 | 4 | 1 | 1 | 8.793 | 1.125 | 10.200 | 3.730-4.550 |

†Malleable.

‡Also for MCI-A cable. Refer to page E-25 for cable ranges.

Refer to chart on page E-24 for a list of cable types.

Concrete tight when taped.




Screw-In Connectors

For flexible metal conduit.
Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| GF38 | 76380 | 3/8 | 1/2 | 50 | 500 | 1.340 | .470 | 1.140 |
| GF50 | 76500 | 1/2 | 1/2 | 50 | 250 | 1.340 | .710 | 1.140 |
| GF75 | 76750 | 3/4 | 3/4 | 25 | 250 | 1.565 | .930 | 1.390 |
| GF100 | 76100 | 1 | 1 | 25 | 100 | 1.700 | 1.125 | 1.580 |
| GF125 | 76125 | 1-1/4 | 1-1/4 | 10 | 40 | 2.120 | 1.410 | 2.115 |
| GF150 | 76150 | 1-1/2 | 1-1/2 | 10 | 40 | 2.406 | 1.695 | 2.370 |
| GF200 | 76200 | 2 | 2 | 5 | 20 | 2.570 | 2.190 | 2.890 |




Screw-In Coupling

For flexible metal conduit.
Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| GFC50 | 76350 | 1/2 | 25 | 250 | 2.200 | 1.160 |
| GFC75 | 76375 | 3/4 | 25 | 250 | 2.200 | 2.200 |
| GFC100 | 76340 | 1 | 10 | 100 | 2.312 | 1.406 |
| GFC125 | 76360 | 1-1/4 | 10 | 100 | 3.125 | 2.125 |
| GFC150 | 76370 | 1-1/2 | 5 | 50 | 3.186 | 2.375 |
| GFC200 | 76372 | 2 | 3 | 30 | 4.125 | 2.937 |




Screw-In Connectors with Insulated Throat

For flexible metal conduit.
Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| GF38A | 76381 | 3/8 | 1/2 | 50 | 500 | 1.371 | .470 | 1.140 |
| GF50A | 76501 | 1/2 | 1/2 | 50 | 250 | 1.450 | .710 | 1.140 |
| GF75A | 76751 | 3/4 | 3/4 | 25 | 250 | 1.596 | .930 | 1.390 |
| GF100A | 76101 | 1 | 1 | 25 | 100 | 1.992 | 1.125 | 1.685 |
| GF125A | 76251 | 1-1/4 | 1-1/4 | 10 | 40 | 2.182 | 1.410 | 2.115 |
| GF150A | 76151 | 1-1/2 | 1-1/2 | 10 | 40 | 2.372 | 1.695 | 2.370 |
| GF200A | 76201 | 2 | 2 | 5 | 20 | 2.663 | 2.190 | 2.890 |



Screw-In SNAP-TITE® Connectors

With spring steel clip. For flexible metal conduit. Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| GF38ST | 80162 | 3/8 | 1/2 | 50 | 500 | 1.470 | .475 | 1.055 |
| GF50ST | 80166 | 1/2 | 1/2 | 50 | 250 | 1.468 | .720 | 1.055 |
| GF75ST | 80170 | 3/4 | 3/4 | 25 | 250 | 1.694 | .940 | 1.350 |

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

PATENTED.



See Page E-1 for ring removal instructions



Screw-In SNAP-TITE® Connectors with Insulated Throat

With spring steel clip. For flexible metal conduit. Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| GF38AST | 80164 | 3/8 | 1/2 | 50 | 500 | 1.456 | .480 | 1.045 |
| GF50AST | 80168 | 1/2 | 1/2 | 50 | 250 | 1.456 | .727 | 1.045 |

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

PATENTED.



See Page E-1 for ring removal instructions




Combination Coupling

EMT to Flex. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------------|
| 860* | 00860 | 1/2 | 3/8 | 50 | 500 | 1.280 | 1.140 | .530-.620 |
| 861 | 00861 | 1/2 | 1/2 | 25 | 250 | 1.645 | 1.340 | .850-910 |
| 862 | 00862 | 3/4 | 3/4 | 25 | 100 | 1.975 | 1.535 | 1.100-1.130 |

*CSA only.




Combination Coupling

EMT set-screw to Flex. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | CABLE RANGE |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------------|
| 8610 | 08610 | 1/2 | 1/2 | 50 | 500 | 1.736 | 1.242 | .850-910 |
| 8620 | 08620 | 3/4 | 3/4 | 25 | 100 | 1.934 | 1.242 | 1.100-1.135 |
| 8630 | 08630 | 1 | 1 | 10 | 40 | 2.285 | 1.700 | 1.255-1.375 |




Combination Coupling

EMT compression to flexible metal conduit. Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|-------|
| GF860 | 76860 | 1/2 | 3/8 | 25 | 100 | 1.535 | .445 | .725 | 1.060 |
| GF861 | 76861 | 1/2 | 1/2 | 25 | 250 | 1.345 | .715 | .725 | 1.060 |
| GF862 | 76862 | 3/4 | 3/4 | 25 | 250 | 1.700 | .935 | .935 | 1.305 |
| GF863 | 80173 | 1 | 1 | 25 | 100 | 1.895 | 1.125 | 1.070 | 1.625 |




Anti-Short Bushings

Plastic.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CABLE SIZES | STD PKG | DIM A | DIM B |
|----------------|--------------------------|-------------|--|---------|-------|-------|
| AS0 | 10500 | 5/16" | 14/2, 14/3, 12/2 | 100/BAG | .590 | .680 |
| AS1 | 10510 | 3/8" | 14/4, 12/3, 6/1, 4/1 | 100/BAG | .630 | .758 |
| AS2 | 10520 | 7/16" | 12/4, 10/2, 10/3, 2/1 | 50/BAG | .680 | .920 |
| AS3 | 10530 | 1/2" | 10/4, 8/2, 8/3, 1/1 | 50/BAG | .770 | 1.130 |
| AS4 | 10540 | 3/4" | 8/4, 6/2, 6/3, 6/4, 4/2, 4/3 | 50/BAG | .880 | 1.340 |
| AS5 | 06052 | 1" | 3-1, 2-1, 2-1/10, 1-300MCM, 1-50MCM, 1-400MCM, 1-450MCM, 1-500MCM | 25/BAG | 1.038 | 1.460 |
| AS6 | 06054 | 1-1/4" | 4-1, 4-1/10, 4-2/0, 3-1/0, 3-2/0, 3-3/0, 2-2/0, 2-3/0, 2-4/0, 1-600MCM, 1-650MCM, 1-700MCM, 1-750MCM, 1-800MCM, 1-900MCM | 10/BAG | 1.100 | 1.720 |
| AS7 | 06056 | 1-1/2" | 4-3/0, 4-4/0, 3-4/0, 3-250MCM, 3-300MCM, 2-250MCM, 2-300MCM, 2-350MCM, 1-1000MCM | 10/BAG | 1.162 | 2.175 |
| AS8 | 06058 | 2 TO 2-1/2" | 4-250MCM, 4-300MCM, 4-350MCM, 4-400MCM, 4-450MCM, 4-500MCM, 3-350MCM, 3-400MCM, 3-450MCM, 3-500MCM, 2-400MCM, 2-450MCM, 2-500MCM | 10/BAG | 1.330 | 2.625 |



1-Hole AC/MC Strap

Plated steel.




310




311

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | CABLE RANGE | CABLE SIZES | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|--|----------|---------|-------|-------|-------|
| 310 | 00310 | .503-.580 | 14/4, 14/3, 12/4, 12/3, 10/3, 10/2, 12/2 | 100 | 1000 | 1.285 | .550 | .750 |
| 311 | 84174 | .200-.320 | #4 and #2 bare copper | 100 | 1000 | 1.125 | .210 | .500 |




90° Connectors

For flexible metal conduit. Screw in type with sliding cover. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|
| GF850 | 85000 | 1/2 | 1/2 | 25 | 100 | 1.975 | 1.820 |



90° SNAP-TITE® Connectors

With spring steel clip. For flexible metal conduit. Screw-in type with sliding cover. Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|
| GF850ST | 84850 | 1/2 | 1/2 | 25 | 100 | 1.969 | 1.969 |

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 7.

PATENTED.



See Page E-1 for ring removal instructions



Stackable AC/MC/ Flex Cable Strap

Holds AC • MCI • Flex cable securely centered on wood or metal studs...14/2, 14/3, 14/4, 12/2, 12/3, 12/4, 10/2, 10/3.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | CABLE RANGE |
|----------------|--------------------------|----------|---------|-------|-------|-------|-------------|
| NM310 | 54010 | 100 | 1000 | 1.345 | 1.224 | .750 | .420-.600 |

PATENTED.



Screw to the stud, then add as many as you need!



The easy to use 'Stackable' Cable Strap holds up to 5 runs of cable!

- Meets 2014 NEC Codes 320.30, 330.30, and 348.30
- Meets requirements of proposed UL standard 2239 for support of conduit and cable
- Includes screw for attaching to wood or metal studs
- Listed for use in environmental air handling spaces per 2014 NEC code requirement 300.22(c).

Listed for support, not just positioning!

Cable Types and Ranges

| Style | Part Number (ST = Snap-Tite®) | Knock-Out Size | ACG90 | AC90 | TECK90 | Outer Armor Diameter Flex • A/C • M/C | Throat Diameter | Number of Cables | Insulated Throat | Flexible Metal Conduit (FMC) | | | | Armored Cable (A/C) | | Metal Clad Cable (M/C) | | A/C M/C | |
|--------------------------------------|-------------------------------|----------------|---------------|---------------|--|--|-----------------|------------------|------------------|------------------------------|----------|--------------------|-----------------------|---------------------|----------|------------------------|---------------------|---------|--------------------------------|
| | | | | | | | | | | Steel | Aluminum | Reduced Wall Steel | Reduced Wall Aluminum | Steel | Aluminum | Steel | Aluminum Corrugated | | Aluminum Continuous Corrugated |
| SNAP2IT® Connectors (Push-In Type) | 38A | 1/2 | | | | 0.405 - 0.605 | 0.405 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 38AST | 1/2 | | 0.450 - 0.550 | | 0.405 - 0.605 | 0.405 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 380ST | 1/2 | | | | 0.405 - 0.605 | 0.400 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 380AST | 1/2 | | | | 0.405 - 0.605 | 0.400 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 3810AST | 1/2 | 0.460 - 0.480 | 0.450 - 0.480 | | 0.370 - 0.510 | 0.316 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 3838ST | 1/2 | | 0.450 - 0.550 | | 0.405 - 0.605 | 0.620 | 2 | • | • | • | • | • | • | • | • | • | • | |
| | 3838AST | 1/2 | | | | 0.405 - 0.605 | 0.620 | 2 | • | • | • | • | • | • | • | • | • | • | |
| | 3890AST | 1/2 | | | | 0.405 - 0.605 | 0.405 | 1 | • | • | • | • | • | • | • | • | • | • | • |
| | 383810AST | 1/2 | 0.460 - 0.480 | 0.450 - 0.550 | | 0.370 - 0.510 | 0.624 | 2 | • | • | • | • | • | • | • | • | • | • | • |
| | 40AST | 1/2 | | 0.480 - 0.550 | | 0.485 - 0.610 | 0.405 | 1 | • | • | • | • | • | • | • | • | • | • | • |
| | 400AST | 1/2 | | | | 0.485 - 0.610 | 0.400 | 1 | • | • | • | • | • | • | • | • | • | • | • |
| | 4010AST | 1/2 | 0.460 - 0.505 | 0.450 - 0.550 | | 0.405 - 0.610 | 0.404 | 1 | • | • | • | • | • | • | • | • | • | • | • |
| | 4040AST | 1/2 | | 0.480 - 0.550 | | 0.485 - 0.610 | 0.620 | 2 | • | • | • | • | • | • | • | • | • | • | • |
| | 4090AST | 1/2 | | | | 0.485 - 0.610 | 0.405 | 1 | • | • | • | • | • | • | • | • | • | • | • |
| | 404010AST | 1/2 | 0.460 - 0.505 | 0.450 - 0.550 | | 0.405 - 0.610 | 0.624 | 2 | • | • | • | • | • | • | • | • | • | • | • |
| | 5010AST | 1/2 | | 0.550 - 0.850 | | 0.590 - 0.920 | 0.614 | 1 | • | • | • | • | • | • | • | • | • | • | • |
| | 5090AST | 1/2 | | | | 0.860 - 0.920 | 0.405 | 1 | • | • | • | • | • | • | • | • | • | • | • |
| 505010AST | 3/4 | | 0.650 - 0.850 | | 0.590 - 0.920 | 0.810 | 2 | • | • | • | • | • | • | • | • | • | • | • | |
| 7510AST | 3/4 | | 0.900 - 0.970 | | 0.895 - 1.110 | 0.828 | 1 | • | • | • | • | • | • | • | • | • | • | • | |
| Multi-End Stop Clamp Type Connectors | 8412 | 1 | | 0.850 - 0.980 | 0.850 - 0.990 | 0.780 - 1.120 | 0.625 - 1.018 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 8413 | 1-1/4 | | 0.850 - 0.980 | 0.990 - 1.350 | 1.000 - 1.460 | 0.782 - 1.361 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 8414 | 1-1/2 | | | 1.350 (4 Conductors) | 1.360 - 1.770 | 1.175 - 1.587 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 8415 | 2 | | | 1.650 (3 Conductors) 2.150 (3 Conductors) 2.250 (4 Conductors) | 1.700 - 2.200 | 1.562 - 2.060 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 8416 | 2-1/2 | | | 2.150 (3 Conductors) 2.250 (4 Conductors) 2.650 (3 Conductors) | 2.100 - 2.700 | 1.979 - 2.462 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | 8417 | 3 | | | 2.650 (3 Conductors) | 2.500 - 3.300 | 2.404 - 3.081 | 1 | • | • | • | • | • | • | • | • | • | • | |
| Clamp Type Two Cable Connectors | 846 | 1/2 | | | | 0.370 - 0.612 | 0.630 | 2 | • | • | • | • | • | • | • | • | • | • | |
| | 846ST | 1/2 | | | | 0.370 - 0.612 | 0.630 | 2 | • | • | • | • | • | • | • | • | • | • | |
| | 846AST | 1/2 | | | | 0.370 - 0.612 | 0.560 | 2 | • | • | • | • | • | • | • | • | • | • | |
| | 846SS | 1/2 | | | | 0.370 - 0.612 | 0.630 | 2 | • | • | • | • | • | • | • | • | • | • | |
| | 84690 | 1/2 | | | | 0.370 - 0.612 | 0.630 | 2 | • | • | • | • | • | • | • | • | • | • | |
| | 84690ST | 1/2 | | | | 0.370 - 0.612 | 0.630 | 2 | • | • | • | • | • | • | • | • | • | • | |
| | 84690AST | 1/2 | | | | 0.370 - 0.612 | 0.630 | 2 | • | • | • | • | • | • | • | • | • | • | |
| Single Screw Clamp Type | L15A | 1/2 | | | | 0.460 - 0.585 | 0.340 x 0.430 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L15AST | 1/2 | | 0.480 - 0.650 | | 0.460 - 0.585 | 0.340 x 0.510 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L16 | 1/2 | 0.480 - 0.600 | 0.480 - 0.650 | | 0.370 - 0.670 | 0.400 x 0.580 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L16ST | 1/2 | 0.480 - 0.600 | 0.480 - 0.650 | | 0.370 - 0.670 | 0.400 x 0.580 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L160 | 1/2 | | | | 0.370 - 0.510 | 0.312 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L160ST | 1/2 | | | | 0.370 - 0.510 | 0.312 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L17 | 1/2 | | 0.650 - 0.980 | 0.850 | 0.630 - 0.890 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L17ST | 1/2 | | 0.650 - 0.980 | 0.850 | 0.630 - 0.890 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L18 | 3/4 | | 0.890 - 0.980 | 0.990 | 0.820 - 1.040 | 0.818 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L18ST | 3/4 | | 0.890 - 0.980 | 0.990 | 0.820 - 1.040 | 0.818 | 1 | • | • | • | • | • | • | • | • | • | • | |
| | L19 | 1 | | | | 1.100 - 1.400 | 1.030 | 1 | • | • | • | • | • | • | • | • | • | • | |
| L19ST | 1 | | | | 1.100 - 1.400 | 1.030 | 1 | • | • | • | • | • | • | • | • | • | • | | |

Cable Types and Ranges

| Style | Part Number (ST = Snap-Tite®) | Knock-Out Size | ACC90 | AC90 | TECK90 | Outer Armor Diameter Flex • A/C • M/C | Throat Diameter | Number of Cables | Insulated Throat | Flexible Metal Conduit (FMC) | | | Armored Cable (A/C) | | Metal Clad Cable (M/C) | | A/C M/C |
|---------------------------------|-------------------------------|----------------|---------------|---------------|---------------|--|-----------------|------------------|------------------|------------------------------|----------|--------------------|-----------------------|-------|------------------------|-------|---------|
| | | | | | | | | | | Steel | Aluminum | Reduced Wall Steel | Reduced Wall Aluminum | Steel | Aluminum | Steel | |
| Straight SADDLEGRIP® Connectors | SG38 | 1/2 | | 0.450 - 0.550 | | 0.430 - 0.612 | 0.395 | 1 | • | • | • | • | • | • | • | • | • |
| | SG38A | 1/2 | | 0.450 - 0.550 | | 0.430 - 0.612 | 0.400 | 1 | • | • | • | • | • | • | • | • | • |
| | SG38AST | 1/2 | | 0.450 - 0.550 | | 0.430 - 0.612 | 0.400 | 1 | • | • | • | • | • | • | • | • | • |
| | SG380 | 1/2 | | | | 0.430 - 0.612 | 0.400 x 0.580 | 1 | • | • | • | • | • | • | • | • | • |
| | SG380A | 1/2 | | | | 0.430 - 0.612 | 0.340 x 0.510 | 1 | • | • | • | • | • | • | • | • | • |
| | SG380AST | 1/2 | | | | 0.430 - 0.612 | 0.340 x 0.510 | 1 | • | • | • | • | • | • | • | • | • |
| | SG40 | 1/2 | | | | 0.530 - 0.790 | 0.630 | 1 | • | • | • | • | • | • | • | • | • |
| | SG50 | 1/2 | | 0.850 | | 0.710 - 0.910 | 0.630 | 1 | • | • | • | • | • | • | • | • | • |
| | SG50A | 1/2 | | 0.850 | | 0.710 - 0.910 | 0.560 | 1 | • | • | • | • | • | • | • | • | • |
| | SG50ST | 1/2 | | 0.850 | | 0.710 - 0.910 | 0.630 | 1 | • | • | • | • | • | • | • | • | • |
| | SG50AST | 1/2 | | 0.850 | | 0.710 - 0.910 | 0.560 | 1 | • | • | • | • | • | • | • | • | • |
| | SG75 | 3/4 | | 0.900 - 0.970 | | 0.840 - 1.110 | 0.845 | 1 | • | • | • | • | • | • | • | • | • |
| | SG75A | 3/4 | | 0.900 - 0.970 | | 0.840 - 1.110 | 0.845 | 1 | • | • | • | • | • | • | • | • | • |
| | SG75ST | 3/4 | | 0.900 - 0.970 | | 0.840 - 1.110 | 0.845 | 1 | • | • | • | • | • | • | • | • | • |
| SG75AST | 3/4 | | 0.900 - 0.970 | | 0.840 - 1.110 | 0.765 | 1 | • | • | • | • | • | • | • | • | • | |
| Duplex SADDLEGRIP® Connectors | SG3838 | 1/2 | | 0.450 - 0.550 | | 0.430 - 0.612 | 0.630 | 2 | • | • | • | • | • | • | • | • | • |
| | SG3838A | 1/2 | | 0.450 - 0.550 | | 0.430 - 0.612 | 0.620 | 2 | • | • | • | • | • | • | • | • | • |
| | SG3838ST | 1/2 | | 0.450 - 0.550 | | 0.430 - 0.612 | 0.620 | 2 | • | • | • | • | • | • | • | • | • |
| | SG3838AST | 1/2 | | 0.450 - 0.550 | | 0.430 - 0.612 | 0.620 | 2 | • | • | • | • | • | • | • | • | • |
| Two Screw Clamp Type Connectors | 4200 | 1/4 | | | | 0.370 - 0.612 | 0.380 | 1 | • | • | • | • | • | • | • | • | • |
| | 4201 | 1/2 | | | | 0.630 - 0.810 | 0.615 | 1 | • | • | • | • | • | • | • | • | • |
| | 4202 | 3/4 | | | | 0.830 - 1.090 | 0.820 | 1 | • | • | • | • | • | • | • | • | • |
| | 4203 | 1 | | | | 1.000 - 1.365 | 0.985 | 1 | • | • | • | • | • | • | • | • | • |
| | 4204 | 1-1/4 | | | | 1.385 - 1.640 | 1.365 | 1 | • | • | • | • | • | • | • | • | • |
| | 4501 | 1/2 | | | | 0.445 - 0.612 | 0.620 | 1 | • | • | • | • | • | • | • | • | • |
| | 4501ST | 1/2 | | | | 0.445 - 0.612 | 0.620 | 1 | • | • | • | • | • | • | • | • | • |
| | 4502 | 1/2 | | | | 0.620 - 0.895 | 0.635 | 1 | • | • | • | • | • | • | • | • | • |
| | 4502ST | 1/2 | | | | 0.620 - 0.895 | 0.635 | 1 | • | • | • | • | • | • | • | • | • |
| | 840 | 1/2 | | | | 0.370 - 0.612 | 0.400 x 0.580 | 1 | • | • | • | • | • | • | • | • | • |
| | 840ST | 1/2 | | | | 0.370 - 0.612 | 0.400 x 0.580 | 1 | • | • | • | • | • | • | • | • | • |
| | 8400 | 1/2 | | | | 0.370 - 0.612 | 0.400 | 1 | • | • | • | • | • | • | • | • | • |
| | 8400ST | 1/2 | | | | 0.370 - 0.612 | 0.375 | 1 | • | • | • | • | • | • | • | • | • |
| | 8401 | 1/2 | | | | 0.410 - 0.612 | 0.375 | 1 | • | • | • | • | • | • | • | • | • |
| | 8402 | 3/4 | | | | 0.525 - 0.780 | 0.620 | 1 | • | • | • | • | • | • | • | • | • |
| | 8403 | 1 | | | | 0.790 - 0.980 | 0.840 | 1 | • | • | • | • | • | • | • | • | • |
| | 8404 | 1-1/4 | | | | 1.050 - 1.345 | 1.030 | 1 | • | • | • | • | • | • | • | • | • |
| 8405 | 1-1/2 | | | | 1.410 - 1.633 | 1.390 | 1 | • | • | • | • | • | • | • | • | • | |
| 8407 | 2 | | | | 1.640 - 2.040 | 1.610 | 1 | • | • | • | • | • | • | • | • | • | |
| 84075 | 2 | | | | 1.640 - 2.040 | 1.743 | 1 | • | • | • | • | • | • | • | • | • | |
| 8408 | 2-1/2 | | | | 1.950 - 2.480 | 1.924 | 1 | • | • | • | • | • | • | • | • | • | |
| 8409 | 3 | | | | 2.420 - 3.070 | 2.390 | 1 | • | • | • | • | • | • | • | • | • | |
| 8410 | 3-1/2 | | | | 2.860 - 3.600 | 2.830 | 1 | • | • | • | • | • | • | • | • | • | |
| Off Center Set Screw Type | 845 | 1/2 | | | | 0.445 - 0.630 | 0.400 x 0.580 | 1 | • | • | • | • | • | • | • | • | • |
| | 845R | 1/2 | | | | 0.445 - 0.630 | 0.400 x 0.580 | 1 | • | • | • | • | • | • | • | • | • |
| | 845ST | 1/2 | | | | 0.445 - 0.630 | 0.375 | 1 | • | • | • | • | • | • | • | • | • |
| Set Screw | L48 | 1/2 | | | | 0.625 - 0.915 | 0.630 | 1 | • | • | • | • | • | • | • | • | • |
| | L49 | 3/4 | | | | 0.820 - 0.910 | 0.845 | 1 | • | • | • | • | • | • | • | • | • |

Cable Types and Ranges

| Style | Part Number (ST = Snap-Tite®) | Knock-Out Size | ACG90 | AC90 | TECK90 | Outer Armor Diameter Flex • A/C • M/C | Throat Diameter | Number of Cables | Insulated Throat | Flexible Metal Conduit (FMC) | | | | Armored Cable (A/C) | | Metal Clad Cable (M/C) | | A/C M/C |
|-------------------------------------|-------------------------------|----------------|-------|------|---------------|--|-----------------|------------------|------------------|------------------------------|----------|--------------------|-----------------------|---------------------|----------|------------------------|---------------------|---------|
| | | | | | | | | | | Steel | Aluminum | Reduced Wall Steel | Reduced Wall Aluminum | Steel | Aluminum | Steel | Aluminum Corrugated | |
| 90° Two Screw Clamp Type Connectors | 85 | 1/2 | | | | 0.370 - 0.510 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 85A | 1/2 | | | | 0.370 - 0.510 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 85ST | 1/2 | | | | 0.370 - 0.510 | 0.560 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 85AST | 1/2 | | | | 0.370 - 0.510 | 0.560 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 850 | 1/2 | | | | 0.480 - 0.650 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 850A | 1/2 | | | | 0.480 - 0.650 | 0.560 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 850ST | 1/2 | | | | 0.480 - 0.650 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 850AST | 1/2 | | | | 0.480 - 0.650 | 0.560 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 851 | 1/2 | | | | 0.650 - 0.850 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 851A | 1/2 | | | | 0.650 - 0.850 | 0.560 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 851ST | 1/2 | | | | 0.650 - 0.850 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 851AST | 1/2 | | | | 0.650 - 0.850 | 0.560 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 852 | 3/4 | | | | 0.830 - 1.380 | 0.825 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 852A | 3/4 | | | | 0.830 - 1.380 | 0.765 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 853 | 1 | | | | 1.330 - 1.570 | 1.025 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 853A | 1 | | | | 1.330 - 1.570 | 0.974 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 854 | 1-1/4 | | | | 1.625 - 1.940 | 1.375 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 854A | 1-1/4 | | | | 1.625 - 1.940 | 1.294 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 855 | 1-1/2 | | | | 1.400 - 2.400 | 1.575 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 855A | 1-1/2 | | | | 1.400 - 2.400 | 1.532 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 856 | 2 | | | | 1.400 - 2.400 | 2.030 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 856A | 2 | | | | 1.400 - 2.400 | 2.007 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 857 | 2-1/2 | | | | 2.600 - 3.100 | 2.450 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 857A | 2-1/2 | | | | 2.600 - 3.100 | 2.425 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 858 | 3 | | | | 3.100 - 3.640 | 3.140 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 858A | 3 | | | | 3.100 - 3.640 | 3.050 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 859 | 3-1/2 | | | | 3.380 - 4.220 | 3.540 | 1 | • | • | • | • | • | • | • | • | • | • |
| | 859A | 3-1/2 | | | | 3.380 - 4.220 | 3.960 | 1 | • | • | • | • | • | • | • | • | • | • |
| 8510 | 4 | | | | 3.730 - 3.730 | 3.540 | 1 | • | • | • | • | • | • | • | • | • | • | |
| 8510A | 4 | | | | 3.730 - 3.730 | 3.960 | 1 | • | • | • | • | • | • | • | • | • | • | |
| Squeeze Connectors | L42 | 1/2 | | | | 0.530 - 0.620 | 0.400 | 1 | • | • | • | • | • | • | • | • | • | |
| | L420 | 1/2 | | | | 0.530 - 0.620 | 0.400 x 0.580 | 1 | • | • | • | • | • | • | • | • | • | |
| | L421 | 1/2 | | | | 0.850 - 0.910 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | |
| | L421A | 1/2 | | | | 0.850 - 0.910 | 0.620 | 1 | • | • | • | • | • | • | • | • | • | |
| | L422 | 3/4 | | | | 1.100 - 1.135 | 0.820 | 1 | • | • | • | • | • | • | • | • | • | |
| | L422A | 3/4 | | | | 1.100 - 1.135 | 0.820 | 1 | • | • | • | • | • | • | • | • | • | |
| | L423 | 1 | | | | 1.255 - 1.375 | 0.940 | 1 | • | • | • | • | • | • | • | • | • | |
| | L423A | 1 | | | | 1.255 - 1.375 | 0.940 | 1 | • | • | • | • | • | • | • | • | • | |
| | L424 | 1-1/4 | | | | 1.550 - 1.610 | 1.240 | 1 | • | • | • | • | • | • | • | • | • | • |
| | L424A | 1-1/4 | | | | 1.550 - 1.610 | 1.240 | 1 | • | • | • | • | • | • | • | • | • | • |
| | L425 | 1-1/2 | | | | 1.810 - 1.895 | 1.460 | 1 | • | • | • | • | • | • | • | • | • | • |
| | L425A | 1-1/2 | | | | 1.810 - 1.895 | 1.460 | 1 | • | • | • | • | • | • | • | • | • | • |
| | L426 | 2 | | | | 2.260 - 2.485 | 1.935 | 1 | • | • | • | • | • | • | • | • | • | • |
| | L426A | 2 | | | | 2.260 - 2.485 | 1.935 | 1 | • | • | • | • | • | • | • | • | • | • |
| | L427 | 2-1/2 | | | | 2.770 - 2.950 | 2.440 | 1 | • | • | • | • | • | • | • | • | • | • |
| | L427A | 2-1/2 | | | | 2.770 - 2.950 | 2.440 | 1 | • | • | • | • | • | • | • | • | • | • |
| | L428 | 3 | | | | 3.170 - 3.560 | 2.980 | 1 | • | • | • | • | • | • | • | • | • | • |
| | L428A | 3 | | | | 3.170 - 3.560 | 2.980 | 1 | • | • | • | • | • | • | • | • | • | • |
| L429 | 3-1/2 | | | | 3.630 - 4.155 | 3.478 | 11 | • | • | • | • | • | • | • | • | • | • | |
| L429A | 3-1/2 | | | | 3.630 - 4.155 | 3.478 | 1 | • | • | • | • | • | • | • | • | • | • | |
| L4210 | 4 | | | | 4.030 - 4.635 | 3.977 | 1 | • | • | • | • | • | • | • | • | • | • | |
| L4210A | 4 | | | | 4.030 - 4.635 | 3.977 | 1 | • | • | • | • | • | • | • | • | • | • | |



MCI-A Cable Ranges


| Style | Part Number (ST = Snap-Tite®) | Knock-Out Size | Cable Range (Aluminum) | Cable Range (Steel) | End Stop Diameter | Number of Cables | Insulated Throat | Aluminum | Steel | Healthcare Facilities |
|--|---|----------------|---------------------------|------------------------|-------------------|------------------|------------------|----------|-------|-----------------------|
| Snap2IT® Connectors (Push-In Type) | 38A | 1/2 | 0.440 - 0.550 | | | 1 | • | • | | • |
| | 38AST | 1/2 | 0.440 - 0.550 | | | 1 | • | • | | • |
| | 380AST | 1/2 | 0.440 - 0.550 | | | 1 | • | • | | • |
| | 3810AST | 1/2 | 0.370 - 0.510 | 0.405 - 0.490 | 0.310 | 1 | • | • | | • |
| | 3838AST | 1/2 | 0.440 - 0.550 | | | 2 | • | • | | • |
| | 383810AST | 1/2 | 0.370 - 0.510 | 0.405 - 0.580 | 0.310 | 2 | • | • | | • |
| | 40AST | 1/2 | 0.480 - 0.550 | | | 1 | • | • | | • |
| | 400AST | 1/2 | 0.480 - 0.550 | | | 1 | • | • | | • |
| | 4010AST | 1/2 | 0.405 - 0.580 | 0.405 - 0.580 | 0.400 | 1 | • | • | | • |
| | 4040AST | 1/2 | 0.440 - 0.550 | | | 2 | • | • | | • |
| | 404010AST | 1/2 | 0.405 - 0.580 | 0.405 - 0.580 | 0.400 | 2 | • | • | | • |
| | SADDLEGRIP® Connectors (Straight and Duplex) | 5010AST | 1/2 | 0.610 - 0.780 | 0.590 - 0.920 | 0.540 | 1 | • | • | |
| 505010AST | | 3/4 | 0.590 - 0.820 | 0.590 - 0.920 | 0.540 | 2 | • | • | | • |
| 7510AST | | 3/4 | 0.895 - 1.110 | 0.895 - 1.110 | 0.776 | 1 | • | • | | • |
| SG38 | | 1/2 | 0.430 - 0.580 | 0.430 - 0.580 | 0.400 | 1 | | • | | • |
| SG38A | | 1/2 | 0.430 - 0.580 | 0.430 - 0.580 | 0.400 | 1 | • | • | | • |
| SG38AST | | 1/2 | 0.430 - 0.580 | 0.430 - 0.580 | 0.400 | 1 | • | • | | • |
| SG380 | | 1/2 | 0.430 - 0.580 | 0.430 - 0.580 | 0.400 | 1 | | • | | • |
| SG380A | | 1/2 | 0.430 - 0.580 | 0.430 - 0.580 | 0.400 | 1 | • | • | | • |
| SG380AST | | 1/2 | 0.430 - 0.580 | 0.430 - 0.580 | 0.400 | 1 | • | • | | • |
| SG3838 | | 1/2 | 0.430 - 0.510 | 0.430 - 0.580 | | 2 | | • | | • |
| SG3838A | | 1/2 | 0.430 - 0.510 | 0.430 - 0.580 | | 2 | • | • | | • |
| SG3838ST | | 1/2 | 0.430 - 0.510 | 0.430 - 0.580 | | 2 | | • | | • |
| SG3838AST | | 1/2 | 0.430 - 0.510 | 0.430 - 0.580 | | 2 | • | • | | • |
| SG40 | | 1/2 | 0.630 - 0.770 | N/A | 0.600 | 1 | | • | | • |
| SG50 | | 1/2 | 0.680 - 0.850 | N/A | 0.620 | 1 | | • | | • |
| SG50A | | 1/2 | 0.680 - 0.850 | N/A | 0.620 | 1 | • | • | | • |
| SG50ST | 1/2 | 0.680 - 0.850 | N/A | 0.620 | 1 | | • | | • | |
| SG50AST | 1/2 | 0.680 - 0.850 | N/A | 0.620 | 1 | • | • | | • | |
| Two Screw Clamp Type Connectors | 840 | 1/2 | 0.440 - 0.520 | 0.370 - 0.612 | 0.400 | 1 | | • | | • |
| | 840ST | 1/2 | 0.440 - 0.520 | 0.370 - 0.612 | 0.400 | 1 | | • | | • |
| | 8400 | 1/2 | 0.440 - 0.520 | 0.370 - 0.612 | 0.400 | 1 | | • | | • |
| | 8400ST | 1/2 | 0.440 - 0.520 | 0.370 - 0.612 | 0.400 | 1 | | • | | • |
| 90° Two-Screw Clamp Type Connectors | 85 | 1/2 | 0.370 - 0.510 | 0.405 - 0.580 | | 1 | | • | | • |
| | 85ST | 1/2 | 0.370 - 0.510 | 0.405 - 0.580 | | 1 | | • | | • |
| | 850 | 1/2 | 0.440 - 0.595 | 0.440 - 0.595 | | 1 | | • | | • |
| | 850A | 1/2 | 0.440 - 0.595 | 0.440 - 0.595 | | 1 | • | • | | • |
| | 850ST | 1/2 | 0.440 - 0.595 | | | 1 | | • | | • |
| | 850AST | 1/2 | 0.440 - 0.595 | | | 1 | • | • | | • |
| | 851 | 1/2 | 0.680 - 0.770 | 0.680 - 0.770 | | 1 | | • | | • |
| | 851A | 1/2 | 0.680 - 0.770 | 0.680 - 0.770 | | 1 | • | • | | • |
| | 851ST | 1/2 | 0.680 - 0.770 | 0.680 - 0.770 | | 1 | | • | | • |
| Clamp Type Two Cable Connectors | 851AST | 1/2 | 0.680 - 0.770 | 0.680 - 0.770 | | 1 | • | • | | • |
| | 846 | 1/2 | 0.370 - 0.580 | 0.405 - 0.580 | | 2 | | • | • | • |
| | 846A | 1/2 | 0.370 - 0.580 | | | 2 | • | • | • | • |
| | 846ST | 1/2 | 0.370 - 0.580 | 0.405 - 0.580 | | 2 | | • | • | • |
| | 846AST | 1/2 | 0.370 - 0.580 | | | 2 | • | • | • | • |
| | 84690 | 1/2 | 0.370 - 0.580 | 0.405 - 0.580 | | 2 | | • | • | • |
| Single Screw Clamp Type Connectors | 84690ST | 1/2 | 0.370 - 0.580 | 0.405 - 0.580 | | 2 | | • | • | • |
| | L15AST | 1/2 | 0.405 - 0.580 | | | 1 | • | • | • | • |
| | L16 | 1/2 | 0.405 - 0.650 | 0.405 - 0.650 | 0.400 | 1 | | • | • | • |
| | L16ST | 1/2 | 0.405 - 0.650 | 0.405 - 0.650 | 0.400 | 1 | | • | • | • |
| | L160 | 1/2 | 0.370 - 0.510 | 0.405 - 0.690 | 0.305 | 1 | | • | • | • |
| L160ST | 1/2 | 0.370 - 0.510 | 0.405 - 0.690 | 0.305 | 1 | | • | • | • | |

SAVES TIME • LOOKS GREAT!

IN BOX™

RECESSED BOX

EXTRA DUTY WEATHERPROOF IN USE COVER • LOW PROFILE



Installs in the wall.
Less shows outside!

View Video



Recessed **IN BOX™** eliminates installing multiple pieces. It installs *in* an exterior wall so less shows outside.
Cost savings. Time savings. A great-looking job.

- One-piece – No extra parts to buy or handle
- Non-metallic electrical box with **extra duty** weatherproof-while-in-use clear or white cover
- Single and two-gang, vertical and horizontal
- For new and retrofit applications
- Accepts single-gang devices – no gaskets required

Made in USA



IN BOX meets 2014 NEC, Section 406.9 (and 2012 CEC (Rule 26-702), NEMA 3R) for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.



Arlington



PVC Entrance Caps

For rigid • IMC • EMT • Rigid PVC.
 Sizes 1/2" - 4" include adapter sleeve
 for EMT.




PVC1020



PVC1040



PVC105, PVC106, & PVC129



PVC109

For 3" conduit use both sleeves.
 For 3-1/2" conduit use the larger
 adapter sleeve.

Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | MAST SIZE | STD PKG | DIM A | DIM B |
|----------------|--------------------------|-------------|-------------|---------|--------|-------|
| PVC1020* | 73146 | 1/2,3/4,1 | 1/2,3/4,1 | 20 | 3.575 | 3.438 |
| PVC1040* | 73147 | 1-1/4,1-1/2 | 1-1/4,1-1/2 | 10 | 5.900 | 5.069 |
| PVC105 | 73105 | 2 | 2 | 5 | 7.790 | 6.660 |
| PVC129 | 73129 | 2 | 2-1/2 | 1 | 7.750 | 6.660 |
| PVC106 | 12512 | 2-1/2 | 2-1/2 | 1 | 9.790 | 7.620 |
| PVC109* | 12513 | 3, 3-1/2, 4 | 3, 3-1/2, 4 | 1 | 12.650 | 9.070 |

*Includes adapters for multiple sizes.


PATENTED.



FEATURES AND BENEFITS

- PVC1020 priced as 1/2" trade size
- PVC1040 priced as 1-1/4" trade size
- PVC109 priced as 3" trade size

**REDUCES
 INVENTORY!
 Saves Money**



Installation Shots



PVC1040



PVC1020

5 PRODUCTS cover 10 TRADE SIZES

Service Entrance Cable Caps


Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRE SIZE | STD PKG | DIM A | DIM B | DIM C | HOLE SIZES |
|----------------|--------------------------|-----------------|---------|-------|-------|-------|------------|
| 660 | 00660 | 7/8" Diam. Max. | 50 | 2.060 | 2.970 | 2.260 | (2).58 |
| 662 | 00662 | 1/0 to 4/0 | 10 | 3.180 | 4.520 | 3.600 | (2).80 |



E66990



PVC Entrance Caps


With galvanized steel strap.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRE SIZE | STD PKG | DIM A | DIM B | HOLE SIZES |
|----------------|--------------------------|--------------------|---------|-------|-------|------------|
| PVC660 | 73660 | (2) 3, 6, 4, 2 | 50 | 2.700 | 2.520 | (2).53 |
| PVC662 | 73662 | (2) 1/0 to (2) 4/0 | 10 | 4.125 | 3.750 | (2).69 |



E66990



Mast Reducer Entrance Caps


Set-screw type.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | MAST SIZE | CAP SIZE | UNIT PKG | STD PKG | DIM A | DIM B | HOLE SIZES |
|----------------|--------------------------|-----------|----------|----------|---------|-------|-------|-------------------------|
| 128 | 00128 | 2 | 1-1/4 | 1 | 6 | 4.020 | 4.842 | (2).43, (3).63 |
| 129 | 00129 | 2-1/2 | 2 | 1 | 6 | 5.236 | 6.506 | (1).53, (2).75, (3)1.00 |



E105706




Service Entrance Hoods

Non-metallic.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | CABLE SIZES | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------------------|---------|-------|-------|-------|
| EH200 | 58201 | (3) 1/0 to (3) 2/0 | 1 | 4.250 | 6.000 | 2.000 |
| EH201 | 43630 | (3) 1/0 to (3) 4/0 | 1 | 6.000 | 6.187 | 2.500 |




Entrance Caps Clamp-On Type

For rigid • IMC • EMT.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | HOLE SIZES |
|----------------|--------------------------|------------|----------|---------|-------|-------|--------------------------|
| 140 | 00140 | 1/2 | 10 | 10 | 2.60 | 2.68 | (4) .30 |
| 141 | 00141 | 3/4 | 10 | 10 | 2.72 | 3.80 | (2) .38 (3) .40 |
| 142 | 00142 | 1 | 10 | 10 | 3.11 | 3.32 | (2) .44 (3) .50 |
| 143 | 00143 | 1-1/4 | 5 | 25 | 3.20 | 4.46 | (2) .42 (3) .63 |
| 144 | 00144 | 1-1/2 | 3 | 15 | 4.34 | 4.85 | (2) .60 (3) .75 |
| 145 | 00145 | 2 | 10 | 10 | 4.55 | 6.62 | (2) .75 (3) 1.00 (1) .53 |
| 146 | 00146 | 2-1/2 | 1 | 1 | 7.80 | 9.74 | (3) 1.31 (3) .87 (1) .99 |
| 147 | 00147 | 3 | 1 | 1 | 8.00 | 10.50 | (3) 1.73 (4) 1.10 |
| 148 | 00148 | 3-1/2 | 1 | 1 | 9.25 | 12.50 | (3) 1.73 (4) 1.10 |
| 149 | 00149 | 4 | 1 | 1 | 9.25 | 12.50 | (3) 1.73 (4) 1.10 |

See Page F-1 for PVC alternatives.





Sill Plates

With screws and compound.
Cast aluminum.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRE SIZE | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|--------------------|---------|-------|-------|-------|-------|
| 663 | 00663 | (3) #4 to (3) #2 | 10 | .875 | 1.200 | 2.750 | 2.965 |
| 664 | 00664 | (3) 3/0 to (3) 4/0 | 10 | 2.475 | 1.850 | 6.250 | 3.725 |




Sill Plates with Duct Seal and Wood Screws

Zinc die-cast. For EMT • SEU cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRE SIZE | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|---------------------|---------|-------|-------|-------|-------|
| SP360 | 17360 | 1/2 EMT & 3/4 EMT | 10 | .812 | 2.593 | 2.421 | .218 |
| SP362 | 17361 | 1 EMT & 3/3 SEU | 10 | 1.250 | 3.000 | 2.500 | .218 |
| SP363 | 17362 | 1-1/4 EMT & 2/3 SEU | 10 | 1.650 | 3.812 | 2.625 | .218 |
| SP364 | 17363 | 1-1/2 EMT & 4/0 SEU | 10 | 1.750 | 3.562 | 3.750 | .281 |
| SP365 | 17364 | 2 EMT | 10 | 2.312 | 4.093 | 4.125 | .281 |





PVC Sill Plates

With screws and compound.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|------------------|----------|---------|-------|-------|-------|-------|
| PVC85 | 00085 | (3) #4 TO (3) #0 | 10 | 100 | 1.188 | 1.093 | 3.093 | 2.970 |



Porcelain Wire Holder

With solid rivet through head.
Porcelain and galvanized steel.



612



613




616



617

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SCREW SIZE | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-----------------------|---------|-------|-------|-------|
| 612 | 00612 | 2-1/4 Lag | 5 | 4.750 | 2.750 | 2.250 |
| 613 | 00613 | 3/8 x 1/2 Match Screw | 5 | 3.350 | 2.750 | 2.250 |
| 616 | 00616 | 2-1/4 Lag | 5 | 5.615 | 3.200 | 1.750 |
| 617 | 00617 | 3/8 x 1/2 Match Screw | 5 | 3.775 | 3.200 | 1.750 |

UL/CSA NOT APPLICABLE




Porcelain Wire Holder

With steel clip. Fits 1-1/4" to 3" pipe.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRE SIZE | STD PKG | DIM A | DIM B | MIN | MAX |
|----------------|--------------------------|------------|---------|-------|-------|-------|-------|
| 610 | 00610 | 1-1/4 to 3 | 5 | 1.875 | 7.625 | 1.620 | 3.930 |

UL/CSA NOT APPLICABLE




Porcelain Wire Holder

With hanger. Fits 2" rigid or 2" EMT.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | CONDUIT SIZE | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------------|---------|-------|-------|-------|
| 645 | 00645 | 2 | 5 | 7.062 | 2.450 | 1.750 |

UL/CSA NOT APPLICABLE




Channel Bar

11" long galvanized.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------------------------|---------|--------|-------|-------|
| 611 | 00611 | For two or three 617's or 613's | 5 | 11.000 | .525 | 1.750 |

UL/CSA NOT APPLICABLE




Universal Pipe Support

10" bolt.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | MAST SIZE | STD PKG |
|----------------|--------------------------|------------|---------|
| 615 | 00615 | 1-1/4 to 3 | 5 |

UL/CSA NOT APPLICABLE




Universal Pipe Support



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | MAST SIZE | STD PKG |
|----------------|--------------------------|------------|---------|
| 620 | 00620 | 1-1/4 to 3 | 5 |

UL/CSA NOT APPLICABLE




Universal Pipe Support

10" bolt. Sand cast aluminum with steel screw.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | MAST SIZE | STD PKG |
|----------------|--------------------------|-----------|---------|
| 2350 | 02350 | 2 | 5 |
| 2850 | 28550 | 2-1/2 | 5 |

UL/CSA NOT APPLICABLE




Steel Roof Flashing

Galvanized steel with neoprene seal. 10-3/4" x 14-1/2" x 22 gauge.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | STD PKG | DIM A | DIM B |
|----------------|--------------------------|----------------|---------|--------|--------|
| 624 | 00624 | 1-1/4 to 1-1/2 | 10 | 10.750 | 12.500 |
| 625 | 00625 | 2 | 10 | 10.750 | 14.500 |
| 626 | 00626 | 2-1/2 | 10 | 10.750 | 14.500 |

UL/CSA NOT APPLICABLE




Neoprene Roof Flashing

All neoprene. Black, one-piece design.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | STD PKG | DIM A | DIM B |
|----------------|--------------------------|----------------|---------|--------|--------|
| 634 | 00634 | 1-1/4 to 1-1/2 | 12 | 9.000 | 11.500 |
| 635 | 00635 | 2 | 12 | 9.000 | 11.500 |
| 636 | 00636 | 2-1/2 | 12 | 9.000 | 11.500 |
| 637 | 00637 | 3 | 12 | 10.000 | 13.500 |
| 639 | 00639 | 4 | 12 | 11.500 | 14.000 |

UL/CSA NOT APPLICABLE



Aluminum Roof Flashing

Cast aluminum. Includes set-screw(s) to secure pipe and compound.




723




726

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|---------|-------|--------|
| 723 | 00723 | 1-1/4 | 10 | 7.250 | 9.500 |
| 724 | 00724 | 1-1/2 | 10 | 9.000 | 11.000 |
| 725 | 00725 | 2 | 5 | 9.000 | 11.000 |
| 726 | 00726 | 1-1/4 to 2 | 10 | 7.750 | 15.000 |

UL/CSA NOT APPLICABLE



723



726

Mast Kits

Service entrance mast kits provide an assortment of S.E. mast components for installing overhead service drops in residential or commercial buildings using conduit.



MK200WH

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | STD PKG | ENTRANCE CAP | ROOF FLASHING | WIRE HOLDER | STRAPS | LAG BOLTS | BOTTOM REDUCER | AMPERE SERVICE |
|----------------|--------------------------|------------|---------|--------------|---------------|------------------|---------|-------------|----------------|----------------|
| MK200 | 42200 | 2 | 1 | 145 | 625 | - | (2) 345 | (2) 3/8 X 3 | 650 | 125-150-200 |
| MK200WH | 42205 | 2 | 1 | 145 | 625 | 645 | (2) 355 | - | - | 125-150-200 |
| MK200ASF | 42210 | 2 | 1 | 145 | 625 | - | (2) 345 | (2) 3/8 X 3 | - | 125-150-200 |
| MK200PS | 32044 | 2 | 1 | 145 | 625 | (1) 610, (1) 620 | - | - | - | 125-150-200 |
| MK250ASF | 42250 | 2-1/2 | 1 | 129 | 625 | - | (2) 346 | (2) 1/2 X 4 | 651 | 125-150-200 |
| MK250ASFX | 42255 | 2-1/2 | 1 | 129 | 625 | (2) 615, (1) 610 | - | - | - | 125-150-200 |
| MK250A | 32027 | 2-1/2 | 1 | 129 | 625 | - | (2) 356 | - | - | 125-150-200 |


Intersystem Grounding Bridges

Available in zinc or bronze.
Provides reliable intersystem bonding between power and communication grounding systems. Comes with textured, paintable, white cover. Cover is UV rated plastic for long outdoor life.

NEW!

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E | DIM F |
|----------------|--------------------------|-----------------|----------|---------|-------|-------|-------|-------|-------|-------|
| GB5 | 76095 | Zinc, w/cover | 1 | 10 | 3.383 | 1.409 | .872 | 4.398 | 1.836 | 1.497 |
| GB5NC | 76094 | Zinc, NO cover | 10 | 10 | 3.383 | 1.409 | .872 | - | - | - |
| GBB5 | 76096 | Bronze, w/cover | 1 | 10 | 3.383 | 1.409 | .872 | 4.398 | 1.836 | 1.497 |
| GBB50 | 09726 | Bronze, w/cover | 1 | 10 | 3.383 | 1.409 | .872 | 4.398 | 1.836 | 1.497 |
| GBB5250 | 09756 | Bronze, w/cover | 1 | 10 | 4.325 | 1.638 | .935 | 5.462 | 1.869 | 1.685 |

PATENTED.



**NEW!
COSTS LESS**



GB5NC Without the cover and screw...and bulk packaged to lower the cost!

FEATURES AND BENEFITS

- Meets 2014 NEC Ground Requirements
- GB5 has four termination points one more than required by 250.94 of the 2014 NEC
- Available in Zinc and Bronze
- Handles multiple hookups of communications systems – such as a phone, cable TV, or satellite dish
- Fast, simple installation on grounding conductor
- Plastic cover is textured and paintable for good looks

Cable Range


- Four termination points for #4-#14 (solid or stranded)
- Attaches to conductor with "Lay in" style lug with cable range of #6-#2
- GBB50 has larger cable range of #6-#1/0



Installation Instructions



Attach bridge to substrate. (Mounting screws not provided.)



Insert grounding electrode conductor into the lay in lug. Tighten screw.



Finish by attaching the cover. Good looks, a great finish.




Scan For Video



Intersystem Grounding Bridges with PVC Adapter

Available in zinc or bronze. Provides reliable intersystem bonding between power and communication grounding systems. Comes with a PVC adapter for 1/2" PVC pipe. Cover is UV rated plastic for long outdoor life.




GBB5P

FEATURES AND BENEFITS

- Meets 2014 NEC Ground Requirements
- GB5P has four termination points – one more than required by 250.94 of the 2014 NEC
- Available in Zinc and Bronze
- Handles multiple hookups of communications systems – for instance phone, cable TV, or a satellite dish
- Fast, simple installation on grounding conductor
- Plastic cover is textured and paintable for good looks

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | MATERIAL | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E | DIM F |
|----------------|--------------------------|----------|----------|---------|-------|-------|-------|-------|-------|-------|
| GB5P | 09720 | Zinc | 1 | 10 | 3.383 | 1.409 | .872 | 1.653 | 4.575 | 3.461 |
| GBB5P | 09721 | Bronze | 1 | 10 | 3.383 | 1.409 | .872 | 1.653 | 4.575 | 3.461 |
| GBB50P | 09726 | Bronze | 1 | 10 | 3.383 | 1.409 | .872 | 1.653 | 4.575 | 3.461 |

PATENTED.



Cable Range

- Four termination points for #4-#14 (solid or stranded)
- Attaches to conductor with "Lay in" style lug with cable range of #6-#2
- GBB50P has larger cable range of #6-#1/0

Installation Instructions



1 Mount conduit adapter plate in desired location using three screws (not provided)



2 Insert grounding electrode conductor into the lay in lug. Tighten screw.



3 Insert grounding electrode conductor into the lay in lug. Tighten screw.



4 Finish by attaching the cover. Good looks, a great finish.

Scan For Video




Insulated Metal Grounding Bushings

Threaded. With dual rated CU-AL
C-clamp grounding lug. Zinc die-cast.
150° C rated.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | GROUND MIN | WIRE MAX | UNIT PKG | STD PKG | DIM A | DIM B | THREADS/ INCH |
|----------------|--------------------------|------------|------------|----------|----------|---------|-------|-------|---------------|
| 450 | 00450 | 1/2 | 14 | 4 | 25 | 100 | 1.896 | .475 | 14 |
| 451 | 00451 | 3/4 | 14 | 4 | 25 | 100 | 2.082 | .520 | 14 |
| 452 | 00452 | 1 | 14 | 4 | 25 | 100 | 2.364 | .575 | 11-1/2 |
| 453 | 00453 | 1-1/4 | 14 | 4 | 20 | 80 | 2.702 | .635 | 11-1/2 |
| 453100 | 01453 | 1-1/4 | 14 | 1/0 | 20 | 20 | 2.702 | .635 | 11-1/2 |
| 454 | 00454 | 1-1/2 | 14 | 2 | 20 | 80 | 3.120 | .760 | 11-1/2 |
| 454100 | 01454 | 1-1/2 | 14 | 1/0 | 20 | 20 | 3.120 | .760 | 11-1/2 |
| 455 | 00455 | 2 | 14 | 2 | 10 | 50 | 3.650 | .755 | 11-1/2 |
| 455100 | 01455 | 2 | 14 | 1/0 | 10 | 10 | 3.650 | .755 | 11-1/2 |
| 456 | 00456 | 2-1/2 | 14 | 2/0 | 5 | 20 | 4.705 | .960 | 8 |
| 456250 | 01456 | 2-1/2 | 6 | 250MCM | 10 | 10 | 4.705 | .960 | 8 |
| 457 | 00457 | 3 | 14 | 2/0 | 5 | 20 | 5.275 | .920 | 8 |
| 457250 | 01457 | 3 | 6 | 250MCM | 10 | 10 | 5.275 | .920 | 8 |
| 458 | 00458 | 3-1/2 | 14 | 2/0 | 5 | 20 | 6.266 | .930 | 8 |
| 458250 | 01458 | 3-1/2 | 6 | 250MCM | 5 | 5 | 6.266 | .930 | 8 |
| 459 | 00459 | 4 | 14 | 2/0 | 5 | 20 | 6.268 | .950 | 8 |
| 459250 | 01459 | 4 | 6 | 250MCM | 5 | 5 | 6.268 | .950 | 8 |
| 4591 | 04591 | 5 | 8 | 2/0 | 5 | 5 | 7.050 | .990 | 8 |
| 4591250 | 45912 | 5 | 2 | 250MCM | 5 | 5 | 7.050 | .990 | 8 |
| 4592 | 04592 | 6 | 8 | 2/0 | 5 | 5 | 8.125 | .975 | 8 |
| 4592250 | 45922 | 6 | 2 | 250MCM | 5 | 5 | 8.125 | .975 | 8 |




Ground Rod Clamps

Conductor range 8 solid - 2 stranded.
Approved for direct burial. Solid brass
alloy with bronze screw.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ROD SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|----------|----------|---------|-------|-------|
| 780 | 00780 | 1/2 | 25 | 25 | 1.250 | .875 |
| 781 | 00781 | 5/8 | 25 | 100 | 1.275 | .593 |
| 782 | 00782 | 3/4 | 25 | 25 | 1.445 | 1.030 |



Grounding Locknuts


For rigid conduit. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|---------|-------|-------|
| GL50 | 77050 | 1/2 | 50 | .220 | 1.250 |
| GL75 | 77075 | 3/4 | 25 | .255 | 1.450 |
| GL100 | 77100 | 1 | 50 | .255 | 1.720 |
| GL125 | 77125 | 1-1/4 | 50 | .255 | 2.020 |
| GL150 | 77150 | 1-1/2 | 50 | .250 | 2.535 |
| GL200 | 77200 | 2 | 25 | .250 | 2.950 |
| GL250 | 77250 | 2-1/2 | 10 | .280 | 3.530 |
| GL300 | 77300 | 3 | 10 | .295 | 4.330 |
| GL350 | 77350 | 3-1/2 | 5 | .300 | 4.490 |
| GL400 | 77400 | 4 | 5 | .300 | 5.395 |



GROUNDING SCREW




Ground Clamp

With solid brass hubs.
For rigid conduit.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | PIPE SIZE | HUB SIZE | UNIT PKG | STD PKG | DIM A | MIN | MAX |
|----------------|--------------------------|-----------|----------|----------|---------|-------|------|-------|
| 730B | 73020 | 1/2 to 1 | 1/2" | 5 | 50 | 2.250 | .550 | 1.795 |




Bare Wire Ground Clamp

Zinc die-cast. Brass color plated.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | PIPE SIZE | WIRE RANGE | UNIT PKG | STD PKG | DIM A | DIM B | MIN | MAX |
|----------------|--------------------------|-----------|------------|----------|---------|-------|-------|------|-------|
| 720S | 72010 | 1/2 to 1 | 8-2 | 25 | 250 | 2.225 | .310 | .550 | 1.575 |

Note: Zinc grounding and bonding products with color plated brass are not UL or CSA listed.




Bare Wire Ground Clamp

Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | PIPE SIZE | WIRE RANGE | UNIT PKG | STD PKG | DIM A | DIM B | MIN | MAX |
|----------------|--------------------------|-----------|------------|----------|---------|-------|-------|------|-------|
| 720Z | 72080 | 1/2 to 1 | 8-2 | 25 | 250 | 2.225 | .550 | .545 | 1.575 |




Bare Wire Ground Clamps

Solid brass with steel screws.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | PIPE SIZE | WIRE RANGE | UNIT PKG | STD PKG | DIM A | DIM B | MIN | MAX |
|----------------|--------------------------|------------|------------|----------|---------|-------|-------|-------|-------|
| 720B | 72020 | 1/2 to 1 | 10-2 | 25 | 250 | 2.430 | .310 | .500 | 1.380 |
| 721B | 00722 | 1-1/4 to 2 | 10-2 | 5 | 20 | 3.600 | .310 | 1.390 | 3.000 |
| 722B | 07222 | 2-1/2 to 4 | 10-2 | 1 | 1 | 6.350 | .310 | 2.700 | 5.900 |
| 723B | 07232 | 4-1/2 to 6 | 10-2 | 1 | 1 | 8.500 | .310 | 4.500 | 8.400 |




Bare Wire Ground Clamp

Solid brass with brass screws.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | PIPE SIZE | WIRE RANGE | UNIT PKG | STD PKG | DIM A | DIM B | MIN | MAX |
|----------------|--------------------------|-----------|------------|----------|---------|-------|-------|------|-------|
| 720BBS | 72022 | 1/2 to 1 | 10-2 | 25 | 250 | 2.430 | .310 | .500 | 1.380 |




Bare Wire Ground Clamp

Solid bronze with bronze screws. Approved for direct burial.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | PIPE SIZE | WIRE RANGE | UNIT PKG | STD PKG | DIM A | DIM B | MIN | MAX |
|----------------|--------------------------|-----------|------------|----------|---------|-------|-------|------|-------|
| 720DB | 00721 | 1/2 to 1 | 10-2 | 25 | 250 | 2.275 | .312 | .675 | 1.850 |




Bare Wire Ground Clamp with Closed Lug

Solid bronze with stainless steel screws. Approved for direct burial on rebar, pipe, tubing, and rod.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | PIPE SIZE | WIRE RANGE | UNIT PKG | STD PKG | DIM A | DIM B | MIN | MAX |
|----------------|--------------------------|-----------|------------|----------|---------|-------|-------|------|-------|
| 718DB | 72000 | 3/8 to 1 | 8-4/0 | 10 | 10 | 2.350 | .620 | .330 | 1.500 |




Bare Wire Ground Clamp with Open Lug

Solid bronze with stainless steel screws. Approved for direct burial on rebar, pipe, tubing, and rod.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | PIPE SIZE | WIRE RANGE | UNIT PKG | STD PKG | DIM A | MIN | MAX |
|----------------|--------------------------|-----------|------------|----------|---------|-------|------|-------|
| 719DB | 72001 | 3/8 to 1 | 8-4/0 | 10 | 10 | 2.588 | .360 | 1.125 |




Bare Wire Ground Clamp with Open Lug

Solid bronze with stainless steel screws. Approved for direct burial on rebar, pipe, tubing, and rod.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | PIPE SIZE | WIRE RANGE | UNIT PKG | STD PKG | DIM A | MIN | MAX |
|----------------|--------------------------|-----------|------------|----------|---------|-------|------|-------|
| 717DB | 12514 | 3/8 to 1 | 10-2 | 25 | 250 | 2.230 | .275 | 1.500 |



Zinc Grounding Bridge Clamp

Zinc with plated steel screws. For indoor or outdoor use.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | MATERIAL | PIPE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|----------|-----------|----------|---------|-------|-------|
| 720GB5 | 09754 | Zinc | 1/2 to 1 | 25 | 25 | 3.413 | .265 |

PATENT PENDING.



FEATURES AND BENEFITS

- For 1/2" to 1" metal underground water pipe and 1/2", 5/8" or 3/4" ground rod
- Has **four** termination points for bonding conductors - one more than required by 250.94 of the 2014 NEC
- Intersystem Bonding and Grounding Conductors: #14 to #4 copper or aluminum, solid or stranded
- Equipment Grounding Conductor/Grounding Conductor: #8 to #2



Bronze Grounding Bridge Clamp

Bronze with stainless steel screws. For indoor or outdoor use.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | MATERIAL | PIPE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|----------|-----------|----------|---------|-------|-------|
| 720GBB5 | 09755 | Bronze | 1/2 to 1 | 25 | 25 | 3.413 | .265 |

PATENT PENDING.




FEATURES AND BENEFITS

- For 1/2" to 1" metal underground water pipe and 1/2", 5/8" or 3/4" ground rod
- Has **four** termination points for bonding conductors - one more than required by 250.94 of the 2014 NEC
- Intersystem Bonding and Grounding Conductors: #14 to #4 copper or aluminum, solid or stranded
- Equipment Grounding Conductor/Grounding Conductor: #8 to #2



Compression Connectors for Terminating Grounding Electrodes

Compression connector for terminating grounding connectors to metal enclosures.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|---------|-------|-------|-------|-------|-------|
| KC4 | 83665 | 10 | 1.806 | .520 | 1.208 | .198 | .160 |
| KC6 | 83667 | 10 | 1.740 | .500 | 1.213 | .154 | .130 |



FEATURES AND BENEFITS





- A new alternative for bonding and grounding separately derived systems, panelboards, and enclosures
- Eliminates the need for installing lugs on the frames of load centers
- Provides adequate strain relief for grounding electrode conductors



ZINC & BRONZE

GROUNDING BRIDGE

AND CLAMPS FOR RELIABLE INTERSYSTEM BONDING



View Video



Arlington's heavy-duty **Grounding Bridge** and **Grounding Bridge Clamps** deliver reliable intersystem bonding between power and communication grounding systems. ALL handle multiple hookups of communications systems: telephone, CATV, satellite dish. **And all meet the requirements for bonding in 250.94 of the 2008, 2011 and 2014 NEC.**

- Four termination points (*more than required by NEC*) accept #14 to #4 AWG intersystem bonding conductors
- For indoor or outdoor use; fast, simple installation
- Textured, paintable plastic cover (grounding bridge)
- Easy access for inspections
- Available in zinc and bronze, in a variety of sizes



**ALL MEET 2014
GROUND REQUIREMENTS**



Arlington



AnyBODY™ Conduit Bodies

Copper-free aluminum die-cast. Five conduit bodies in one! Ships as an LB, but converts to a T, LL, LR, or C. Switch covers and threaded flanges as needed to create the style you need.



930 ships as LB



Converts to a...



C



LL



LR



T

Scan For Video




Combination threaded IMC or rigid and set-screw EMT.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CUBIC INCHES | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|--------------|----------|---------|--------|-------|-------|
| 930 | 17900 | 1/2 | 4.80 | 10 | 10 | 5.111 | 2.520 | 1.670 |
| 931 | 17901 | 3/4 | 7.80 | 10 | 10 | 5.640 | 2.770 | 2.020 |
| 932 | 17902 | 1 | 11.50 | 5 | 5 | 6.530 | 3.280 | 2.160 |
| 933 | 17903 | 1-1/4 | 32.30 | 2 | 10 | 8.550 | 4.020 | 2.980 |
| 934 | 17904 | 1-1/2 | 32.30 | 2 | 10 | 8.550 | 4.020 | 2.980 |
| 935 | 17905 | 2 | 69.50 | 1 | 5 | 10.730 | 4.670 | 3.500 |

Refer to page H-2 for flange illustration.

PATENTED.



Threaded only for IMC or rigid.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CUBIC INCHES | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|--------------|----------|---------|--------|-------|-------|
| 936 | 17906 | 2-1/2 | 175.50 | 1 | 1 | 13.900 | 5.970 | 4.800 |
| 937 | 17907 | 3 | 175.50 | 1 | 1 | 14.340 | 6.400 | 4.800 |
| 938 | 17908 | 3-1/2 | 334.00 | 1 | 1 | 16.840 | 7.330 | 5.840 |
| 939 | 17909 | 4 | 334.00 | 1 | 1 | 16.840 | 7.330 | 5.840 |

PATENTED.



FEATURES AND BENEFITS

- Meets NEC 2014 Section 314.16 Paragraph (C) (2) for conduit bodies with splices, taps, or devices
- Convenient and easy to use
- Saves the time, space, and cost of stocking five different conduit bodies (LB, T, LL, LR, C)
- 1/2" to 2" sizes are combination EMT/rigid – they're threaded for rigid, but also have a set-screw for use with EMT
- Includes threaded flanges for three openings
- Volume and wire fill marked inside bodies
- Recessed O-rings under covers and flanges


930
1/2" AnyBODY
Showing Conversion to LR

Threaded Flange
Cover Plate
Screwdriver

1. Remove cover plate.
2. Remove threaded flange.
3. Reinstall cover plate and flange in the appropriate opening to convert AnyBODY to the desired configuration.



Recessed O-Ring Illustration




(Note: cover removed)
Seated O-rings on all Metallic AnyBODY™ Conduit Bodies maintain liquid-tight seal!


Flange Illustration

Combination Threaded and Set-Screw Conduit Bodies

AnyBODY™ conduit bodies, #'s 930 through 935, whether in T, LB, C, LR, or LL configurations have combination flanges which are threaded for rigid and include set-screws for EMT. The set-screws may be used for rigid, but are not necessary. They are listed raintight with rigid and concrete-tight for EMT. These products can also be used for EMT to rigid.



Shown with Rigid




Shown with EMT

AnyBODY™ Cover and Gasket Kits

Replacement kits for the AnyBODY Series. Includes aluminum cover, neoprene gasket, and two combination screws.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|--------|-------|
| 930CG | 16500 | 1/2 | 1 | 1 | 4.140 | 1.380 |
| 931CG | 16501 | 3/4 | 1 | 1 | 4.600 | 1.720 |
| 932CG | 16502 | 1 | 1 | 1 | 5.250 | 1.860 |
| 933CG | 16503 | 1-1/4 | 1 | 1 | 7.200 | 2.600 |
| 934CG | 16504 | 1-1/2 | 1 | 1 | 7.200 | 2.600 |
| 935CG | 16505 | 2 | 1 | 1 | 9.440 | 3.130 |
| 936CG | 93605 | 2-1/2 | 1 | 1 | 12.500 | 4.360 |
| 937CG | 93705 | 3 | 1 | 1 | 12.500 | 4.360 |
| 938CG | 93805 | 3-1/2 | 1 | 1 | 15.000 | 5.400 |
| 939CG | 93905 | 4 | 1 | 1 | 15.000 | 5.400 |



Set-Screw AnyBODY™ Conduit Bodies for EMT or Rigid

Copper-free aluminum die-cast. Five conduit bodies in one! Ships as an LB, but converts to a T, LL, LR, or C. Switch covers and flanges as needed to create the style you need.




For set-screw sizes 1/2" - 2" see page H-1.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CUBIC INCHES | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|--------------|----------|---------|--------|-------|-------|
| 16 | 16400 | 2-1/2 | 175.50 | 1 | 1 | 14.340 | 6.390 | 4.800 |
| 17 | 16401 | 3 | 175.50 | 1 | 1 | 14.340 | 6.400 | 4.800 |
| 18 | 16402 | 3-1/2 | 334.00 | 1 | 1 | 16.840 | 7.330 | 5.840 |
| 19 | 16403 | 4 | 334.00 | 1 | 1 | 16.840 | 7.330 | 5.840 |

Refer to page H-2 for flange illustration.

PATENTED.



FEATURES AND BENEFITS

- Meets NEC 2014 Section 314.16 Paragraph (C) (2) for conduit bodies with splices, taps, or devices
- Convenient and easy to use
- Saves the time, space, and cost of stocking five different conduit bodies (LB, T, LL, LR, C)
- Includes flanges for three openings
- Volume and wire fill marked inside bodies
- Recessed O-rings under covers and flanges

16
2-1/2" AnyBODY
Converted from LB
to LR

Set-screw Flange Cover Plate

1. Remove cover plate.
2. Remove set-screw flange.
3. Reinstall cover plate and flange in the appropriate opening to convert AnyBODY to the desired configuration.


Service Entrance SLB Conduit Bodies

With aluminum cover and velumoid gasket. Copper-free aluminum die-cast.



Threaded for IMC or rigid.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| 920SLB | 92013 | 1/2 | 10 | 10 | 3.155 | 1.450 | 1.178 |
| 921SLB | 92113 | 3/4 | 10 | 10 | 3.470 | 1.650 | 1.360 |
| 922SLB | 92213 | 1 | 5 | 5 | 4.180 | 1.915 | 1.723 |
| 923SLB | 92313 | 1-1/4 | 5 | 5 | 5.515 | 2.320 | 2.164 |
| 924SLB | 92413 | 1-1/2 | 2 | 2 | 6.095 | 2.410 | 2.420 |
| 925SLB | 92513 | 2 | 2 | 10 | 6.595 | 2.975 | 2.835 |




Non-Metallic AnyBODY™

Conduit Bodies

Non-metallic. Five conduit bodies in one! Ships as an LB, but converts to a T, LL, LR, or C. Switch covers and flanges as needed to create the style you need. Includes cover, foam gaskets, and screws.



935NM ships as LB



Converts to a...



C



LL



LR




T

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | CUBIC INCHES | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|--------------|----------|---------|--------|-------|-------|
| 930NM | 12500 | 1/2 | 4.50 | 10 | 10 | 5.150 | 2.560 | 1.750 |
| 931NM | 12501 | 3/4 | 8.50 | 10 | 10 | 5.670 | 2.800 | 2.100 |
| 932NM | 12502 | 1 | 12.00 | 5 | 5 | 6.560 | 3.260 | 2.240 |
| 933NM | 12503 | 1-1/4 | 33.50 | 2 | 10 | 8.510 | 3.910 | 3.000 |
| 934NM | 12504 | 1-1/2 | 33.50 | 2 | 10 | 8.510 | 3.910 | 3.000 |
| 935NM | 12505 | 2 | 65.30 | 1 | 5 | 10.840 | 4.710 | 3.630 |
| 936NM | 12506 | 2-1/2 | 194.00 | 1 | 1 | 14.440 | 6.470 | 4.980 |
| 937NM | 12507 | 3 | 194.00 | 1 | 1 | 14.560 | 6.600 | 4.980 |
| 938NM | 12508 | 3-1/2 | 369.00 | 1 | 1 | 17.170 | 7.610 | 6.090 |
| 939NM | 12509 | 4 | 369.00 | 1 | 1 | 17.250 | 7.690 | 6.090 |

PATENTED.



E170558 LR49636



930NM shown

FEATURES AND BENEFITS

- Meets NEC 2014 Section 314.16 Paragraph (C) (2) for conduit bodies with splices, taps, or devices
- Convenient and easy to use
- Saves the time, space, and cost of stocking five different conduit bodies (LB, T, LL, LR, C)
- Includes flanges for three openings
- Volume and wire fill marked inside bodies
- Using standard PVC cement, AnyBODY glues onto pipe for easy installation
- AnyBODY NM Cover and Gasket Kits available soon
- All gaskets are secured and maintain a rain-tight seal



935NM
2" AnyBODY
Showing Conversion
to LR

Cover Plate

1. Remove cover plate.
2. Remove flange.
3. Reinstall cover plate and flange in the appropriate opening to convert AnyBODY to the desired configuration.



Insulating Bushings

For Rigid • IMC. Press fit. Holds firmly in place while pulling cables.



EMT400S

NEW!

Example:
Telephone cable protected by Rigid insulating bushing.


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|---------------------------|--------------------------|------------|----------|---------|-------|-------|
| RGD50 | 51930 | 1/2 | 100 | 1000 | .531 | .989 |
| RGD75 | 51932 | 3/4 | 100 | 1000 | .531 | 1.185 |
| RGD100 | 51933 | 1 | 100 | 100 | .625 | 1.542 |
| RGD125 | 51934 | 1-1/4 | 100 | 100 | .625 | 1.891 |
| RGD150 | 51935 | 1-1/2 | 100 | 100 | .625 | 2.062 |
| RGD200 | 51936 | 2 | 50 | 50 | .625 | 2.655 |
| EMT250* | 12240 | 2-1/2 | 25 | 25 | 1.225 | 3.062 |
| EMT300* | 12245 | 3 | 25 | 25 | 1.225 | 3.690 |
| EMT350* | 12250 | 3-1/2 | 25 | 25 | 1.231 | 4.187 |
| EMT400* | 12255 | 4 | 25 | 25 | 1.233 | 4.815 |
| Split Insulating Bushings | | | | | | |
| EMT250S* | 12270 | 2-1/2 | 25 | 25 | 1.240 | 3.065 |
| EMT300S* | 12271 | 3 | 25 | 25 | 1.240 | 3.695 |
| EMT350S* | 12272 | 3-1/2 | 25 | 25 | 1.240 | 4.311 |
| EMT400S* | 22001 | 4 | 25 | 25 | 1.240 | 4.812 |

See page B-1 for EMT Insulating Bushings size 1/2" through 4".

*Can also be used for EMT.



E105706 LR49636



EMT200S - EMT400S





NEW!

The new EMT400S insulating bushing is split for easy installation when cables are already in place. They press fit onto conduit and secure with a cable tie. When used for cable protection only, these insulating bushings are a perfect substitution for costly fittings.

Arlington's Rigid Insulating Bushings protect cables from abrasion by rigid. Examples: Power, Cable TV, computer datalines, telephone/modem, a/v cables, alarm systems, security systems. Rigid is often used to protect cables where damage could occur in a house or building.

Note: Meets 2014 NEC code requirements for 300.15(c) protection. Listed for use in environmental air handling spaces per 2014 NEC code requirements 300.22(c).



Place board over bushing and tap onto Rigid or EMT with hammer.

Zinc Combination Couplings

EMT to Rigid


EMT set-screw to screw-in flexible metal conduit. Zinc die-cast.



2400

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| 2400 | 06920 | 1/2" | 50 | 50 | 1.000 | 1.267 | .946 |
| 2410 | 06921 | 3/4" | 50 | 50 | 1.000 | 1.412 | 1.200 |
| 2411 | 06922 | 3/4" | 50 | 50 | 1.210 | 1.475 | 1.200 |

Use with any listed fitting.



Conduit Caps


Conduit cap and insulating bushing.



RGD200C

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| RGD50C | 51937 | 1/2 | 100 | 1000 | .531 | .840 |
| RGD75C | 51938 | 3/4 | 100 | 1000 | .531 | 1.056 |
| RGD100C | 51939 | 1 | 100 | 100 | .625 | 1.280 |
| RGD125C | 51940 | 1-1/4 | 100 | 100 | .625 | 1.660 |
| RGD150C | 51941 | 1-1/2 | 100 | 100 | .625 | 1.915 |
| RGD200C | 51942 | 2 | 50 | 50 | .625 | 2.377 |
| EMT250C† | 12215 | 2-1/2 | 25 | 25 | 1.225 | 3.062 |
| EMT300C† | 12217 | 3 | 25 | 25 | 1.225 | 3.690 |
| EMT350C† | 12219 | 3-1/2 | 25 | 25 | 1.231 | 4.187 |
| EMT400C† | 12221 | 4 | 25 | 25 | 1.233 | 4.815 |

See page B-1 for EMT Insulating Bushings size 1/2" through 4".
† Can also be used for EMT.



Use this capped version to seal off conduit during concrete pours.
Then remove cap/seal with razor knife or use screwdriver to punch hole in cap. (EMT300C)



String can be used to aid removal.

Long Conduit Nipples


Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| 501L | 50130 | 1/2 | 100 | 1000 | .900 | .800 | 1.055 |
| 502L | 50230 | 3/4 | 50 | 500 | .900 | .800 | 1.300 |
| 503L | 50330 | 1 | 25 | 100 | .900 | .770 | 1.670 |



E60812 LR49636




Conduit Nipples

Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| 501 | 00501 | 1/2 | 100 | 1000 | .585 | .425 | 1.050 |
| 502 | 00502 | 3/4 | 50 | 500 | .614 | .514 | 1.310 |
| 503 | 00503 | 1 | 25 | 100 | .654 | .518 | 1.616 |
| 504 | 00504 | 1-1/4 | 10 | 100 | .810 | .578 | 1.978 |
| 505 | 00505 | 1-1/2 | 10 | 100 | .835 | .613 | 2.410 |
| 506 | 00506 | 2 | 10 | 50 | .888 | .676 | 2.945 |
| 507 | 00507 | 2-1/2 | 10 | 30 | 1.200 | .876 | 3.555 |
| 508 | 00508 | 3 | 10 | 10 | 1.375 | 1.008 | 4.390 |
| 509 | 00509 | 3-1/2 | 10 | 10 | 1.375 | 1.008 | 4.925 |
| 510 | 00510 | 4 | 5 | 5 | 1.375 | 1.011 | 5.420 |
| 511† | 00511 | 5 | 1 | 1 | 1.700 | 1.232 | 5.812 |
| 512† | 00512 | 6 | 1 | 1 | 1.500 | 1.500 | 7.000 |

† Malleable.




Conduit Nipples

Non-metallic.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| NM501 | 54501 | 1/2 | 100 | 1000 | .754 | .654 | 1.047 |
| NM501EL | 54584 | 1/2 | 100 | 1000 | 1.884 | 1.784 | .946 |
| NM502 | 54502 | 3/4 | 50 | 500 | .779 | .534 | 1.300 |
| NM503 | 54503 | 1 | 25 | 100 | .900 | .575 | 1.592 |
| NM504 | 54504 | 1-1/4 | 10 | 100 | .900 | .575 | 2.415 |
| NM505 | 54505 | 1-1/2 | 10 | 100 | .912 | .662 | 2.623 |
| NM506 | 54506 | 2 | 10 | 50 | .975 | .570 | 3.096 |




3-Piece Coupling Rigid • IMC

Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|-------|-------|-------|
| 200 | 00200 | 1/2 | 50 | 1.430 | 1.310 | 1.250 |
| 201 | 00201 | 3/4 | 50 | 1.520 | 1.610 | 1.560 |
| 202 | 00202 | 1 | 25 | 1.700 | 2.125 | 2.100 |
| 203 | 00203 | 1-1/4 | 25 | 2.125 | 2.400 | 2.415 |
| 204 | 00204 | 1-1/2 | 25 | 2.125 | 2.890 | 2.940 |
| 205 | 00205 | 2 | 20 | 2.360 | 3.400 | 3.500 |
| 206 | 00206 | 2-1/2 | 10 | 2.520 | 4.030 | 4.390 |
| 207 | 00207 | 3 | 5 | 2.580 | 4.620 | 4.930 |
| 208 | 00208 | 3-1/2 | 5 | 2.645 | 5.350 | 5.425 |
| 209 | 00209 | 4 | 2 | 3.420 | 5.870 | 5.780 |
| 210† | 00210 | 5 | 1 | 4.375 | 7.000 | 7.000 |
| 211† | 00211 | 6 | 1 | 4.375 | 8.250 | 8.250 |

† Malleable.




3/4" Offset Nipples

Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|
| 6A2 | 61200 | 1/2 | 1/2 | 20 | 200 | 2.460 | 1.000 |
| 6A3 | 61300 | 3/4 | 3/4 | 10 | 100 | 2.560 | 1.220 |
| 6A4 | 61400 | 1 | 1 | 10 | 100 | 2.535 | 1.525 |
| 6A5 | 61500 | 1-1/4 | 1-1/4 | 10 | 40 | 2.937 | 1.910 |
| 6A6 | 61600 | 1-1/2 | 1-1/2 | 10 | 40 | 3.080 | 2.125 |
| 6A7 | 61700 | 2 | 2 | 10 | 10 | 3.145 | 2.665 |
| 6A8† | 61800 | 2-1/2 | 2-1/2 | 2 | 2 | 3.970 | 3.280 |
| 6A9† | 61900 | 3 | 3 | 1 | 1 | 4.420 | 3.795 |
| 6A10† | 64000 | 3-1/2 | 3-1/2 | 1 | 1 | 5.000 | 4.477 |
| 6A11† | 64002 | 4 | 4 | 1 | 1 | 5.000 | 4.960 |

† Malleable.




Conduit Locknuts

Plated steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 401 | 00401 | 1/2 | 200 | 2000 | 1.125 | .130 |
| 402 | 00402 | 3/4 | 100 | 1000 | 1.383 | .140 |
| 403 | 00403 | 1 | 100 | 1000 | 1.730 | .160 |
| 404 | 00404 | 1-1/4 | 50 | 250 | 2.080 | .187 |
| 405 | 00405 | 1-1/2 | 50 | 250 | 2.376 | .187 |
| 406 | 00406 | 2 | 25 | 250 | 2.890 | .250 |
| 407 | 00407 | 2-1/2 | 30 | 30 | 3.470 | .250 |
| 408 | 00408 | 3 | 25 | 25 | 4.165 | .250 |
| 409 | 00409 | 3-1/2 | 25 | 25 | 4.700 | .275 |
| 410 | 00410 | 4 | 25 | 25 | 5.320 | .275 |
| 411 | 00411 | 5 | 10 | 10 | 6.487 | .450 |
| 412 | 00412 | 6 | 10 | 10 | 7.830 | .450 |




Plastic Insulating Bushings

105° C rated.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 440 | 00440 | 1/2 | 100 | 1000 | 1.050 | .365 |
| 441 | 00441 | 3/4 | 100 | 1000 | 1.280 | .390 |
| 442 | 00442 | 1 | 50 | 500 | 1.632 | .490 |
| 443 | 00443 | 1-1/4 | 25 | 250 | 1.986 | .535 |
| 444 | 00444 | 1-1/2 | 25 | 250 | 2.160 | .550 |
| 445 | 00445 | 2 | 25 | 125 | 2.680 | .600 |
| 446 | 00446 | 2-1/2 | 10 | 100 | 3.150 | .635 |
| 447 | 00447 | 3 | 10 | 50 | 3.800 | .725 |
| 448 | 00448 | 3-1/2 | 10 | 50 | 4.275 | .725 |
| 449 | 00449 | 4 | 10 | 50 | 4.775 | .750 |
| 4491 | 04491 | 5 | 5 | 5 | 6.350 | .975 |
| 4492 | 04492 | 6 | 5 | 5 | 7.475 | .975 |




Combination Threaded Rigid and Set-Screw EMT to Box

90° pulling elbows with cover and gasket. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 9100 | 91005 | 1/2 | 5 | 50 | 2.030 | 1.945 |
| 9110 | 91100 | 3/4 | 5 | 50 | 2.260 | 2.140 |
| 9120 | 50165 | 1 | 5 | 25 | 2.610 | 2.610 |
| 9130 | 50167 | 1-1/4 | 2 | 10 | 3.037 | 3.037 |

See hub illustration on page B-8.




Combination Threaded Rigid and Set-Screw EMT 90° Pulling Elbow

90° pulling elbows with cover and gasket. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| HL5000 | 83105 | 1/2 | 10 | 100 | 2.120 | 2.120 |
| HL7500 | 83175 | 3/4 | 5 | 50 | 2.380 | 2.380 |
| HL100 | 50171 | 1 | 5 | 25 | 3.040 | 3.040 |
| HL125 | 50173 | 1-1/4 | 2 | 10 | 3.900 | 3.900 |

See hub illustration on page B-8.




Watertight Conduit Hubs

For rigid • IMC conduit. With insulated throat. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|---------|-------|-------|
| WH1 | 58100 | 1/2 | 10 | 1.325 | 1.325 |
| WH2 | 58200 | 3/4 | 10 | 1.450 | 1.512 |
| WH3 | 58300 | 1 | 10 | 1.450 | 1.790 |
| WH4 | 58400 | 1-1/4 | 5 | 1.575 | 2.295 |
| WH5 | 58500 | 1-1/2 | 2 | 1.700 | 2.450 |
| WH6 | 58600 | 2 | 2 | 1.700 | 2.875 |
| WH7 | 58700 | 2-1/2 | 1 | 2.045 | 3.325 |
| WH8 | 58800 | 3 | 1 | 2.150 | 4.040 |
| WH9 | 58900 | 3-1/2 | 1 | 2.420 | 4.550 |
| WH10 | 58101 | 4 | 1 | 2.420 | 5.030 |
| WH11† | 58103 | 5 | 1 | 3.000 | 6.750 |
| WH12† | 58105 | 6 | 1 | 3.085 | 7.600 |

† Malleable.



Steel Sealing Locknut


With PVC molded seal.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| SL50 | 13500 | 1/2 | 50 | 50 | 1.125 | .230 |
| SL75 | 13750 | 3/4 | 50 | 50 | 1.375 | .240 |
| SL100 | 13100 | 1 | 25 | 25 | 1.715 | .260 |
| SL125 | 13125 | 1-1/4 | 25 | 25 | 2.065 | .300 |
| SL150 | 13150 | 1-1/2 | 25 | 25 | 2.375 | .300 |
| SL200 | 13200 | 2 | 25 | 25 | 2.885 | .350 |
| SL250 | 13250 | 2-1/2 | 10 | 10 | 3.450 | .350 |
| SL300 | 13300 | 3 | 10 | 10 | 4.125 | .350 |
| SL350 | 13350 | 3-1/2 | 10 | 10 | 4.675 | .375 |
| SL400 | 13400 | 4 | 10 | 10 | 5.225 | .375 |
| SL500 | 13501 | 5 | 10 | 10 | 6.487 | .550 |
| SL600 | 13600 | 6 | 10 | 10 | 7.830 | .550 |



E60812 LR49636



Die-Cast Locknuts


Cast thread. Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| DLN1 | 43510 | 1/2 | 200 | 2000 | 1.100 | .160 |
| DLN2 | 43520 | 3/4 | 100 | 1000 | 1.387 | .160 |
| DLN3 | 43530 | 1 | 100 | 500 | 1.685 | .190 |
| DLN4 | 43540 | 1-1/4 | 50 | 250 | 2.115 | .190 |
| DLN5 | 43450 | 1-1/2 | 50 | 250 | 2.370 | .190 |
| DLN6 | 43560 | 2 | 25 | 250 | 2.885 | .190 |
| DLN7 | 43570 | 2-1/2 | 60 | 60 | 3.450 | .250 |
| DLN8 | 43580 | 3 | 50 | 50 | 4.190 | .250 |
| DLN9 | 43590 | 3-1/2 | 50 | 50 | 4.700 | .250 |
| DLN10 | 43511 | 4 | 30 | 30 | 5.300 | .250 |




E60812 LR49636



Reducing Washers

Plated steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------|----------|---------|-------|-------|-------|
| RW1 | 95100 | 3/4 x 1/2 | 250 | 1000 | .870 | 1.420 | .035 |
| RW2 | 95200 | 1 x 1/2 | 100 | 400 | .870 | 1.710 | .035 |
| RW3 | 95300 | 1 x 3/4 | 100 | 400 | 1.060 | 1.710 | .035 |
| RW4 | 95400 | 1-1/4 x 1/2 | 200 | 200 | .870 | 2.080 | .035 |
| RW5 | 95500 | 1-1/4 x 3/4 | 200 | 200 | 1.060 | 2.080 | .035 |
| RW6 | 95600 | 1-1/4 x 1 | 200 | 200 | 1.380 | 2.080 | .035 |
| RW7 | 95700 | 1-1/2 x 1/2 | 100 | 100 | .870 | 2.635 | .035 |
| RW8 | 95800 | 1-1/2 x 3/4 | 100 | 100 | 1.060 | 2.635 | .035 |
| RW9 | 95900 | 1-1/2 x 1 | 100 | 100 | 1.335 | 2.635 | .035 |
| RW10 | 95101 | 1-1/2 x 1-1/4 | 100 | 100 | 1.690 | 2.635 | .035 |
| RW11 | 95110 | 2 x 1/2 | 50 | 50 | .870 | 3.265 | .035 |
| RW12 | 95120 | 2 x 3/4 | 50 | 50 | 1.060 | 3.265 | .035 |
| RW13 | 95130 | 2 x 1 | 50 | 50 | 1.335 | 3.265 | .035 |
| RW14 | 95140 | 2 x 1-1/4 | 50 | 50 | 1.690 | 3.265 | .035 |
| RW15 | 95150 | 2 x 1-1/2 | 50 | 50 | 1.935 | 3.265 | .035 |
| RW16 | 95160 | 2-1/2 x 1/2 | 50 | 50 | .870 | 3.265 | .035 |
| RW17 | 95170 | 2-1/2 x 3/4 | 50 | 50 | 1.060 | 3.265 | .035 |
| RW18 | 95180 | 2-1/2 x 1 | 50 | 50 | 1.370 | 3.265 | .035 |
| RW19 | 95190 | 2-1/2 x 1-1/4 | 50 | 50 | 1.750 | 3.265 | .035 |
| RW20 | 95201 | 2-1/2 x 1-1/2 | 50 | 50 | 1.935 | 3.265 | .035 |
| RW21 | 95210 | 2-1/2 x 2 | 50 | 50 | 2.425 | 3.265 | .035 |
| RW22 | 95220 | 3 x 1/2 | 25 | 25 | .870 | 4.490 | .040 |
| RW23 | 95230 | 3 x 3/4 | 25 | 25 | 1.060 | 4.490 | .040 |
| RW24 | 95240 | 3 x 1 | 25 | 25 | 1.360 | 4.490 | .045 |
| RW25 | 95250 | 3 x 1-1/4 | 25 | 25 | 1.750 | 4.490 | .040 |
| RW26 | 95260 | 3 x 1-1/2 | 25 | 25 | 1.935 | 4.490 | .040 |
| RW27 | 95270 | 3 x 2 | 25 | 25 | 2.424 | 4.490 | .040 |
| RW28 | 95280 | 3 x 2-1/2 | 25 | 25 | 2.940 | 4.490 | .040 |
| RW29 | 95290 | 3-1/2 x 1/2 | 10 | 10 | .870 | 5.000 | .060 |
| RW30 | 95301 | 3-1/2 x 3/4 | 10 | 10 | 1.060 | 5.000 | .060 |
| RW31 | 95310 | 3-1/2 x 1 | 10 | 10 | 1.360 | 5.000 | .060 |
| RW32 | 95320 | 3-1/2 x 1-1/4 | 10 | 10 | 1.750 | 5.000 | .060 |
| RW33 | 95330 | 3-1/2 x 1-1/2 | 10 | 10 | 1.935 | 5.000 | .060 |
| RW34 | 95340 | 3-1/2 x 2 | 10 | 10 | 2.425 | 5.000 | .060 |
| RW35 | 95350 | 3-1/2 x 2-1/2 | 10 | 10 | 2.920 | 5.000 | .060 |
| RW36 | 95360 | 3-1/2 x 3 | 10 | 10 | 3.560 | 5.000 | .060 |
| RW37 | 95370 | 4 x 1/2 | 10 | 10 | .870 | 5.500 | .065 |
| RW38 | 95380 | 4 x 3/4 | 10 | 10 | 1.060 | 5.500 | .065 |
| RW39 | 95390 | 4 x 1 | 10 | 10 | 1.360 | 5.500 | .065 |
| RW40 | 95401 | 4 x 1-1/4 | 10 | 10 | 1.715 | 5.500 | .065 |
| RW41 | 95410 | 4 x 1-1/2 | 10 | 10 | 1.970 | 5.500 | .065 |
| RW42 | 95420 | 4 x 2 | 10 | 10 | 2.435 | 5.500 | .065 |
| RW43 | 95430 | 4 x 2-1/2 | 10 | 10 | 2.920 | 5.500 | .065 |
| RW44 | 95440 | 4 x 3 | 10 | 10 | 3.560 | 5.500 | .065 |
| RW45 | 95450 | 4 x 3-1/2 | 10 | 10 | 4.050 | 5.500 | .065 |



E181788 LR104691

Pipe Hangers

One-piece. Non-metallic.
UV rated.



NM1000



NM2000



NM2080


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | RIGID SIZE* | EMT SIZE | LT SIZE | FLEX SIZE | ENT SIZE | COPPER TUBING | COPPER PIPE | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-----------|----------|---------------|-------------|---------|-------|-------|-------|
| NM1000† | 54615 | - | - | - | - | - | - | - | 100 | 1.563 | .777 | 1.563 |
| NM1900 | 54514 | - | - | 5/16 | - | - | 1/2 | - | 100 | .844 | .668 | 1.270 |
| NM2000 | 54515 | - | 1/2 | 3/8 | - | - | - | 3/8 | 100 | .922 | .795 | 1.412 |
| NM2005 | 54525 | 1/2 | - | 1/2 | 1/2 | 1/2 | - | 1/2 | 100 | 1.077 | .795 | 1.588 |
| NM2010 | 54516 | - | 3/4 | - | - | - | 3/4 | - | 100 | 1.178 | .800 | 1.667 |
| NM2015 | 54526 | 3/4 | - | 3/4 | 3/4 | 3/4 | - | 3/4 | 100 | 1.277 | .800 | 1.826 |
| NM2020 | 54517 | - | 1 | - | - | - | 1 | - | 100 | 1.377 | .790 | 1.983 |
| NM2025 | 54518 | 1 | - | 1 | 1 | 1 | - | 1 | 100 | 1.582 | .830 | 2.180 |
| NM2030 | 54528 | - | 1-1/4 | - | - | - | 1-1/4 | - | 100 | 1.700 | .820 | 2.346 |
| NM2040 | 54519 | 1-1/4 | 1-1/2 | - | - | - | 1-1/2 | 1-1/4 | 100 | 1.830 | .830 | 2.523 |
| NM2045 | 54544 | 1-1/2 | - | 1-1/2 | 1-1/2 | - | - | 1-1/2 | 100 | 2.212 | .860 | 2.846 |
| NM2150 | 54547 | - | - | - | - | - | 2 | - | 50 | 2.640 | .910 | 3.100 |
| NM2050 | 54520 | 2 | 2 | 2 | 2 | - | - | 2 | 50 | 3.020 | .910 | 3.470 |
| NM2060 | 54521 | 2-1/2 | 2-1/2 | 2-1/2 | 2-1/2 | - | - | - | 50 | 3.460 | 1.115 | 5.095 |
| NM2070 | 54522 | 3 | 3 | 3 | 3 | - | - | - | 25 | 4.224 | 1.362 | 6.153 |
| NM2080 | 54523 | 3-1/2 | 3-1/2 | 3-1/2 | 3-1/2 | - | - | - | 25 | 4.720 | 1.548 | 7.000 |
| NM2090 | 54592 | 4 | 4 | 4 | 4 | - | - | - | 10 | 5.365 | 1.743 | 7.850 |



E161207 LR49636

* Rigid sizes also same for IMC and PVC.
For additional information on QuickLATCH plumbing applications, call or visit our website.

† PATENTED.



FEATURES AND BENEFITS

- Saves 25 seconds per installation...over 20¢ at \$30.00 per hour labor rate
- Costs the same as a steel pipe hanger with bolt and nut
- Conduit snaps into place, locking automatically
- Accommodates thinwall, rigid conduit, PVC conduit, or copper
- Mounts horizontally or vertically
- UV rated for outdoor application
- Corrosion resistant
- Listed for use in environmental air handling spaces per 2014 NEC code requirement 300.22(c)
- 2-1/2" to 4" hangers feature tabs with openings for the optional securing of a cable tie

QuickLATCH™
Use it anywhere
you would use a pipe hanger!

Installation Instructions



To Remove
Use a screwdriver to lift tab.

1. Mount to wall, strut, stud, or threaded rod up to 1/4-20
2. Press pipe down firmly into QuickLATCH to lock it in place
3. That's it!

Scan For Video




Pipe Hangers

Plated steel. With nut and bolt.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | RIGID SIZE | EMT SIZE | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|------------|----------------|---------|-------|-------|-------|
| 2000 | 02000 | 0 | 3/8, 1/2 | 1/2 | 100 | 1.875 | 0.810 | 0.750 |
| 2010 | 02010 | 1 | 3/4 | 3/4 | 100 | 2.150 | 0.850 | 0.750 |
| 2020 | 02020 | 2 | 1 | 1 | 100 | 2.485 | 0.970 | 0.875 |
| 2025 | 02025 | 2-1/2 to 3 | 1-1/4 | 1-1/4 to 1-1/2 | 100 | 3.265 | 1.206 | 0.875 |
| 2040 | 02040 | 4 | 1-1/2 | - | 100 | 3.220 | 1.090 | 1.000 |
| 2050 | 02050 | 5 | 2 | 2 | 50 | 4.090 | 1.220 | 1.000 |
| 2060 | 02060 | 6 | 2-1/2 | 2-1/2 | 50 | 4.820 | 1.150 | 1.250 |
| 2070 | 02070 | 7 | 3 | 3 | 25 | 5.180 | 1.160 | 1.250 |
| 2080 | 02080 | 8 | 3-1/2 | 3-1/2 | 25 | 5.740 | 1.140 | 1.250 |
| 2090 | 02090 | 9 | 4 | 4 | 10 | 6.500 | 1.172 | 1.250 |




Pipe Hangers

With formed thread in one end of the hanger, nut not required. Plated steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | RIGID SIZE | EMT SIZE | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|------------|----------|---------|-------|-------|-------|
| 2200 | 22000 | 0 | 3/8 x 1/2 | 1/2 | 100 | 1.875 | .990 | .750 |
| 2210 | 22100 | 1 | 3/4 | 3/4 | 100 | 2.175 | 1.260 | .875 |
| 2220 | 22200 | 2 | 1 | 1 | 100 | 2.370 | 1.295 | .875 |
| 2225 | 22250 | 2-1/2 | - | 1-1/4 | 100 | 3.175 | 1.965 | .875 |
| 2230 | 22300 | 3 | 1-1/4 | 1-1/2 | 100 | 3.255 | 1.875 | .875 |
| 2240 | 22400 | 4 | 1-1/2 | - | 100 | 3.780 | 2.220 | 1.065 |
| 2250 | 22500 | 5 | 2 | 2 | 50 | 4.100 | 2.450 | 1.210 |




Reducing Bushings

Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|---------------|----------|---------|-------|-------|
| 522 | 00522 | 3/4 x 1/2 | 50 | 500 | .650 | .920 |
| 523 | 00523 | 1 x 1/2 | 25 | 100 | .715 | 1.125 |
| 524 | 00524 | 1 x 3/4 | 25 | 100 | .715 | 1.125 |
| 525 | 00525 | 1-1/4 x 1/2 | 25 | 25 | .820 | 1.470 |
| 526 | 00526 | 1-1/4 x 3/4 | 25 | 25 | .820 | 1.470 |
| 527 | 00527 | 1-1/4 x 1 | 25 | 25 | .820 | 1.470 |
| 528 | 00528 | 1-1/2 x 1/2 | 25 | 25 | .850 | 1.700 |
| 529 | 00529 | 1-1/2 x 3/4 | 25 | 25 | .850 | 1.700 |
| 530 | 00530 | 1-1/2 x 1 | 25 | 25 | .850 | 1.700 |
| 531 | 00531 | 1-1/2 x 1-1/4 | 25 | 25 | .850 | 1.700 |
| 532 | 00532 | 2 x 1/2 | 10 | 10 | .970 | 2.230 |
| 533 | 00533 | 2 x 3/4 | 10 | 10 | .970 | 2.230 |
| 534 | 00534 | 2 x 1 | 10 | 10 | .970 | 2.230 |
| 535 | 00535 | 2 x 1-1/4 | 10 | 10 | .970 | 2.230 |
| 536 | 00536 | 2 x 1-1/2 | 10 | 10 | .970 | 2.230 |



Larger Reducing Bushings


Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------|----------|---------|-------|-------|-------|
| 1274 | 01274 | 2-1/2 x 1-1/4 | 5 | 5 | 2.090 | .430 | 2.845 |
| 1275 | 01275 | 2-1/2 x 1-1/2 | 5 | 5 | 1.125 | .430 | 2.820 |
| 1276 | 01276 | 2-1/2 x 2 | 5 | 5 | 1.200 | .300 | 3.485 |
| 1283 | 01283 | 3 x 1 | 5 | 5 | 1.785 | .500 | 4.075 |
| 1284 | 01284 | 3 x 1-1/4 | 5 | 5 | 2.100 | .410 | 3.445 |
| 1285 | 01285 | 3 x 1-1/2 | 5 | 5 | 2.020 | .440 | 3.460 |
| 1286 | 01286 | 3 x 2 | 5 | 5 | 2.000 | .400 | 3.380 |
| 1287 | 01287 | 3 x 2-1/2 | 5 | 5 | 1.390 | .375 | 4.395 |
| 1296 | 01296 | 3-1/2 x 2 | 2 | 2 | 1.905 | .565 | 4.575 |
| 1297 | 01297 | 3-1/2 x 2-1/2 | 2 | 2 | 2.020 | .450 | 3.945 |
| 1298 | 01298 | 3-1/2 x 3 | 2 | 2 | 1.385 | .380 | 4.920 |
| 1307 | 01307 | 4 x 2-1/2 | 2 | 2 | 2.070 | .570 | 5.250 |
| 1308 | 01308 | 4 x 3 | 2 | 2 | 1.775 | .500 | 5.250 |
| 1309 | 01309 | 4 x 3-1/2 | 2 | 2 | 1.400 | .375 | 5.420 |



Reducing bushings, unlike reducing washers, maintain grounding path and are able to pass UL high current testing.




1-Hole Rigid Straps

Snap-on type. Plated steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|-------|
| 340 | 00340 | 1/2 | 50 | 500 | 1.915 | .875 | .625 | .250 |
| 341 | 00341 | 3/4 | 50 | 500 | 2.230 | 1.050 | .750 | .250 |
| 342 | 00342 | 1 | 25 | 250 | 2.615 | 1.295 | .875 | .312 |
| 343 | 00343 | 1-1/4 | 25 | 100 | 2.975 | 1.630 | .875 | .375 |
| 344 | 00344 | 1-1/2 | 25 | 100 | 3.660 | 1.860 | 1.000 | .437 |
| 345 | 00345 | 2 | 25 | 100 | 4.150 | 2.240 | 1.125 | .562 |
| 346 | 00346 | 2-1/2 | 25 | 25 | 4.927 | 2.958 | 1.245 | .550 |
| 347 | 00347 | 3 | 25 | 25 | 5.560 | 3.441 | 1.250 | .550 |
| 348 | 00348 | 3-1/2 | 10 | 10 | 6.337 | 3.951 | 1.250 | .575 |
| 349 | 00349 | 4 | 10 | 10 | 6.811 | 4.441 | 1.240 | .575 |




2-Hole Rigid Straps

Snap-on type. Plated steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|-------|
| 350 | 00350 | 1/2 | 50 | 500 | 2.440 | .900 | .620 | .200 |
| 351 | 00351 | 3/4 | 50 | 500 | 2.810 | 1.060 | .690 | .200 |
| 352 | 00352 | 1 | 25 | 250 | 3.350 | 1.365 | .750 | .275 |
| 353 | 00353 | 1-1/4 | 25 | 100 | 4.110 | 1.700 | .865 | .275 |
| 354 | 00354 | 1-1/2 | 25 | 100 | 4.450 | 1.960 | .940 | .275 |
| 355 | 00355 | 2 | 25 | 150 | 5.350 | 2.240 | .995 | .325 |
| 356 | 00356 | 2-1/2 | 25 | 25 | 6.025 | 2.855 | .985 | .345 |
| 357 | 00357 | 3 | 25 | 25 | 6.460 | 3.425 | .995 | .345 |
| 358 | 00358 | 3-1/2 | 10 | 10 | 7.300 | 3.925 | .990 | .345 |
| 359 | 00359 | 4 | 10 | 10 | 7.895 | 4.435 | .995 | .345 |




1-Hole Straps

For rigid conduit. Malleable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| 3100 | 03100 | 1/2 | 50 | 500 | 1.437 | .625 | .312 |
| 3101 | 03101 | 3/4 | 50 | 500 | 1.750 | .750 | .312 |
| 3102 | 03102 | 1 | 25 | 500 | 2.125 | .937 | .312 |
| 3103 | 03103 | 1-1/4 | 25 | 250 | 2.375 | 1.062 | .437 |
| 3104 | 03104 | 1-1/2 | 25 | 250 | 2.750 | 1.062 | .500 |
| 3105 | 03105 | 2 | 25 | 150 | 3.937 | 1.250 | .562 |
| 3106 | 03106 | 2-1/2 | 25 | 25 | 3.937 | 1.250 | .562 |
| 3107 | 03107 | 3 | 25 | 25 | 5.187 | 1.750 | .562 |
| 3108 | 03108 | 3-1/2 | 10 | 10 | 5.562 | 2.125 | .750 |
| 3109 | 03109 | 4 | 10 | 10 | 6.500 | 2.250 | .750 |




Clamp Back Spacer

Malleable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| CB1 | 30100 | 1/2 | 50 | 500 | 2.062 | 1.000 | .500 |
| CB2 | 30105 | 3/4 | 50 | 500 | 2.375 | 1.062 | .500 |
| CB3 | 30110 | 1 | 25 | 500 | 3.000 | 1.250 | .562 |
| CB4 | 30115 | 1-1/4 | 25 | 250 | 3.500 | 1.500 | .653 |
| CB5 | 30120 | 1-1/2 | 25 | 250 | 4.000 | 1.600 | .812 |
| CB6 | 30125 | 2 | 25 | 150 | 4.750 | 2.000 | .986 |
| CB7 | 30130 | 2-1/2 | 25 | 25 | 5.800 | 2.437 | .812 |
| CB8 | 30135 | 3 | 25 | 25 | 6.687 | 2.625 | .875 |
| CB9 | 30140 | 3-1/2 | 10 | 10 | 7.125 | 2.875 | 1.062 |
| CB10 | 30145 | 4 | 10 | 10 | 8.875 | 3.062 | 1.062 |



FOR OUTDOOR FIXTURES & DEVICES

GARD-N-POST™

UL LISTED ENCLOSURES & SUPPORTS



GP19


UL Listed Support for Fixtures and/or Devices Power & Low Voltage Openings



GPD19

UL Listed Enclosure with EXTRA-DUTY Code Compliance

Made in USA



Arlington's **GARD-N-POST** enclosures and supports offer the attractive, safe, and easy way to install a light fixture and/or one or two devices outdoors! Power and low voltage in the same post.

- Non-metallic, heavy-duty UV rated plastic
- Damage resistant
- No chipping or loss of color
- GARD-N-POST in a variety of styles from 9" to 73" tall



Molded-in colors!

MOLDED-IN COLOR. NO CHIPPING!



Arlington



19.5" & 26" Supports for Outdoor Light Fixtures

For installing a light fixture and/or GFCI devices outdoors. UV rated plastic for long outdoor life. Four non-chipping colors.



GP19B



GP26G

Comes complete with...

Installed 3/4" x 1/2" NPT metal reducing bushing, locknut with copper ground wire for fixture installation, (2) blank device plates, gaskets & screws, plug for top hole (when fixture is not installed), low voltage separator, and removable KO plate.


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|--------|
| GP19B | 77086 | Black | 1 | 6 | 8.110 | 3.361 | 19.500 |
| GP19BR | 77087 | Bronze | 1 | 6 | 8.110 | 3.361 | 19.500 |
| GP19G | 77088 | Green | 1 | 6 | 8.110 | 3.361 | 19.500 |
| GP19W | 77089 | White | 1 | 6 | 8.110 | 3.361 | 19.500 |
| GP26B | 77090 | Black | 1 | 6 | 8.110 | 3.361 | 26.000 |
| GP26BR | 77092 | Bronze | 1 | 6 | 8.110 | 3.361 | 26.000 |
| GP26G | 77094 | Green | 1 | 6 | 8.110 | 3.361 | 26.000 |
| GP26W | 77096 | White | 1 | 6 | 8.110 | 3.361 | 26.000 |

Add suffix "GC" to Catalog # when ordering in Canada, for example GP19BGC.

PATENTED.



E170558 LR49636
CSA listed with grounding lug.



FEATURES AND BENEFITS

- Molded-in color is permanent – unlike painted posts where lawn equipment chips the color off
- Openings on both sides of the post for back-to-back power
- Low voltage separator provided for Power use on one side and Low Voltage on the other (phone, security, & cable TV)
- Built-in stabilizers need no assembly and provide rigid support
- GP19's stabilizers offer greater use of above ground height
- GP26's taller design provides additional height for wiring devices and increased burial depth
- Angle cut post for easy access to underground wiring
- (2) 1/2" KOs for a UL Listed enclosure

OPENINGS ON BOTH SIDES!



Install one or two GFCI Wiring Devices with Weatherproof Cover...

Or add the Low Voltage Separator and run Low Voltage on one side and Power on the other!

19.5" Low-Profile Enclosure with Built-in Cover

For use with a GFCI device. Features clear, extra-duty weatherproof-in-use cover. UV rated plastic for long outdoor life. Four non-chipping colors.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|--------|
| GPD19B | 77020 | Black | 1 | 6 | 7.761 | 6.269 | 8.177 | 19.500 |
| GPD19BR | 77021 | Bronze | 1 | 6 | 7.761 | 6.269 | 8.177 | 19.500 |
| GPD19G | 77022 | Green | 1 | 6 | 7.761 | 6.269 | 8.177 | 19.500 |
| GPD19W | 77023 | White | 1 | 6 | 7.761 | 6.269 | 8.177 | 19.500 |

Add suffix "GC" to Catalog # when ordering in Canada, for example GPD19BGC.

Refer to K-18 for replacement cover DBPV1C.


PATENTED.



E170558 LR49636
CSA listed with grounding lug.

WEATHERPROOF-IN-USE

EXTRA-DUTY



FEATURES AND BENEFITS

- Molded-in color is permanent – unlike painted posts where lawn equipment chips the color off
- Includes clear extra-duty cover for weatherproof while-in-use, GFCI and duplex wall plates
- Installed cover, no gasket necessary
- Meets NEC box support requirements
- Built-in stabilizers need no assembly and provide rigid support
- Code approved installation
- No chipping...colorant runs throughout the product
- Extra Duty Rated

Comes with...

Built-in extra-duty weatherproof-while-in-use cover, standard duplex & GFCI cover plates, and removable KO plate.

Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

COMPARE!



Why install boxes this way...



When you can have a great looking, long-lasting job like this!

COLOR CHART

| | | | |
|--|-------|---|--------|
|  | Black |  | Green |
|  | White |  | Bronze |

35" Gard-N-Post™ Bollard Kit

GARD-N-POST with pagoda-style light fixture included. Post is UV rated plastic for long outdoor life. Two non-chipping colors.



GPBK35B/R

Kit comes with...

GARD-N-POST & metal stabilizer, boot, (pagoda light fixture & decorative spacer or IN-AND-OUT™ cover), (2) blank device plates with gaskets & screws, low voltage separator, and removable KO plate with screws.

Recommended anchors (not included)...

Concrete: (4) 3/8" x 2-1/2 Tapcons®

Cast-In-Place Concrete: (4) 3/8" anchor bolts

Wood Deck: (4) 3/8" bolts with nuts and washers

Tapcons® is a registered trademark of ITW Buildex.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------|----------|---------|-------|-------|--------|--------|-------|
| GPBK35B | 77040 | Black | 1 | 1 | 6.070 | 6.070 | 35.000 | 27.000 | 3.500 |
| GPBK35BR | 77041 | Bronze | 1 | 1 | 6.070 | 6.070 | 35.000 | 27.000 | 3.500 |

Add suffix "GC" to Catalog # when ordering in Canada, for example GPBK35BGC.

PATENTED. ADDITIONAL PATENTS PENDING.



CSA listed with grounding lug.



FEATURES AND BENEFITS

- Molded-in color is permanent – unlike painted posts where lawn equipment chips the color off
- Openings on both sides of the post for back-to-back power
- Low voltage separator provided for Power use on one side and Low Voltage on the other (phone, security, & cable TV)
- Perfect for wood decks, boat docks, and concrete walkways
- Makes a very low cost bollard
- Kit includes everything needed for installation, except anchor bolts, caulking, and bulb.
- Includes Arlington's Large Louvered Pagoda Light Fixture
- (2) combination KOs for a UL Listed enclosure

Installation Instructions



1 Metal support post attaches easily to surface.



2 The non-metallic GARD-N-POST slides over the support post.



3 Both posts are held firmly in place with the supplied screws.



4 Place decorative curb over GARD-N-POST. Slide it down to cover the installation.




5 Press fit spacer to base of lamp.



6 Install pagoda light to post with locknut inside the top of the post. Wire fixture.

37" Gard-N-Post™ Support for Outdoor Light Fixtures

Two-piece, super tall GARD-N-POST™. Supports most light fixtures and/or GFCI wiring devices. UV rated plastic for long outdoor life. Four non-chipping colors.



Add the Low Voltage Separator to run Low Voltage on one side and Power on the other!

Comes complete with...

Installed 3/4" x 1/2" NPT metal reducing bushing, locknut with copper ground wire for fixture installation, (2) blank device plates, gaskets & screws, plug for top hole (when fixture is not installed), low voltage separator, and removable KO plate.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-------------|----------|---------|-------|-------|--------|--------|
| GP37B | 76153 | Black | 1 | 4 | 9.000 | 4.000 | 25.000 | 12.000 |
| GP37BR | 76154 | Bronze | 1 | 4 | 9.000 | 4.000 | 25.000 | 12.000 |
| GP37G | 76156 | Green | 1 | 4 | 9.000 | 4.000 | 25.000 | 12.000 |
| GP37W | 76155 | White | 1 | 4 | 9.000 | 4.000 | 25.000 | 12.000 |

Add suffix "GC" to Catalog # when ordering in Canada, for example GP37BGC.

See GPX18 Extender (optional) on page J-6.


PATENTED. ADDITIONAL PATENTS PENDING.



CSA listed with grounding lug.

FEATURES AND BENEFITS

- Molded-in color is permanent – unlike painted posts where lawn equipment chips the color off
- Openings on both sides of the post for back-to-back power
- Low voltage separator provided for Power use on one side and Low Voltage on the other (phone, security, & cable TV)
- Built-in stabilizers need no assembly and provide rigid support
- Angle cut post for easy access to underground wiring
- (2) combination KOs for a UL Listed enclosure
- May be field modified for time clocks and disconnects



To assemble (with or without the Extender) use standard PVC cement.



9" Post/Deck Mount Support for Outdoor Light Fixtures

Two-piece. Mounts most light fixtures and/or a GFCI wiring device on a 4x4 post or deck. UV rated plastic for long outdoor life. Four non-chipping colors.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|-------|
| GPD9B | 76161 | Black | 1 | 6 | 3.375 | 3.375 | 9.000 | .250 |
| GPD9BR | 76162 | Bronze | 1 | 6 | 3.375 | 3.375 | 9.000 | .250 |
| GPD9G | 76164 | Green | 1 | 6 | 3.375 | 3.375 | 9.000 | .250 |
| GPD9W | 76163 | White | 1 | 6 | 3.375 | 3.375 | 9.000 | .250 |

Add suffix "GC" to Catalog # when ordering in Canada, for example GPD9BGC.

PATENTED. ADDITIONAL PATENTS PENDING.



CSA listed with grounding lug.



FEATURES AND BENEFITS

- Molded-in color is permanent – unlike painted posts where lawn equipment chips the color off
- (2) 1/2" KOs for a UL Listed enclosure
- Metal grounding bushing assembly included

Comes complete with...

Installed 3/4" x 1/2" NPT metal reducing bushing, locknut with copper ground wire for fixture installation, blank device plate, gasket & screws, plug for top hole (when fixture is not installed), removable KO plate, and mounting base.



GPD9B shown with light fixture

Install on a 4x4 post...or a dock!

Optional 18" Extender for 37" Support

Add to GP37 in 18" increments for even more height...up to 73".




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|-------------|----------|---------|--------|-------|
| GPX18B | 76157 | Black | 1 | 4 | 18.000 | 4.000 |
| GPX18BR | 76158 | Bronze | 1 | 4 | 18.000 | 4.000 |
| GPX18G | 76160 | Green | 1 | 4 | 18.000 | 4.000 |
| GPX18W | 76159 | White | 1 | 4 | 18.000 | 4.000 |

Use with GP37 on page J-4.

PATENTED. ADDITIONAL PATENTS PENDING.



Use the Extender to make the 37" GARD-N-POST even taller: add **one** 18" Extender for a 55" height; add a **second** Extender for 73"! For even more options, the GPX18 may be cut (top end only) to **any** desired height! When assembling the Extender with GP37 (see J-5) use standard PVC cement.



19.5" Low-Profile Support Just for Outdoor Light Fixtures

For use with light fixtures exclusively. Accommodates most fixture styles. UV rated plastic for long outdoor life. Four non-chipping colors.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|--------|
| GPL19B | 77000 | Black | 1 | 6 | 7.125 | 2.250 | 19.500 |
| GPL19BR | 77001 | Bronze | 1 | 6 | 7.125 | 2.250 | 19.500 |
| GPL19G | 77002 | Green | 1 | 6 | 7.125 | 2.250 | 19.500 |
| GPL19W | 77003 | White | 1 | 6 | 7.125 | 2.250 | 19.500 |

PATENTED. ADDITIONAL PATENTS PENDING.



FEATURES AND BENEFITS

- Molded-in color is permanent – unlike painted posts where lawn equipment chips the color off
- Streamline design...one of our most competitively priced 19.5" GARD-N-POSTS
- Removable 1/2" KO in cover for photocell installation
- Metal bushing with ground wire for 2- or 3-wire fixtures
- Resists damage from lawn equipment



Comes complete with...

Access panel cover, gasket, installed 3/4" x 1/2" NPT metal grounding bushing and locknut with copper ground wire for fixture installation.


19.5" Low-Profile Support Just for 3-Wire Outdoor Light Fixtures

Non-metallic bushing exclusively for 3-wire light fixtures. UV rated plastic for long outdoor life.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|--------|
| GPLN19B | 69108 | Black | 1 | 6 | 7.125 | 2.250 | 19.500 |
| GPLN19BR | 76192 | Bronze | 1 | 6 | 7.125 | 2.250 | 19.500 |

PATENTED. ADDITIONAL PATENTS PENDING.



FEATURES AND BENEFITS

- Molded-in color is permanent – unlike painted posts where lawn equipment chips the color off
- Streamline design...one of our most competitively priced 19.5" GARD-N-POSTs
- Designed for 3-wire light fixtures
- Comes with a 3/4" NPT threaded opening and an installed 3/4" x 1/2" non metallic reducing bushing for use with 1/2" or 3/4" NPT fixtures.
- Installed cover

Comes complete with...

Access panel cover, gasket, installed 3/4" x 1/2" NPT non-metallic bushing for fixture installation.

GPLN19B shown with light fixture




15" Low-Profile Support Just for 3-Wire Outdoor Light Fixtures

Non-metallic bushing exclusively for 3-wire light fixtures. UV rated plastic for long outdoor life.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|---------|-------|-------|--------|
| GPLN15B | 76205 | Black | 10 | 2.250 | 2.250 | 15.000 |
| GPLN15GR | 76181 | Gray | 10 | 2.250 | 2.250 | 15.000 |

PATENT PENDING.



FEATURES AND BENEFITS

- Streamline design...our most competitively priced GARD-N-POST
- Designed for 3-wire light fixtures
- Comes with a 3/4" NPT threaded opening, and an installed 3/4" x 1/2" non-metallic reducing bushing for use with 1/2" or 3/4" NPT fixtures.
- Installed cover
- Molded-in color is permanent – unlike painted posts where lawn equipment chips the color off

Comes complete with...

Access panel cover, gasket, installed 3/4" x 1/2" NPT non-metallic bushing for fixture installation.

Landscape Light Fixtures

Decorative, 3-wire light fixtures for our GARD-N-POST™ line. Comes in two attractive colors.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | COLOR | BULB | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------|----------------------|---------|----------|---------|-------|-------|-------|
| GPI75B | 77042 | Black | Up to 75 Watt, Flood | 1/2 | 1 | 4 | 4.062 | 4.062 | 8.135 |
| GPI75BR | 76159 | Bronze | Up to 75 Watt, Flood | 1/2 | 1 | 4 | 4.062 | 4.062 | 8.135 |

Note: Uses a (maximum) 75 Watt PAR 16 or a 50 Watt PAR 20 halogen bulb. Bulb not included.



FEATURES AND BENEFITS

- Complements Arlington's GARD-N-POST line
- Powder coated color match
- Made for heavy-duty commercial & residential applications
- Mounts with 1/2" NPT thread
- Perfect for illuminating signs, flagpoles, walkways, buildings, dwellings, driveways, yards and recreational areas
- Adds safety and security



Pagoda-Style Landscape Light Fixtures

Decorative, pagoda-style 3-wire light fixtures for our GARD-N-POST™ line. Durable cast aluminum. Comes in two attractive colors.





| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------|----------|---------|-------|-------|-------|
| GPP60B | 77046 | Black | 1 | 4 | 4.750 | 4.750 | 8.573 |
| GPP60BR | 77047 | Bronze | 1 | 4 | 4.750 | 4.750 | 8.573 |
| GPP60LB | 04605 | Black | 1 | 4 | 6.070 | 6.070 | 8.573 |
| GPP60LBR | 04606 | Bronze | 1 | 4 | 6.070 | 6.070 | 8.573 |

Note: Uses a (maximum) 40 Watt halogen, 40 Watt incandescent, or a 14 Watt fluorescent bulb. Bulb not included.



FEATURES AND BENEFITS

- Complements Arlington's GARD-N-POST line
- Powder coated color match
- Made for heavy-duty commercial & residential applications
- Mounts with 3/4" NPT thread with locking nut
- Made for incandescent, halogen, and energy-saving compact fluorescent bulbs (bulbs not included)
- Perfect for illuminating signs, flagpoles, walkways, buildings, dwellings, driveways, yards, and recreational areas
- Adds safety and security



Low Profile IN BOX™ for New Brick Construction

Recessed electrical box with weatherproof-in-use cover for new brick construction. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Box and white cover are textured/paintable. UV rated plastic for long outdoor life.



DBHB1C

FEATURES AND BENEFITS

- IN BOX's one-piece assembly replaces the installation of an electrical box, siding block, and bubble cover assembly
- Built-in anchor tabs seat IN BOX sleeve into mortar for a super secure installation
- Installs in the wall, so less of it shows outside
- Installed, disposable, mud cover extends all the way over the flange, providing maximum protection during construction
- Install option: Cover is removable for easier device installation
- No gaskets required



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|-------|-------|
| DBHB1C | 77628 | Horizontal/Clear | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.313 | 3.847 |
| DBHB1W | 77630 | Horizontal/White | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.313 | 3.847 |

Replacement covers available on page K-17.

PATENTED. ADDITIONAL PATENTS PENDING.




**WEATHERPROOF-IN-USE
EXTRA-DUTY**

IN BOX for new brick includes...

Box with weatherproof-in-use extra-duty cover, installed bug plugs, (1) standard duplex, (1) standard GFCI face plate, installation screws, (1) NM cable connector, and an in-place, disposable mud cover.

22 cu. in.



Installation Shots



Oversized, installed mud cover offers maximum protection because it extends over the entire flange.



Completed installation with weatherproof-in-use extra-duty cover. DBHB1C shown.

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Low Profile IN BOX™ for New Vinyl Siding Construction

One-piece, recessed electrical box with weatherproof-in-use extra-duty cover for new siding applications. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Box and white cover are textured/paintable. UV rated plastic for long outdoor life.

See page K-8
for our NEW
2-Gang style!



DBVS1C



DBHS1W

FEATURES AND BENEFITS

- IN BOX's one-piece assembly replaces the installation of an electrical box, siding block, and bubble cover assembly
- Installs in the wall, so less of it shows outside
- Outer flange covers cut ends of siding
- Install option: Cover is removable for easier device installation
- No gaskets required



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | SIDING TYPE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|-------------|----------|---------|-------|-------|-------|-------|-------|
| DBVS1C | 14317 | Vertical/Clear | All Types | 1 | 4 | 9.058 | 7.012 | 5.160 | 1.313 | 2.879 |
| DBVS1W | 14318 | Vertical/White | All Types | 1 | 4 | 9.058 | 7.012 | 5.160 | 1.313 | 2.879 |
| DBHS1C | 77600 | Horizontal/Clear | All Types | 1 | 4 | 7.012 | 9.058 | 5.160 | 1.313 | 2.879 |
| DBHS1W | 77602 | Horizontal/White | All Types | 1 | 4 | 7.012 | 9.058 | 5.160 | 1.313 | 2.879 |

Add suffix "GC" to Catalog # when ordering in Canada, for example DBVS1CGC.

Replacement covers available on page K-17.

2-Gang style available on page K-8.

PATENTED. ADDITIONAL PATENTS PENDING.




WEATHERPROOF-IN-USE

EXTRA-DUTY

IN BOX for new siding includes...

Box with weatherproof-in-use extra-duty cover; installed bug plugs; (1) standard duplex and (1) standard GFCI face plate; installation screws; and (1) NM cable connector.



Installation Instructions



1 Cut a 3-1/4" x 5-1/2" hole in substrate. Pull wiring.



2 Install NM cable connector and wire, attach IN BOX to substrate.



3 Install siding, inserting the cut ends of the siding under the outer flange of the IN BOX.



4 Install wiring device per manufacturer's instructions, Local and National Electrical Codes.



Accepts most single gang wiring devices and uses a standard indoor wall plate.



Completed installation with weatherproof-in-use cover. DBVS1C shown.

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Scan For Video



Low Profile IN BOX™ for New Construction Stucco, Textured Surfaces, and Rigid Siding

One-piece, recessed electrical box with weatherproof-in-use extra-duty cover for stucco over masonry or wood construction. Also for cementitious/fiber rigid lap siding. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Box and white cover are textured/paintable. UV rated plastic for long outdoor life.

See page K-8 for our NEW 2-Gang style!



FEATURES AND BENEFITS

- One-piece assembly replaces the installation of an electrical box and bubble cover assembly
- Installs in the wall, so less of it shows outside
- Holes in flange allow stucco to bond firmly
- Install option: Cover is removable for easier device installation

Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|-------|-------|
| DBVM1C | 14315 | Vertical/Clear | 1 | 4 | 9.058 | 7.012 | 5.160 | 1.805 | 3.222 |
| DBVM1W | 14316 | Vertical/White | 1 | 4 | 9.058 | 7.012 | 5.160 | 1.805 | 3.222 |
| DBHM1C | 77608 | Horizontal/Clear | 1 | 4 | 7.012 | 9.058 | 5.160 | 1.805 | 3.222 |
| DBHM1W | 77610 | Horizontal/White | 1 | 4 | 7.012 | 9.058 | 5.160 | 1.805 | 3.222 |

Add suffix "GC" to Catalog # when ordering in Canada, for example DBVM1CGC.

Replacement covers available on page K-17.

2-Gang style available on page K-8.


PATENTED. ADDITIONAL PATENTS PENDING.



**WEATHERPROOF-IN-USE
EXTRA-DUTY**



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.



IN BOX for new stucco, textured surfaces, and rigid siding includes... Box with weatherproof-in-use extra-duty cover; installed bug plugs; (1) standard duplex and (1) standard GFCI face plate; (1) NM cable connector; block bushing with washer; and an in-place, disposable mud cover.

Note: Additional Installation Methods shown on page K-4.

Installation Instructions for New Masonry Construction




1 Make a 3-1/4" x 5-1/2" hole in block. Pull wiring through plastic block bushing and opening in block. Block bushing mounts to interior side of block.

3 Install NM cable connector and wire. Attach recessed IN BOX to block. Holes in flange allow stucco to bond firmly.

4 Install wiring device per manufacturer's instructions, Local, and National Electrical Codes. Accepts most devices and a standard indoor wall plate.



Completed installation with weatherproof-in-use cover. DBVM1C shown.




Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Additional **New Construction** Installation Methods for the DBVM1 & DBHM1 series.

Installation Instructions for Wood Substrate Stucco



1 Make a 3-1/4" x 5-1/2" hole in plywood. Pull wiring through opening.



2 Install NM cable connector and wire. Attach recessed IN BOX to plywood.



3 IN BOX is ready for stucco.



4 Install wiring device per manufacturer's instructions, Local, and National Electrical Codes. Accepts most devices and a standard indoor wall plate. DBVM1W shown.

IN BOX

Installation Instructions for New Rigid Siding - Method 1



1 Install NM cable connector and wire. Attach IN BOX to stud.



2 Install moisture barrier around IN BOX per manufacturer's instructions.



3 Cut rigid siding to fit around IN BOX. Caulk around box.



4 Install wiring device per manufacturer's instructions, Local, and National Electrical Codes. Accepts most devices and a standard indoor wall plate. DBVM1W shown.

Installation Instructions for New Rigid Siding - Method 2



1 Make a 3-1/4" x 5-1/2" hole in plywood. Pull wiring through opening.



2 Install NM cable connector and wire. Attach recessed IN BOX to substrate, then install moisture barrier around box as shown above in Method 1.



3 Cut rigid siding to fit around IN BOX. Caulk around box.



4 Install wiring device per manufacturer's instructions, Local, and National Electrical Codes. Accepts most devices and a standard indoor wall plate. DBVM1W shown.

Low Profile IN BOX™ for Retrofit Siding Construction


Recessed electrical box with weatherproof-in-use extra-duty cover for existing siding construction. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Box and white cover are textured/paintable. UV rated plastic for long outdoor life.



DBVR131C

FEATURES AND BENEFITS

- IN BOX's one-piece assembly replaces the installation of an electrical box, siding block, and bubble cover assembly
- Installs in the wall, so less of it shows outside
- Install option: Cover is removable for easier device installation
- No gaskets required



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | SIDING LAP SIZE | UNIT | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|-----------------|------|---------|-------|-------|-------|-------|-------|
| DBVR131C | 14370 | Vertical/Clear | 1/4" or 5/16" | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.567 | 3.539 |
| DBVR131W | 14375 | Vertical/White | 1/4" or 5/16" | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.567 | 3.539 |
| DBVR141C | 14371 | Vertical/Clear | 1/2" | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.567 | 3.539 |
| DBVR141W | 14376 | Vertical/White | 1/2" | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.567 | 3.539 |
| DBVR151C | 14372 | Vertical/Clear | 5/8" | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.567 | 3.539 |
| DBVR151W | 14377 | Vertical/White | 5/8" | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.567 | 3.539 |
| DBVR171C | 14373 | Vertical/Clear | Dutch | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.567 | 3.539 |
| DBVR171W | 14378 | Vertical/White | Dutch | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.567 | 3.539 |

*Add suffix "GC" to Catalog # when ordering in Canada, for example DBVR131CGC.



Replacement covers available on page K-17.

PATENTED. ADDITIONAL PATENTS PENDING.



WEATHERPROOF-IN-USE
EXTRA-DUTY

22 cu. in.



IN BOX for retrofit siding includes...

Box with weatherproof-in-use extra-duty cover, installed bug plugs, siding profile adapter plate, (1) standard duplex and (1) standard GFCI face plate, (2) sets installation screws, (1) NM cable connector, and (2) rolls of caulk.

Installation Instructions for Existing Siding



Using the siding profile adapter plate as a template, cut hole in existing siding. Pull wiring.



Apply caulk around edges of back of adapter. Press onto siding.



Attach adapter to siding with provided short screws. Trim excess caulk as needed.



Apply caulk to reverse side of IN BOX flange.



Install NM cable connector and wire, then attach with provided long screws. Trim excess caulk as needed. Install wiring device per manufacturer's instructions, Local and National Electrical Codes.

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Low Profile IN BOX™ for Retrofit Siding Construction

Recessed electrical box with weatherproof-in-use extra-duty cover for existing siding construction. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Box and white cover are textured/paintable. UV rated plastic for long outdoor life.




DBHR131W

FEATURES AND BENEFITS

- IN BOX's one-piece assembly replaces the installation of an electrical box, siding block, and bubble cover assembly
- Installs in the wall, so less of it shows outside
- Install option: Cover is removable for easier device installation
- No gaskets required

Siding Profiles



DBHR131
1/4\"/>

DBHR141
1/2\"/>

DBHR151
5/8\"/>

DBHR171
DUTCH
LAP



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | SIDING LAP SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|-----------------|----------|---------|-------|-------|-------|-------|-------|
| DBHR131C | 77612 | Horizontal/Clear | 1/4" or 5/16" | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.567 | 3.539 |
| DBHR131W | 77614 | Horizontal/White | 1/4" or 5/16" | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.567 | 3.539 |
| DBHR141C | 77616 | Horizontal/Clear | 1/2" | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.567 | 3.539 |
| DBHR141W | 77618 | Horizontal/White | 1/2" | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.567 | 3.539 |
| DBHR151C | 77620 | Horizontal/Clear | 5/8" | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.567 | 3.539 |
| DBHR151W | 77622 | Horizontal/White | 5/8" | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.567 | 3.539 |
| DBHR171C | 77624 | Horizontal/Clear | Dutch | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.567 | 3.539 |
| DBHR171W | 77626 | Horizontal/White | Dutch | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.567 | 3.539 |

*Add suffix "GC" to Catalog # when ordering in Canada, for example DBHR131WGC.
Replacement covers available on page K-17.


PATENTED. ADDITIONAL PATENTS PENDING.



WEATHERPROOF-IN-USE
EXTRA-DUTY

IN BOX for retrofit siding includes...

Box with weatherproof-in-use extra-duty cover, installed bug plugs, siding profile adapter plate, (1) standard duplex and (1) standard GFCI face plate, (2) sets installation screws, (1) NM cable connector, and (2) rolls of caulk.



Installation Instructions for Existing Siding



Using the siding profile adapter plate as a template, cut hole in existing siding. Pull wiring.



Apply caulk around edges of back of adapter (see page J-14, step 2a). Press onto siding. Attach adapter to siding with provided short screws. Trim excess caulk as needed.



Apply caulk to reverse side of IN BOX flange (see page J-14, step 3a). Install NM cable connector and wire, then attach with provided long screws. Trim excess caulk as needed.



Install wiring device per manufacturer's instructions, Local and National Electrical Codes. Completed installation with weatherproof-in-use cover. DBHR131W shown.

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Scan For Video



Low Profile IN BOX™ for Flat Surface Retrofit Construction

One-piece, recessed electrical box with weatherproof-in-use extra-duty cover for flat surfaces in existing construction. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Box and white cover are textured/ paintable. UV rated plastic for long outdoor life.

See page K-8 for our NEW 2-Gang style!



DBVR1C



DBHR1W

FEATURES AND BENEFITS

- IN BOX's one-piece assembly replaces the installation of an electrical box and bubble cover assembly
- Installs in the wall, so less of it shows outside
- Use the retrofit IN BOX on plywood, T-111, and other flat surfaces.
- Install option: Cover is removable for easier device installation
- No gaskets required



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|-------|-------|
| DBVR1C | 14313 | Vertical/Clear | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.313 | 3.847 |
| DBVR1W | 14314 | Vertical/White | 1 | 4 | 7.186 | 4.934 | 5.160 | 1.313 | 3.847 |
| DBHR1C | 77604 | Horizontal/Clear | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.313 | 3.847 |
| DBHR1W | 77606 | Horizontal/White | 1 | 4 | 4.934 | 7.186 | 5.160 | 1.313 | 3.847 |

Add suffix "GC" to Catalog # when ordering in Canada, for example DBVR1CGC.

Replacement covers and siding profiles to convert for use on existing siding available on page K-17.

2-Gang style available on page K-8.

PATENTED. ADDITIONAL PATENTS PENDING.




WEATHERPROOF-IN-USE

EXTRA-DUTY

IN BOX for retrofit, flat surfaces includes...

Box with weatherproof-in-use extra-duty cover; installed bug plugs; (1) standard duplex and (1) standard GFCI face plate; (1) set installation screws; (1) NM cable connector; and (1) roll of caulk.



Installation Instructions



1 Cut a 3-1/4" x 5-1/2" hole in substrate. Pull wiring.



2 Apply the supplied caulk around back edges of flange. Install NM cable connector and wire, then press onto surface.



3 Attach IN BOX with stainless steel screws (provided).



4 Install wiring device per manufacturer's instructions, Local and National Electrical Codes.



Accepts most single gang wiring devices, and uses a standard indoor wall plate. DBVR1C shown.



DBVR1W shown. **IN BOX Saves Time. Looks Great!**

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Two-Gang, Low Profile IN BOX™

Two-gang, recessed electrical box with weatherproof-in-use extra-duty cover for flat surfaces, masonry, retrofit, and siding construction (see below for product use). Non-metallic cover and base. Installs two outlets or combo devices. Box and white cover are textured/ paintable. UV rated plastic for long outdoor life.

See page **K-3** for more information.



DBVM2C -
Masonry & textured surfaces

See page **K-7** for more information.



DBVR2W -
Flat surfaces

See page **K-2** for more information.



DBVS2C -
Vinyl siding



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/COVER COLOR | UNIT | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|------|---------|-------|-------|-------|-------|-------|
| DBVM2C | 03962 | 2-Gang, Vertical/Clear | 1 | 4 | 9.058 | 8.992 | 5.142 | 1.919 | 3.223 |
| DBVM2W | 03963 | 2-Gang, Vertical/White | 1 | 4 | 9.058 | 8.992 | 5.142 | 1.919 | 3.223 |
| DBVR2C | 03964 | 2-Gang, Vertical/Clear | 1 | 4 | 7.159 | 6.888 | 5.142 | 1.295 | 3.847 |
| DBVR2W | 03965 | 2-Gang, Vertical/White | 1 | 4 | 7.159 | 6.888 | 5.142 | 1.295 | 3.847 |
| DBVS2C | 03960 | 2-Gang, Vertical/Clear | 1 | 4 | 9.058 | 8.992 | 5.142 | 2.263 | 2.879 |
| DBVS2W | 03961 | 2-Gang, Vertical/White | 1 | 4 | 9.058 | 8.992 | 5.142 | 2.263 | 2.879 |

Add suffix "GC" to Catalog # when ordering in Canada, for example DBVM2CGC.


2-Gang, replacement covers available on page K-17.

PATENTED. ADDITIONAL PATENTS PENDING.



E170558 LR49636

**WEATHERPROOF-IN-USE
EXTRA-DUTY**



DBVM2
34.0 cu. in.

DBVR2
34.0 cu. in.

DBVS2
34.0 cu. in.

Two-Gang IN BOX includes...

Box with weatherproof-in-use extra-duty cover; installed bug plugs; (1) decorator wall plate; and (2) NM cable connectors. DBVM2 also includes a block bushing with washer; and an in-place, disposable mud cover. DBVR2 also includes (1) set installation screws; and (1) roll of caulk. DBVS2 also includes (1) set installation screws.



Completed installation,
DBVS2C shown.

FEATURES AND BENEFITS

- IN BOX's one-piece assembly replaces the installation of an electrical box and bubble cover assembly
- Installs in the wall, so less of it shows outside
- No gaskets required
- For flat surfaces, vinyl siding, stucco over masonry or wood (with or without lath), and retrofit
- Install an outlet and a switch, or two switches in one location
- Includes 1/2" and 3/4" NM cable connectors and a two-gang rectangular device plate

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Scan For Video



Low Profile IN BOX™ with Adapter Sleeve for New Brick Construction

Recessed electrical box with weatherproof-in-use extra-duty cover for new brick construction. Includes a protective adapter sleeve that keeps mortar out. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. White box and cover are textured/ paintable. UV rated plastic for long outdoor life.



DHB1BRC

FEATURES AND BENEFITS

- IN BOX's one-piece assembly replaces the installation of an electrical box and bubble cover assembly
- Adapter sleeve, with loops in back for tying off cable, keeps mortar out of the box while brick mason works
- The clean IN BOX slips into the sleeve for easy installation!
- Built-in anchor tabs seat IN BOX sleeve into mortar for a super secure installation
- Installs in the wall, so less of it shows outside
- Install option: Cover is removable for easier device installation
- No gaskets required



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/COVER COLOR | UNIT | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|--------------------------------|------|---------|-------|-------|-------|-------|-------|
| DHB1C | 54880 | Horiz./Clear Cover/White Box | 1 | 4 | 4.934 | 7.186 | 5.283 | 1.658 | 3.625 |
| DHB1W | 54882 | Horiz./White Cover/White Box | 1 | 4 | 4.934 | 7.186 | 5.283 | 1.658 | 3.625 |
| DHB1BRC | 54881 | Horiz./Clear Cover/Brown Box | 1 | 4 | 4.934 | 7.186 | 5.283 | 1.658 | 3.625 |
| DHB1BR | 54875 | Horiz./Brown Cover/Brown Box | 1 | 4 | 4.934 | 7.186 | 5.283 | 1.658 | 3.625 |
| DVB1C | 43609 | Vertical/Clear Cover/White Box | 1 | 4 | 7.186 | 4.934 | 5.283 | 1.658 | 3.625 |
| DVB1W | 43620 | Vertical/White Cover/White Box | 1 | 4 | 7.186 | 4.934 | 5.283 | 1.658 | 3.625 |
| DVB1BRC | 43608 | Vertical/Clear Cover/Brown Box | 1 | 4 | 7.186 | 4.934 | 5.283 | 1.658 | 3.625 |
| DVB1BR | 43595 | Vertical/Brown Cover/Brown Box | 1 | 4 | 7.186 | 4.934 | 5.283 | 1.658 | 3.625 |

Add suffix "GC" to Catalog # when ordering in Canada, for example DHB1CGC.


Replacement covers available on page K-17.

PATENTED. ADDITIONAL PATENTS PENDING.



IN BOX for new brick includes...

Box with weatherproof-in-use extra-duty cover, adapter sleeve, installed bug plugs, (1) standard duplex and (1) standard GFCI face plate, installation screws, (1) NM cable connector, and (1) roll of caulk, disposable mud cover.



Installation Instructions



Mortar in adapter sleeve. Pull wire and tie off to loop in adapter sleeve.



When ready to complete... apply supplied caulk as shown and press around edges of adapter sleeve.



Install the supplied NM cable connector and wire. Insert the clean IN BOX into the sleeve.



Attach IN BOX with screws provided. Install wiring device per manufacturer's instructions, Local and National Electrical Codes.



Accepts most single gang wiring devices, and uses a standard indoor wall plate. DHB1C shown.



Weatherproof-in-use. DHB1BRC shown.

IN BOX Saves Time. Looks Great!

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Low Profile IN BOX™ with Metal Box for Flat Surface Retrofit Construction

Recessed, metallic electrical box with non-metallic, extra-duty weatherproof-in-use cover for flat surfaces in existing construction. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Non-metallic portion and covers are UV rated plastic for long outdoor life.



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|-------|-------|
| DSBVR1C | 09654 | Vertical/Clear | 1 | 4 | 7.196 | 4.937 | 5.129 | 1.283 | 3.846 |
| DSBVR1W | 09655 | Vertical/White | 1 | 4 | 7.196 | 4.937 | 5.129 | 1.283 | 3.846 |
| DSBHR1C | 09656 | Horizontal/Clear | 1 | 4 | 4.937 | 7.196 | 5.129 | 1.283 | 3.846 |
| DSBHR1W | 09657 | Horizontal/white | 1 | 4 | 4.937 | 7.196 | 5.129 | 1.283 | 3.846 |


Replacement covers and siding profiles to convert for use on existing siding available on page K-17.

PATENTED. ADDITIONAL PATENTS PENDING.



**WEATHERPROOF-IN-USE
EXTRA-DUTY**

IN BOX for retrofit, flat surfaces includes...
Metallic box with non-metallic, weatherproof-in-use extra-duty cover; installed bug plugs; (1) standard duplex and (1) standard GFCI face plate; (1) set installation screws; and (1) roll of caulk.



FEATURES AND BENEFITS

- IN BOX replaces the installation of an electrical box and bubble cover assembly
- Installs in the wall, so less of it shows outside
- No gaskets required
- Use the retrofit IN BOX on plywood, T-111, and other flat surfaces
- Install option: Cover is removable for easier device installation
- White, non-metallic portion and white cover are textured/paintable
- Grounding wire provided
- For use with metal raceway systems

Scan For Video



Low Profile IN BOX™ with Metal Box for New Vinyl Siding Construction

Recessed, metallic electrical box with non-metallic, weatherproof-in-use extra-duty cover for new siding applications. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Non-metallic portion and covers are UV rated plastic for long outdoor life.



DSBHS1C



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | SIDING TYPE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|-------------|----------|---------|-------|-------|-------|-------|-------|
| DSBVS1C | 09650 | Vertical/Clear | All Types | 1 | 4 | 9.058 | 7.012 | 5.129 | 1.775 | 3.221 |
| DSBVS1W | 09651 | Vertical/White | All Types | 1 | 4 | 9.058 | 7.012 | 5.129 | 1.775 | 3.221 |
| DSBHS1C | 09652 | Horizontal/Clear | All Types | 1 | 4 | 7.012 | 9.058 | 5.129 | 1.775 | 3.221 |
| DSBHS1W | 09653 | Horizontal/white | All Types | 1 | 4 | 7.012 | 9.058 | 5.129 | 1.775 | 3.221 |

Replacement covers available on page K-17.

PATENTED. ADDITIONAL PATENTS PENDING.




**WEATHERPROOF-IN-USE
EXTRA-DUTY**

IN BOX for new siding includes...
Metallic box with non-metallic, weatherproof-in-use extra-duty cover; installed bug plugs; (1) standard duplex and (1) standard GFCI face plate; and (1) set installation screws.

FEATURES AND BENEFITS

- IN BOX replaces the installation of an electrical box, siding block, and bubble cover assembly
- Installs in the wall, so less of it shows outside
- Outer flange covers cut ends of siding
- Install option: Cover is removable for easier device installation
- White, non-metallic portion and white cover are textured/paintable
- Grounding wire provided
- For use with metal raceway systems




25.0 cu. in.

Scan For Video



Low Profile IN BOX™ with Metal Box for New Construction Stucco, Textured Surfaces, and Rigid Siding

Recessed, metallic electrical box with non-metallic, extra-duty weatherproof-in-use cover for stucco over masonry or wood construction. Also for cementitious/fiber rigid lap siding. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Non-metallic portion and covers are UV rated plastic for long outdoor life.



DSBVM1W



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|-------|-------|
| DSBVM1C | 09642 | Vertical/Clear | 1 | 4 | 9.058 | 7.012 | 5.129 | 1.775 | 3.221 |
| DSBVM1W | 09646 | Vertical/White | 1 | 4 | 9.058 | 7.012 | 5.129 | 1.775 | 3.221 |
| DSBHM1C | 09643 | Horizontal/Clear | 1 | 4 | 7.012 | 9.058 | 5.129 | 1.775 | 3.221 |
| DSBHM1W | 09648 | Horizontal/white | 1 | 4 | 7.012 | 9.058 | 5.129 | 1.775 | 3.221 |

Replacement covers available on page K-17.

PATENTED. ADDITIONAL PATENTS PENDING.



WEATHERPROOF-IN-USE


EXTRA-DUTY

IN BOX for new stucco, textured surfaces, and rigid siding includes...

Metallic box with non-metallic, weatherproof-in-use extra-duty cover; installed bug plugs; (1) standard duplex and (1) standard GFCI face plate; block bushing with washer; and an in-place, disposable mud cover.

FEATURES AND BENEFITS

- IN BOX replaces the installation of an electrical box and bubble cover assembly
- Installs in the wall, so less of it shows outside
- No gaskets required
- Holes in flange allow stucco to bond firmly
- Install option: Cover is removable for easier device installation
- White, non-metallic portion and white cover are textured/paintable
- Grounding wire provided
- For use with metal raceway systems



25.0 cu. in.

Scan For Video



Low Profile IN BOX™ with Metal Box and Adapter Sleeve for New Brick Construction

Recessed, metallic electrical box with non-metallic, weatherproof-in-use extra-duty cover for new brick. Includes a protective adapter sleeve that keeps mortar out. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Non-metallic portion and covers are UV rated plastic for long outdoor life.



DSHB1C


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|------------------------------|----------|---------|-------|-------|-------|-------|-------|
| DSHB1C | 43610 | Horiz./Clear Cover/White Box | 1 | 4 | 4.937 | 7.196 | 5.283 | 1.283 | 4.000 |
| DSHB1W | 43611 | Horiz./White Cover/White Box | 1 | 4 | 4.937 | 7.196 | 5.283 | 1.283 | 4.000 |
| DSHB1BRC | 43612 | Horiz./Clear Cover/Brown Box | 1 | 4 | 4.937 | 7.196 | 5.283 | 1.283 | 4.000 |
| DSHB1BR | 43613 | Horiz./Brown Cover/Brown Box | 1 | 4 | 4.937 | 7.196 | 5.283 | 1.283 | 4.000 |

Replacement covers available on page K-17.

PATENTED. ADDITIONAL PATENTS PENDING.



IN BOX for new brick includes...
Metallic box with non-metallic, weatherproof-in-use extra-duty cover; installed bug plugs; adapter sleeve; (1) standard duplex and (1) standard GFCI face plate; (1) set installation screws; (1) NM cable connector; an in-place, disposable mud cover; and (1) roll of caulk.



25.0 cu. in.

FEATURES AND BENEFITS

- IN BOX replaces the installation of an electrical box and bubble cover assembly
- Installs in the wall, so less of it shows outside
- No gaskets required
- Install option: Cover is removable for easier device installation
- White, non-metallic portion and white cover are textured/paintable
- Grounding wire provided
- For use with metal raceway systems



Weatherproof-in-use.
DSHB1BRC shown.
IN BOX Saves Time. Looks Great!



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Scan For Video



Low Profile IN BOX™ for 1-1/2" Wall Systems

Recessed electrical box with weatherproof-in-use extra-duty cover for 1-1/2" wall systems, including foam. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Box and white cover are textured/paintable. UV rated plastic for long outdoor life.



DBVME1W

FEATURES AND BENEFITS

- IN BOX's one-piece assembly replaces the installation of an electrical box and bubble cover assembly
- Fewer parts to handle – save on materials and labor.
- Installs in the wall, so less of it shows outside
- Features a fixed, built-in flange, large enough to eliminate the need for a separate flashing.
- Install option: Cover is removable for easier device installation
- No gaskets required



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|-------|-------|
| DBVME1C | 77645 | Vertical/Clear | 1 | 4 | 8.000 | 5.750 | 4.950 | 2.461 | 2.567 |
| DBVME1W | 77646 | Vertical/White | 1 | 4 | 8.000 | 5.750 | 4.950 | 2.461 | 2.567 |

Add suffix "GC" to Catalog # when ordering in Canada, for example DVBME1CGC.
Replacement covers available on page K-17.


PATENTED. ADDITIONAL PATENTS PENDING.



IN BOX for 1-1/2" wall systems includes...

Box with weatherproof-in-use extra-duty cover, installed bug plugs, (1) standard duplex and (1) standard GFCI face plate, (1) NM cable connector, and disposable mud cover.

22 cu. in.



Saves Time – Looks Great!

Cover ships with disposable mud cover



Low profile IN BOX for a neat, clean look



Low Profile IN BOX™ for Foam Wall Systems

Recessed electrical box with weatherproof-in-use extra-duty cover. Adjustable to fit any foam board thickness. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Box and white cover are textured/ paintable. UV rated plastic for long outdoor life.



DBVMA1W

FEATURES AND BENEFITS

- IN BOX's one-piece assembly replaces the installation of an electrical box and bubble cover assembly
- Adjustable flange depth fits any foam board thickness or custom finish in concrete block and stucco applications
- Installs in the wall, so less of it shows outside
- Adjusts for finishes from 1/4" to 2-1/2" thick - in walls, from 2-3/4" to 5" deep
- Install option: Cover is removable for easier device installation
- No gaskets required



Bug Plugs ship installed in all IN BOX styles to seal unused cord hole openings.

Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D MIN / MAX |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|-----------------|
| DBVMA1C | 77632 | Vertical/Clear | 1 | 4 | 9.058 | 7.012 | 5.160 | .250-5.000 |
| DBVMA1W | 77634 | Vertical/White | 1 | 4 | 9.058 | 7.012 | 5.160 | .250-5.000 |

Add suffix "GC" to Catalog # when ordering in Canada, for example DBVMA1CGC.

Replacement covers available on page K-17.


PATENTED. ADDITIONAL PATENTS PENDING.




**WEATHERPROOF-IN-USE
EXTRA-DUTY**

IN BOX for foam wall systems includes...

Box with weatherproof-in-use extra-duty cover, installed bug plugs, (1) standard duplex and (1) standard GFCI face plate, (4) installation screws, (1) NM cable connector, and an in-place, disposable mud cover.




Installation Instructions



Flange in position for thin foam board or finish thickness

Remove screw.

Adjust flange depth. Insert screw in the appropriate opening to hold flange securely in place.



Flange depth opened to accommodate thicker foam board or finishes



1/2" foam board



2" foam board

The flange depth adjusts to fit any foam thickness!

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Low Profile IN-AND-OUT™

Covers for New or Existing Construction

Low profile when not in use and a deeper, weatherproof-in-use extra-duty cover when cord is plugged in. Non-metallic cover and base. Comes in clear or textured/ paintable white. UV rated plastic for long outdoor life.



60VC

FEATURES AND BENEFITS

- Low profile when not in use – weatherproof-while-in-use
- IN position provides a sealed box to keep bugs out
- Extends quickly and easily into the OUT position to accommodate a plug
- Fits over all boxes or openings in new or existing projects
- The 61 Series has an installed, oversized base for large openings or a 3.5" round outlet box
- Installed gaskets
- Install option: Cover is removable for easier device installation
- Vertical and horizontal styles

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C IN | DIM C OUT | DIM D | DIM E |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|----------|-----------|-------|-------|
| 60VC | 00682 | Vertical/Clear | 1 | 4 | 6.274 | 3.752 | 1.670 | 3.005 | - | - |
| 60VW | 00680 | Vertical/White | 1 | 4 | 6.274 | 3.752 | 1.670 | 3.005 | - | - |
| 61VC | 00683 | Vertical/Clear | 1 | 4 | 6.274 | 3.752 | 1.670 | 3.005 | 5.561 | 4.250 |
| 61VW | 00681 | Vertical/White | 1 | 4 | 6.274 | 3.752 | 1.670 | 3.005 | 5.561 | 4.250 |
| 60HC | 00686 | Horizontal/Clear | 1 | 4 | 4.192 | 5.836 | 1.670 | 3.005 | - | - |
| 60HW | 00684 | Horizontal/white | 1 | 4 | 4.192 | 5.836 | 1.670 | 3.005 | - | - |
| 61HC | 00687 | Horizontal/Clear | 1 | 4 | 4.192 | 5.836 | 1.670 | 3.005 | 4.250 | 5.561 |
| 61HW | 00685 | Horizontal/white | 1 | 4 | 4.192 | 5.836 | 1.670 | 3.005 | 4.250 | 5.561 |

PATENTED.



**WEATHERPROOF-IN-USE
EXTRA-DUTY**

IN AND OUT COVER includes...
Low profile cover, (1) standard duplex and (1) standard GFCI face plate, installation screws, and installed gaskets.



61V
61 Series base shown separately for dimensional purposes only.

Installation Instructions



1 Feed device through opening (cover is removable for easier access).



2 Install wiring device per manufacturer's instructions, Local and National Electrical Codes using the pre-drilled holes in base.



3 Install plate and the installation is done!



60VW

IN for **GOOD LOOKS** and to stay bug free...



61HW

OUT to **PLUG IN** for weatherproof-in-use!



To close: Bow out sides of extended cover and push in.

Scan For Video



Extra-Duty IN BOX™ Replacement Covers


Replacement covers sold separately. Clear is not paintable and white is textured, paintable. UV rated plastic for long outdoor life.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-----------------------------|----------|---------|-------|-------|-------|
| DBVC | 77640 | Single-Gang, Vert. / Clear | 10 | 10 | 5.650 | 3.420 | .370 |
| DBVW | 77642 | Single-Gang, Vert. / White | 10 | 10 | 5.650 | 3.420 | .370 |
| DBHC | 77650 | Single-Gang, Horiz. / Clear | 10 | 10 | 3.420 | 5.650 | .370 |
| DBHW | 77652 | Single-Gang, Horiz. / White | 10 | 10 | 3.420 | 5.650 | .370 |
| DBV2C | 13009 | 2-Gang, Vert. / Clear | 10 | 10 | 5.650 | 5.410 | .370 |
| DBV2W | 13010 | 2-Gang, Vert. / White | 10 | 10 | 5.650 | 5.410 | .370 |

EXTRA-DUTY

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.



Weatherproof Box Holder

Zinc die-cast and non-metallic.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|-------|
| FS50 | 61050 | 1/2 | 25 | 25 | .380 | 1.550 | 1.125 | .860 |
| FS75 | 61075 | 3/4 | 25 | 25 | .380 | 1.550 | 1.125 | .860 |
| NMFS50* | 54050 | 1/2 | 25 | 25 | .380 | 1.550 | 1.125 | .860 |
| NMFS75 | 54075 | 3/4 | 25 | 25 | .380 | 1.550 | 1.125 | .860 |

*UV rated non-metallic body.

Note: Can be used as an external means of support to meet the requirements of 2014 NEC Section 314.23.



E161207 LR49636




Assembly Instructions

Just screw the box support into the electrical box; the entire assembly is held secure with a 1/2" rigid steel conduit or water pipe.

Other Uses

- Stubbing up electrical enclosures above concrete slabs with rigid pipe.
- Suspending electrical boxes with rigid pipe between bar joists.
- Suspending fire alarms (smoke detectors) with rigid pipe between bar joists.
- Can be used for installation of equipment where a rigid pipe can be used for a holding means and a 1/2" knockout is present for attachment.



Dri-Box[®] Adapters with Non-Metallic Cover and Base

This adapter will accept any wiring device and standard size wall plate. Colors: clear and textured/paintable white. UV rated plastic for long outdoor life.



DBPV1C

DBPV1/DBPV1C:
VERTICAL MOUNT, SINGLE GANG

DBPH1/DBPH1C:
HORIZONTAL MOUNT, SINGLE GANG

DBP2/DBP2C/DBP21D/DBP21DC:
VERTICAL MOUNT, TWO GANG

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | ORIENTATION/COVER COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|
| DBPV1* | 17852 | Vertical/White | 1 | 4 | 6.313 | 3.375 | 2.940 |
| DBPV1C* | 17840 | Vertical/Clear | 1 | 4 | 6.313 | 3.375 | 2.940 |
| DBPH1* | 17853 | Horizontal/White | 1 | 4 | 4.000 | 5.685 | 2.940 |
| DBPH1C* | 17845 | Horizontal/Clear | 1 | 4 | 4.000 | 5.685 | 2.940 |
| DBP2 | 17855 | Vertical/White | 1 | 4 | 6.313 | 5.250 | 2.940 |
| DBP2C | 17857 | Vertical/Clear | 1 | 4 | 6.313 | 5.250 | 2.940 |
| DBP21D | 17849 | Vertical/White | 1 | 4 | 6.313 | 5.250 | 4.175 |
| DBP21DC | 17848 | Vertical/Clear | 1 | 4 | 6.313 | 5.250 | 4.175 |

*Includes (1) standard duplex and (1) GFCI face plate.

PATENTED. ADDITIONAL PATENTS PENDING.




E170558

LR49636

WEATHERPROOF-IN-USE


EXTRA-DUTY



Installation Instructions

Remove the cover by expanding ear tabs over the pivot pins. To replace the cover, simply snap over the pivot pins.

NOTE: It is not required to remove the cover for installation.



Arlington's DRI-BOX[®] Adapter comes with both standard duplex and GFCI plates for added convenience, but works with any standard plastic or metal wall plate. Our DRI-BOX[®] meets OSHA lockout/tagout requirements using a standard padlock.

Siding Box Kits


For smooth vertical mounting of fixtures and receptacles on sided structures. Paintable. UV rated plastic for long outdoor life.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | USES | UNIT PKG | STD PKG | STYLE |
|----------------|--------------------------|--------------|------------------|----------|---------|------------|
| 8081* | 80812 | All Types | Fixtures/Devices | 25 | 25 | w/o Flange |
| 8081F* | 80814 | All Types | Fixtures/Devices | 25 | 25 | w/ Flange |
| 8082F* | 32240 | 1/2" or Less | Fixtures/Devices | 25 | 25 | w/ Flange |
| 8081FC | 10939 | All Types | Fixtures/Devices | 25 | 25 | Cover Only |
| 8081FB* | 10941 | All Types | Fixtures/Devices | 25 | 25 | Box Only |

*Add suffix "GC" to Catalog # when ordering in Canada, for example 8081FGC.

PATENTED.



FEATURES AND BENEFITS

- UL Listed electrical box
- Works on all siding types – Before or After the siding is up!
- Flanges may be removed for retrofit work
- Textured, paintable surface
- NM cable connector included

For Installation Instructions 'AFTER Siding is Up' see Below. For Installation Instructions 'BEFORE Siding is Up' see Page L-2.

Installation Instructions

AFTER Siding is Up...

Without Flange (8081 & 8081DBL)

NOTE: 8081F, 8081FDBL, 8082F, 8091F, and 8091FDBL may also be installed when siding is already up – Score and break off flanges before step one (below).



1 Disconnect electrical power. Place box section in desired location and pencil outline onto siding.



2 Cut along pencil line with razor knife and remove vinyl siding.



3 Mount box section to substrate. Caulk as required.



4 Place siding block over box section (8081 shown).



5 Connect wires and install fixture per manufacturer's instructions.

Siding Box Kits

For smooth vertical mounting of fixtures, receptacles, and GFCIs on sided structures. Paintable. UV rated plastic for long outdoor life.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | USES | UNIT PKG | STD PKG | STYLE |
|----------------|--------------------------|-------------|-----------------|----------|---------|------------|
| 8091F* | 17856 | All Types | GFCIs, Fixtures | 25 | 25 | w/ Flange |
| 8091FC | 10946 | All Types | GFCIs, Fixtures | 10 | 10 | Cover Only |
| 8091FB* | 10945 | All Types | GFCIs, Fixtures | 10 | 10 | Box Only |


*Add suffix "GC" to Catalog # when ordering in Canada, for example 8091FGC.

PATENTED.



FEATURES AND BENEFITS

- UL Listed electrical box
- Works on all siding types – Before or After the siding is up!
- Flanges may be removed for retrofit work
- Textured, paintable surface
- NM cable connector included
- Works with fixtures, standard receptacles, and GFCIs




For Installation Instructions 'BEFORE Siding is Up' see Below. For Installation Instructions 'AFTER Siding is Up' see Page L-1.

Installation Instructions

BEFORE Siding is Up...

With Flange (8081F, 8081FDBL, 8082F, 8091F, & 8091FDBL)



1. Before siding is installed, using the flanged style, screw the box to the wall using the holes provided in the flange.
2. Disconnect electrical power. Pull the wire through the knockout of your choice.
3. Install siding around box section and caulk as required.
4. Attach cover.
5. Connect the wires and install the fixture per manufacturer's instructions.

The All-in-One Electrical Box and Cover



Siding block cover is placed over the electrical box.

The rectangular hole provides access to the wire connections.

Siding Box Kits

For smooth vertical mounting of large fixtures on sided structures. Paintable, UV rated plastic for long outdoor life.



8081DBL



8081FDBL

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | USES | UNIT PKG | STD PKG | STYLE |
|----------------|--------------------------|-------------|----------------|----------|---------|------------|
| 8081DBL | 80813 | All Types | Large Fixtures | 25 | 25 | w/o Flange |
| 8081FDBL | 80815 | All Types | Large Fixtures | 25 | 25 | w/ Flange |
| 8081FDBLC | 10943 | All Types | Large Fixtures | 10 | 10 | Cover Only |

Add suffix "GC" to Catalog # when ordering in Canada, for example 8081DBLGC


PATENTED.



E170558 LR49636

FEATURES AND BENEFITS

- UL Listed electrical box
- Works on all siding types – Before or After the siding is up!
- Flanges may be removed for retrofit work
- Textured, paintable surface
- NM cable connector included
- Perfect for installation of large fixtures



For Installation Instructions 'AFTER Siding is Up' see Page L-1. For Installation Instructions 'BEFORE Siding is Up' see Page L-2.

Siding Box Kit with Mega Mounting Plate

Mount the largest coach lamps on all siding types with the sturdy MEGA Mounting Plate! It's an electrical box and cover all-in-one! Paintable. UV rated plastic for long outdoor life.



FEATURES AND BENEFITS

- Provides a solid mount for extra large fixtures
- UL Listed electrical box
- Use up or down to fit any mounting hole configuration
- Flanges may be removed for retrofit work
- Deep design to accommodate GFCl's


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | USES | UNIT PKG | STD PKG | STYLE |
|----------------|--------------------------|-------------|------------------------------|----------|---------|------------|
| 8091FDBL | 24168 | All Types | GFCl's, Extra Large Fixtures | 10 | 10 | w/ Flange |
| 8091FDBLC | 10947 | All Types | GFCl's, Extra Large Fixtures | 10 | 10 | Cover Only |

Add suffix "GC" to Catalog # when ordering in Canada, for example 8091FDBLGC

PATENTED.



E170558 LR49636



Installation Instructions

1. Disconnect electrical power. Insert provided NM cable connector through the KO of your choice and pull wires through.
2. Box section mounts to substrate. Caulk as required.
3. Place MEGA Plate over box section and install large fixture per manufacturer's instructions.



Siding Mounting Kits with Built-in Box

For smooth vertical mounting of light fixtures on all siding types. Kit includes mounting block with built-in electrical box, NM cable connector, and 4 screws. Paintable, UV rated plastic for long outdoor life.



8141



8141DBL

FEATURES AND BENEFITS

- Mounts light fixtures on all siding types, including T-111, HardiePlank® Lap Siding, and flat surfaces
- Fast and easy to install after siding is up
- Textured, paintable surface
- NM cable connector included
- Built-in electrical box design ensures UL listed installation

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------------------------------|----------|---------|-------------------------|-------|--------|
| 8131 | 08131 | 1/4" & 5/16" Siding & Shingles | 1 | 10 | 4" Diameter X 1/2" Deep | 6.625 | 6.625 |
| 8141 | 10751 | 1/2" Lap | 1 | 10 | 4" Diameter X 1/2" Deep | 6.625 | 6.625 |
| 8141DBL | 54524 | 1/2" Lap Double | 1 | 10 | 4" Diameter X 1/2" Deep | 6.900 | 10.200 |
| 8151 | 10753 | 5/8" Lap | 1 | 10 | 4" Diameter X 1/2" Deep | 6.625 | 6.625 |
| 8161 | 08161 | Flat Surfaces | 1 | 10 | 4" Diameter X 1/2" Deep | 6.625 | 6.625 |
| 8171 | 10757 | Dutch Lap | 1 | 10 | 4" Diameter X 1/2" Deep | 6.625 | 6.625 |



Add suffix "GC" to Catalog # when ordering in Canada, for example 8141GC.

PATENTED.




E170558 LR49636

8131, 8141,
8151, 8161,
8171



8141DBL



Installation Instructions for Siding



1 Select location for light fixture and caulk opening around cable.



2 Remove knockout from electrical box and insert cable connector. Push cable through connector and position mounting block onto siding.



3 Secure mounting block with provided screws. Install fixture per manufacturer's instructions.

Mega Siding Plate

Use the 8100LP to convert octagonal size covers to MEGA covers for mounting large fixtures or coach lamps. UV rated plastic for long outdoor life.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|-------------|----------|---------|-------|--------|-------|-------|-------|
| 8100LP | 10749 | All Types | 1 | 10 | .783 | 13.500 | 7.125 | 5.125 | 4.105 |

PATENTED.

FEATURES AND BENEFITS

- Accommodates light fixtures with mounting brackets up to 12"
- To center fixtures, use slotted mounting screw holes to provide adjustments up to 1"
- Provides a smooth, secure mounting surface for large fixtures
- Instantly converts a previously installed octagonal siding block to a MEGA Siding Plate
- Features alignment mounting slots to guarantee the MEGA Siding Plate will stay securely in position



Installation Instructions

The 8100LP MEGA Siding Plate is designed to install directly over the existing mounting block for installations of large light fixtures. If screw holes are offset, simply rotate the 8100LP 180°.



For use with Arlington's Siding Blocks

- 8131 • 8141 • 8141DBL
- 8151 • 8161 • 8171

Super MEGA Siding Plate

Converts existing octagonal block for installation of extra large light fixtures or coach lamps. Paintable, UV rated plastic for long outdoor life.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|--------|-------|
| 8100MLP | 10752 | All Types | 1 | 10 | .838 | 16.000 | 8.500 |

PATENTED.

FEATURES AND BENEFITS

- Supports light fixtures with canopies up to 8" wide x 15-1/2" tall
- To center fixtures, use slotted mounting screw holes to provide adjustments up to 2"
- Fits over all Arlington's octagonal siding blocks and 8091F
- Provides a sturdy, extra large mounting surface



Installation Instructions

Use with an existing mounting block. Disconnect electrical power. Align slots and secure the 8100MLP to the siding block. Install extra large fixture per manufacturer's instructions. If screw holes are offset, simply rotate the 8100MLP 180°.



For use with Arlington's Siding Blocks

- 8091F • 8131 • 8141 • 8141DBL
- 8151 • 8161 • 8171

Dryer Vent Mounting Block Kit


Non-metallic dryer vent mounting block for new construction.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|
| DV1 | 43607 | All Types | 1 | 1 | 7.226 | 7.226 | 1.738 |

FEATURES AND BENEFITS

- Provides a secure, attractive and time saving way to install dryer vents on new siding
- Installs before siding is up and fits 1/2" and 5/8" step, and dutch lap siding
- Textured, paintable surface
- Overhang covers cut ends of siding for a clean, neat look
- Easy to install – provides an attractive, flush-look mounting
- UV rated plastic for long outdoor life



Kit includes a low profile, louver-type hood; a snap together 4" diameter x 11" aluminum tube; and a siding block with built-in J-channel.

Siding Mounting Block

Mounting block with built-in electrical box for smooth vertical mounting of light fixtures on all siding types. Paintable. UV rated plastic for long outdoor life.



EASY TO INSTALL
BEFORE or AFTER
THE SIDING!


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-----------------------------|-------|
| 8141F | 10761 | All Types | 10 | 10 | 6.652 | 6.652 | 4.125" Diameter x 1/2" Deep | 1.126 |



Add suffix "GC" to Catalog # when ordering in Canada, for example 8141FGC.
PATENTED.

FEATURES AND BENEFITS

- Installs before or after siding is installed. Remove break-away flanges for installation on previously sided structures.
- One-piece design
- Textured, paintable surface
- NM cable connector included



Installation Instructions

BEFORE siding is up...

1. Remove knockout from 8141F. Insert cable connector. Pull NM cable through connector.
2. Attach block to substrate with (2) screws mounted diagonally.
3. Install fixture according to manufacturer's instructions.

AFTER siding is up...

1. Cut hole in siding.
2. Break flanges off the back of the 8141F. Remove knockout. Insert cable connector in KO, then pull NM cable through connector.
3. Attach mounting block to substrate with (2) screws.
4. Install fixture according to manufacturer's instructions.

Hose Bib

Two-piece non-metallic hose bib for all siding types.


NEW!

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|-------|-------|-------|
| HB1 | 15300 | 2-piece, Non-Metallic for all siding types | 1 | 10 | 8.251 | 6.562 | 1.031 |



FEATURES AND BENEFITS

- Built-in J channel
- Installs before the siding is installed
- Paintable
- Easy to install slip-fit design.
- Fits most standard and frost-free 3/4" hose bibs.



Weatherproof FS Outlet Box

For installing devices on all siding types. Paintable, UV rated plastic for long outdoor life.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|
| FS8091F | 17304 | All Types | 10 | 10 | 4.511 | 6.558 | 2.656 |

Add suffix "GC" to Catalog # when ordering in Canada, for example FS8091FGC.

PATENTED.



Costs Less Than Our 8081F and 8091F Siding Boxes



EASY TO INSTALL BEFORE or AFTER THE SIDING!

Installation Instructions

FEATURES AND BENEFITS

- Costs less...one-piece design
- For use with all single-gang devices, including GFCIs
- Installs before or after siding is installed. Remove break-away flanges for installation on previously sided structures.
- Can be installed vertically or horizontally
- For all types of siding
- Textured, paintable surface.
- UL listed

BEFORE siding is up...

1. Disconnect electrical power. Remove knockout. Insert cable connector. Pull NM cable through connector.
2. Attach outlet box to substrate with (2) screws.
3. Install device, FS8091F works with all single gang devices.

Complete installation with code required weatherproof while-in-use cover.



GFCI

Standard Outlet

AFTER siding is up...

1. Disconnect electrical power. Cut hole in siding.
2. Break flanges off the back of the FS8091F. Remove knockout. Insert cable connector in KO, then pull NM cable through connector.
3. Attach outlet box to substrate with (2) screws.
4. Install single gang device (standard or GFCI). Complete installation with code required weatherproof while-in-use cover.



Standard Outlet

GFCI

Non-metallic FR Series Device & Fixture Boxes

Extra-wide flanges prevent water and air intrusion, no need for gaskets or caulking. Use for mounting coach lights on stucco and/or flat siding. For new construction.





FEATURES AND BENEFITS

- Converts **FAST** for use on any cladding system up to 1-7/8"!
- Ships pre-assembled, ready for use with 1-3/8" finish or cladding thicknesses
- Easily converts for 5/8" finish thicknesses by removing back and reinstalling on the opposite side
- Add extension ring for 7/8" thickness
- Extra-wide flanges help meet the International Energy Conservation Code by creating a protective barrier against air and water infiltration. No gaskets or caulking required.
- Large 20 cubic inch volume
- Made of high strength polycarbonate
- Wall mount – one-piece design for new installations
- Up to a 10 lb. fixture rating

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | APPLICATION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|-------|
| FR101F | 12680 | Device Box | 10 | 10 | 7.875 | 7.125 | 3.750 | 3.525 |
| FR405F | 12681 | Pan Box | 10 | 10 | 6.750 | 6.750 | 4.000 | 1.375 |
| FR420F | 09615 | Fixture Box | 10 | 10 | 6.750 | 6.750 | 4.000 | 1.986 |


PATENTED.




Installation Instructions

- For 5/8" wall finish thickness, loosen two screws and remove back.
- Re-install the back on the **OPPOSITE** side of the box.
- Assembled for 5/8" finish thickness.
- For 7/8" wall finish thickness, install the 1/4" extension ring
- ...to the front of the box.

For New Construction Install FR series box BEFORE



or AFTER weather barrier house wrap



Weatherproof FS Boxes

One-piece construction electrical box provides a clean, weatherproof, UL Listed installation. Deep design for GFCIs. Paintable, UV rated plastic for long outdoor life.





FEATURES AND BENEFITS

- Provides a solid, attractive, UL listed installation
- Accommodates GFCI, switches, and outlets
- For use with all siding types...1/2", 5/8", dutch lap, and flat surfaces

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE/STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------|----------|---------|-------|-------|-------|
| FS8141 | 17340 | 1/2" Lap | 25 | 25 | 5.093 | 3.312 | 2.056 |
| FS8151 | 17341 | 5/8" Lap | 25 | 25 | 5.093 | 3.312 | 2.056 |
| FS8161 | 17342 | Flat Surfaces | 25 | 25 | 5.093 | 3.312 | 2.056 |
| FS8171 | 17343 | Dutch Lap | 25 | 25 | 5.093 | 3.312 | 2.056 |

Add suffix "GC" to Catalog # when ordering in Canada, for example FS8141GC.

PATENTED. ADDITIONAL PATENTS PENDING.



Installation Instructions



Remove KO from FS Box and insert NM cable connector. Push cable through connector and position box onto siding.



Mount box to siding and install your choice of either a GFCI, switch or duplex receptacle.

Complete installation with one of Arlington's code required extra-duty weatherproof while-in-use 60 Series or 61 Series Low Profile IN-AND-OUT™ covers. See Page K-16 for more information.



One-Piece Weatherproof Outlet Box for Siding

One-piece outlet box for siding has an installed extra-duty weatherproof cover. For single-gang devices including GFCIs.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------------------|----------|---------|-------|-------|-------|
| F8091V | 22006 | Vertical/White Cover | 1 | 4 | 4.990 | 7.248 | 4.987 |
| F8091VC | 22008 | Vertical/Clear Cover | 1 | 4 | 4.990 | 7.248 | 4.987 |
| F8091H | 22002 | Horizontal/White Cover | 1 | 4 | 7.248 | 4.990 | 4.987 |
| F8091HC | 22045 | Horizontal/Clear Cover | 1 | 4 | 7.248 | 4.990 | 4.987 |

Add suffix "GC" to Catalog # when ordering in Canada, for example F8091VGC.



F8091V



F8091HC



Bug Plugs included

FEATURES AND BENEFITS

- Lockable
- Vertical or horizontal
- Clear or white Extra-Duty covers
- For single gang devices including GFCIs

Note: Meets 2014 NEC Section 406.9; for the protection of exterior outlets which require the use of an extra-duty weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.

Meter Mounting Bases

One-piece construction.
Paintable. Gangable. UV rated plastic for long outdoor life.





FEATURES AND BENEFITS

- Provides a smooth, flat mounting surface
- Provides a 1" overhang to cover siding
- Gangable to accommodate most meter sizes
- Break off flanges for retrofit work

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIDING TYPE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-------------|----------|---------|-------|-------|--------|--------|
| MM10 | 42278 | All Types | 10 | 10 | .750 | 1.125 | 10.000 | 7.000 |
| MM18 | 42280 | All Types | 10 | 10 | .750 | 1.125 | 17.625 | 15.875 |
| MM23 | 42282 | All Types | 10 | 10 | .750 | 1.125 | 23.000 | 17.625 |

PATENTED.

 Installs before or after the siding is up and works with any siding type!



Installation Instructions

BEFORE siding is up



Note: For support, meter mounting nails or screws must penetrate through mounting base into substrate.


Fasten to substrate through 'notched flanges'.

Siding butts to edge of Meter Base, overlapping the 'notched flanges'.




Meter Base mounting surface provides a 1" overhang to cover cut ends of siding.

MM10 mounting block also mounts **disconnects, time clocks, cable TV boxes, and more!**

Gangable Meter Base Combinations...



Seal joint channel with Arlington's DSC1 duct sealing compound. See page M-14.



Rotate all illustrated combinations 90° for additional surface mounting options.

Versatile Box for Power or Low Voltage

Mount security cameras, fixtures, detectors, and more inside or out.

Security



8161BR



8161CB



8161PM



8161BP



8161BPBL



8161TR

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | WEIGHT RATING | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------------------------------|------------------------------|----------|---------|--------|-------|-------|
| 8161BR | 08881 | Box w/ built-in bracket | 50 lb/wall | 1 | 10 | 10.921 | 6.451 | - |
| 8161BP | 08880 | Box w/ built-in base plate | 50 lb/down rod | 1 | 10 | 7.046 | .844 | 3.500 |
| 8161BPBL | 12785 | Box w/ built-in base plate (black) | 50 lb/down rod | 1 | 10 | 7.046 | .844 | 3.500 |
| 8161CB | 01530 | Box w/ corner-mount bracket | 50 lb/corner | 1 | 5 | 10.921 | 6.451 | - |
| 8161PM | 09020 | Pole Mount Box | 50 lb/pole | 1 | 5 | 10.921 | 6.451 | - |
| 8161TR | 00878 | Box w/ threaded openings | 50 lb/ceiling; 10 lb/wall | 1 | 10 | 6.720 | 1.343 | - |


Add suffix "GC" to Catalog # when ordering in Canada, for example 8161BRGC.

PATENTED.



FEATURES AND BENEFITS

- Non-metallic, UV rated for long outdoor life
- **OPTION** For cameras with base diameter smaller than 4.5" use Arlington's SC5 CAM-KIT™ camera mounting kit on top of the box.
- Mounts security cameras, electrical accessories and fixtures indoors or outdoors
- Screw pattern matches standard 4" fixture box
- Box includes 3/4" to 1/2" reducing bushing



Installation Shots



8161BP



8161BR



8161CB



8161BPBL

Scan For Video



CAM-LIGHT™ BOX for Suspended Ceilings

Offers a great way to install fixtures and smoke detectors (and more) on a suspended ceiling, drywall ceiling or wall.



FL430



FL430S

FEATURES AND BENEFITS


- Designed to install fixtures and more to a suspended ceiling panel – fast with a 4" hole saw
- Rated up to 50 lbs on a suspended ceiling (or drywall ceiling) in combination with the drop wire for support
- Rated up to 10 lbs on a drywall ceiling without drop wire (not for fixtures)
- Rated up to 7 lbs on walls
- Drop wire provides overhead support.
- Mounting wings hold bracket securely against wall when screws are tightened
- Box may be turned to any angle for proper inline positioning of exit signs and direct lighting
- White, non-metallic, paintable flange
- Steel box version for use where metal raceways are required
- Steel version installs with 4-1/2" hole saw
- Boxes have 1/2" and 3/4" knockouts
- To install a security camera on this box check out our CAM-KIT™ camera mounting kit (SC5) on page M-4

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ CUBIC INCHES | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------------------|----------|---------|-------|-------|-------|
| FL430* | 09740 | Non-Metallic / 27.0 | 1 | 10 | 7.380 | 3.085 | 1.331 |
| FL430S | 09741 | Steel / 17.0 | 1 | 10 | 7.345 | 2.375 | 1.688 |

*Add suffix "GC" to Catalog # when ordering in Canada, for example FL430GC.

Box includes 12' of drop wire, and box. Non-metallic box also includes (2) NM94 cable connectors.

PATENTED.



Installation Instructions - FL430 for Fixtures



1 Cut hole in a ceiling grid with 4" hole saw. 4-1/2" for steel.



2 Install CAM-LIGHT™ box. Rotate to desired position. Tighten mounting wing screws.



3 Add drop wire to loop. Attach to framing member above.



4 **To Complete:** Using the appropriate KO (1/2" or 3/4") install NM94 cable connector (supplied) and pull cable. Install fixture per manufacturer's instructions.

Scan For Video



CAM-BOX™ KIT for Installation of a Security Camera

For installation of most security cameras on suspended ceilings, drywall ceiling, exterior soffits, or wall.



FEATURES AND BENEFITS

- Designed to install security cameras to a suspended ceiling panel – fast with a 4" hole saw
- Rated up to 50 lbs on a suspended ceiling (or drywall ceiling) in combination with the drop wire for support
- Rated up to 10 lbs on a drywall ceiling without drop wire
- Rated up to 7 lbs on walls
- For security cameras, it fits any hole pattern because you drill the holes in the appropriate location in the flange, cameras with mounting holes set wider than 4.5" apart install directly to the box flange
- Mounting wings hold bracket securely against wall when screws are tightened
- White, non-metallic, paintable flange box
- Steel version for use where metal raceways are required
- Steel version installs with 4-1/2" hole saw
- 1/2" and 3/4" knockouts
- Box rotates in either direction for proper camera position

Scan For Video




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ CUBIC INCHES | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------------------|----------|---------|-------|-------|-------|
| FLC430* | 09742 | Non-Metallic / 27.0 | 1 | 10 | 7.380 | 3.085 | 1.331 |
| FLC430S | 09743 | Steel / 17.0 | 1 | 10 | 7.345 | 2.375 | 1.688 |

*Add suffix "GC" to Catalog # when ordering in Canada, for example FLC430GC.

Kit includes 12' of drop wire, box, bracket, mounting plate, and installation screws. Non-metallic box also includes (2) NM94 cable connectors.

PATENTED.



Installation Instructions - FLC430 for Security Cameras



1 Cut hole in a ceiling grid with 4" hole saw. 4-1/2" for steel.



2 Install CAM-BOX™ kit. Rotate to desired position. Tighten mounting wing screws.



3 Add drop wire to loop. Attach to framing member above.



4 Add bracket to the box using screws provided.



5 Attach camera to mounting plate (screws provided). Box fits any camera hole pattern because YOU drill the holes in the appropriate location in the flange.



6 With camera mounted, install the mounting plate to the box by placing it on the bracket and turning clockwise to lock. Install set screw.



Finished installation.

For camera installations on existing boxes, check out our CAM-KIT™ camera mounting kit on page M-4

CAM-KIT™

Security camera mounting kit. Universal bracket mounts to 3-1/2" and 4" round or octagonal boxes and single-gang device boxes. Also fits FL430 CAM-LIGHT™ BOX.



SC5


FEATURES AND BENEFITS

- Fits any camera hole pattern
- Low cost
- Installs in less than two minutes
- Installs cameras with a base diameter up to 4-1/2"

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E | DIM F |
|----------------|--------------------------|-------|----------|---------|-------|-------|-------|-------|-------|-------|
| SC5 | 18058 | White | 1 | 20 | 4.875 | 5.564 | .703 | 5.375 | .750 | .718 |
| SC5BL | 18220 | Black | 1 | 20 | 4.875 | 5.564 | .703 | 5.375 | .750 | .718 |

Includes 5" plastic mounting plate, camera mounting bracket and mounting screws.

PATENTED.



Installation Instructions - SC5 for Security Cameras



1 Use your camera base as a template and drill holes.



2 Attach camera to mounting plate (screws provided).



3 Mount the bracket to the existing box using screws provided.



4 With camera mounted, install the mounting plate to the box by placing it on the bracket and turning clockwise to lock. Install set screw.



Finished installation.

Scan For Video




Weatherproof, Non-Metallic Keypad Enclosures

Keypad cover protects against moisture and weather. Accommodates single or double-gang boxes and most keypad styles. Heavy-duty, white enclosure with paintable white or clear plastic cover.

Security



DBK88C




DBK88W

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| DBK55C | 77664 | Clear, Inside Size 5" x 5" x 1-1/2" | 1 | 10 | 6.207 | 5.733 | 1.937 |
| DBK55W | 77665 | White, Inside Size 5" x 5" x 1-1/2" | 1 | 10 | 6.207 | 5.733 | 1.937 |
| DBK88C | 77662 | Clear, Inside Size 7-1/2" x 7-1/2" x 1-1/2" | 1 | 5 | 8.140 | 8.480 | 1.810 |
| DBK88W | 77663 | White, Inside Size 7-1/2" x 7-1/2" x 1-1/2" | 1 | 5 | 8.140 | 8.480 | 1.810 |

PATENTED.

FEATURES AND BENEFITS

- Provides keypad protection (weatherproof with closed cover/vertical mounting)
- Versatile mounting, our keypad enclosure mounts horizontally or vertically
- Suitable for indoor or outdoor use
- Can be mounted, with or without a box, on flat surfaces for low voltage keypads
- Includes gasket
- Universal hole pattern accommodates most keypads and single, 2-gang, or 4x4 boxes!
- Lockable cover



Installation Shots

DBK88C - Weatherproof keypad enclosure!



(keypad not included)

Non-Metallic Enclosures

Made of heavy-duty, non-metallic UV-rated material.



EB1212BP


NEW!




FEATURES AND BENEFITS

- Optional cam lock, **sold separately**
- Handy 1/2" and 3/4" knockouts on top and bottom of enclosure box
- Non-metallic
- NEMA 1 Rated

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------------------------------|----------|---------|--------|--------|-------|
| EB0708 | 12672 | 7" x 8" x 3.5" | 1 | 4 | 8.522 | 8.233 | 3.812 |
| EB1111 | 12670 | 11" x 11" x 3.5" | 1 | 5 | 11.916 | 13.133 | 3.812 |
| EB1212 | 12671 | 12" x 12" x 4" | 1 | 5 | 12.519 | 13.573 | 4.688 |
| EB1212BP | 23155 | 12" x 12" x 4" with Back Plate | 1 | 5 | 12.519 | 13.573 | 4.688 |
| EBL1 | 11400 | Optional Cam Lock | 1 | 10 | - | - | - |



Installation Shots



Optional Cam Lock, EBL1

Multiple Gang Recessed TV BOX™ for Power and Low Voltage

For new or existing construction. Non-metallic, recessed combo boxes for power and low voltage for class 2 wiring of satellite or cable TV, speakers, etc.



TVBR505K Kit

Includes: Recessed combo box; (1) tamper-resistant duplex receptacle; (1) CEDH1 & (1) CED130; and (1) wall plate.



Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------------------------------|----------|---------|-------|-------|-------|
| TVBU505* | 09680 | 2-Gang, White, (1) Power/ (1) LV | 1 | 4 | 6.942 | 6.254 | 3.750 |
| TVBU505BL* | 09681 | 2-Gang, Black, (1) Power/ (1) LV | 1 | 4 | 6.942 | 6.254 | 3.750 |
| TVBR505K* | 09670 | Kit, 2-Gang, White, (1) Power/ (1) LV | 1 | 4 | 6.942 | 6.254 | 3.750 |
| TVBU507 | 09661 | 3-Gang, White, (1) Power/ (2) LV | 1 | 4 | 7.930 | 6.818 | 3.875 |
| TVBU507BL | 09662 | 3-Gang, Black, (1) Power/ (2) LV | 1 | 4 | 7.930 | 6.818 | 3.875 |

Add suffix "GC" to Catalog # when ordering in Canada, for example TVBU505GC.


*Optional box covers available on page Q-4.

PATENTED.



FEATURES AND BENEFITS

- Recessed combo box allows you to mount LCD/ plasma TVs and other system components flush against the wall
- For new work...Use supplied screws to install on stud. For convenience, box positioning tabs are set for 1/2" or 5/8" drywall
- Trim plate is textured/paintable and covers edges of cut wall surface
- Mounting wings hold bracket securely against wall when screws are tightened
- For walls up to 1-1/2" thick
- Use with Arlington's SCOOP™ series entrance hoods and plates (see pages O-7 to O-9)




Includes...
Recessed combo box; (1) trim plate; (1) decorator style cover plate; and installation screws.

Installation Instructions

New Work (TVBU507 shown)



Attach box to stud. Use tabs for proper positioning of box depth. See 2.



Positioning tabs are set for 1/2" or 5/8" drywall.



Attach paintable trim plate with screws provided. See Photo B.



Tighten mounting wing screws to pull the box securely against the wall board. See Photo B.

Retrofit Work (TVBU507 shown)



Using box, without trim plate as a template, mark location. Cut hole.



Attach trim plate to box. See Photo B. Pull wire/cables. Install box assembly in opening.



Tighten mounting wing screws to pull the box securely against the wall board. See Photo B.



TVBU505 with power in one side; low voltage in the other. CED13 (page O-6) used to secure wall plate to box.

Recessed Steel TV BOX™

For new or existing construction. Metallic, recessed combo boxes for power and/or low voltage for class 2 wiring of satellite or cable TV, speakers, etc.



TVBS505



TVBS507



TVBS613


FEATURES AND BENEFITS

- Steel box with non-metallic paintable white or black trim plate
- Easy to install, secure installation
- Mounting wings on two-gang and three-gang styles hold boxes securely against the wall in retrofit projects
- Boxes screw-mount to stud in new construction
- Two hour fire rating
- Optional covers for unused boxes

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|--------|-------|
| TVBS505* | 37955 | 2-Gang steel box w/ white non-metallic trim plate | 1 | 4 | 6.818 | 6.698 | 3.937 |
| TVBS507 | 37956 | 3-Gang steel box w/ white non-metallic trim plate | 1 | 4 | 6.818 | 7.930 | 3.937 |
| TVBS613 | 09633 | 4-Gang steel box with white non-metallic trim plate | 1 | 1 | 7.000 | 17.000 | 3.848 |
| TVBS613BL | 09660 | 4-Gang steel box with black non-metallic trim plate | 1 | 1 | 7.000 | 17.000 | 3.848 |
| TVB613C | 09631 | 4-Gang white cover | 5 | 5 | 7.000 | 17.000 | .127 |

*Optional box covers available on page Q-4.

PATENTED.



Installation Instructions



New Work

Attach box to stud using #6 screws. Pull wires. (New Installation)



Retrofit

Cut a hole using enclosure, without trimplate, as a template. (Mounting wings hold box in wall. Retrofit)



After drywall is installed, add trim plate, then install enclosure assembly to the wall with outer screws.



Finished Installed Shot.

Scan For Video



Plastic Recessed TV Box™ with Angled Openings

For new or existing construction. Non-metallic, recessed combo boxes for power and low voltage for class 2 wiring of satellite or cable TV, speakers, etc.



TVB712



TVB713


FEATURES AND BENEFITS

- Non-metallic, paintable trim plate
- For new or old work
 - Positioning tabs for 1/2" wall thickness assure accurate placement on stud in new construction
 - For retrofit, use enclosure (without the trim plate) as a template for the wall opening
- Optional cover available for TVB713

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|--------|-------|-------|
| TVB712 | 09712 | Power and/or low voltage | 1 | 1 | 10.210 | 7.561 | 3.906 |
| TVB713 | 09713 | Power and multiple low voltage openings w/ interchangeable tray. | 1 | 1 | 17.000 | 7.000 | 3.906 |
| TVB613C | 09631 | 4-Gang white cover (fits TVB713) | 5 | 5 | 17.000 | 7.000 | .127 |

Add suffix "GC" to Catalog # when ordering in Canada, for example TVB713GC.

PATENTED.



Installation Instructions

Retrofit



Cut a hole using enclosure next to stud. Use box without trim plate, as a template. Pull wires and insert box in hole.



Assemble trim plate. (Retrofit must also use a minimum of (2) #6 x 1-5/8" wood screws in adjacent stud.)

New Work



Attach box to stud through slotted holes. Use minimum of (2) #6 x 1-5/8" wood screws. Pull wires.



Installed TVB712.

Installed TVB713.



Scan For Video



Recessed TV Box™ for Power and Low Voltage

Non-metallic and metallic, combination power and low voltage box. For power and phone/cable/speaker/surround sound installations.



TVB613

Note: Receptacle and cover plates are not included.



TVB613C

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ PLATE COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------------------------|----------|---------|-------|--------|-------|
| TVB613 | 09630 | 4-Gang w/ white trim plate | 1 | 1 | 7.000 | 17.000 | 3.880 |
| TVB613BL | 09634 | 4-Gang w/ black trim plate | 1 | 1 | 7.000 | 17.000 | 3.880 |
| TVB613C | 09631 | 4-Gang white cover | 5 | 5 | 7.000 | 17.000 | .127 |


Add suffix "GC" to Catalog # when ordering in Canada, for example TVB613GC.

PATENTED.



FEATURES AND BENEFITS

- Use metallic boxes where metal raceways are required
- Perfect for flat screen plasma/LCD televisions
- For new or existing construction
- Recessed, so plugs do not protrude from wall
- Trim ring covers cut edge of drywall
- Trim ring (TVB613) and cover (TVB613C) are textured/paintable
- (2) low voltage mounts are built-in
- Low voltage separator provided for built-in 2-gang device box so power and low voltage can be combined



Installation Shots



Scan For Video



TV BRIDGE™ II Kits

Non-metallic pre-wired, pre-assembled box kits for flat screen TV installations.

FEATURES AND BENEFITS

- Pre-wired for easy install
- Mounting wing screws hold the boxes secure against the wall
- Plugs and connections stay inside the recessed boxes so TV mounts flush against the wall
- No mess! - wires stay hidden behind the wall

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG |
|----------------|--------------------------|---|----------|---------|
| TVBRA1K | 24180 | w/ single-gang boxes | 1 | 1 |
| TVBRA2K | 24181 | w/ 2-Gang power/low voltage box | 1 | 1 |
| TVBRA3K | 24195 | 2-Gang power/low voltage box | 1 | 1 |
| TVB712BK | 12781 | w/ 2-Gang power/low voltage box (power w/ angled opening) | 1 | 1 |

Add suffix "GC" to Catalog # when ordering in Canada, for example TVBRA1KGC.

PATENTED.



| Kits | TVBRA1K | TVBRA2K | TVBRA3K | TVB712BK |
|----------|---|---|---|---|
| Contents | Single gang recessed box containing an outlet is connected to 7 feet of NM cable. Second single gang recessed box connected to the NM cable and includes a pre-wired 4 foot 110V outlet plug, trim, and face plate. | Double gang recessed box containing low-voltage and power outlet connected to 7 feet of NM cable. Second Double Gang recessed box containing low-voltage and power connected to the NM cable and includes a pre-wired 4 foot 110V outlet plug, trim plate and face plate. | Double gang recessed box containing low-voltage and power outlet connected to 7 feet of NM cable. Second single gang recessed box connected to the NM cable and includes a pre-wired 4 foot 110V outlet plug, trim, and face plate. | Double gang recessed box containing low-voltage and an angled power outlet connected to 7 feet of NM cable. Second Double Gang recessed box containing low-voltage and power connected to the NM cable and includes a pre-wired 4 foot 110V outlet plug, trim plate and face plate. |

Installation Instructions



Cut Top hole in wall for the TV. Cut Lower hole directly below the top hole, close to existing outlet. Drop the pre-wired device box assembly and cable through the top hole. Insert box and tighten wings.



Pull pre-wired device assembly through the bottom hole.



Attach device box to trim plate with screws provided. Secure trim plate to wall with mounting wing screws. Install CED130 in 2-Gang boxes. Pull cables.





Scan For Video




Metal and Non-Metallic 8 x 10 TV BOX™

Non-metallic, installation versatility, and perfect for Home Theater Installations. For new or retrofit work.




FEATURES AND BENEFITS

- Accepts standard-style plates with receptacles and decorator-style devices with plates - and Arlington's SCOOP™ series entrance plates and hoods
- Mounting wing screws hold box secure against wall
- Supplied with cover blanks, wall plate, cable entry device (CED130) and cable connectors for unused openings
- 1-1/2" knockout for ENT or other low voltage wiring
- CULUS Listed



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------------------------------------|----------|---------|--------|--------|-------|
| TVBS810 | 09757 | 8"x10" power/low voltage box (steel) | 1 | 1 | 12.531 | 10.656 | 3.140 |
| TVBU810* | 09758 | 8"x10" power/low voltage box | 1 | 1 | 12.531 | 10.656 | 3.140 |
| TVB810C | 24193 | Cover Fits TVBS810 or TVBU810 | 1 | 10 | 12.530 | 10.656 | 0.140 |

*Add suffix "GC" to Catalog # when ordering in Canada, for example TVBU810GC.



Installation Instructions

New Work



Retrofit



Finished Installation



Ideal for home theater systems where multiple connections are needed for sound systems, satellite TV, cable TV, DVRs, and more. Box can be installed horizontally or vertically.

Scan For Video




Low Profile TV Box™

For flush-to-the-wall tv installations on walls as shallow as 3/4". Non-metallic. Plugs stay inside box so TV mounts closer to the wall. Mounting wing screws hold box securely in the wall. For new work or retrofit.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------------------------------|----------|---------|--------|-------|-------|
| TVL508 | 52307 | 5"x8" power and/or low voltage box | 1 | 4 | 10.210 | 7.561 | 1.852 |

Add suffix "GC" to Catalog # when ordering in Canada, for example TVL508GC.
PATENT PENDING.



Low Profile TV Bridge™ Kit

For flush-to-the-wall tv installations on walls as shallow as 3/4". For new work or retrofit.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG |
|----------------|--------------------------|---|----------|---------|
| TVL2508K | 52305 | 5"x8" power/ low voltage recessed TV Bridge Kit | 1 | 1 |



Add suffix "GC" to Catalog # when ordering in Canada, for example TVL2508KGC.
PATENT PENDING.



TVL2508K

FEATURES AND BENEFITS

- Plugs stay inside upper box so TV mounts closer to the wall
- Mounting wing screws hold box securely in the wall
- Applications in new work or retrofit include furring strips on concrete block walls, and 2x2, 2x3 and 2x4 or larger studs
- Kit includes all you need to install a flat screen TV close to a wall and connect to additional components

Installation Instructions for TVL2508K



After locating position of TV and installing mounting bracket, cut holes for upper and lower boxes in a clear space within the same stud bay.



Position lower box so that supplied cord reaches existing receptacle (or power conditioner). Feed NM cable connector from lower box, behind the wall, to upper box opening. Low voltage cable and speaker wire may also be pulled at this time.



Install box/power cord assembly by tightening four wing screws.



Install trim plate. Pull NM cable through connector. Install box in hole by tightening wing screws (see 3).



Attach electrical receptacle to receptacle mounting bracket.



Attach receptacle mounting bracket to box.

Scan For Video



TV Bridge™ Kit

Kit includes two recessed power/low voltage combo boxes and all the connections you need (except NM cable) to install a flat screen TV and additional components.



Includes...

- (2) TVBR505 recessed dual voltage boxes
- (2) cover plates
- (2) CED1 entrance hoods
- (2) CED130 cable entry device
- (1) KD4550 45° knockout device
- (1) tamper-resistant duplex receptacle
- (1) 4 ft. 14 AWG cord
- (1) LPCG50W cord grip
- installation screws
- (3) wire nuts

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG |
|----------------|--------------------------|--|----------|---------|
| TVBR2505K | 09658 | 2 recessed power/low voltage combo boxes and connections | 1 | 1 |

*Add suffix "GC" to Catalog # when ordering in Canada, for example TVBR2505KGC.



Finished Installation



There's no need to run cable from a panel box or cut holes in your framing members. Just cut 2 holes in the wall and access power from an existing nearby source.

FEATURES AND BENEFITS


- Fast, easy, convenient - saves time and money!
- Secure installation. Good looks. A great finish.
- All wires stay hidden behind the wall - no messy wires running down the wall from TV to components
- Plugs stay inside the electrical box - don't protrude past the wall
- Mounting wings hold boxes securely against the wall when screws are tightened.
- Paintable trim plate
- 18.0 cubic inch recessed boxes.

Low Voltage Mounting Brackets

Single through 4-gang brackets for installations on existing construction. Designed to install LOW VOLTAGE Class 2 ONLY.


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|----------|---------|-------|-------|-------|-------|-----------|
| LV1 | 58175 | 10 | 100 | 5.460 | 4.250 | 2.500 | 1.690 | 1/4" - 1" |
| LV2 | 10952 | 5 | 50 | 5.460 | 4.250 | 4.185 | 1.750 | 1/4" - 1" |
| LV3 | 09600 | 5 | 50 | 5.570 | 4.250 | 6.000 | 1.700 | 1/4" - 1" |
| LV4 | 09601 | 5 | 50 | 5.570 | 4.250 | 7.810 | 1.700 | 1/4" - 1" |

Dim E refers to wall thickness adjustment.



FEATURES AND BENEFITS


- Non-metallic – better than metal and costs less too!
- For communications, cable TV, computer wiring.
- CAT 5 listed
- Adjusts to fit 1/4" to 1" thick wallboard, paneling, or drywall
- Bracket is its own template for cut out
- Mounting wings hold bracket securely against wall when screws are tightened




LV1



LV2




LV3



LV4

For Low Voltage Fire Alarm Installations too!



Arlington's LV2, for existing construction, and LVMB2, for new construction (see pg. O-4), can also be used for the installation of fire alarms.

Installation Instructions



Locate bracket position. Level. Trace inside of LV1 and cut on the outside of the line.

Scan For Video



Low Profile Low Voltage Mounting Bracket

Single gang for use with 1/4" or 5/8" drywall installed on cast concrete or concrete block walls with furring strips LOW VOLTAGE Class 2 ONLY.



LV1LP

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|
| LV1LP | 58177 | Single Gang | 10 | 100 | 4.260 | 2.500 | 1.200 |
| LV2LP | 23102 | 2-Gang | 5 | 50 | 4.260 | 4.185 | 1.200 |


PATENT PENDING.



E253895 LR49636

FEATURES AND BENEFITS

- Non-metallic – better than metal and costs less too
- Bracket is its own template for cut out
- Adjusts to fit 1/4" to 5/8" thick wallboard, paneling, or drywall
- For communications, cable TV, computer wiring
- Mounting wings hold bracket securely against wall when screws are tightened



Non-Metallic Wire Bushings for Class 2 Wire

For installation of low voltage wire through wall finish. Covers cut edges of opening. Paintable. Designed to install LOW VOLTAGE Class 2 ONLY.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|----------|---------|-------|-------|-------|-------|-------|
| WB500 | 52950 | 100 | 100 | .500 | .750 | .281 | .875 | .400 |
| WB875 | 52951 | 100 | 100 | .875 | .750 | .281 | 1.250 | .750 |
| WB112 | 52952 | 50 | 50 | 1.125 | .750 | .281 | 1.500 | 1.000 |
| WB200 | 52953 | 50 | 50 | 2.000 | .750 | .281 | 2.500 | 1.875 |

PATENT PENDING.

FEATURES AND BENEFITS

- Provides a great-looking job and easy, smooth insertion of cable through wall
- Quick installation with a drill bit or a hole saw
- Easy entry and exit of low voltage cable or speaker wire through wall
- The attractive way to finish cut edges



Nail or Screw On Low Voltage Mounting Brackets for New Construction

Single through 4-gang brackets for the installation of LOW VOLTAGE Class 2 ONLY.



LVS1



LVN2



LVN3



LVS4

Scan For Video




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------------|----------|---------|-------|-------|-------|
| LVN1 | 00261 | Nail On Style | 50 | 50 | 2.810 | 4.170 | 1.500 |
| LVN2 | 00275 | Nail On Style | 25 | 25 | 5.492 | 4.170 | 1.500 |
| LVN3 | 00277 | Nail On Style | 10 | 10 | 7.804 | 4.170 | 1.500 |
| LVN4 | 00278 | Nail On Style | 10 | 10 | 9.615 | 4.170 | 1.500 |
| LVS1 | 00262 | Screw On Style | 50 | 50 | 2.810 | 4.170 | 1.500 |
| LVS2 | 00280 | Screw On Style | 25 | 25 | 5.492 | 4.170 | 1.500 |
| LVS3 | 00282 | Screw On Style | 10 | 10 | 7.804 | 4.170 | 1.500 |
| LVS4 | 00283 | Screw On Style | 10 | 10 | 9.615 | 4.170 | 1.500 |

PATENTED. ADDITIONAL PATENTS PENDING.



FEATURES AND BENEFITS

- Non-metallic
- Built-in loop to tie off cable
- Eliminates pushback
- Comes complete with nails parked in place ready to install!
- Installs in 25% less time than steel or plastic mud rings
- Nail-on ("N" styles) for wood studs
- Screw-on ("S" styles) for metal studs



LOWER COST THAN STEEL MUD RINGS



LVN1



LVN2




LVS1



LVS2

Low Voltage Mounting Brackets for New Construction

Designed to install LOW VOLTAGE Class 2 ONLY. Mounts vertical or horizontal on wood or metal studs.



LVH1

LVH1K

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|----------|---------|-------|-------|-------|-------|
| LVH1 | 10979 | 50 | 50 | 4.552 | 3.187 | 2.000 | 1.205 |
| LVH1K | 10984 | 50 | 50 | 4.552 | 3.187 | 2.000 | 1.205 |


PATENTED. ADDITIONAL PATENTS PENDING.



E253895 LR49636

FEATURES AND BENEFITS

- Non-metallic
- Sturdy tabs provide extra-secure vertical or horizontal mounting of class 2, low voltage wiring.
- Convenient wire tie-off through slot at top
- Versatile LVH1K permits the use of 3/4" EMT or a 1" fitting.
- Costs 20% less than metal extension rings!



LVH1

LVH1K

Low Voltage Mounting Brackets for New Construction

Designed to install LOW VOLTAGE Class 2 ONLY.



LVMB1

LVMB2

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|----------|---------|-------|-------|-------|-------|
| LVMB1 | 14364 | 10 | 100 | 4.158 | 3.147 | 1.970 | .375 |
| LVMB2 | 14365 | 5 | 50 | 4.158 | 4.842 | 1.970 | .375 |


PATENTED.



E253895 LR49636

FEATURES AND BENEFITS

- Non-metallic
- For communications, cable TV, computer wiring
- Cat 5 listed
- Permits the use of 3/4" EMT
- Works with 1/2" or 5/8" drywall
- Available in single or double-gang models



LVMB1

LVMB2



Scan For Video



Recessed Low Voltage Mounting Brackets

Single through 4-gang brackets for retrofit or new construction. Available in paintable white (trim plate). Designed to install **LOW VOLTAGE Class 2 ONLY**.



LVU1W

FEATURES AND BENEFITS


- Non-metallic
- Suitable for old or new work
- Quick and easy installation and it's recessed so connectors don't extend past the wall surface
- Adjusts to fit 1/4" to 1-1/2" wall thicknesses
- Mounting wings hold bracket securely against wall when screws are tightened
- Recessed bracket includes loops for tie-off; two attachable knockouts; one device plate; one trim plate; and four screws

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------|----------|---------|-------|-------|-------|
| LVU1W | 00285 | Single Gang/White | 1 | 4 | 6.698 | 4.200 | 2.000 |
| LVU2W | 20011 | 2-Gang/White | 1 | 4 | 6.698 | 6.012 | 2.048 |
| LVU3W | 20012 | 3-Gang/White | 1 | 1 | 6.818 | 7.930 | 2.048 |
| LVU4W | 20013 | 4-Gang/White | 1 | 1 | 6.818 | 9.742 | 2.048 |

PATENT PENDING.



E253895 LR49636



Installation Instructions for Existing Wall

- Determine bracket location. Using bracket without trim plate as a template. Level. Mark. Cut hole.
- Attach trim plate to bracket with supplied screws. Insert bracket assembly into opening.
- Tighten mounting wing screws to hold bracket securely against wall board.
- Finished installation. **LVU1W** shown. Connectors **stay inside** this recessed low voltage mounting bracket.

Installation Instructions for New Work

- Option:** Insert knockouts in openings (back) if installing conduit. Knockouts fit 3/4" (as shipped) and 1" (break out center).
- Note positioning tabs and loops for tying off cable.
- Mount bracket to stud.
- Option:** Attach 3/4" or 1" conduit as desired (3/4" shown).

Cable Entry Bracket with Slotted Cover

White non-metallic cable entry device with slotted cover for low-voltage wire.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| CE1RP | 10560 | Non-metallic bracket with reinforced, slotted cover | 25 | 25 | .771 | 4.406 | 2.918 |

PATENTED.

FEATURES AND BENEFITS

- Installs with a 3.5" hole saw in less than a minute
- Adjusts to fit 1/4" to 1-1/2" wall thicknesses

Installation Shots



Cable Entry Device with Slotted Cover

White non-metallic cable entry device with slotted cover for low-voltage wire. Includes (2) #6 screws.





| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| CED130 | 13015 | Non-metallic bracket with slotted cover | 1 | 25 | .534 | 4.111 | 1.450 |

PATENTED.

FEATURES AND BENEFITS

- Non-metallic
- Organizes low voltage cable in a neat bundle



45° Knock-Out Entry Device

White, non-metallic 45° knock-out entry device for installation of 1/2" trade-size fittings. Includes (2) #6 screws.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|
| KD4550 | 83668 | Single-Gang | 1 | 25 | 1.198 | 4.125 | 1.450 |

PATENTED.

FEATURES AND BENEFITS

- 1/2" KO at 45° for the installation of 1/2" trade size fittings
- Can also be used as a cable entry device for low voltage cable



THE SCOOP™ Reversible, Non-Metallic Cable Entrance Hoods for Existing Cable


White cable entrance hood for use with decorator style wall plates. Protects cable and provides installation versatility. Designed to install LOW VOLTAGE Class 2 ONLY.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ PLATE COLOR | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-----------------------------|----------|---------|-------|-------|-------|
| CED1 | 10465 | Single-Gang/White | 1 | 25 | 1.450 | 4.112 | 1.708 |
| CED13 | 13000 | Single-Gang/White | 1 | 25 | 1.450 | 4.112 | .410 |
| CEDH1 | 10478 | Single-Gang, Horiz. /White | 1 | 25 | 1.450 | 4.112 | 1.510 |

PATENTED.

Includes (2) #6 screws.



Installation Instructions



FEATURES AND BENEFITS

- Reversible for installation versatility – Use it facing **IN** or **OUT**!
- Protects low voltage cable against damage
- Best way to run cable where you need it
- CED13 provides widest opening for cables with large connectors


Easy to Install

Use one or more of Arlington's low voltage mounting brackets (LV1 - LV4 not supplied) to install CED Series.

Scan For Video



*Note: LV1 through LV4 are available on O-1



THE SCOOP™ Reversible, Non-Metallic Cable Entrance Plates for Existing Cable


Protects cable and provides installation versatility. Non-rusting, white paintable plastic. Designed to install LOW VOLTAGE Class 2 ONLY.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------------------|----------|---------|-------|-------|-------|
| CE1 | 10460 | Single-Gang | 1 | 25 | 2.853 | 4.620 | 1.513 |
| CE2 | 10461 | 2-Gang | 1 | 25 | 4.562 | 4.620 | 1.759 |
| CEH1 | 10480 | Horiz. Scoop Plate | 1 | 25 | 4.620 | 2.853 | 1.500 |

PATENTED.

Includes screws that match plate color.



Easy to Install!



CE2 with SCOOP facing IN



CE2 with SCOOP facing OUT

FEATURES AND BENEFITS

- Reversible for installation versatility – Use it facing **IN** or **OUT**!
- Offers both cable protection and good looks
- Best way to cover existing cable

Each of our SCOOPS mounts directly to the wall with drywall screws. For added support, mount to one of Arlington's low voltage mounting brackets; LV1 to LV4.



*Note: LV1 through LV4 are available on O-1

Scan For Video




THE SCOOP™ Reversible, Non-Metallic Cable Entrance Plates for Existing Cable

Protects cable and provides installation versatility. Removable lower plate for easier access to cables that are already run. Non-rusting, white paintable plastic. Designed to install LOW VOLTAGE Class 2 ONLY.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|
| CER1 | 10473 | Single-Gang | 1 | 25 | 2.853 | 4.620 | 1.513 |
| CER2 | 10474 | 2-Gang | 1 | 25 | 4.562 | 4.620 | 1.759 |

PATENTED.

Includes screws that match plate color.



Easy to Install!



CER2 with Scoop facing **OUT** & lower plate removed.



CER2 with Scoop facing **OUT**. Lower plate secured.

Each of our SCOOPS mounts directly to the wall with drywall screws.

For added support, mount to one of Arlington's low voltage mounting brackets; LV1 to LV4.

FEATURES AND BENEFITS

- Reversible for installation versatility – Use it facing **IN** or **OUT**!
- Offers both cable protection and good looks
- Best way to cover existing cable
- Lower plate is removable for easier and quicker access to cables that are already run

*Note: LV1 through LV4 are available on O-1

The Loop™

Hanger for communications cable support. For CAT 5, 6, 7 cable and fiber optic cable.



TL20

TL25



TL50

TL50 holds up to a 5" diameter bundle of CAT 5 or fiber optic cable!

The **LOOP**™

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | LOOP SIZE | # CAT 5 CABLES | UNIT PKG | STD PKG | DIM A | DIM B | LOAD RATING |
|----------------|--------------------------|-----------|----------------|----------|---------|--------|-------|-------------|
| TL20 | 38084 | 2" | 60 | 100 | 100 | 11.375 | .652 | 25 |
| TL25 | 38085 | 2-1/2" | 100 | 50 | 50 | 12.250 | 1.500 | 25 |
| TL2520 | 22031 | 2-1/2" | 100 | 20 | 20 | 12.250 | 1.500 | 25 |
| TL50 | 38086 | 5" | 300 | 25 | 25 | 22.500 | 5.000 | 75 |
| TL20P* | 38087 | 2" | 60 | 100 | 100 | 11.375 | .652 | 25 |
| TL25P* | 38088 | 2-1/2" | 100 | 50 | 50 | 12.250 | 1.500 | 25 |
| TL50P* | 38089 | 5" | 300 | 25 | 25 | 22.500 | 5.000 | 75 |


*"P" indicates UV Rated.

PATENTED.



FEATURES AND BENEFITS

- Easy to use...cheaper than trays!
- Flexible and non-metallic
- Holds 2" to 5" diameter bundle of CAT 5 or fiber optic cable – without damaging the cable.
- Available with or without UV rating
- Versatile mounting – rotates to any angle!
- TL25 holds the same amount of cable as a J-hook, at half the cost!



Installation Shots



Single Hanger

1. Single LOOP mounted parallel to beam.
2. Single LOOP mounted perpendicular to beam.

(TL50 shown)

Multiple Hangers

3. Stacked – perpendicular mounting
4. Stacked – parallel mounting

(TL50 shown)

Note: Listed for use in environmental air handling spaces per 2014 NEC code requirements 300.22(c).

Scan For Video



Cable Standoffs

Positions non-metallic sheathed cable, phone/data cable, and coaxial cable. Installs with a screw or nail. Nail included with CS4.



CS4



CS7

CS4 Holds...

- One 14/3 to one 10/3
- Three 14/2 W/G to three 10/3

CS7 Holds...

- Up to five runs of 12/2 non-metallic sheathed cable.
- Up to eight runs of Cat 5 cable.
- Up to four runs of Cat 6 cable.
- Up to five runs of coaxial cable.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------|---------|-------|-------|-------|
| CS4 | 50174 | 100 | 100 | 4.100 | .750 | 1.200 |
| CS7* | 71007 | 100 | 100 | 3.490 | .880 | .740 |



*UL and CSA only
Note: For position only.

FEATURES AND BENEFITS

- Positions cables at a safe distance from nailing surface
- CS4 provides a neat, organized cable installation and prevents tangles
- CS7 positions cable 2" from a furring strip or 2x4 stud
- CS7 features positive lock to keep cables in place
- Positions both flat and round NM cables
- Complies with 2014 NEC Article 300.4d



"D" Rings



Non-conductive. Smooth bearing surfaces for easy wire management.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | WIRING SPACE | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|--------------|---------|-------|-------|-------|-------|-------|
| D22 | 40022 | 2.25 x 2 | 100 | 2.756 | 4.867 | 4.381 | 3.137 | 1.498 |
| D33 | 40033 | 3.25 x 3.25 | 100 | 3.768 | 6.117 | 5.631 | 4.387 | 2.553 |
| D35 | 40035 | 3.25 x 5 | 100 | 3.730 | 8.268 | 7.782 | 6.538 | 4.711 |

FEATURES AND BENEFITS

- Designed with two mounting holes per side for several mounting methods
- Will not damage conductor insulation



Cable Supports

Ideal for supporting runs of low voltage cables. For new construction or retrofit. Non-metallic.






T23W

T23H

T23F

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|----------------------|---------|-------|-------|-------|-------|
| T23H | 38063 | Support Bracket | 25 | 5.500 | 3.880 | 3.620 | 1.500 |
| T23F | 38066 | Flat Surface Bracket | 25 | 5.750 | 2.850 | 3.600 | 2.190 |
| T23W | 38068 | Wall Mount Bracket | 10 | 2.410 | 5.240 | 5.970 | - |

PATENTED.



Insulating Bushings

Press fit. Holds firmly in place when pulling cables.

For use with EMT, Rigid, IMC, PVC.



Example:
Telephone cable protected by EMT insulating bushing.

Arlington's Insulating Bushings protect cables from abrasion by the conduit. Examples: Power, Cable TV, computer datalines, telephone/modem, audio/video cables, alarm systems, security systems. Conduit is often used to protect cables where damage could occur in a house or building.

Note: Meets 2014 NEC code requirements for 300.15(c) protection. Listed for use in environmental air handling spaces per 2014 NEC code requirements 300.22(c).

For use with EMT.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| EMT50 | 12200 | 1/2 | 100 | 1000 | .531 | .840 |
| EMT75 | 12205 | 3/4 | 100 | 1000 | .531 | 1.056 |
| EMT100 | 12220 | 1 | 100 | 100 | .625 | 1.280 |
| EMT125 | 12225 | 1-1/4 | 100 | 100 | .625 | 1.660 |
| EMT150 | 12230 | 1-1/2 | 100 | 100 | .625 | 1.915 |
| EMT200 | 12235 | 2 | 50 | 50 | .625 | 2.377 |
| EMT250* | 12240 | 2-1/2 | 25 | 25 | 1.225 | 3.062 |
| EMT300* | 12245 | 3 | 25 | 25 | 1.225 | 3.690 |
| EMT350* | 12250 | 3-1/2 | 25 | 25 | 1.231 | 4.187 |
| EMT400* | 12255 | 4 | 25 | 25 | 1.233 | 4.815 |

NEW!

Split Insulating Bushings

| | | | | | | |
|----------|-------|-------|----|----|-------|-------|
| EMT200S | 15301 | 2 | 50 | 50 | 0.875 | 2.327 |
| EMT250S* | 12270 | 2-1/2 | 25 | 25 | 1.240 | 3.065 |
| EMT300S* | 12271 | 3 | 25 | 25 | 1.240 | 3.695 |
| EMT350S* | 12272 | 3-1/2 | 25 | 25 | 1.240 | 4.311 |
| EMT400S* | 22001 | 4 | 25 | 25 | 1.240 | 4.812 |

*Can also be used with Rigid, IMC, PVC.

For use with Rigid, IMC, PVC.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| RGD50 | 51930 | 1/2 | 100 | 1000 | .531 | .989 |
| RGD75 | 51932 | 3/4 | 100 | 1000 | .531 | 1.185 |
| RGD100 | 51933 | 1 | 100 | 100 | .625 | 1.542 |
| RGD125 | 51934 | 1-1/4 | 100 | 100 | .625 | 1.891 |
| RGD150 | 51935 | 1-1/2 | 100 | 100 | .625 | 2.062 |
| RGD200 | 51936 | 2 | 50 | 50 | .625 | 2.655 |



NEW!



The new EMT400S insulating bushing is split for easy installation when cables are already in place. They press fit onto conduit and secure with a cable tie. When used for cable protection only, these insulating bushings are a perfect substitution for costly fittings.



Place board over bushing and tap onto EMT or Rigid with hammer.

Non-Metallic Bushings for Metal Studs


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | STUD SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-----------|----------|---------|-------|-------|-------|-------|
| SB13 | 40115 | 2 X 4 | 500 | 500 | 5.670 | 2.500 | .505 | 1.300 |
| SB130 | 40130 | 2 X 4 | 100 | 100 | 5.670 | 2.500 | .505 | 1.300 |
| SB13BL | 40151 | 2 X 4 | 25 | 250 | 5.670 | 2.500 | .505 | 1.300 |

These bushings fit existing irregular shaped holes in metal studs, alleviating the need to punch holes in metal studs, weakening the structural member. Use these bushings to comply with paragraph 300.4(b)(1) of the 2014 NEC code which states that: "In both exposed and concealed locations where nonmetallic-sheathed cables pass through either factory or field punched, cut, or drilled slots or holes in metal members, the cable shall be protected by bushings or grommets covering all metal edges and securely fastened in the opening prior to installation of the cable."

PATENTED.



FITS
a standard
1" KNOCKOUT





SB13




SB13BL

Installation Instructions

To install these bushings in an irregular shaped hole, pass one end of the joined connector through the hole in the stud. Snap the bushing and the washer ends together. There's no need to separate the two halves. If a punched hole is required, the SB13 can be installed in a standard 1" trade size, round punched hole (1-3/8" diameter). Snap the bushing end into the hole.



Common hole configurations in metal studs.




THE EASY WAY TO PUT A RECEPTACLE IN THE FLOOR

FLOOR BOXES

**EXPANDED
LINE**

OF KITS, BOXES, COVERS & ACCESSORIES



Flip Lid Cover
for concrete box

Made in USA 

With a variety of floor box kits and individual metal covers and accessories, Arlington offers just about any option you could possibly need.

Our **UL Listed Floor Box Kits** come with single-gang non-metallic boxes with either a non-metallic or metal cover. They're available in three styles... for existing floors, adjustable to fit floors up to 2" and for new concrete pours.

Our **NEW FLOOR BOX LINE** for existing or new floors, features cost-effective kits, boxes, steel covers, and a variety of accessories that deliver convenience and interchangeability with many other manufacturers' floor boxes.

- Single and two-gang floor box kits with steel boxes... and a combination box kit with an installed divider for power and low voltage in the same box
- Gasketed metal covers with flip lids or threaded plugs to protect receptacle, also sold separately

View Video




Arlington



Non-Metallic Concrete Floor Boxes with Non-Metallic Covers

Low cost, clean, and neat concrete floor boxes. For New Concrete pours.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION RECTANGULAR COVER | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------------------|----------|---------|-------|-------|-------|
| FLBC101W | 04352 | White, Threaded Plugs | 1 | 1 | 4.125 | 6.500 | 6.199 |
| FLBC101LA | 04353 | Light Almond, Threaded Plugs | 1 | 1 | 4.125 | 6.500 | 6.199 |
| FLBC101BR | 04355 | Brown, Threaded Plugs | 1 | 1 | 4.125 | 6.500 | 6.199 |
| FLBC101BL | 04354 | Black, Threaded Plugs | 1 | 1 | 4.125 | 6.500 | 6.199 |
| FLBCF101W | 06950 | White, Flip Lids | 1 | 1 | 4.125 | 6.000 | 6.199 |
| FLBCF101LA | 06951 | Light Almond, Flip Lids | 1 | 1 | 4.125 | 6.000 | 6.199 |
| FLBCF101BR | 06952 | Brown, Flip Lids | 1 | 1 | 4.125 | 6.000 | 6.199 |
| FLBCF101BL | 06953 | Black, Flip Lids | 1 | 1 | 4.125 | 6.000 | 6.199 |

PATENTED.



FEATURES AND BENEFITS

- Non-metallic boxes with gasketed box covers in four decorator colors; white, black, brown, light almond
- Cover gasket prevents water intrusion
- Low cost solution
- Threaded plugs or "flip lid" protect receptacle when not in use



Includes: Concrete box, mud cover, (4) 3/4" plugs, (1) 1/8" spacer, (1) 1/4" spacer, (1) 1/2" spacer and (1) 3/4" spacer, mounting bracket, duplex receptacle, gasketed cover plate, (5) #6-32 x 1/2" long cover plate screws, (4) #8 x 5/8" long sheet metal screws, #8 x 1-1/4" long sheet metal screws and threaded plugs (or flip lids)

Scan For Video




Installation Instructions



1 Install mud cover; set concrete box. Install plugs in openings not used for conduit. Pull conductors through openings.



2 (Concrete poured around box)



3 After concrete sets, trim box to finished floor height.



4 Install mounting bracket on concrete box...



5 ...through (4) outer holes on bracket, into corresponding holes in the box (#8 screws provided).



6 Wire tamper-resistant receptacle; install in box.



7 Install back plate and gasketed cover (#6-32 screws provided). Insert threaded blanks.



8 Supplied spacers allow for adjustment to final floor thickness.

Concrete Floor Boxes with Metal Covers

Competitively priced, clean, and neat concrete floor boxes. For New Concrete pours.



Includes: Concrete box, mud cover, (4) 3/4" plugs, (1) 1/8" spacer, (1) 1/4" spacer, (1) 1/2" spacer and (1) 3/4" spacer, mounting bracket, duplex receptacle, gasketed cover plate, (5) #6-32 x 1/2" long cover plate screws, (4) #8 x 5/8" long sheet metal screws, #8 x 1-1/4" long sheet metal screws and threaded plugs (or flip lids)


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION RECTANGULAR COVER | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------------------------|----------|---------|-------|-------|-------|
| FLBC101MB | 52265 | Brass, Threaded Plugs | 1 | 1 | 4.125 | 6.500 | 6.199 |
| FLBC101NL | 52452 | Nickel-Plated Brass, Threaded Plugs | 1 | 1 | 4.125 | 6.500 | 6.199 |
| FLBCF101MB | 52454 | Brass, Flip Lids | 1 | 1 | 4.152 | 6.022 | 6.199 |
| FLBCF101NL | 52455 | Nickel-Plated Brass, Flip Lids | 1 | 1 | 4.152 | 6.022 | 6.199 |

PATENTED.



FEATURES AND BENEFITS

- Non-metallic boxes with gasketed metal covers in brass or nickel-plated brass
- Cover gasket prevents water intrusion
- Competitively priced
- Threaded plugs protect receptacle when not in use




Installation Instructions



1 Install mud cover; set concrete box. Install plugs in openings not used for conduit. Pull conductors through openings.



(Concrete poured around box)



2 After concrete sets, trim box to finished floor height.



3 Install mounting bracket on concrete box...



4 ...through (4) outer holes on bracket, into corresponding holes in the box (#8 screws provided).



5 Wire tamper-resistant receptacle; install in box.



Install back plate and gasketed cover (#6-32 screws provided). Insert threaded blanks.




Supplied spacers allow for adjustment to final floor thickness.

Scan For Video



Non-Metallic Adjustable Floor Boxes

Low cost, clean, and neat adjustable floor boxes that fit most floor heights up to 2".



FLBAR101LA



FLBA101LA

FEATURES AND BENEFITS


- Non-metallic boxes with gasketed box covers in four decorator colors; white, black, brown, light almond
- Cover gasket prevents water intrusion
- Threaded plugs or "flip lid" protect receptacle when not in use
- Low cost solution

Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION RECTANGULAR COVER | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------------------|----------|---------|-------|-------|-------|
| FLBA101W | 04344 | White, Threaded Plugs | 1 | 4 | 4.250 | 5.155 | 4.031 |
| FLBA101LA | 04345 | Light Almond, Threaded Plugs | 1 | 4 | 4.250 | 5.155 | 4.031 |
| FLBA101BR | 04347 | Brown, Threaded Plugs | 1 | 4 | 4.250 | 5.155 | 4.031 |
| FLBA101BL | 04346 | Black, Threaded Plugs | 1 | 4 | 4.250 | 5.155 | 4.031 |
| FLBAF101W | 04340 | White, Flip Lids | 1 | 4 | 3.750 | 4.655 | 4.047 |
| FLBAF101LA | 04341 | Light Almond, Flip Lids | 1 | 4 | 3.750 | 4.655 | 4.047 |
| FLBAF101BR | 04343 | Brown, Flip Lids | 1 | 4 | 3.750 | 4.655 | 4.047 |
| FLBAF101BL | 04342 | Black, Flip Lids | 1 | 4 | 3.750 | 4.655 | 4.047 |
| ROUND COVER | | | | | | | |
| FLBAR101W | 04348 | White, Threaded Plugs | 1 | 4 | 5.800 | 5.800 | 4.031 |
| FLBAR101LA | 04349 | Light Almond, Threaded Plugs | 1 | 4 | 5.800 | 5.800 | 4.031 |
| FLBAR101BR | 04351 | Brown, Threaded Plugs | 1 | 4 | 5.800 | 5.800 | 4.031 |
| FLBAR101BL | 04350 | Black, Threaded Plugs | 1 | 4 | 5.800 | 5.800 | 4.031 |

PATENTED.




Includes: (1) adjustable floor box, (1) tamper-resistant (TR) duplex receptacle, (1) cover plate w/gasket, flip lids (or threaded plugs), (2) #6-32 x 1" long screws, (2) #6 drywall screws, (1) NM94 connector, (1) NM900 plug, (1) cap (covers adjustable screw hole in cover plate)

Installation Shots





Adjustable Floor Boxes with Metallic Covers

Competitively priced, clean, and neat adjustable floor boxes that fit most floor heights up to 2".




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION RECTANGULAR COVER | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------------------|----------|---------|-------|-------|-------|
| FLBA101MB | 52259 | Brass, Threaded Plugs | 1 | 4 | 4.250 | 5.155 | 4.031 |
| FLBA101NL | 52450 | Nickel-Plated, Threaded Plugs | 1 | 4 | 4.250 | 5.155 | 4.031 |
| FLBAF101MB | 13805 | Brass, Flip Lids | 1 | 4 | 4.000 | 4.646 | 4.047 |
| FLBAF101NL | 13806 | Nickel-Plated, Flip Lids | 1 | 4 | 4.000 | 4.646 | 4.047 |
| ROUND COVER | | | | | | | |
| FLBAR101MB | 52261 | Brass, Threaded Plugs | 1 | 4 | 5.800 | 5.800 | 4.031 |
| FLBAR101NL | 52451 | Nickel-Plated, Threaded Plugs | 1 | 4 | 5.800 | 5.800 | 4.031 |


PATENTED.



Includes: (1) adjustable floor box, (1) tamper-resistant (TR) duplex receptacle, (1) cover plate w/gasket, flip lids (or threaded plugs), (2) #6-32 x 1" long screws, (2) #6 drywall screws, (1) NM94 connector, (1) NM900 plug, (1) cap (covers adjustable screw hole in cover plate)



Installation Shots



FEATURES AND BENEFITS

- Non-metallic boxes with gasketed metal covers in brass or nickel-plated
- Cover gasket prevents water intrusion
- Competitively priced
- Threaded plugs protect receptacle when not in use

Scan For Video



Non-Metallic Floor Boxes with Non-Metallic Covers for Existing Floors

UL Listed, low cost way to put a receptacle in an existing floor. Oversized rectangular cover - with threaded plugs or flip lids - hides miscut flooring.



FLBR101LA



FLBRF101BL

Includes: Floor box, duplex receptacle, (1) NM94 connector, back plate, gasketed cover, (5) #6-32 cover plate screws and threaded plugs or flip lids

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|-------|-------|-------|
| FLBR101W | 04356 | Rectangular w/Threaded Plugs, White | 1 | 4 | 4.125 | 6.500 | 3.738 |
| FLBR101LA | 04357 | Rectangular w/Threaded Plugs, Light Almond | 1 | 4 | 4.125 | 6.500 | 3.738 |
| FLBR101BR | 04359 | Rectangular w/Threaded Plugs, Brown | 1 | 4 | 4.125 | 6.500 | 3.738 |
| FLBR101BL | 04358 | Rectangular w/Threaded Plugs, Black | 1 | 4 | 4.125 | 6.500 | 3.738 |
| FLBRF101W | 16253 | Rectangular w/Flip Lids, White | 1 | 4 | 4.100 | 5.970 | 3.738 |
| FLBRF101LA | 16252 | Rectangular w/Flip Lids, Light Almond | 1 | 4 | 4.100 | 5.970 | 3.738 |
| FLBRF101BR | 16251 | Rectangular w/Flip Lids, Brown | 1 | 4 | 4.100 | 5.970 | 3.738 |
| FLBRF101BL | 16250 | Rectangular w/Flip Lids, Black | 1 | 4 | 4.100 | 5.970 | 3.738 |


See P-4 for a QR code to view our Floor Box video.

PATENTED.



FEATURES AND BENEFITS

- Low-cost non-metallic boxes with gasketed box covers in four decorator colors
- Cover gasket prevents water intrusion
- Threaded plugs or flip lids protect receptacle when not in use
- Oversized covers hide miscut flooring



Installation Instructions



Finished Installation



FLBR101LA



FLBRF101W

Non-Metallic Boxes with Metal Covers for Existing Floors

The low-cost way to install a receptacle in an existing floor.



FLBR101NL



FLBRF101MB

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| FLBR101MB | 52263 | Rectangular w/Threaded Plugs, Brass | 1 | 4 | 4.125 | 6.500 | 3.738 |
| FLBR101NL | 52453 | Rectangular w/Threaded Plugs, Nickel-Plated | 1 | 4 | 4.125 | 6.500 | 3.738 |
| FLBRF101MB | 16254 | Rectangular w/Flip Lids, Brass | 1 | 4 | 4.125 | 6.000 | 3.738 |
| FLBRF101NL | 16255 | Rectangular w/Flip Lids, Nickel-Plated | 1 | 4 | 4.125 | 6.000 | 3.738 |


See P-4 for a QR code to view our Floor Box video.

PATENTED.



FEATURES AND BENEFITS

- Non-metallic boxes with gasketed metal covers in brass or nickel-plated brass
- Cover gasket prevents water intrusion
- Competitively priced
- Threaded plugs protect receptacle when not in use



Installation Shots



FLBR101MB



FLBRF101NL

Includes: Floor box, duplex receptacle, (1) NM94 connector, back plate, gasketed cover, (5) #6-32 cover plate screws and threaded plugs or flip lids

Metal Covers with Flip Lids

Single and 2-gang covers with flip lids that fit Arlington's floor boxes and a variety of other manufacturer's boxes. Includes cover, gaskets and tamper resistant receptacle(s).

NEW!

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|--|----------|---------|-------|-------|
| FLB5330MB | 22017 | Brass Cover, Single Gang w/2 Flip Lids | 1 | 10 | 5.000 | 2.900 |
| FLB5330NL | 22018 | Nickel-plated Cover, Single Gang w/2 Flip Lids | 1 | 10 | 5.000 | 2.900 |
| FLB5550MB | 22036 | Brass Cover, 2-Gang w/4 Flip Lids | 1 | 10 | 5.018 | 5.018 |
| FLB5550NL | 22037 | Nickel-plated Cover, 2-Gang w/4 Flip Lids | 1 | 10 | 5.018 | 5.018 |



FLB5550MB

FLB5330NL


Installation Shots



FLB5330NL (Cover Only)



FLB5550MB (Cover Only)



Metal Covers with Threaded Plugs

Single and 2-gang covers with threaded plugs that fit Arlington's floor boxes and a variety of other manufacturer's boxes. Includes cover, gaskets, and tamper resistant receptacle(s).

NEW!

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|---|----------|---------|-------|-------|
| FLB5320MB | 22013 | Brass Cover, Single Gang w/2 Threaded Plugs | 1 | 10 | 2.850 | 4.937 |
| FLB5320NL | 22014 | Nickel-plated Cover, Single Gang w/2 Threaded Plugs | 1 | 10 | 2.850 | 4.937 |
| FLB5540MB | 22005 | Brass Cover, 2-Gang w/4 Threaded Plugs | 1 | 10 | 4.662 | 4.937 |
| FLB5540NL | 22033 | Nickel-plated Cover, 2-Gang w/4 Threaded Plugs | 1 | 10 | 4.662 | 4.937 |




FLB5540MB

FLB5320MB

Installation Shots



FLB5320NL Cover Only



See P-4 for a QR code to view our Floor Box video.

Combo Floor Box Kit with Installed Low Voltage Divider

Square metal cover has flip lids to protect the receptacles when not in use. For new and existing floors.

NEW!

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-----------------------------|----------|---------|-------|-------|-------|
| FLB5552MB | 22050 | Square Cover, Brass | 1 | 10 | 5.018 | 5.018 | 3.764 |
| FLB5552NL | 22051 | Square Cover, Nickel-plated | 1 | 10 | 5.018 | 5.018 | 3.764 |



FLB5552MB



Installation Shots



FLB5552MB



FLB5552NL



Includes:

Two-gang steel combo box with installed low voltage divider, metal cover with flip lids, gaskets, (1) duplex receptacle, (1) low voltage duplex plate, and mounting screws.

Floor Box Kit with Steel Box and Metal Cover

Kit includes steel box (single or 2-gang), gaskets, receptacle(s), and mounting screws

NEW!

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|-------|-------|-------|
| FLB5331MB | 22019 | Brass Cover, Single Gang w/2 Flip Lids | 1 | 10 | 2.900 | 5.000 | 3.725 |
| FLB5331NL | 22020 | Nickel-plated Cover, Single Gang w/2 Flip Lids | 1 | 10 | 2.900 | 5.000 | 3.725 |
| FLB5551MB | 22038 | Brass Cover, 2-Gang w/4 Flip Lids | 1 | 10 | 5.018 | 5.018 | 3.764 |
| FLB5551NL | 22039 | Nickel-plated Cover, 2-Gang w/4 Flip Lids | 1 | 10 | 5.018 | 5.018 | 3.764 |





FLB5331NL

Installation Shots



FLB5551MB



Includes:

Steel box (single or 2-gang), metal cover with flip lids, gaskets, receptacle(s), and mounting screws.

Floor Box Kit with Steel Box and Metal Cover with Threaded Plugs

For new and existing floors.

NEW!

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| FLB5321MB | 22015 | Brass Cover, Single Gang w/2 Threaded Plugs | 1 | 10 | 2.850 | 4.937 | 3.725 |
| FLB5321NL | 22016 | Nickel-plated Cover, Single Gang w/2 Threaded Plugs | 1 | 10 | 2.850 | 4.937 | 3.725 |
| FLB5541MB | 22034 | Brass Cover, 2-Gang w/4 Threaded Plugs | 1 | 10 | 4.662 | 4.937 | 3.725 |
| FLB5541NL | 22035 | Nickel-plated Cover, 2-Gang w/4 Threaded Plugs | 1 | 10 | 4.662 | 4.937 | 3.725 |





FLB5321MB



FLB5321NL

FEATURES AND BENEFITS

- Low cost convenient way to install a receptacle in the floor
- Gasketed metal cover prevents water intrusion
- Threaded plugs in cover protect receptacle when not in use
- Cover kits also available. See page P-7.



Installation Shots



FLB5321NL



FLB5321MB



FLB5541MB



FLB5541NL

Includes:

Steel box (single or 2-gang), gaskets, receptacle(s), and mounting screws.


Floor Box Accessories

For new concrete.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|-------|-------|-------|
| FLBC4500 | 22010 | 4.5" Non-Metallic Round Box with Plugs, Low Voltage Divider and Mud Cover | 1 | 5 | 5.950 | 4.937 | 3.933 |
| FLB6230MB | 22025 | Cover Kit 6" Round Brass w/2 Flip Lids (fits FLBC4500LR) | 1 | 10 | 5.700 | 0.125 | - |
| FLB6230NL | 22026 | Cover Kit 6" Round Nickel-plated w/2 Flip Lids (fits FLBC4500LR) | 1 | 10 | 5.700 | 0.125 | - |
| FLB6220MB | 22021 | Cover Kit 6" Round Brass w/2 Threaded Plugs (fits FLBC4500LR) | 1 | 10 | 5.700 | 0.125 | - |
| FLB6220NL | 22022 | Cover Kit 6" Round Nickel-plated w/2 Threaded Plugs (fits FLBC4500LR) | 1 | 10 | 5.700 | 0.125 | - |
| FLBC4500LR | 22011 | Leveling Ring for FLBC4500 | 1 | 10 | 4.515 | 0.990 | 1.490 |
| FLBT6615MB | 22030 | Round Trapdoor Cover, Brass. Pre-mounted gasket & decorator-style 15A receptacle | 1 | 10 | 5.870 | 2.237 | 0.300 |
| FLBT6615NL | 22031 | Round Trapdoor Cover, Nickel-plated. Pre-mounted gasket & decorator-style 15A receptacle | 1 | 10 | 5.870 | 2.237 | 0.300 |
| FLBT6615LR | 22029 | Leveling Ring for Arlington FLBC4500 box w/FLBT6615 trapdoor style cover | 1 | 10 | 4.515 | 0.990 | 0.500 |
| FLBC4500AR | 22004 | Oversized Adapter Ring for 5" Diameter Concrete Boxes | 1 | 10 | 4.994 | 0.980 | 4.730 |
| FLBC4500Y | 22012 | "Y" Adapter - Provides (2) 1" openings for conduit entering 1" hub | 1 | 10 | 3.140 | 2.937 | 1.531 |


FLBC4500




FLB6230NL & FLB6230MB




FLB6220NL & FLB6220MB




FLBC4500LR




FLBT6615MB & FLBT6615NL




FLBT6615LR



FLBC4500AR



FLBC4500Y




Cover Kits Include:
Cover, gasket, gasket plate, and receptacle




Concrete Rough-In Floor Box and Trim Kits

For new concrete.

NEW!




FLBC101WTK




FLBC101RK

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|---|--------------------------|--|----------|---------|-------|-------|-------|
| FLBC101RK | 13820 | Concrete Box with Plugs and mud cover | 1 | 5 | 6.512 | 4.261 | 5.960 |
| TRIM KITS WITH NON-METALLIC COVERS | | | | | | | |
| FLBC101WTK | 13821 | White Trim Kit with Threaded Plugs | 1 | 1 | 4.125 | 6.500 | - |
| FLBC101LATK | 13822 | Light Almond Trim Kit with Threaded Plugs | 1 | 1 | 4.125 | 6.500 | - |
| FLBC101BRTK | 13823 | Brown Trim Kit with Threaded Plugs | 1 | 1 | 4.125 | 6.500 | - |
| FLBC101BLTK | 13824 | Black Trim Kit with Threaded Plugs | 1 | 1 | 4.125 | 6.500 | - |
| FLBCF101WTK | 13827 | White Trim Kit with Flip Lids | 1 | 1 | 4.125 | 6.000 | - |
| FLBCF101LATK | 13828 | Light Almond Trim Kit with Flip Lids | 1 | 1 | 4.125 | 6.000 | - |
| FLBCF101BRTK | 13829 | Brown Trim Kit with Flip Lids | 1 | 1 | 4.125 | 6.000 | - |
| FLBCF101BLTK | 13830 | Black Trim Kit with Flip Lids | 1 | 1 | 4.125 | 6.000 | - |
| TRIM KITS WITH METAL COVERS | | | | | | | |
| FLBC101MBTK | 13825 | Brass Cover Trim Kit with Threaded Plugs | 1 | 1 | 4.125 | 6.500 | - |
| FLBC101NLTK | 13826 | Nickel Plated Cover Trim Kit with Threaded Plugs | 1 | 1 | 4.125 | 6.500 | - |
| FLBCF101MBTK | 13831 | Brass Cover Trim Kit with Flip Lids | 1 | 1 | 4.152 | 6.022 | - |
| FLBCF101NLTK | 13832 | Nickel Plated Cover Trim Kit with Flip Lids | 1 | 1 | 4.152 | 6.022 | - |




FLBC101RK




Trim Kit Cover

Non-Metallic Cover Colors



White Light Almond Brown Black

Metal Covers



Brass Nickel Plated

Cover Trim Kits Include:

(1) 1/8" spacer, (1) 1/4" spacer, (1) 1/2" spacer and (1) 3/4" spacer, mounting bracket, duplex receptacle, and gasketed cover plate.

Steel Single Gang Floor Outlet Box

NEW!


Box only. For new or retrofit construction.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|
| FLB5319 | 22060 | Single Gang | 1 | 10 | 1.937 | 3.500 | 3.000 |

FEATURES AND BENEFITS


- Metal cover trim kits available on page P-7
- Comes with installed grounding screw
- Adjustable mounting ear
- Features nine 1/2" knockouts
- Boxes compatible with Arlington's floor box cover trim kits and a variety of other manufacturer's covers
- 18.0 Cubic Inches



Steel Two Gang Floor Outlet Box

NEW!


Box only. For new or retrofit construction.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------|----------|---------|-------|-------|-------|
| FLB5548 | 22061 | Two Gang | 1 | 10 | 3.749 | 3.500 | 3.000 |

FEATURES AND BENEFITS

- Metal cover trim kits available on page P-7
- Installed grounding screw
- Adjustable mounting ears
- Features fourteen 1/2" knockouts
- Boxes compatible with Arlington's floor box cover trim kits and a variety of other manufacturer's covers
- 36.0 Cubic Inches



Steel Two Gang Floor Outlet Box with Installed Low Voltage Divider

NEW!


Box only. For new or retrofit construction.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| FLB5549 | 22062 | Two Gang with Installed Low Voltage Divider | 1 | 10 | 3.749 | 3.500 | 3.000 |

FEATURES AND BENEFITS

- Metal cover trim kits available on page P-7
- Low voltage divider comes installed and is removable
- Installed grounding screw
- Adjustable mounting ears
- Features fourteen 1/2" knockouts
- Boxes compatible with Arlington's floor box cover trim kits and a variety of other manufacturer's covers
- 36.0 Cubic Inches



ONE-BOX™ Non-Metallic Outlet Boxes

For new or retrofit construction.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ CU. IN. | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------------------|----------|---------|-------|-------|-------|
| F101 | 43626 | Single Gang Vert. / 22.5 | 50 | 50 | 2.280 | 3.720 | 3.510 |
| F101H | 43634 | Single Gang Horiz. / 22.3 | 25 | 25 | 3.720 | 2.280 | 3.500 |
| F102 | 43640 | 2-Gang Vert. / 41.3 | 25 | 25 | 4.110 | 3.740 | 3.510 |
| F102D | 43544 | Voltage Divider | 25 | 25 | .233 | 3.560 | 3.400 |
| F103 | 43641 | 3-Gang Vert. / 61.0 | 25 | 25 | 5.930 | 3.740 | 3.510 |
| F104 | 43642 | 4-Gang Vert. / 74.5 | 10 | 10 | 7.740 | 3.740 | 3.510 |

Add suffix "GC" to Catalog # when ordering in Canada, for example F101GC.

PATENTED. OTHER PATENTS PENDING.



F101H



Installation Instructions

F101 NEW CONSTRUCTION



Attach ONE-BOX to wood or steel stud with captive installation screws. If the box is too far forward or back, simply back the screws out and reposition.




Pull wire through the knockout connector. (Ships with installed NM cable connector.)

Mounts **DIRECTLY** to **WOOD or STEEL STUD**


FEATURES AND BENEFITS

- For a variety of wall thicknesses – the ONE-BOX is removable, adjustable, and remountable even after the wall is in place
- Fast and easy to install
- Mounts directly to a wood or steel stud for a super secure installation
- Angled screws inside the ONE-BOX affix it firmly to the stud
- For both power and low voltage applications with the F102D voltage divider installed
- NM cable connector supplied

F101 Installation Instructions - RETROFIT



For old work, position ONE-BOX adjacent to stud. Use box as the template to cut hole.



Pull wire. Insert ONE-BOX.



Mount ONE-BOX directly to stud with shipped in place screws.

Non-Metallic Outlet Box for New Construction

Adjustable for wall thicknesses from 1/4" to 1-1/2". It's perfect for use when the final wall thickness is unknown. Mounts directly to a wood or steel stud.



FA101



FA102



FA103



FA104



FA102D


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ CU. IN. | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------------------|----------|---------|-------|-------|-------|
| FA101 | 04241 | Single Gang / 21.0 | 25 | 25 | 3.720 | 2.299 | 3.875 |
| FA102 | 04242 | 2-Gang / 43.5 | 10 | 10 | 3.720 | 4.111 | 3.875 |
| FA102D | 04245 | Voltage Divider | 25 | 25 | 3.531 | 3.775 | .109 |
| FA103 | 04243 | 3-Gang / 65.0 | 10 | 10 | 3.720 | 5.923 | 3.875 |
| FA104 | 04244 | 4-Gang / 87.0 | 10 | 10 | 3.720 | 7.735 | 3.875 |

Add suffix "GC" to Catalog # when ordering in Canada, for example FA101GC.

PATENTED. OTHER PATENTS PENDING.



E170558



FEATURES AND BENEFITS

- Fast and easy to install
- No more set back boxes - IN/OUT BOX depth adjusts before OR after the wall finish is done
- Depth adjustment screw is accessible even after the wall finish is in place
- Secure installation - Mounts to wood or steel studs in new construction
- Complies with 2014 NEC, 314.20 for set back boxes
- FA102D low voltage separator for use with multiple gang versions

Installation Instructions



1 Attach IN/OUT BOX to wood or steel stud with captive installation screws. Feed the wires through the knockout.



2 If the box is too far forward or back, simply adjust the depth by turning the screw.

FA101
NEW CONSTRUCTION

Mounts
DIRECTLY to
WOOD or STEEL
STUD

Recessed Indoor IN BOX™ for New & Retrofit Construction

Non-metallic, recessed electrical boxes with trim plates and wall plates. Low voltage divider included for multiple gang boxes.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / CU. IN. | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| DVFR1W | 14330 | Single Gang / 21.0 | 1 | 4 | 4.200 | 6.698 | .750 |
| DVFR2W | 14331 | 2-Gang, White / 34.0 | 1 | 4 | 6.012 | 6.698 | .750 |
| DVFR3W | 14340 | 3-Gang, White / 49.3 | 1 | 1 | 7.930 | 6.818 | 3.875 |
| DVFR4W | 14342 | 4-Gang, White / 64.5 | 1 | 1 | 9.742 | 6.818 | 3.875 |
| DVFC | 14337 | 2-Gang, White Cover | 10 | 10 | 6.012 | 6.698 | 1.017 |
| DVFR3C | 10570 | Non-Metallic Blank Cover for 3-Gang Box | 10 | 10 | 9.742 | 6.818 | 1.017 |

*Includes Voltage Separator for power and/or low voltage.

†Add suffix "GC" to Catalog # when ordering in Canada, for example DVFR1WGC.



Single Gang Indoor IN BOX includes... Recessed box, trim plate, (1) standard duplex and (1) standard GFCI face plate, (1) NM94 cable connector, (2) mounting screws, and (2) installation screws.



FEATURES AND BENEFITS

- Recessed box allows items, such as furniture, to be placed closer to the wall
- Plugs don't extend past the wall like a regular box
- Trim plate is textured/paintable
- For power or low voltage applications
- Mounting wings hold bracket securely against wall when screws are tightened



New Work...
Screws provided for fast and easy mounting to stud



Attractive!
DVFR1W shown.



Optional box cover.
DVFC shown.



Box positioning tabs are set for 1/2" or 5/8" drywall.

DVFC can be used with the following Arlington Boxes...

- DVFR1W
- DVFR2W
- TVBS505
- TVBU505
- TVBU505BL
- TVBR505K

Scan For Video

Scan For Video



DVFR1W

DVFR2W

Recessed Steel TV BOX™

For new or existing construction. Metallic recessed combo boxes for power and/or low voltage for class 2 wiring of satellite or cable TV, speakers, etc.



TVBS505



TVBS507



TVBS613


FEATURES AND BENEFITS

- Steel box with non-metallic paintable white or black trim plate
- Easy to install, secure installation
- Mounting wings on two- and three- gang styles hold boxes securely against the wall in retrofit projects
- Boxes screw-mount to stud in new construction
- Optional covers for unused boxes

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|--------|-------|
| TVBS505* | 37955 | 2-Gang steel box w/ white non-metallic trim plate | 1 | 4 | 6.818 | 6.698 | 3.937 |
| TVBS507 | 37956 | 3-Gang steel box w/ white non-metallic trim plate | 1 | 4 | 6.818 | 7.930 | 3.937 |
| TVBS613 | 09633 | 4-Gang steel box w/ white non-metallic trim plate | 1 | 1 | 7.000 | 17.000 | 3.848 |
| TVBS613BL | 09660 | 4-Gang steel box w/ black non-metallic trim plate | 1 | 1 | 7.000 | 17.000 | 3.848 |
| TVB613C | 09631 | 4-Gang white cover | 5 | 5 | 7.000 | 17.000 | .127 |

*Optional box covers available on page Q-4.

PATENTED. ADDITIONAL PATENTS PENDING.



Installation Instructions



New Work

Attach box to stud using #6 screws. Pull wires. (New Installation)



Retrofit

Cut a hole using enclosure, without trimplate, as a template. (Mounting wings hold box in wall. Retrofit)



After drywall is installed, add trim plate, then install enclosure assembly to the wall with outer screws.



Finished Installed Shot.

Scan For Video



Multiple Gang Recessed TV BOX™ for Power and Low Voltage

For new or existing construction. Non-metallic, recessed combo boxes for power and low voltage for class 2 wiring of satellite or cable TV, speakers, etc.



TVBU507



TVBU507BL

TVBR505K Kit

Includes: Recessed combo box; (1) tamper-resistant duplex receptacle, (1) CEDH1, (1) CED130, and (1) wall plate.




Photo B - Screws

Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------------------------------|------|---------|-------|-------|-------|
| TVBU505* | 09680 | 2-Gang, White, (1) Power/ (1) LV | 1 | 4 | 6.942 | 6.254 | 3.750 |
| TVBU505BL* | 09681 | 2-Gang, Black, (1) Power/ (1) LV | 1 | 4 | 6.942 | 6.254 | 3.750 |
| TVBR505K* | 09670 | Kit, 2-Gang, White, (1) Power/ (1) LV | 1 | 4 | 6.942 | 6.254 | 3.750 |
| TVBU507 | 09661 | 3-Gang, White, (1) Power/ (2) LV | 1 | 4 | 7.930 | 6.818 | 3.875 |
| TVBU507BL | 09662 | 3-Gang, Black, (1) Power/ (2) LV | 1 | 4 | 7.930 | 6.818 | 3.875 |

Add suffix "GC" to Catalog # when ordering in Canada, for example TVBU505GC.

*Optional box covers available on page Q-4.


PATENTED. ADDITIONAL PATENTS PENDING.



E170558 LR49636

FEATURES AND BENEFITS

- Recessed combo box allows you to mount flat panel TVs and other system components flush against the wall
- For new work...Use supplied screws to install on stud. For convenience, box positioning tabs are set for 1/2" or 5/8" drywall
- Trim plate is textured/paintable and covers edges of cut wall surface
- Mounting wings hold bracket securely against wall when screws are tightened
- For walls up to 1-1/2" thick
- Use with Arlington's SCOOP™ series entrance hoods and plates (see pages O-6 to O-9)



18.0 cu. in.

TVBU507


Includes...

Recessed combo box; (1) trim plate; (1) decorator style cover plate; and installation screws.

Installation Instructions - New Work (TVBU507 shown)



1 Attach box to stud. Use tabs for proper positioning of box depth. See 2.



2 Positioning tabs are set for 1/2" or 5/8" drywall.



3 Attach paintable trim plate with screws provided. See Photo B.



4 Tighten mounting wing screws to pull the box securely against the wall board. See Photo B.

Retrofit Work (TVBU507 shown)



1 Using box, without trim plate as a template, mark place location. Cut hole.



2 Attach trim plate to box. See Photo B. Pull wire/cables. Install box assembly in opening.



3 Tighten mounting wing screws to pull the box securely against the wall board. See Photo B.



4 TVBU505 with power in one side; low voltage in the other. CED13 (page O-6) used to secure wall plate to box.


Plastic Recessed TV Box™ with Angled Openings

For new or existing construction. Non-Metallic recessed combo boxes for power and low voltage for class 2 wiring of satellite or cable TV, speakers, etc.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|--------|-------|-------|
| TVB712 | 09712 | Power and/or low voltage | 1 | 1 | 10.210 | 7.561 | 3.906 |
| TVB713 | 09713 | Power and multiple low voltage openings w/ interchangeable tray. | 1 | 1 | 17.000 | 7.000 | 3.906 |
| TVB613C | 09631 | 4-Gang white cover (fits TVB713) | 5 | 5 | 17.000 | 7.000 | .127 |

Add suffix "GC" to Catalog # when ordering in Canada, for example TVB713GC.



FEATURES AND BENEFITS

- Non-metallic, paintable trim plate
- For new or old work
 - Positioning tabs for 1/2" wall thickness assure accurate placement on stud in new construction
 - For retrofit, use enclosure (without the trim plate) as a template for the wall opening
- Optional covers for unused boxes

Installation Instructions

Retrofit



Cut a hole using enclosure next to stud. Use box without trimplate as a template. Pull wires and insert box in hole.



Assemble trimplate. (Retrofit must also use a minimum of (2) #6 x 1-5/8" wood screws in adjacent stud.)

New Work



Attach box to stud through slotted holes. Use minimum of (2) #6 x 1-5/8" wood screws. Pull wires.



Installed TVB712.



Scan For Video



TV BRIDGE™ II Kits

Non-metallic pre-wired, pre-assembled box kits for flat screen TV installations.

FEATURES AND BENEFITS

- Pre-wired for easy install
- Mounting wing screws hold the boxes secure against the wall
- Plugs and connections stay inside the recessed boxes so TV mounts flush against the wall
- No mess! - wires stay hidden behind the wall

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG |
|----------------|--------------------------|---|----------|---------|
| TVBRA1K | 24180 | w/ single-gang boxes | 1 | 1 |
| TVBRA2K | 24181 | w/ 2-Gang power/low voltage box | 1 | 1 |
| TVBRA3K | 24195 | 2-Gang power/low voltage box | 1 | 1 |
| TVB712BK | 12781 | w/ 2-Gang power/low voltage box (power w/ angled opening) | 1 | 1 |

*Add suffix "GC" to Catalog # when ordering in Canada, for example TVBRA1KGC.

PATENTED.



| Kits | TVBRA1K | TVBRA2K | TVBRA3K | TVB712BK |
|----------|---|---|---|---|
| Contents | <p>Single gang recessed box containing an outlet is connected to 7 feet of NM cable.</p> <p>Second single gang recessed box connected to the NM cable and includes a pre-wired 4 foot 110V outlet plug, trim, and face plate.</p> | <p>Double gang recessed box containing low-voltage and power outlet connected to 7 feet of NM cable.</p> <p>Second Double Gang recessed box containing low-voltage and power connected to the NM cable and includes a pre-wired 4 foot 110V outlet plug, trim plate and face plate.</p> | <p>Double gang recessed box containing low-voltage and power outlet connected to 7 feet of NM cable.</p> <p>Second single gang recessed box connected to the NM cable and includes a pre-wired 4 foot 110V outlet plug, trim, and face plate.</p> | <p>Double gang recessed box containing low-voltage and an angled power outlet connected to 7 feet of NM cable.</p> <p>Second Double Gang recessed box containing low-voltage and power connected to the NM cable and includes a pre-wired 4 foot 110V outlet plug, trim plate and face plate.</p> |

Installation Instructions



Cut Top hole in wall for the TV. Cut Lower hole directly below the top hole, close to existing outlet. Drop the pre-wired device box assembly and cable through the top hole. Insert box and tighten wings.



Pull pre-wired device assembly through the bottom hole.



Attach device box to trim plate with screws provided. Secure trim plate to wall with mounting wing screws. Install CED130 in 2-Gang boxes. Pull cables.



Low Profile TV Box™


For flush-to-the-wall tv installations on walls as shallow as 3/4". Non-metallic. Plugs stay inside box so TV mounts closer to the wall. Mounting wing screws hold box securely in the wall. For new work or retrofit.



NEW!

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------------------------------|----------|---------|--------|-------|-------|
| TVL508 | 52307 | 5"x8" power and/or low voltage box | 1 | 4 | 10.210 | 7.561 | 1.852 |

Add suffix "GC" to Catalog # when ordering in Canada, for example TVL508GC.
PATENT PENDING.



Low Profile TV Bridge™ Kit

For flush-to-the-wall tv installations on walls as shallow as 3/4". For new work or retrofit.



FEATURES AND BENEFITS

- Plugs stay inside upper box so TV mounts closer to the wall
- Mounting wing screws hold box securely in the wall
- Applications in new work or retrofit include furring strips on concrete block walls, and 2x2, 2x3 and 2x4 or larger studs
- Kit includes all you need to install a flat screen TV close to a wall and connect to additional components

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG |
|----------------|--------------------------|---|----------|---------|
| TVL2508K | 52305 | 5"x8" power/ low voltage recessed TV Bridge Kit | 1 | 1 |



Add suffix "GC" to Catalog # when ordering in Canada, for example TVL2508KGC.
PATENT PENDING.

Installation Instructions for TVL2508K

- After locating position of TV and installing mounting bracket, cut holes for upper and lower boxes in a clear space within the same stud bay.
- Lower Box**

Position lower box so that supplied cord reaches existing receptacle (or power conditioner). Feed NM cable connector from lower box, behind the wall, to upper box opening. Low voltage cable and speaker wire may also be pulled at this time.
- Install box/power cord assembly by tightening four wing screws.
- Upper Box**

Install trim plate. Pull NM cable through connector. Install box in hole by tightening wing screws (see 3).
- Attach electrical receptacle to receptacle mounting bracket.
- Attach receptacle mounting bracket to box.

Scan For Video



CAM-LIGHT™ BOX for Suspended Ceilings

Offers a great way to install fixtures and smoke detectors (and more) on a suspended ceiling, drywall ceiling or wall.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ CUBIC INCH | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|
| FL430* | 09740 | Non-Metallic / 27.0 | 1 | 10 | 7.380 | 3.085 | 1.331 |
| FL430S | 09741 | Steel / 17.0 | 1 | 10 | 7.345 | 2.375 | 1.688 |

*Add suffix "GC" to Catalog # when ordering in Canada, for example FL430GC.

Box includes 12' of drop wire, and box. Non-metallic box also includes (2) NM94 cable connectors.

PATENTED.



Installation Instructions

FL430 for Fixtures



1 Cut hole in a ceiling grid with 4" hole saw. 4-1/2" for steel.



2 Install CAM-LIGHT™ box. Rotate to desired position. Tighten mounting wing screws.



3 Add drop wire to loop. Attach to framing member above.



4 To Complete: Using the appropriate KO (1/2" or 3/4") install NM94 cable connector (supplied) and pull cable. Install fixture per manufacturer's instructions.

FEATURES AND BENEFITS

- Designed to install fixtures and more to a suspended ceiling panel – fast with a 4" hole saw
- Rated up to 50 lbs on a suspended ceiling (or drywall ceiling) in combination with the drop wire for support
- Rated up to 10 lbs on a drywall ceiling without drop wire (not for fixtures)
- Rated up to 7 lbs on walls
- Mounting wings hold box securely against ceiling or wall when screws are tightened
- Box may be turned to any angle for proper inline positioning of exit signs and direct lighting
- White, non-metallic, paintable flange
- Steel box version for use where metal raceways are required
- Steel version installs with 4-1/2" hole saw
- Boxes have 1/2" and 3/4" knockouts
- To install a security camera on this box check out our CAM-KIT™ camera mounting kit (SC5) on page M-4

Scan For Video



Power and Low Voltage Box for New Construction

Non-metallic, combination power and low voltage box. For power, phone/cable, and fiber optic installations.



Power Low Voltage

FEATURES AND BENEFITS


- Neatly installs power and phone/cable outlets together, in one location
- Saves time and money
- For wood stud installation, LVD2 features parked in place nails ready for use
- For metal stud installation, LVD2 features screw holes on either side of the front flange (screws not included)
- For raceway, the low voltage side provides a combo 1/2" and 3/4" KO
- Two hour fire rating

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------|---------|-------|-------|-------|
| LVD2 | 10957 | 25 | 25 | 3.625 | 5.360 | 5.000 |

PATENTED.



COMPETITIVELY PRICED!



Installation Instructions

For New Construction




Simple, Nail On Installation...



or Screw onto Metal Stud!

Power and Low Voltage Box for Existing Construction

Non-metallic, combination power and low voltage box. For power, phone/cable, and fiber optic installations.



Power Low Voltage


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|----------|---------|-------|-------|
| LVDR2 | 01000 | 25 | 25 | 4.250 | 4.185 |

PATENTED.



FEATURES AND BENEFITS

- Saves time and money...competitively priced!
- Neatly installs power and phone/cable outlets together, in one location
- Fast and easy installation...bracket is its own template for cut out
- Adjusts to fit 1/4" to 1-1/2" thick wallboard, paneling, or drywall
- For raceway, the low voltage side provides a combo 1/2" and 3/4" KO
- Mounting wings hold bracket securely against wall when screws are tightened
- Includes installed NM connector on power side
- Two hour fire rating



Hole Saw Box™ for Device Retrofit Construction 17.6 Cu. In. Volume

Non-metallic, 3-1/4" diameter sconce/
device box for existing construction. Fits
duplex receptacles and most GFCIs.



FEATURES AND BENEFITS

- Ready to use, easy to install
- 17.6 cu. inch SUPER-SIZE capacity
- No loose parts – self-contained
- Ships with installed NM cable connector and captive fixture bracket installation screws
- Saves time – installs with a 3-1/4" standard hole saw
- Saw teeth cut a path through the drywall for the device screws and hold the device firmly in place
- Rated for light duty 3 lb. fixtures

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ ATTACHMENT | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|----------------------------|----------|---------|-------|-------|-------|-------|
| FSC3227R | 12525 | Retrofit / Screws, Bracket | 25 | 25 | 4.100 | 3.220 | 2.780 | 1.540 |

PATENTED.




**TWO HOUR
FIRE RATING**




SAVES TIME!

Quick, super-easy installation with a hole saw.

17.6 cu. in.



Installation Instructions



1 Cut hole with a 3-1/4" standard hole saw and pull wire. Push box through drywall. Built-in "teeth" create a path for device screws.




2 Pull NM cable through installed hole saw and pull wire. Push box through drywall. Built-in "teeth" create a path for device screws. Tighten bracket screws inside box to seat bracket securely against drywall.



3 Install device (GFCI shown) and maxi-size cover plate (not provided).

Small Diameter Sconce Boxes for Retrofit Construction

Non-metallic, 3-1/4" diameter sconce/
fixture boxes with large interior
volume. 6.8 cu. in.





FSC3212R

FEATURES AND BENEFITS

- Ready to use, easy to install
- No loose parts – totally self-contained
- Ships with installed NM cable connector and captive fixture bracket installation screws
- Small diameter allows most sconce light canopies to cover the box, hiding it completely
- For retrofit construction: sconce lights up to 3 lbs.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ ATTACHMENT | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------------------------|----------|---------|-------|-------|-------|
| FSC3212R | 43633 | Retrofit / Screws, Bracket | 25 | 25 | 4.280 | 3.250 | 1.240 |

PATENTED.



Installation Instructions

FSC3212R - RETROFIT



Cut hole in drywall. Insert box and bracket. Box is secured by tightening screws that pull bracket against drywall.

FITS DOUBLE DRYWALL OR UP TO 1.90".

Use this Box to center a
SCONCE LIGHT
over a **MIRROR**

One-Piece Non-Metallic Boxes

Single and 2-gang boxes for retrofit installations.

Provides fast installation with a hole saw.



FD1RP



FD2RP

FEATURES AND BENEFITS

- Easiest and fastest installation of a device in a retrofit project
- Single-gang FD1RP installs with a 3.5" hole saw and 2-Gang FD2RP installs with a 4.5" hole saw
- Textured paintable front surface
- Adjusts to fit 1/4" to 1-1/2" wall thicknesses
- Mounting wings hold bracket securely against wall when screws are tightened
- Finishes with any standard, mid-size, or maximum wall plate
- Secure, level device installation
- Includes an installed NM cable connector


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ ATTACHMENT | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|-------|-------|-------|
| FD1RP | 75229 | Single-Gang / 18.0 cu. in. / 3.5" diam. hole saw | 25 | 25 | 5.635 | 3.885 | 3.085 |
| FD2RP | 75301 | 2-Gang / 31.0 cu. in. / 4.5" diam. hole saw | 10 | 10 | 5.704 | 5.454 | 2.938 |

Add suffix "GC" to Catalog # when ordering in Canada, for example FD1RPGC.

PATENTED.



FD2RP
install complete!



Installation Instructions



1 Determine box location. Cut opening with a hole saw; 3.5" for single-gang FD1RP, 4.5" for the 2-gang FD2RP.



2 Pull cable(s) from behind the wall. (Easy cable access is another reason to use Arlington's FDRP boxes.)



3 Push cable through connector. Insert box into the opening. Shown with single-gang FD1RP.



4 Level the box. Tighten the mounting "wing" screws to pull the box snug against the drywall.



5 If desired, paint front surface to match wall. Install device.



6 Finish with any standard or mid-size wall plate. (Front surface shown unpainted.)

Scan For Video




Non-Metallic and Plated Steel 4x4 Boxes

For retrofit construction. Screw hole patterns for 4x4 and 2-gang devices. Available in non-metallic (black and red plastic) and plated steel versions.



FSR404BL



FSR404RD



FSR404S



FSR404SRD



FSR404SD

FEATURES AND BENEFITS

- Non-metallic and steel versions in red are ideal for installations of fire alarms or signaling devices
- 1/2" and 3/4" knockouts
- Spring clip holds box securely against wall when screws are tightened
- Weight rating: 6 lbs. for walls; 10 lbs. for ceilings
- Non-metallic boxes include (2) NM94 cable connectors

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ ATTACHMENT | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------------|----------|---------|-------|-------|-------|
| FSR404BL | 00596 | Plastic 4x4 Box, Black | 25 | 25 | 4.250 | 4.185 | 2.796 |
| FSR404RD | 00598 | Plastic 4x4 Box, Red | 25 | 25 | 4.250 | 4.185 | 2.796 |
| FSR404S* | 00597 | Steel 4x4 Box, Plated | 25 | 25 | 4.250 | 4.185 | 2.815 |
| FSR404SRD* | 00599 | Steel 4x4 Box, Red | 25 | 25 | 4.250 | 4.185 | 2.815 |
| FSR404SD* | 00600 | Steel 4x4 Box Divider | 25 | 25 | 3.581 | 0.141 | 2.750 |

*CSA listed.



PATENTED.



E170558 LR49636



For wall thicknesses up to 1-1/4" – field modify bracket for thicknesses greater than 1-1/4".



Typical Installation of Low Voltage Fire Alarm Box using Red 4x4 Box



1 Determine position of device. Cut hole. Pull wire(s) through appropriate knockout (connector). Install box in opening. FSR404RD shown.



2 Install fire alarm (or other device) through the screw holes in the box.

Typical Installation of Device using Steel or Black Plastic 4x4 Box



1 Determine position of device. Cut hole. Pull wire(s) through appropriate knockout (connector). Install box in opening. FSR404S shown.



2 Install devices through the screw holes in the box.

Eliminate all this!...



Using two boxes...



Remove ears...



Position...



Drill and tap...



Add switch box support...

Gangable Plastic Boxes

Build the box you need with these nail and screw-on gangable plastic boxes for new and retrofit work.



FER102 nail-on with one **FER102C** center




FES102 screw-on with one **FE102C** center



FEN102 nail-on with two **FE102C** centers



FES102 screw-on with **FE101** plate
Snap together to create single gang box.



FE102E

FE102D

FEATURES AND BENEFITS


- Use a screwdriver to disassemble or separate the parts. Add or remove the center section(s), then snap the pieces back together... fast and easy!
- Great-looking installation of multiple gang boxes
- Nail-on style for new construction or screw-on style for new or old construction
- For old work, mounting wings hold the box securely against the wall

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|-------|-------|-------|
| FE102C | 01582 | Each adds one gang Center section for FEN102 and FES102 | 10 | 10 | 3.688 | 3.500 | 2.686 |
| FE102D | 01586 | Optional Voltage Divider | 25 | 25 | 3.476 | 3.335 | .125 |
| FE102E | 01585 | Two gang (includes 2 brackets) Mounts with brackets for New Construction | 10 | 10 | 4.250 | 3.500 | 2.236 |
| FEN102 | 01580 | Two gang (includes 1 bracket) Nail-on for New Construction | 1 | 10 | 6.002 | 3.500 | 2.609 |
| FER102 | 01583 | Two Gang w/Mounting Wings for Old Work | 1 | 10 | 4.258 | 3.500 | 2.097 |
| FER102C | 01584 | Each adds one gang Center section for Old Work Use with FER102 | 10 | 10 | 3.615 | 3.500 | 1.812 |
| FES102 | 01581 | Two gang (includes 1 bracket) Screw-on for Retrofit or New Construction | 1 | 10 | 3.688 | 3.500 | 2.044 |
| FE101 | 06930 | Single Gang Plate Converts any box to single gang | 10 | 10 | 3.688 | 3.500 | 2.754 |


PATENTED.



E170558



FE101



Installation Instructions

Assemble



Each section adds one gang to the box. Snap the pieces together to make your desired box. From three to ten gangs.

Disassemble



To disassemble or separate the parts, insert a screwdriver between the tabs at the top of the box (on each side) as shown above, and twist.

**UL Listed
up to
10 GANGS**

(two end sections
plus up to
8 center sections)



FEN102 nail-on with
five **FE102C** centers

Scan For Video



ONE-BOX™ Vapor Boxes for Devices

Versatile, non-conductive outlet box for new construction. Mounts directly to a wood or steel stud.



F101F



FN102F



F103F



FN104FD

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ CU. IN. | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|-------|
| F101F | 12520 | Single Gang Screw-on / 22.0 | 25 | 25 | 5.990 | 4.500 | 3.510 | .500 |
| F102F | 06900 | Two-Gang Screw-on / 42.0 | 10 | 10 | 5.990 | 6.313 | 3.510 | .500 |
| F103F | 06901 | Three-Gang Screw-on / 59.0 | 10 | 10 | 5.990 | 8.125 | 3.510 | .500 |
| F104F | 06902 | Four-Gang Screw-on / 81.0 | 10 | 10 | 5.990 | 9.937 | 3.510 | .500 |
| FN101F | 15130 | Single Gang Nail-on / 23.0 | 20 | 20 | 5.990 | 4.500 | 3.510 | .500 |
| FN102F | 15132 | Two-Gang Nail-on / 43.5 | 10 | 10 | 5.990 | 6.313 | 3.510 | .500 |
| FN103F | 15134 | Three-Gang Nail-on / 63.5 | 10 | 10 | 5.990 | 8.125 | 3.510 | .500 |
| FN104F | 15136 | Four-Gang Nail-on / 85.3 | 10 | 10 | 5.990 | 9.937 | 3.510 | .500 |
| FN101FD* | 15131 | Single Gang Double Drywall Nail-on / 28.0 | 20 | 20 | 5.990 | 4.500 | 4.344 | 1.312 |
| FN102FD* | 15133 | Two-Gang Double Drywall Nail-on / 53.0 | 10 | 10 | 5.990 | 6.312 | 4.344 | 1.312 |
| FN103FD* | 15135 | Three-Gang Double Drywall Nail-on / 77.8 | 10 | 10 | 5.990 | 8.124 | 4.344 | 1.312 |
| FN104FD* | 15137 | Four-Gang Double Drywall Nail-on / 103.5 | 10 | 10 | 5.990 | 9.936 | 4.344 | 1.312 |

* For use with double drywall installation and has a Two hour fire rating

Add suffix "GC" to Catalog # when ordering in Canada, for example F101FGC.

Refer to R-1 and R-2 for additional Vapor Boxes.

PATENTED. ADDITIONAL PATENTS PENDING.




E170558 LR49636



NEW! Installed NM cable connectors with gasket material attached.

Saves time - Pull wire through; knockouts are sealed



FEATURES AND BENEFITS

- Fast and easy to install
- Mounts directly to a wood or steel stud for a super secure installation
- Flange forms a protective barrier against air infiltration

Multi-gang boxes work with the F102D divider



F102D

FEATURES AND BENEFITS

For both power and low voltage applications with the F102D voltage divider installed

See Page Q-1 for Ordering Details.

FLUSH-WITH-THE-CEILING INSTALLATIONS

FAN/FIXTURE BOX

THE LOW COST BOX...WITH ADJUSTABLE STEEL BRACKET AND PLASTIC BOX



FBR423 UL ratings
70 lb fan
Up to 150 lb fixture


Captive
fan bracket
installation
screws



Bracket mounts
securely to joists



Loosen
center screw
to position box
on bracket



FBR423

Patent pending

Made in USA



Arlington's low cost, economical steel fan/fixture bracket with plastic box delivers super-secure, versatile on-center mounting between joists spaced 16" to 24".

- Easy mounting in new construction... fan bracket installation screws ship captive
- Flush installations..Bracket ends are pre-set for 1/2" ceiling; adjustable for ceilings up to 1-1/4" thick.
- Position box anywhere along bracket



**CHECK OUT
OUR ENTIRE LINE
OF FAN BOXES!**

A
Arlington



ONE-BOX™ Side Mount Vapor Boxes for Fixtures

Economical L-shaped fan/fixture boxes mount securely to joist with a shipped-in-place center screw.



FB442F



FB442FD


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ CU. IN. | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|--------------------------------------|----------|---------|-------|-------|-------|-------|
| FB442F | 76220 | Joist Mount Single Drywall/ 15.5 | 25 | 25 | 4.240 | 3.885 | .562 | 2.948 |
| FB443F | 76222 | Fan or Fixture Single Drywall/ 18.8 | 25 | 25 | 4.240 | 5.183 | .562 | 4.246 |
| FB442FD* | 76221 | Joist Mount Double Drywall / 25.0 | 25 | 25 | 4.227 | 4.635 | 1.312 | 2.948 |
| FB443FD* | 76223 | Fan or Fixture Double Drywall / 28.5 | 25 | 25 | 4.227 | 5.933 | 1.312 | 4.246 |

* For use with double drywall installation. Add suffix "GC" to Catalog # when ordering in Canada, for example FB442FGC.

Refer to chart on page R-18 for load ratings and number of single conductors.

Refer to Q-3 for additional Vapor Boxes.

PATENTED.



FEATURES AND BENEFITS

- Fast and easy to install
- Mounts directly to a wood or steel stud for a super secure installation
- Flange forms a protective barrier against air infiltration
- UL Ratings: 70 lb fan/200 lb fixture; CSA: 50 lb fan or fixture



Non-Metallic Vapor Box with Adjustable Steel Bracket

Plastic Vapor Box with Adjustable Steel Bracket for Fans/Fixtures



FBR415F



FBR425F

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ CU. IN. | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|---------------------------------------|----------|---------|-------|------------|
| FBR415F | 72204 | Joist Mount for Fan or Fixture / 18.3 | 5 | 5 | 2.658 | 16" to 24" |
| FBR425F* | 72205 | Joist Mount for Fan or Fixture / 27.5 | 5 | 5 | 3.408 | 16" to 24" |



* For use with double drywall installation.

Add suffix "GC" to Catalog # when ordering in Canada, for example FBR415GC.

Refer to chart on page R-18 for load ratings and number of single conductors.

Refer to Q-3 for additional Vapor Boxes.

PATENTED.



FEATURES AND BENEFITS

- Fast and easy to install
- Mounts directly to a wood or steel stud for a super secure installation
- Flange forms a protective barrier against air infiltration
- UL Fan Ratings: 70 lb at 24" o.c., 110 lb at 16" o.c.
- UL Fixture Ratings: 90 lb at 24" o.c., 150 lb at 16" o.c.
- CSA Ratings: 50 lb fan/fixture at 16"-24" o.c.

ONE-BOX™ Vapor Boxes for Fixtures

Versatile, non-conductive fixture box for new construction. Mounts directly to a wood or steel stud.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ CU. IN. | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------------------|----------|---------|-------|-------|-------|
| F426F | 06903 | Round Screw-on 28.0 | 20 | 20 | 6.250 | 4.230 | .500 |
| FN430F | 15100 | Round Nail-on 30.5 | 20 | 20 | 6.250 | 4.230 | .500 |
| FN440F* | 15120 | Round Nail-on 39.5 | 20 | 20 | 6.250 | 4.230 | 1.250 |


* For use with double drywall installation.

Add suffix "GC" to Catalog # when ordering in Canada, for example F426FGC.

Refer to chart on page R-18 for load ratings and number of single conductors.

Refer to Q-3 for additional Vapor Boxes.

PATENTED.



NEW! Installed NM cable connectors with gasket material attached.

Save time - seal knockouts during installation

FEATURES AND BENEFITS

- Non-metallic, non-conductive
- Ships with captive mounting screws
- Includes additional gasket material for knockouts

Steel ONE-BOX™

Designed for new construction or retrofit, side-mounts to a joist for a super secure, fan-rated installation - with no wobble.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------------------------|----------|---------|-------|-------|-------|
| FBS1423 | 76190 | 2-3/8" Box Depth / 23.0 Cu. In. | 10 | 10 | 3.572 | 4.250 | 2.375 |

Mounts on Side of Joist.

Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.



FEATURES AND BENEFITS

- Fast, easy installation.
- Tabs for 1/2" positioning
- Installation screws ship captive
- Installed NM cable connector
- Two # 10 thread holes, including screws for fan
- Two # 8 thread holes, including screws for fixtures.
- UL rated 70 lb. fan/fixture; cUL rated 50 lb. fan/fixture

NEW CONSTRUCTION



RETROFIT



Steel Pan Fan & Fixture Mounting Boxes

Ceiling fan/fixture pan boxes mount directly to a joist for a secure installation. Steel box.



FEATURES AND BENEFITS



- No loose parts to misplace, totally self-contained!
- Center screw is shipped-in-place
- Competitively priced
- Protective plastic tips on the installation screws for added safety
- Plated steel finish
- Combination hex/Phillips head screws for easy installation with power screwdrivers
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- UL rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / CU. IN. | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|---|----------|---------|-------|-------|
| FBS405 | 76185 | For 1/2" or 5/8" Drywall 6.0 Cu. In. | 25 | 25 | .570 | 4.250 |
| FBS407 | 76187 | For 5/8" Drywall 8.0 Cu. In. | 25 | 25 | .660 | 4.250 |
| FBS405T* | 40500 | For 1/2" or 5/8" Drywall 6.0 Cu. In. | 25 | 25 | .570 | 4.250 |
| FBS407T* | 40700 | For 5/8" Drywall 8.0 Cu. In. | 25 | 25 | .720 | 4.250 |

* Fan/fixture mounting bracket attaches to box through threaded openings using provided #10 screws.

Refer to chart on page R-18 for load ratings and number of single conductors.



Each fan/fixture box includes...

Installation screws, installed NM cable connector, mud cover, additional KOs, and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

Installation Instructions for FBS405



1 Install FBS405 on joist using shipped-in-place screw near center of box.



2 Drill (2) 1/8" diameter holes into joist through the elongated openings on each side of box. Remove the (2) long screws noted above to mount the fan/fixture bracket.



3 Mount the fan/fixture bracket into the drilled holes. And you're ready to install the fan or fixture.

Steel, Octagonal Fan & Fixture Joist Mounting Boxes

Ceiling fan/fixture boxes mount directly to a joist for a super-secure installation. Two styles. Ships ready-to-install. For new work only.



FBS415



FBS415S

FEATURES AND BENEFITS

- No loose parts to misplace, totally self-contained!
- Combination hex/Phillips head screws for easy installation with power screwdrivers.
- FBS415/FBS420 are UL rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture
- FBS415S/FBS420S are UL rated: 70 lb. fan/fixture; CSA rated: 50 lb. fan/fixture

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|-------|
| FBS415 | 75204 | 1-1/2" Box Depth 14.6 Cu. In. Mounts Under Joist | 25 | 25 | 4.250 | 3.572 | 1.500 | - |
| FBS420 | 75200 | 2" Box Depth 20.0 Cu. In. Mounts Under Joist | 25 | 25 | 4.250 | 3.572 | 2.000 | - |
| FBS415S | 75206 | 1-1/2" Box Depth 14.6 Cu. In. Mounts on Side of Joist | 25 | 25 | 4.250 | 3.572 | 2.500 | 6.000 |
| FBS420S | 75202 | 2" Box Depth 20.0 Cu. In. Mounts on Side of Joist | 25 | 25 | 4.250 | 3.572 | 2.500 | 6.000 |

Refer to chart on page R-18 for load ratings and number of single conductors.


PATENTED.



E48106 LR49636



FBS415



FBS415S

FBS415/FBS420 Mount UNDER Joist



FBS415S/FBS420S Mount on SIDE of Joist



Each fan/fixture box includes...
Installed NM cable connector, mud cover, multiple KOs, four installation screws parked-in-place (ready for installer), and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

Steel Fan & Fixture Box Kits for Suspended Ceilings


Plated steel fan/fixture box with adjustable mounting bar. For mounting a fan or fixture on a suspended ceiling grid. FS420SCL and FS427SCL for fixtures only.



FBRS420SC



FS420SCL



FS427SCL

FEATURES AND BENEFITS

- Installs quickly and securely, saves 30 minutes of installation time
- Ships fully assembled
- Comes preset for a 24" grid
- No parts to lose – installation and adjustment screws ship parked in place
- FBRS420SC features breakable, mounting clips to lower box position for ceiling tiles that extend below the grid
- FBRS420SC has **parked** fan/fixture installation screws – ready for easy fan/fixture bracket installation!
- FBRS420SC is UL rated: 70 lb. fan, 70 lb. fixture; CSA rated: 50 lb. fan/fixture
- FS420SCL is UL and CSA rated: 50 lb. fixture
- FS427SCL is UL and CSA rated: 50 lb. fixture

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|-------|-------|--------|
| FBRS420SC*† | 75300 | For Suspended Ceilings 2" Box Depth 20.0 Cu. In. | 1 | 5 | 4.805 | 8.343 | 24.000 |
| FS420SCL | 12526 | For Suspended Ceilings 2" Box Depth 20.0 Cu. In. | 1 | 10 | 3.041 | 3.982 | 25.000 |
| FS427SCL | 12537 | For Suspended Ceilings 1-1/2" Box Depth 30.0 Cu. In. | 1 | 10 | 3.222 | 3.500 | 24.000 |

* Listed for use in environmental air handling spaces per

† Packaged with Wire Grabber™ Kit on page S-2


2014 NEC code requirements 300.22(c).

Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.



E48106 LR49636



Installation Instructions for FBRS420SC



1. Cut a 4-1/16" diameter hole in the center of a 24" ceiling tile. Place box over hole. Snap ends of support bar over the ceiling grid.



Now with WireGrabber™ kit for drop wire support of static loads.



2. Pull cable through installed NM cable connector and remove captive screws for fan/fixture bracket installation.



FBRS420SC Installation Option



To Mount Box Off-Center: Loosen screws and slide box into position.

Installation with FL430 is even faster and it costs less than our FS420SCL fixture box with adjustable bracket.

Steel Fan & Fixture Box with Adjustable Mounting Bracket for Existing Construction

Heavy-duty, plated steel fan/fixture box with fully adjustable mounting bracket for retrofit installations. Adjusts from 16" to 24" o.c. spacing.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------------------------|----------|---------|-------|-------|--------|
| FBRS4200R | 75315 | 2" Box Depth 20.0 Cu. In. | 1 | 10 | 3.563 | 3.438 | 13.979 |

Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.



NEW
Higher Weight Ratings



For Joist or Rafters 16" to 24" on center

FEATURES AND BENEFITS

- No parts to lose – installation and adjustment screws ship parked in place
- Installs quickly and securely between joists or rafters 16" to 24" o.c.
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- UL rated: 70 lb. fan/90 lb. fixture at 24" o.c. and 70 lb. fan/150 lb. fixture at 16" o.c.; CSA rated: 50 lb. fan/fixture

FBRS4200R includes...

Box/bracket, screws to adjust box position, installed NM cable connector, multiple KOs, and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

Installation Instructions



1. Cut a 4-1/16" diameter hole in ceiling. Remove box from sled and fit mounting bracket into hole. Position bracket between joists, with bracket resting on the ceiling.



2. Tighten the hex bar with a wrench to secure bracket between joists. As the hex bar is tightened, bracket ends bite into the joists, holding the unit secure.



3. Pull cable through installed NM cable connector. Reattach box, and center it in hole. Attach fan/fixture bracket with supplied screws.

Scan For Video



Steel Fan & Fixture Mounting Box with Adjustable Mounting Bracket for New Construction

Heavy-duty, plated steel fan/fixture box with fully adjustable mounting bracket. Adjusts from 16" to 24" o.c. spacing.



FEATURES AND BENEFITS

- No loose parts to misplace
- Heavy-duty plated steel construction eliminates fan wobble
- Versatile 16" to 24" on-center positioning
- Bracket preset for 1/2" ceiling thicknesses
- Works on ceilings up to 1-1/4" thick – fully adjustable! For ceiling material greater than 5/8", convenient indicator marks allow you to bend the bracket at the scoreline matching your ceiling depth for a flush ceiling installation.
- Locator tabs included for installation ease
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- UL rated: 70 lb. fan/90 lb. fixture at 24" o.c. and 70 lb. fan/150 lb fixture at 16" o.c.; CSA rated: 50 lb. fan/fixture


Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|--|----------|---------|-------|-------|
| FBS415 | 72250 | For up to 1-1/4" ceiling thickness 15.6 Cu. In. | 1 | 10 | 4.250 | 3.572 |

For fan/fixture BOX dimensions, refer to FBS415 on page R-4.


Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.



Installation Instructions for 1/2" Ceilings

1. Nail "tooth" to joist to temporarily hold bracket in place.
2. Remove parked screws provided on each side of bracket and use them to attach bracket to joists.
3. Use provided box screw to adjust box position from 16" to 24" on-center between joists.
4. Use provided parked fan/fixture installation screws to install fan/fixture mounting bracket. (Installation of drywall not shown.)



FBS415 includes...

Box/bracket, screws to adjust box position, installed NM cable connector & mud cover, multiple KOs, four installation screws parked-in-place (ready for installer), and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

For a **LOWER COST** option, check out **FBR423** on page Q-8

Mounts easily and securely between joists...adjusts from 16" to 24" o.c.



Bend bracket along the scorelines for 3/4", 1", or 1-1/4" ceiling depths!



Steel Adjustable Bracket with Plastic Box

NEW!

Low-cost, economical steel fan/fixture bracket with plastic box delivers super-secure, versatile on-center mounting between joists 16" to 24".



FBR423

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A |
|----------------|--------------------------|--|----------|---------|-------|
| FBR423 | 52310 | Plastic Box with Adjustable Steel Bracket / 23 cu. in. | 1 | 10 | 2.548 |


Refer to chart on page R-18 for load ratings and number of single conductors.

PATENT PENDING.



E170558 LR49636

NEW LOWER COST LARGER BOX
than our FBR415



FEATURES AND BENEFITS

- Fan/fixture installation screws ship captive
- Bracket ends adjust for flush installation on ceilings up to 1-1/4" thick
- **UL rating:**
@ 24" on-center:
70 lb. fan, 90 lb. fixture
@ 16" on-center:
70 lb fan; 150 lb fixture
- **CSA rating:**
50 lb fan or fixture
- 23.0 cubic inch plastic box



Made in USA

Installation Instructions



Bracket mounts securely to joists.



Loosen center screw to position box on bracket.



Bracket ends are pre-set for a 1/2" ceiling. For other ceiling depths, bend the bracket ends along the appropriate score line.

Steel Fan & Fixture Pan Box with Adjustable Mounting Bracket for Wood I-Joists in Existing Construction

Heavy-duty, plated steel fan/fixture box with fully adjustable mounting bracket. For retrofit installations on wood I-beams or rafters set 16 to 24 inches on-center.



FEATURES AND BENEFITS

- No parts to lose – installation and adjustment screws ship parked in place
- Installs quickly and securely on wood I-beams
- Position the box anywhere along the bracket to center the fan/fixture in the room
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- UL rated: 35 lb. fan, 50 lb. fixture; CSA rated: 50 lb. fan/fixture



FBR5407R includes...

Box/bracket, screws to adjust box position, installed NM cable connector, multiple KOs, and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------------------------------------|----------|---------|-------|-------|-------|
| FBR5407R | 72248 | For 1/2" or 5/8" Drywall 8.0 Cu. In. | 1 | 10 | 3.620 | 2.098 | 13.25 |

Refer to chart on page R-18 for load ratings and number of single conductors.




Installation Instructions



1. Cut a 4-3/8" diameter hole in ceiling. Remove pan box from sled and fit mounting bracket into hole, positioning between wood I-joists with feet resting on ceiling.



2. Loosen sled screws and slide over to access hex bar. (Note: no need to remove sled.)



3. Tighten hex bar with a wrench to embed points and secure between I-joists.



4. Tighten sled to hex in center of hole. Pull cable through NM cable connector and remount box. Attach fan/fixture bracket with supplied screws.



Cut away showing FBR5407R installed between wood I-beams

Fan & Fixture Mounting Boxes

Ceiling fan/fixture pan boxes.



FEATURES AND BENEFITS

- No loose parts to misplace – totally self-contained!
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- Works well on double joists or wood I-beams
- Combination hex/Phillips head screws for easy installation with power screwdrivers
- UL rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| FB405 | 72185 | For 1/2" or 5/8" Drywall 6.0 Cu. In. | 25 | 25 | 2.315 | .570 | 4.250 |
| FB405* | 28101 | For 1/2" or 5/8" Drywall 6.0 Cu. In. | 100 | 100 | 2.315 | .570 | 4.250 |
| FB407 | 72177 | For 5/8" Drywall 8.0 Cu. In. | 25 | 25 | 2.315 | .660 | 4.250 |
| FB4070 | 28102 | For 5/8" Drywall 8.0 Cu. In. | 100 | 100 | 2.315 | .660 | 4.250 |

*Bulk packing for lower cost.

Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.




**TWO HOUR
FIRE RATING**

Each fan/fixture box includes...

A ready-to-tighten center screw, installed NM cable connector, mud cover, second KO, and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.



Fan & Fixture Mounting Boxes

Boxes accommodate 1/2" or 5/8" drywall with 3/4" furring strips or hat channel.



FB412



FB423

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---------------------------|----------|---------|-------|-------|-------|
| FB412 | 72189 | Pan Box 14.4 Cu. In. | 25 | 25 | 3.000 | 1.250 | 4.250 |
| FB423 | 72190 | Press-On Box 19.5 Cu. In. | 25 | 25 | 3.000 | 1.250 | 4.250 |

Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.




**TWO HOUR
FIRE RATING**

Each fan/fixture box includes...

A ready-to-tighten center screw, installed NM cable connector, mud cover, second KO, and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

FEATURES AND BENEFITS

- No loose parts to misplace – totally self-contained!
- For use with 1/2" or 5/8" drywall with 3/4" furring strips or hat channel
- Also for double 5/8" drywall
- Attaches securely to joist through shipped-in-place center screw
- UL rated: 70 lb. fan; 200 lb. fixture; CSA rated: 50 lb. fan/fixture



FB412

Nail On Fan & Fixture Boxes with Steel

Mounting Bracket

Plastic box with steel mounting bracket for fast and easy nail on installation to a single or double joist.



FB417S



FB417SLP - Low Profile

Each fan/fixture box includes...

Plastic box with steel mounting bracket, installed NM cable connector, mud cover, second KO, two parked-in-place bracket nails, and two fan/fixture bracket installation screws (screwed in place until removed by installer).


| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|---|----------|---------|-------|-------|-------|
| FB417S | 72171 | For up to 1-1/2" ceiling thickness (Including drywall on furring strips or hat channel) 20.0 Cu. In. | 25 | 25 | 4.563 | 3.500 | 4.279 |
| FB417SLP | 72199 | For 1/2" to 5/8" Ceiling thicknesses only 20.0 Cu. In. | 25 | 25 | 6.625 | 2.906 | 4.570 |

Refer to chart on page R-18 for load ratings and number of single conductors.


PATENTED.



E170558 LR49636
TWO HOUR FIRE RATING



FB417S



FB417SLP

FEATURES AND BENEFITS

- No loose parts to misplace – totally self-contained!
- FB417S features convenient indicator marks for 1/2", 5/8", and 3/4" ceiling thicknesses
- Works well on single or double wood joists
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- FB417SLP also works with wood and manufactured I-beams
- UL rated: 70 lb. fan/fixture; CSA rated: 50 lb. fan/fixture

Installation Instructions



Nails to **SINGLE JOIST**



Saves Time!

Nails to the Joist for a Super Secure Installation!

All photos shown with FB417S

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.



DOUBLE JOIST

Fan & Fixture Mounting Box

Our deepest L-shaped fan/fixture box mounts securely to single or double joists with a shipped-in-place center screw.

Locator posts for positioning of bracket installation screws



FEATURES AND BENEFITS

- No loose parts to misplace – totally self-contained!
- Arlington's deepest fan box!
- Easy wire access
- Locator posts assure proper positioning of fan/fixture bracket
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- UL rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|-------|-------|-------|
| FB444 | 72187 | For 1/2" or 5/8" Drywall 25.6 Cu. In. | 25 | 25 | 5.330 | 4.000 | 4.716 |

Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.



TWO HOUR FIRE RATING



FB444 includes...

A ready-to-tighten center screw, installed NM cable connector, mud cover, multiple KOs, and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

Installation Instructions



1. Position box alongside joist. Tighten center screw, mounting box to joist.



2. Position mounting bracket over locator position.



3. Remove captive bracket installation screws. Use them to mount fan/fixture bracket.



Optional
If necessary, the bottom of the box can be opened to access wires.



4. Pull wires through knockout. (Installation of drywall not shown.)

Press-On Fan & Fixture Mounting Boxes

The fastest, easiest way to mount fans and fixtures. Ships ready-to-install!



FB415

FEATURES AND BENEFITS

- No loose parts to misplace, totally self-contained!
- Gripping tangs press-hold to the joist while you reach for your screwdriver
- Comes with NM connector installed and mud cover in place
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- FB426F's flanged design forms a protective barrier against air infiltration
- UL rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--|----------|---------|-------|-------|-------|
| FB415 | 72167 | For 1/2" or 5/8" Drywall 10.3 Cu. In. | 25 | 25 | 2.250 | .500 | 4.250 |
| FB4150* | 72182 | For 1/2" or 5/8" Drywall 10.3 Cu. In. | 100 | 100 | 2.250 | .500 | 4.250 |
| FB426 | 72179 | For 1/2" or 5/8" Drywall 16.0 Cu. In. | 25 | 25 | 2.625 | .500 | 4.250 |

*Bulk packing for lower cost.

Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.




TWO HOUR FIRE RATING

E170558 LR49636



Each fan/fixture box includes...

Press-on box with ready-to-tighten center screw, installed NM cable connector, mud cover, second KO, and two screws for fan/fixture bracket installation (screwed in place until removed by installer).



Installation Instructions

FB415



1. Press box onto joist. Gripping tangs hold the box in place temporarily.
2. Tighten center screw to secure to joist.
3. Push NM cable through connector.
4. Remove two long, "parked" screws for installation of bracket.
5. Use the screws to install fan/fixture bracket through the oval slots in the box, directly into the joist.

Fan & Fixture Mounting Boxes

Our lowest cost L-shaped fan/fixture boxes mount securely to single or double joists with a shipped-in-place center screw.

Locator posts for positioning of bracket installation screws



FEATURES AND BENEFITS

- No loose parts to misplace – totally self-contained!
- Locator posts assure proper positioning of fan/fixture bracket
- Competitively priced
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- UL rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|---------------------------------------|----------|---------|-------|-------|-------|-------|
| FB442 | 72194 | For 1/2" or 5/8" Drywall 13.4 Cu. In. | 25 | 25 | 4.236 | 3.773 | 4.250 | 3.273 |
| FB443 | 72197 | For 1/2" or 5/8" Drywall 18.3 Cu. In. | 25 | 25 | 4.236 | 5.071 | 4.250 | 4.571 |

Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.



TWO HOUR FIRE RATING



Each fan/fixture box includes...

A ready-to-tighten center screw, installed NM cable connector, mud cover, multiple KOs, and two screws for fan/fixture bracket installation (screwed in place until removed by installer).

Installation Instructions



1. Position box alongside joist. Tighten center screw, mounting box to joist.



2. Position mounting bracket over locator posts to assure proper position. Pull wires through KO.



3. Remove captive bracket installation screws. Use them to mount fan/fixture bracket. (Installation of drywall not shown.)

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

Fan & Fixture Mounting Boxes

for New Construction
Mounts fans and fixtures on sloped or cathedral ceilings.



FB450



FB900

FEATURES AND BENEFITS


- No loose parts to misplace – totally self-contained!
- Large, 8" square mounting surface handles newer fans with larger canopies
- Installs quickly and securely
- FB900 has taller sides to fit cathedral ceilings with angles greater than 80°
- Paintable, textured finish
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- UL rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|--|----------|---------|-------|-------|-------|-------|
| FB450 | 75240 | Fits Sloped Ceilings up to 45° / 14.5 Cu. In. | 1 | 6 | 8.000 | 8.000 | 9.729 | 3.875 |
| FB900 | 75250 | Fits Cathedral Ceilings 80° or greater, 14.5 Cu. In. | 1 | 6 | 8.000 | 8.000 | 6.364 | 3.875 |

Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.




FB450

THE SIMPLE WAY TO A GREAT FINISH!

Each fan/fixture box includes...

Mounting block with built-in electrical box, installed NM94 cable connector, two installation screws ready to tighten, and two parked-in-place fan/fixture bracket installation screws (ready for installer).



FB900

Installation Instructions

FB450



Trim a 2x8, approximately 18" long. Allow the panel to extend 9-11" past the FB450.



Install the FB450 on the 2x8 using the (2) #8 x 1-1/2" long parked screws provided.



Score and trim the FB450 as necessary, keeping bottom of box level. (Short side needs to touch rafter.) Trim wood as necessary to butt it to rafter. Nail or screw assembly to rafter.



Push the cable through the installed cable connector in the electrical box.

FB900



Cut a 2x4 approximately 14" long to span the pitched rafters.



Install the FB900 in the center of the cut 2x4 using the (2) #8 x 1-1/2" long parked screws provided.



Position the 2x4 with the FB900 attached to the angled rafters, keeping bottom of box level, and the short sides of the box touching the angled rafters. Nail or screw the assembly, spanning both angled rafters.



Push the cable through the installed cable connector in the electrical box.

Fan & Fixture Mounting Box with Adjustable Brackets for New Construction

Mounts fans and fixtures on cathedral ceilings between two framing members for perfect centering within room.



FEATURES AND BENEFITS

- Expandable brackets hold box securely between joists – no need to cut and nail 2x4s to center the fan or fixture
- Allows fans/fixtures to be perfectly centered within room
- Large, 8" square mounting surface handles newer fans with larger canopies
- No loose parts to misplace – totally self-contained!
- Installs quickly and securely
- Includes a template to level and position brackets between rafters
- Taller sides fit cathedral ceilings with angles greater than 80°
- Paintable, textured finish
- Fan/fixture installation screws are **parked**...ready for easy fan/fixture bracket installation!
- UL rated: 70 lb. fan/fixture; CSA rated: 50 lb. fan/fixture

Scan For Video



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|--|----------|---------|-------|--------|
| FBX900 | 75224 | Adjustable. Fits Cathedral Ceilings 80° or Greater, 14.5 Cu. In. | 1 | 1 | 2.300 | 13.200 |

For fan/fixture BOX information, refer to FB900 on page R-15.


Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.




FBX900 includes...

Expandable brackets with mounting screws, screws to adjust box position, mounting block with built-in electrical box, installed NM94 cable connector, and two parked-in-place fan/fixture bracket installation screws (ready for installer).



Installation Instructions

Remove and use these screws to attach bracket ends to rafters



Loosen these screws to expand brackets and position box between rafters

"Tooth" holds brackets temporarily in place on rafter



For proper fan/fixture installation, use supplied template to level and position brackets between rafters. Remove captive screws on sides of brackets and use to attach FBX900 assembly to rafters.



Loosen the screws noted above. Slide box to center it between rafters. Tighten screws. Install wires.



Cut and position drywall to fit around the box. (Note: captive screws in box.) Install fan or fixture per manufacturer's instructions using captive installation screws.

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

8" Mounting Block

With built-in box for fan and fixture installations.



FEATURES AND BENEFITS

- Ceiling medallion and electrical box combined
- Supports flood lights, smoke detectors, fans, light fixtures - any fixture needing a safe, strong installation.
- UV rated plastic
- For interior or exterior use
- Mounts directly to soffit or ceiling joist without the need to cut ceiling drywall
- Paintable
- UL rated: 70 lb. fan, 200 lb. fixture; CSA rated: 50 lb. fan/fixture

Note: Install fan or fixture (not included) in accordance with manufacturer's instructions and all local applicable electrical codes, using the parked screws provided.

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION / STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------------------|----------|---------|-------|-------|-------|
| MB8 | 42330 | Flat Mount 6.1 Cu. In. | 1 | 10 | 8.000 | 3.792 | .740 |


Refer to chart on page R-18 for load ratings and number of single conductors.

PATENTED.




MB8 includes...

Two #10 x 3" wood screws, one #8 x 1-1/2" wood screw, two KOs, and one NM94 non-metallic cable connector.



Installation Instructions



1 Locate the ceiling joist using a stud finder or similar device. Drill a hole approximately 1/2" in diameter, in the ceiling next to the joist. Remove desired knockout. Insert the cable connector into the opening. Pull the NM cable through the connector.



2 Using the #8 x 1-1/2" wood screws provided, mount the MB8 to the joist (through the ceiling).



3 Install the fixture or fan mounting bar (provided with the fixture or fan) directly to the joist with the (2) #10 x 3" wood screws and lock washers provided. Wire the fixture or fan following the instructions included with the product.

Fan/Fixture Box Rating and Number of Single Conductors

| CATALOG NUMBER | CUBIC INCHES | UL FAN LOAD RATING (LBS.) | CSA FAN LOAD RATING (LBS.) | UL FIXTURE STATIC RATING (LBS.) | CSA FIXTURE STATIC RATING (LBS.) | # OF SINGLE CONDUCTORS | | |
|----------------|--------------|--------------------------------|----------------------------|---------------------------------|----------------------------------|------------------------|-----|-----|
| | | | | | | #14 | #12 | #10 |
| F426F | 28.0 | - | - | 50 | 50 | - | - | - |
| FB405 | 6.0 | 70 | 50 | 200 | 50 | 3 | - | - |
| FB4050 | 6.0 | 70 | 50 | 200 | 50 | 3 | - | - |
| FB407 | 8.0 | 70 | 50 | 200 | 50 | 4 | 3 | 3 |
| FB4070 | 8.0 | 70 | 50 | 200 | 50 | 4 | 3 | 3 |
| FB412 | 14.4 | 70 | 50 | 200 | 50 | 7 | 6 | 5 |
| FB415 | 10.3 | 70 | 50 | 200 | 50 | 5 | 4 | 4 |
| FB4150 | 10.3 | 70 | 50 | 200 | 50 | 5 | 4 | 4 |
| FB417S | 20.0 | 70 | 50 | 70 | 50 | 10 | 8 | 8 |
| FB417SLP | 20.0 | 70 | 50 | 70 | 50 | 10 | 8 | 8 |
| FB423 | 19.5 | 70 | 50 | 200 | 50 | 9 | 8 | 7 |
| FB426 | 16.0 | 70 | 50 | 200 | 50 | 8 | 7 | 6 |
| FB426F | 16.0 | 70 | 50 | 200 | 50 | 8 | 7 | 6 |
| FB442 | 13.4 | 70 | 50 | 200 | 50 | 6 | 4 | 4 |
| FB442F | 15.5 | 70 | 50* | 200 | 50* | - | - | - |
| FB442FD | 25.0 | 70 | 50* | 200 | 50* | - | - | - |
| FB443 | 18.3 | 70 | 50 | 200 | 50 | 8 | 7 | 7 |
| FB443F | 18.8 | 70 | 50* | 200 | 50* | - | - | - |
| FB443FD | 28.5 | 70 | 50* | 200 | 50* | - | - | - |
| FB444 | 25.6 | 70 | 50 | 200 | 50 | 13 | 11 | 10 |
| FB450 | 14.5 | 70 | 50 | 200 | 50 | 7 | 6 | 5 |
| FB900 | 14.5 | 70 | 50 | 200 | 50 | 7 | 6 | 5 |
| FBR415F | 18.3 | 70 | 50* | 200 | 50* | - | - | - |
| FBR423 | 23.0 | 70 @ 24" o.c. 70 @ 16" o.c. | 50 | 90 @ 24" o.c. 150 @ 16" o.c. | 50 | - | - | - |
| FBR425F | 27.3 | 70 | 50* | 200 | 50* | - | - | - |
| FBRS407R | 8.0 | 35 | 50 | 50 | 50 | 4 | 3 | 3 |
| FBRS415 | 15.6 | 70 @ 24" o.c. 70 @ 16" o.c. | 50 | 90 @ 24" o.c. 150 @ 16" o.c. | 50 | 7 | 6 | 6 |
| FBRS4200R | 20.0 | 70 @ 24" o.c. 70 @ 16" o.c. | 50 | 70 @ 24" o.c. 150 @ 16" o.c. | 50 | - | - | - |
| FBRS420R | 20.0 | 35 | 50 | 50 | 50 | 10 | 8 | 8 |
| FBRS420SC | 20.0 | 70 | 50 | 50 | 50 | 10 | 8 | 8 |
| FBS1423 | 23.0 | 70 | 50 | 70 | 50 | - | - | - |
| FBS405 | 6.0 | 70 | 50 | 200 | 50 | 3 | - | - |
| FBS405T | 6.0 | 70 | 50 | 200 | 50 | 3 | - | - |
| FBS407 | 8.0 | 70 | 50 | 200 | 50 | 4 | 3 | 3 |
| FBS407T | 8.0 | 70 | 50 | 200 | 50 | 4 | 3 | 3 |
| FBS415 | 14.6 | 70 | 50 | 200 | 50 | 7 | 6 | 6 |
| FBS415S | 14.6 | 70 | 50 | 70 | 50 | 7 | 6 | 6 |
| FBS420 | 20.0 | 70 | 50 | 200 | 50 | 10 | 8 | 8 |
| FBS420S | 20.0 | 70 | 50 | 70 | 50 | 10 | 8 | 8 |
| FBX900 | 14.5 | 70 | 50 | 70 | 50 | 7 | 6 | 5 |
| FN430F | 30.5 | - | - | 50 | 50 | - | - | - |
| FN440F | 39.5 | - | - | 50 | 50 | - | - | - |
| MB8 | 6.1 | 70 | 50 | 200 | 50 | 3 | - | - |

* cUL listed

Roof Topper™

Supports raise conduit or raceway
4" - or more - off the roof surface.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D | DIM E |
|----------------|--------------------------|------------------------------------|----------|---------|--------|--------|--------|--------|-------|
| RTS4 | 10492 | Open Base 9" W x 5-5/8" H | 10 | 10 | 9.500 | 1-5/8 | 4.000 | 10.732 | 6.000 |
| RTS12 | 10490 | Open Base 9" W x 12" H | 5 | 5 | 9.500 | 1-5/8 | 10.625 | 11.779 | 8.870 |
| RTS421 | 10493 | Open Base 21" x 5-5/8" H | 5 | 5 | 21.500 | 1-5/8 | 4.000 | 22.697 | 6.000 |
| RTS1221 | 10491 | Open Base 21" W x 12" H | 5 | 5 | 9.500 | 1-5/8 | 10.625 | 11.779 | 8.870 |
| RTS402* | 00916 | 9"W x 4-7/8"H | 10 | 10 | 10.000 | 1-5/8 | 4.185 | 10.000 | 6.000 |
| RTS409L | 52311 | 9"W x 5-5/8"H with Sled | 10 | 10 | 9.5 | 1-5/8" | 4.125 | 10.932 | 6.200 |
| RTSB405 | 00910 | Open Base only 5"W x 4"H | 10 | 10 | 5.281 | - | 4.000 | 6.530 | 6.000 |
| RTSB409 | 00911 | Open Base only 9"W x 4"H | 10 | 10 | 9.500 | - | 4.000 | 10.732 | 6.000 |
| RTSB1209 | 00912 | Open Base only 9"W x 10-3/8"H | 5 | 5 | 9.000 | - | 10.625 | 11.779 | 8.870 |
| RTSE405 | 00913 | Open Base w/strut 5"W x 5-5/8"H | 10 | 10 | 4.750 | 1-5/8 | 4.000 | 6.530 | 6.000 |
| RTSE405L | 52312 | 5"W x 5-5/8"H with Sled | 10 | 10 | 4.750 | 1-5/8 | 4.125 | 6.732 | 6.200 |
| RTSE409 | 00914 | Open Base w/strut 9"W x 5-5/8"H | 10 | 10 | 9.000 | 1-5/8 | 4.000 | 10.730 | 6.000 |
| RTSE409L | 52313 | 9"W x 5-5/8"H with Sled | 10 | 10 | 9.000 | 1-5/8 | 4.125 | 10.932 | 6.200 |
| RTSE1209 | 00915 | Open Base w/strut 9"W x 12"H | 5 | 5 | 9.000 | 1-5/8 | 10.625 | 11.779 | 8.870 |
| RTSL405 | 38010 | Sled to Fit Open Bases 4" x 5" | 10 | 10 | 6.732 | 6.200 | 0.375 | - | - |
| RTSL409 | 38011 | Sled to Fit Open Bases 4" x 9" | 10 | 10 | 10.932 | 6.200 | 0.375 | - | - |

* Rated for 1,000 lbs.


PATENTED.

FEATURES AND BENEFITS

- Allows the contractor to comply with 2014 NEC for temperature adjustment for circular conduit.
- Made of 100% UV resistant recycled material, the heavy-duty base sits on the roof deck without the need for mechanical fasteners.
- Most ship assembled with strut and/or threaded rod installed on base
- Supports up to 2,000 lbs



NEW! SLED STYLE



Sled snaps onto open base to allow for expansion and contraction without damaging the roof surface

Installation Shots



Wire Grabber™ and Kits


Reliable hanging support for fixture boxes, fixtures, cable tray and other static loads up to 75 lbs requiring drop wire support.




FLG3



DWB0805



DWYH0805



DWYT0805



BW580

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | LENGTH |
|----------------|--------------------------|---|----------|---------|--------|
| DWB0805 | 06805 | Straight Kit | 1 | 10 | 5' |
| DWB0812 | 06883 | w/ Looped End | 1 | 10 | 10' |
| DWB0815 | 06815 | holds static loads up to 75 lbs (w/ supplied .080" wire) | 1 | 10 | 15' |
| DWB0820 | 06820 | | 1 | 10 | 20' |
| DWB0830 | 06830 | | 1 | 10 | 30' |
| DWH0805 | 15022 | Straight Kit with Hook holds static loads up to 75 lbs | 1 | 10 | 5' |
| DWH0810 | 15023 | | 1 | 10 | 10' |
| DWT0805 | 15020 | Straight Kit with Toggle holds static loads up to 75 lbs | 1 | 10 | 5' |
| DWT0810 | 15021 | | 1 | 10 | 10' |
| DWY2H0810 | 11312 | "Y" Kit with Hooks Two Pack | 2 | 10 | 10' |
| DWYH0805 | 11307 | 18 Inch "Y" Kit with Hooks | 1 | 10 | 5' |
| DWYH0810 | 11308 | holds static loads up to 75 lbs (w/ supplied .080" wire) | 1 | 10 | 10' |
| DWYH0815 | 11309 | | 1 | 10 | 15' |
| DWYH0820 | 11310 | | 1 | 10 | 20' |
| DWYH0830 | 11311 | | 1 | 10 | 30' |
| DWY2T0810 | 11306 | "Y" Kit with Toggles Two Pack | 2 | 10 | 10' |
| DWY2T0812 | 11314 | | 2 | 10 | 5' |
| DWYT0812 | 11313 | 12 Inch "Y" Kit with Toggles | 1 | 10 | 5' |
| DWYT0805 | 11301 | | 1 | 10 | 5' |
| DWYT0810 | 11302 | 18 Inch "Y" Kit with Toggles holds static loads up to 75 lbs (w/ supplied .080" wire) | 1 | 10 | 10' |
| DWYT0815 | 11303 | | 1 | 10 | 15' |
| DWYT0820 | 11304 | | 1 | 10 | 20' |
| DWYT0830 | 11305 | | 1 | 10 | 30' |
| FLG3* | 01590 | Wire hanger for static loads up to 75 lbs on .080" galvanized braided wire | 50 | 50 | - |
| BW562 | 83775 | 500' Roll of .062" Galvanized Braided Support Wire 50 lb Capacity | 1 | 4 | 500' |
| BW580 | 21250 | 500' Roll of .080" Galvanized Braided Support Wire 75 lb Capacity | 1 | 4 | 500' |

* PATENTED.




NEW Thumb Screw Adjustment

Secure grip on wire:
Tightening this screw engages six points of contact on wire.

FLG3 ships fully assembled.

Easy to use:
Push wire through connector and out the other side. Loop wire back through connector. Tighten screw.



Scan For Video



Snap-on Wire Clip


Galvanized Steel Wire Clip, designed to hold cables/cords securely in place. Ideal for solar panel installation.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-------------------------------|----------|---------|-------|-------|-------|
| SC100 | 06300 | Plated Spring Steel Wire Clip | 100 | 1000 | .484 | .375 | .731 |

FEATURES AND BENEFITS

- Wire Clip Capacity:
 - ONE cable: min .160" to max .425"
 - TWO cables: min .160" to max .300"
- Smooth finish on clip prevents cable damage
- Locking tab secures clip onto sheet metal, fits sheet metal frame up to .080" thick
- Easy, time-saving installation



Installation Instructions




Choose the method of attachment that works best for you.



Snap Wire Clip onto sheet metal up to .080" thick.



Snap one or two USE-2 or PV cables securely in place.




Switch Box Supports

Galvanized steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | MATERIAL DIM |
|----------------|--------------------------|----------|---------|-------|-------|--------------|
| SBS | 18055 | 100 | 1000 | 5.310 | 2.160 | 0.020 |

UL/CSA NOT APPLICABLE.



Box Extenders


Levels and supports the wiring device where the box is set back from the wall surface. Extends the box up to 1-1/2".



BE1



BE2



BE4

BE3

Scan For Video



HEAVY-DUTY PLASTIC
UL Listed!

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------|---------|-------|-------|-------|
| BE1 | 40160 | 25 | 250 | 2.313 | 4.188 | 1.813 |
| BE1BAG | 51905 | 1 | 100 | 2.313 | 4.188 | 1.813 |
| BE2 | 48960 | 25 | 25 | 4.100 | 4.188 | 1.813 |
| BE3 | 48967 | 10 | 10 | 5.937 | 4.188 | 1.813 |
| BE4 | 48968 | 10 | 10 | 7.749 | 4.188 | 1.813 |

BE1BAG includes two #6 x 2" long screws.

PATENTED.




E170558 LR49636

TWO HOUR FIRE RATING

FEATURES AND BENEFITS

- Allows the contractor to comply with 2014 NEC Article 314.20
- Levels and supports the wiring device where the box is set back from the wall surface (adjusts up to a 1-1/2" box extension)
- Works in handy boxes and 4" square electrical boxes with plaster rings for single switches or receptacle
- Functions with all standard devices, switches, and GFCIs
- Manufactured from 105°C continuous use 94V0 rated flame retardant plastic for safer installations



Installation Instructions

PROBLEM..



Electrical box set back from wall surface.

SOLUTION...



1 Pull wires through, then press the BE1 firmly into the electrical box.



2 Attach wires to receptacle. Then tighten screws for a level, fully supported, code compliant installation.

To install without removing device wires, tilt the device through the BE1 at a slight angle, straighten it and tighten the screws!

Ceiling Box Extender

For set back ceiling boxes. Fits 3-1/2" and 4" round or octagonal boxes.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------|---------|-------|-------|-------|
| BE1R | 40161 | 25 | 25 | 4.850 | 4.350 | 1.500 |

PATENTED.




E170558 LR49636

TWO HOUR FIRE RATING

FEATURES AND BENEFITS

- Complies with 2014 NEC Article 314.20
- Extends box up to 1-1/2" to bring it level with ceiling surface
- Trims to accommodate shallow boxes or to avoid obstructions
- Manufactured from 105°C continuous use 94V0 rated flame retardant plastic for safer installations



Box Covers


Covers 4" round or octagonal boxes. Non-metallic. Will not rust.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | BOX SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|----------|----------|---------|-------|-------|-------|
| CP40 | 15040 | 4" | 1 | 40 | 3.500 | 4.750 | .150 |


FEATURES AND BENEFITS

- Paintable to blend with any wall or ceiling
- Comes with white painted screws to blend with cover
- Reusable and flexible
- Will not rust or discolor



Drive Rings

Made of corrosion-resistant galvanized steel, this series of drive rings provides sturdy support for wire and cable.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ STYLE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|--------------------|----------|---------|--------|--------|
| DR1 | 01551 | 1/2" Drive Ring | 100 | 1000 | 1/2" | 1-1/4" |
| DR2 | 01552 | 5/8" Drive Ring | 50 | 500 | 5/8" | 1-3/8" |
| DR3 | 01553 | 7/8" Drive Ring | 50 | 500 | 7/8" | 1-3/8" |
| DR4 | 01554 | 1-1/4" Drive Ring | 25 | 250 | 1-1/4" | 1-7/8" |

FEATURES AND BENEFITS

- Can be used on outside walls, inside walls, wood studs and utility poles
- Quick and easy to install, fastens to surface with a hammer
- Loop is open making it easy to insert or remove cable.
- Size is measurement between loops.



Slip Meter Riser Fitting

Designed to create an expansion joint in the installation of an electrical service entrance.



FEATURES AND BENEFITS

- Fast, easy underground service installations
- Protects cable from freeze/thaw ground movement
- Meets 2014 NEC 300.7(B) and 300.5(J)

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION/ STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|--------------------|----------|---------|-------|-------|-------|
| NM2520 | 54565 | 2" K.O. size | 10 | 10 | 3.329 | 2.625 | 3.276 |

PATENTED.




Installation Instructions



1
Glue NM2520 onto 2-1/2" PVC conduit. Slip 2-1/2" conduit over 2" non-metallic conduit coming from the ground (PVC conduit not supplied).



2
Attach the NM2520 to the bottom of the meter enclosure. 2 to 2-1/2" meter riser fitting holds conduit firmly in place (locknut is not supplied).



Ceiling Box Cover

Covers unused 3-1/2" and 4" round and octagonal boxes prior to the installation of a fan or fixture. Non-rusting, paintable plastic.



Mounting screws are invisible on the ceiling

Covers Pan Boxes!



For box attachment without removing screws

For box attachment using screws provided

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | BOX SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| CP3540 | 54090 | 3-1/2 & 4" | 1/Bag | 50 Bags | .437 | 5.390 | .812 |

Two #8-32 x 3/4" flat head screws and bracket are included.

PATENTED.




IMPROVED FEATURES


- Deeper cover works with pan boxes without the need to cut the post
- Use #8 screws provided or back out existing screws to accept notched bracket
- Bracket has two separate cover mounting options. Threaded post pushes in, for flat ceilings, or screws on for textured/uneven ceilings. (see photo below)

BENEFITS

- Attractive cover. Screws don't show on the ceiling
- Plastic eliminates the scratches you get with painted metal covers
- Covers poorly cut drywall




For Flat and Uneven Ceilings...



Installation Instructions



Back the screws out enough to slip the bracket on.



Use the opening in the bracket most suitable for your ceiling condition... 'A' for flat ceilings, push post into opening to seat cover; 'B' for uneven or textured ceilings, screw threaded post into opening until tight.

Spring-Mount Ceiling Cover Plate

New 9" diameter Ceiling Cover Plate is the neatest way to cover unused 'high hat' cans. Non-metallic. Will not rust.




FEATURES AND BENEFITS

- Paintable to blend with any ceiling
- 9" diameter covers most 'high hat' cans
- Reusable and flexible
- Will not rust or discolor
- Attractive way to hide an empty opening in the ceiling

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | BOX SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|----------|----------|---------|-------|-------|
| CP9000 | 69112 | 9" | 1 | 20 | 9.000 | .400 |

PATENTED.



Installation Instructions



Installation Method A

Slip plastic anchor brackets into the tabs in the 'can'.



Installation Method B

No tabs inside the can or too close to fixture. Attach the springs directly to the 'can'.



Attach the anchor brackets or extension springs to the inside of the 'can'. Tension on the springs pull the cover plate snug against the ceiling. Paint cover as desired to match ceiling.



CP9000 ... The attractive way to cover unused 'high hats'!

Scan For Video



Non-Metallic Bushings for Metal Studs




FITS
a standard
1" KNOCKOUT

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | STUD SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|-----------|----------|---------|-------|-------|-------|-------|
| SB13 | 40115 | 2 x 4 | 500 | 500 | 5.670 | 2.500 | .505 | 1.300 |
| SB130 | 40130 | 2 x 4 | 100 | 100 | 5.670 | 2.500 | .505 | 1.300 |
| SB13BL | 40151 | 2 x 4 | 25 | 250 | 5.670 | 2.500 | .505 | 1.300 |



These bushings fit existing irregular shaped holes in metal studs, alleviating the need to punch holes in metal studs, weakening the structural member. Use these bushings to comply with paragraph 300-4(b)(1) of the 2014 NEC code which states that: "In both exposed and concealed locations where nonmetallic-sheathed cables pass through either factory or field punched, cut, or drilled slots or holes in metal members, the cable shall be protected by bushings or grommets covering all metal edges and securely fastened in the opening prior to installation of the cable."

PATENTED.




Installation Instructions

To install these bushings in an irregular shaped hole, pass one end of the joined connector through the hole in the stud. Snap the bushing and the washer ends together. There's no need to separate the two halves. If a punched hole is required, the SB13 can be installed in a standard 1" trade size, round punched hole (1-3/8" diameter). Snap the bushing end into the hole.



Common hole configurations in metal studs.




Non-Metallic Bushings for Metal Studs



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| SB1 | 18001 | 1/2 | 1000 | 1000 | .940 | .470 | .700 |
| SB10 | 18010 | 1/2 | 100 | 100 | .940 | .470 | .700 |
| SB3 | 18050 | 1 | 1000 | 1000 | 1.750 | .400 | 1.150 |
| SB30 | 18053 | 1 | 100 | 100 | 1.750 | .400 | 1.150 |

Note: See page S-9 for larger sizes.




Snap-In Bushings

For knockouts. All-plastic, snap-in type.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| 4400 | 04400 | 1/2 | 100 | 1000 | 1.140 | .679 | .505 |
| 4401 | 04401 | 3/4 | 100 | 1000 | 1.420 | .900 | .505 |
| 4402 | 04402 | 1 | 50 | 500 | 1.770 | 1.157 | .505 |
| 4403 | 04403 | 1-1/4 | 25 | 250 | 2.281 | 1.509 | .505 |
| 4404 | 04404 | 1-1/2 | 25 | 250 | 2.598 | 1.748 | .505 |
| 4405 | 04405 | 2 | 20 | 200 | 2.919 | 2.223 | .563 |
| 4406 | 04409 | 2-1/2 | 20 | 200 | 3.421 | 2.725 | .563 |




Plastic Snap-In Blanks

All plastic. For knockouts. Black color.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| NM900 | 54000 | 1/2 | 100 | 1000 | 1.015 | .468 |
| NM901 | 54001 | 3/4 | 50 | 50 | 1.250 | .468 |
| NM902 | 54002 | 1 | 50 | 50 | 1.500 | .468 |
| NM903 | 54003 | 1-1/4 | 25 | 25 | 1.906 | .468 |
| NM904 | 54004 | 1-1/2 | 25 | 25 | 2.156 | .468 |
| NM905 | 54005 | 2 | 20 | 20 | 2.750 | .750 |




These items cost less than steel snap-in blanks, and provide a safer installation. A metal blank in a plastic box or enclosure is not grounded and could become a shock hazard.

Steel Snap-In Blanks

Plated steel. For knockouts.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 900 | 00900 | 1/2 | 100 | 1000 | 1.070 | .310 |
| 901 | 00901 | 3/4 | 50 | 50 | 1.235 | .310 |
| 902 | 00902 | 1 | 50 | 50 | 1.480 | .310 |
| 903 | 00903 | 1-1/4 | 25 | 25 | 1.800 | .310 |
| 904 | 00904 | 1-1/2 | 25 | 25 | 2.215 | .360 |
| 905 | 00905 | 2 | 20 | 20 | 2.675 | .360 |



Concrete Pipe Sleeves



Provides an economical method of sleeving through concrete pour allowing cable or conduit to easily run from one floor to the next.
Color - black.



FEATURES AND BENEFITS

- Stackable for extra deep pours
- Venting prevents sleeves from sticking together when wet
- Plastic

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | DESCRIPTION | FITS | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|-----------------|-------------|---------|-------|-------|-------|
| CPS15 | 72150 | For 1-1/2" hole | 1" pipe | 10 | 8.500 | 1.625 | 3.125 |
| CPS20 | 10960 | For 2" hole | 1-1/2" pipe | 10 | 8.500 | 2.125 | 3.625 |
| CPS30 | 72152 | For 3" hole | 2" pipe | 10 | 8.500 | 3.125 | 4.625 |
| CPS40 | 10962 | For 4" hole | 3" pipe | 10 | 8.500 | 4.125 | 5.625 |
| CPS50 | 72154 | For 5" hole | 4" pipe | 10 | 8.500 | 5.125 | 6.625 |
| CPS60 | 10964 | For 6" hole | 5" pipe | 10 | 8.500 | 6.125 | 7.625 |





Adjustable Throat Liners

To be installed in fittings after conduit, fitting and wire are in place. Allows installation to meet local electrical code. Non-metallic.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 4001 | 04001 | 1/2 | 25 | 100 | .670 | .900 |
| 4002 | 04002 | 3/4 | 25 | 100 | .710 | 1.220 |
| 4003 | 04003 | 1 | 25 | 100 | .880 | 1.450 |
| 4004 | 04004 | 1-1/4 | 10 | 40 | 1.015 | 1.735 |
| 4005 | 04005 | 1-1/2 | 10 | 40 | 1.015 | 2.050 |
| 4006 | 04006 | 2 | 10 | 40 | 1.250 | 2.312 |



Duct Seal Compound

Asbestos-free, non-drying, non-toxic, permanently soft.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG |
|----------------|--------------------------|------------|----------|---------|
| DSC1 | 43600 | 1 LB | 1 | 50 |
| DSC5 | 43605 | 5 LB | 1 | 10 |



FEATURES AND BENEFITS


- Adheres to most clean, dry surfaces
- Will not adversely affect plastic materials or corrode metals

Beam Clamps

Plated steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | STATIC LOAD RATING | TRADE SIZE | UNIT PKG | STD PKG | DIM A | THREADED ROD SIZE |
|----------------|--------------------------|--------------------|------------|----------|---------|-------|-------------------|
| BC25 | 23250 | 75 LBS | 1 | 25 | 100 | .608 | 1/4-20 |
| BC38 | 23380 | 200 LBS | 2 | 25 | 100 | .930 | 3/8-16 |




Beam Clamps

Malleable iron. Plated.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | STATIC LOAD RATING | TRADE SIZE | UNIT PKG | STD PKG | DIM A | THREADED ROD SIZE |
|----------------|--------------------------|--------------------|------------|----------|---------|-------|-------------------|
| MBC25 | 34810 | 125 LBS | 1 | 25 | 100 | .772 | 1/4-20 |
| MBC25A | 42321 | 125 LBS | 1 | 25 | 100 | .772 | 10-24 |
| MBC26 | 42326 | 300 LBS | 1-1/2 | 50 | 50 | .878 | 5/16-18 |
| MBC27 | 42327 | 300 LBS | 2 | 50 | 50 | .878 | 3/8-16 |
| MBC28 | 42328 | 600 LBS | 2-1/2 | 25 | 25 | 1.108 | 1/2-13 |




Safety Plate

Flat 16 gauge steel.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C | DIM D |
|----------------|--------------------------|---------------|----------|---------|-------|-------|-------|-------|
| SP100 | 17100 | 1-1/2 x 2-3/4 | 100 | 600 | 2.750 | 1.500 | .475 | .155 |



Jack Chain

Zinc-plated steel. 100 feet per steel reel. Maximum load limit 25 lbs.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | SIZE | UNIT CTN | STD CTN |
|----------------|--------------------------|------|----------|---------|
| JC12 | 13120 | 1/2 | 100 ft | 100 ft |

UL LISTED • RELIABLE • SECURE

MADE IN USA

INNOVATIVE PRODUCTS

LOWEST COST, NON-METALLIC CONNECTORS • BUSHINGS • HANGERS

PRESS-ON • INSULATING BUSHINGS

THE BEST CABLE PROTECTION

- Easy press-on installation
- Protects cable; holds tight as cables are pulled
- Less expensive alternative to costly fittings when used just for wire protection



LOW COST • LOW PROFILE CONNECTORS


3 SIZES HANDLE WIDEST CORD RANGE IN INDUSTRY



Unique grommet and gripper deliver superior pullout resistance... and liquid-tight, oil-tight seal when the nut is tightened



Scan for Info



Grommet BEFORE tightening Grommet tightened

LOW COST HANGER THE LOOP™

FOR COMMUNICATIONS CABLE

Holds a 2" to 5" diameter bundle of CAT 5 or fiber optic cable without sagging, bending or damage!

TL25 holds the same amount of cable as a J-hook at 1/2 the COST!

View video



LOWEST COST • NON-METALLIC CABLE CONNECTORS

FAST, EASY INSTALLATION

- Listed for 1 or 2 cables
- Fast, easy installation
- Snaps into k.o. with light finger pressure
- Smooth cable insertion
- Holds wires secure – exceeds UL pullout tests



NM94 1/2"
NM95 3/4"
NM96 1"



Arlington

DISTRIBUTED BY:



Arlington

WHERE INNOVATION GROWS.

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646

www.aifittings.com