




LARGE RADIUS HORIZONTAL BENDS




SMALL RADIUS HORIZONTAL BENDS




RIGHT RADIUS HORIZONTAL BENDS



T/CROSS AT LARGE RADIUS





REDUCING SIZE



VERTICAL BENDS

BASORFIL





Cable Trays Installation





HOW TO CUT

Always use asymmetrical-cut wire cutters.


Cut as close as you can to where horizontal and vertical rods cross each other, as shown.




LARGE RADIUS HORIZONTAL BENDS - RIGHT ANGLE






FAST BOLT NUT



WIDTH	N	ACCESSORIES	RADIUS inches mm.	USED LENGTH inches mm.	USED LENGTH inches mm.
2"	50mm.	2x (BF Bolt-Nut Set + Multiunion joint)	-	5x4"	5x100
4"	100mm.	3x (BF Bolt-Nut Set + Multiunion joint)	8'65 220	7x4"	7x100
6"	150mm.	4x (BF Bolt-Nut Set + Multiunion joint)	11'03 280	9x4"	9x100
8"	200mm.	[2x (2xBF Bolt-Nut Set + Multiunion joint) + 2x (Bolt-Staple Set)]	11'03 280	9x4"	9x100
12"	300mm.	[2x (2xBF Bolt-Nut Set + Multiunion joint) + 4x (Bolt-Staple Set)]	16'92 430	13x4"	13x100
16"	400mm.	[2x (2xBF Bolt-Nut Set + Multiunion joint) + 6x (Bolt-Staple Set)]	18'11 460	17x4"	17x100
20"	500mm.	9x (Bolt-Staple Set)	27'56 700	19x4"	19x100
24"	600mm.	11x (Bolt-Staple Set)	30'31 770	23x4"	23x100





LARGE RADIUS HORIZONTAL BENDS - RIGHT ANGLE




WIDTH	N	COUPLERS	RADIUS inches	mm.	USED LENGTH inches	mm.	
4"	100mm.	2	CU BFR MB	5'51	140	5x4"	5x100
6"	150mm.	3	CU BFR MB	8'65	220	7x4"	9x100
8"	200mm.	4	CU BFR MB	11'81	300	9x4"	9x100
12"	300mm.	6	CU BFR MB	17'72	450	13x4"	13x100
16"	400mm.	8	CU BFR MB	24	610	17x4"	17x100
20"	500mm.	9	CU BFR MB	29'92	760	21x4"	21x100
24"	600mm.	11	CU BFR MB	35'83	910	25x4"	25x100

SMALL RADIUS HORIZONTAL BENDS - RIGHT ANGLE






WIDTH	D	L	ACCESSORIES	RADIUS inches mm.	USED LENGTH inches mm.
2"	50mm.	-	1x BF Bolt-Staple Set	-	3x4" 3x100
4"	100mm.	1	1+1 1x BF Bolt-Staple Set	2 50	5x4" 5x100
6"	150mm.	1	2+2 1x (2 SSC+BF BOLT-NUT SET)	4'72 120	7x4" 7x100
8"	200mm.	2	2+2 1x (2 SSC+BF BOLT-NUT SET)	4'92 125	8x4" 8x100
12"	300mm.	2	3+3 1x (2 SSC+BF BOLT-NUT SET)	4'72 120	10x4" 10x100
16"	400mm.	2	4+4 1x (2 SSC+BF BOLT-NUT SET)	5'12 130	12x4" 12x100
20"	500mm.	2	5+5 1x (2 SSC+BF BOLT-NUT SET)	5'12 130	14x4" 14x100
24"	600mm.	2	6+6 1x (2 SSC+BF BOLT-NUT SET)	5'31 135	16x4" 16x100






D and L = nº of rows to cut

RIGHT RADIUS HORIZONTAL BENDS - RIGHT ANGLE






FAST BOLT NUT




L = nº of rows to cut

WIDTH	L	ACCESSORIES
4"	100mm.	1 2x BF Bolt-Staple Set
6"	150mm.	2 2x BF Bolt-Staple Set
8"	200mm.	2 2x BF Bolt-Staple Set
12"	300mm.	3 2x BF Bolt-Staple Set
16"	400mm.	4 2x BF Bolt-Staple Set
20"	500mm.	5 2x BF Bolt-Staple Set
24"	600mm.	6 2x BF Bolt-Staple Set


T/CROSS - RIGHT ANGLE



FAST BOLT NUT





WIDTH		L	ACCESSORIES
2"	50mm.	1	3x (BF Bolt-Staple Set + Multiunion joint)
4"	100mm.	1	3x (BF Bolt-Staple Set + Multiunion joint)
6"	150mm.	2	3x (BF Bolt-Staple Set + Multiunion joint)
8"	200mm.	2	3x (BF Bolt-Staple Set + Multiunion joint)
12"	300mm.	3	3x (BF Bolt-Staple Set + Multiunion joint)
16"	400mm.	4	3x (BF Bolt-Staple Set + Multiunion joint)
20"	500mm.	5	3x (BF Bolt-Staple Set + Multiunion joint)
24"	600mm.	6	3x (BF Bolt-Staple Set + Multiunion joint)





L = nº of rows to cut





T/CROSS AT LARGE RADIUS - RIGHT ANGLE





FAST BOLT NUT

**L and T = nº of rows to cut**



WIDTH	Piece 1		Piece 2		ACCESSORIES
	L	T	L	T	
4"	100mm.	2	1+1	1+1	3x (BF Bolt-Staple Set)
6"	150mm.	3	1+1	1+1	1x (BF Bolt-Staple Set) + 2x (2x Bolt-Staple set + Multiunion Joint)
8"	200mm.	3	1+1	1+1	3x (BF Bolt-Staple Set)
12"	300mm.	4	1+1	1+1	4x (BF Bolt-Staple Set)
16"	400mm.	5	1+1	1+1	1x (BF Bolt-Staple Set) + 2x (2x Bolt-Staple set + Multiunion Joint)
20"	500mm.	6	1+1	1+1	4x (BF Bolt-Staple Set)
24"	600mm.	7	1+1	1+1	4x (BF Bolt-Staple Set)

REDUCING SIZE - 4"

REDUCING SIZE - 8"

CHOOSE THE ONE YOU NEED


VERTICAL BENDS



CHANGING LEVEL



BASORFIL GIVES YOU MANY POSSIBILITIES

