



GREENCREATIVE



2019 LAMPS CATALOG



GREENCREATIVE
LAMPS



2019 LAMPS CATALOG



Your Partner for Innovative Lighting Solutions

GREEN CREATIVE, founded in 2010, is a solid state lighting development and manufacturing company based in Silicon Valley, CA. The company offers a comprehensive line of high-performance LED lighting solutions which has been widely adopted by some of the largest companies in the world.



Bringing you the latest in LED technology


Anchored by strong integrated R&D capabilities and patented technology, GREEN CREATIVE innovation, performance and reliability have been recognized year after year by the Illuminating Engineering Society Progress Report, the LEDs Magazine Sapphire Awards, Edison Report, NAILD and more.

A complete line with national & international distribution

GREEN CREATIVE's full product line of ENERGY STAR, DLC, NSF & JA8 certified indoor retrofit and new construction lighting solutions serves the Retail, Hospitality, Food & Beverage, Office, Education & Industrial sectors through multiple distribution centers and sales networks across the USA.



2019 LAMPS TABLE OF CONTENTS



2019 LAMPS FEATURED PRODUCTS



NEW!

P3-4

PAR HO SERIES

Very high lumen & candela output
Exceptional color rendering CRI 92
Direct line voltage 120-277V
Narrow Flood / Flood beam angles



NEW!

P5-6

MR16 75W SERIES

Suitable for use in totally enclosed fixtures
Exceptional color rendering CRI 92
Tight LED binning for consistent CCT
Spot / Narrow Flood / Flood beam angles




NEW!

P9

VALUE SELECT TUBE SERIES

T5 DIR - 4' HE/HO
T8 DIR - 4'
Deliver great value through quality performance and price




NEW!

P10-11

EXTERNAL TUBE SERIES

T8 - 2' / 3' / 4' / Ubent;
T5HE - 2' / 3' / 4'
T5HO - 4'
0-10V dimmable external driver




SPECIFICATIONS													
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
58104	8PAR20DIM/927SP15	2700K	535	92	67	5300	Yes	50W	15°	50,000	120V	Yes	✓
58105	8PAR20DIM/927NF25	2700K	535	92	67	2700	Yes	50W	25°	50,000	120V	Yes	✓
58106	8PAR20DIM/927FL40	2700K	535	92	67	1170	Yes	50W	40°	50,000	120V	Yes	✓
58107	8PAR20DIM/930SP15	3000K	550	92	69	5400	Yes	50W	15°	50,000	120V	Yes	✓
58108	8PAR20DIM/930NF25	3000K	550	92	69	2800	Yes	50W	25°	50,000	120V	Yes	✓
58109	8PAR20DIM/930FL40	3000K	550	92	69	1200	Yes	50W	40°	50,000	120V	Yes	✓
58112	8PAR20DIM/940FL40	4000K	570	92	71	1250	Yes	50W	40°	50,000	120V	Yes	✓
97901	8PAR20DIM/930FL40/B •	3000K	550	92	69	1200	Yes	50W	40°	50,000	120V	Yes	✓
58113	13PAR30DIM/927SP15	2700K	870	92	67	7800	Yes	75W	15°	50,000	120V	Yes	✓
58114	13PAR30DIM/927NF25	2700K	1000	92	77	4500	Yes	90W	25°	50,000	120V	Yes	✓
58115	13PAR30DIM/927FL40	2700K	1000	92	77	2200	Yes	90W	40°	50,000	120V	Yes	✓
58116	13PAR30DIM/930SP15	3000K	880	92	68	8000	Yes	75W	15°	50,000	120V	Yes	✓
58117	13PAR30DIM/930NF25	3000K	1050	92	81	4700	Yes	90W	25°	50,000	120V	Yes	✓
58118	13PAR30DIM/930FL40	3000K	1050	92	81	2300	Yes	90W	40°	50,000	120V	Yes	✓
58121	13PAR30DIM/940FL40	4000K	1100	92	85	2500	Yes	90W	40°	50,000	120V	Yes	✓
97902	13PAR30DIM/930FL40/B •	3000K	1050	92	81	2300	Yes	90W	40°	50,000	120V	Yes	✓
58127	13PAR30/930FL40/277V	3000K	1050	92	81	2300	No	90W	40°	50,000	120-277V	Yes	✓
58130	13PAR30/940FL40/277V	4000K	1100	92	85	2500	No	90W	40°	50,000	120-277V	Yes	✓

• Black finish


SPECIFICATIONS													
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
58140	13PAR30SNDIM/927SP15	2700K	870	92	67	7800	Yes	75W	15°	50,000	120V	Yes	✓
58141	13PAR30SNDIM/927NF25	2700K	1000	92	77	4500	Yes	90W	25°	50,000	120V	Yes	✓
58142	13PAR30SNDIM/927FL40	2700K	1000	92	77	2200	Yes	90W	40°	50,000	120V	Yes	✓
58143	13PAR30SNDIM/930SP15	3000K	880	92	68	8000	Yes	75W	15°	50,000	120V	Yes	✓
58144	13PAR30SNDIM/930NF25	3000K	1050	92	81	4700	Yes	90W	25°	50,000	120V	Yes	✓
58145	13PAR30SNDIM/930FL40	3000K	1050	92	81	2300	Yes	90W	40°	50,000	120V	Yes	✓
58148	13PAR30SNDIM/940FL40	4000K	1100	92	85	2500	Yes	90W	40°	50,000	120V	Yes	✓
97903	13PAR30SNDIM/930FL40/B •	3000K	1050	92	81	2300	Yes	90W	40°	50,000	120V	Yes	✓
58149	17PAR38DIM/927SP15	2700K	1150	92	68	12,200	Yes	120W	15°	50,000	120V	Yes	✓
58150	17PAR38DIM/927NF25	2700K	1400	92	82	7300	Yes	120W	25°	50,000	120V	Yes	✓
58151	17PAR38DIM/927FL40	2700K	1400	92	82	3100	Yes	120W	40°	50,000	120V	Yes	✓
58152	17PAR38DIM/930SP15	3000K	1200	92	71	12,500	Yes	120W	15°	50,000	120V	Yes	✓
58153	17PAR38DIM/930NF25	3000K	1430	92	84	7500	Yes	120W	25°	50,000	120V	Yes	✓
58154	17PAR38DIM/930FL40	3000K	1430	92	84	3200	Yes	120W	40°	50,000	120V	Yes	✓
58157	17PAR38DIM/940FL40	4000K	1450	92	85	3300	Yes	120W	40°	50,000	120V	Yes	✓
97904	17PAR38DIM/930NF25/B •	3000K	1430	92	84	7500	Yes	120W	25°	50,000	120V	Yes	✓
97905	17PAR38DIM/930FL40/B •	3000K	1430	92	84	3200	Yes	120W	40°	50,000	120V	Yes	✓
58172	17PAR38DIM/930FL40/GU24	3000K	1430	92	84	3200	Yes	120W	40°	50,000	120V	Yes	✓
58163	17PAR38/930FL40/277V	3000K	1430	92	84	3200	No	120W	40°	50,000	120-277V	Yes	✓
58166	17PAR38/940FL40/277V	4000K	1450	92	85	3300	No	120W	40°	50,000	120-277V	Yes	✓


• Black finish




- Very high candela output PAR HO to replace 75W/250W halogen
- Exceptional color rendering CRI 92
- Richer reds and natural skin tones (R9 92, R13 91)
- Direct line voltage 120-277V - Not compatible with ballasts

SPECIFICATIONS													
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
98206	19.5PAR30HO/930NF25/277V	3000K	1700	92	87	8160	No	75W	25°	50,000	120-277V	No	✓
98207	19.5PAR30HO/930FL40/277V	3000K	1700	92	87	3400	No	75W	40°	50,000	120-277V	No	✓
98208	19.5PAR30HO/940NF25/277V	4000K	1700	92	87	8160	No	75W	25°	50,000	120-277V	No	✓
98209	19.5PAR30HO/940FL40/277V	4000K	1700	92	87	3400	No	75W	40°	50,000	120-277V	No	✓
98223	25PAR38HO/927NF25/277V	2700K	2400	92	96	10,000	No	250W	25°	50,000	120-277V	No	✓
98210	25PAR38HO/930NF25/277V	3000K	2500	92	100	10,200	No	250W	25°	50,000	120-277V	No	✓
98211	25PAR38HO/930FL40/277V	3000K	2500	92	100	4800	No	250W	40°	50,000	120-277V	No	✓
98212	25PAR38HO/940NF25/277V	4000K	2500	92	100	10,000	No	250W	25°	40,000	120-277V	No	✓
98213	25PAR38HO/940FL40/277V	4000K	2500	92	100	4800	No	250W	40°	40,000	120-277V	No	✓







SPECIFICATIONS													
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
40713	3MR11/827NF30	2700K	200	82	67	600	No	20W	30°	25,000	12V	Yes	N.A.
40715	3MR11/840NF30	4000K	220	82	73	620	No	20W	30°	25,000	12V	Yes	N.A.
58285	6MR16DIM/827FL35/35W/R	2700K	425	82	71	910	Yes	35W	35°	25,000	120V	Yes	✓
58286	6MR16DIM/830FL35/35W/R	3000K	450	82	75	910	Yes	35W	35°	25,000	120V	Yes	✓
57984	6MR16DIM/827FL35/R	2700K	480	82	80	1350	Yes	50W	35°	25,000	12V	Yes	✓
57985	6MR16DIM/830FL35/R	3000K	500	82	83	1400	Yes	50W	35°	25,000	12V	Yes	✓
57986	6MR16DIM/840FL35/R	4000K	520	82	86	1450	Yes	50W	35°	25,000	12V	Yes	✓
57987	6GU10DIM/827FL35/R	2700K	480	82	80	1000	Yes	50W	35°	25,000	120V	Yes	✓
57988	6GU10DIM/830FL35/R	3000K	500	82	83	1050	Yes	50W	35°	25,000	120V	Yes	✓




- Most efficient high CRI MR16 75W Halogen replacement
- Exceptional color rendering CRI 92
- Richer reds and natural skin tones (R9 53, R13 93)
- Suitable for use in totally enclosed fixtures



SPECIFICATIONS														
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES / JA8 / T20	
57990	6PAR16DIM/827FL35/R	2700K	480	82	80	1000	Yes	60W	35°	25,000	120V	Yes	✓ / N.A. / N.A.	
57991	6PAR16DIM/830FL35/R	3000K	500	82	83	1050	Yes	60W	35°	25,000	120V	Yes	✓ / N.A. / N.A.	
98481	7MR16DIM/927SP15	2700K	580	92	83	5850	Yes	75W	15°	25,000	12V	Yes	✓ / ✓ / Feb.	
98482	7.5MR16DIM/927NF25	2700K	580	92	77	2800	Yes	75W	25°	25,000	12V	Yes	✓ / ✓ / Feb.	
98483	7.5MR16DIM/927FL35	2700K	580	92	77	1600	Yes	75W	35°	25,000	12V	Yes	✓ / ✓ / Feb.	
98484	7MR16DIM/930SP15	3000K	580	92	83	5850	Yes	75W	15°	25,000	12V	Yes	✓ / ✓ / Feb.	
98485	7.5MR16DIM/930NF25	3000K	580	92	77	2800	Yes	75W	25°	25,000	12V	Yes	✓ / ✓ / Feb.	
98486	7.5MR16DIM/930FL35	3000K	580	92	77	2800	Yes	75W	25°	25,000	12V	Yes	✓ / ✓ / Feb.	

T8 DIR LINE



- Easy to install – Plug & play direct
- Instant Start & Programmed Start ballast compatible
- 0-10V dimming ballast compatible
- Meets NSF requirements (use of a shatter guard required)

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
97841	8T8/2F/830/DIR/R	3000K	1300	82	163	Yes	17W	160°	50,000	120-277V	Yes	✓
97842	8T8/2F/835/DIR/R	3500K	1300	82	163	Yes	17W	160°	50,000	120-277V	Yes	✓
97843	8T8/2F/840/DIR/R	4000K	1300	82	163	Yes	17W	160°	50,000	120-277V	Yes	✓
98352	8T8/3F/830/DIR/R	3000K	1200	82	150	Yes	25W	160°	50,000	120-277V	Yes	✓
98353	8T8/3F/835/DIR/R	3500K	1200	82	150	Yes	25W	160°	50,000	120-277V	Yes	✓
98354	8T8/3F/840/DIR/R	4000K	1250	82	156	Yes	25W	160°	50,000	120-277V	Yes	✓
28397	10.5T8/4F/830/DIR/RC	3000K	1650	82	157	Yes	32W	160°	50,000	120-277V	Yes	✓
28398	10.5T8/4F/835/DIR/RC	3500K	1650	82	157	Yes	32W	160°	50,000	120-277V	Yes	✓
28399	10.5T8/4F/840/DIR/RC	4000K	1700	82	162	Yes	32W	160°	50,000	120-277V	Yes	✓
28400	10.5T8/4F/850/DIR/RC	5000K	1700	82	162	Yes	32W	160°	50,000	120-277V	Yes	✓
28403	13T8/4F/840/DIR/R	4000K	2050	82	158	Yes	32W	160°	50,000	120-277V	Yes	✓
28404	13T8/4F/850/DIR/R	5000K	2050	82	158	Yes	32W	160°	50,000	120-277V	Yes	✓
97958	16T8U6/830/DIR	3000K	2200	82	138	Yes	32W	140°	50,000	120-277V	Yes	✓
97959	16T8U6/840/DIR	4000K	2200	82	138	Yes	32W	140°	50,000	120-277V	Yes	✓
97960	16T8U6/850/DIR	5000K	2250	82	141	Yes	32W	140°	50,000	120-277V	Yes	✓



DIRect

Compatible with Electronic Ballasts - Dimmable

INSTANT START BALLAST

PROGRAMMED START BALLAST


DIMMABLE

Extra Wide Beam Design - End-to-End Lighting

Lamp Front View



Lamp Back View




T5 DIR LINE



- Easy to install – Plug & play direct
- Instant Start & Programmed Start ballast compatible
- Plastic construction meets NSF requirements
- Dimmable

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
57958	8T5HE/2F/830/DIR	3000K	950	82	119	Yes	14W	120°	50,000	120-277V	Yes	N.A.
57959	8T5HE/2F/835/DIR	3500K	950	82	119	Yes	14W	120°	50,000	120-277V	Yes	N.A.
57960	8T5HE/2F/840/DIR	4000K	1020	82	128	Yes	14W	120°	50,000	120-277V	Yes	N.A.
57954	12T5HE/3F/830/DIR	3000K	1420	82	118	Yes	21W	120°	50,000	120-277V	Yes	N.A.
57955	12T5HE/3F/835/DIR	3500K	1420	82	118	Yes	21W	120°	50,000	120-277V	Yes	N.A.
57956	12T5HE/3F/840/DIR	4000K	1500	82	125	Yes	21W	120°	50,000	120-277V	Yes	N.A.
97929	15T5HE/4F/830/DIR/R	3000K	2200	82	147	Yes	28W	120°	50,000	120-277V	Yes	✓
97930	15T5HE/4F/835/DIR/R	3500K	2200	82	147	Yes	28W	120°	50,000	120-277V	Yes	✓
97931	15T5HE/4F/840/DIR/R	4000K	2250	82	150	Yes	28W	120°	50,000	120-277V	Yes	✓
97932	15T5HE/4F/850/DIR/R	5000K	2250	82	150	Yes	28W	120°	50,000	120-277V	Yes	✓
98165	10.5T5HO/2F/830/DIR	3000K	1500	82	143	Yes	24W	120°	50,000	120-277V	Yes	N.A.
98166	10.5T5HO/2F/835/DIR	3500K	1500	82	143	Yes	24W	120°	50,000	120-277V	Yes	N.A.
98167	10.5T5HO/2F/840/DIR	4000K	1600	82	152	Yes	24W	120°	50,000	120-277V	Yes	N.A.
98168	14.5T5HO/3F/830/DIR	3000K	2050	82	142	Yes	39W	120°	50,000	120-277V	Yes	N.A.
98169	14.5T5HO/3F/835/DIR	3500K	2050	82	142	Yes	39W	120°	50,000	120-277V	Yes	N.A.
98170	14.5T5HO/3F/840/DIR	4000K	2200	82	152	Yes	39W	120°	50,000	120-277V	Yes	N.A.
97924	24T5HO/4F/830/DIR/R	3000K	3450	82	144	Yes	54W	120°	50,000	120-277V	Yes	✓
97925	24T5HO/4F/835/DIR/R	3500K	3450	82	144	Yes	54W	120°	50,000	120-277V	Yes	✓
97926	24T5HO/4F/840/DIR/R	4000K	3500	82	146	Yes	54W	120°	50,000	120-277V	Yes	✓
97927	24T5HO/4F/850/DIR/R	5000K	3500	82	146	Yes	54W	120°	50,000	120-277V	Yes	✓



DIRect


Compatible with Electronic Ballasts - Dimmable

INSTANT START BALLAST

PROGRAMMED START BALLAST


DIMMABLE

T8 / T5 DIR VALUE SELECT LINE



DIRect

- Easy to install – Plug & play direct
 - Instant Start ballast compatible
- Easy to install – Plug & play direct
 - Instant Start & Programmed Start ballast compatible
 - Glass construction
 - Dimmable

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
T8												
98551	10.5T8/4F/830/IS/DIR	3000K	1600	82	152	No	32W	160°	50,000	120-277V	Yes	✓
98552	10.5T8/4F/835/IS/DIR	3500K	1600	82	152	No	32W	160°	50,000	120-277V	Yes	✓
98553	10.5T8/4F/840/IS/DIR	4000K	1650	82	157	No	32W	160°	50,000	120-277V	Yes	✓
98554	10.5T8/4F/850/IS/DIR	5000K	1650	82	157	No	32W	160°	50,000	120-277V	Yes	✓
98557	13T8/4F/840/IS/DIR	4000K	2000	82	154	No	32W	160°	50,000	120-277V	Yes	✓
98558	13T8/4F/850/IS/DIR	5000K	2000	82	154	No	32W	160°	50,000	120-277V	Yes	✓
T5												
98490	15T5HE/4F/830/GL/DIR	3000K	2200	82	142	Yes	28W	120°	50,000	120-277V	Yes	✓
98491	15T5HE/4F/835/GL/DIR	3500K	2200	82	142	Yes	28W	120°	50,000	120-277V	Yes	✓
98492	15T5HE/4F/840/GL/DIR	4000K	2250	82	152	Yes	28W	120°	50,000	120-277V	Yes	✓
98494	24T5HO/4F/830/GL/DIR	3000K	3450	82	144	Yes	54W	120°	50,000	120-277V	Yes	✓
98495	24T5HO/4F/835/GL/DIR	3500K	3450	82	144	Yes	54W	120°	50,000	120-277V	Yes	✓
98496	24T5HO/4F/840/GL/DIR	4000K	3500	82	146	Yes	54W	120°	50,000	120-277V	Yes	✓
98497	24T5HO/4F/850/GL/DIR	5000K	3500	82	146	Yes	54W	120°	50,000	120-277V	Yes	✓

T8 BYP LINE



BYPass



- Built-in universal voltage driver – Bypass installation
- Compatible with non-shunted lamp holders only
- Extra high efficacy series up to 167LPW available
- Meets NSF requirements (use of a shatter guard required)

BYPass Installation - Single Ended

~~BALLAST~~ 120-277V UNIVERSAL

UL1598C classification ensures fixture maintains original UL compliance

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
28413	8T8/2F/830/BYP/R	3000K	1000	82	125	No	17W	160°	50,000	120-277V	Yes	✓
28414	8T8/2F/835/BYP/R	3500K	1050	82	131	No	17W	160°	50,000	120-277V	Yes	✓
28415	8T8/2F/840/BYP/R	4000K	1050	82	131	No	17W	160°	50,000	120-277V	Yes	✓
97893	12T8/3F/830/BYP/R	3000K	1500	82	125	No	25W	160°	50,000	120-277V	Yes	✓
97894	12T8/3F/835/BYP/R	3500K	1500	82	125	No	25W	160°	50,000	120-277V	Yes	✓
97895	12T8/3F/840/BYP/R	4000K	1550	82	129	No	25W	160°	50,000	120-277V	Yes	✓
28405	13T8/4F/830/BYP/R	3000K	1650	82	123	No	32W	160°	50,000	120-277V	Yes	✓
28406	13T8/4F/835/BYP/R	3500K	1650	82	127	No	32W	160°	50,000	120-277V	Yes	✓
28407	13T8/4F/840/BYP/R	4000K	1700	82	131	No	32W	160°	50,000	120-277V	Yes	✓
28408	13T8/4F/850/BYP/R	5000K	1700	82	131	No	32W	160°	50,000	120-277V	Yes	✓
28411	16T8/4F/840/BYP/R	4000K	2050	82	128	No	32W	160°	50,000	120-277V	Yes	✓
28412	16T8/4F/850/BYP/R	5000K	2050	82	128	No	32W	160°	50,000	120-277V	Yes	✓
98379	10.5T8/4F/830/BYP	3000K	1650	82	157	No	32W	160°	50,000	120-277V	Yes	✓
98380	10.5T8/4F/835/BYP	3500K	1650	82	157	No	32W	160°	50,000	120-277V	Yes	✓
98381	10.5T8/4F/840/BYP	4000K	1750	82	167	No	32W	160°	50,000	120-277V	Yes	✓
98382	10.5T8/4F/850/BYP	5000K	1750	82	167	No	32W	160°	50,000	120-277V	Yes	✓
98473	14.5T8/4F/840/BYP	4000K	2200	82	152	No	32W	160°	50,000	120-277V	Yes	✓
98474	14.5T8/4F/850/BYP	5000K	2200	82	152	No	32W	160°	50,000	120-277V	Yes	✓
98162	17T8U6/830/BYP	3000K	2100	82	124	No	32W	140°	50,000	120-277V	Yes	✓
98163	17T8U6/840/BYP	4000K	2300	82	135	No	32W	140°	50,000	120-277V	Yes	✓
98164	17T8U6/850/BYP	5000K	2300	82	135	No	32W	140°	50,000	120-277V	Yes	✓
57840	17.5T8/4F/GOLD/BYP	N.A.	1100	82	63	No	32W	160°	50,000	120-277V	Yes	N.A.

T8 BYP LINE



FLICKER FREE



BYPass

BYPass Installation - Single Ended

~~BALLAST~~

120-277V
UNIVERSAL

UL1598C classification ensures fixture maintains original UL compliance



- Built-in universal voltage driver – Bypass installation
- Flicker Free light output
- Suitable for use in totally enclosed fixtures
- Meets NSF requirements (use of a shatter guard required)

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98191	8T8/2F/830/BYP/FF	3000K	1000	82	125	No	17W	160°	50,000	120-277V	Yes	✓
98192	8T8/2F/835/BYP/FF	3500K	1050	82	131	No	17W	160°	50,000	120-277V	Yes	✓
98193	8T8/2F/840/BYP/FF	4000K	1050	82	131	No	17W	160°	50,000	120-277V	Yes	✓
98194	12T8/3F/830/BYP/FF	3000K	1500	82	125	No	25W	160°	50,000	120-277V	Yes	✓
98195	12T8/3F/835/BYP/FF	3500K	1500	82	125	No	25W	160°	50,000	120-277V	Yes	✓
98196	12T8/3F/840/BYP/FF	4000K	1550	82	129	No	25W	160°	50,000	120-277V	Yes	✓
98197	13T8/4F/830/BYP/FF	3000K	1600	82	123	No	32W	160°	50,000	120-277V	Yes	✓
98198	13T8/4F/835/BYP/FF	3500K	1650	82	127	No	32W	160°	50,000	120-277V	Yes	✓
98199	13T8/4F/840/BYP/FF	4000K	1700	82	131	No	32W	160°	50,000	120-277V	Yes	✓
98200	13T8/4F/850/BYP/FF	5000K	1700	82	131	No	32W	160°	50,000	120-277V	Yes	✓
98201	16T8/4F/840/BYP/FF	4000K	2050	82	128	No	32W	160°	50,000	120-277V	Yes	✓
98202	16T8/4F/850/BYP/FF	5000K	2050	82	128	No	32W	160°	50,000	120-277V	Yes	✓

T5 BYP LINE



BYPass



BYPass Installation - Single Ended

~~BALLAST~~

120-277V
UNIVERSAL

UL1598C classification ensures fixture maintains original UL compliance

Balanced Light Output

GREEN CREATIVE
T5 BYPass




Other brand
T5 BYPass

- Built-in universal voltage driver – Bypass installation
- Wide beam design 270° light emitting area
- Suitable for use in totally enclosed fixtures
- Plastic construction meets NSF requirements

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98287	9.5T5HE/2F/830/BYP	3000K	1100	82	116	No	14W	120°	50,000	120-277V	Yes	N.A.
98288	9.5T5HE/2F/835/BYP	3500K	1150	82	121	No	14W	120°	50,000	120-277V	Yes	N.A.
98289	9.5T5HE/2F/840/BYP	4000K	1200	82	126	No	14W	120°	50,000	120-277V	Yes	N.A.
98290	12T5HE/3F/830/BYP	3000K	1350	82	113	No	21W	120°	50,000	120-277V	Yes	N.A.
98291	12T5HE/3F/835/BYP	3500K	1400	82	117	No	21W	120°	50,000	120-277V	Yes	N.A.
98292	12T5HE/3F/840/BYP	4000K	1500	82	125	No	21W	120°	50,000	120-277V	Yes	N.A.
98293	14.5T5HE/4F/830/BYP	3000K	1750	82	121	No	28W	120°	50,000	120-277V	Yes	✓
98294	14.5T5HE/4F/835/BYP	3500K	1800	82	124	No	28W	120°	50,000	120-277V	Yes	✓
98295	14.5T5HE/4F/840/BYP	4000K	2000	82	138	No	28W	120°	50,000	120-277V	Yes	✓
98296	11.5T5HO/2F/830/BYP	3000K	1350	82	117	No	24W	120°	50,000	120-277V	Yes	N.A.
98297	11.5T5HO/2F/835/BYP	3500K	1400	82	122	No	24W	120°	50,000	120-277V	Yes	N.A.
98298	11.5T5HO/2F/840/BYP	4000K	1500	82	130	No	24W	120°	50,000	120-277V	Yes	N.A.
98299	14.5T5HO/3F/830/BYP	3000K	1800	82	124	No	39W	120°	50,000	120-277V	Yes	N.A.
98300	14.5T5HO/3F/835/BYP	3500K	1850	82	128	No	39W	120°	50,000	120-277V	Yes	N.A.
98301	14.5T5HO/3F/840/BYP	4000K	1900	82	131	No	39W	120°	50,000	120-277V	Yes	N.A.
98302	25T5HO/4F/830/BYP	3000K	3200	82	128	No	54W	120°	50,000	120-277V	Yes	✓
98303	25T5HO/4F/835/BYP	3500K	3200	82	128	No	54W	120°	50,000	120-277V	Yes	✓
98304	25T5HO/4F/840/BYP	4000K	3200	82	128	No	54W	120°	50,000	120-277V	Yes	✓
98305	25T5HO/4F/850/BYP	5000K	3200	82	128	No	54W	120°	50,000	120-277V	Yes	✓



BYPass




- Double-ended bypass installation – Wired at both ends
- Utilizes existing lampholders – Non-shunted or shunted
- Extra high efficacy series up to 148LPW available
- Meets NSF requirements (use of a shatter guard required)

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
97934	8.5T8/2F/830/DEB/RC	3000K	1050	82	124	No	17W	160°	50,000	120-277V	Yes	✓
97935	8.5T8/2F/835/DEB/RC	3500K	1050	82	124	No	17W	160°	50,000	120-277V	Yes	✓
97936	8.5T8/2F/840/DEB/RC	4000K	1100	82	129	No	17W	160°	50,000	120-277V	Yes	✓
98340	12T8/3F/830/DEB/R	3000K	1400	82	117	No	25W	160°	50,000	120-277V	Yes	✓
98341	12T8/3F/835/DEB/R	3500K	1400	82	117	No	25W	160°	50,000	120-277V	Yes	✓
98342	12T8/3F/840/DEB/R	4000K	1450	82	121	No	25W	160°	50,000	120-277V	Yes	✓
98435	14T8/4F/830/DEB	3000K	1700	82	121	No	25W	160°	50,000	120-277V	Yes	✓
98436	14T8/4F/835/DEB	3500K	1700	82	124	No	32W	160°	50,000	120-277V	Yes	✓
98437	14T8/4F/840/DEB	4000K	1800	82	129	No	32W	160°	50,000	120-277V	Yes	✓
98438	14T8/4F/850/DEB	5000K	1800	82	129	No	32W	160°	50,000	120-277V	Yes	✓
98433	17T8/4F/840/DEB	4000K	2200	82	117	No	25W	160°	50,000	120-277V	Yes	✓
98434	17T8/4F/850/DEB	5000K	2200	82	117	No	25W	160°	50,000	120-277V	Yes	✓
58272	11.5T8/4F/830/DEB/RC	3000K	1650	82	143	No	32W	160°	50,000	120-277V	Yes	✓
58273	11.5T8/4F/835/DEB/RC	3500K	1650	82	143	No	32W	160°	50,000	120-277V	Yes	✓
58274	11.5T8/4F/840/DEB/RC	4000K	1700	82	148	No	32W	160°	50,000	120-277V	Yes	✓
58275	11.5T8/4F/850/DEB/RC	5000K	1700	82	148	No	32W	160°	50,000	120-277V	Yes	✓
58270	14.5T8/4F/840/DEB/RC	4000K	2100	82	145	No	32W	160°	50,000	120-277V	Yes	✓
58271	14.5T8/4F/850/DEB/RC	5000K	2100	82	145	No	32W	160°	50,000	120-277V	Yes	✓




EXTERNAL Driver




- Compatible with external drivers only
- 0-10V dimming
- Utilizes existing lamp holders – shunted or non-shunted
- Meets NSF requirements (use of a shatter guard required)

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98325	9.5T8/2F/830/EXT	3000K	1350	82	142	Yes	17W	160°	50,000	120-277V	Yes	✓
98326	9.5T8/2F/835/EXT	3500K	1400	82	147	Yes	17W	160°	50,000	120-277V	Yes	✓
98327	9.5T8/2F/840/EXT	4000K	1500	82	158	Yes	17W	160°	50,000	120-277V	Yes	✓
98328	10.5T8/3F/830/EXT	3000K	1450	82	138	Yes	25W	160°	50,000	120-277V	Yes	✓
98329	10.5T8/3F/835/EXT	3500K	1500	82	143	Yes	25W	160°	50,000	120-277V	Yes	✓
98330	10.5T8/3F/840/EXT	4000K	1600	82	152	Yes	25W	160°	50,000	120-277V	Yes	✓
98331	11.5T8/4F/830/EXT	3000K	1600	82	139	Yes	32W	160°	50,000	120-277V	Yes	✓
98332	11.5T8/4F/835/EXT	3500K	1650	82	143	Yes	32W	160°	50,000	120-277V	Yes	✓
98333	11.5T8/4F/840/EXT	4000K	1700	82	148	Yes	32W	160°	50,000	120-277V	Yes	✓
98334	11.5T8/4F/850/EXT	5000K	1700	82	148	Yes	32W	160°	50,000	120-277V	Yes	✓
98335	14T8/4F/840/EXT	4000K	2050	82	146	Yes	32W	160°	50,000	120-277V	Yes	✓
98336	14T8/4F/850/EXT	5000K	2050	82	146	Yes	32W	160°	50,000	120-277V	Yes	✓
98337	14.5T8U6/830/EXT	3000K	2000	82	138	Yes	32W	140°	50,000	120-277V	Yes	✓
98338	14.5T8U6/840/EXT	4000K	2200	82	152	Yes	32W	140°	50,000	120-277V	Yes	✓
98339	14.5T8U6/850/EXT	5000K	2200	82	152	Yes	32W	140°	50,000	120-277V	Yes	✓
98259	15T8T5HEDRIVER/2CH/R		120-277V with 0-10V Dimming External LED Driver for Use with 1-2 T8/T5 HE Lamps									
98260	15T8T5HEDRIVER/4CH/R		120-277V with 0-10V Dimming External LED Driver for Use with 3-4 T8/T5 HE Lamps									




EXternal Driver

- Compatible with external drivers only
- 0-10V dimming
- Utilizes existing lamp holders – shunted or non-shunted
- Plastic construction meets NSF requirements



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98306	9.5T5HE/2F/830/EXT	3000K	1350	82	142	Yes	14W	120°	50,000	120-277V	Yes	N.A.
98307	9.5T5HE/2F/835/EXT	3500K	1400	82	147	Yes	14W	120°	50,000	120-277V	Yes	N.A.
98308	9.5T5HE/2F/840/EXT	4000K	1500	82	158	Yes	14W	120°	50,000	120-277V	Yes	N.A.
98309	11T5HE/3F/830/EXT	3000K	1500	82	136	Yes	21W	120°	50,000	120-277V	Yes	N.A.
98310	11T5HE/3F/835/EXT	3500K	1550	82	141	Yes	21W	120°	50,000	120-277V	Yes	N.A.
98311	11T5HE/3F/840/EXT	4000K	1600	82	150	Yes	21W	120°	50,000	120-277V	Yes	N.A.
98312	13.5T5HE/4F/830/EXT	3000K	1800	82	133	Yes	28W	120°	50,000	120-277V	Yes	✓
98313	13.5T5HE/4F/835/EXT	3500K	1850	82	137	Yes	28W	120°	50,000	120-277V	Yes	✓
98314	13.5T5HE/4F/840/EXT	4000K	2000	82	148	Yes	28W	120°	50,000	120-277V	Yes	✓
98321	22T5HO/4F/830/EXT	3000K	3200	82	145	Yes	54W	120°	50,000	120-277V	Yes	✓
98322	22T5HO/4F/835/EXT	3500K	3200	82	145	Yes	54W	120°	50,000	120-277V	Yes	✓
98323	22T5HO/4F/840/EXT	4000K	3400	82	155	Yes	54W	120°	50,000	120-277V	Yes	✓
98324	22T5HO/4F/850/EXT	5000K	3400	82	155	Yes	54W	120°	50,000	120-277V	Yes	✓
98259	15T8T5HEDRIVER/2CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 1-2 T8/T5 HE Lamps										
98260	15T8T5HEDRIVER/4CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 3-4 T8/T5 HE Lamps										
98261	24T5HODRIVER/2CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 1-2 T5 HO Lamps										
98262	24T5HODRIVER/4CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 3-4 T5 HO Lamps										



- Easy to install – Plug & play direct
- Instant Start & Programmed Start ballast compatible
- 0-10V dimming ballast compatible
- Plastic film prevents glass from shattering

Compatible with Electronic Ballasts - Dimmable



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98477	13PLL/830/GL/DIR	3000K	2050	82	158	Yes	40W	160°	50,000	120-277V	Yes	✓
98478	13PLL/835/GL/DIR	3500K	2100	82	162	Yes	40W	160°	50,000	120-277V	Yes	✓
98479	13PLL/840/GL/DIR	4000K	2100	82	162	Yes	40W	160°	50,000	120-277V	Yes	✓
98488	14.5PLL/835/GL/DIR	3500K	1950	82	134	Yes	36W	160°	50,000	120-277V	Yes	N.A.
98489	14.5PLL/840/GL/DIR	4000K	2000	82	138	Yes	36W	160°	50,000	120-277V	Yes	N.A.




SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
57895	5.5PLH/827/DIR/RC	2700K	520	82	95	Yes	13-18W	110°	50,000	120-277V	No	N.A.
57896	5.5PLH/830/DIR/RC	3000K	550	82	100	Yes	13-18W	110°	50,000	120-277V	No	N.A.
57897	5.5PLH/835/DIR/RC	3500K	550	82	100	Yes	13-18W	110°	50,000	120-277V	No	N.A.
57898	5.5PLH/840/DIR/RC	4000K	560	82	102	Yes	13-18W	110°	50,000	120-277V	No	N.A.
28366	8.5PLH/827/DIR/R	2700K	870	82	102	Yes	26W	110°	50,000	120-277V	No	✓
28367	8.5PLH/830/DIR/R	3000K	950	82	112	Yes	26W	110°	50,000	120-277V	No	✓
28368	8.5PLH/835/DIR/R	3500K	950	82	112	Yes	26W	110°	50,000	120-277V	No	✓
28369	8.5PLH/840/DIR/R	4000K	1020	82	120	Yes	26W	110°	50,000	120-277V	No	✓
57903	10.5PLH/930/DIR	3000K	890	92	85	Yes	26W	110°	50,000	120-277V	No	N.A.
98244	14.5PLH/830/DIR	3000K	1700	82	117	Yes	42W	110°	50,000	120-277V	No	N.A.
98245	14.5PLH/835/DIR	3500K	1750	82	121	Yes	42W	110°	50,000	120-277V	No	N.A.
98246	14.5PLH/840/DIR	4000K	1800	82	124	Yes	42W	110°	50,000	120-277V	No	N.A.

PL H & V high output versions replace 42W CFL lamps




High Performance - Ballast Smart Control		
Ballast Type	Lumens	Bare Lamp
13W	600	4.5W
18W	700	5.5W
26W	1020	8.5W
PL H 8.5W DIR		

- Plug & play direct – Electronic ballast compatible
- Compatible with G24q & GX24q installations
- Patented design
- 0-10V dimming ballast compatible



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
28370	6PLV/827/DIR/R	2700K	600	82	100	Yes	13-18W	120°	50,000	120-277V	No	N.A.
28371	6PLV/830/DIR/R	3000K	620	82	103	Yes	13-18W	120°	50,000	120-277V	No	N.A.
28372	6PLV/835/DIR/R	3500K	620	82	103	Yes	13-18W	120°	50,000	120-277V	No	N.A.
28373	6PLV/840/DIR/R	4000K	640	82	107	Yes	13-18W	120°	50,000	120-277V	No	N.A.
28374	9.5PLV/827/DIR/R	2700K	950	82	100	Yes	26W	120°	50,000	120-277V	No	✓
28375	9.5PLV/830/DIR/RC	3000K	1000	82	105	Yes	26W	120°	50,000	120-277V	No	✓
28376	9.5PLV/835/DIR/RC	3500K	1000	82	105	Yes	26W	120°	50,000	120-277V	No	✓
28377	9.5PLV/840/DIR/RC	4000K	1020	82	107	Yes	26W	120°	50,000	120-277V	No	✓
57918	11PLV/930/DIR	3000K	920	92	84	Yes	26W	120°	50,000	120-277V	No	N.A.
98248	17PLV/830/DIR	3000K	1900	82	112	Yes	42W	110°	50,000	120-277V	No	✓
98249	17PLV/835/DIR	3500K	1950	82	115	Yes	42W	110°	50,000	120-277V	No	✓
98250	17PLV/840/DIR	4000K	2000	82	118	Yes	42W	110°	50,000	120-277V	No	✓



Horizontal Installation


SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98391	5.5PLH/835/HYBM	3500K	550	82	100	Yes	13-18W	110°	50,000	120-277V	No	N.A.
98392	5.5PLH/840/HYBM	4000K	560	82	102	Yes	13-18W	110°	50,000	120-277V	No	N.A.
98393	5.5PLH/830/BYP/E26	3000K	550	82	100	Yes	13W	110°	50,000	120-277V	No	N.A.
98394	5.5PLH/835/BYP/E26	3500K	550	82	100	Yes	13W	110°	50,000	120-277V	No	N.A.
98395	5.5PLH/840/BYP/E26	4000K	560	82	102	Yes	13W	110°	50,000	120-277V	No	N.A.
98396	5.5PLH/830/BYP/GU24	3000K	550	82	100	Yes	13W	110°	50,000	120-277V	No	N.A.
98397	5.5PLH/835/BYP/GU24	3500K	550	82	100	Yes	13W	110°	50,000	120-277V	No	N.A.
98398	5.5PLH/840/BYP/GU24	4000K	560	82	102	Yes	13W	110°	50,000	120-277V	No	N.A.
98399	8PLH/827/HYBM	2700K	870	82	108	Yes	26W	110°	50,000	120-277V	No	N.A.
98400	8PLH/830/HYBM	3000K	920	82	115	Yes	26W	110°	50,000	120-277V	No	N.A.
98401	8PLH/835/HYBM	3500K	920	82	115	Yes	26W	110°	50,000	120-277V	No	N.A.
98402	8PLH/840/HYBM	4000K	950	82	119	Yes	26W	110°	50,000	120-277V	No	N.A.
98252	15.5PLH/830/BYP	3000K	1700	82	110	Yes	42W	110°	50,000	120-277V	No	N.A.
98253	15.5PLH/835/BYP	3500K	1750	82	113	Yes	42W	110°	50,000	120-277V	No	N.A.
98254	15.5PLH/840/BYP	4000K	1800	82	116	Yes	42W	110°	50,000	120-277V	No	N.A.


* Note PL H 15.5W BYP operates on line voltage only and is not compatible with magnetic ballasts

PL H & V high output versions replace 42W CFL lamps




Hybrid Installation


MAGNETIC
BALLAST
COMPATIBLE


120-
277V
UNIVERSAL

Note PL H 15.5W BYP & PL V 16.5W BYP are not compatible with magnetic ballasts


- Hybrid installation – Mag. ballast or 120-277V line voltage
- Compatible with G24d, GX24d, G24q & GX24q installations
- Patented design
- E26 & GU24 versions available



Vertical Installation

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98385	5.5PLV/835/HYBM	3500K	600	82	109	No	13-18W	120°	50,000	120-277V	No	N.A.
98386	5.5PLV/840/HYBM	4000K	620	82	113	No	13-18W	120°	50,000	120-277V	No	N.A.
98387	8.5PLV/827/HYBM	2700K	950	82	112	No	26W	120°	50,000	120-277V	No	N.A.
98388	8.5PLV/830/HYBM	3000K	1000	82	118	No	26W	120°	50,000	120-277V	No	N.A.
98389	8.5PLV/835/HYBM	3500K	1000	82	118	No	26W	120°	50,000	120-277V	No	N.A.
98390	8.5PLV/840/HYBM	4000K	1020	82	120	No	26W	120°	50,000	120-277V	No	N.A.
98256	16.5PLV/830/BYP	3000K	1800	82	109	No	42W	120°	50,000	120-277V	No	N.A.
98257	16.5PLV/835/BYP	3500K	1850	82	112	No	42W	120°	50,000	120-277V	No	N.A.
98258	16.5PLV/840/BYP	4000K	1900	82	115	No	42W	120°	50,000	120-277V	No	N.A.

* Note PL V 16.5W BYP operates on line voltage only and is not compatible with magnetic ballasts



Extra Wide Beam Design - 180° Rotatable Base



Compact Form Factor Fits All Applications




- **BYPass installation – Requires bypassing the ballast**
- **Suitable for use in totally enclosed fixtures**
- **180° rotatable base**
- **Compact form factor fits most fixtures**

SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.
57818	3.5PLS/835/BYP/2G7	3500K	300	82	86	No	7-9W	180°	50,000	120-277V	Yes
57826	5.5PLS/835/BYP/2GX7	3500K	500	82	91	No	13W	180°	50,000	120-277V	Yes



Hybrid Installation



170° Rotatable Base



- **HYBrid installation - DIRect or BYPass**
- **Compatible with magnetic ballasts - DIRect installation**
- **Built-in universal voltage driver - BYPass installation**
- **Exceptional efficacy**

SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.
57812	3.5PLS/827/HYB/G23	2700K	280	82	80	No	7-9W	120°	50,000	120-277V	Yes
57813	3.5PLS/830/HYB/G23	3000K	280	82	80	No	7-9W	120°	50,000	120-277V	Yes
57814	3.5PLS/835/HYB/G23	3500K	300	82	86	No	7-9W	120°	50,000	120-277V	Yes
57815	3.5PLS/840/HYB/G23	4000K	300	82	86	No	7-9W	120°	50,000	120-277V	Yes
98403	5.5PLSV/827/HYB/GX23	2700K	570	82	104	No	13W	120°	50,000	120-277V	No
98404	5.5PLSV/830/HYB/GX23	3000K	600	82	109	No	13W	120°	50,000	120-277V	No
98405	5.5PLSV/835/HYB/GX23	3500K	600	82	109	No	13W	120°	50,000	120-277V	No
98406	5.5PLSV/840/HYB/GX23	4000K	620	82	113	No	13W	120°	50,000	120-277V	No
98407	5.5PLSH/827/HYB/GX23	2700K	520	82	95	No	13W	110°	50,000	120-277V	No
98408	5.5PLSH/830/HYB/GX23	3000K	550	82	100	No	13W	110°	50,000	120-277V	No
98409	5.5PLSH/835/HYB/GX23	3500K	550	82	100	No	13W	110°	50,000	120-277V	No
98410	5.5PLSH/840/HYB/GX23	4000K	560	82	102	No	13W	110°	50,000	120-277V	No
57820	5.5PLS/827/HYB/GX23	2700K	450	82	82	No	13W	120°	50,000	120-277V	Yes
57821	5.5PLS/830/HYB/GX23	3000K	500	82	91	No	13W	120°	50,000	120-277V	Yes
57822	5.5PLS/835/HYB/GX23	3500K	500	82	91	No	13W	120°	50,000	120-277V	Yes
57823	5.5PLS/840/HYB/GX23	4000K	520	82	95	No	13W	120°	50,000	120-277V	Yes

HID BOLLARD LINE



Designed for Bollard & Post Top Applications

HID Replacements

25W: 70-100W
16.5W: 50-70W
HID
120-277V

- Universal voltage 120-277V – Not compatible with ballasts
- E26 base – ENERGY STAR® certified
- EX39 base – DLC® qualified
- Suitable for use in totally enclosed fixtures

SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES / DLC
58238	16.5A21/830/277V	3000K	2000	82	121	No	125W Inc.	330°	40,000	120-277V	✓ / N.A.
58239	16.5A21/840/277V	4000K	2000	82	121	No	125W Inc.	330°	40,000	120-277V	✓ / N.A.
58240	16.5A21/850/277V	5000K	2050	82	124	No	125W Inc.	330°	40,000	120-277V	✓ / N.A.
97972	25HID/830/277V/E26	3000K	3200	82	128	No	200W Inc.	290°	50,000	120-277V	✓ / N.A.
97973	25HID/840/277V/E26	4000K	3300	82	132	No	200W Inc.	290°	50,000	120-277V	✓ / N.A.
97974	25HID/850/277V/E26	5000K	3400	82	136	No	200W Inc.	290°	50,000	120-277V	✓ / N.A.
97968	25HID/830/277V/EX39	3000K	3200	82	128	No	70-100W HID	290°	50,000	120-277V	N.A. / ✓
97969	25HID/840/277V/EX39	4000K	3300	82	132	No	70-100W HID	290°	50,000	120-277V	N.A. / ✓
97970	25HID/850/277V/EX39	5000K	3400	82	136	No	70-100W HID	290°	50,000	120-277V	N.A. / ✓
16325	E26 EXTENDER	E26 Lamp Extender Adds 1.30" (33mm) to Lamp Height									
97718	10SURGE/277V	10kV Surge Protector									

HID POST TOP LINE



Designed for Post Top Applications

- Universal voltage 120-277V – Not compatible with ballasts
- Fully omnidirectional beam angle
- Compatible with EX39 & E39 sockets
- Suitable for use in totally enclosed fixtures

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98087	37HID/830/277V/E26	3000K	4700	82	127	No	100-175W HID	320°	50,000	120-277V	Yes	N.A.
98088	37HID/840/277V/E26	4000K	5200	82	141	No	100-175W HID	320°	50,000	120-277V	Yes	N.A.
98089	37HID/850/277V/E26	5000K	5200	82	141	No	100-175W HID	320°	50,000	120-277V	Yes	N.A.
98084	37HID/830/277V/EX39	3000K	4700	82	127	No	100-175W HID	320°	50,000	120-277V	Yes	✓
98085	37HID/840/277V/EX39	4000K	5200	82	141	No	100-175W HID	320°	50,000	120-277V	Yes	✓
98086	37HID/850/277V/EX39	5000K	5200	82	141	No	100-175W HID	320°	50,000	120-277V	Yes	✓
98090	54HID/830/277V/EX39	3000K	7300	82	135	No	175-250W HID	320°	50,000	120-277V	Yes	✓
98091	54HID/840/277V/EX39	4000K	7550	82	140	No	175-250W HID	320°	50,000	120-277V	Yes	✓
98092	54HID/850/277V/EX39	5000K	7550	82	140	No	175-250W HID	320°	50,000	120-277V	Yes	✓
98097	68HID/840/277V/EX39	4000K	9500	82	140	No	175-250W HID	320°	50,000	120-277V	Yes	✓
98098	68HID/850/277V/EX39	5000K	9500	82	140	No	175-250W HID	320°	50,000	120-277V	Yes	✓
98100	100HID/840/277V/EX39	4000K	14,000	82	140	No	250-400W HID	320°	50,000	120-277V	Yes	✓
98101	100HID/850/277V/EX39	5000K	14,000	82	140	No	250-400W HID	320°	50,000	120-277V	Yes	✓
97718	10SURGE/277V					10kV Surge Protector						

HID HIGH BAY / LOW BAY LINE


HID WALL PACK LINE



E26 Version Available

- Universal voltage 120-277V – Not compatible with ballasts
- Visible uplighting
- Compatible with EX39 & E39 sockets
- Exceptional efficacy >126 LPW

Designed for High Bay & Low Bay Applications



Intentional Uplighting

All High Bay and Low Bay products feature a ring of LEDs mounted around the base to provide visible uplighting for improved aesthetics and comfort




SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98121	35HIDLB/840/BYP/E26	4000K	4400	82	126	No	100-175W HID	110°	50,000	120-277V	No	N.A.
98122	35HIDLB/850/BYP/E26	5000K	4400	82	126	No	100-175W HID	110°	50,000	120-277V	No	N.A.
98118	35HIDLB/840/BYP/EX39	4000K	4400	82	126	No	100-175W HID	110°	50,000	120-277V	No	✓
98119	35HIDLB/850/BYP/EX39	5000K	4400	82	126	No	100-175W HID	110°	50,000	120-277V	No	✓
98124	65HIDHB/840/BYP/EX39	4000K	8600	82	132	No	175-250W HID	110°	50,000	120-277V	No	✓
98125	65HIDHB/850/BYP/EX39	5000K	8600	82	132	No	175-250W HID	110°	50,000	120-277V	No	✓
98127	90HIDHB/840/BYP/EX39	4000K	12,400	82	138	No	250-400W HID	110°	50,000	120-277V	No	✓
98128	90HIDHB/850/BYP/EX39	5000K	12,400	82	138	No	250-400W HID	110°	50,000	120-277V	No	✓



E26 Version Available

- Universal voltage 120-277V – Not compatible with ballasts
- Designed for horizontally-mounted wall pack applications
- Exceptional efficacy >140 LPW
- Suitable for use in totally enclosed fixtures

Designed for Wall Pack Applications



350° Rotatable Base




Horizontal lamp supports included



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98179	20HIDWP/840/277V/E26	4000K	2800	82	140	No	70-100W HID	120°	50,000	120-277V	Yes	N.A.
98180	20HIDWP/850/277V/E26	5000K	2800	82	140	No	70-100W HID	120°	50,000	120-277V	Yes	N.A.
98183	40HIDWP/840/277V/E26	4000K	5800	82	145	No	100-175W HID	120°	50,000	120-277V	Yes	N.A.
98184	40HIDWP/850/277V/E26	5000K	5800	82	145	No	100-175W HID	120°	50,000	120-277V	Yes	N.A.
98185	40HIDWP/840/277V/EX39	4000K	5800	82	145	No	100-175W HID	120°	50,000	120-277V	Yes	✓
98186	40HIDWP/850/277V/EX39	5000K	5800	82	145	No	100-175W HID	120°	50,000	120-277V	Yes	✓
98189	54HIDWP/840/277V/EX39	4000K	7800	82	144	No	175-250W HID	120°	50,000	120-277V	Yes	✓
98190	54HIDWP/850/277V/EX39	5000K	7800	82	144	No	175-250W HID	120°	50,000	120-277V	Yes	✓



- Revolutionary CLOUD design
- 60% lighter due to environmentally friendly construction
- BR30 high CRI & GU24 versions available
- Suitable for use in totally enclosed fixtures




SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
98460	7.5R20DIM/827	2700K	525	82	70	Yes	45W	120°	25,000	120V	Yes	✓
98461	9BR30DIM/827	2700K	650	82	72	Yes	65W	120°	25,000	120V	Yes	✓
98462	9BR30DIM/830	3000K	650	82	72	Yes	65W	120°	25,000	120V	Yes	✓
98463	9BR30DIM/840	4000K	650	82	72	Yes	65W	120°	25,000	120V	Yes	✓
98464	11BR40DIM/827	2700K	950	82	86	Yes	75W	120°	25,000	120V	Yes	✓
98465	11BR40DIM/830	3000K	950	82	86	Yes	75W	120°	25,000	120V	Yes	✓
98466	15.5BR40DIM/827	2700K	1100	82	71	Yes	85W	120°	25,000	120V	No	✓
98467	15.5BR40DIM/830	3000K	1100	82	71	Yes	85W	120°	25,000	120V	No	✓

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES / JA8 / T20
98023	9.5BR30DIM/927/R	2700K	700	92	74	Yes	65W	110°	25,000	120V	Yes	✓ / ✓ / ✓
98024	9.5BR30DIM/927/GU24	2700K	700	92	74	Yes	65W	110°	25,000	120V	Yes	✓ / ✓ / ✓




- Enclosed rated 100W, 75W & 60W replacements
- High CRI 100W, 75W & 60W replacements
- Enclosed rated GU24 100W & 60W replacements
- 120-277V universal voltage 60W replacements



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
97985	6A19DIM/827/R	2700K	480	82	80	Yes	40W	220°	25,000	120V	No	✓
97986	6A19DIM/830/R	3000K	480	82	80	Yes	40W	220°	25,000	120V	No	✓
98011	8A19DIM/827/R	2700K	800	82	100	Yes	60W	220°	25,000	120V	No	✓
98012	8A19DIM/830/R	3000K	800	82	100	Yes	60W	220°	25,000	120V	No	✓
98013	8A19DIM/840/R	4000K	800	82	100	Yes	60W	220°	25,000	120V	No	✓
98559	9A19DIM/927	2700K	800	92	89	Yes	60W	240°	25,000	120V	Yes	✓
98560	9A19DIM/930	3000K	820	92	91	Yes	60W	240°	25,000	120V	Yes	✓
98561	9A19DIM/940	4000K	860	92	96	Yes	60W	240°	25,000	120V	Yes	✓
97908	9A19DIM/827/GU24/R	2700K	800	82	89	Yes	60W	240°	25,000	120V	Yes	✓
97909	9A19DIM/830/GU24/R	3000K	820	82	91	Yes	60W	240°	25,000	120V	Yes	✓
97910	9A19DIM/840/GU24/R	4000K	860	82	96	Yes	60W	240°	25,000	120V	Yes	✓
97964	10A19DIM/827	2700K	1100	82	110	Yes	75W	240°	25,000	120V	Yes	✓
97965	10A19DIM/830	3000K	1150	82	115	Yes	75W	240°	25,000	120V	Yes	✓
97966	10A19DIM/840	4000K	1200	82	120	Yes	75W	240°	25,000	120V	Yes	✓
97961	14A21DIM/827	2700K	1600	82	114	Yes	100W	230°	25,000	120V	Yes	✓
97962	14A21DIM/830	3000K	1650	82	118	Yes	100W	230°	25,000	120V	Yes	✓
97963	14A21DIM/840	4000K	1700	82	121	Yes	100W	230°	25,000	120V	Yes	✓
16332	17A21DIM/827/GU24	2700K	1600	82	94	Yes	100W	330°	25,000	120V	Yes	✓

SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES / JA8 / T20
28395	9A19DIM/927	2700K	860	92	89	Yes	60W	240°	30,000	120V	✓ / ✓ / ✓
97911	9A19DIM/927/GU24	2700K	800	92	89	Yes	60W	240°	25,000	120V	✓ / ✓ / ✓
98562	9A19/927/277V	2700K	1100	92	89	No	60W	300°	25,000	120-277V	✓ / N.A. / N.A.
98563	9A19/930/277V	3000K	800	92	91	No	60W	300°	25,000	120-277V	✓ / N.A. / N.A.
98564	9A19/940/277V	4000K	820	92	96	No	60W	300°	25,000	120-277V	✓ / N.A. / N.A.
16326	15A21DIM/927	2700K	1100	92	73	Yes	75W	330°	25,000	120V	✓ / N.A. / N.A.
16329	18.5A21DIM/927	2700K	1600	92	86	Yes	100W	330°	25,000	120V	✓ / ✓ / ✓
			500		125		40W				
98083	14A19/827/3WAY	2700K	1000	82	125	No	75W	230°	15,000	120V	✓ / N.A. / N.A.
			1500		107		100W				



All Warm Dim Lamps Feature 2700K-2200K CCT Dimming




- Smooth dimming from 2700K-2200K CCT
- Traditional incandescent style dimming
- Exceptional efficacy
- Available in Downlight, BR, A19 & Candle lamps


Lighting for Any Occasion



2700K-2200K Warm Dim



WARM DIM



WARM DIM

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
57884	5B11DIM/8CCTD	2200K-2700K	300	82	60	Yes	40W	230°	25,000	120V	Yes	✓
58001	6.5R20DIM/8CCTD	2200K-2700K	500	82	77	Yes	45W	110°	25,000	120V	Yes	✓
57885	9BR30DIM/8CCTD	2200K-2700K	650	82	72	Yes	65W	110°	25,000	120V	Yes	✓
57883	9.5A19DIM/8CCTD	2200K-2700K	800	82	84	Yes	60W	330°	25,000	120V	Yes	✓
58002	10.5BR40DIM/8CCTD	2200K-2700K	735	82	70	Yes	65W	110°	25,000	120V	Yes	✓
58100	11DL6DIM/8CCTD	2200K-2700K	770	82	70	Yes	65W	110°	40,000	120V	N.A.	✓

CREATE THE PERFECT AMBIENCE




These GREEN CREATIVE lamps feature 2700K-2200K CCT dimming designed to replicate the warm dimming effect of traditional incandescent light sources. As the lamp dims, its CCT gradually warms, helping to create the perfect ambience for all occasions.

FILAMENT LINE



- Micro-designed driver - No heatsink required
- Comfortable warm diffused light
- Smooth dimming with existing installations
- Sliver bowl design helps redirect light and minimizes glare




SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Finish	ES / T20
98458	1FS14/820/A	2000K	35	82	75	Yes	10W	300°	15,000	120V	Amber	N.A. / N.A.
98457	1FS14/827	2700K	55	82	37	Yes	10W	300°	15,000	120V	Clear	N.A. / N.A.
98459	3FT6DIM/820/A	2000K	110	82	71	Yes	25W	300°	15,000	120V	Amber	N.A. / N.A.
57946	3.5FT10DIM/822/A	2200K	250	82	90	Yes	25W	330°	15,000	120V	Amber	N.A. / N.A.
98240	4.5FBA11DIM/820/FT/A	2000K	240	82	68	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
98241	3.3FB11DIM/927	2700K	300	92	90	Yes	40W	300°	15,000	120V	Clear	✓ / ✓
98242	3.3FB11DIM/927/E26	2700K	300	92	107	Yes	40W	300°	15,000	120V	Clear	✓ / ✓
98456	3.8FB11DIM/827/FR	2700K	300	82	80	Yes	40W	300°	15,000	120V	Frosted	N.A. / N.A.
98454	5FB11DIM/827	2700K	500	82	107	Yes	60W	300°	15,000	120V	Clear	N.A. / N.A.
98455	5FB11DIM/827/E26	2700K	500	82	93	Yes	60W	300°	15,000	120V	Clear	✓ / N.A.
98239	4FST19DIM/820/A	2000K	300	82	90	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
98357	5FA19DIM/820/A	2000K	340	82	92	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
98376	5FA19DIM/827	2700K	450	82	63	Yes	40W	300°	15,000	120V	Clear	N.A. / N.A.
98450	5FA19DIM/827/FR	2700K	450	82	89	Yes	40W	300°	15,000	120V	Frosted	N.A. / N.A.
98448	7.5FA19DIM/820/A	2000K	600	82	94	Yes	60W	300°	15,000	120V	Amber	N.A. / N.A.
98278	7.5FA19DIM/827	2700K	800	82	91	Yes	60W	300°	15,000	120V	Clear	✓ / N.A.
98449	7.5FA19DIM827/FR	2700K	800	82	91	Yes	60W	300°	15,000	120V	Frosted	N.A. / N.A.
98358	7.5FA19DIM/827/SB	2700K	700	82	53	Yes	60W	N.A.	15,000	120V	Silver Bowl	N.A. / N.A.
98279	9FA19DIM/927	2700K	810	92	79	Yes	60W	300°	15,000	120V	Clear	✓ / ✓
98453	4FG16.5DIM/820/A	2000K	250	82	100	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
98451	4FG16.5DIM/827	2700K	350	82	100	Yes	40W	300°	15,000	120V	Clear	N.A. / N.A.
98452	4FG16.5DIM/827/E26	2700K	350	82	88	Yes	40W	300°	15,000	120V	Clear	N.A. / N.A.
98378	4FG25DIM/820/A	2000K	250	82	88	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
97826	4.5FG25DIM/827/SB	2700K	400	82	63	Yes	40W	N.A.	15,000	120V	Silver Bowl	N.A. / N.A.
98377	3.8FG25DIM/927	2700K	350	92	55	No	40W	300°	15,000	120V	Clear	✓ / ✓
57945	5FG40DIM/827	2700K	470	82	35	No	40W	330°	15,000	120V	Clear	✓ / N.A.

DECORATIVE LINE



- 40W incandescent replacements
- Perfect decorative retrofit needs
- Omnidirectional: 275° beam angle
- Powerful 450 lumens in 2700K



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
97729	6G25DIM/827/R	2700K	450	82	75	Yes	40W	275°	25,000	120V	No	✓



GREEN CREATIVE

1200 Bayhill Drive, Suite 220

San Bruno, CA 94066

Tel / Fax: (866) 774-5433

info@greencreative.com

www.greencreative.com



/ GREENCREATIVELED



/ GClightingLed



/ GREEN CREATIVE



GREENCREATIVE



GREENCREATIVE

 LUMINAIRES



2019 LUMINAIRES CATALOG



Your Partner for Innovative Lighting Solutions

GREEN CREATIVE, founded in 2010, is a solid state lighting development and manufacturing company based in Silicon Valley, CA. The company offers a comprehensive line of high-performance LED lighting solutions which has been widely adopted by some of the largest companies in the world.



Bringing you the latest in LED technology


Anchored by strong integrated R&D capabilities and patented technology, GREEN CREATIVE innovation, performance and reliability have been recognized year after year by the Illuminating Engineering Society Progress Report, the LEDs Magazine Sapphire Awards, Edison Report, NAILD and more.

A complete line with national & international distribution

GREEN CREATIVE's full product line of ENERGY STAR, DLC, NSF & JA8 certified indoor retrofit and new construction lighting solutions serves the Retail, Hospitality, Food & Beverage, Office, Education & Industrial sectors through multiple distribution centers and sales networks across the USA.



2019 LUMINAIRES TABLE OF CONTENTS



2019 LUMINAIRES FEATURED PRODUCTS



SPECFIT SERIES

4", 6", 8" & 9.5" form factors
Adjustable lumen output
Reflector & lens options



SELECFIT SERIES

Adjustable light output
Selectable CCT
120V or 0-10V dimming



MINIFIT GIMBAL SERIES

1" & 2" compact form factors
360° rotation, 30° tilt
IC and air-tight rated




THINFIT EXT SERIES

External driver
Wet, IC & air-tight rated
120V or 0-10V dimming



CHOICE OF MUTIPLE OPTICS



SELECTABLE LIGHT OUTPUT



LES & LEM

LES - 500/700/1000 Lumens
LEM - 1500/2000/2500 Lumens



LEL

LEL - 3000/4000/5000 Lumens



SelectDrive Technology - Adjustable Lumen Output



- Field interchangeable optics
- Selectable CCT & Light Output
- High CRI 90 – CRI 97 also available
- Multiple reflector options – CC, CW, WH & BL

SPECIFICATIONS										
Light Engine and Driver							Reflector			
Series	Light Engine	CRI	CCT	Driver	Voltage	Optical Distribution	Reflector Shape	Finish	Options	ES
AD4 4"	LES 500-700-1000 lumens	90 90+ CRI	27 2700K	DIM010 0-10V Dim to 5%	UNV 120-277 50/60Hz	MD Medium	ADR4 4" Round Reflector	CC Clear Diffuse Trim and Flange	SD347 347V Transformer	✓
AD6 6"	LEM 1500-2000-2500 lumens	97 97 CRI 3000K only	30 3000K			VN Very Narrow	ADR6 6" Round Reflector	CW Clear Diffuse Trim, White Flange	SD480 480V Transformer	✓
AD8 8"	LEL 3000-4000-5000 lumens		35 3500K			NR Narrow	ADR8 8" Round Reflector	WH Matte White Trim and Flange	EM Emergency Backup	✓
AD9.5 9.5"			40 4000K			WD Wide	ADR9.5 9.5" Round Reflector	BL Matte Black Trim and Flange		✓
			50 5000K							✓

ACCESSORIES		
Product	Model	Description
98079	ADWAW	Wall Wash Accessory
98569	GOOFRING4	4" Goof Ring Outer Diameter 8-1/8"
98568	GOOFRING6	6" Goof Ring Outer Diameter 10-7/16"
98567	GOOFRING8	8" Goof Ring Outer Diameter 12-6/16"
98566	GOOFRING9.5	9.5" Goof Ring Outer Diameter 14-3/16"
98501	NCPLATE/T4689	New Construction or Remodel Plate for T-Grid Ceilings for Use with 4", 6", 8" and 9.5" Models
98502	NCPLATE468	New Construction Plate for Stud/Joist Mounting for Use with 4", 6" and 8" Models



Select White Select Drive



SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES
98539	SLFT4/80CCTS/DIM120V	3000/3500/4000K	500/700/1000	80	100/105/100	120V	7W - 1x13W 9W - 1x18W 12W - 1x26W	90°	50,000	120V	Mar.
98540	SLFT4/80CCTS/DIM010UNV	3000/3500/4000K	500/700/1000	80	100/105/100	0-10V		90°	50,000	120-277V	Mar.
98541	SLFT4/80CCT2750/DIM010UNV	2700/5000K	500/700/1000	80	100/103	0-10V		90°	50,000	120-277V	Mar.
98542	SLFT6/80CCTS/DIM120V	3000/3500/4000K	700/1000/1500	80	100/105/100	120V	8W - 1x18W 10W - 1x26W 15W - 1x32W	90°	50,000	120V	Mar.
98543	SLFT6/80CCTS/DIM010UNV	3000/3500/4000K	700/1000/1500	80	100/105/100	0-10V		90°	50,000	120-277V	Mar.
98544	SLFT6/80CCT2750/DIM010UNV	2700/5000K	700/1000/1500	80	100/103	0-10V		90°	50,000	120-277V	Mar.
98545	SLFT8/80CCTS/DIM120V	3000/3500/4000K	1000/1500/2000	80	100/105/100	120V	11W - 1x26W 15W - 1x32W 19W - 1x42W/2x26W	90°	50,000	120V	Mar.
98546	SLFT8/80CCTS/DIM010UNV	3000/3500/4000K	1000/1500/2000	80	100/105/100	0-10V		90°	50,000	120-277V	Mar.
98547	SLFT8/80CCT2750/DIM010UNV	2700/5000K	1000/1500/2000	80	100/103	0-10V		90°	50,000	120-277V	Mar.
98548	SLFT9.5/80CCTS/DIM120V	3000/3500/4000K	2000/2500/3200	80	100/105/100	120V	18W - 1x42W/2x26W 23W - 1x57W/2x32W 30W - 2x42W	90°	50,000	120V	Mar.
98549	SLFT9.5/80CCTS/DIM010UNV	3000/3500/4000K	2000/2500/3200	80	100/105/100	0-10V		90°	50,000	120-277V	Mar.
98550	SLFT9.5/80CCT2750/DIM010UNV	2700/5000K	2000/2500/3200	80	100/103	0-10V		90°	50,000	120-277V	Mar.

SELECTABLE CCT

Make retrofit projects easier with the SELECTFIT commercial downlight family of fixtures, powered by SelectWhite technology. Select the CCT before, during or after installation with just the flip of a switch and never worry about having the correct CCT for a project again.

- For retrofit or new construction installation
- Innovative design saves time & materials
- IC and air-tight rated
- 120V TRIAC/ELV or 0-10V dimming



SELECTABLE LIGHT OUTPUT

Get the right amount of light with SELECTFIT, powered by SelectDrive technology. Choose either Low, Medium or High light output, equivalent to various CFL lamp combinations. With just the flip of a switch ensure that every space has just the right amount of light.

QUALITY, DURABILITY AND SIMPLICITY



ACCESSORIES


Product	Model	Description
98569	GOOFRING4	4" Goof Ring Outer Diameter 8-1/8"
98568	GOOFRING6	6" Goof Ring Outer Diameter 10-7/16"
98567	GOOFRING8	8" Goof Ring Outer Diameter 12-6/16"
98566	GOOFRING9.5	9.5" Goof Ring Outer Diameter 14-3/16"
98501	NCPLATE/T4689	New Construction or Remodel Plate for T-Grid Ceilings for Use with 4", 6", 8" and 9.5" Models
98502	NCPLATE468	New Construction Plate for Stud/Joist Mounting for Use with 4", 6" and 8" Models
98583	NCPLATEJB	Additional J-Box for New Construction Installation
58012	35EMINVERTER	Emergency Inverter 35W for Use with 4", 6" and 8" Models Only
98235	50EMINVERTER	Emergency Inverter 50W for Use with 9.5" Model

COMMERCIAL DOWNLIGHT - INNOFIT




SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES
57863	14CDLA4/827/277V	2700K	465/650/930	80	78/72/66	No	6W - 1x13W 9W - 1x18W 14W - 1x26W/2x13W	110°	40,000	120-277V	✓
57864	14CDLA4/830/277V	3000K	500/700/1000	80	83/78/71	No		110°	40,000	120-277V	✓
57865	14CDLA4/835/277V	3500K	500/700/1000	80	83/78/71	No		110°	40,000	120-277V	✓
57866	14CDLA4/840/277V	4000K	500/700/1000	80	83/78/71	No		110°	40,000	120-277V	✓
57873	21CDLA6/827/277V/R	2700K	930/1400/1860	80	78/74/69	No	12W - 1x26W/2x13W 19W - 1x32W/2x18W 27W - 1x42W/2x26W	110°	40,000	120-277V	✓
57874	21CDLA6/830/277V/R	3000K	1000/1500/2000	80	83/79/74	No		110°	40,000	120-277V	✓
57875	21CDLA6/835/277V/R	3500K	1000/1500/2000	80	83/79/74	No		110°	40,000	120-277V	✓
57876	21CDLA6/840/277V/R	4000K	1000/1500/2000	80	83/79/74	No		110°	40,000	120-277V	✓
57868	27CDLA8/827/277V	2700K	650/930/1400	80	76/69/67	No	8.5W - 1x18W 13.5W - 1x26W/2x13W 21W - 1x32W/2x18W	110°	40,000	120-277V	✓
57869	27CDLA8/830/277V	3000K	700/1000/1500	80	82/74/71	No		110°	40,000	120-277V	✓
57870	27CDLA8/835/277V	3500K	700/1000/1500	80	82/74/71	No		110°	40,000	120-277V	✓
57871	27CDLA8/840/277V	4000K	700/1000/1500	80	82/74/71	No		110°	40,000	120-277V	✓
57878	45CDLA9.5/827/277V	2700K	1860/2325/2975	80	79/73/76	No	23.5W - 1x42W/2x26W 32W - 1x57W/2x32W 45W - 2x42W	110°	40,000	120-277V	✓
57879	45CDLA9.5/830/277V	3000K	2000/2500/3200	80	85/78/71	No		110°	40,000	120-277V	✓
57880	45CDLA9.5/835/277V	3500K	2000/2500/3200	80	85/78/71	No		110°	40,000	120-277V	✓
57881	45CDLA9.5/840/277V	4000K	2000/2500/3200	80	85/78/71	No		110°	40,000	120-277V	✓

COMMERCIAL DOWNLIGHT - INNOFIT



Dimensions		
Model	Aperture Min.	Aperture Max.
4"	3-15/16"	5-1/8"
6"	6"	7-1/2"
8"	7-11/16"	9-7/16"
9.5"	8-11/16"	10-7/16"

SelectDrive Technology - Adjustable Lumen Output



- For retrofit or new construction installation
- Universal housing compatibility
- Adjustable lumen output – 3 defined light levels
- Easy fit installation – Spring-action housing clips


ACCESSORIES		
Product	Model	Description
98569	GOOFRING4	4" Goof Ring Outer Diameter 8-1/8"
98568	GOOFRING6	6" Goof Ring Outer Diameter 10-7/16"
98567	GOOFRING8	8" Goof Ring Outer Diameter 12-6/16"
98566	GOOFRING9.5	9.5" Goof Ring Outer Diameter 14-3/16"
98501	NCPLATE/T4689	New Construction or Remodel Plate for T-Grid Ceilings for Use with 4", 6", 8" and 9.5" Models
98502	NCPLATE468	New Construction Plate for Stud/Joist Mounting for Use with 4", 6" and 8" Models
98583	NCPLATEJB	Additional J-Box for New Construction Installation
58012	35EMINVERTER	Emergency Inverter 35W for Use with 4", 6" and 8" Models Only
98235	50EMINVERTER	Emergency Inverter 50W for Use with 9.5" Model

COMMERCIAL DOWNLIGHT - CDL




SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES
98264	18CDL6DIM/830/277V	3000K	1440	80	80	0-10V	2x18W	90°	50,000	120-277V	✓
98265	18CDL6DIM/835/277V	3500K	1440	80	80	0-10V		90°	50,000	120-277V	✓
98266	18CDL6DIM/840/277V	4000K	1480	80	82	0-10V		90°	50,000	120-277V	✓
98269	24CDL8DIM/830/277V	3000K	1920	80	80	0-10V	2x26W	90°	50,000	120-277V	✓
98270	24CDL8DIM/835/277V	3500K	1920	80	80	0-10V		90°	50,000	120-277V	✓
98271	24CDL8DIM/840/277V	4000K	1970	80	82	0-10V		90°	50,000	120-277V	✓
98274	30CDL9.5DIM/830/277V	3000K	2700	80	90	0-10V	2x42W	90°	50,000	120-277V	✓
98275	30CDL9.5DIM/835/277V	3500K	2700	80	90	0-10V		90°	50,000	120-277V	✓
98276	30CDL9.5DIM/840/277V	4000K	2760	80	92	0-10V		90°	50,000	120-277V	✓


COMMERCIAL DOWNLIGHT - CDL



Slide-on Retaining Clips




LED Driver Box





- Fits existing architectural & commercial housing
- 120-277V, 0-10V Dimming
- Easy installation – Quick connector and pre-wired conduit
- Superior savings and performance over CFL

Accessories include a carabiner safety clip that can be used during installation for easy wiring. Slide-on retaining clips are also included to secure the fixture and driver's quick connector for easy installation.

Dimensions		
Model	A	B
18CDL6DIM/8xx/277V	6-3/16"	5-11/16"
24CDL8DIM/8xx/277V	7-3/4"	6-5/16"
30CDL9.5DIM/8xx/277V	9-3/8"	7-7/8"






- Compatible with 4" and 5-6" housings
- Installs in just minutes – No rewiring
- High output, up to 1260 lumens
- High CRI versions rated for wet locations

SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES / JA8
97988	10DL4DIM/927	2700K	700	90	70	120V	65W	100°	50,000	120V	✓/✓
97989	10DL4DIM/930	3000K	700	90	70	120V		100°	50,000	120V	✓/✓
97990	10DL4DIM/940	4000K	700	90	70	120V		100°	50,000	120V	✓/✓
97991	12DL6DIM/927	2700K	840	90	70	120V	75W	100°	50,000	120V	✓/✓
97992	12DL6DIM/930	3000K	840	90	70	120V		100°	50,000	120V	✓/✓
97993	12DL6DIM/940	4000K	840	90	70	120V		100°	50,000	120V	✓/✓
97994	18DL6DIM/927	2700K	1260	90	70	120V	100W	100°	50,000	120V	✓/✓
97995	18DL6DIM/930	3000K	1260	90	70	120V		100°	50,000	120V	✓/✓
97996	18DL6DIM/940	4000K	1260	90	70	120V		100°	50,000	120V	✓/✓

APPLICATIONS





SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES / JA8
98439	GIMB1/927/FL/DIM120	2700K	320	90	64	120V		38°	50,000	120V	N.A. / Mar.
98440	GIMB1/930/FL/DIM120	3000K	350	90	70	120V	35W	38°	50,000	120V	Mar. / Mar.
98441	GIMB1/940/FL/DIM120	4000K	390	90	78	120V		38°	50,000	120V	Mar. / Mar.
98442	GIMB2/927/FL/DIM120	2700K	680	90	73	120V		38°	50,000	120V	Mar. / Mar.
98443	GIMB2/930/FL/DIM120	3000K	720	90	75	120V	50W	38°	50,000	120V	Mar. / Mar.
98444	GIMB2/940/FL/DIM120	4000K	750	90	78	120V		38°	50,000	120V	Mar. / Mar.




Adjustable Fixture Aiming

Get the right light in the right place with the miniFIT gimbals. The gimbals come with a 38° beam acrylic optic, producing a consistent, precise beam of light. In addition, they rotate 360° and tilt up to 30° so you can mount them in any orientation in the ceiling and still aim the light to graze textured walls, highlight artwork, or emphasize architectural features. Perfect for residential, retail and hospitality applications.

Quick and Easy Installation

The miniFIT family is quick and easy to install. Connecting power in the external junction box is a breeze with the push in connectors. Wiring the fixture is even easier with the plenum rated quick connector. The optional new construction plates, keyhole mounting slots and spring clip hooks allow for a simple installation and compliance with local building codes. The sturdy spring action clips will keep the fixture tight to the ceiling, ensuring an aesthetically pleasing installation.




ACCESSORIES		
Product	Model	Description
98584	GIMB1NCPLATE	Gimbal 1" New Construction Plate for Stud / Joist Mounting
98585	GIMB2NCPLATE	Gimbal 2" New Construction Plate for Stud / Joist Mounting

NEW CONSTRUCTION - THINFIT EXT



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Wet	ES / JA8
98104	10NCDLR4DIM/927/EXT	2700K	720	90	70	120V	65W	110°	50,000	120V	Yes	✓ / ✓
98105	10NCDLR4DIM/930/EXT	3000K	720	90	72	120V	65W	110°	50,000	120V	Yes	✓ / ✓
98106	10NCDLR4DIM/940/EXT	4000K	740	90	74	120V	65W	110°	50,000	120V	Yes	✓ / ✓
98214	10NCDLR4DIM/930/277V/EXT	3000K	700	90	72	0-10V	65W	110°	50,000	120-277V	Yes	✓ / ✓
98215	10NCDLR4DIM/935/277V/EXT	3500K	720	90	72	0-10V	65W	110°	50,000	120-277V	Yes	✓ / ✓
98216	10NCDLR4DIM/940/277V/EXT	4000K	740	90	74	0-10V	65W	110°	50,000	120-277V	Yes	✓ / ✓
98107	12NCDLR6DIM/927/EXT	2700K	900	90	75	120V	85W	110°	50,000	120V	Yes	✓ / ✓
98108	12NCDLR6DIM/930/EXT	3000K	920	90	77	120V	85W	110°	50,000	120V	Yes	✓ / ✓
98109	12NCDLR6DIM/940/EXT	4000K	940	90	78	120V	85W	110°	50,000	120V	Yes	✓ / ✓
98217	12NCDLR6DIM/930/277V/EXT	3000K	920	90	77	0-10V	85W	110°	50,000	120-277V	Yes	✓ / ✓
98218	12NCDLR6DIM/935/277V/EXT	3500K	920	90	77	0-10V	85W	110°	50,000	120-277V	Yes	✓ / ✓
98219	12NCDLR6DIM/940/277V/EXT	4000K	940	90	78	0-10V	85W	110°	50,000	120-277V	Yes	✓ / ✓
98110	24.5NCDLR8DIM/927/EXT	2700K	1820	90	74	120V	125W	110°	50,000	120V	Yes	✓ / ✓
98111	24.5NCDLR8DIM/930/EXT	3000K	1920	90	78	120V	125W	110°	50,000	120V	Yes	✓ / ✓
98112	24.5NCDLR8DIM/940/EXT	4000K	1920	90	78	120V	125W	110°	50,000	120V	Yes	✓ / ✓
98220	24.5NCDLR8DIM/930/277V/EXT	3000K	1920	90	78	0-10V	125W	110°	50,000	120-277V	Yes	✓ / ✓
98221	24.5NCDLR8DIM/935/277V/EXT	3500K	1920	90	78	0-10V	125W	110°	50,000	120-277V	Yes	✓ / ✓
98222	24.5NCDLR8DIM/940/277V/EXT	4000K	1920	90	78	0-10V	125W	110°	50,000	120-277V	Yes	✓ / ✓

NEW CONSTRUCTION - THINFIT EXT




- For new construction or remodel installation
- Innovative design saves time & materials
- Easy to use spring action clips
- 120V TRIAC/ELV or 0-10V dimming

ACCESSORIES		
Product	Model	Description
97847	DLNC4GOOF/R	4" Goof Ring Outer Diameter 6"
97848	DLNC6GOOF/R	6" Goof Ring Outer Diameter 8-1/2"
98238	DLNC8GOOF	8" Goof Ring Outer Diameter 10-1/4"
98501	NCPLATE/T4689	New Construction or Remodel Plate for T-Grid Ceilings for Use with 4" and 6" Models
98502	NCPLATE468	New Construction Plate for Stud/Joist Mounting for Use with 4", 6" and 8" Models
98583	NCPLATEJB	Additional J-Box for New Plate Construction Installation
58012	35EMINVERTER	Emergency Inverter 35W for Use with 4", 6" and 8" Models


Suitable for Shallow Ceiling Applications


Wet location, IC & Air-tight Rated



Installs Directly into Ceiling - No Housing Needed

No J-box or Recessed Can Required IC-Rated






SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Wet	ES
58025	8.5DLNC4DIM/827	2700K	510	82	60	120V	50W	100°	40,000	120V	No	✓
58026	8.5DLNC4DIM/830	3000K	530	82	62	120V	50W	100°	40,000	120V	No	✓
58027	8.5DLNC4DIM/840	4000K	550	82	65	120V	50W	100°	40,000	120V	No	✓
58028	11.6DLNC6DIM/827	2700K	810	82	70	120V	75W	100°	40,000	120V	No	✓
58029	11.6DLNC6DIM/830	3000K	830	82	72	120V	75W	100°	40,000	120V	No	✓
58030	11.6DLNC6DIM/840	4000K	850	82	73	120V	75W	100°	40,000	120V	No	✓


- For new construction or remodel installation
- Innovative design saves time & materials
- Easy to use spring action clips
- Goof Ring available

Edge Lighting Technology




Installs Directly into Ceiling - No Housing Needed

No J-box or Recessed Can Required IC-Rated



ACCESSORIES		
Product	Model	Description
97847	DLNC4GOOF/R	4" Goof Ring Outer Diameter 6"
97848	DLNC6GOOF/R	6" Goof Ring Outer Diameter 8-1/2"
98501	NCPLATE/T4689	New Construction or Remodel Plate for T-Grid Ceilings for Use with 4" and 6" Models
98502	NCPLATE468	New Construction Plate for Stud/Joist Mounting for Use with 4" and 6" Models
98583	NCPLATEJB	Additional J-Box for New Construction Plate Installation
58012	35EMINVERTER	Emergency Inverter 35W for Use with 4" and 6" Models

SURFACE MOUNT - CLICK ROUND



SPECIFICATIONS - ROUND												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Wet	ES / JA8
58260	10SMPR5.5DIM/927	2700K	550	90	55	120V	50W	100°	50,000	120V	Yes	✓ / N.A.
58261	10SMPR5.5DIM/930	3000K	550	90	55	120V	50W	100°	50,000	120V	Yes	✓ / N.A.
58262	10SMPR5.5DIM/940	4000K	560	90	56	120V	50W	100°	50,000	120V	Yes	✓ / N.A.
58257	15SMPR7DIM/927	2700K	850	90	57	120V	75W	100°	50,000	120V	Yes	✓ / N.A.
58258	15SMPR7DIM/930	3000K	850	90	57	120V	75W	100°	50,000	120V	Yes	✓ / N.A.
58259	15SMPR7DIM/940	4000K	870	90	58	120V	75W	100°	50,000	120V	Yes	✓ / N.A.
97978	15SMPR7DIM/927/R	2700K	850	90	57	120V	75W	100°	50,000	120V	Yes	✓ / ✓
97979	15SMPR7DIM/930/R	3000K	850	90	57	120V	75W	100°	50,000	120V	Yes	✓ / ✓
97980	15SMPR7DIM/940/R	4000K	870	90	58	120V	75W	100°	50,000	120V	Yes	✓ / ✓
58265	15SMPR7DIM/930/277V	3000K	870	90	57	0-10V	75W	100°	50,000	120-277V	Yes	✓ / N.A.
58266	15SMPR7DIM/940/277V	4000K	850	90	58	0-10V	75W	100°	50,000	120-277V	Yes	✓ / N.A.
58255	20SMPR9DIM/930	3000K	1200	90	60	120V	100W	100°	50,000	120V	Yes	✓ / N.A.
58256	20SMPR9DIM/940	4000K	1250	90	63	120V	100W	100°	50,000	120V	Yes	✓ / N.A.
58263	20SMPR9DIM/930/277V	3000K	1200	90	60	0-10V	100W	100°	50,000	120-277V	Yes	✓ / N.A.
58264	20SMPR9DIM/940/277V	4000K	1250	90	63	0-10V	100W	100°	50,000	120-277V	Yes	✓ / N.A.
58033	SMP/ACC	4" & 6" Recessed Can Accessories for 5.5" & 7" Round & Square (5.5" for Use in 4" Can Only, 7" for Use in 4" or 6" Can)										

SURFACE MOUNT - CLICK SQUARE



- Innovative CLICK design - Edge lighting technology
- Wet location & high CRI
- Compatible with 4" J-boxes (standard)
- 120V TRIAC/ELV or 0-10V dimming


SootheOptic Low Glare Technology

Viewing Angle

0° 45° >65°

SootheOptic low glare technology reduces visual glare and creates a comfortable lighting environment


SPECIFICATIONS - SQUARE												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Wet	ES / JA8
58247	10SMPS5.5DIM/927	2700K	550	90	55	120V	50W	100°	50,000	120V	Yes	✓ / N.A.
58248	10SMPS5.5DIM/930	3000K	550	90	55	120V	50W	100°	50,000	120V	Yes	✓ / N.A.
58249	10SMPS5.5DIM/940	4000K	560	90	56	120V	50W	100°	50,000	120V	Yes	✓ / N.A.
58244	15SMPS7DIM/927	2700K	850	90	57	120V	75W	100°	50,000	120V	Yes	✓ / N.A.
58245	15SMPS7DIM/930	3000K	850	90	57	120V	75W	100°	50,000	120V	Yes	✓ / N.A.
58246	15SMPS7DIM/940	4000K	870	90	58	120V	75W	100°	50,000	120V	Yes	✓ / N.A.
97975	15SMPS7DIM/927/R	2700K	850	90	57	120V	75W	100°	50,000	120V	Yes	✓ / ✓
97976	15SMPS7DIM/930/R	3000K	850	90	57	120V	75W	100°	50,000	120V	Yes	✓ / ✓
97977	15SMPS7DIM/940/R	4000K	870	90	58	120V	75W	100°	50,000	120V	Yes	✓ / ✓
58252	15SMPS7DIM/930/277V	3000K	870	90	57	0-10V	75W	100°	50,000	120-277V	Yes	✓ / N.A.
58253	15SMPS7DIM/940/277V	4000K	850	90	58	0-10V	75W	100°	50,000	120-277V	Yes	✓ / N.A.
58242	20SMPS9DIM/930	3000K	1200	90	60	120V	100W	100°	50,000	120V	Yes	✓ / N.A.
58243	20SMPS9DIM/940	4000K	1250	90	63	120V	100W	100°	50,000	120V	Yes	✓ / N.A.
58250	20SMPS9DIM/930/277V	3000K	1200	90	60	0-10V	100W	100°	50,000	120-277V	Yes	✓ / N.A.
58251	20SMPS9DIM/940/277V	4000K	1250	90	63	0-10V	100W	100°	50,000	120-277V	Yes	✓ / N.A.



Seamless Installation



CLICK 6" 14.5W & 11W - High CRI




- Innovative CLICK design
- Compatible with 4" J-boxes (standard)
- 4" & 5-6" recessed can accessories sold separately
- Installs in just minutes – No rewiring

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Wet	ES
58101	11SMDL6DIM/927	2700K	680	90	62	120V	65W	110°	40,000	120V	Yes	✓
58102	11SMDL6DIM/930	3000K	720	90	65	120V	65W	110°	40,000	120V	Yes	✓
58103	11SMDL6DIM/940	4000K	750	90	68	120V	65W	110°	40,000	120V	Yes	✓
40842	14.5SMDL6DIM/927	2700K	920	90	63	120V	85W	110°	40,000	120V	Yes	✓
40843	14.5SMDL6DIM/930	3000K	950	90	66	120V	85W	110°	40,000	120V	Yes	✓
40847	14.5SMDL6DIM/840	4000K	1050	82	72	120V	100W	110°	40,000	120V	Yes	✓
57973	SMDL4/ACC	4" Recessed Can Accessories										
57974	SMDL6/ACC	5-6" Recessed Can Accessories										

INSTALLATION GUIDE

4" J-BOX

ACCESSORIES INCLUDED:



- Attach mounting bracket to J-box
- Click downlight into mounting bracket



Mounting Bracket



J-Box Screws




Wire Nuts



LED Adapter

4" CAN

ACCESSORIES SOLD SEPARATELY:



- Connect E26 adapter to the LED adapter
- Insert mounting clips and push downlight up until flush with ceiling



E26 Adapter



LED Adapter




Mounting Bracket



Mounting Clips

5-6" CAN

ACCESSORIES SOLD SEPARATELY:



- Connect E26 adapter to the LED adapter
- Squeeze mounting springs and push downlight up until flush with ceiling



E26 Adapter





LED Adapter




Mounting Springs




Interchangeable lens options (TRACK L & M)



Dimensions




TRACK L & M - High CRI



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES
16340	8TRSG4DIM/827NF30/W/H	2700K	600	82	68	1905	120V	75W	30°	40,000	120V	✓
16346	8TRSG4DIM/830NF30/W/H	3000K	625	82	71	1905	120V	75W	30°	40,000	120V	✓
16341	8TRSG4DIM/827NF30/W/J	2700K	600	82	68	1905	120V	75W	30°	40,000	120V	✓
16347	8TRSG4DIM/830NF30/W/J	3000K	625	82	71	1905	120V	75W	30°	40,000	120V	✓
16343	8TRSG4DIM/827NF30/B/H •	2700K	600	82	68	1905	120V	75W	30°	40,000	120V	✓
16349	8TRSG4DIM/830NF30/B/H •	3000K	625	82	71	1905	120V	75W	30°	40,000	120V	✓
16344	8TRSG4DIM/827NF30/B/J •	2700K	600	82	68	1905	120V	75W	30°	40,000	120V	✓
16350	8TRSG4DIM/830NF30/B/J •	3000K	625	82	71	1905	120V	75W	30°	40,000	120V	✓
97587	22TRMG4DIM/927/W/H	2700K	1200	90	55	6300/3250/12,200	120V	85W	25°/38°/15°	40,000	120V	✓
97599	22TRMG4DIM/930/W/H	3000K	1250	90	57	6700/3450/13,000	120V	85W	25°/38°/15°	40,000	120V	✓
97588	22TRMG4DIM/927/W/J	2700K	1200	90	55	6300/3250/12,200	120V	85W	25°/38°/15°	40,000	120V	✓
97600	22TRMG4DIM/930/W/J	3000K	1250	90	57	6700/3450/13,000	120V	85W	25°/38°/15°	40,000	120V	✓
97590	22TRMG4DIM/927/B/H •	2700K	1200	90	55	6300/3250/12,200	120V	65W	25°/38°/15°	40,000	120V	✓
97602	22TRMG4DIM/930/B/H •	3000K	1250	90	57	6700/3450/13,000	120V	65W	25°/38°/15°	40,000	120V	✓
97591	22TRMG4DIM/927/B/J •	2700K	1200	90	55	6300/3250/12,200	120V	65W	25°/38°/15°	40,000	120V	✓
97603	22TRMG4DIM/930/B/J •	3000K	1250	90	57	6700/3450/13,000	120V	65W	25°/38°/15°	40,000	120V	✓

- Exceptional color rendering CRI 90
- Tight LED binning – 4-step Macadam ellipse
- Sleek design, integrated driver
- NF & FL optics ship with TRL & TRM versions


SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES
97623	33TRLG4DIM/927/W/H	2700K	2200	90	65	10,000/5150	120V	125W	25°/38°	40,000	120V	✓
97629	33TRLG4DIM/930/W/H	3000K	2300	90	68	10,350/5250	120V	125W	25°/38°	40,000	120V	✓
97624	33TRLG4DIM/927/W/J	2700K	2200	90	65	10,000/5150	120V	125W	25°/38°	40,000	120V	✓
97630	33TRLG4DIM/930/W/J	3000K	2300	90	68	10,350/5250	120V	125W	25°/38°	40,000	120V	✓
97626	33TRLG4DIM/927/B/H •	2700K	2200	90	65	10,000/5150	120V	125W	25°/38°	40,000	120V	✓
97632	33TRLG4DIM/930/B/H •	3000K	2300	90	68	10,350/5250	120V	125W	25°/38°	40,000	120V	✓
97627	33TRLG4DIM/927/B/J •	2700K	2200	90	65	10,000/5150	120V	85W	25°/38°	40,000	120V	✓
97633	33TRLG4DIM/930/B/J •	3000K	2300	90	68	10,350/5250	120V	85W	25°/38°	40,000	120V	✓




QWIKLINK Sensor

SPECIFICATIONS										
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Beam Angle	Life (hrs)	Voltage	DLC
28317	22.5STRIPDIM/830/277V	3000K	2500	82	111	0-10V	120°	100,000	120-277V	✓
28318	22.5STRIPDIM/835/277V	3500K	2500	82	111	0-10V	120°	100,000	120-277V	✓
28319	22.5STRIPDIM/840/277V	4000K	2600	82	115	0-10V	120°	100,000	120-277V	✓
28320	22.5STRIPDIM/850/277V	5000K	2600	82	115	0-10V	120°	100,000	120-277V	✓
28321	38.5STRIPDIM/830/277V/R	3000K	5000	82	130	0-10V	120°	100,000	120-277V	✓
28322	38.5STRIPDIM/835/277V/R	3500K	5000	82	130	0-10V	120°	100,000	120-277V	✓
28323	38.5STRIPDIM/840/277V/R	4000K	5050	82	131	0-10V	120°	100,000	120-277V	✓
28324	38.5STRIPDIM/850/277V/R	5000K	5050	82	131	0-10V	120°	100,000	120-277V	✓
STEP DIMMING MODULE 100/50		To order this option add /STEPDIM after the model number ex. 22.5STRIPDIM/840/277V/STEPDIM					To order this and emergency add both: ex. 22.5STRIPDIM/840/277V/STEPDIM/EM			
EMERGENCY DRIVER 10W		To order this option add /EM after the model number ex. 22.5STRIPDIM/840/277V/EM					To order this and step dimming add both: ex. 22.5STRIPDIM/840/277V/STEPDIM/EM			

QWIKLINK Connector



QWIKLINK Cable




- Surface mount, pendant or suspended installation
- LED quick connectors for fast & easy wiring
- 120-277V & 0-10V dimming control compatible
- 100,000-hr lifetime, 10-yr warranty

The QWIKLINK connection system uses the latest in toolless technology to easily and seamlessly connect up to 64’ of fixtures


QWIKLINK Sensor - Single Fixture or Entire Row



Even Distribution & Uplighting




ACCESSORIES		
Product	Model	Description
28388	STPSENSOR	Microwave Sensor QWIKLINK Connection Module 120-277V - Tri-level - Field Adjustable
97881	SENSORRC	Remote Control for STPSENSOR
28384	JBOXPLATE	J-box Cover Plate
97906	STPBACKPLATE	47-13/16"x5-5/16" Plate for Covering Form Factor of Old Fixture
28385	WIRECON20	7-7/8" QWIKLINK Cable
28386	WIRECON150	5' QWIKLINK Cable
28382	STP6CABLE	6' Aircraft Cable with Y-toggle (Set of 2 Cables Suitable for 1 Fixture)
28383	STP10CABLE	10' Aircraft Cable with Y-toggle (Set of 2 Cables Suitable for 1 Fixture)
28387	STPLATE4C	Back Plate for Mechanical Connection Between Suspended Fixtures in a Continuous Run (2 Aircraft Cables Per Fixture)
97885	STPLATE2C	Back Plate for Mechanical Connection Between Suspended Fixtures in a Continuous Run (1 Aircraft Cable Per Fixture)
97860	PC6	6' Power Cord 18/3 (Not Pre-wired to Fixture)
97861	PC12	12' Power Cord 18/3 (Not Pre-wired to Fixture)




- Recessed, surface mount or suspended installation
- Integrated J-box for fast & easy wiring
- 120-277V & 0-10V dimming control compatible
- 75,000-hr lifetime, 10-yr warranty

Edge Lighting Technology




Unified Glare Rating (UGR) <19




- GREEN CREATIVE Panel
UGR <19
- Comfortable light at all viewing angles
 - More useful light
 - No perceptible discomfort
- Standard LED Panel
UGR >23
- Harsh glare at viewing angles >65°
 - More wasted light
 - Perceptible discomfort

SPECIFICATIONS										
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Beam Angle	Life (hrs)	Voltage	DLC
28345	30PAN22DIM/830/277V	3000K	3350	82	112	0-10V	95°	75,000	120-277V	✓
28346	30PAN22DIM/835/277V	3500K	3350	82	112	0-10V	95°	75,000	120-277V	✓
28347	30PAN22DIM/840/277V	4000K	3450	82	115	0-10V	95°	75,000	120-277V	✓
28349	38PAN24DIM/830/277V	3000K	4150	82	109	0-10V	95°	75,000	120-277V	✓
28350	38PAN24DIM/835/277V	3500K	4150	82	109	0-10V	95°	75,000	120-277V	✓
28351	38PAN24DIM/840/277V	4000K	4300	82	113	0-10V	95°	75,000	120-277V	✓
EMERGENCY DRIVER 10W				To order this option add /EM after the model number ex. 38PAN24DIM/840/277V/EM						


ACCESSORIES		
Product	Model	Description
28390	MOUNTFRAME22	2X2' Surface Mount Frame 23-13/16" x 23-13/16" x 2-13/16"
28391	MOUNTFRAME24	2X4' Surface Mount Frame 47-13/16" x 23-13/16" x 2-13/16"
98035	DWFRAME22	2X2' Drywall Frame 25-5/16" x 25-5/16" x 1-1/2"
98036	DWFRAME24	2X4' Drywall Frame 49-5/16" x 23-5/16" x 1-1/2"
28392	SUSPCABLE22	70-7/8" Aircraft Suspension Cable (Set of 4 Cables for 1 2X2' Fixture)
28393	SUSPCABLE24	70-7/8" Aircraft Suspension Cable (Set of 6 Cables for 1 2X4' Fixture)



- High performance lighting distribution
- Exceptional efficacy >140 LPW
- 120-277V & 0-10V dimming control compatible
- 100,000-hr lifetime, 10-yr warranty




Elevate Your Lighting




SPECIFICATIONS										
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Beam Angle	Life (hrs)	Voltage	DLC
28329	25TROF22DIM/830/277V	3000K	3500	82	140	0-10V	120°	50,000	120-277V	✓
28330	25TROF22DIM/835/277V	3500K	3500	82	140	0-10V	120°	50,000	120-277V	✓
28331	25TROF22DIM/840/277V	4000K	3600	82	143	0-10V	120°	50,000	120-277V	✓
97939	26TROF14DIM/835/277V	3500K	3250	82	125	0-10V	120°	50,000	120-277V	✓
97940	26TROF14DIM/840/277V	4000K	3300	82	127	0-10V	120°	50,000	120-277V	✓
28333	30TROF24DIM/830/277V	3000K	4200	82	140	0-10V	120°	50,000	120-277V	✓
28334	30TROF24DIM/835/277V	3500K	4200	82	140	0-10V	120°	50,000	120-277V	✓
28335	30TROF24DIM/840/277V	4000K	4300	82	143	0-10V	120°	50,000	120-277V	✓
STEP DIMMING MODULE 100/50		To order this option add /STEPDIM after the model number ex. 30TROF24DIM/835/277V/STEPDIM			To order this and emergency add both: ex. 30TROF24DIM/835/277V/STEPDIM/EM					
SENSOR		To order this option add /OCCDIM after the model number ex. 30TROF24DIM/835/277V/OCCDIM			To order this and emergency add both: ex. 30TROF24DIM/835/277V/OCCDIM/EM					
EMERGENCY DRIVER 10W		To order this option add /EM after the model number ex. 30TROF24DIM/835/277V/EM			To order this and step dimming or sensor add both: ex. 30TROF24DIM/835/277V/STEPDIM/EM					

ACCESSORIES		
Product	Model	Description
98037	DWFRAME14	1X4' Drywall Frame
98035	DWFRAME22	2X2' Drywall Frame
98036	DWFRAME24	2X4' Drywall Frame



Universally compatible to upgrade 2x2' and 2x4' troffers and louvers while continuing to utilize the existing luminaire housing.


High-Performance Light Distribution



GREEN CREATIVE Retrofit Kit

Other Retrofit Kit


Elevate Your Lighting



SPECIFICATIONS										
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Beam Angle	Life (hrs)	Voltage	DLC
28337	25TROFKIT22DIM/830/277V	3000K	3500	82	140	0-10V	120°	100,000	120-277V	✓
28338	25TROFKIT22DIM/835/277V	3500K	3500	82	140	0-10V	120°	100,000	120-277V	✓
28339	25TROFKIT22DIM/840/277V	4000K	3600	82	144	0-10V	120°	100,000	120-277V	✓
28341	30TROFKIT24DIM/830/277V	3000K	4200	82	140	0-10V	120°	100,000	120-277V	✓
28342	30TROFKIT24DIM/835/277V	3500K	4200	82	140	0-10V	120°	100,000	120-277V	✓
28343	30TROFKIT24DIM/840/277V	4000K	4300	82	144	0-10V	120°	100,000	120-277V	✓
STEP DIMMING MODULE 100/50		To order this option add /STEPDIM after the model number ex. 30TROF24DIM/835/277V/STEPDIM					To order this and emergency add both: ex. 30TROF24DIM/835/277V/STEPDIM/EM			
SENSOR		To order this option add /OCCDIM after the model number ex. 30TROF24DIM/835/277V/OCCDIM					To order this and emergency add both: ex. 30TROF24DIM/835/277V/OCCDIM/EM			
EMERGENCY DRIVER 10W		To order this option add /EM after the model number ex. 30TROF24DIM/835/277V/EM					To order this and step dimming or sensor add both: ex. 30TROF24DIM/835/277V/STEPDIM/EM			

* Remote control available for SENSOR

INSTALLATION GUIDE





GREEN CREATIVE

1200 Bayhill Drive, Suite 220

San Bruno, CA 94066

Tel / Fax: (866) 774-5433

info@greencreative.com

www.greencreative.com



/ GREENCREATIVELED



/ GClightingLED



/ GREEN CREATIVE



GREENCREATIVE