



GREENCREATIVE

 LAMPS



**CATALOG**



GREENCREATIVE

### Your partner for professional lighting solutions

GREEN CREATIVE, founded in 2010, is a major solid-state lighting development and manufacturing company based in the San Francisco Bay area. The company offers a comprehensive line of high-performance LED lighting solutions which has been widely adopted by some of the largest companies in the world.



### Bringing you the latest in LED technology


Anchored by strong integrated R&D capabilities and patented technology, GREEN CREATIVE's innovation, performance and reliability have been recognized year after year by the Illuminating Engineering Society Progress Report, the LEDs Magazine Sapphire Awards, Edison Report, NAILD and more.

### A complete line with national & international distribution

GREEN CREATIVE's full product line of ENERGY STAR®, DLC®, TITLE 20 & JA8 certified indoor retrofit and new construction lighting solutions serves the Retail, Hospitality, Food & Beverage, Office, Education & Industrial sectors through multiple distribution centers and sales networks across the USA.



# TABLE OF CONTENTS



# 2019 FEATURED PRODUCTS




**PAR HO SERIES**

Very high lumen & candela output  
 Exceptional color rendering CRI 92  
 Direct line voltage 120-277V  
 Narrow Flood / Flood beam angles



**MR16 HIGH CRI SERIES**

Suitable for use in totally enclosed fixtures  
 Exceptional color rendering CRI 92  
 Tight LED binning for consistent CCT  
 Spot / Narrow Flood / Flood beam angles



**VALUE SELECT TUBE SERIES**



T5 DIR - 4' HE/HO  
 T8 DIR - 4'  
 Deliver great value through quality performance and price



**EXTERNAL TUBE SERIES**

T8 - 2' / 3' / 4' / Ubent;  
 T5HE - 2' / 3' / 4'  
 T5HO - 4'  
 0-10V dimmable external driver





### SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
58104	8PAR20DIM/927SP15	2700K	535	92	67	5,300	Yes	50W	15°	50,000	120V	Yes	✓
58105	8PAR20DIM/927NF25	2700K	535	92	67	2,700	Yes	50W	25°	50,000	120V	Yes	✓
58106	8PAR20DIM/927FL40	2700K	535	92	67	1,170	Yes	50W	40°	50,000	120V	Yes	✓
58107	8PAR20DIM/930SP15	3000K	550	92	69	5,400	Yes	50W	15°	50,000	120V	Yes	✓
58108	8PAR20DIM/930NF25	3000K	550	92	69	2,800	Yes	50W	25°	50,000	120V	Yes	✓
58109	8PAR20DIM/930FL40	3000K	550	92	69	1,200	Yes	50W	40°	50,000	120V	Yes	✓
58112	8PAR20DIM/940FL40	4000K	570	92	71	1,250	Yes	50W	40°	50,000	120V	Yes	✓
97901	8PAR20DIM/930FL40/B •	3000K	550	92	69	1,200	Yes	50W	40°	50,000	120V	Yes	✓
58113	13PAR30DIM/927SP15	2700K	870	92	67	7,800	Yes	75W	15°	50,000	120V	Yes	✓
58114	13PAR30DIM/927NF25	2700K	1,000	92	77	4,500	Yes	90W	25°	50,000	120V	Yes	✓
58115	13PAR30DIM/927FL40	2700K	1,000	92	77	2,200	Yes	90W	40°	50,000	120V	Yes	✓
58116	13PAR30DIM/930SP15	3000K	880	92	68	8,000	Yes	75W	15°	50,000	120V	Yes	✓
58117	13PAR30DIM/930NF25	3000K	1,050	92	81	4,700	Yes	90W	25°	50,000	120V	Yes	✓
58118	13PAR30DIM/930FL40	3000K	1,050	92	81	2,300	Yes	90W	40°	50,000	120V	Yes	✓
58121	13PAR30DIM/940FL40	4000K	1,100	92	85	2,500	Yes	90W	40°	50,000	120V	Yes	✓
97902	13PAR30DIM/930FL40/B •	3000K	1,050	92	81	2,300	Yes	90W	40°	50,000	120V	Yes	✓
58127	13PAR30/930FL40/277V	3000K	1,050	92	81	2,300	No	90W	40°	50,000	120-277V	Yes	✓
58130	13PAR30/940FL40/277V	4000K	1,100	92	85	2,500	No	90W	40°	50,000	120-277V	Yes	✓


• Black finish

### SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
58140	13PAR30SNDIM/927SP15	2700K	870	92	67	7,800	Yes	75W	15°	50,000	120V	Yes	✓
58141	13PAR30SNDIM/927NF25	2700K	1,000	92	77	4,500	Yes	90W	25°	50,000	120V	Yes	✓
58142	13PAR30SNDIM/927FL40	2700K	1,000	92	77	2,200	Yes	90W	40°	50,000	120V	Yes	✓
58143	13PAR30SNDIM/930SP15	3000K	880	92	68	8,000	Yes	75W	15°	50,000	120V	Yes	✓
58144	13PAR30SNDIM/930NF25	3000K	1,050	92	81	4,700	Yes	90W	25°	50,000	120V	Yes	✓
58145	13PAR30SNDIM/930FL40	3000K	1,050	92	81	2,300	Yes	90W	40°	50,000	120V	Yes	✓
58148	13PAR30SNDIM/940FL40	4000K	1,100	92	85	2,500	Yes	90W	40°	50,000	120V	Yes	✓
97903	13PAR30SNDIM/930FL40/B •	3000K	1,050	92	81	2,300	Yes	90W	40°	50,000	120V	Yes	✓
58149	17PAR38DIM/927SP15	2700K	1,150	92	68	12,200	Yes	120W	15°	50,000	120V	Yes	✓
58150	17PAR38DIM/927NF25	2700K	1,400	92	82	7,300	Yes	120W	25°	50,000	120V	Yes	✓
58151	17PAR38DIM/927FL40	2700K	1,400	92	82	3,100	Yes	120W	40°	50,000	120V	Yes	✓
58152	17PAR38DIM/930SP15	3000K	1,200	92	71	12,500	Yes	120W	15°	50,000	120V	Yes	✓
58153	17PAR38DIM/930NF25	3000K	1,430	92	84	7,500	Yes	120W	25°	50,000	120V	Yes	✓
58154	17PAR38DIM/930FL40	3000K	1,430	92	84	3,200	Yes	120W	40°	50,000	120V	Yes	✓
58157	17PAR38DIM/940FL40	4000K	1,450	92	85	3,300	Yes	120W	40°	50,000	120V	Yes	✓
97904	17PAR38DIM/930NF25/B •	3000K	1,430	92	84	7,500	Yes	120W	25°	50,000	120V	Yes	✓
97905	17PAR38DIM/930FL40/B •	3000K	1,430	92	84	3,200	Yes	120W	40°	50,000	120V	Yes	✓
58172	17PAR38DIM/930FL40/GU24	3000K	1,430	92	84	3,200	Yes	120W	40°	50,000	120V	Yes	✓
58163	17PAR38/930FL40/277V	3000K	1,430	92	84	3,200	No	120W	40°	50,000	120-277V	Yes	✓
58166	17PAR38/940FL40/277V	4000K	1,450	92	85	3,300	No	120W	40°	50,000	120-277V	Yes	✓


• Black finish






- Very high candela output PAR HO to replace 75W/250W halogen
- Exceptional color rendering CRI 92
- Richer reds and natural skin tones (R9 57, R13 91)
- Direct line voltage 120-277V - Not compatible with ballasts

SPECIFICATIONS													
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
98206	19.5PAR30HO/930NF25/277V	3000K	1,700	92	87	8,160	No	75W	25°	50,000	120-277V	No	✓
98207	19.5PAR30HO/930FL40/277V	3000K	1,700	92	87	3,400	No	75W	40°	50,000	120-277V	No	✓
98208	19.5PAR30HO/940NF25/277V	4000K	1,700	92	87	8,160	No	75W	25°	50,000	120-277V	No	✓
98209	19.5PAR30HO/940FL40/277V	4000K	1,700	92	87	3,400	No	75W	40°	50,000	120-277V	No	✓
98223	25PAR38HO/927NF25/277V	2700K	2,400	92	96	10,000	No	250W	25°	50,000	120-277V	No	✓
98210	25PAR38HO/930NF25/277V	3000K	2,500	92	100	10,200	No	250W	25°	50,000	120-277V	No	✓
98211	25PAR38HO/930FL40/277V	3000K	2,500	92	100	4,800	No	250W	40°	50,000	120-277V	No	✓
98212	25PAR38HO/940NF25/277V	4000K	2,500	92	100	10,000	No	250W	25°	40,000	120-277V	No	✓
98213	25PAR38HO/940FL40/277V	4000K	2,500	92	100	4,800	No	250W	40°	40,000	120-277V	No	✓






- Suitable to replace 50W, 75W Halogen MR16 lamps
- Exceptional color rendering CRI 92
- Richer reds and natural skin tones (R9 53, R13 93)
- Suitable for use in totally enclosed fixtures



- Suitable to replace 20W, 35W, 50W, 60W Halogen MR16 lamps
- Compatible with most low-voltage electronic transformers
- Smooth dimming with most electronic low-voltage dimming controls
- Suitable for use in totally enclosed fixtures



SPECIFICATIONS													
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES / JA8 / T20
98151	5.5GU10DIM/927FL35	2700K	450	92	82	800	Yes	50W	35°	25,000	120V	Yes	✓/✓/✓
98152	5.5GU10DIM/930FL35	3000K	470	92	85	850	Yes	50W	35°	25,000	120V	Yes	✓/✓/✓
98153	7MR16DIM/927FL35	2700K	530	92	76	1,350	Yes	50W	35°	25,000	12V	Yes	✓/✓/✓
98154	7MR16DIM/930FL35	3000K	550	92	79	1,400	Yes	50W	35°	25,000	12V	Yes	✓/✓/✓
98155	7MR16DIM/940FL35	4000K	570	92	81	1,450	Yes	50W	35°	25,000	12V	Yes	✓/ N.A. / ✓
98481	7MR16DIM/927SP15	2700K	580	92	83	5,850	Yes	75W	15°	25,000	12V	Yes	✓/✓/✓
98482	7.5MR16DIM/927NF25	2700K	580	92	77	2,800	Yes	75W	25°	25,000	12V	Yes	✓/✓/✓
98483	7.5MR16DIM/927FL35	2700K	580	92	77	1,600	Yes	75W	35°	25,000	12V	Yes	✓/✓/✓
98484	7MR16DIM/930SP15	3000K	580	92	83	5,850	Yes	75W	15°	25,000	12V	Yes	✓/✓/✓
98485	7.5MR16DIM/930NF25	3000K	580	92	77	2,800	Yes	75W	25°	25,000	12V	Yes	✓/✓/✓
98486	7.5MR16DIM/930FL35	3000K	580	92	77	2,800	Yes	75W	35°	25,000	12V	Yes	✓/✓/✓

SPECIFICATIONS														
Product	Model	CCT	Lumens	CRI (typ.)	LPW	CBCP	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES	
40713	3MR11/827NF30	2700K	200	82	67	600	No	20W	30°	25,000	12V	Yes	N.A.	
40715	3MR11/840NF30	4000K	220	82	73	620	No	20W	30°	25,000	12V	Yes	N.A.	
58285	6MR16DIM/827FL35/35W/R	2700K	425	82	71	910	Yes	35W	35°	25,000	120V	Yes	✓	
58286	6MR16DIM/830FL35/35W/R	3000K	450	82	75	910	Yes	35W	35°	25,000	120V	Yes	✓	
57984	6MR16DIM/827FL35/R	2700K	480	82	80	1,350	Yes	50W	35°	25,000	12V	Yes	✓	
57985	6MR16DIM/830FL35/R	3000K	500	82	83	1,400	Yes	50W	35°	25,000	12V	Yes	✓	
57986	6MR16DIM/840FL35/R	4000K	520	82	86	1,450	Yes	50W	35°	25,000	12V	Yes	✓	
57987	6GU10DIM/827FL35/R	2700K	480	82	80	1,000	Yes	50W	35°	25,000	120V	Yes	✓	
57988	6GU10DIM/830FL35/R	3000K	500	82	83	1,050	Yes	50W	35°	25,000	120V	Yes	✓	
57990	6PAR16DIM/827FL35/R	2700K	480	82	80	1,000	Yes	60W	35°	25,000	120V	Yes	✓	
57991	6PAR16DIM/830FL35/R	3000K	500	82	83	1,050	Yes	60W	35°	25,000	120V	Yes	✓	


# T8 DIR LINE




DIRect



Compatible with Electronic Ballasts - Dimmable



Extra Wide Beam Design - End-to-End Lighting



- Easy to install – Plug & play direct
- Instant Start & Programmed Start ballast compatible
- 0-10V dimming ballast compatible
- Meets NSF requirements (use of a shatter guard required)

## SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
97841	8T8/2F/830/DIR/R	3000K	1,300	82	163	Yes	17W	160°	50,000	120-277V	Yes	✓
97842	8T8/2F/835/DIR/R	3500K	1,300	82	163	Yes	17W	160°	50,000	120-277V	Yes	✓
97843	8T8/2F/840/DIR/R	4000K	1,300	82	163	Yes	17W	160°	50,000	120-277V	Yes	✓
98352	8T8/3F/830/DIR/R	3000K	1,200	82	150	Yes	25W	160°	50,000	120-277V	Yes	✓
98353	8T8/3F/835/DIR/R	3500K	1,200	82	150	Yes	25W	160°	50,000	120-277V	Yes	✓
98354	8T8/3F/840/DIR/R	4000K	1,250	82	156	Yes	25W	160°	50,000	120-277V	Yes	✓
28397	10.5T8/4F/830/DIR/RC	3000K	1,650	82	157	Yes	32W	160°	50,000	120-277V	Yes	✓
28398	10.5T8/4F/835/DIR/RC	3500K	1,650	82	157	Yes	32W	160°	50,000	120-277V	Yes	✓
28399	10.5T8/4F/840/DIR/RC	4000K	1,700	82	162	Yes	32W	160°	50,000	120-277V	Yes	✓
28400	10.5T8/4F/850/DIR/RC	5000K	1,700	82	162	Yes	32W	160°	50,000	120-277V	Yes	✓
28403	13T8/4F/840/DIR/R	4000K	2,050	82	158	Yes	32W	160°	50,000	120-277V	Yes	✓
28404	13T8/4F/850/DIR/R	5000K	2,050	82	158	Yes	32W	160°	50,000	120-277V	Yes	✓
97958	16T8U6/830/DIR	3000K	2,200	82	138	Yes	32W	140°	50,000	120-277V	Yes	✓
97959	16T8U6/840/DIR	4000K	2,200	82	138	Yes	32W	140°	50,000	120-277V	Yes	✓
97960	16T8U6/850/DIR	5000K	2,250	82	141	Yes	32W	140°	50,000	120-277V	Yes	✓


# T5 DIR LINE



DIRect



Compatible with Electronic Ballasts - Dimmable



- Easy to install – Plug & play direct
- Instant Start & Programmed Start ballast compatible
- Plastic construction meets NSF requirements
- 0-10V dimming ballast compatible


## SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
57958	8T5HE/2F/830/DIR	3000K	950	82	119	Yes	14W	120°	50,000	120-277V	Yes	N.A.
57959	8T5HE/2F/835/DIR	3500K	950	82	119	Yes	14W	120°	50,000	120-277V	Yes	N.A.
57960	8T5HE/2F/840/DIR	4000K	1,020	82	128	Yes	14W	120°	50,000	120-277V	Yes	N.A.
57954	12T5HE/3F/830/DIR	3000K	1,420	82	118	Yes	21W	120°	50,000	120-277V	Yes	N.A.
57955	12T5HE/3F/835/DIR	3500K	1,420	82	118	Yes	21W	120°	50,000	120-277V	Yes	N.A.
57956	12T5HE/3F/840/DIR	4000K	1,500	82	125	Yes	21W	120°	50,000	120-277V	Yes	N.A.
97929	15T5HE/4F/830/DIR/R	3000K	2,200	82	147	Yes	28W	120°	50,000	120-277V	Yes	✓
97930	15T5HE/4F/835/DIR/R	3500K	2,200	82	147	Yes	28W	120°	50,000	120-277V	Yes	✓
97931	15T5HE/4F/840/DIR/R	4000K	2,250	82	150	Yes	28W	120°	50,000	120-277V	Yes	✓
97932	15T5HE/4F/850/DIR/R	5000K	2,250	82	150	Yes	28W	120°	50,000	120-277V	Yes	✓
98165	10.5T5HO/2F/830/DIR	3000K	1,500	82	143	Yes	24W	120°	50,000	120-277V	Yes	N.A.
98166	10.5T5HO/2F/835/DIR	3500K	1,500	82	143	Yes	24W	120°	50,000	120-277V	Yes	N.A.
98167	10.5T5HO/2F/840/DIR	4000K	1,600	82	152	Yes	24W	120°	50,000	120-277V	Yes	N.A.
98168	14.5T5HO/3F/830/DIR	3000K	2,050	82	142	Yes	39W	120°	50,000	120-277V	Yes	N.A.
98169	14.5T5HO/3F/835/DIR	3500K	2,050	82	142	Yes	39W	120°	50,000	120-277V	Yes	N.A.
98170	14.5T5HO/3F/840/DIR	4000K	2,200	82	152	Yes	39W	120°	50,000	120-277V	Yes	N.A.
97924	24T5HO/4F/830/DIR/R	3000K	3,450	82	144	Yes	54W	120°	50,000	120-277V	Yes	✓
97925	24T5HO/4F/835/DIR/R	3500K	3,450	82	144	Yes	54W	120°	50,000	120-277V	Yes	✓
97926	24T5HO/4F/840/DIR/R	4000K	3,500	82	146	Yes	54W	120°	50,000	120-277V	Yes	✓
97927	24T5HO/4F/850/DIR/R	5000K	3,500	82	146	Yes	54W	120°	50,000	120-277V	Yes	✓



# T8 DIR VALUE SELECT LINE

# T5 DIR VALUE SELECT LINE



- Easy to install – Plug & play direct
- Instant Start ballast compatible
- Meets NSF Requirements (use of a shatter guard required)

- Easy to install – Plug & play direct
- Instant Start & Programmed Start ballast compatible
- Glass construction
- 0-10V dimming ballast compatible

## SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98551	10.5T8/4F/830/IS/DIR	3000K	1,600	82	152	No	32W	160°	50,000	120-277V	Yes	✓
98552	10.5T8/4F/835/IS/DIR	3500K	1,600	82	152	No	32W	160°	50,000	120-277V	Yes	✓
98553	10.5T8/4F/840/IS/DIR	4000K	1,650	82	157	No	32W	160°	50,000	120-277V	Yes	✓
98554	10.5T8/4F/850/IS/DIR	5000K	1,650	82	157	No	32W	160°	50,000	120-277V	Yes	✓
98557	13T8/4F/840/IS/DIR	4000K	2,000	82	154	No	32W	160°	50,000	120-277V	Yes	✓
98558	13T8/4F/850/IS/DIR	5000K	2,000	82	154	No	32W	160°	50,000	120-277V	Yes	✓

## SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98490	15T5HE/4F/830/GL/DIR	3000K	2,200	82	142	Yes	28W	120°	50,000	120-277V	Yes	✓
98491	15T5HE/4F/835/GL/DIR	3500K	2,200	82	142	Yes	28W	120°	50,000	120-277V	Yes	✓
98492	15T5HE/4F/840/GL/DIR	4000K	2,250	82	152	Yes	28W	120°	50,000	120-277V	Yes	✓
98494	24T5HO/4F/830/GL/DIR	3000K	3,450	82	144	Yes	54W	120°	50,000	120-277V	Yes	✓
98495	24T5HO/4F/835/GL/DIR	3500K	3,450	82	144	Yes	54W	120°	50,000	120-277V	Yes	✓
98496	24T5HO/4F/840/GL/DIR	4000K	3,500	82	146	Yes	54W	120°	50,000	120-277V	Yes	✓
98497	24T5HO/4F/850/GL/DIR	5000K	3,500	82	146	Yes	54W	120°	50,000	120-277V	Yes	✓




BYPass



BYPass




FLICKER FREE



- Integral driver suitable for 120-277V
- Compatible with non-shunted lamp holders only
- Extra high efficacy series up to 167LPW available
- Meets NSF requirements (use of a shatter guard required)

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
28413	8T8/2F/830/BYP/R	3000K	1,000	82	125	No	17W	160°	50,000	120-277V	Yes	✓
28414	8T8/2F/835/BYP/R	3500K	1,050	82	131	No	17W	160°	50,000	120-277V	Yes	✓
28415	8T8/2F/840/BYP/R	4000K	1,050	82	131	No	17W	160°	50,000	120-277V	Yes	✓
97893	12T8/3F/830/BYP/R	3000K	1,500	82	125	No	25W	160°	50,000	120-277V	Yes	✓
97894	12T8/3F/835/BYP/R	3500K	1,500	82	125	No	25W	160°	50,000	120-277V	Yes	✓
97895	12T8/3F/840/BYP/R	4000K	1,550	82	129	No	25W	160°	50,000	120-277V	Yes	✓
28405	13T8/4F/830/BYP/R	3000K	1,650	82	123	No	32W	160°	50,000	120-277V	Yes	✓
28406	13T8/4F/835/BYP/R	3500K	1,650	82	127	No	32W	160°	50,000	120-277V	Yes	✓
28407	13T8/4F/840/BYP/R	4000K	1,700	82	131	No	32W	160°	50,000	120-277V	Yes	✓
28408	13T8/4F/850/BYP/R	5000K	1,700	82	131	No	32W	160°	50,000	120-277V	Yes	✓
28411	16T8/4F/840/BYP/R	4000K	2,050	82	128	No	32W	160°	50,000	120-277V	Yes	✓
28412	16T8/4F/850/BYP/R	5000K	2,050	82	128	No	32W	160°	50,000	120-277V	Yes	✓
98379	10.5T8/4F/830/BYP	3000K	1,650	82	157	No	32W	160°	50,000	120-277V	Yes	✓
98380	10.5T8/4F/835/BYP	3500K	1,650	82	157	No	32W	160°	50,000	120-277V	Yes	✓
98381	10.5T8/4F/840/BYP	4000K	1,750	82	167	No	32W	160°	50,000	120-277V	Yes	✓
98382	10.5T8/4F/850/BYP	5000K	1,750	82	167	No	32W	160°	50,000	120-277V	Yes	✓
98473	14.5T8/4F/840/BYP	4000K	2,200	82	152	No	32W	160°	50,000	120-277V	Yes	✓
98474	14.5T8/4F/850/BYP	5000K	2,200	82	152	No	32W	160°	50,000	120-277V	Yes	✓
98162	17T8U6/830/BYP	3000K	2,100	82	124	No	32W	140°	50,000	120-277V	Yes	✓
98163	17T8U6/840/BYP	4000K	2,300	82	135	No	32W	140°	50,000	120-277V	Yes	✓
98164	17T8U6/850/BYP	5000K	2,300	82	135	No	32W	140°	50,000	120-277V	Yes	✓
57840	17.5T8/4F/GOLD/BYP	N.A.	1,100	82	63	No	32W	160°	50,000	120-277V	Yes	N.A.





- Integral driver suitable for 120-277V
- Flicker Free light output
- Suitable for use in totally enclosed fixtures
- Meets NSF requirements (use of a shatter guard required)



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98191	8T8/2F/830/BYP/FF	3000K	1,000	82	125	No	17W	160°	50,000	120-277V	Yes	✓
98192	8T8/2F/835/BYP/FF	3500K	1,050	82	131	No	17W	160°	50,000	120-277V	Yes	✓
98193	8T8/2F/840/BYP/FF	4000K	1,050	82	131	No	17W	160°	50,000	120-277V	Yes	✓
98194	12T8/3F/830/BYP/FF	3000K	1,500	82	125	No	25W	160°	50,000	120-277V	Yes	✓
98195	12T8/3F/835/BYP/FF	3500K	1,500	82	125	No	25W	160°	50,000	120-277V	Yes	✓
98196	12T8/3F/840/BYP/FF	4000K	1,550	82	129	No	25W	160°	50,000	120-277V	Yes	✓
98197	13T8/4F/830/BYP/FF	3000K	1,600	82	123	No	32W	160°	50,000	120-277V	Yes	✓
98198	13T8/4F/835/BYP/FF	3500K	1,650	82	127	No	32W	160°	50,000	120-277V	Yes	✓
98199	13T8/4F/840/BYP/FF	4000K	1,700	82	131	No	32W	160°	50,000	120-277V	Yes	✓
98200	13T8/4F/850/BYP/FF	5000K	1,700	82	131	No	32W	160°	50,000	120-277V	Yes	✓
98201	16T8/4F/840/BYP/FF	4000K	2,050	82	128	No	32W	160°	50,000	120-277V	Yes	✓
98202	16T8/4F/850/BYP/FF	5000K	2,050	82	128	No	32W	160°	50,000	120-277V	Yes	✓

# T8 BYP LINE - DIMMABLE

# T5 BYP LINE



- Integral driver suitable for 120V
- Replaces 32W T8 Fluorescent lamps
- High efficacy up to 138 LPW
- Compatible with most phase dimmers

- Integral driver suitable for 120-277V
- Wide beam design 270° light emitting area
- Suitable for use in totally enclosed fixtures
- Plastic construction meets NSF requirements



## SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98372	13T8/4F/DIM/830/BYP	3000K	1,700	82	128	Yes	32W	160°	50,000	120V	Yes	✓
98373	13T8/4F/DIM/835/BYP	3500K	1,700	82	128	Yes	32W	160°	50,000	120V	Yes	✓
98374	13T8/4F/DIM/840/BYP	4000K	1,800	82	138	Yes	32W	160°	50,000	120V	Yes	✓
98375	13T8/4F/DIM/850/BYP	5000K	1,800	82	138	Yes	32W	160°	50,000	120V	Yes	✓

## SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98287	9.5T5HE/2F/830/BYP	3000K	1,100	82	116	No	14W	120°	50,000	120-277V	Yes	N.A.
98288	9.5T5HE/2F/835/BYP	3500K	1,150	82	121	No	14W	120°	50,000	120-277V	Yes	N.A.
98289	9.5T5HE/2F/840/BYP	4000K	1,200	82	126	No	14W	120°	50,000	120-277V	Yes	N.A.
98290	12T5HE/3F/830/BYP	3000K	1,350	82	113	No	21W	120°	50,000	120-277V	Yes	N.A.
98291	12T5HE/3F/835/BYP	3500K	1,400	82	117	No	21W	120°	50,000	120-277V	Yes	N.A.
98292	12T5HE/3F/840/BYP	4000K	1,500	82	125	No	21W	120°	50,000	120-277V	Yes	N.A.
98293	14.5T5HE/4F/830/BYP	3000K	1,750	82	121	No	28W	120°	50,000	120-277V	Yes	✓
98294	14.5T5HE/4F/835/BYP	3500K	1,800	82	124	No	28W	120°	50,000	120-277V	Yes	✓
98295	14.5T5HE/4F/840/BYP	4000K	2,000	82	138	No	28W	120°	50,000	120-277V	Yes	✓
98296	11.5T5HO/2F/830/BYP	3000K	1,350	82	117	No	24W	120°	50,000	120-277V	Yes	N.A.
98297	11.5T5HO/2F/835/BYP	3500K	1,400	82	122	No	24W	120°	50,000	120-277V	Yes	N.A.
98298	11.5T5HO/2F/840/BYP	4000K	1,500	82	130	No	24W	120°	50,000	120-277V	Yes	N.A.
98299	14.5T5HO/3F/830/BYP	3000K	1,800	82	124	No	39W	120°	50,000	120-277V	Yes	N.A.
98300	14.5T5HO/3F/835/BYP	3500K	1,850	82	128	No	39W	120°	50,000	120-277V	Yes	N.A.
98301	14.5T5HO/3F/840/BYP	4000K	1,900	82	131	No	39W	120°	50,000	120-277V	Yes	N.A.
98302	25T5HO/4F/830/BYP	3000K	3,200	82	128	No	54W	120°	50,000	120-277V	Yes	✓
98303	25T5HO/4F/835/BYP	3500K	3,200	82	128	No	54W	120°	50,000	120-277V	Yes	✓
98304	25T5HO/4F/840/BYP	4000K	3,200	82	128	No	54W	120°	50,000	120-277V	Yes	✓
98305	25T5HO/4F/850/BYP	5000K	3,200	82	128	No	54W	120°	50,000	120-277V	Yes	✓







BYPass



BYPass



- Double-ended bypass installation – Wired at both ends
- Utilizes existing lampholders – Non-shunted or shunted
- Extra high efficacy series up to 148LPW available
- Meets NSF requirements (use of a shatter guard required)



R17d



Fa8

- Integral driver suitable for 120-277V
- Replaces 8ft F96T8/F96T12 Fluorescent lamps
- Available in Single pin & Recessed Double Contact pin
- Double ended installation, no need to change existing sockets

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
97934	8.5T8/2F/830/DEB/RC	3000K	1,050	82	124	No	17W	160°	50,000	120-277V	Yes	✓
97935	8.5T8/2F/835/DEB/RC	3500K	1,050	82	124	No	17W	160°	50,000	120-277V	Yes	✓
97936	8.5T8/2F/840/DEB/RC	4000K	1,100	82	129	No	17W	160°	50,000	120-277V	Yes	✓
98340	12T8/3F/830/DEB/R	3000K	1,400	82	117	No	25W	160°	50,000	120-277V	Yes	✓
98341	12T8/3F/835/DEB/R	3500K	1,400	82	117	No	25W	160°	50,000	120-277V	Yes	✓
98342	12T8/3F/840/DEB/R	4000K	1,450	82	121	No	25W	160°	50,000	120-277V	Yes	✓
98435	14T8/4F/830/DEB	3000K	1,700	82	121	No	25W	160°	50,000	120-277V	Yes	✓
98436	14T8/4F/835/DEB	3500K	1,700	82	124	No	32W	160°	50,000	120-277V	Yes	✓
98437	14T8/4F/840/DEB	4000K	1,800	82	129	No	32W	160°	50,000	120-277V	Yes	✓
98438	14T8/4F/850/DEB	5000K	1,800	82	129	No	32W	160°	50,000	120-277V	Yes	✓
98433	17T8/4F/840/DEB	4000K	2,200	82	117	No	25W	160°	50,000	120-277V	Yes	✓
98434	17T8/4F/850/DEB	5000K	2,200	82	117	No	25W	160°	50,000	120-277V	Yes	✓
58272	11.5T8/4F/830/DEB/RC	3000K	1,650	82	143	No	32W	160°	50,000	120-277V	Yes	✓
58273	11.5T8/4F/835/DEB/RC	3500K	1,650	82	143	No	32W	160°	50,000	120-277V	Yes	✓
58274	11.5T8/4F/840/DEB/RC	4000K	1,700	82	148	No	32W	160°	50,000	120-277V	Yes	✓
58275	11.5T8/4F/850/DEB/RC	5000K	1,700	82	148	No	32W	160°	50,000	120-277V	Yes	✓
58270	14.5T8/4F/840/DEB/RC	4000K	2,100	82	145	No	32W	160°	50,000	120-277V	Yes	✓
58271	14.5T8/4F/850/DEB/RC	5000K	2,100	82	145	No	32W	160°	50,000	120-277V	Yes	✓

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
34869	43T8/8F/840/DEB/Fa8	4000K	5,500	82	128	No	F96T8 F96T12	160°	50,000	120-277V	Yes	✓
34870	43T8/8F/850/DEB/Fa8	5000K	5,500	82	128	No	F96T8 F96T12	160°	50,000	120-277V	Yes	✓
34871	43T8/8F/840/DEB/R17d	4000K	5,500	82	128	No	F96T8 F96T12	160°	50,000	120-277V	Yes	N.A.
34872	43T8/8F/850/DEB/R17d	5000K	5,500	82	128	No	F96T8 F96T12	160°	50,000	120-277V	Yes	N.A.

# T8 EXT LINE




EXTERNAL Driver




# T5 EXT LINE




EXTERNAL Driver



- Compatible with external drivers only
- Dimmable
- Utilizes existing lamp holders – shunted or non-shunted
- Meets NSF requirements (use of a shatter guard required)





SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98325	9.5T8/2F/830/EXT	3000K	1,350	82	142	Yes	17W	160°	50,000	120-277V	Yes	✓
98326	9.5T8/2F/835/EXT	3500K	1,400	82	147	Yes	17W	160°	50,000	120-277V	Yes	✓
98327	9.5T8/2F/840/EXT	4000K	1,500	82	158	Yes	17W	160°	50,000	120-277V	Yes	✓
98328	10.5T8/3F/830/EXT	3000K	1,450	82	138	Yes	25W	160°	50,000	120-277V	Yes	✓
98329	10.5T8/3F/835/EXT	3500K	1,500	82	143	Yes	25W	160°	50,000	120-277V	Yes	✓
98330	10.5T8/3F/840/EXT	4000K	1,600	82	152	Yes	25W	160°	50,000	120-277V	Yes	✓
98331	11.5T8/4F/830/EXT	3000K	1,600	82	139	Yes	32W	160°	50,000	120-277V	Yes	✓
98332	11.5T8/4F/835/EXT	3500K	1,650	82	143	Yes	32W	160°	50,000	120-277V	Yes	✓
98333	11.5T8/4F/840/EXT	4000K	1,700	82	148	Yes	32W	160°	50,000	120-277V	Yes	✓
98334	11.5T8/4F/850/EXT	5000K	1,700	82	148	Yes	32W	160°	50,000	120-277V	Yes	✓
98335	14T8/4F/840/EXT	4000K	2,050	82	146	Yes	32W	160°	50,000	120-277V	Yes	✓
98336	14T8/4F/850/EXT	5000K	2,050	82	146	Yes	32W	160°	50,000	120-277V	Yes	✓
98337	14.5T8U6/830/EXT	3000K	2,000	82	138	Yes	32W	140°	50,000	120-277V	Yes	✓
98338	14.5T8U6/840/EXT	4000K	2,200	82	152	Yes	32W	140°	50,000	120-277V	Yes	✓
98339	14.5T8U6/850/EXT	5000K	2,200	82	152	Yes	32W	140°	50,000	120-277V	Yes	✓
98259	15T8T5HEDRIVER/2CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 1-2 T8/T5 HE Lamps										
98260	15T8T5HEDRIVER/4CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 3-4 T8/T5 HE Lamps										



- Compatible with external drivers only
- Dimmable
- Utilizes existing lamp holders – shunted or non-shunted
- Plastic construction meets NSF requirements

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98306	9.5T5HE/2F/830/EXT	3000K	1,350	82	142	Yes	14W	120°	50,000	120-277V	Yes	N.A.
98307	9.5T5HE/2F/835/EXT	3500K	1,400	82	147	Yes	14W	120°	50,000	120-277V	Yes	N.A.
98308	9.5T5HE/2F/840/EXT	4000K	1,500	82	158	Yes	14W	120°	50,000	120-277V	Yes	N.A.
98309	11T5HE/3F/830/EXT	3000K	1,500	82	136	Yes	21W	120°	50,000	120-277V	Yes	N.A.
98310	11T5HE/3F/835/EXT	3500K	1,550	82	141	Yes	21W	120°	50,000	120-277V	Yes	N.A.
98311	11T5HE/3F/840/EXT	4000K	1,600	82	150	Yes	21W	120°	50,000	120-277V	Yes	N.A.
98312	13.5T5HE/4F/830/EXT	3000K	1,800	82	133	Yes	28W	120°	50,000	120-277V	Yes	✓
98313	13.5T5HE/4F/835/EXT	3500K	1,850	82	137	Yes	28W	120°	50,000	120-277V	Yes	✓
98314	13.5T5HE/4F/840/EXT	4000K	2,000	82	148	Yes	28W	120°	50,000	120-277V	Yes	✓
98321	22T5HO/4F/830/EXT	3000K	3,200	82	145	Yes	54W	120°	50,000	120-277V	Yes	✓
98322	22T5HO/4F/835/EXT	3500K	3,200	82	145	Yes	54W	120°	50,000	120-277V	Yes	✓
98323	22T5HO/4F/840/EXT	4000K	3,400	82	155	Yes	54W	120°	50,000	120-277V	Yes	✓
98324	22T5HO/4F/850/EXT	5000K	3,400	82	155	Yes	54W	120°	50,000	120-277V	Yes	✓
98259	15T8T5HEDRIVER/2CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 1-2 T8/T5 HE Lamps										
98260	15T8T5HEDRIVER/4CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 3-4 T8/T5 HE Lamps										
98261	24T5HODRIVER/2CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 1-2 T5 HO Lamps										
98262	24T5HODRIVER/4CH/R	120-277V with 0-10V Dimming External LED Driver for Use with 3-4 T5 HO Lamps										




### Compatible with Electronic Ballasts



- Easy to install – Plug & play direct
- Instant Start & Programmed Start ballast compatible
- Plastic film prevents glass from shattering
- Installs into 2G11 sockets with existing ballast

- Integral driver suitable for 120-277V
- Replaces 18W / 24W / 36W / 40W 4-pin (2G11) CFL lamps
- High efficacy up to 138 LPW
- 16W / 17W models suitable for use in enclosed fixture

### BYPass Installation



### SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98477	13PLL/830/GL/DIR	3000K	2,050	82	158	No	40W	160°	50,000	120-277V	Yes	✓
98478	13PLL/835/GL/DIR	3500K	2,100	82	162	No	40W	160°	50,000	120-277V	Yes	✓
98479	13PLL/840/GL/DIR	4000K	2,100	82	162	No	40W	160°	50,000	120-277V	Yes	✓
98488	14.5PLL/835/GL/DIR	3500K	1,950	82	134	No	36W	160°	50,000	120-277V	Yes	N.A.
98489	14.5PLL/840/GL/DIR	4000K	2,000	82	138	No	36W	160°	50,000	120-277V	Yes	N.A.

### SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
34858	8.5PLL/835/GL/BYP	3500K	950	82	112	No	18W	160°	50,000	120-277V	No	N.A.
34859	8.5PLL/840/GL/BYP	4000K	980	82	115	No	18W	160°	50,000	120-277V	No	N.A.
34861	10PLL/835/GL/BYP	3500K	1,200	82	120	No	24W	160°	50,000	120-277V	No	N.A.
34862	10PLL/840/GL/BYP	4000K	1,250	82	125	No	24W	160°	50,000	120-277V	No	N.A.
34864	16PLL/835/GL/BYP	3500K	1,950	82	122	No	36W	160°	50,000	120-277V	Yes	N.A.
34865	16PLL/840/GL/BYP	4000K	2,000	82	125	No	36W	160°	50,000	120-277V	Yes	N.A.
34866	17PLL/830/GL/BYP	3000K	2,050	82	121	No	40W	160°	50,000	120-277V	Yes	July
34867	17PLL/835/GL/BYP	3500K	2,150	82	126	No	40W	160°	50,000	120-277V	Yes	July
34868	17PLL/840/GL/BYP	4000K	2,200	82	129	No	40W	160°	50,000	120-277V	Yes	July






High Flexibility - Ballast Adaptive Technology		
Ballast Type	Lumens	Bare Lamp
13W	600	4.5W
18W	700	5.5W
26W	1020	8.5W

**PL H 8.5W DIR**

- Plug & play direct – Electronic ballast compatible
- Compatible with G24q & GX24q installations
- 310° rotatable base to maximize lamp performance in fixture
- 0-10V dimming ballast compatible
- Ballast Adaptive Technology allows one LED lamp to be powered by a range of fluorescent ballasts instead of restricting to one wattage rating




SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
57895	5.5PLH/827/DIR/RC	2700K	520	82	95	Yes	13-18W	110°	50,000	120-277V	No	N.A.
57896	5.5PLH/830/DIR/RC	3000K	550	82	100	Yes	13-18W	110°	50,000	120-277V	No	N.A.
57897	5.5PLH/835/DIR/RC	3500K	550	82	100	Yes	13-18W	110°	50,000	120-277V	No	N.A.
57898	5.5PLH/840/DIR/RC	4000K	560	82	102	Yes	13-18W	110°	50,000	120-277V	No	N.A.
28366	8.5PLH/827/DIR/R	2700K	870	82	102	Yes	26W	110°	50,000	120-277V	No	✓
28367	8.5PLH/830/DIR/R	3000K	950	82	112	Yes	26W	110°	50,000	120-277V	No	✓
28368	8.5PLH/835/DIR/R	3500K	950	82	112	Yes	26W	110°	50,000	120-277V	No	✓
28369	8.5PLH/840/DIR/R	4000K	1,020	82	120	Yes	26W	110°	50,000	120-277V	No	✓
57903	10.5PLH/930/DIR	3000K	890	92	85	Yes	26W	110°	50,000	120-277V	No	N.A.
98244	14.5PLH/830/DIR	3000K	1,700	82	117	Yes	42W	110°	50,000	120-277V	No	N.A.
98245	14.5PLH/835/DIR	3500K	1,750	82	121	Yes	42W	110°	50,000	120-277V	No	N.A.
98246	14.5PLH/840/DIR	4000K	1,800	82	124	Yes	42W	110°	50,000	120-277V	No	N.A.



High Flexibility - Ballast Adaptive Technology		
Ballast Type	Lumens	Bare Lamp
13W	590	5W
18W	820	6W
26W	1020	9.5W

**PL V 9.5W DIR**

- Plug & play direct – Electronic ballast compatible
- Compatible with G24q & GX24q installations
- Patented design
- 0-10V dimming ballast compatible
- Ballast Adaptive Technology allows one LED lamp to be powered by a range of fluorescent ballasts instead of restricting to one wattage rating



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
28370	6PLV/827/DIR/R	2700K	600	82	100	Yes	13-18W	120°	50,000	120-277V	No	N.A.
28371	6PLV/830/DIR/R	3000K	620	82	103	Yes	13-18W	120°	50,000	120-277V	No	N.A.
28372	6PLV/835/DIR/R	3500K	620	82	103	Yes	13-18W	120°	50,000	120-277V	No	N.A.
28373	6PLV/840/DIR/R	4000K	640	82	107	Yes	13-18W	120°	50,000	120-277V	No	N.A.
28374	9.5PLV/827/DIR/R	2700K	950	82	100	Yes	26W	120°	50,000	120-277V	No	✓
28375	9.5PLV/830/DIR/RC	3000K	1,000	82	105	Yes	26W	120°	50,000	120-277V	No	✓
28376	9.5PLV/835/DIR/RC	3500K	1,000	82	105	Yes	26W	120°	50,000	120-277V	No	✓
28377	9.5PLV/840/DIR/RC	4000K	1,020	82	107	Yes	26W	120°	50,000	120-277V	No	✓
57918	11PLV/930/DIR	3000K	920	92	84	Yes	26W	120°	50,000	120-277V	No	N.A.
98248	17PLV/830/DIR	3000K	1,900	82	112	Yes	42W	110°	50,000	120-277V	No	✓
98249	17PLV/835/DIR	3500K	1,950	82	115	Yes	42W	110°	50,000	120-277V	No	✓
98250	17PLV/840/DIR	4000K	2,000	82	118	Yes	42W	110°	50,000	120-277V	No	✓




**Hybrid Installation**

**MAGNETIC**  
BALLAST  
COMPATIBLE

**120-  
277V**  
UNIVERSAL

**Note PL H 15.5W BYP is not compatible with magnetic ballasts**

- **HYBRid installation - DIRect or BYPass**
- **Compatible with magnetic ballasts - DIRect installation**
- **Built-in universal voltage driver - BYPass installation**
- **310° rotatable base to maximize lamp performance in fixture**
- **E26 & GU24 versions available**



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98391	5.5PLH/835/HYBM	3500K	550	82	100	Yes	13-18W	110°	50,000	120-277V	No	N.A.
98392	5.5PLH/840/HYBM	4000K	560	82	102	Yes	13-18W	110°	50,000	120-277V	No	N.A.
98393	5.5PLH/830/BYP/E26	3000K	550	82	100	Yes	13W	110°	50,000	120-277V	No	N.A.
98394	5.5PLH/835/BYP/E26	3500K	550	82	100	Yes	13W	110°	50,000	120-277V	No	N.A.
98395	5.5PLH/840/BYP/E26	4000K	560	82	102	Yes	13W	110°	50,000	120-277V	No	N.A.
98396	5.5PLH/830/BYP/GU24	3000K	550	82	100	Yes	13W	110°	50,000	120-277V	No	N.A.
98397	5.5PLH/835/BYP/GU24	3500K	550	82	100	Yes	13W	110°	50,000	120-277V	No	N.A.
98398	5.5PLH/840/BYP/GU24	4000K	560	82	102	Yes	13W	110°	50,000	120-277V	No	N.A.
98399	8PLH/827/HYBM	2700K	870	82	108	Yes	26W	110°	50,000	120-277V	No	N.A.
98400	8PLH/830/HYBM	3000K	920	82	115	Yes	26W	110°	50,000	120-277V	No	N.A.
98401	8PLH/835/HYBM	3500K	920	82	115	Yes	26W	110°	50,000	120-277V	No	N.A.
98402	8PLH/840/HYBM	4000K	950	82	119	Yes	26W	110°	50,000	120-277V	No	N.A.
98252	15.5PLH/830/BYP	3000K	1,700	82	110	Yes	42W	110°	50,000	120-277V	No	N.A.
98253	15.5PLH/835/BYP	3500K	1,750	82	113	Yes	42W	110°	50,000	120-277V	No	N.A.
98254	15.5PLH/840/BYP	4000K	1,800	82	116	Yes	42W	110°	50,000	120-277V	No	N.A.

\* Note PL H 15.5W BYP operates on line voltage only and is not compatible with magnetic ballasts




**Hybrid Installation**

**MAGNETIC**  
BALLAST  
COMPATIBLE

**120-  
277V**  
UNIVERSAL



**Note PL V 16.5W BYP is not compatible with magnetic ballasts**

- **HYBRid installation - DIRect or BYPass**
- **Compatible with magnetic ballasts - DIRect installation**
- **Built-in universal voltage driver - BYPass installation**
- **Patented design**





SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98385	5.5PLV/835/HYBM	3500K	600	82	109	No	13-18W	120°	50,000	120-277V	No	N.A.
98386	5.5PLV/840/HYBM	4000K	620	82	113	No	13-18W	120°	50,000	120-277V	No	N.A.
98387	8.5PLV/827/HYBM	2700K	950	82	112	No	26W	120°	50,000	120-277V	No	N.A.
98388	8.5PLV/830/HYBM	3000K	1,000	82	118	No	26W	120°	50,000	120-277V	No	N.A.
98389	8.5PLV/835/HYBM	3500K	1,000	82	118	No	26W	120°	50,000	120-277V	No	N.A.
98390	8.5PLV/840/HYBM	4000K	1,020	82	120	No	26W	120°	50,000	120-277V	No	N.A.
98256	16.5PLV/830/BYP	3000K	1,800	82	109	No	42W	120°	50,000	120-277V	No	N.A.
98257	16.5PLV/835/BYP	3500K	1,850	82	112	No	42W	120°	50,000	120-277V	No	N.A.
98258	16.5PLV/840/BYP	4000K	1,900	82	115	No	42W	120°	50,000	120-277V	No	N.A.

\* Note PL V 16.5W BYP operates on line voltage only and is not compatible with magnetic ballasts



- **BYPass installation – Requires bypassing the ballast**
- **Suitable for use in totally enclosed fixtures**
- **180° rotatable base**
- **Compact form factor fits most fixtures**

SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.
57818	3.5PLS/835/BYP/2G7	3500K	300	82	86	No	7-9W	180°	50,000	120-277V	Yes
57826	5.5PLS/835/BYP/2GX7	3500K	500	82	91	No	13W	180°	50,000	120-277V	Yes



- **HYBrid installation - DIRect or BYPass**
- **Compatible with magnetic ballasts - DIRect installation**
- **Built-in universal voltage driver - BYPass installation**
- **Exceptional efficacy**

SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.
57812	3.5PLS/827/HYB/G23	2700K	280	82	80	No	7-9W	120°	50,000	120-277V	Yes
57813	3.5PLS/830/HYB/G23	3000K	280	82	80	No	7-9W	120°	50,000	120-277V	Yes
57814	3.5PLS/835/HYB/G23	3500K	300	82	86	No	7-9W	120°	50,000	120-277V	Yes
57815	3.5PLS/840/HYB/G23	4000K	300	82	86	No	7-9W	120°	50,000	120-277V	Yes
98403	5.5PLSV/827/HYB/GX23	2700K	570	82	104	No	13W	120°	50,000	120-277V	No
98404	5.5PLSV/830/HYB/GX23	3000K	600	82	109	No	13W	120°	50,000	120-277V	No
98405	5.5PLSV/835/HYB/GX23	3500K	600	82	109	No	13W	120°	50,000	120-277V	No
98406	5.5PLSV/840/HYB/GX23	4000K	620	82	113	No	13W	120°	50,000	120-277V	No
98407	5.5PLSH/827/HYB/GX23	2700K	520	82	95	No	13W	110°	50,000	120-277V	No
98408	5.5PLSH/830/HYB/GX23	3000K	550	82	100	No	13W	110°	50,000	120-277V	No
98409	5.5PLSH/835/HYB/GX23	3500K	550	82	100	No	13W	110°	50,000	120-277V	No
98410	5.5PLSH/840/HYB/GX23	4000K	560	82	102	No	13W	110°	50,000	120-277V	No
57820	5.5PLS/827/HYB/GX23	2700K	450	82	82	No	13W	120°	50,000	120-277V	Yes
57821	5.5PLS/830/HYB/GX23	3000K	500	82	91	No	13W	120°	50,000	120-277V	Yes
57822	5.5PLS/835/HYB/GX23	3500K	500	82	91	No	13W	120°	50,000	120-277V	Yes
57823	5.5PLS/840/HYB/GX23	4000K	520	82	95	No	13W	120°	50,000	120-277V	Yes



# HID BOLLARD LINE



## Designed for Bollard & Post Top Applications



## HID Replacements



**25W: 70-100W**  
**16.5W: 50-70W**  
**HID**  
**120-277V**

- Integral driver suitable for 120-277V
- E26 base – ENERGY STAR® certified
- EX39 base – DLC® qualified
- Suitable for use in totally enclosed fixtures

SPECIFICATIONS											
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	ES / DLC
58238	16.5A21/830/277V	3000K	2,000	82	121	No	125W Inc.	330°	40,000	120-277V	✓ / N.A.
58239	16.5A21/840/277V	4000K	2,000	82	121	No	125W Inc.	330°	40,000	120-277V	✓ / N.A.
58240	16.5A21/850/277V	5000K	2,050	82	124	No	125W Inc.	330°	40,000	120-277V	✓ / N.A.
97972	25HID/830/277V/E26	3000K	3,200	82	128	No	200W Inc.	290°	50,000	120-277V	✓ / N.A.
97973	25HID/840/277V/E26	4000K	3,300	82	132	No	200W Inc.	290°	50,000	120-277V	✓ / N.A.
97974	25HID/850/277V/E26	5000K	3,400	82	136	No	200W Inc.	290°	50,000	120-277V	✓ / N.A.
97968	25HID/830/277V/EX39	3000K	3,200	82	128	No	70-100W HID	290°	50,000	120-277V	N.A. / ✓
97969	25HID/840/277V/EX39	4000K	3,300	82	132	No	70-100W HID	290°	50,000	120-277V	N.A. / ✓
97970	25HID/850/277V/EX39	5000K	3,400	82	136	No	70-100W HID	290°	50,000	120-277V	N.A. / ✓
16325	E26 EXTENDER	E26 Lamp Extender Adds 1.30" (33mm) to Lamp Height									
97718	10SURGE/277V	10kV Surge Protector									

# HID POST TOP LINE



## Designed for Post Top Applications



- Integral driver suitable for 120-277V
- Fully omnidirectional beam angle
- Compatible with EX39 & E39 sockets
- Suitable for use in totally enclosed fixtures

SPECIFICATIONS													
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC	
98087	37HID/830/277V/E26	3000K	4,700	82	127	No	100-175W HID	320°	50,000	120-277V	Yes	N.A.	
98088	37HID/840/277V/E26	4000K	5,200	82	141	No	100-175W HID	320°	50,000	120-277V	Yes	N.A.	
98089	37HID/850/277V/E26	5000K	5,200	82	141	No	100-175W HID	320°	50,000	120-277V	Yes	N.A.	
98084	37HID/830/277V/EX39	3000K	4,700	82	127	No	100-175W HID	320°	50,000	120-277V	Yes	✓	
98085	37HID/840/277V/EX39	4000K	5,200	82	141	No	100-175W HID	320°	50,000	120-277V	Yes	✓	
98086	37HID/850/277V/EX39	5000K	5,200	82	141	No	100-175W HID	320°	50,000	120-277V	Yes	✓	
98090	54HID/830/277V/EX39	3000K	7,300	82	135	No	175-250W HID	320°	50,000	120-277V	Yes	✓	
98091	54HID/840/277V/EX39	4000K	7,550	82	140	No	175-250W HID	320°	50,000	120-277V	Yes	✓	
98092	54HID/850/277V/EX39	5000K	7,550	82	140	No	175-250W HID	320°	50,000	120-277V	Yes	✓	
98097	68HID/840/277V/EX39	4000K	9,500	82	140	No	175-250W HID	320°	50,000	120-277V	Yes	✓	
98098	68HID/850/277V/EX39	5000K	9,500	82	140	No	175-250W HID	320°	50,000	120-277V	Yes	✓	
98100	100HID/840/277V/EX39	4000K	14,000	82	140	No	250-400W HID	320°	50,000	120-277V	Yes	✓	
98101	100HID/850/277V/EX39	5000K	14,000	82	140	No	250-400W HID	320°	50,000	120-277V	Yes	✓	
97718	10SURGE/277V	10kV Surge Protector											


# HID HIGH BAY / LOW BAY LINE

# HID WALL PACK LINE



E26 Version Available

## Designed for High Bay & Low Bay Applications



## Intentional Uplighting

All High Bay and Low Bay products feature a ring of LEDs mounted around the base to provide visible uplighting for improved aesthetics and comfort




- Integral driver suitable for 120-277V
- Visible uplighting
- Compatible with EX39 & E39 sockets
- Exceptional efficacy >126 LPW

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC
98121	35HIDLB/840/BYP/E26	4000K	4,400	82	126	No	100-175W HID	110°	50,000	120-277V	No	N.A.
98122	35HIDLB/850/BYP/E26	5000K	4,400	82	126	No	100-175W HID	110°	50,000	120-277V	No	N.A.
98118	35HIDLB/840/BYP/EX39	4000K	4,400	82	126	No	100-175W HID	110°	50,000	120-277V	No	✓
98119	35HIDLB/850/BYP/EX39	5000K	4,400	82	126	No	100-175W HID	110°	50,000	120-277V	No	✓
98124	65HIDHB/840/BYP/EX39	4000K	8,600	82	132	No	175-250W HID	110°	50,000	120-277V	No	✓
98125	65HIDHB/850/BYP/EX39	5000K	8,600	82	132	No	175-250W HID	110°	50,000	120-277V	No	✓
98127	90HIDHB/840/BYP/EX39	4000K	12,400	82	138	No	250-400W HID	110°	50,000	120-277V	No	✓
98128	90HIDHB/850/BYP/EX39	5000K	12,400	82	138	No	250-400W HID	110°	50,000	120-277V	No	✓



E26 Version Available

## Designed for Wall Pack Applications



## 350° Rotatable Base




Horizontal lamp supports included



- Integral driver suitable for 120-277V
- Designed for horizontally-mounted wall pack applications
- Exceptional efficacy >140 LPW
- Suitable for use in totally enclosed fixtures

SPECIFICATIONS													
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	DLC	
98179	20HIDWP/840/277V/E26	4000K	2,800	82	140	No	70-100W HID	120°	50,000	120-277V	Yes	N.A.	
98180	20HIDWP/850/277V/E26	5000K	2,800	82	140	No	70-100W HID	120°	50,000	120-277V	Yes	N.A.	
98183	40HIDWP/840/277V/E26	4000K	5,800	82	145	No	100-175W HID	120°	50,000	120-277V	Yes	N.A.	
98184	40HIDWP/850/277V/E26	5000K	5,800	82	145	No	100-175W HID	120°	50,000	120-277V	Yes	N.A.	
98185	40HIDWP/840/277V/EX39	4000K	5,800	82	145	No	100-175W HID	120°	50,000	120-277V	Yes	✓	
98186	40HIDWP/850/277V/EX39	5000K	5,800	82	145	No	100-175W HID	120°	50,000	120-277V	Yes	✓	
98189	54HIDWP/840/277V/EX39	4000K	7,800	82	144	No	175-250W HID	120°	50,000	120-277V	Yes	✓	
98190	54HIDWP/850/277V/EX39	5000K	7,800	82	144	No	175-250W HID	120°	50,000	120-277V	Yes	✓	





- Revolutionary CLOUD design
- 60% lighter due to environmentally friendly construction
- BR30 high CRI & GU24 versions available
- Suitable for use in totally enclosed fixtures




- Suitable to replace 45W, 65W, 75W, 85W incandescent
- Energy efficient and environmentally friendly
- Providing a comfortable diffused level of light
- Smooth dimming with existing dimmers

SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES / JA8 / T20
98023	9.5BR30DIM/927/R	2700K	700	92	74	Yes	65W	110°	25,000	120V	Yes	✓/✓/✓/✓
98024	9.5BR30DIM/927/GU24	2700K	700	92	74	Yes	65W	110°	25,000	120V	Yes	✓/✓/✓/✓

SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
98460	7.5R20DIM/827	2700K	525	82	70	Yes	45W	120°	25,000	120V	Yes	✓
98461	9BR30DIM/827	2700K	650	82	72	Yes	65W	120°	25,000	120V	Yes	✓
98462	9BR30DIM/830	3000K	650	82	72	Yes	65W	120°	25,000	120V	Yes	✓
98463	9BR30DIM/840	4000K	650	82	72	Yes	65W	120°	25,000	120V	Yes	✓
98464	11BR40DIM/827	2700K	950	82	86	Yes	75W	120°	25,000	120V	Yes	✓
98465	11BR40DIM/830	3000K	950	82	86	Yes	75W	120°	25,000	120V	Yes	✓
98466	15.5BR40DIM/827	2700K	1,100	82	71	Yes	85W	120°	25,000	120V	No	✓
98467	15.5BR40DIM/830	3000K	1,100	82	71	Yes	85W	120°	25,000	120V	No	✓




- Suitable to replace 60W, 75W, 100W Incandescent
- High CRI and R values (R9 57, R13 95)
- Suitable for use in totally enclosed fixtures
- 120-277V universal voltage 60W replacements

SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES / JA8 / T20
98559	9A19DIM/927	2700K	800	92	89	Yes	60W	240°	25,000	120V	Yes	✓/✓/✓
98560	9A19DIM/930	3000K	820	92	91	Yes	60W	240°	25,000	120V	Yes	✓/N.A./✓
98561	9A19DIM/940	4000K	860	92	96	Yes	60W	240°	25,000	120V	Yes	✓/N.A./✓
98565	9A19DIM/927/GU24/R	2700K	800	92	89	Yes	60W	240°	25,000	120V	Yes	✓/✓/✓
98562	9A19/927/277V	2700K	1,100	92	89	No	60W	300°	25,000	120-277V	Yes	✓/N.A./N.A.
98563	9A19/930/277V	3000K	800	92	91	No	60W	300°	25,000	120-277V	Yes	✓/N.A./N.A.
98564	9A19/940/277V	4000K	820	92	96	No	60W	300°	25,000	120-277V	Yes	✓/N.A./N.A.
98141	11A19DIM/927	2700K	1,100	92	100	Yes	75W	240°	25,000	120V	Yes	✓/N.A./✓
98142	11A19DIM/930	3000K	1,150	92	105	Yes	75W	240°	25,000	120V	Yes	✓/N.A./✓
98143	11A19DIM/940	4000K	1,200	92	109	Yes	75W	240°	25,000	120V	Yes	✓/N.A./✓
98147	15A21DIM/927/N	2700K	1,600	92	107	Yes	100W	240°	25,000	120V	Yes	✓/✓/✓
98148	15A21DIM/930/N	3000K	1,650	92	110	Yes	100W	240°	25,000	120V	Yes	✓/N.A./✓
98149	15A21DIM/940/N	4000K	1,700	92	113	Yes	100W	240°	25,000	120V	Yes	✓/N.A./✓




- Suitable to replace 40W, 60W, 75W, 100W Incandescent
- Comfortable warm diffused light
- Tight LED binning for consistent CCT across all lamps
- Smooth dimming with existing dimmers



SPECIFICATIONS												
Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
97985	6A19DIM/827/R	2700K	480	82	80	Yes	40W	220°	25,000	120V	No	✓
97986	6A19DIM/830/R	3000K	480	82	80	Yes	40W	220°	25,000	120V	No	✓
98011	8A19DIM/827/R	2700K	800	82	100	Yes	60W	220°	25,000	120V	No	✓
98012	8A19DIM/830/R	3000K	800	82	100	Yes	60W	220°	25,000	120V	No	✓
98013	8A19DIM/840/R	4000K	800	82	100	Yes	60W	220°	25,000	120V	No	✓
97908	9A19DIM/827/GU24/R	2700K	800	82	89	Yes	60W	240°	25,000	120V	Yes	✓
97909	9A19DIM/830/GU24/R	3000K	820	82	91	Yes	60W	240°	25,000	120V	Yes	✓
97910	9A19DIM/840/GU24/R	4000K	860	82	96	Yes	60W	240°	25,000	120V	Yes	✓
98138	11A19DIM/827	2700K	1100	82	100	Yes	75W	240°	25,000	120V	Yes	✓
98139	11A19DIM/830	3000K	1150	82	105	Yes	75W	240°	25,000	120V	Yes	✓
98140	11A19DIM/840	4000K	1200	82	109	Yes	75W	240°	25,000	120V	Yes	✓
98144	15A21DIM/827	2700K	1600	82	107	Yes	100W	240°	25,000	120V	Yes	✓
98145	15A21DIM/830	3000K	1650	82	110	Yes	100W	240°	25,000	120V	Yes	✓
98146	15A21DIM/840	4000K	1700	82	113	Yes	100W	240°	25,000	120V	Yes	✓
98150	15A21DIM/827/GU24	2700K	1600	82	107	Yes	100W	240°	25,000	120V	Yes	✓
98083	14A19/827/3WAY	2700K	1,000	82	125	No	75W	230°	15,000	120V	No	✓
			500		125		40W					
			1,500		107		100W					






All Warm Dim Lamps Feature 2700K-2200K CCT Dimming




### Lighting for Any Occasion



### 2700K-2200K Warm Dim



WARM DIM



WARM DIM

- Smooth dimming from 2700K-2200K CCT
- Traditional incandescent style dimming
- Exceptional efficacy
- Available in Downlight, BR, A19 & Candle lamps

### SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
57884	5B11DIM/8CCTD	2200K-2700K	300	82	60	Yes	40W	230°	25,000	120V	Yes	✓
58001	6.5R20DIM/8CCTD	2200K-2700K	500	82	77	Yes	45W	110°	25,000	120V	Yes	✓
57885	9BR30DIM/8CCTD	2200K-2700K	650	82	72	Yes	65W	110°	25,000	120V	Yes	✓
57883	9.5A19DIM/8CCTD	2200K-2700K	800	82	84	Yes	60W	330°	25,000	120V	Yes	✓
58002	10.5BR40DIM/8CCTD	2200K-2700K	735	82	70	Yes	65W	110°	25,000	120V	Yes	✓
58100	11DL6DIM/8CCTD	2200K-2700K	770	82	70	Yes	65W	110°	40,000	120V	N.A.	✓

### CREATE THE PERFECT AMBIENCE




+ 2700K

- 2200K



These GREEN CREATIVE lamps feature 2700K-2200K CCT dimming designed to replicate the warm dimming effect of traditional incandescent light sources. As the lamp dims, its CCT gradually warms, helping to create the perfect ambience for all occasions.

# FILAMENT LINE



- Micro-designed driver - No heatsink required
- Comfortable warm diffused light
- Smooth dimming with existing installations
- Silver bowl design helps redirect light and minimizes glare


## SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Finish	ES / T20
98458	1FS14/820/A	2000K	35	82	75	Yes	10W	300°	15,000	120V	Amber	N.A. / N.A.
98457	1FS14/827	2700K	55	82	37	Yes	10W	300°	15,000	120V	Clear	N.A. / N.A.
98459	3FT6DIM/820/A	2000K	110	82	71	Yes	25W	300°	15,000	120V	Amber	N.A. / N.A.
57946	3.5FT10DIM/822/A	2200K	250	82	90	Yes	25W	330°	15,000	120V	Amber	N.A. / N.A.
98240	4.5FBA11DIM/820/FT/A	2000K	240	82	68	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
98241	3.3FB11DIM/927	2700K	300	92	90	Yes	40W	300°	15,000	120V	Clear	✓ / ✓
98242	3.3FB11DIM/927/E26	2700K	300	92	107	Yes	40W	300°	15,000	120V	Clear	✓ / ✓
98456	3.8FB11DIM/827/FR	2700K	300	82	80	Yes	40W	300°	15,000	120V	Frosted	N.A. / N.A.
98454	5FB11DIM/827	2700K	500	82	107	Yes	60W	300°	15,000	120V	Clear	N.A. / N.A.
98455	5FB11DIM/827/E26	2700K	500	82	93	Yes	60W	300°	15,000	120V	Clear	✓ / N.A.
98239	4FST19DIM/820/A	2000K	300	82	90	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
98357	5FA19DIM/820/A	2000K	340	82	92	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
98376	5FA19DIM/827	2700K	450	82	63	Yes	40W	300°	15,000	120V	Clear	N.A. / N.A.
98450	5FA19DIM/827/FR	2700K	450	82	89	Yes	40W	300°	15,000	120V	Frosted	N.A. / N.A.
98448	7.5FA19DIM/820/A	2000K	600	82	94	Yes	60W	300°	15,000	120V	Amber	N.A. / N.A.
98278	7.5FA19DIM/827	2700K	800	82	91	Yes	60W	300°	15,000	120V	Clear	✓ / N.A.
98449	7.5FA19DIM/827/FR	2700K	800	82	91	Yes	60W	300°	15,000	120V	Frosted	N.A. / N.A.
98358	7.5FA19DIM/827/SB	2700K	700	82	53	Yes	60W	N.A.	15,000	120V	Silver Bowl	N.A. / N.A.
98279	9FA19DIM/927	2700K	810	92	79	Yes	60W	300°	15,000	120V	Clear	✓ / ✓
98453	4FG16.5DIM/820/A	2000K	250	82	100	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
98451	4FG16.5DIM/827	2700K	350	82	100	Yes	40W	300°	15,000	120V	Clear	N.A. / N.A.
98452	4FG16.5DIM/827/E26	2700K	350	82	88	Yes	40W	300°	15,000	120V	Clear	N.A. / N.A.
98378	4FG25DIM/820/A	2000K	250	82	88	Yes	40W	300°	15,000	120V	Amber	N.A. / N.A.
97826	4.5FG25DIM/827/SB	2700K	400	82	63	Yes	40W	N.A.	15,000	120V	Silver Bowl	N.A. / N.A.
98377	3.8FG25DIM/927	2700K	350	92	55	No	40W	300°	15,000	120V	Clear	✓ / ✓
57945	5FG40DIM/827	2700K	470	82	35	No	40W	330°	15,000	120V	Clear	✓ / N.A.

# DECORATIVE LINE



Suitable for All Decorative Applications




- 40W incandescent replacements
- Perfect decorative retrofit needs
- Omnidirectional: 275° beam angle
- Powerful 450 lumens in 2700K

## SPECIFICATIONS

Product	Model	CCT	Lumens	CRI (typ.)	LPW	Dim	Equiv.	Beam Angle	Life (hrs)	Voltage	Encl.	ES
97729	6G25DIM/827/R	2700K	450	82	75	Yes	40W	275°	25,000	120V	No	✓


**V2019.2**



**Tel / Fax: (866) 774-5433**

**info@greencreative.com**

**www.greencreative.com**

 / GREENCREATIVELED

 / GClightingLED

 / GREEN CREATIVE



**GREENCREATIVE**