LENOX *Gold*® RECIPROCATING SAW BLADES

Longest Lasting Blade. Ever.

EXTENDED BLADE LIFE
T2™ Technology and precision applied titanium coating help dissipate heat making blades last longer

FASTER CUTS
Titanium coating makes teeth more wear resistant so they stay sharp for quicker cuts

LONGER BLADE LIFE AND VERSATILITY
T2 technology's patented tooth design delivers longer blade life and enables faster cutting in the widest array of cutting applications







Wood | **Metal** | **Demolition** | ***LAZER***® **Extreme Metal**

LENOX *Gold* RECIPROCATING SAW BLADES (CONTINUED)

	TPI	LENGTH X WIDTH X THICKNESS IN	LENGTH X WIDTH X THICKNESS MM	5-PACK PROD NO	25-PACK PROD NO		APPLICATION
WOOD	6	6 x 7/16 x .050	152 x 11 x 1.3	21063676GRC	—		
	6	6 x 3/4 x .050	152 x 19 x 1.3	21060656GR	21074B656GR	RAPID PLUNGE	
	6	9 x 3/4 x .050	229 x 19 x 1.3	21062956GR	21076B956GR		
	6	12 x 3/4 x .050	305 x 19 x 1.3	21061156GR	21075B156GR		
METAL	10	6 x 3/4 x .035	152 x 19 x .9	21064610GR	21078B610GR		
	10	8 x 3/4 x .050	203 x 19 x 1.3	21065810GR	21079B810GR		
	14	4 x 3/4 x .035	102 x 19 x .9	21066414GR	21080B414GR		
	14	6 x 3/4 x .035	152 x 19 x .9	21067614GR	21081B614GR		
	18	4 x 3/4 x .035	102 x 19 x .9	21068418GR	21082B418GR		
	18	6 x 3/4 x .035	152 x 19 x .9	21069618GR	21083B618GR		
	18	8 x 3/4 x .035	203 x 19 x .9	21070818GR	21084B818GR		
	24	4 x 3/4 x .035	102 x 19 x .9	21071424GR	—		
	24	6 x 3/4 x .035	152 x 19 x .9	21072624GR	21086B624GR		
	24	8 x 3/4 x .035	203 x 19 x .9	21073824GR	21087B824GR		
DEMOLITION	6	6 x 1 x .062	152 x 22 x 1.6	210886066GR	21220B6066GR		
	6	9 x 1 x .062	229 x 22 x 1.6	21090966GR	21222B966GR		
	6	12 x 1 x .062	305 x 22 x 1.6	21091106GR	21223B106GR		
	10	9 x 1 x .062	229 x 22 x 1.6	21089960GR	21221B960GR		
EXTREME METAL CUTTING	8	6 x 1 x .042	152 x 25 x 1.07	210926108GR	—		
	8	9 x 1 x .042	229 x 25 x 1.07	210969108GR	—		
	10	6 x 1 x .042	152 x 25 x 1.07	210936110GR	21225B6110GR		
	10	9 x 1 x .042	229 x 25 x 1.07	210979110GR	21229B9110GR		
	10	12 x 1 x .042	305 x 25 x 1.07	2110012110GR	21237B12110GR		
	14	6 x 1 x .042	152 x 25 x 1.07	210946114GR	21226B6114GR		
	14	9 x 1 x .042	229 x 25 x 1.07	210989114GR	21235B9114GR		
	14	12 x 1 x .042	305 x 25 x 1.07	2110112114GR	21238B12114GR		
	18	6 x 1 x .042	152 x 25 x 1.07	210956118GR	21227B6118GR		
	18	9 x 1 x .042	229 x 25 x 1.07	210999118GR	21236B9118GR		
	18	12 x 1 x .042	305 x 25 x 1.07	2110212118GR	21239B12118GR		

ICON REFERENCE CHART

WOOD	NAIL-EMBEDDED WOOD	CONTOUR WOOD	PLASTIC	THICK METAL	MEDIUM METAL	THIN METAL	NON-FEROUS METAL
							

DEMOLITION	FIRE & RESCUE	PLASTER & DRYWALL	CAST IRON	CEMENT BOARD	TILE	ABRASIVES	NATURAL STONE
							



PLUNGE CUTTING WOOD BLADE

Patent pending plunge cutting tooth design prevents blade from walking to deliver faster, easier plunge cuts

LAZER® RECIPROCATING SAW BLADES

Best for Heavy Metal Cutting



FAST AND EASY HEAVY METAL CUTTING
T2 technology's patented tooth design delivers longer blade life and enables faster cutting

OPTIMIZED FOR HIGHER PERFORMANCE
Reinforced tooth design ensures higher performance in the most demanding jobs

STRAIGHT CUTS
Wider than conventional blades, this blade cuts straighter



TPI	LENGTH X WIDTH X THICKNESS IN	LENGTH X WIDTH X THICKNESS MM	2-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	50-PACK PROD NO	APPLICATION STRUCTURAL
8	6 x 1 x .042	152 x 25 x 1.07	—	201926108R	20196B6108R	—	Structural Steels greater than 3/16"
8	9 x 1 x .042	229 x 25 x 1.07	—	201939108R	20195B9108R	—	
8	12 x 1 x .042	305 x 25 x 1.07	—	2019412108R	20197B12108R	—	
10	6 x 1 x .042	152 x 25 x 1.07	24901T6110R	201706110R	20171B6110R	—	Structural Steels and All Metals 3/16"–1/2"
10	9 x 1 x .042	229 x 25 x 1.07	24905T9110R	201769110R	20177B9110R	—	
10	12 x 1 x .042	305 x 25 x 1.07	24909T12110R	2018212110R	20183B12110R	—	
14	6 x 1 x .042	152 x 25 x 1.07	24902T6114R	201726114R	20173B6114R	22764OSB6114R	Structural Steels and All Metals 3/32"–3/8"
14	9 x 1 x .042	229 x 25 x 1.07	24906T9114R	201789114R	20179B9114R	22766OSB9114R	
14	12 x 1 x .042	305 x 25 x 1.07	24910T12114R	2018412114R	20185B12114R	—	
18	6 x 1 x .042	152 x 25 x 1.07	24903T6118R	201746118R	20175B6118R	22765OSB6118R	Structural Steels and All Metals 1/16"–1/4"
18	9 x 1 x .042	229 x 25 x 1.07	24907T9118R	201809118R	20181B9118R	22767OSB9118R	
18	12 x 1 x .042	305 x 25 x 1.07	24911T12118R	2019012118R	20191B12118R	—	

DEMOLITION RECIPROCATING SAW BLADES

Best for Demolition and Nail-Embedded Wood

DEMOLITION JOBS ARE EASIER
T2 technology's patented tooth design delivers longer blade life and enables faster cutting

MAXIMUM DURABILITY
The tallest blade on the market prevents bending and provides maximum control in the toughest demolition applications

AGGRESSIVE CUTS EVEN IN TIGHT SPACES
Each blade has an optimized blade geometry including an aggressive tang angle and tapered blade shape to allow for cutting in tight areas





TPI	LENGTH X WIDTH X THICKNESS IN	LENGTH X WIDTH X THICKNESS MM	2-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	50-PACK PROD NO	APPLICATION
6	6 x 1 x .062	152 x 22 x 1.6	205126066R	203706066R5	20514B6066R	—	
6	9 x 1 x .062	229 x 22 x 1.6	20598966R	20371966R5	20523B966R	22763OSB966R	
6	12 x 1 x .062	305 x 22 x 1.6	20500106R	20373106R5	20485B106R	—	
10	9 x 1 x .062	229 x 22 x 1.6	20597960R	20372960R5	20524B960R	22762OSB960R	

BI-METAL RECIPROCATING SAW BLADES

Long Lasting, Fast Cutting and Versatile



LONGER BLADE LIFE AND VERSATILITY
T2 technology's patented tooth design delivers longer blade life and enables faster cutting in the widest array of cutting applications

MINIMIZE FRICTION AND HEAT BUILD UP
Engineered for performance this blade can handle the widest variety of metal materials providing an optimized cutting experience



TPI	LENGTH X WIDTH X THICKNESS IN	LENGTH X WIDTH X THICKNESS MM	1-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	50-PACK PROD NO	APPLICATION
4	6 x 3/4 x .050	152 x 19 x 1.3	20574S634R	20575634R	—	—	
6	4 x 3/4 x .050	102 x 19 x 1.3	—	20449456RP	—	—	
6	6 x 3/4 x .050	152 x 19 x 1.3	20571S636RP	20570636RP	20497B636RP	—	
6	6 x 3/4 x .035	152 x 19 x .9	20559S606R	20560606R	20492B606R	—	
6	6 x 7/16 x .050	152 x 11 x 1.3	20557S676RC	20556676RC	—	—	
6	6 x 3/4 x .050	152 x 19 x 1.3	20573S656R	20572656R	20530B656R	22750OSB656R	
6	9 x 3/4 x .050	229 x 19 x 1.3	20587S956R	20582956R	20558B956R	22752OSB956R	
6	12 x 3/4 x .050	305 x 19 x 1.3	20586S156R	20585156R	20495B156R	22755OSB156R	
10	6 x 3/4 x .035	152 x 19 x .9	20561S610R	20562610R	20493B610R	22761OSB610R	
10	8 x 3/4 x .050	203 x 19 x 1.3	20581S810R	20580810R	20590B810R	22753OSB810R	
10/14	6 x 3/4 x .050	152 x 19 x 1.3	20592650R*	20374650R5	20515B650R		
10/14	8 x 3/4 x .050	203 x 19 x 1.3	—	20577850R	20535B850R		
10/14	12 x 3/4 x .050	305 x 19 x 1.3	20584S110R	20583110R	20491B110R	22758OSB110R	
10/14	6 x 3/4 x .035	152 x 19 x .9	—	12129635R	—	—	
10/14	8 x 3/4 x .035	203 x 19 x .9	—	12130835R	—	—	

** This item is a 2-pack*

BI-METAL RECIPROCATING SAW BLADES (CONTINUED)



TPI	LENGTH X WIDTH X THICKNESS IN	LENGTH X WIDTH X THICKNESS MM	1-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	50-PACK PROD NO	APPLICATION
14	3-5/8 x 5/16 x .035	92 x 8 x .9	—	20520314RC	—	—	
14	4 x 3/4 x .035	102 x 19 x .9	20551S414R	20550414R	20488B414R	22760OSB414R	
14	6 x 3/4 x .035	152 x 19 x .9	20565S614R	20564614R	20494B614R	22756OSB614R	
14	8 x 3/4 x .035	203 x 19 x .9	—	21519814R	1855567	1855570	
14	9 x 3/4 x .050	225 x 19 x 1.3	205119514R*				
18	3-5/8 x 5/16 x .035	92 x 8 x .9	20522S318RC	20521318RC	—	—	
18	4 x 3/4 x .035	102 x 19 x .9	20553S418R	20552418R	20489B418R	22759OSB418R	
18	6 x 3/4 x .035	152 x 19 x .9	20567S618R	20566618R	20529B618R	22751OSB618R	
18	8 x 3/4 x .035	203 x 19 x .9	20563S818R	20578818R	20487B818R	22754OSB818R	
18	12 x 3/4 x .035	305 x 29 x .9	—	21510118R	21511B118R	—	
24	4 x 3/4 x .035	102 x 19 x .9	20555S424R	20554424R	20490B424R	—	
24	6 x 3/4 x .035	152 x 19 x .9	20569S624R	20568624R	20496B624R	22757OSB624R	
24	8 x 3/4 x .035	203 x 19 x .9	—	20579824R	—	—	

** This item is a 2-pack*

LENOX *DIAMOND*™ RECIPROCATING SAW BLADES

Cuts Cast. Fast.



LASTS LONGER
Nickel alloy-brazed diamond particles maintain sharpness to keep cutting after conventional carbide grit fails

CUTS 3X FASTER*
A narrow kerf design enables thinner, faster cuts

STRAIGHT, CLEAN CUTS
Unlike bulky snap cutters which crush pipes and leave ragged, uneven cuts, LENOX *DIAMOND* cuts clean. Durable chrome alloy backing steel provides extra stability

**Speed measured cutting 4" cast iron pipe at maximum speed vs. the leading competitor*

LENGTH X WIDTH X THICKNESS		1-PACK	APPLICATION
IN	MM	PROD NO	
8 x 3/4 x .040	203 x 19 x 1	10833800RDG	Cast Iron, Tile, Brick and Natural Stone
DOUBLE TANG			
9 x 3/4 x .042	225 x 19 x 1.07	1766338	
11 x 3/4 x .042	275 x 19 x 1.07	1766356	



CARBIDE GRIT RECIPROCATING SAW BLADES

For Cutting Non-Metallic Materials

HIGH PERFORMANCE IN ABRASIVE MATERIALS
Cuts through tough materials that resist chip-forming, including ceramics, pipe, man-made stone, brick, marble and more

SMOOTH, QUICK CUTS
Uniformly applied, durable carbide grit particles on a flexible blade provide fast cuts without snagging or binding





LENGTH X WIDTH X THICKNESS		2-PACK		APPLICATION
IN	MM	PROD NO	GRIT	
6 x 3/4 x .032	152 x 19 x .8	20505600RG	Medium	Fiberglass, Ceramic Tile, Cultured Marble, Clays, Brick
8 x 3/4 x .040	203 x 19 x 1	20576800RG	Medium	
10 x 3/4 x .050	254 x 19 x 1.3	20506100RG	Medium	



CARBIDE TIPPED RECIPROCATING SAW BLADES

Engineered to Cut the Toughest Materials



VERSATILE AND EFFECTIVE
Cuts tough materials including cement board, cast aluminum, pressure treated wood, engineered lumber, and more

ENGINEERED FOR FASTER PERFORMANCE
Triple chip tooth design cuts 25% faster than standard carbide blades and provides exceptional fatigue resistance



	LENGTH X WIDTH X THICKNESS		1-PACK		APPLICATION
TPI	IN	MM	PROD NO	PROFILE	
3	8 x 3/4 x .050	203 x 19 x 1.3	205998535RCT	Straight	Fiberglass, Particle Board, Pressure-Treated Woods, Plywood, Cast Aluminum
6	6 x 3/4 x .050	152 x 19 x 1.3	205966565RCT	Straight	
6	6 x 3/4 x .050	152 x 19 x 1.3	205956563RCT	Contour	



EXTRA SHARP FLEAM GROUND RECIPROCATING BLADES

Fast, Clean Cutting in Wood or Plastic



BI-METAL CONSTRUCTION
Durable and flexible to survive nail strikes

FLEAM GROUND TOOTH FORM
Fast, clean wood cutting

IDEAL FOR CLEAN WOOD, PLASTIC PIPE AND TREE PRUNING



	LENGTH X WIDTH X THICKNESS		5-PACK	APPLICATION
TPI	IN	MM	PROD NO	
6	6 x 3/4 x .050	152 x 19 x 1.3	121016W6R	Clean Wood, Plastics, Pruning
6	9 x 3/4 x .050	229 x 19 x 1.3	121029W6R	



PALLET DISMANTLING RECIPROCATING SAW BLADES

High Performance Cutting for Pallet Refurbishing



ENGINEERED FOR STRENGTH
Specially treated to enhance performance and withstand nail strikes to keep cutting fast

LONG CUTTING LIFE
Patented tooth design and a rounded nose provide long blade life and enable easy access in tight spots

	LENGTH X WIDTH X THICKNESS		250-PACK	APPLICATION
TPI	IN	MM	PROD NO	
10	8 x 3/4 x .035	203 x 19 x .9	10729810RPC	Dismantling Pallets
10	10 x 3/4 x .035	254 x 19 x .9	107301010RPC	

RECIPROCATING SAW BLADE KITS



121439KPE
9 PIECE
GENERAL PURPOSE KIT
Includes Storage Case

QTY	PROD NO	TPI	LENGTH X WIDTH X THICKNESS IN	MM
2	656R	6	6 x 3/4 x .050	152 x 19 x 1.3
2	624R	24	6 x 3/4 x .035	152 x 19 x .9
2	818R	18	8 x 3/4 x .035	203 x 19 x .9
2	810R	10	8 x 3/4 x .050	203 x 19 x 1.3
1	960R	10	9 x 7/8 x .062	229 x 22 x 1.6



1214412RKD
12 PIECE
DEMOLITION KIT
Includes Storage Case

QTY	PROD NO	TPI	LENGTH X WIDTH X THICKNESS IN	MM
3	6066R	6	6 x 7/8 x .062	150 x 22 x 1.6
3	6114R	14	6 x 1 x .042	150 x 25 x 1.1
2	9114R	14	9 x 1 x .042	225 x 25 x 1.1
2	966R	6	9 x 7/8 x .062	225 x 22 x 1.6
2	960R	10	9 x 7/8 x .062	225 x 22 x 1.6



20502546A
5 PIECE
4" AND 6" BLADE ASSORTMENT

QTY	PROD NO	TPI	LENGTH X WIDTH X THICKNESS IN	MM
1	414R	14	4 x 3/4 x .035	102 x 19 x .9
1	418R	18	4 x 3/4 x .035	102 x 19 x .9
1	614R	14	6 x 3/4 x .035	152 x 19 x .9
1	618R	18	6 x 3/4 x .035	152 x 19 x .9
1	656R	6	6 x 3/4 x .050	152 x 19 x 1.3



1839466
5 PIECE
METAL CUTTING KIT

QTY	PROD NO	TPI	LENGTH X WIDTH X THICKNESS IN	MM
3	618R	18	6 x 3/4 x .035	152 x 19 x .9
2	818R	18	8 x 3/4 x .035	203 x 19 x .9



1839467
5 PIECE
WOOD CUTTING KIT

QTY	PROD NO	TPI	LENGTH X WIDTH X THICKNESS IN	MM
3	656R	6	6 x 3/4 x .050	52 x 19 x 1.3
2	956R	6	9 x 3/4 x .035	29 x 19 x 1.3



1839465
5 PIECE
DEMOLITION KIT

QTY	PROD NO	TPI	LENGTH X WIDTH X THICKNESS IN	MM
1	6066R	6	6 x 1 x .062	150 x 25 x 1.6
1	6114R	14	6 x 1 x .042	150 x 25 x 1.1
1	9114R	14	9 x 1 x .042	225 x 25 x 1.1
1	966R	6	9 x 1 x .062	225 x 25 x 1.6
1	960R	10	9 x 1 x .062	225 x 25 x 1.6




1073415RKG
15 PIECE KIT
Includes Storage Case

QTY	PROD NO	TPI	LENGTH X WIDTH X THICKNESS IN	MM
5	614R	14	6 x 3/4 x .035	152 x 19 x .9
5	618R	18	6 x 3/4 x .035	152 x 19 x .9
5	656R	6	6 x 3/4 x .050	152 x 19 x 1.3

RECIPROCATING SAW BLADE SELECTION GUIDE


	WOOD	NAIL-EMBEDDED WOOD	NON-FERROUS METAL	DEMO-LITION	FIRE & RESCUE	PLASTICS & COMPOSITES	THICK METAL	MEDIUM METAL	THIN METAL	DRYWALL/ PLASTER	CEMENT BOARD	CAST IRON	ABRASIVES
													
BEST	LENOX *GOLD*®									CARBIDE TIPPED		LENOX *DIAMOND*™	
BETTER	BI-METAL	*LAZER*®	BI-METAL				*LAZER*			BI-METAL	LENOX *DIAMOND*	CARBIDE GRIT	
GOOD	—	BI-METAL	—				BI-METAL			—	CARBIDE GRIT	—	


TEETH PER INCH SELECTION GUIDE



BLADE LENGTH SELECTION GUIDE













Always keep 2 teeth in the cut.
















WIDTH OF MATERIAL + 3" = BLADE LENGTH
EXAMPLE: 5" (WIDTH) + 3" = 8". USE AN 8" OR 9" BLADE

RECIPROCATING SAW BLADES CROSS REFERENCE CHART

	TPI	LENGTH IN	LENGTH MM	DESC	SHAPE	BOSCH® / BOSCH EDGE	DEWALT®	MILWAUKEE®/ MILWAUKEE ICE	MK MORSE®
LENOX Gold®	6	6	152	676GRC					
	6	6	152	656GR					
	6	6	152	6066GR					
	6	9	229	956GR					
	6	9	229	966GR					
	6	12	305	156GR					
	6	12	305	106GR					
	8	6	152	6108GR					
	8	9	229	9108GR					
	10	6	152	610GR					
	10	6	152	6110GR					
	10	8	203	810GR					
	10	9	229	9110GR					
	10	12	305	12110GR					
	14	4	102	414GR					
	14	6	152	614GR					
	14	6	152	6114GR					
	14	9	229	9114GR					
	14	12	305	12114GR					
	18	4	102	418GR					
	18	6	152	618GR					
	18	6	152	6118GR					
	18	8	203	818GR					
	18	9	229	9118GR					
	18	12	305	12118GR					
	24	4	102	424GR					
	24	6	152	624GR					
	24	8	203	824GR					
LENOX DIAMOND™	Grit	9	225	800DTDG					—
	Grit	11	275	100DTDG					—
LAZER®	8	6	152	6108R		RSM6X2, RSM7X2 RESM6X2	—	5700, 5701	—
	8	9	229	9108R		RSM9X2, RESM9X2	—	5705, 5706	—
	8	12	305	12108R		RSM12X2	—	5710, 5711	—
	10	6	152	6110R		S123XF, RPRM6, SAPP6, RESM6X2	—	5712, 4712	RB66210, RBFR66210W, RBMC64210
	10	9	229	9110R		RESM9X2	—	5713, 4713	RB1010, RBMC95010
	10	12	305	12110R		RAP1210	—	5714	RB1210, RB126210, RBFR126210W, RBMC125010
	14	6	152	6114R		RCM6X2, RECM6X2	DWA4186	5782, 4782	RBFR66214W, RBMC64214
	14	9	229	9114R		RCM9X2, RECM9X2	DWA4188	5787, 5795, 4788	RBFR96214W, RBMC95014
	14	12	305	12114R		RCM12X2	DWA4112	5794	RB1214, RBFR126214W, RBMC125014, RBU10514
	18	6	152	6118R		RCTM6X2,RECM6X2	—	5784, 4784	RB65018, RBMC64218
	18	9	229	9118R		RECM9X2	—	5788, 5798, 4788	RBMC95018
	18	12	305	12118R		—	—	5789	RBMC125018

NO COMPETITIVE EQUIVALENT

	TPI	LENGTH IN	LENGTH MM	DESC	SHAPE	BOSCH® / BOSCH EDGE	DEWALT®	MILWAUKEE®/ MILWAUKEE ICE	MK MORSE®
DEMOLITION	6	6	152	6066R		RDN6V	DW4862	5021, 5701	RB66206C
	6	9	229	966R		RDN9V	DW4863	5026	RB96206
	6	12	305	106R		RDN12V	DW4806, DW4806B, DW4845, DW4877	5027	RB126206
	10	9	229	960R		REDM6X2, REDM9X2	—	—	RB96210, RBFR96210W
STANDARD BI-METAL	4	6	152	634R		S234XF	DW4801	—	RC603
	6	4	102	456RP		—	—	5052	RB606
	6	6	152	636RP		RDW66	—	—	RB606P
	6	6	152	656R		RDN6V, RHN66, RW66, RN66, RN96, RN126	DW4802, DW4802B, DW4847, DW4848B, DW4876	5031, 5035	RB63506, RB65006, RB65058, RC606
	6	6	152	676RC		—	DW4816	5041	RB65006C
	6	6	152	606R		—	DW4850	5012, 5015	RB606ST, RB658, RC606ST
	6	9	229	956R		RPRW8, RDN9V, RSN9V, RHN96, RW96	DW4803, DW4803B, DW4848	5016, 5036	RB93506, RB95006, RC905, RC906
	6	12	305	156R		RHN126, RW126	DW4804, DW4804B, DW4849	5017, 5037	RB123506, RB125006, RB125058ST, RB125058, RC1206
	10	6	152	610R		RPRAP6, RAP610	DW4806, DW4806B, DW4845, DW4877	4091, 5090, 5091, 5092	RB610, RB65010, RBMC610, RC610
	10	8	203	810R		RPRAP8, RAP810, RAP910	DW4865B	5093, 5175	RB810, RB8501014, RBMC810
	10/14	6	152	635R					
	10/14	6	152	650R		RD6V, RRD6V, SRD6, RAP6V	DW4864, DW4864B	—	RB61014, RB6501014, RB6501014T
	10/14	8	203	835R				5193	
	10/14	8	203	850R		RD9V, RRD9V, SRD9, RAP9V	DW4865	5193	RB81014, RB8501014
	10/14	12	305	110R		RD12V, RRD12V, SRD12, RFM10V, SHMF10, RAP12V	DW4838	5094, 5194	RB121014, RB12501014, RB12501014ST, RB12501014
	14	3-5/8	92	314RC		—	DW4814	5161, 5162	—
	14	4	102	414R		—	DW4807, DW4807B	5181	RB414, RH414
	14	6	152	614R		RM614	DW4808, DW4808B	5182, 5282, 4182	RB614, RB65014, RBMC614, RH614
	14	8	203	814R		RM914	—	5187, 4187	RB814, RBMC814
	14	9	225	9514R					
	18	3-5/8	92	318RC		RSM418	—	5163	RB318S, RH318S, RH324S
	18	4	102	418R		RS418	DW4810	5183	RB418, RH318, RH418
	18	6	152	618R		RS618, RM618	DW4811, DW4811B, DW4878	5184, 5284, 4184	RB618, RBMC618, RH618
	18	8	203	818R		RM918	DW4921	5188, 4188	RB814, RB818, RBMC818
	18	12	305	118R		RM1218	—	5189, 4189	RB1018, RB1218, RBMC1218
	24	4	102	424R		S518A, S518AF, S518AF-100, S518EF, S518G	DW4812	5185	RB424, RH424
	24	6	152	624R		RM624	DW4815	5186, 5286, 4186	RB624, RBMC624, RH624
	24	8	203	824R		RM924	—	—	—
LENOX *DIAMOND*™	Grit	8	203	800DRDG		RCB8DG	—	1450	—
CARBIDE GRIT	Grit	6	152	600RG		RCB6G	DW4844	1400, 1410, 1420	RTCG4, RTCG6
	Grit	8	203	800RG		RCB9G	DW4843	1430	RTCG8
	Grit	10	254	100RG		—	—	—	RTCT6065
CARBIDE TIPPED	3	8	203	8535RCT		—	—	—	RTCT6065
	6	6	152	6565RCT		—	—	—	RCFP66
	6	6	152	6563RCT		—	—	—	—
FLEAM GROUND	6	6	152	6W6R		—	—	5015	—
	6	9	229	9W6R		—	—	5016	—

LENOX

MASTER-BAND™ BLADES

Maximum Performance for Portable Band Saws



ENHANCED BEAM STRENGTH
Specially treated bands of .023 and .025 thicknesses offer increased blade strength, reducing deflection and twisting of blades during severe cutting conditions

SHATTER RESISTANT
Bi-metal blades bend and resist breaking and extend blade life

LONG LASTING
LENOX *TUFF TOOTH* design reinforces tooth for longer blade life

TPI	LENGTH X WIDTH X THICKNESS IN	LENGTH X WIDTH X THICKNESS MM	EDGE MATERIAL	3-PACK PROD NO	25-PACK PROD NO	APPLICATION
10/14	44-7/8 x 1/2 x .023	1140 x 12.7 x .6	Matrix	8011438EW1014	9403B38EW1014	1/4" & larger, most metals
14	44-7/8 x 1/2 x .023	1140 x 12.7 x .6	Matrix	8011538EW14	9404B38EW14	3/16"– 3/8," most metals
14/18	44-7/8 x 1/2 x .023	1140 x 12.7 x .6	Matrix	8011238EW1418	9407B38EW1418	1/8"– 5/16," most metals
18	44-7/8 x 1/2 x .023	1140 x 12.7 x .6	Matrix	8011638EW18	9405B38EW18	3/32"– 1/4," most metals
24	44-7/8 x 1/2 x .023	1140 x 12.7 x .6	Matrix	8011738EW24	9406B38EW24	up to 1/8," most metals
8/12	44-7/8 x 1/2 x .025	1140 x 12.7 x .6	M42	80143385EW812	9398B385EW812	3/8"– 1/2," metals, including stainless steel
10/14	44-7/8 x 1/2 x .025	1140 x 12.7 x .6	M42	80144385EW1014	9399B385EW1014	1/4" & larger, metals, including stainless steel
14	44-7/8 x 1/2 x .025	1140 x 12.7 x .6	M42	80145385EW14	9400B385EW14	3/16"– 3/8," metals, including stainless steel
14/18	44-7/8 x 1/2 x .025	1140 x 12.7 x .6	M42	80142385EW1418	9401B385EW1418	1/8"– 5/16," metals, including stainless steel
18	44-7/8 x 1/2 x .025	1140 x 12.7 x .6	M42	82310385EW18	9402B385EW18	3/32"– 1/4," metals, including stainless steel

WOLF-BAND® BLADES

Professional Performance and Exceptional Value



LONG LASTING
High speed steel teeth provide a strong, long lasting cutting edge

SHATTER RESISTANT
Bi-metal blades bend and resist breaking and extend blade life

EXCEPTIONAL VALUE
Professional performance and competitive pricing provide extraordinary cost-per-cut value

TPI	LENGTH X WIDTH X THICKNESS IN	LENGTH X WIDTH X THICKNESS MM	1-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	APPLICATION
10/14	44-7/8 x 1/2 x .020	1140 x 12.7 x .5	3842838PW10141	8009838PW10145	3842338PW1014	1/4" & larger
14	44-7/8 x 1/2 x .020	1140 x 12.7 x .5	3842938PW141	8010738PW145	3842438PW14	3/16"– 3/8"
14/18	44-7/8 x 1/2 x .020	1140 x 12.7 x .5	3843038PW14181	8009938PW14185	3842738PW1418	1/8"– 5/16"
18	44-7/8 x 1/2 x .020	1140 x 12.7 x .5	3843138PW181	8010838PW185	3842538PW18	3/32"– 1/4"
24	44-7/8 x 1/2 x .020	1140 x 12.7 x .5	3843238PW241	8010938PW245	3842638PW24	up to 1/8"
			COMPACT PORTABLE BAND SAW BLADES			
10/14	35-3/8 x 1/2 x .020	900 x 13 x .50	1786692	1786673	1786678	1/4" (6mm) & larger
14	35-3/8 x 1/2 x .020	900 x 13 x .50	1786693	1786674	1786679	3/16" (5mm)– 3/8" (10mm)
18	35-3/8 x 1/2 x .020	900 x 13 x .50	1786695	1786675	1786680	3/32" (2mm)– 1/4" (6mm)
24	35-3/8 x 1/2 x .020	900 x 13 x .50	1786660	1786676	1786761	up to 1/8" (3,2mm)



JIG SAW BLADES

Bi-metal.....28
High Carbon Steel & LENOX *DIAMOND*™ Grit 29
Carbide Grit, Jig Saw Blade Sets &
Air Saw Blades 30
Metal Cutting Circular Saw Blades.....31

BI-METAL JIG SAW BLADES

Ideal for Woodworking and Metal Cutting

PRECISION CUTTING
Super sharp to cut fast without deflection

SMOOTH FINISH
Ground to precision sharpness for straight cuts and a smooth finish

IDEAL FOR WOODWORKING
Designed for optimal performance in wood cutting, including hardwoods

SHATTER RESISTANT
Bi-metal technology flexes and resists breaking and extends blade life



	TPI	LENGTH IN	LENGTH MM	T-SHANK	PROCESS	2-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	APPLICATION	COMPETITIVE CROSS REFERENCE BOSCH®
WOOD CUTTING	6	4	102		Milled	20305BT406S	—	20812B406S	Fast, rough cut	T144DF
	6	4	102		Ground	20315BT456S	20850F456S	20781B456S	Very fast, clean cut	
	6	6	102		Milled	20309BT686S			Fast cut	
	10	4	102		Milled	20306BT410S	20851F410S	20813B410S	Fast, nail-embedded wood	T127DF
	10	4	102		Ground	20313BT450S	20842F450S	20814B450S	Clean, smooth cut	T101BF
	10D	4	102		Ground	20314BT450SR	20843F450SR	20782B450SR	Down cut	T101BRF
	20	3-1/4	82.5		Ground	20311BT320SC	—	—	Scroll cut, laminates	T101AOF
METAL CUTTING	14	3-5/8	92.1		Milled	20301BT314S	20832F314S	20815B314S	Thick metal	T188BF/T118B
	18	3-5/8	92.1		Milled	20302BT318S	20834F318S	20816B318S	Medium metal	T118EF
	18	5-1/4	133.4		Milled	20308BT518S	20854F518S	—	Medium metal	T318B
	24	3-5/8	92.1		Milled	20303BT324S	20835F324S	20817B324S	Thin metal	T118A/T118AF
	32	3-5/8	92.1		Milled	20803BT332S	—	—	Very thin metal	T118G

	TPI	LENGTH IN	LENGTH MM	U-SHANK	PROCESS	2-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	APPLICATION	COMPETITIVE CROSS REFERENCE BOSCH®
WOOD CUTTING	6	4	102		Milled	20329BT486J	20652F486J	—	Fast, rough cut	U111DF
	6	4	102		Ground	20337BT456J	—	20784B456J	Very fast, clean cut	U101DF
	6	6	102		Milled	20331BT686J	—	—	Fast cut	—
	10	4	102		Milled	20328BT480J	20654F480J	—	Fast, nail-embedded wood	—
	10	4	102		Ground	20335BT450J	20648F450J	20702B450J	Clean, smooth cut	U101BF
	10D	4	102		Ground	20336BT450JR	—	20791B450JR	Down cut	—
	20	2-3/4	69.9		Ground	20333BT320JC	—	—	Scroll cut, laminates	U1AOF
METAL CUTTING	14	3-5/8	92.1		Milled	20321BT314J	20641F314J	20705B314J	Thick metal	U118B/U118BF
	18	3-5/8	92.1		Milled	20322BT318J	20643F318J	20706B318J	Medium metal	U118E/U118EF
	18	5-1/4	133.4		Milled	20330BT518J	—	—	Medium metal	—
	24	3-5/8	92.1		Milled	20323BT324J	20644F324J	20707B324J	Thin metal	U118A/U118AF
	32	3-5/8	92.1		Milled	20609BT332J	—	—	Very thin metal	U118G/U118GF

BOSCH *is a registered trademark of Robert Bosch Tool Corporation*

HIGH CARBON STEEL JIG SAW BLADES

Ideal for Woodworking

PRECISION CUTTING
Super sharp to cut fast without deflection

SMOOTH FINISH
Ground to precision sharpness for straight cuts and a smooth finish

IDEAL FOR WOODWORKING
Designed for optimal performance in wood cutting, including hardwoods



TPI	LENGTH IN	LENGTH MM	T-SHANK	PROCESS	2-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	APPLICATION	COMPETITIVE CROSS REFERENCE BOSCH®
6	4	102		Milled	20750CTS406S	20298CFS406S	—	Fast, rough cut	T111C
6	4	102		Ground	20751CT456S	20297CF456S	20292BC456S	Very fast, clean	T101D
6	3-5/8	92.1		Ground	20312CT416SC	—	—	Scroll cut	T244D
10	4	102		Ground	20752CT450S	20296CF450S	20291BC450S	Clean, smooth cut	T101B
10D	4	102		Ground	20753CT450SR	20295CF450SR	20290BC450SR	Down cut	T101BR
20	3-1/4	82.5		Ground	20754CT320SC	20299CF320SC	20294BC320SC	Scroll cut, laminates	T101AO

TPI	LENGTH IN	LENGTH MM	U-SHANK	PROCESS	2-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	APPLICATION	COMPETITIVE CROSS REFERENCE BOSCH®
6	4	102		Milled	20755CTS406J	—	—	Fast, rough cut	U111D
6	4	102		Ground	20756CT456J	—	20794BC456J	Very fast, clean cut	U101D
6	3-5/8	92.1		Ground	20334CT416JC	—	—	Scroll cut	U244D
10	4	102		Ground	20757CT450J	—	20795BC450J	Clean, smooth cut	U101B
10D	4	102		Ground	20758CT450JR	—	—	Down cut	U101BR
20	2-3/4	69.9		Ground	20759CT320JC	—	20797BC320JC	Scroll cut, laminates	U101A0

LENOX *DIAMOND*™ GRIT JIG SAW BLADE



TPI	LENGTH IN	LENGTH MM	T-SHANK	PROCESS	1-PACK PROD NO	APPLICATION
Grit	3-1/2	88.9		Grit	12149	Ceramic Tile, Fiberglass

CARBIDE GRIT JIG SAW BLADES



TPI	LENGTH IN	LENGTH MM	SHAPE	PROCESS	2-PACK PROD NO	5-PACK PROD NO	APPLICATION	COMPETITIVE CROSS REFERENCE BOSCH®
Grit	3-1/2	88.9	T-SHANK	Grit	20300GT300S	20830F300SG	Ceramic Tile	T130RF3
			U-SHANK					
Grit	3-1/2	88.9		Grit	20320GT300J	—	Ceramic Tile	—

BOSCH *is a registered trademark of Robert Bosch Tool Corporation*

JIG SAW BLADE SETS

Bi-Metal Sets



20868U743SA
7 PIECE T-SHANK
BI-METAL SET

456S, 450SR, 450S,
406S, 324S, 318S, 314S

VINYL POUCH



20606U743JA
7 PIECE U-SHANK
BI-METAL SET

456J, 450JR, 450J,
406J, 324J, 318J, 314J

VINYL POUCH

High Carbon Steel Sets



20764C543SA
5 PIECE T-SHANK
MULTI-PURPOSE SET

456S, 450S, 324S,
320SC, 318S

BLISTER PACK



20769C543JA
5 PIECE U-SHANK
MULTI-PURPOSE SET

456J, 450J, 324J,
320JC, 318J

BLISTER PACK

AIR SAW BLADES

Maximum Durability for Pneumatic Machine Cutting

SHATTER RESISTANT
Bi-metal blades bend and resist breaking and extend blade life

LONG LASTING
High speed steel teeth provide a strong, long lasting cutting edge



TPI	LENGTH X WIDTH X THICKNESS IN	LENGTH X WIDTH X THICKNESS MM	5-PACK PROD NO	25-PACK PROD NO	APPLICATION
18	4 x 1/2 x .025	102 x 12.7 x .6	20426418T	20423B418T	For pneumatic machine cutting applications in automotive repair & sheet metal
24	4 x 1/2 x .025	102 x 12.7 x .6	20427424T	20424B424T	
32	4 x 1/2 x .025	102 x 12.7 x .6	20428432T	20425B432T	

METAL CUTTING CIRCULAR SAW BLADES

A Faster Way to Cut Metal™

EXTENDED LIFE
Titanium carbide tipped

Resists material build-up on teeth

CLEAN, COOL CUTS
Less burr than abrasive blades

No need for secondary grinding

Reduced material burning

MODIFIED TRIPLE CHIP GRIND
For added durability

RESHARPENABLE





	DIAMETER		PROD NO	TOOTH COUNT	RPM	ARBOR		APPLICATION
	IN	MM				IN	MM	
STEEL	5-3/8	135	21876ST538030CT	30	3500	—	20	Structurals Thick walled pipe Threaded rod Channel steel Plate Solid steel
	6-3/4	171	21878ST634040CT	40	5800	—	20	
	7	180	21879ST700038CT	38	4300	—	20	
	7-1/4	184	21881ST714040CT	40	5800	5/8	16	
	8	203	21884ST800050CT	50	5800	5/8	16	
	9	230	21885ST900048CT	48	5200	1	25.4	
	10	254	21886ST100052CT	52	5200	5/8	16	
	12	305	21888ST120060CT	60	1500	1	25.4	
	14	355	21891ST140080CT	80	1800	1	25.4	
THIN STEEL	6-1/2	165	21877TS612048CT	48	5800	5/8	16	Sheet metal Thin walled pipe Metal roofing Metal decking
	7	180	21880TS700068CT	68	4300	—	20	
	7-1/4	184	21883TS714068CT	68	5800	5/8	16	
	12	305	21890TS120080CT	80	1500	1	25.4	
	14	355	21893TS140090CT	90	1800	1	25.4	
ALUMINUM	7-1/4	184	21882AL714060CT	60	5800	5/8	16	Aluminum Copper Brass
	10	254	21887AL100080CT	80	5200	5/8	16	
	12	305	21889AL120080CT	80	4000	1	25.4	
	14	355	21892AL140080CT	80	3000	1	25.4	


LENOX
METAL



HOLE SAWS

Bi-metal *SPEED SLOT®* Hole Saws 34, 35

SNAP-BACK™ Arbors & Quick Change Extensions 36

Standard Arbors & Accessories 37

Bi-metal Kits 38, 39

Carbide Tipped & Kits 40

Carbide Grit & Kits 41

LENOX® *DIAMOND™* 42

Carbide Hole Cutters & LENOX *PROTOOL LUBE®* 43

ONE TOOTH® Rough Wood Hole Cutters 44

Carbide Grit Recessed Lighting & Hole Saw Selection Guide 45

Recommended Hole Saw RPM 46

BI-METAL *SPEED SLOT*® HOLE SAWS

Long Lasting, Fast Cutting and Versatile

PLUG REMOVAL AS EASY AS 1-2-3
SPEED SLOT features a staircase design for easy plug removal

UP TO 2X LIFE IN METAL CUTTING
Enhanced tooth geometry, a thin kerf design, and an advanced coating contribute to the efficiency of the cutting process


1


2


3









DIAMETER		1 PER BOX	1 PER BLISTER SEAL	1 PACK ARBORED	PIPE TAP		PIPE ENTRANCE		USE ARBOR	
IN	MM	PROD NO	PROD NO	PROD NO	IN	MM	IN	MM	*SNAP-BACK*™	STANDARD
9/16	14.3	300099L	1787781	1772423	—	—	—	—	5L	1L, 4L or 5L
5/8	15.9	3001010L	1771823	1772424	—	—	—	—	5L	1L, 4L or 5L
11/16	17.5	3001111L	1787773	1772425	—	—	—	—	5L	1L, 4L or 5L
3/4	19.1	3001212L	1771952	1772426	1/2	12.7	3/8	9.5	5L	1L, 4L or 5L
25/32	19.8	3009820MMHS	1771962	1772427	—	—	—	—	5L	1L, 4L or 5L
13/16	20.6	3001313L	1787775	1772428	—	—	—	—	5L	1L, 4L or 5L
7/8	22.2	3001414L	1771953	1772429	3/4	19.1	1/2	12.7	5L	1L, 4L or 5L
15/16	23.8	3001515L	1787776	1772430	—	—	—	—	5L	1L, 4L or 5L
1	25.4	3001616L	1771954	1772481	—	—	—	—	5L	1L, 4L or 5L
1-1/16	27.0	3001717L	1771955	1772482	—	—	—	—	5L	1L, 4L or 5L
1-1/8	28.6	3001818L	1771959	1772483	1	25.4	3/4	19.1	5L	1L, 4L or 5L
1-3/16	30.2	3001919L	1787777	1772474	—	—	—	—	5L	1L, 4L or 5L
1-1/4	31.8	3002020L	1771960	1772491	—	—	—	—	2L, 6L	2L, 3L or 6L
1-5/16	33.3	3002121L	1787778	1772492	—	—	—	—	2L, 6L	2L, 3L or 6L
1-3/8	34.9	3002222L	1771961	1772727	—	—	1	25.4	2L, 6L	2L, 3L or 6L
1-7/16	36.5	3002323L	1787779	1772728	—	—	—	—	2L, 6L	2L, 3L or 6L
1-1/2	38.1	3002424L	1771963	1772729	1-1/4	31.8	—	—	2L, 6L	2L, 3L, 6L or 7L
1-9/16	39.7	3002525L	1787780	1772730	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
1-5/8	41.3	3002626L	1771964	1772931	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
1-11/16	42.9	3002727L	1787800	1772932	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
1-3/4	44.5	3002828L	1771967	1772933	1-1/2	38.1	1-1/4	31.8	2L, 6L	2L, 3L, 6L or 7L
1-13/16	46.0	3002929L	1787841	1772935	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
1-7/8	47.6	3003030L	1771968	1772778	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
2	50.8	3003232L	1771970	1772779	—	—	1-1/2	38.1	2L, 6L	2L, 3L, 6L or 7L
2-1/16	52.4	3003333L	1787842	1772780	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
2-1/8	54.0	3003434L	1772003	1772951	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
2-1/4	57.2	3003636L	1771983	1772952	2	50.8	—	—	2L, 6L	2L, 3L, 6L or 7L
2-3/8	60.3	3003838L	1771984	1772953	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
2-1/2	63.5	3004040L	1771987	1772954	—	—	2	50.8	2L, 6L	2L, 3L, 6L or 7L
2-9/16	65.1	3004141L	1787843	1772955	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
2-5/8	66.7	3004242L	1771988	1772956	2-1/2	63.5	—	—	2L, 6L	2L, 3L, 6L or 7L
2-11/16	68.3	3004343L	1771989	—	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L













DIAMETER		1 PER BOX	1 PER BLISTER SEAL	1 PACK ARBORED	PIPE TAP		PIPE ENTRANCE		USE ARBOR	
IN	MM	PROD NO	PROD NO	PROD NO	IN	MM	IN	MM	*SNAP-BACK*	STANDARD
2-3/4	69.9	3004444L	1771990	1772961	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
2-7/8	73.0	3004646L	1787844	1772962	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
3	76.2	3004848L	1772021	1772963	—	—	2-1/2	63.5	2L, 6L	2L, 3L, 6L or 7L
3-1/8	79.4	3005050L	1772022	1772964	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
3-1/4	82.6	3005252L	1772023	1772966	3	76.2	—	—	2L, 6L	2L, 3L, 6L or 7L
3-3/8	85.7	3005454L	1787845	1772945	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
3-1/2	88.9	3005656L	1772012	1772946	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
3-5/8	92.1	3005858L	1772013	1772949	—	—	3	76.2	2L, 6L	2L, 3L, 6L or 7L
3-3/4	95.3	3006060L	1787846	1772950	3-1/2	85.7	—	—	2L, 6L	2L, 3L, 6L or 7L
3-7/8	98.4	3006262L	1787847	1773001	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
4	101.6	3006464L	1772014	1773002	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
4-1/8	104.8	3006666L	1772018	1773003	—	—	3-1/2	85.7	2L, 6L	2L, 3L, 6L or 7L
4-1/4	108.0	3006868L	1772019	1773004	4	95.3	—	—	2L, 6L	2L, 3L, 6L or 7L
4-3/8	111.1	3007070L	1787848	1773005	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
4-1/2	114.3	3007272L	1772075	1773006	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
4-5/8	117.5	3007474L	1787850	—	—	—	4	95.3	2L, 6L	2L, 3L, 6L or 7L
4-3/4	120.7	3007676L	1772076	1773008	4-1/2	108.0	—	—	2L, 6L	2L, 3L, 6L or 7L
5	127.0	3008080L	1772077	—	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
5-1/2	139.7	3008888L	1787785	—	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L
6	152.4	3009696L	1772121	—	—	—	—	—	2L, 6L	2L, 3L, 6L or 7L

CONTRACTOR'S HOLE SAW 5 PACKS

VALUE & CONVENIENCE
Unique packaging provides value and convenience for high volume users

PROD NO	IN	MM
10735B14L	7/8	22.2
10736B16L	1	25.4
10737B18L	1-1/8	28.6
10738B20L	1-1/4	31.8
10739B22L	1-3/8	34.9
10740B24L	1-1/2	38.1
10741B28L	1-3/4	44.5
10742B32L	2	50.8



LENOX

SNAP-BACK™ ARBORS

No Tools. No Adaptors. No Screwing Around.

QUICK CHANGE
Faster and easier to engage/disengage hole saw

PREVENTS THREADS FROM STRIPPING
Drives off pins, not threads

NO TOOLS NEEDED
Prevents hole saw from locking on arbor

NO ADAPTOR REQUIRED
Arbor threads directly into all hole saws

EASIER PLUG REMOVAL





PROD NO	DESC	FITS HOLE SAWS	SIZES		THREAD SIZE	SHANK TYPE	SHANK SIZE	
			IN	MM			IN	MM
1779772	2L	20L-96L	1-1/4–6	31.8–152.4	5/8–18	Solid Hex	1/2 & larger	12.7 & larger
1779669	5L	9L-19L	9/16–1-3/16	14–30	1/2–20	Solid Hex	3/8 & larger	9.5 & larger
1779670	6L	20L-96L	1-1/4–6	31.8–152.4	5/8–18	Solid Hex	3/8 & larger	9.5 & larger

Solid Hex









SNAP-BACK QUICK CHANGE EXTENSIONS

DURABILITY AND EXTENDED LIFE
Carbon steel collar and shaft for durability and extended life

ONE-HANDED RELEASE
SNAP-BACK Quick Change mechanism for quick and easy release

BIT HELD SECURELY IN PLACE
Patented jaw design holds bits securely on 6-flatted shanks and ball detent bits



PROD NO	IN	MM	CHUCK SIZE		FITS ARBOR	
			IN	MM	*SNAP-BACK*	STANDARD
1852050	5-1/2	140	7/16	11	2L	1L, 2L, 3L
1852047	12	305	3/8	9.5	5L, 6L	5L, 6L, 7L
1852048	12	305	7/16	11	2L	1L, 2L, 3L
1852049	18	457	7/16	11	2L	1L, 2L, 3L

STANDARD ARBORS & ACCESSORIES

Arbors & Accessories for All Your Drilling Needs

ADDED DURABILITY
Hardened carbon steel for strength

STARTS ON CONTACT
Split point pilot drill for faster penetration and less walking



LENOX 6L Arbor with quick change feature (product no 1779805)

PROD NO	DESC	FITS HOLE SAWS	SIZES IN	SIZES MM	SHANK TYPE	SHANK SIZE IN	SHANK SIZE MM	PRIMARY FEATURE
1779774	1L	9L–19L	9/16–1-3/16	14.3–30.2	Hollow Hex	1/2 & larger	12.7 & larger	Adjustable pilot bit
1779801	2L	20L–96L	1-1/4–6	31.8–152.4	Solid Hex	1/2 & larger	12.7 & larger	Use for enlarging holes
1856058	2L	20L–96L	1-1/4–6	31.8–152.4	Hollow Hex	1/2 & larger	12.7 & larger	Use for enlarging holes, adjustable pilot bit
1779802	3L	20L–96L	1-1/4–6	31.8–152.4	Solid Hex	1/2 & larger	12.7 & larger	Solid shank
1779803	4L	9L–19L	9/16–1-3/16	14.3–30.2	3 Sided	1/4 & larger	6.4 & larger	Adjustable pilot bit, 3 flats on shank
1779804	5L	9L–19L	9/16–1-3/16	14.3–30.2	Hex	3/8 & larger	9.5 & larger	Use for 9A-19A arbored hole saws
1779805	6L	20L–96L	1-1/4–6	31.8–152.4	Hex	3/8 & larger	9.5 & larger	Quick change arbor
1779806	7L	24L–96L	1-1/2–6	31.8–152.4	Hex	3/8 & larger	9.5 & larger	Plug ejection feature

ACCESSORIES

PROD NO	DESCRIPTION	CHUCK SIZE IN	CHUCK SIZE MM	FITS ARBOR *SNAP BACK*	FITS ARBOR SOLID HEX	FITS ARBOR HOLLOW HEX
1779771	4-1/4" Pilot Drill (1 pack)	1/4	6.4	—	1L, 4L	2L
1779841	4-1/4" Pilot Drill (25 pack)	1/4	6.4	—	1L, 4L	2L
1779810	3-1/4" Pilot Drill (1 pack)	1/4	6.4	2L, 5L, 6L	2L, 3L, 5L, 6L, 7L	—
1864904	3-1/4" Pilot Drill (25/pack)	1/4	6.4	2L, 5L, 6L	2L, 3L, 5L, 6L, 7L	—
30297123CT	Carbide Tipped Pilot Drill (1 pack)	1/4	6.4	—	1L, 4L	2L
3029865CTPD	Carbide Tipped Pilot Drill (1pack)	1/4	6.4	2L,5L, 6L	2L, 3L, 5L, 6L, 7L	—
30857AA1	Arbor Adaptor (1 pack)	—	—	5L	1L, 4L, 5L	—
3084818X	18" Extension (1 pack)	1/2 & larger	12.7 & larger	2L	1L, 2L, 3L	2L
3084712 X	12" Extension (1 pack)	1/2 & larger	12.7 & larger	2L	1L, 2L, 3L	2L
3084310X*	10" Extension (1 pack)	3/8 & larger	9.5 & larger	5L, 6L	5L, 6L, 7L	—
3084655X	5-1/2" Extension (1 pack)	1/2 & larger	12.7 & larger	2L	1L, 2L, 3L	2L
2910114	1/4" x 1/4" Set Screw	—	—	2L, 5L, 6L	2L, 3L, 5L, 6L, 7L	2L
29102516	5/16" x 5/16" Set Screw	—	—	—	1L, 4L, Extension	

** Fits arbored hole saws*



BI-METAL HOLE SAW KITS

Convenient Storage for Trade-Specific Uses

DURABLE
Durable construction resists damage caused by drops and tough workplace environments

SECURE
Latches close case tightly and securely. Lockable with standard padlocks

LONG LASTING
Metal latches and metal pin hinges won't break or tear





LARGE KIT
10"h x 14"w

MEDIUM KIT
8"h x 11"w

COMPACT KIT
4-11/16"h x 7-1/2"w

MINI KIT
9"h x 5"w

CONTRACTOR'S KITS



30370400G
5 PIECE KIT

2", 3", 3-3/8", 4-1/8"
SNAP-BACK Arbor: 2L

LARGE KIT



3082012006
17 PIECE KIT

5/8", 3/4", 7/8", 1", 1-1/8", 1-1/4", 1-3/8", 1-1/2", 1-3/4", 2", 2-1/2", 3"
SNAP-BACK Arbor: 2L

Arbor: 1L. Three pilot drills

LARGE KIT



30374500G
9 PIECE KIT

2-1/8", 2-9/16", 3-1/4", 3-3/4", 4-3/4"
SNAP-BACK Arbor: 2L

Three pilot drills

LARGE KIT



3080420006
26 PIECE KIT-*BIG DADDY™*

3/4", 7/8", 1", 1-1/8", 1-3/8", 1-1/2", 1-3/4", 2", 2-1/8", 2-1/4", 2-1/2", 2-11/16", 3", 3-1/4", 3-3/8", 3-5/8", 3-3/4", 4-1/8", 4-1/2", 4-3/4"
SNAP-BACK Arbors: 2L, 5L

Arbor: 1L. Three pilot drills

LARGE KIT



30807700G
9 PIECE KIT

7/8", 1", 1-1/4", 1-3/8", 1-1/2", 1-3/4", 2-1/8"
SNAP-BACK Arbors: 5L, 6L

MEDIUM KIT



1815140
7 PIECE KIT

7/8", 1-1/8", 1-3/8", 1-1/2", 2"
SNAP-BACK Arbors: 2L, 5L

MINI KIT

ELECTRICIAN'S KITS



30856C600L
9 PIECE KIT

7/8", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/2"
SNAP-BACK Arbors: 2L, 5L

One arbor adaptor

MEDIUM KIT



30800600L
10 PIECE KIT

7/8", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/2"
SNAP-BACK Arbors: 2L, 5L

One pilot drill
One arbor adaptor

LARGE KIT



308021200L
17 PIECE KIT

3/4", 7/8", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/2", 2-11/16", 3", 3-5/8", 4-1/8", 4-3/4".
SNAP-BACK Arbors: 2L, 5L

Three pilot drills

LARGE KIT



1815139
8 PIECE KIT

7/8", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/2"
SNAP-BACK Arbors: 2L, 5L

MINI KIT

PLUMBER'S KITS



30860C600P
9 PIECE KIT

3/4", 7/8", 1-1/8", 1-3/8", 2", 2-1/2"
SNAP-BACK Arbors: 2L, 5L

One arbor adaptor

MEDIUM KIT



30808600P
10 PIECE KIT

3/4", 7/8", 1-1/8", 1-1/2", 1-3/4", 2-1/4"
SNAP-BACK Arbors: 2L, 5L

One pilot drill
One arbor adaptor

LARGE KIT



1853786
10 PIECE KIT

2-1/8", 2-1/4", 2-9/16", 2-3/4", 3-5/8", 4", 4-5/8"
SNAP-BACK Arbor: 2L

Two pilot drills

LARGE KIT



308011200P
17 PIECE KIT

3/4", 7/8", 1-1/8", 1-1/2", 1-3/4", 2-1/4", 2-9/16", 3", 3-1/2", 4", 4-1/4", 4-1/2"
SNAP-BACK Arbors: 2L, 5L

Three pilot drills

LARGE KIT



1815195
7 PIECE KIT

1-1/4", 1-3/8", 1-1/2", 2", 2-1/2"
SNAP-BACK Arbors: 2L, 5L

MINI KIT

REFRIGERATION KIT



30830600R
8 PIECE KIT

5/8", 7/8", 1-1/8"
1-3/8", 1-5/8", 2-1/8"
SNAP-BACK Arbors: 5L, 6L

MEDIUM KIT

WELDER'S KIT



14789600W
9 PIECE KIT

3/4", 7/8", 1", 1-1/4",
1-1/2", 2"
SNAP-BACK Arbors: 2L, 5L

One arbor adaptor

MEDIUM KIT

AUTOMOTIVE KIT



30805500A
7 PIECE KIT

3/4", 7/8", 1",
1-1/8", 1-1/4"
Arbor: 5L

One arbor adaptor

COMPACT KIT

CARBIDE TIPPED HOLE SAWS

Designed for Cutting Tile and Stainless Steel

LONG TOOL LIFE
Heat resistant carbide teeth for long life in tile and stainless steel

ADDED DURABILITY
Thick backing plate resists damage and increases life

UNIQUE TOOTH CONFIGURATION
Engineered design provides ability to cut in stainless steel like no other

USE STANDARD ARBOR OR SNAP-BACK™ ARBOR



1 PER PACK	DIAMETER		PIPE TAP		PIPE ENTRANCE		USE ARBOR	
PROD NO	IN	MM	IN	MM	IN	MM	*SNAP-BACK*	STANDARD
3021111CT	11/16	17.5	—	—	—	—	5L	1L ,4L, 5L
3021212CT	3/4	19.1	1/2	12.7	3/8	9.5	5L	1L ,4L, 5L
3021414CT	7/8	22.2	3/4	19.1	1/2	12.7	5L	1L ,4L, 5L
3021616CT	1	25.4	—	—	—	—	5L	1L ,4L, 5L
3021818CT	1-1/8	28.6	1	25.4	3/4	19.1	5L	1L ,4L, 5L
3022020CT	1-1/4	31.8	—	—	—	—	2L	2L, 3L 6L
3022222CT	1-3/8	34.9	—	—	1	25.4	2L	2L, 3L 6L
3022424CT	1-1/2	38.1	1-1/4	31.8	—	—	2L	2L, 3L, 6L, 7L
3022626CT	1-5/8	41.3	—	—	—	—	2L	2L, 3L, 6L, 7L
3022828CT	1-3/4	44.5	1-1/2	38.1	1-1/4	31.8	2L	2L, 3L, 6L, 7L
3023232CT	2	50.8	—	—	1-1/2	38.1	2L	2L, 3L, 6L, 7L
3023434CT	2-1/8	54.0	—	—	—	—	2L	2L, 3L, 6L, 7L
3023636CT	2-1/4	57.2	2	50.8	—	—	2L	2L, 3L, 6L, 7L
3023838CT	2-3/8	60.3	—	—	—	—	2L	2L, 3L, 6L, 7L
3024040CT	2-1/2	63.5	—	—	2	50.8	2L	2L, 3L, 6L, 7L
3024141CT	2-9/16	65.1	—	—	—	—	2L	2L, 3L, 6L, 7L
3024242CT	2-5/8	66.7	2-1/2	63.5	—	—	2L	2L, 3L, 6L, 7L
3024343CT	2-11/16	68.3	—	—	—	—	2L	2L, 3L, 6L, 7L
3024848CT	3	76.2	—	—	2-1/2	63.5	2L	2L, 3L, 6L, 7L
3025252CT	3-1/4	82.6	3	76.2	—	—	2L	2L, 3L, 6L, 7L
3025454CT	3-3/8	85.7	—	—	—	—	2L	2L, 3L, 6L, 7L
3025656CT	3-1/2	88.9	—	—	—	—	2L	2L, 3L, 6L, 7L
3025858CT	3-5/8	92.1	—	—	3	76.2	2L	2L, 3L, 6L, 7L
3026060CT	3-3/4	95.3	3-1/2	88.9	—	—	2L	2L, 3L, 6L, 7L
3026464CT	4	101.6	—	—	—	—	2L	2L, 3L, 6L, 7L
3026666CT	4-1/8	104.8	—	—	3-1/2	88.9	2L	2L, 3L, 6L, 7L
3026868CT	4-1/4	108.0	4	101.6	—	—	2L	2L, 3L, 6L, 7L
3027272CT	4-1/2	114.3	—	—	—	—	2L	2L, 3L, 6L, 7L
3027676CT	4-3/4	120.7	4-1/2	114.3	4	101.6	2L	2L, 3L, 6L, 7L
3028080CT	5	127.0	—	—	—	—	2L	2L, 3L, 6L, 7L
3028888CT	5-1/2	139.7	—	—	—	—	2L	2L, 3L, 6L, 7L
3029696CT	6	152.4	—	—	—	—	2L	2L, 3L, 6L, 7L

Recommended RPM for each Carbide Tipped Hole Saw on page 46
Note: We recommend the use of a carbide tipped pilot drill when cutting ceramic wall tile.
Pilot drill 123CT fits the SNAP-BACK 2L or standard arbors 1L, 2L, 4L or 7L. Pilot drill 65CTPD fits the SNAP-BACK 2L or standard arbors 5L and 6L. See pages 36-37.

PLUMBER'S KIT



30294600CTP
8 PIECE

3/4", 7/8", 1-1/8", 1-1/2", 1-3/4", 2-1/4"
SNAP-BACK Arbor: 2L
Arbor: 1L

MEDIUM KIT

ELECTRICIAN'S KIT



30295600CTL
8 PIECE

7/8", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/2"
SNAP-BACK Arbor: 2L
Arbor: 1L

MEDIUM KIT

CONTRACTOR'S KIT



302901100CTG
15 PIECE

3/4", 7/8", 1", 1-1/8", 1-1/4", 1-3/8", 1-1/2", 1-3/4", 2", 2-9/16", 3"
SNAP-BACK Arbor: 2L
Arbor: 1L
Two pilot drills

LARGE KIT

CARBIDE GRIT HOLE SAWS

Best for Cutting Abrasive Materials

CUTS ABRASIVE MATERIALS
Tungsten carbide grit cuts through fiberglass, ceramic tile, laminates and other abrasive materials

CLEAN CUTTING
Carbide grit edge will not snag or chip when cutting thin materials

USE STANDARD ARBOR OR SNAP-BACK™ ARBOR



1 PER BOX	DIAMETER		PIPE TAP		PIPE ENTRANCE		USE ARBOR	
PROD NO	IN	MM	IN	MM	IN	MM	*SNAP-BACK*	STANDARD
2991212CG	3/4	19.1	1/2	12.7	3/8	9.5		1L, 4L
2999820MMCG	25/32	19.8	—	—	—	—		1L, 4L
2991414CG	7/8	22.2	3/4	19.1	1/2	12.7		1L, 4L
2991616CG	1	25.4	—	—	—	—		1L, 4L
2991818CG	1-1/8	28.6	1	25.4	3/4	19.1		1L, 4L
2992020CG	1-1/4	31.8	—	—	—	—	2L	2L
2992222CG	1-3/8	34.9	—	—	1	25.4	2L	2L
2992424CG	1-1/2	38.1	1-1/4	31.8	—	—	2L	2L, 7L
2992828CG	1-3/4	44.5	1-1/2	38.1	1-1/4	31.8	2L	2L, 7L
2993232CG	2	50.8	—	—	1-1/2	38.1	2L	2L, 7L
2993434CG	2-1/8	54	—	—	—	—	2L	2L, 7L
2993636CG	2-1/4	57.2	2	50.8	—	—	2L	2L, 7L
2993838CG	2-3/8	60.3	—	—	—	—	2L	2L, 7L
2994040CG	2-1/2	63.5	—	—	2	50.8	2L	2L, 7L
2994141CG	2-9/16	65.1	—	—	—	—	2L	2L, 7L
2994848CG	3	76.2	—	—	2-1/2	63.5	2L	2L, 7L
2995252CG	3-1/4	82.6	3	76.2	—	—	2L	2L, 7L
2995858CG	3-5/8	92.1	—	—	3	76.2	2L	2L, 7L
2996464CG	4	101.6	—	—	—	—	2L	2L, 7L
2996666CG	4-1/8	104.8	—	—	3-1/2	88.9	2L	2L, 7L

PLUMBER'S KIT



29984600CGP

9 PIECE

3/4", 7/8", 1-1/8", 1-1/2", 2-1/8", 2-9/16"
SNAP-BACK Arbor: 2L
Arbor: 1L. One arbor adaptor

MEDIUM KIT

CONTRACTOR'S KIT



29985700CGK

10 PIECE

7/8", 1", 1-1/4", 1-3/8", 1-1/2", 1-3/4", 2-1/8"
SNAP-BACK Arbor: 2L
Arbor: 1L. One arbor adaptor

MEDIUM KIT

LENOX *DIAMOND*™ HOLE SAWS

More Holes. Less Time.



ONE PIECE HOLE SAWS

LONG LASTING
Continuous, brazed edge lasts longer in tile and stone

FAST, EASY CUTTING
Low torque, little pressure required

EASIER PLUG REMOVAL
Over-sized slot in hole saw for easy plug removal

1 PER PACK			PIPE TAP		PIPE ENTRANCE	
PROD NO	IN	MM	IN	MM	IN	MM
121063DGDS	3/16	5				
121074DGDS	1/4	6				
121085DGDS	5/16	8				
121096DGDS	3/8	10				
121108DGDS	1/2	13				
1211110DGDS	5/8	16				
1211212DGDS	3/4	19	3/4	13	3/8	10
1211416DGDS	1	25				
1211622DGDS	1-3/8	35			1	25
12158DGDS4A	4 pc kit*					

** Sizes: 3/16", 1/4", 5/16", 3/8"*



Diamond Edge



Easier Plug Removal



No Arbor Needed



1856785
10 PIECE KIT

1/4", 3/4", 7/8", 1-1/8", 1-3/8", 2", 2-1/2"
SNAP-BACK Arbors: 2L, 5L
Hex Wrench

LARGE KIT

STANDARD HOLE SAWS

LONG LASTING
Brazed diamond edge for more holes in tile and stone

DURABLE
Robust design for greater durability in tough applications


FAST CUTTING
Cuts holes in less time than carbide grit or carbide tipped hole saws

EASIER PLUG REMOVAL
Round holes make removing plugs faster and easier

USE STANDARD ARBOR OR SNAP-BACK™ ARBOR



1 PER PACK			PIPE TAP		PIPE ENTRANCE		USE ARBOR	
PROD NO	IN	MM	IN	MM	IN	MM	*SNAP-BACK*	STANDARD
1211314DGHS	7/8	22	3/4	19	1/2	13	5L	1L, 4L, 5L
1225618DGHS	1-1/8	29	1	25	3/4	19	5L	1L, 4L, 5L
1211520DGHS	1-1/4	32					2L, 6L	2L, 3L, 6L
1211722DGHS	1-3/8	35			1	25	2L, 6L	2L, 3L or 6L
1211824DGHS	1-1/2	38	1-1/4	32			2L, 6L	2L, 3L, 6L, 7L
1211932DGHS	2	51			1-1/2	38	2L, 6L	2L, 3L, 6L, 7L
1212040DGHS	2-1/2	64			2	51	2L, 6L	2L, 3L, 6L, 7L



Diamond Edge



Easier Plug Removal

CARBIDE HOLE CUTTERS

Designed Specifically for Sheet Metal Hole Cutting



ACCURATE, BURR-FREE HOLES
Precision ground carbide teeth for fast cutting of clean, round holes

WILL NOT DAMAGE WORK
Over-drill stopper prevents the tool from penetrating beyond the hole

STARTS ON CONTACT
Split point pilot bit for faster penetration and less walking

1 PER BOX	DIAMETER		CONDUIT	USE ARBOR	
PROD NO	IN	MM	SIZE	*SNAP-BACK*	STANDARD
2009212CHC	3/4	19.1	3/8"	5L	5L
2009314CHC	7/8	22.2	1/2"	5L	5L
2009416CHC	1	25.4	—	5L	5L
2009618CHC	1-1/8	28.6	3/4"	5L	5L
20097195CHC	1-7/32	30.9	—	5L	5L
2009820CHC	1-1/4	31.8	—		3L, 6L
2010022CHC	1-3/8	34.9	1"		3L, 6L
2010224CHC	1-1/2	38.1	—		3L, 6L
2010328CHC	1-3/4	44.5	1-1/4"		3L, 6L
2010432CHC	2	50.8	1-1/2"		3L, 6L
2010534CHCt	2-1/8	54.0	—		3L, 6L
2010840CHC	2-1/2	63.5	2"		3L, 6L
2010942CHC	2-5/8	66.7	—		3L, 6L
2011344CHC	2-3/4	69.9	—		3L, 6L
2011448CHC	3	76.2	2-1/2"		3L, 6L

ACCESSORIES

PROD NO	DESCRIPTION
3087935PD	1/4" Split point stubby pilot bit
308803CHCAS	Plug ejection springs
300033L	3L, 1/2" Arbor for 20CHC – 48CHC. Solid hex shank
300055L	5L, 3/8" Arbor for 11CHC – 19.5CHC. Solid hex shank
12203K5LSC	5L *SNAP-BACK* Arbor

ELECTRICIAN'S KITS



30877300CHC
12 PIECE KIT

7/8", 1-1/8", 1-3/8". Arbors: 3L, 5L
1/4" split point pilot bit. Plug ejection springs, 1/8" hex wrench

COMPACT KIT



30878500CHC
15 PIECE KIT

7/8", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/2"
Arbors: 3L, 5L. 1/4" split point pilot bit
Plug ejection springs, 1/8" hex wrench

MEDIUM KIT



LENOX *PROTOOL LUBE*®

Extends Tool Life

SHORTENS CUTTING TIME BY UP TO 50%
Provides smoother, cleaner cutting and dramatically longer tool life


REDUCES HEAT AND FRICTION
Water soluble, so it cleans up with water

Biodegradable and non-toxic

PROD NO	CONTAINER SIZE		CONTAINERS PER CASE
	GALLON	LITER	
68040LNX	6 oz	.17	12
68047	1	3.8	4
68048	5	18.9	—
68050	55	208.2 drum	—

NFPA CODE SPECS

HMIS/WHMIS
HEALTH INDEX – 1
FLAMMABILITY – 0
REACTIVITY – 0
PERSONAL PROTECTION – A



Use this product as it comes from the container—do not mix with water.
MSDS available in hard copy or downloadable from lenoxtools.com

ONE TOOTH® ROUGH WOOD HOLE CUTTER

Drills Faster Than Self-Feed Bits



LONG LASTING
High speed steel tooth provides long tool life

CUTS FAST / LOW TORQUE
Designed to run at high speeds with very little torque

DURABLE WOOD CUTTING TOOL
Cuts wet, frozen, pressure treated and hard wood without binding

EASY PLUG REMOVAL
Patented design allows easy plug removal

CUTS AT AN ANGLE
Unique design provides the ability to cut at an angle

USE STANDARD ARBOR OR SNAP-BACK™ ARBOR
For optimal performance usa a 3/8" Stubby Spade Bit with arbor



1 PER PACK	CUTTER SIZE		CUTTING DEPTH		APPLICATION	USE ARBOR	
PROD NO	IN	MM	IN	MM		*SNAP-BACK*	STANDARD
2542222HC	1-3/8	34.9	2-7/16"	62	1" pipe & lock installation	2L	2L, 3L
2543434HC	2-1/8	54.0	2-7/16"	62	1-1/2" pipe & lock installation	2L	2L, 3L
2543636HC	2-1/4	57.2	2-7/16"	62	1-1/2" pipe & 45˚/90˚ bend couplings	2L	2L, 3L
2544141HC	2-9/16	65.1	2-7/16"	62	2" pipe	2L	2L, 3L
2544444HC	2-3/4	69.9	2-7/16"	62	2" pipe & 45˚/90˚ bend couplings	2L	2L, 3L
2545454HC	3-3/8	85.7	2-7/16"	62	3" duct pipe & bendable duct pipe	2L	2L, 3L
2545656HC	3-5/8	92.1	2-7/16"	62	3" pipe	2L	2L, 3L
2546464HC	4	101.6	2-7/16"	62	3" pipe & coupling & dryer vent	2L	2L, 3L
2546969HC	4-5/16	109.5	2-7/16"	62	4" duct pipe & bendable duct pipe	2L	2L, 3L
2547474HC	4-5/8	117.5	2-7/16"	62	4" pipe	2L	2L, 3L
2548080HC	5	127.0	2-7/16"	62	4" pipe & coupling	2L	2L, 3L
2548787HC	5-1/2	139.7	2-7/16"	62	Toilet flange	2L	2L, 3L
2550000HC	6-1/4	158.8	2-7/16"	62	6" duct pipe	2L	2L, 3L
25310SB38	—	—	—	—	3/8" stubby spade bit	2L	2L, 3L
25312DIAF1	—	—	—	—	Diamond file for re-sharpening		



25476301G
7 PIECE

2-1/8", 2-9/16", 3-5/8"
SNAP-BACK Arbor: 2L, Diamond file
Two 3/8" stubby spade bits

LARGE KIT



25477701G
11 PIECE

2-1/8", 2-1/4", 2-9/16", 2-3/4",
3-5/8", 4", 4-5/8"
SNAP-BACK Arbor: 2L, Diamond file
Two 3/8" stubby spade bits

LARGE KIT

CARBIDE GRIT RECESSED LIGHTING HOLE SAWS

Best for Cutting Abrasive Materials

LONG LIFE
Hard tungsten carbide grit edge for a long life in abrasive materials

FAST, EASY CUTTING
Continuous cutting edge for smooth cutting

LIMITS DUST / DEBRIS
Solid back design collects dust and debris

NEW DESIGN



1 PER BOX	DIAMETER		FOR FIXTURES	USE ARBOR	
PROD NO	IN	MM		*SNAP-BACK*	STANDARD
30861438RL	4-3/8	111	Capri, Marco & Halo, Mini-Juno	2L	2L
12100538RL	5-3/8	137	Capri, Marco & Halo, Mini-Juno, Lightolier & Halo	2L	2L
30862638RL	6-3/8	162	Capri, Halo, Pathway & Thomas	2L	2L
30863658RL	6-5/8	168	Juno, Progress & Pathway	2L	2L
30864678RL	6-7/8	175	Capri, Hubbell,® Lightolier,® Lithonia,® Marco, Prescolite,® Progress	2L	2L

Use 123CT or 4321 Pilot Drill

HALO is a registered trademark of Halo Lighting, JUNO is a registered trademark of Juno Lighting Inc., LITHONIA is a registered trademark of Lithonia, Inc., LIGHTOLIER is a registered trademark of Lightolier, Inc., and PRESCOLITE is a registered trademark of Prescolite, Inc.

HOLE SAW SELECTION GUIDE

	WOOD	NAIL-EMBEDDED WOOD	NON-FERROUS METAL	PLASTICS & COMPOSITES	METAL	STAINLESS STEEL	DRYWALL/ PLASTER	CAST IRON	CEMENT BOARD	ABRASIVES	TILE	STONE
												
BEST	CARBIDE TIPPED			CARBIDE GRIT	CARBIDE TIPPED			LENOX® *DIAMOND™*				
BETTER	BI-METAL		BI-METAL					CARBIDE TIPPED	CARBIDE GRIT			
GOOD	CARBIDE GRIT	—	CARBIDE GRIT	CARBIDE TIPPED	CARBIDE GRIT			CARBIDE GRIT	BI-METAL	—	CARBIDE TIPPED	—