


2500 Series Electric Baseboard Heaters



DIMENSIONS



All knockouts are 7/8" diameter for 1/2" conduit



- ▶ **DURABLE TEXTURED POWDER COAT FINISH WITH LOW PROFILE DESIGN**
 - NORTHERN WHITE OR NAVAJO WHITE FINISH
- ▶ **HIGH TEMPERATURE SAFETY LIMIT**
 - ADDED PROTECTION IN CASE OF AIRFLOW BLOCKAGE
- ▶ **EASY INSTALLATION**
 - PRE-NOTCHED GUIDE MARKS IN REAR OF CABINET
 - BUILT-IN CABLE CLAMPS FOR FAST WIRING
 - POWER SUPPLY CAN BE CONNECTED AT EITHER END OF BASEBOARD
- ▶ **UL LISTED FOR INSTALLATION ON WALL OR LEVEL FLOOR SURFACE**
- ▶ **APPLICATIONS INCLUDE:**
 - SINGLE FAMILY HOMES
 - APARTMENTS
 - MODULAR OR MOBILE
 - SUPPLEMENTAL HEAT ADDITION
 - REMODELS
 - AND MUCH MORE



SELECTION CHART

LENGTH	NAVAJO WHITE	UPC 0 98319	NORTHERN WHITE	UPC 0 98319	WATTS @ 277V/240V/208V	WATTS @ 240V/208V	WATTS @ 208V	WATTS @ 120V	WEIGHT (LBS)
2	2542W	73002 2	2542NW	72052 8		400/300			5.2
2'6"	25426W	73006 0	25426NW	72055 9		500/376			6.3
3	2543W	73010 7	2543NW	72059 7		750/564			7.5
4	2544W	73014 5	2544NW	72064 1		1000/752			10
5	2545W	73018 3	2545NW	72069 6		1250/940			11.5
6	2546W	73022 0	2546NW	72074 0		1500/1128			14
8	2548W	73025 1	2548NW	72078 8		2000/1504			18.5
8	25408W	72982 8	25408NW	72086 3		2500/1880			18.5
2	2512W	73000 8	2512NW	72050 4				400	5.2
2'6"	25126W	73004 6	25126NW	72053 5				500	6.3
3	2513W	73008 4	2513NW	72057 3				750	7.5
4	2514W	73012 1	2514NW	72062 7				1000	10
5	2515W	73016 9	2515NW	72067 2				1250	11.5
6	2516W	73020 6	2516NW	72072 6				1500	14
2	2502W	73001 5	2502NW	72051 1			400		5.2
2'6"	25026W	73005 3	25026NW	72054 2			500		6.3
3	2503W	73009 1	2503NW	72058 0			750		7.5
4	2504W	73013 8	2504NW	72063 4			1000		10
5	2505W	73017 6	2505NW	72068 9			1250		11.5
6	2506W	73002 1	2506NW	72073 3			1500		14
8	2508W	73024 4	2508NW	72077 1			2000		18.5
8	25008W	72981 1	25008NW	72085 6			2500		18.5
2	2572W	73003 9	2572NW	72088 7	400/300/225				5.2
2'6"	25726W	73007 7	25726NW	72089 4	500/376/282				6.3
3	2573W	73011 4	2573NW	72090 0	750/564/423				7.5
4	2574W	73015 2	2574NW	72091 7	1000/752/564				10
5	2575W	73019 0	2575NW	72092 4	1250/940/705				11.5
6	2576W	73023 7	2576NW	72093 1	1500/1128/846				14
8	2578W	73026 8	2578NW	72094 8	2000/1504/1128				18.5
8	25708W	72983 5	25708NW	72087 0	2500/1880/1410				18.5


Accessories

CATALOG NUMBER	DESCRIPTION	CASE QTY.	CASE WEIGHT (lbs.)
TA-1AW	Baseboard Thermostat, SP 22 Ampere, 40° to 100°F.	36	16
TA-2AW	Baseboard Thermostat, DP 22 Ampere, 40° to 100°F.	36	20
TA-1TPAW	Baseboard Thermostat, SP 22 Ampere, Tamperproof, 40° to 100°F	36	16
TA-2TPAW	Baseboard Thermostat, DP 22 Ampere, Tamperproof, 40° to 100°F	36	20
	Thermostats Rated 2500W @ 208V, 5000W @ 240/277V		
HCA12-15/20W	Heat-Cool Control, 125V 15 and 20 AMP Receptacle.	40	57
HCA24-15/20W	Heat-Cool Control, 250V connected to 20 AMP Max. Circuit	40	57
RA1COMPW	Duplex Receptacle Cover Only (Carton of 10)	1	1
RA-1W	Duplex Receptacle	36	10
1CAW	Inside Corner Allow 2-1/2" for installation	20	11
DSW2W	Double Pole Disconnect Switch Rated 20A @ 120-277V.	1	1
PR24	24 Volt AC, Class 2 Power Relay SPST 30A @ 120-240 VAC, 23A @ 277 VA	1	1
PR120	120 Volt AC, Class 2 Power Relay SPST 30A @ 120-240 VAC, 23A @ 277 VAC	1	1
RSA	12/24 Low Voltage Relay w/Transformer 120V/24V. -25A.	1	2
RSA	20/24 Low Voltage Relay w/Transformer 208V/24V. -25A.	1	2
RSA	24/24 Low Voltage Relay w/Transformer 240V/24V. -25A.	1	2
RSA	27/24 Low Voltage Relay w/Transformer 277V/24V. -25A.	1	2

Filler Sections

CATALOG NUMBER	DESCRIPTION	SHIP WEIGHT (lbs.)
FS12	1 Foot Filler Section	2
FS24	2 Foot Filler Section	4
FS36	3 Foot Filler Section	6
FS48	4 Foot Filler Section	8
FSJ2	2 Inch Joiner Strip	1/2

FEATURES



- ① Element lead wires are stripped and connect at each end of the baseboard
- ② Rounded corners provide contemporary look and eliminate sharp corners
- ③ Large wiring compartment enable fast, easy wiring
- ④ "Chimney-fin" type element moves air at greater velocity and results in less wall streaking
- ⑤ Suspended heating element designed to lower noise of heater when warming up
- ⑥ "Easy-out" knockouts at each end of heater facilitates fast and easy wire entry and exit from wiring compartments.
- ⑦ Back entry cable clamp provides access to wiring compartment from rear for fast wiring
- ⑧ Pre-notched guide marks for fast installation.