



# e-Vision Low Wattage 20-150W

## E-VISION RMH20KBLSM

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

### Product data


General Information		Input Power (Nom)	
ANSI Code	C175	26 W	
Lamp Type	22W Philips Mini MC	Rated Lamp Power	
Number Of Lamps	1 piece/unit	22 W	
Ballast Type	Electronic HID	Wiring	
Base Model	RMH20KBLS	Color Input Terminals	
Suitable For Outdoor Use	Yes	No terminals	
Operating and Electrical		Color Output Terminals	
Input Voltage	120 V	No terminals	
Input Frequency	50 to 60 Hz	Wire Striplength	
Total Harmonic Distortion USA	15 %	0.50 mm	
Crestfactor (Nom)	1.8	Control Wire Gauge	
Ignition Time (Nom)	1200 s	NA	
Ballast Factor (Nom)	1	Wire Length By Color	
Power Factor (Nom)	0.90	All leads = 6"	
Input Current (Max)	0.23 A	Wire Gauge (Nom)	
Input Current (Min)	0.23 A	18AWG mm	
		Wire Type	
		Stranded	
		Remote Wiring Configuration Allowed	
		Yes	
		Tandem Wiring Configuration Allowed	
		No	
		Through Wiring Configuration Allowed	
		No	
		Connector Type	
		No connector	

e-Vision Low Wattage 20-150W

Temperature	
T-Case Maximum (Nom)	90 °C
Mechanical and Housing	
Housing Material	Metal
Housing	K
Housing Dimensions	4.1" x 1.3" x 1.2"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate RoHS Compliant
Hum And Noise Level	A

UL Recognized	No
Product Data	
Order product name	E-VISION RMH20KBLSM
EAN/UPC - Product	781087092026
Order code	913701221502
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913701221502
Net Weight (Piece)	178.000 g

Dimensional drawing



E-VISION RMH20KBLSM

Product	A1	A2	A3	B1	B2	C1
---------	----	----	----	----	----	----

