



Representative Image

Catalog No. THQB1140

Description: THQB 1 POLE 120/240V 10K IC 40 AMP

UPC No 783164012200

Products > Circuit Breakers > Mini Circuit Breakers & Supplementary Protectors > Q-Line

Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications.

Descriptors

| | |
|-------------|-----------------------------------|
| Category | Q-Line Miniature Circuit Breakers |
| GO Schedule | EB |

Specifications

| | |
|---------------------------------|-------------------------|
| Trip Style | Non-Interchangeable |
| Frame Type | Q-Line |
| Amperage | 40 A |
| System Voltage | 120 Vac, 120/240 Vac |
| Poles | 1 |
| Trip Function | LI |
| Continuous Current Rated | Standard |
| 120 Vac Interrupting Rating | 10 KAIC |
| 120/240 Vac Interrupting Rating | 10 KAIC |
| Suitable for Reverse Feed | Yes |
| Wire Range (Cu/Al) | 14-8 kcmil / 12-8 kcmil |
| Product Line | TEY / Q-Line (Bolt-On) |
| Long Time | Fixed |
| Instantaneous | Fixed |
| Protective Relays | No |
| Current Metering | No |
| Special Markings | HACR |
| GSA Compliance | No |

Classifications

| | |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|

Publications

| Title | Publication No. | Publication Type |
|--|-----------------|----------------------------------|
| Q-Line Bolt-On MCCB, 100A Frame 1-, 2-, or 3- Pole, Drawing 1-Page fully dimensioned outline drawing in .pdf format | 455C873-SH1 | Drawings-Outline and Dimensional |

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.