



# Lytecaster® Recessed Downlighting **1004F26RESR**



Ceiling Opening 5 3/8" diameter

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit		Reflector Trims — See Individual Reflector Trim Specification Sheets							
Voltage	Lamp	Open Downlight						Enclosed Diffusers	Wall Washer
		Anodized Reflector	Anodized Cone	Satin Cone	Baffles	Basic White			
1004F26RESR	120V	26W Quad or Triple Tube	1045*	1012*	1008*	1005*	1071*	1021 1024 1078**	1035** 1035WH 1085* 1095* 1096* 1096CD*
			1046*	1012NM*	1008NM*	1005BNM*			
			1046CD*	1013*	1010*	1005NM*			
				1013BK*	1010NM*	1005WH*			
			1013BKNM*		1076*				
			1013CD*		1076WH*				
			1013CDNM*						
			1013NM*						
			1013WH*						

\* Recommend Triple Tube Lamp for Optimal Performance  
 \*\* Use Triple Tube Lamp Only.

## Features

- Housing:** .032" (#20 ga.) UL listed for direct contact with thermal insulation. Allows installation in ceilings up to 2" thick. Can be removed for access to junction box, ballast and ceiling plenum. AirSeal® housing minimizes air leakage to less than 2 CFM at 1.57 PSF (or 75pa), which complies with Model Energy Code (Section 602.3.3) and Washington State Energy Code (Section 502.4) and reduces heat loss and condensation in ceiling.
- Junction Box:** 2 1/2" X 2 1/2" X 3 1/2" (21 cu. in.) .032" (#22 ga.) galvanized steel. UL listed for branch circuit wiring supplying connected luminaires. Integral cable clamps permit attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors.
- Socket Housing:** Trim retaining spring secures trim to any height on housing wall.
- Socket:** (4 Pin, GX24q-3) base, molded thermo-plastic. Pre-wired with #18 AWG leads to junction box.
- Ballast:** Electronic 120V, end of life protected, FCC class "B" consumer limits, class "A" sound rating. Energy Star® qualified.

## Electrical

Input Watts: 28  
 Amps: .40  
 Ballast Factor: .98  
 Power Factor: > 50  
 Max THD %: < 150  
 Min Start Temp: 0°F/ -18°C

## Options & Accessories

**AirSeal® Kit: LAS56R (Optional)**

**Note:** Use only if factory installed tape or knockouts are removed from vertical adjustment slots in housing wall.

## Labels

UL (Type IC Suitable for Damp Locations)

Complies with Air Leakage Requirements stated in the Model Energy Code, California Title 24 and the Washington State Energy Code.

Romex® is a registered trademark of General Cable Industries Inc.

Job Information	Type:
<b>Job Name:</b>	
<b>Cat. No.:</b>	
<b>Lamp(s):</b>	
<b>Notes:</b>	