


**4 IN. OCTAGON DRAWN BOXES & EXTENSION RINGS WITH CONDUIT KO'S****4 in. Octagon Box, 1-1/2" Deep - Drawn with Conduit KO's****A38**

Catalog #: 125

APPLICATIONS

RACO® Octagon Boxes are used in the installation of ceiling or wall lighting fixtures
N/A

PRODUCT FEATURES

Combination screw heads provide for faster installation

UL LISTED

File E195978

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Conduit
Country of Origin: USA

RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.: No
Fixture (Static) Lbs.: 50

CONFIGURATION

Bracket Type: No Bracket
Drawn or Welded: Drawn
Raised Ground: No
Side Knockout(s): (4) 1/2 in.
Bottom Knockouts(s): (5) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 1-1/2 in.
Dimension B: 4 in.

PRODUCT MEASUREMENTS

Depth: 1-1/2 in.
Cubic Inches (cm3): 15.5 (254.0)
Wt. Ea. (Lbs.): 0.484
Product Length (in.): 1.56
Product Width (in.): 4.00
Product Height (in.): 4.00

PACKAGING

Minimum Pack Qty.: 50
Std. Pkg.: 50
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 48.40
Ship Carton Length (in.): 19.00
Ship Carton Width (in.): 9.00
Ship Carton Height (in.): 7.75
Ctn Weight (Lbs.): 24.20
Pallet Qty: 3500
UPC Number: 050169901250
I2of5: 50050169901255