



Color: Black

UPC Code: 07847707373

Country Of Origin: Mexico

MS602-BW

Brand Features

Leviton's line of industrial grade AC Manual Motor Controllers provide safe, reliable control of a variety of motor loads. Typical applications include manual ON/OFF switching control of bottling lines, pumping machines, air compressors and other heavy manufacturing equipment. These Motor Controllers are available for both single-phase and three-phase applications, with a continuous current rating at all-Voltages up to 600V AC and maximum horsepower ratings of 20HP.

Item Description

60 Amp, 600 Volt, Single Phase, Toggle Double-Pole AC Motor Starting Switch, Industrial Grade, Non-Grounding, Back Wired, - Black

Technical Information

AC Horsepower Ratings

HP Rating: 10HP-240V 15HP-480V
20HP-600V

Electrical Specifications

Amperage: 60 Amp

Dielectric Voltage: Withstands 2200V for 1 min.

Endurance: 6,000 cycles inductive motor type load

Grounding: Non-Grounding

Overload UL20 Test: 100 cycles of OL at 4.8 times rated current

Pole: 2

Temperature Rise: 50°C Max at full rated current

Voltage: 600 Volt

Environmental Specifications

Flammability: Rated V-0 per UL94

Operating Temperature: -40C to 60C

Material Specifications

Base Material: Thermoplastic Polyester

Color: Black

Contacts: .046" Thick Silver-Cadmium Oxide

Face Material: Thermoplastic Polyester

Strap Material: Nickel-Plated Brass

Terminal Screws: Zinc-Plated Steel, Triple Combination

Toggle: Thermoplastic Polyester

Yoke: Nickel-Plated Brass

Mechanical Specifications

Product ID: Ratings are permanently marked on device

Terminal Accom.: 10-4 AWG

Terminal ID: T1, T2, T3, L1, L2 & L3 marked on back of device

Termination: Back

Torque Range: 25 inch pounds maximum

Product Features

Actuator Material: Valox

Body Material: Rynite

Color: Black

Device Type: Manual Motor Controller

Standards and Certifications: UL/CSA

Strap Material: Nickel-Plated Brass

Warranty: 10-Year Limited

Standards and Certifications

ANSI: C-73


cUL per CSA C22.2 No. 111: File #E63969

NEMA: WD-1 & WD-6


NOM: NOM-ANCE

UL 60947-4-1: supersedes UL 508

Warranty: 10-Year Limited



Wiring Diagram Double Pole



SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

