


# CONCORD SERIES


The Concord provides indirect illumination featuring perforated metal for a contemporary design of decor.



## Dimensional Data



Pendant Linear End View



Optional joiner for tandem configurations

## Specifications

**Mounting:** Fixture individually pendant mounted or row mounted by means of airplane cable or rods.

**Construction:** Ballast housing and end caps die-formed of 20 gauge steel for maximum strength and uniformity. Perforated basket is attached to the ends for safety and easy top relamping.

**Finish:** All metal parts are thoroughly cleaned and treated to prevent rust and deterioration with a phosphate coating. Surfaces are then electrostatically sprayed with high white enamel with a reflectance of 87%.

**Wiring:** Standard ballast are Universal Voltage (UV).

**Approval:** All units are Underwriter's Laboratories (UL ) approved.

## Ordering Information

<i>Catalog #</i>	<i>Lamp</i>	<i>Length</i>
<b>ELECTRONIC OCTRON T8</b>		
<b>CON140EBO</b>	<b>1-F32T8</b>	<b>4'</b>
<b>CON240EBO</b>	<b>2-F32T8</b>	<b>4'</b>
<b>CON340EBO</b>	<b>3-F32T8</b>	<b>4'</b>
<b>T5 HIGH PERFORMANCE</b>		
<b>CON228T5</b>	<b>2-F28T5</b>	<b>4'</b>
<b>T5 PERFORMANCE HIGH OUTPUT</b>		
<b>CON254HOT5</b>	<b>2-F54T5HO</b>	<b>4'</b>

## Options and Accessories Add Suffix

<b>DIM</b>	Dimming Ballast	<b>FS</b>	External Fuse and Holder
<b>EM</b>	Emergency Ballast (1 lamp)	<b>UV</b>	Univolt
<b>*EM/2</b>	Emergency Ballast (2 lamp)		

•Note: Supply voltage required

Photometrics Photometric Information available upon request.

