

## USE / RHH / RHW



SIZE (AWG OR KCMIL)	NO. STRANDS	INSUL. THICKNESS (INCHES)	APPROX. OUTSIDE DIAMETER (INCHES)	AMPACITY ■			APPROX. WEIGHT 1000 FT. (LBS)
				60°C	75°C	90°C	
12	19	.045	.179	20	20	20	30
10	19	.045	.202	30	30	30	43
8	7	.060	.266	40	50	55	72
6	7	.060	.304	55	65	75	106
4	7	.060	.352	70	85	95	157
3	7	.060	.380	85	100	110	201
2	7	.060	.412	95	115	130	237
1	19	.080	.481	110	130	150	309
1/0	19	.080	.520	125	150	170	382
2/0	19	.080	.564	145	175	195	471
3/0	19	.080	.614	165	200	225	587
4/0	19	.080	.670	195	230	260	729
250	37	.095	.732	215	255	290	861
300	37	.095	.784	240	285	320	1029
350	37	.095	.831	260	310	350	1193
400	37	.095	.875	280	335	380	1354
500	37	.095	.956	320	380	430	1672
600	61	.110	1.086	355	420	475	2012
750	61	.110	1.188	400	475	535	2493
1000	61	.110	1.337	455	545	615	3287

■ Allowable ampacity based on National Electrical Code.