

XHHW



SIZE (AWG OR KCMIL)	NO. STRANDS	INSUL. THICKNESS (MILS)	APPROX. OUTSIDE DIAMETER (MILS)	AMPACITY ■			APPROX. WEIGHT 1000 FT. (LBS)
				60°C	75°C	90°C	
14	7	30	130	15	15	15	18
12	7	30	147	20	20	20	26
10	7	30	171	30	30	30	40
8	7	45	232	40	50	55	66
6	7	45	267	55	65	75	99
4	7	45	314	70	85	95	149
3	7	45	340	85	100	110	185
2	7	45	370	95	115	130	230
1	19	45	434	110	130	150	292
1/0	19	55	473	125	150	170	363
2/0	19	55	517	145	175	195	452
3/0	19	55	567	165	200	225	565
4/0	19	55	623	195	230	260	705
250	37	65	691	215	255	290	835
300	37	65	744	240	285	320	995
350	37	65	794	260	310	350	1155
400	37	65	839	280	335	380	1314
500	37	65	923	320	380	430	1633
600	61	80	1029	355	420	475	1966
700	61	80	1098	385	460	520	2283
750	61	80	1131	400	475	535	2441
1000	61	80	1280	455	545	615	3230

■ Allowable ampacity based on National Electrical Code.

