



GE
Lighting

10104 - GE Cool White Starcoat® T8

F14T8/CW

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	18 mg
Mercury-Picogram per mean lm hr	4137.9
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	7500 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	580 lm
Nominal Initial Lumen per Watt	49
Initial Lumens-nominal	685 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	10104
Description	F14T8/CW
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168101042
Standard Package GTIN	10043168101049
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168101042

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.1 in
Bulb Diameter (DIA) <Min>	0.94 in
Diameter	1.0 in
End of Base Pin to Pin	14.67 in
Face to End of Opposing Pin (B) <Max>	14.5 in
Face to End of Opposing Pin (B) <Min>	14.4 in
Nominal Length	15.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	157.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	14 W

CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jan 6, 2017 11:08:25 AM For additional information, visit www.gelighting.com