



GE  
Lighting

## 46671 - GE Ecolux® Starcoat® T5

### F14W/T5/835/ECO

☞ Passes TCLP, which can lower disposal costs.

## Product Photo



## GENERAL CHARACTERISTICS

Base Description	Miniature Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.5 mg
Mercury-Picogram per mean lm hr	67.2
Rated Life Rapid Start - Hrs	30000 h @ 3 h 36000 h @ 12 h
Starting Temp (MIN) C-degrees	-20 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	30000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G5
Bulb Shape	T5

## PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1240 lm
Nominal Initial Lumen per Watt	96
Initial Lumens-nominal	1350 lm
Color Rendering Index-CRI	85
Color Temperature	3500 K

## PRODUCT INFORMATION

Product Code	46671
Description	F14W/T5/835/ECO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168466714
Standard Package GTIN	10043168466711
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168466714

## DIMENSIONS

Bulb Diameter (DIA) <Max>	0.67 in
Diameter	0.62 in
Face to End of Opposing Pin (B) <Max>	21.89 in
Face to End of Opposing Pin (B) <Min>	21.79 in
Nominal Length	21.6 in

## ELECTRICAL CHARACTERISTICS

Scotopic/Photopic Ratio	1.5
Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	230.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	14 W

## CAUTIONS & WARNINGS

### Warning

Risk of Electric Shock

Turn power off before inspection  
installation or removal.


### Caution

Lamp may shatter and cause injury if broken

Wear safety glasses and gloves when handling lamp.

Do not use excessive force when installing lamp.





Jan 6, 2017 10:48:18 AM For additional information, visit [www.gelighting.com](http://www.gelighting.com)