



Powering Business Worldwide

pe.eaton.com

37MM-Three-Phase Commercial Meter Stack Modules

37MM140R1240

UPC:782114754450

Dimensions:

- **Height:** 52.63 IN
- **Length:** 8.75 IN
- **Width:** 18.25 IN

Weight:133 LB

Notes:Unit is bottom exit only. 208Y/120V, three-phase, four-wire 240/120V, three-phase, four-wire delta (B-phase is high leg).

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 400A
- **Bus Material:** Aluminum
- **Bus Rating:** 1200 A
- **Bypass:** Lever bypass
- **Enclosure:** NEMA 3R
- **Interrupt Rating:** Per installed main breaker rating
- **Number Of Jaws:** Seven-jaws
- **Number Of Sockets:** 1
- **Phase:** Three-phase in, three-phase out
- **Phase Balance:** Factory A-B
- **Secondary Circuit Breaker:** 400A, K-frame included
- **Security:** Ringless
- **Socket Amperage:** 400 A
- **Voltage Rating:** 208Y/120V



Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - 37MM140R1240](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.