



GE
Lighting

14674 - GE Ecolux® Lucalox® High Pressure Sodium ED18

LU250/ECO/NC

- ☞ Passes TCLP, which can lower disposal costs.
- ☞ Non-cycling feature makes locating and replacing end-of-life lamps quick and easy

Product Photo



GENERAL CHARACTERISTICS

Base Description	Mogul Screw
Base Type	Screw-In
Lamp Enclosure Type (LET)	Open or enclosed fixtures
Mercury-Picogram per mean lm hr	4.9
Rated Life Hours-nominal	40000 h
Bulb Finishes and Colors	Clear
Mercury Content EMEA ONLY	5.1
Bulb Material	Hard glass
Product Technology	High Intensity Discharge
Base	E39
Bulb Shape	ED18

PHOTOMETRIC CHARACTERISTICS

Effective Arc Length	2.75 in
Mean Lumens nominal	26100 lm
Nominal Lumens per Watt	116 lm
Initial Lumens-nominal	29000 lm
Color Rendering Index-CRI	30
Color Temperature	2000 K

PRODUCT INFORMATION

Product Code	14674
Description	LU250/ECO/NC
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168146746
Standard Package GTIN	10043168146743
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168146746
Alternative Unit Of Measure	EACH
Standard Package Quantity	12
Ean UPC	043168146746
Standard Package GTIN	00043168146746
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
Sales Unit	Each
UCC	043168146746

DIMENSIONS

Diameter	2.25 in
Light Center Length Millimeter	5.75 in
Nominal Length	9.75 in

ELECTRICAL CHARACTERISTICS

Burn Position	Universal burning position
Hot Restart Time to 90%MAX	5 min
Open Circuit Voltage (RMS lag ballast) (MIN)	198 V
Rated power (Watts)	250 W

CAUTIONS & WARNINGS

WARNING: This lamp can cause serious skin burn and eye inflammation from shortwave ultraviolet radiation if outer envelope of the lamp is broken or punctured, and the arc tube continues to operate. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain types of lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available. Visit the FDA website for more information: <http://www.fda.gov/cdrh/radhealth/products/urburns.html>

Caution

Risk of Burn

- Allow lamp to cool before handling.
- Do not turn on lamp until fully installed.

Lamp may shatter and cause injury if broken

- Dispose of lamp in a closed container.

- Do not use excessive force when installing lamp.
- Do not use lamp if outer glass is scratched or broken.
- Wear safety glasses and gloves when handling lamp.

Warning

- Contains sodium ? chemical burn risk
- Avoid skin contact with broken pieces.

Risk of Electric Shock

- Do not use where directly exposed to water or outdoors without an enclosed fixture.
- Turn power off before inspection installation or removal.

Risk of Fire

- Keep combustible materials away from lamp.
- Use in fixture rated for this product.

Unexpected lamp rupture may cause injury, fire, or property damage

- Do not exceed rated voltage.
- Do not store flammable materials near/below S-rated lamp in open fixture
- Do not turn on lamp until fully installed.
- Do not use lamp if outer glass is scratched or broken.
- Do not use where directly exposed to water or outdoors

