



GE
Lighting

10374 - GE Cool White T12

F36T12/CW/HO

Product Photo



GENERAL CHARACTERISTICS

Base Description	Recessed Double Contact
Base Type	Pin/Plug-In
Mercury Content	60 mg
Mercury-Picogram per mean lm hr	2732.2
Starting Temp (MIN) C-degrees	-29 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	9000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	R17d
Bulb Shape	T12

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2440 lm
Nominal Initial Lumen per Watt	62
Initial Lumens-nominal	2800 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	10374
Description	F36T12/CW/HO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168103749
Standard Package GTIN	10043168103746
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168103749

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.59 in
Bulb Diameter (DIA) <Min>	1.41 in
Diameter	1.5 in
End of Base Pin to Pin	33.72 in
Nominal Length	36.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	195.00 V @ 10 °C
260.00 V @ -29 °C	Cathode Resistance Ratio - Rh/Rc (MIN)
4.250	Cathode Resistance Ratio - Rh/Rc (MAX)
6.500	Rated power (Watts)



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jan 6, 2017 10:46:46 AM For additional information, visit www.gelighting.com