



GE
Lighting

10415 - GE Ecolux® Starcoat® T8

F17T8XLSPX50/ECO

☞ Passes TCLP, which can lower disposal costs.

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.95 mg
Mercury-Picogram per mean lm hr	59.7
Rated Life Instant Start-Hrs	18000 h @ 3 h 24000 h @ 12 h
Rated Life Rapid Start - Hrs	40000 h @ 3 h 45000 h @ 12 h
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	40000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1235 lm
Nominal Initial Lumen per Watt	76
Initial Lumens-nominal	1300 lm
Color Rendering Index-CRI	82
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	10415
Description	F17T8XLSPX50/ECO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168104159
Standard Package GTIN	10043168104156
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168104159

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.1 in
Bulb Diameter (DIA) <Min>	0.94 in
Diameter	1.0 in
End of Base Pin to Pin	23.67 in
Face to End of Opposing Pin (B) <Max>	23.5 in
Face to End of Opposing Pin (B) <Min>	23.4 in
Nominal Length	24.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	210.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	17 W



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jan 6, 2017 10:51:27 AM For additional information, visit www.gelighting.com