



# **DESCRIPTION**

The I-13-EM-B from IOTA Engineering is a UL Listed fluorescent emergency ballast that allows the same fixture to be used for both normal and emergency operation. In the event of a power failure, the I-13-EM-B switches to the emergency mode and operates one of the existing lamps for 90 minutes. The unit contains a battery, charger, and inverter circuit in a single can. The I-13-EM-B can be used with most 7, 9, & 13 watt 2-pin twin tube compact fluorescent lamps, with an initial output of up to 650 lumens for one lamp. The I-13-EM-B features an integral can profile for installation directly within the ballast compartment and is suitable for use in damp locations and enclosed and gasketed fixtures.

# **SPECIFICATIONS**

Input Voltage	(Dual) 120/277V, 60Hz
Input Wattage	3.5 Watts
Lamps Operated	7,9 & 13 Watt Twin Tube 2-PIN with integral starter 9W-13W USA quad 2-PIN with integral starter
Emergency Operation	90 minutes
Initial Illumination	(1) lamp 650 lumens
Operating Temp	0° to 50° C
Battery	24 Hour Recharge 7-10 Year Life Expectancy
Weight	2.5 lbs.
Approval	



# MODEL NO: \_\_\_\_\_\_ TYPE: \_\_\_ PROJECT: \_\_\_\_ COMMENTS:

# INITIAL LUMEN OUTPUT 650 Lumens

# LAMPS OPERATED\*



(1) 7,9, or 13 Watt Twin Tube **2-PIN** with integral starter (1) 9W-13W USA Quad **2-PIN** with integral starter


\*Refer to Lumen Reference Chart for list of compatible lamps


#### **FEATURES**

- Will cold start and operate all specified lamps
- Long life high temperature recyclable Ni-Cad battery
- Galvanized steel case
- Includes test switch and charge indicator accessory kit
- For use with switched or unswitched fixtures
- 5-Year Warranty. See Warranty Page for details.
- Rated for use in damp locations, plenum, and enclosed and gasketed fixtures
- Meets or exceeds all NEC, IBC, and Life Safety Code Emergency Lighting Requirements
- RoHS Compliant
- International Voltage Models available

# **DIMENSIONS**

9.5" x 2.4" x 1.5" (mounting center 9.0")







# I-13-EM-B

FLUORESCENT EMERGENCY BALLAST FOR 2-PIN LAMPS

# **OPTIONS**

# **TEST KIT CONFIGURATION**

■ TWO-PIECE TEST SWITCH AND CHARGE INDICATOR

# **MOUNTING CONFIGURATION**

EM-B

# **VOLTAGE RATINGS**

- O 120/277V 60HZ (STANDARD)
- O 220V 50HZ
- O 240V 60HZ
- O 120V 50HZ

# **INITIAL LUMEN RATINGS**

LAMP	1 LAMP
7W PL CF 2-pin	350
9W PL CF 2-pin	500
13W PL CF 2-pin	650

# **REMOTE MOUNTING**

When battery packs are remote mounted, consult Customer Service for the maximum allowable distance between the battery pack and lamp(s).