

09 02 240 Lineman's Pliers

American style



- Technical details
- Description
- Applications
- Videos

	No.	09 02 240
	EAN	4003773065005
	Pliers	black atramentized
	Head	polished
	Handles	with multi-component grips
	medium hard wire	4,6 Ø mm
	hard wire	3,0 Ø mm
	Length	240 mm
	Net weight	470 g

- high transmission ratio for easy cutting
- requires 50 % less effort compared with conventional combination pliers thanks to optimised transmission ratio
- solid construction for heaviest strain; universally applicable
- ergonomically optimised handle shape for firm contact to the hand and fatigue reducing operation
- particularly effective cross-hatched knurled gripping zone in the jaws - for strong gripping and pulling
- additional gripping zone below the joint for powerful leverage and pressing performance
- with cutting edges for soft and hard wire
- cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Vanadium electric steel; forged, oil-hardened






Long cutting edges for cutting flat cables



Cross-hatched, knurled gripping zone for firm gripping and pulling, e. g. for fence construction



09 11/12 240: universal mandrel crimping area below the joint



09 11/12 240: fish tape puller in the joint gap





Long cutting edges for cutting flat cables

KNIPEX Lineman's Pliers



technical change and errors excepted