



GE  
Lighting

10560 - GE Daylight T12

F42T12/D/HO

Product Photo



### GENERAL CHARACTERISTICS

Base Description	Recessed Double Contact
Base Type	Pin/Plug-In
Mercury Content	60 mg
Mercury-Picogram per mean lm hr	2645.5
Starting Temp (MIN) C-degrees	-29 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	9000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	R17d
Bulb Shape	T12

### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2520 lm
Nominal Initial Lumen per Watt	53
Initial Lumens-nominal	2900 lm
Color Rendering Index-CRI	74
Color Temperature	6500 K

### PRODUCT INFORMATION

Product Code	10560
Description	F42T12/D/HO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168105606
Standard Package GTIN	10043168105603
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168105606

### DIMENSIONS

Bulb Diameter (DIA) <Max>	1.59 in
Bulb Diameter (DIA) <Min>	1.41 in
Diameter	1.5 in
Nominal Length	42.0 in

### ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	55 W



### CAUTIONS & WARNINGS

#### Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

#### Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jan 6, 2017 10:48:16 AM For additional information, visit [www.gelighting.com](http://www.gelighting.com)