



GE
Lighting

10720 - GE Cool White T6

F42T6/CW

GENERAL CHARACTERISTICS

Base Description	Single Pin
Base Type	Pin/Plug-In
Mercury Content	60 mg
Mercury-Picogram per mean lm hr	5063.3
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	7500 h
Primary Application	Speciality
Product Technology	Linear Fluorescent
Base	Fa8
Bulb Shape	T6

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1580 lm
Nominal Initial Lumen per Watt	70
Initial Lumens-nominal	1750 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	10720
Description	F42T6/CW
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168107204
Standard Package GTIN	10043168107201
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168107204
Alternative Unit Of Measure	EACH
Standard Package Quantity	24
Ean UPC	043168107204
Standard Package GTIN	00043168107204
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
Sales Unit	Each
UCC	043168107204

DIMENSIONS

Bulb Diameter (DIA) <Max>	0.81 in
Bulb Diameter (DIA) <Min>	0.69 in
Diameter	0.75 in
End of Base Pin to Pin	9.74 in
Face to End of Opposing Pin (B) <Max>	39.65 in
Face to End of Opposing Pin (B) <Min>	39.42 in
Nominal Length	42.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (instant start) Min @ Temperature	405.00 V @ 10 °C
Open Circuit Voltage (rapid start) Min @ Temperature	405.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	25 W

CAUTIONS & WARNINGS

Caution

Lamp may shatter and cause injury if broken


Wear safety glasses and gloves when handling lamp.

Do not use excessive force when installing lamp.

Warning

Risk of Electric Shock

Turn power off before inspection
installation or removal.



Jan 6, 2017 10:48:29 AM For additional information, visit www.gelighting.com