



Dependable Power for Any Application

hubbell-acmeelectric.com

www.hubbell.com

480Δ - 240Δ/120  
480Δ Primary Volts - 240Δ/120 Secondary Volts - 3Ø  
Dry Type Distribution Transformer - Three Phase

1018



Catalog #: T2A533281S

#### PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

#### BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

#### UL STANDARD

UL 506

#### CSA STANDARD

C22.2 No. 47

#### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

#### GENERAL PRODUCT INFORMATION

kVA:	3.00
Primary Voltage:	480Δ
Secondary Voltage:	240Δ/120
Frequency:	60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5.0%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	10.38 (26.4)
Width (In./cm):	12.37 (31.4)
Depth (In./cm):	7.47 (19.0)

#### CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.75-1.25 (1.9-3.2)

Wiring Diagram: 25

PACKAGING

Ship Weight (Lbs/Kg): 75 (34.0)

COMPLIANCES

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No. 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)