


## M8300-HI



Color:



Ivory

UPC Code: 07847745621

Country Of Origin: Mexico

\*Eligible for ARRA funded projects > \$7,443,000

NEMA:  
5-20R



## M8300-HI

### Brand Features

The Lev-Lok® Modular Wiring Device System is engineered for fast and easy installation. These devices employ a simple twist and lock wiring module that ensures a safe, reliable connection while at the same time providing for extremely fast and easy installation. Lev-Lok brand wiring devices address the reliability and performance concerns of specification engineers without sacrificing the contractor's need for fast, easy installation. Available in extra heavy duty hospital and industrial grades, and heavy duty commercial grade platforms.

### Item Description

20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Narrow Body Duplex Receptacle, Straight Blade, Hospital Grade, Self Grounding, Modular Terminals, Steel Strap, Lev-Lok - IVORY

### Mating Lev-Lok Wiring Module Required for Use

### Technical Information

#### AC Horsepower Ratings

**Horsepower Rating:** 1 HP

#### Electrical Specifications

**Dielectric Voltage:** Withstands 2000V per UL498

**Grounding:** Self Grounding

**Temperature Rise:** Max 30C after 250 cycles OL at 200 percent rated current

**Maximum Working Voltage:** 125V as rated

**Voltage:** 125 Volt

**Current Interrupting:** Certified for current interrupting at full rated current

**Amperage:** 20 Amp

**Wire:** 3

**Pole:** 2

#### Environmental Specifications

**Operating Temperature:** -40C to 60C

**Flammability:** Rated V-2 per UL94

#### Material Specifications

**Mounting Strap:** Galvanized Steel with Riveted Ground Contacts

**Ground Clips:** Brass

**Mounting Screws:** Triple Combination Head, Steel

**Cover Material:** Nylon

**Line Contacts:** 0.040" Thick Solid Brass

**Locking Pins:** Solid Brass

**Bushing:** Solid Brass

**Base Material:** Nylon

#### Mechanical Specifications

**Product ID:** Ratings are permanently marked on device

**Termination:** Modular Terminals

#### Product Features

**Color:** Ivory

**NEMA:** 5-20R

#### Standards and Certifications


**cULus:** Listed

**Warranty:** 10 Year Limited

**NOM Certified:** 057


**ANSI:** C-73

**NEMA:** WD-1 & WD-6



Standard

### Wiring Diagram



5-20R

### SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)



*\*Leviton is the smart choice, providing the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial buildings. Leveraging more than a century of experience, Leviton helps customers create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, and lighting energy management systems. From switches and receptacles, to daylight harvesting controls, networking systems, and equipment for charging electric vehicles, Leviton solutions help customers achieve savings in energy, time and cost, all while enhancing safety.*