



GE  
Lighting

13766 - GE Cool White T12

F84T12CW/HO 15PK

### Product Photo



### GENERAL CHARACTERISTICS

Base Description	Recessed Double Contact
Base Type	Pin/Plug-In
Mercury Content	90 mg
Mercury-Picogram per mean lm hr	1119.4
Starting Temp (MIN) C-degrees	-29 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	12000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	R17d
Bulb Shape	T12

### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	6700 lm
Nominal Initial Lumen per Watt	77
Initial Lumens-nominal	7700 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

### PRODUCT INFORMATION

Product Code	13766
Description	F84T12CW/HO 15PK
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168137669
Standard Package GTIN	10043168137666
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168137669

### DIMENSIONS

Bulb Diameter (DIA) <Max>	1.59 in
Bulb Diameter (DIA) <Min>	1.41 in
Diameter	1.5 in
End of Base Pin to Pin	81.72 in
Nominal Length	84.0 in

### ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	430.00 V @ 10 °C
455.00 V @ -29 °C	Cathode Resistance Ratio - Rh/Rc (MIN)
4.250	Cathode Resistance Ratio - Rh/Rc (MAX)
6.500	Rated power (Watts)



### CAUTIONS & WARNINGS

#### Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

#### Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jan 6, 2017 10:53:23 AM For additional information, visit [www.gelighting.com](http://www.gelighting.com)