


Grounding - Zinc

Images



[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 1.54
Dimension B in Inches: 2.47
Dimension C in Inches: 0.73
Dimension D in Inches: 1.34
Dimension E in Inches: 2.08

Application

Used in situations where wires have already been pulled through conduit or EMT fittings, and an insulated Grounding bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed to UL514B and UL467 specifications. Patented

Product Information

Material: Zinc Alloy
Finish: Ball Burnished, Mirror Smooth,
Grounding lug: Tin Electro-plate

Certifications & Codes:

Federal Specification Number: A-A-50553
NEMA Standard: FB-1
UL File Number: E20412
UL Standard: UL514B,UL467
UNSPSC: 39121312
Patent Number: 7,182,611; 6,840,782;
8,419,449

Catalog ID: SGB-384CL

UPC Number: 78174790384

Description: Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 1-1/4 Inch, 14-1/0 Lug

Application: Used in situations where wires have already been pulled through conduit or EMT fittings, and an insulated Grounding bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed to UL514B and UL467 specifications. Patented

Trade Size: 1-1/4"

Std Pkg Qty: 200

Unit Qty: 20