

PORTABLE CORD

Type SJE00W/SJTO0W
105C -300 Volt



CONSTRUCTION	
Conductor	- Fully annealed Stranded Bare copper per ASTM B-174
Insulation	- Thermoplastic Elastomer
Jacket	- Thermoplastic Elastomer, black, white, or yellow - Add -02 to the part number for a white jacket - Add -08 to the part number for a yellow jacket - Temperature range: -50C to 105C

COLOR CODE CHART	
Cond. #	Color
1	Black
2	White
3	Green
4	Red

Applications:

- Indoor applications for:
- Portable power tools
- Industrial and consumer lighting fixtures
- Office equipment power supplies
- Construction site power
- Industrial floor care equipment

Features:

- Lightweight
- Oil-resistant jacket
- Non-marking
- Very good flexibility
- Excellent molding characteristics
- Water-resistant jacket, insulation, and fillers
- UL Listed and c(UL) Listed for Indoor or Outdoor Use

Standards:

- UL and c(UL) Flexible Cord
- RoHS Compliant

Part #	AWG	Conductors	Stranding	Insulation Thickness	Nom. O.D.	Lbs./M'
BEJ1802	18	2	16/30	.030"	.293"	45
BEJ1803	18	3	16/30	.030"	.310"	50
BEJ1804	18	4	16/30	.030"	.340"	75
BEJ1602	16	2	26/30	.030"	.319"	55
BEJ1603	16	3	26/30	.030"	.338"	70
BEJ1604	16	4	26/30	.030"	.372"	85
BEJ1402	14	2	41/30	.030"	.351"	70
BEJ1403	14	3	41/30	.030"	.372"	85
BEJ1404	14	4	41/30	.030"	.409"	100
BEJ1202	12	2	65/30	.030"	.419"	90
BEJ1203	12	3	65/30	.030"	.443"	115
BEJ1204	12	4	65/30	.030"	.486"	145

Note: The information in this specification sheet is approximate and subject to standard industry and manufacturer tolerances. Please verify specific requirements with your Omni Cable account manager.