



Representative Image

Catalog No. THQL2150GF1

Description: SOURCED C/B & INSTRUCTIONS

UPC No 783164108538

Products > Circuit Breakers > Residential Circuit Breakers > Feeder Plug-in Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications.

Descriptors

Category	Feeder Plug-in Circuit Breakers
GO Schedule	R6

Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	50 A
System Voltage	120 Vac, 120/240 Vac
Poles	2
Trip Function	LIG
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Product Line	Q-Line (Plug-In)
Long Time	Fixed
Instantaneous	Fixed
Ground Fault	Yes
Protective Relays	No
Current Metering	No
GSA Compliance	No

Classifications

UL File #	E51075
-----------	--------

Publications

Title	Publication No.	Publication Type
Q-Line MCCB, 100A Frame 2- Pole with Ground Fault Protection, Drawing 1-Page, Fully dimensioned outline drawing in .pdf format	139C4446-SH3	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.