



GE
Lighting

**16948 - GE Blax® T6 - Facilities. Retail Display. Hospitality. Office.
Restaurant. Warehouse**
F27BXSPX35RS10PK

GENERAL CHARACTERISTICS

| | |
|---------------------------------|--|
| Base Type | Pin/Plug-In |
| Mercury Content | 4 mg |
| Rated Life Hours-nominal | 12000 h |
| Starting Temp (MIN) C-degrees | 10 °C |
| Base Description | 4-Pin |
| Mercury-Picogram per mean lm hr | 205.8 |
| Primary Application | Facilities Retail Display Hospitality Office Restaurant Warehouse |
| Product Technology | Compact Fluorescent |
| Base | 2G11 |
| Bulb Shape | T6 |

PHOTOMETRIC CHARACTERISTICS

| | |
|--------------------------------|---------|
| Mean Lumens nominal | 1620 lm |
| Nominal Initial Lumen per Watt | 67 |
| Initial Lumens-nominal | 1800 lm |
| Color Rendering Index-CRI | 82 |
| Color Temperature | 3500 K |

PRODUCT INFORMATION

| | |
|----------------------------------|------------------|
| Product Code | 16948 |
| Description | F27BXSPX35RS10PK |
| Alternative Unit Of Measure | PACK |
| Standard Package Quantity | |
| Ean UPC | 043168169486 |
| Standard Package GTIN | 30043168169487 |
| No Of Items Per Sales Unit | |
| No Of Items Per Standard Package | |
| Sales Unit | Inner Pack |
| UCC | 043168169486 |
| Alternative Unit Of Measure | CASE |
| Standard Package Quantity | |
| Ean UPC | 043168169486 |
| Standard Package GTIN | 10043168169483 |
| No Of Items Per Sales Unit | |
| No Of Items Per Standard Package | |
| Sales Unit | Case |
| UCC | 043168169486 |

DIMENSIONS

| | |
|-----------------------------|---------|
| Nominal Length | 12.8 in |
| Bulb Max Overall Length-MOL | 12.8 in |

ELECTRICAL CHARACTERISTICS

| | |
|-------------------------------|-------|
| Equivalent Incandescent Watts | 100 W |
| Rated power (Watts) | 27 W |

CAUTIONS & WARNINGS


Caution

Lamp may shatter and cause injury if broken

Remove and install by grasping only plastic portion of the lamp.

NOTES

4-Pin lamp minimum starting temperature is a function of the ballast. Most ballasts are rated with a minimum starting temperature of 50 degrees F (10 C). Ballasts are also available that provide reliable starting to 0 degrees F (-18C) and -20 F (-29C).



Jan 6, 2017 10:52:18 AM For additional information, visit www.gelighting.com