



GE
Lighting

16952 - GE Blax® T6 - Facilities. Retail Display. Hospitality. Office.
Restaurant. Warehouse

F39BXSPX41RS10PK

Product Photo



GENERAL CHARACTERISTICS

Base Type	Pin/Plug-In
Mercury Content	4 mg
Rated Life Hours-nominal	12000 h
Starting Temp (MIN) C-degrees	10 °C
Base Description	4-Pin
Mercury-Picogram per mean lm hr	132.8
Primary Application	Facilities Retail Display Hospitality Office Restaurant Warehouse
Product Technology	Compact Fluorescent
Base	2G11
Bulb Shape	T6

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2510 lm
Nominal Initial Lumen per Watt	73
Initial Lumens-nominal	2850 lm
Color Rendering Index-CRI	82
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	16952
Description	F39BXSPX41RS10PK
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168169523
Standard Package GTIN	10043168169520
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168169523
Alternative Unit Of Measure	PACK
Standard Package Quantity	
Ean UPC	043168169523
Standard Package GTIN	30043168169524
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Inner Pack
UCC	043168169523

DIMENSIONS

Nominal Length	16.5 in
Bulb Max Overall Length-MOL	16.5 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	180 W
Rated power (Watts)	39 W

CAUTIONS & WARNINGS

Caution

Lamp may shatter and cause injury if broken

Remove and install by grasping only plastic portion of the lamp.

NOTES

4-Pin lamp minimum starting temperature is a function of the ballast. Most ballasts are rated with a minimum starting temperature of 50 degrees F (10 C). Ballasts are also available that provide reliable starting to 0 degrees F (-18C) and -20 F (-29C).