



GE
Lighting

10064 - GE Warm White Starcoat® T5

F8T5/WW

Product Photo



GENERAL CHARACTERISTICS

Base Description	Miniature Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	6 mg
Mercury-Picogram per mean lm hr	3636.4
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	5000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G5
Bulb Shape	T5

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	330 lm
Nominal Initial Lumen per Watt	51
Initial Lumens-nominal	410 lm
Color Rendering Index-CRI	52
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	10064
Description	F8T5/WW
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168100649
Standard Package GTIN	10043168100646
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168100649

DIMENSIONS

Bulb Diameter (DIA) <Max>	0.63 in
Bulb Diameter (DIA) <Min>	0.53 in
Diameter	0.62 in
Face to End of Opposing Pin (B) <Max>	11.63 in
Face to End of Opposing Pin (B) <Min>	11.53 in
Nominal Length	12.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	140.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	8 W


CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jan 6, 2017 10:53:53 AM For additional information, visit www.gelighting.com