



GE  
Lighting

10349 - GE T8 - Appliance

F30T8/CW/4

## Product Photo



### GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	18 mg
Mercury-Picogram per mean lm hr	2051.3
Rated Life Instant Start-Hrs	7500 h @ 3 h
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	7500 h
Primary Application	Appliance Speciality
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1170 lm
Nominal Initial Lumen per Watt	72
Initial Lumens-nominal	1375 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

### PRODUCT INFORMATION

Product Code	10349
Description	F30T8/CW/4
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168103497
Standard Package GTIN	10043168103494
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168103497

### DIMENSIONS

Bulb Diameter (DIA) <Max>	1.1 in
Bulb Diameter (DIA) <Min>	0.94 in
Diameter	1.0 in
End of Base Pin to Pin	29.67 in
Face to End of Opposing Pin (B) <Max>	29.5 in
Face to End of Opposing Pin (B) <Min>	29.4 in
Nominal Length	30.0 in

### ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	108.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	19 W

### CAUTIONS & WARNINGS

#### Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

#### Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jan 6, 2017 11:00:49 AM For additional information, visit [www.gelighting.com](http://www.gelighting.com)