



GE
Lighting

10485 - GE Mod-U-line® Starcoat® T8

F32T8/SPX35/U/6

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Face to Top of Lamp Max	22.250
Base Type	Pin/Plug-In
Mercury Content	90 mg
Mercury-Picogram per mean lm hr	1711
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	20000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2630 lm
Nominal Initial Lumen per Watt	88
Initial Lumens-nominal	2800 lm
Color Rendering Index-CRI	82
Color Temperature	3500 K

PRODUCT INFORMATION

Product Code	10485
Description	F32T8/SPX35/U/6
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168104852
Standard Package GTIN	10043168104859
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168104852

DIMENSIONS

Diameter	1.0 in
Bulb Diameter in Bend <Max>	1.13 in
Bulb Diameter in Bend <Min>	0.89 in
Bulb Diameter in Legs <Max>	1.1 in
Bulb Diameter in Legs <Min>	0.94 in
Lamplegs Center-Center Length	6.0 in
Nominal Length	22.5 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	315.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	32 W

CAUTIONS & WARNINGS


Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.





Jan 6, 2017 11:06:06 AM For additional information, visit www.gelighting.com