

# Product data sheet

## Characteristics

# QOB3100VH

## QO Mini CB, 100A, 3P, 120/240V, 22kA, Bolt-on Mount

Product availability : Stock - Normally stocked in distribution facility



Price\* : 629.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	100 A
Voltage Rating	120 V AC 120/240 V AC 240 V AC
Mounting Type	Bolt-on
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	22 kA at: 120/240 V AC 22 kA at: 120 V AC 22 kA at: 240 V AC
Number of Panel Spaces	3
Wire Size	AWG 4...AWG 2/0 (copper or aluminium)
Height	3.5 in
Depth	2.91 in
Width	2.25 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901054801
Nbr. of units in pkg.	1
Package weight(Lbs)	1.0900000000000001
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructio	Need no specific recycling operations

## Contractual warranty

Period	18 months
--------	-----------