



PL-T Triple 4-Pin Base

PL-T 42W/830/A/4P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

General Information		LLMF 8000 h Rated		LLMF 12000 h Rated	
Cap-Base	GX24Q-4 [GX24q-4]		84 %		
Life To 50% Failures Preheat (Nom)	0 h				
LSF Preheat 2000 h Rated	99 %				
LSF Preheat 4000 h Rated	98 %				
LSF Preheat 6000 h Rated	97 %				
LSF Preheat 8000 h Rated	90 %				
Light Technical		Operating and Electrical			
Color Code	830 [CCT of 3000K]	Power (Rated) (Nom)	38.0 W		
Initial lumen (Nom)	3200 lm	Lamp Current (Nom)	0.320 A		
Luminous Flux (Rated) (Nom)	3050 lm				
Color Designation	Warm White (WW)	Temperature			
Chromaticity Coordinate X (Nom)	436	Design Temperature (Nom)	28 °C		
Chromaticity Coordinate Y (Nom)	401	Controls and Dimming			
Correlated Color Temperature (Nom)	3000 K	Dimmable	Yes		
Luminous Efficacy (rated) (Min)	80 lm/W	Mechanical and Housing			
Color Rendering Index (Nom)	82	Cap-Base Information	4P		
LLMF 2000 h Rated	92 %	Approval and Application			
LLMF 4000 h Rated	88 %	Energy Efficiency Label (EEL)	B		
LLMF 6000 h Rated	85 %	Mercury (Hg) Content (Nom)	1.4 mg		


PL-T Triple 4-Pin Base

Product Data

Order product name	PL-T 42W/830/A/4P/ALTO
EAN/UPC - Product	046677149017
Order code	149013
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	927911483020
Net Weight (Piece)	83.000 g
ILCOS Code	FSM-42/30/1B-E-GX24q=4

Dimensional drawing



PL-T ALTO 42W/830/4P A

Product	D	A	B	C
PL-T 42W/830/A/4P/ALTO	41 mm	120.7 mm	145.0 mm	160.7 mm

