



GE
Lighting

10490 - GE Blax® T6 - Facilities. Retail Display. Hospitality. Office.
Restaurant. Warehouse

F40/30BX/SPX50RS

Product Photo



GENERAL CHARACTERISTICS

Base Type	Pin/Plug-In
Mercury Content	4 mg
Rated Life Hours-nominal	20000 h
Starting Temp (MIN) C-degrees	10 °C
Base Description	4-Pin
Mercury-Picogram per mean lm hr	74.1
Primary Application	Standard<General Purpose> Facilities Hospitality Office Restaurant Retail Display Warehouse

Product Technology	Compact Fluorescent
Base	2G11
Bulb Shape	T6

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2700 lm
Nominal Initial Lumen per Watt	73
Initial Lumens-nominal	2900 lm
Color Rendering Index-CRI	80
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	10490
Description	F40/30BX/SPX50RS
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168104906
Standard Package GTIN	10043168104903
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168104906

DIMENSIONS

Nominal Length	22.5 in
Bulb Max Overall Length-MOL	22.5 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	180 W
Rated power (Watts)	40 W

CAUTIONS & WARNINGS

Caution

Lamp may shatter and cause injury if broken

Remove and install by grasping only plastic portion of the lamp.

NOTES

4-Pin lamp minimum starting temperature is a function of the ballast. Most ballasts are rated with a minimum starting temperature of 50 degrees F (10 C). Ballasts are also available that provide reliable starting to 0 degrees F (-18C) and -20 F (-29C).