



Siemens Low Voltage Residential Circuit Breakers Main Breakers - Type QS Breakers are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: QS Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240 V Amperage Rating: 150A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 2P

Number of poles	2
Suitability for operation	Electrical Distribution
Electricity	
Continuous current rated value	150 A
Voltage between phase and Ground (GND) rated value	120 V
Voltage between phase and phase rated value	240 V
Model	
Product brand name	SIEMENS
Type of electrical connection	PLUG-IN
Mechanical Design	
Depth [in]	9 in
Design of the overload release	Thermal Magnetic
Design of the product	QS
Height [in]	3 in
Width [in]	6 in
General product approval	
Standard	UL 489

last modified:

05/28/2019