



GE
Lighting

10742 - GE T10 - Cold Temperature

F48T10/CW

The T10 is designed to be used in cold temperature applications from 10 degrees F to 40 degrees F.

Product Photo



GENERAL CHARACTERISTICS

Base Description	Recessed Double Contact
Base Type	Pin/Plug-In
Mercury Content	90 mg
Mercury-Picogram per mean lm hr	1612.9
Rated Life Instant Start-Hrs	9000 h @ 3 h
Starting Temp (MIN) C-degrees	10 °C
Rated Life Hours-nominal	9000 h
Primary Application	Cold Temperature Speciality
Product Technology	Linear Fluorescent
Base	R17d
Bulb Shape	T10

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	56
Initial Lumens-nominal	6200 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	10742
Description	F48T10/CW
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168107426
Standard Package GTIN	10043168107423
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168107426

DIMENSIONS

Diameter	1.25 in
Nominal Length	48.0 in

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	110 W
---------------------	-------

CAUTIONS & WARNINGS

Caution


- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection
installation or removal.

NOTES

Because Power Groove® and Very High Output lamps are most used in commercial applications, the life rating is based on 12 hrs. per start.



Jan 6, 2017 10:48:53 AM For additional information, visit www.gelighting.com