



### Ordering Information

Catalog No.	Finishes	Mounting	Dimensions
7589	Matte White	All Lytespan	2 3/8" High
7589 BK	Matte Black	Track Systems	2" Wide 1" Deep

### Features

- Housing:** Molded polycarbonate .075" wall thickness; integral matte white finish.
- Movable Brass Contact:** Extends for connection to 2nd circuit in Advent Lytespan Track.
- Expansion Clamp:** Fingertip squeeze-release for quick attachment; thumbscrew lock for rigid mounting.
- Screw Terminals:** Connect onto individual conductors.
- Strain Relief Cap:** Molded thermoplastic. Use with pendant cord.
- Fixture Cord, Stem or Chain:** note: Cord max dia. .340" (not supplied). Stem size: 1/2" O.D., .065" wall, 1/4"-18 thread 1/2" long (not supplied). Chain: 1/4"-18 loop (not supplied).
- 1/4"-18 Knurled Ring.**
- 1/4"-20 Set Screw:** Nylon. Secures fixture cord, stem or chain loop.
- 1/4"-18 Nipple**
- Electrical Contacts:** move in conjunction with lever.
- Max. Wire Ga.:** #18
- Lever:** energizes attachment fitting.
- Polarity Keyway**

### Electrical

Can be used with fixture cords up to a maximum diameter of 0.340"; suitable for 2 conductor and 3 conductor applications. Can also be used with stem or yoke supported fixtures terminating in 1/4" pipe size fittings.

### Finish

All painted finishes baked enamel.

### Labels

UL

### Job Information

### Type:

**Job Name:**

**Cat. No.:**

**Lamp(s):**

**Notes:**

631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710

We reserve the right to change details of design, materials and finish.

www.lightolier.com © 2008 Philips Group • B0508