



GE
Lighting

10805 - GE Cool White T6

F64T6/CW

GENERAL CHARACTERISTICS

Base Description	Single Pin
Base Type	Pin/Plug-In
Mercury Content	90 mg
Mercury-Picogram per mean lm hr	4761.9
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	7500 h
Primary Application	Speciality
Product Technology	Linear Fluorescent
Base	Fa8
Bulb Shape	T6

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2520 lm
Nominal Initial Lumen per Watt	70
Initial Lumens-nominal	2800 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	10805
Description	F64T6/CW
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168108058
Standard Package GTIN	10043168108055
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168108058

DIMENSIONS

Bulb Diameter (DIA) <Max>	0.81 in
Bulb Diameter (DIA) <Min>	0.69 in
Diameter	0.75 in
End of Base Pin to Pin	61.74 in
Face to End of Opposing Pin (B) <Max>	61.65 in
Face to End of Opposing Pin (B) <Min>	61.42 in
Nominal Length	64.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (instant start) Min @ Temperature	540.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	40 W

CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jan 6, 2017 10:52:08 AM For additional information, visit www.gelighting.com