



Philips Forecast
Suspension light

Suspension

F5100/19/NV

Suspension 1-light Pendant in Black finish

One-light Pendant in Black finish. Holder only - shade sold separately.

Create an atmosphere anywhere

- Designed for indoor use

Feel welcome home with light

- UL Listed for Dry locations

Let the light blend naturally into your interior

- A wide variety of bulbs may be used in this fixture

Colors and finishes bring harmony to your home

- Black

PHILIPS

 F O R E C A S T

Suspension light
Suspension

F510019NV

Specifications

Design and finishing

- Material: metal
- Color: matt chrome

Extra feature/accessory incl.

- A la carte

Product dimensions & weight

- Height minimum: 5.0 inch
- Height maximum: 5.0 inch
- Length: 120 inch
- Width: 5.3 inch
- Net weight: 1.764 lb

Technical specifications

- Mains power: 120 V, 60 Hz
- Number of bulbs: 1

- Fitting/cap: E26
- Maximum wattage replacement bulb: 75 W
- IP code: dry

Service

- Warranty: 1 year(s)

Packaging dimensions & weight

- Height: 6.0 inch
- Length: 6.0 inch
- Depth: 6.0 inch
- Weight: 1.874 lb

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Contemporary
- Type: Suspension light

Highlights

Indoor

When decorating your home with light, consider if the area requires general lighting, accent lighting, task lighting, or perhaps all three, to complete the necessary layers of light for comfortable ambience.

Dry

UL Listed for Dry locations

Standard incan lamp

This fixture will accept bulbs in a variety of shapes, sizes, and wattages, including high-efficiency screw-in bulbs such as the Philips LED, EcoVantage, and Twister.

Black

Black color differentiates this cable from others, providing easy identification at a glance.

Issue date 2013-11-27

© 2013 Koninklijke Philips N.V.
All Rights reserved.

Version: 1.0.1

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

12 NC: 9150 028 94501
UPC: 7 42546 04512 0

www.philips.com