
MAGNETIC LATCHING RELAY, 24VAC/24VDC CONTROL

1070B | [Pass & Seymour](#)



FEATURES & BENEFITS

Low Voltage Component, Magnetic Latching Relay, 24VAC/24VDC Control. Reliable field-tested switching circuitry that provide central or local control of lighting loads.



- **Mount** in standard 1/2" KO through noise suppressing nylon ring.
- **Maximum ambient temp:** 140°F (60°).
- **Insulated flame retardant** nylon shell.
- **Prestripped** 5-1/2" (140mm) #22 AWG leads for easy wiring.
- **Split coil design** energizes ON coil to close line contacts, and OFF coil to open contacts.
- **Can be mounted in any position.**
- **Operates** on momentary impulse.
- **Draws** .520 mA.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Type: Magnetic Latching Relay

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: 347V
CSA Standard: Yes
UL Standard: Yes

DIMENSIONS

Diameter (US): 1.176"
Length (US): 3.156"

TECHNICAL INFORMATION

Volts: 24VAC/24VDC

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

